



## Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCF
Product Type	Emergency stop switch disconnecter

## Complementary

Device Composition	Switch Handle
Mounting Support	Handle door Switch door
Mounting Method	By 4 screws handle
Performance Level	High performance
Number of Poles	3P
Contact Type and Composition	3 NO
[Ue] IEC Rated Operational Voltage	690 V AC 50/60 Hz
IEC Rated Operational Power in W	11 KW 500 V AC-23A) 15 KW 690 V AC-23A) 7.5 KW 500 V AC-3) 7.5 KW 690 V AC-3) 1.5 KW 230...240 V AC-3) 5.5 KW 230...240 V AC-23A) 11 KW 400...415 V AC-23A) 7.5 kW 400...415 V AC-3)
[Ie] Rated Operational Current	21.8 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	32 A
[Ithe] Conventional Enclosed Thermal Current	25 A
Making Capacity ( I Rms)	320 A 400 V AC-21A 320 A 400 V AC-22A 320 A 400 V AC-23A
Breaking Capacity	250 A 400 V AC-21A) 250 A 400 V AC-22A) 250 A 400 V AC-23A)
Rated Conditional Short Circuit Current	10 KA 400 V 35 A aM 10 kA 400 V 35 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA 400 V at Ipeak
[Icw] Rated Short Time Withstand Current	384 A 400 V 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV
Suitability for Isolation	Yes
Network Type	DC AC
Intermittent Duty Class	30
Control Type	Rotary handle
Rotary Handle Mounting Style	Direct

Handle Color	Red
Handle Front Plate Color	Yellow
Rotary Handle Padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 Cycles AC-21 30000 cycles DC-1...5
IEC Terminal Connection	Power circuit screw clamp terminals 0.02 in <sup>2</sup> (10 mm <sup>2</sup> ) solid Power circuit screw clamp terminals 0.01 in <sup>2</sup> (6 mm <sup>2</sup> ) flexible - with cable end
Tightening Torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Base Dimension	60 x 60 mm
Height	2.91 in (74 mm)
Width	2.36 in (60 mm)
Product Weight	0.55 lb(US) (0.25 kg)

## Environment

Standards	IEC 60947-3
Product Certifications	UL CSA CCC GL UKCA
Degree of Protection	IP20 conforming to IEC 60529 IP65
Protective Treatment	TC
Mechanical Robustness	Vibrations 10...150 Hz 1 gn IEC 60068-2-6 Shocks 11 ms 30 Gn IEC 60068-2-27
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	Main switch disconnecter

## Ordering and shipping details

Category	21730-V VARIO SWITCH
Discount Schedule	CP1
GTIN	3389110449365
Returnability	Yes
Country of origin	CZ

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	3.35 in (8.500 cm)
Package 1 Length	4.72 in (12.000 cm)
Package 1 Weight	7.72 oz (219.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	12.44 lb(US) (5.642 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	192
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	117.14 lb(US) (53.136 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------