



Main

| | |
|------------------------------|---|
| Range of product | Pumptrol |
| Pressure sensor name | 9013FH |
| Pressure sensor size | 1034.21 kPa |
| Value of setting | Off at 150 psi |
| Electrical circuit type | Power circuit |
| Product specific application | Control small electrically driven air compressors |
| Quantity per set | 1 |
| Type of packing | Individual |

Complementary

| | |
|-------------------------------------|--|
| Pressure sensor type | Electromechanical pressure switch |
| Controlled fluid | Air (-0...70 °C) |
| Adjustable range on rising pressure | 482.63...1034.21 kPa |
| Approximate fixed differential | 206.84 kPa |
| Destruction pressure | 1516.85 kPa |
| Pressure actuator | Diaphragm |
| Pressure switch type of operation | Regulation between 2 thresholds |
| Scale type | Fixed differential |
| Setting | Internal |
| Local display | Without |
| Contacts type and composition | 2 NC, snap action, DPST-DB, Form YY |
| Cable entry number | 2 22.35 mm cable entries with 0.84 in across flats conforming to UL 508 |
| Electrical connection | Screw-clamp terminals, clamping capacity: 10 AWG Screw-clamp terminals, clamping capacity: 5.261 mm ² |
| Fluid connection type | 0.25 inch NPSF internal conforming to UL 508 |
| Short-circuit protection | 20 A cartridge fuse, type gG |
| Materials in contact with fluid | Zinc plated steel or equivalent flange Nitrile (Buna-N) or equivalent rubber diaphragm |
| Material | Polypropylene: cover Noryl thermoplastic resin or equivalent: cover |
| Operating position | Any position |
| Motor power kW | 1.1 KW (1.5 hp) at 115 V AC, 1 phase 1.5 KW (2 hp) at 230 V AC, 1 phase 1.5 KW (2 hp) at 115 V AC, 3 phases 2.2 KW (3 hp) at 230 V AC, 3 phases 0.75 KW (1 hp) at 460 V AC, 3 phases 0.75 kW (1 hp) at 575 V AC, 3 phases |
| Electrical durability | 100000 cycles, operating rate <10 cyc/mn |
| Mechanical durability | 300000 cycles |
| Terminal block type | 4 terminals |
| Maximum operating rate | 10 cyc/mn |
| [Ui] rated insulation voltage | 575 V conforming to UL 508 |
| Net weight | 0.45 kg |
| Repeat accuracy | +/- 3 % |
| Terminals description ISO n°1 | L2-T2 L1-T1 |
| Width | 78.74 mm |

| | |
|----------------------|--|
| Height | 94.23 mm |
| Depth | 95.50 mm |
| Factory modification | Maintained manual cut-out lever (AUTO-OFF) |

Environment

| | |
|---------------------------------------|------------------------------|
| Standards | UL 508 CE |
| Ambient air temperature for operation | -30...70 °C |
| Ambient air temperature for storage | -30...70 °C |
| Protective treatment | None |
| NEMA degree of protection | NEMA 1 conforming to UL 50 |
| IP degree of protection | IP20 conforming to IEC 60529 |
| Product certifications | UL listed[RETURN]CSA |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.9 cm |
| Package 1 Width | 9.7 cm |
| Package 1 Length | 10.4 cm |
| Package 1 Weight | 376.5 g |

Offer Sustainability

| | |
|--|---|
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| For all Reach Rohs enquiries contact us at | sustainability@tesensors.com |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|