

# H362DSWA

Safety switch, heavy duty, fusible, 60A,  
600VAC/VDC, 3 poles, 50hp, NEMA Type 4,  
4X, 5, 304 steel, appleton receptacle



## Main

|                            |   |
|----------------------------|---|
| Product                    | Receptacle Switch   |
| For Use With               | Plug ACP6034BC Appleton Powertite   |
| Disconnect Type            | Fusible disconnect switch   |
| Phase                      | 3 phase   |
| Number of Poles            | 3   |
| Current rating             | 60 A  |
| Voltage Rating             | 600 V AC<br>250 V DC  |
| Enclosure Rating NEMA 3R   | NEMA 4/4X/5 stainless steel 304   |
| Maximum Horse Power Rating | 15 Hp at 480 V AC 50-60 Hz for 3 phase motors<br>30 Hp at 480 V AC 50-60 Hz for 3 phase motors<br>15 Hp at 600 V AC 50-60 Hz for 3 phase motors<br>50 Hp at 600 V AC 50-60 Hz for 3 phase motors<br>10 hp at 250 V DC |

## Complementary

|                       |  |
|-----------------------|--|
| Mounting Type         | Surface  |
| Electrical Connection | Receptacle   |
| Wire Configuration    | 4-wire   |
| Wire Size             | AWG 12...AWG 2 aluminium<br>AWG 14...AWG 2 copper  |
| Tightening torque     | 45 Lbf.In (5.08 N.m) (AWG 6...AWG 4)<br>40 Lbf.In (4.52 N.m) (AWG 8)<br>35 lbf.in (3.95 N.m) (AWG 14...AWG 10) |
| Depth                 | 5.11 in (129.79 mm)  |
| Width                 | 10.81 in (274.57 mm)   |
| Height                | 16.87 in (428.50 mm)   |

## Environment

|                |           |
|----------------|-----------|
| Certifications | UL Listed |
|----------------|-----------|

## Ordering and shipping details

|                   |                                     |
|-------------------|-------------------------------------|
| Category          | 00124-H&HU SW,W/APPLETON RECPT - WA |
| Discount Schedule | DE1                                 |
| GTIN              | 785901878261                        |
| Returnability     | Yes                                 |
| Country of origin | US                                  |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Number of Units in Package 1 | 1                       |
| Package 1 Height             | 18.69 in (47.464 cm)    |
| Package 1 Width              | 7.37 in (18.732 cm)     |
| Package 1 Length             | 11.00 in (27.94 cm)     |
| Package 1 Weight             | 17.00 lb(US) (7.711 kg) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| RoHS exemption information | <a href="#">Yes</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| PVC free                   | Yes   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|