



Main

Range	Multi9
Product name	Multi9 C60
Product or Component Type	Miniature circuit-breaker
Device short name	C60BPR
Device Application	Distribution
Poles description	3P
Number of protected poles	3
Line Rated Current	15 A 77 °F (25 °C) EN/IEC 60947-2
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	D
Breaking capacity	6 KA Icu 440 V AC EN/IEC 60947-2 10 KA Icu 415 V AC EN/IEC 60947-2 20 KA Icu 240 V AC EN/IEC 60947-2 6 KA Icu 440 V AC GB 14048.2 10 KA Icu 415 V AC GB 14048.2 20 KA Icu 240 V AC GB 14048.2 14 KA AIR 240 V AC UL 489 10 KA AIR 480Y/277 V AC UL 489 14 KA AIR 240 V AC CSA C22.2 No 5 10 kA AIR 480Y/277 V AC CSA C22.2 No 5
Suitability for isolation	Yes EN/IEC 60947-2
Standards	EN/IEC 60947-2 GB 14048.2 UL 489 CSA C22.2 No 5
Product certifications	IEC CCC CSA UL

Complementary

[Ue] rated operational voltage	240 V AC 50/60 Hz 415 V AC 50/60 Hz 440 V AC 50/60 Hz
Magnetic tripping limit	12 x In +/- 20 % AC
[Ics] rated service breaking capacity	4.5 KA 75 % EN/IEC 60947-2 - 440 V AC 7.5 KA 75 % EN/IEC 60947-2 - 415 V AC 15 KA 75 % EN/IEC 60947-2 - 240 V AC 4.5 KA 75 % GB 14048.2 - 440 V AC 7.5 KA 75 % GB 14048.2 - 415 V AC 15 kA 75 % GB 14048.2 - 240 V AC
[Ui] rated insulation voltage	500 V AC EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kVEN/IEC 60947-2
Contact position indicator	Yes
Control Type	Toggle
Local signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 mm pitches	6

Height	5.00 in (127 mm)
Width	2.13 in (54 mm)
Depth	2.83 in (72 mm)
Color	Gray
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Ring terminal top or bottom)
Tightening torque	17.70 lbf.in (2 N.m) top or bottom
Earth-leakage protection	Without

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 EN/IEC 60947-2
Tropicalisation	2 IEC 60068-1
Relative humidity	95 % 131 °F (55 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)




Ordering and shipping details

Category	00949-M9 GEN 2 CB UL489
Discount Schedule	DE2
GTIN	3606481171535
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.95 in (7.5 cm)
Package 1 Width	2.13 in (5.4 cm)
Package 1 Length	5.00 in (12.7 cm)
Package 1 Weight	15.98 oz (453 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	3.15 in (8 cm)
Package 2 Width	8.66 in (22 cm)
Package 2 Length	5.20 in (13.2 cm)
Package 2 Weight	4.12 lb(US) (1.868 kg)
Unit Type of Package 3	S03
Number of Units in Package 3	32
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	34.03 lb(US) (15.438 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free product