#### WWW.PHIHONG.COM



### DC-DC Power over Ethernet Splitter Fully Compliant IEEE802.3af PD Power Supply



# 

#### Features

- Fully Compliant IEEE802.3af DC Power Supply
- DC Good LED
- Non-Vented Case

#### Applications

- IP Telephones
- Wireless Network Access Points
- Blue Tooth Access Points

• Full Protection OTP, OCP, OVP

**Gigabit Compatible** 

• 1 Year Warranty

•

- Security Cameras
  ID Drint Services
- IP Print Servers

Safety Approvals

#### • CE

- Mechanical Characteristics
  - Length: 100mm (3.94in)
  - Width: 56mm (2.2in)

- Height: 28mm (1.1in)
- Weight: 0.2Kg (7.05oz)

**Output Specifications** 

Model	DC Output Voltage	Output Current
POE14-033-R	3.3V	2.5A
POE14-050-R	5V	2.5A
POE14-120-R	12V	1.17A

Reference files: POE14\_user\_manual.pdf

#### **POE14 Characteristics<sup>1</sup>**

#### **INPUT: Input Voltage Range** 36 to 56V DC; Receives power from either data or spare pairs

**Input Current** 0.6A (DC) 36 V DC at max load

#### **Inrush Current** 0.4A maX

# OUTPUT:

**Regulation** Line and Load ±5%

#### Ripple

12V model 120mVp-p 5V & 3.3V models 75mVp-p

#### Efficiency<sup>2</sup>

72% (typical) at max load and 48V DC

#### **Output Power**

Output Model	Limit
3.3V	8.25W at 36-57V DC
5V	12.5W at 36-57V DC
12V	12W at 36-55V DC
12V	14W at 55-57V DC

#### **ENVIRONMENTAL:**

#### Temperature

Operation	0 to +40°C
Non-Operation	-25 to +65°C
Humidity	5 to 90%

#### WWW.PHIHONG.COM

#### Immunity

ESD:	EN61000-4-2 Level 3	
RS:	EN61000-4-3 Level 2	
EFT:	EN61000-4-4 Level 2	
Surge:	EN61000-4-5 Level 3	
CS:	EN61000-4-6 Level 2	
Voltage Dips:	EN61000-4-11Harmonic:	
EN61000-3-2		
Note: CS, Surge, Harmonics and Dips tested		
with POE20U		
EMC		
Complies with FCC Class B		
Complies with EN55032 Class B		

## Dielectric withstand (HI-POT) Test

1500V AC for 1 minute, 10mA

#### **Insulation Resistance**

Primary to secondary: >10M Ohm 500V DC

#### **FEATURES:**

#### **Short Circuit Protection**

Output can be shorted permanently without damage

#### **Over Voltage Protection**

By Zener clamping

#### Indicators

Green LED – Output Good

**Input and Output Data Connector** RJ45

#### **Output Connector**

Center Positive Barrel 9mm x 2.5mm x 5.5mm. Tip is user changeable for other sizes. Note: The + molded on replaceable tip must line up with the word "tip" on DC cord to ensure that the center pin DC jack is +.


Notes:

1. The characteristics defined are at ambient temperature of 25°C unless otherwise specified

2. Efficiency is measured after 30 minutes burn-in

#### Dimensional Diagram Unit: mm

WWW.PHIHONG.COM





Supplier's Declaration of Conformity 47 CFR § 2.1077 Compliance Information

> Phihong USA Corporation 47800 Fremont Boulevard Fremont, CA 94538 Telephone: (510) 445-0100 www.phihong.com

This device complies with/The devices in this product series comply with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.