



CYLINDRICAL SEMI-HOUSED LINEAR VOICE COIL ACTUATORS (VCA)

Introduction

Semi-housed voice coil actuators (VCA) enhance the basic frameless VCAs by adding both a shaft and self-aligning bushings to the unit. The lead wires have also been upgraded to a high flex variant, allowing for added protection from wear and tear. Various shaft options are available depending on the size of the actuator, including both external and internal threading, as well as a standard smooth shaft.



Features

- Precision shaft with multiple options available
- Zero cogging and backlash free
- Life tested in excess of 500 million cycles

SPECIFICATIONS

Part Number	Peak Force (N / lb)	Total Stroke (mm / in)	Continuous Stall Force (N / lb)	Actuator Constant (N $\sqrt{\text{watt}}$ / lb $\sqrt{\text{watt}}$)	Outside Diameter/Width (mm / in)	Length at Mid-stroke (mm / in)
LA13-11-001A-3E	15.5 / 3.50	6.36 / 0.25	5.07 / 1.14	2.36 / 0.53	31.6 / 1.24	27.3 / 1.07
LA13-11-001A-3S	15.5 / 3.50	6.36 / 0.25	5.07 / 1.14	2.36 / 0.53	31.6 / 1.24	27.3 / 1.07
LA16-16-001A-4E	89.0 / 20.0	6.36 / 0.25	24.4 / 5.50	5.83 / 1.31	40.0 / 1.57	39.6 / 1.56
LA16-16-001A-4S	89.0 / 20.0	6.36 / 0.25	24.4 / 5.50	5.83 / 1.31	40.0 / 1.57	39.6 / 1.56
LA28-43-001A-12E	266 / 60.0	25.0 / 0.98	75.6 / 17.0	13.0 / 2.90	70.0 / 2.76	129 / 5.10
LA28-43-001A-12I	266 / 60.0	25.0 / 0.98	75.6 / 17.0	13.0 / 2.90	70.0 / 2.76	129 / 5.10
LA28-43-001A-12S	266 / 60.0	25.0 / 0.98	75.6	13.0 / 2.90	70.0 / 2.76	129 / 5.10
LA100-93-001A-50I	2447 / 500	50.8 / 2.00	1443 / 325	86.2 / 19.4	254 / 10.0	236 / 5.90
LA100-93-001A-50S	2447 / 500	50.8 / 2.00	1443 / 325	86.2 / 19.4	254 / 10.0	236 / 5.90

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

Americas

+1 (760) 597 7042

sales.beikimco@sensata.com

Europe, Middle East & Africa

+1 (760) 597 7042

support@sensata.com

Pacific

sales.isasia@list.sensata.com

China +86 (21) 2306 1500 Japan

+81 (45) 277 7117 Korea +82

(31) 601 2004 India +91 (80)

67920890

Rest of Asia +603-5566 6001