




Sensors > Safety Light Curtains



Safety Level: **Type 4 - PL e - Cat.4 , SIL3, SILCL3**

Detection Type: **Finger**

Detection Resolution: **14 mm**

Response Time: **11 msec**

### Features

#### Configuration Features

Safety Output Type	2 OSSD Pairs (400mA)
Connections Type	M12 5-Pole Connector (Emitter) & M12 8-Pole Connector (Receiver)
Number of Safety Outputs	2
Safety Functions	Integrated
Status Light Type	LED

#### Electrical Characteristics

Power Supply Voltage	24 ± 20% VDC
Output Current (Max)	.4 A
Output Voltage	24 VDC

#### Body Features

Product Weight	1649 g
----------------	--------

#### Dimensions

Overall Height	813 mm
Controlled Height	760 mm
Connection Cable Length (Max)	100 m
Product Depth	28 mm

Product Length	30 mm
Product Height	813 mm

### Usage Conditions

Storage Temperature Range	-30 – 70 °C[-22 – 158 °F]
Operating Temperature Range	-20 – 55 °C[-4 – 131 °F]
Detection Resolution	14 mm

### Operation/Application

Number of Beams	75
Protected Height	760 mm
Detection & Functioning System	Emitter & Receiver
Start & Restart Type	Automatic & Manual
Detection Type	Finger
Response Time	11 msec

### Industry Standards

IP Rating	IP67
Safety Level	Type 4 - PL e - Cat.4 , SIL3, SILCL3

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # 1-2447912-0  
SLC-FC15-M12-90-5P



TE Part # 1-2447912-1  
SLC-FC-M12-5P-CG9



TE Part # 1-2447912-2  
SLC-FC-M12-90-5P-CG9



TE Part # 1-2447913-0  
SLC-FC15-M12-90-8P



TE Part # 1-2447913-1  
SLC-FC-M12-8P-CG11



TE Part # 1-2447913-2  
SLC-FC-M12-90-8P-CG11



TE Part # 1-2447913-3  
SLC-FC-M12-8P-CG9



TE Part # 1-2447913-4  
SLC-FC-M12-90-8P-CG9



TE Part # 1-2447915-0  
SLC-FMC-CG11-197



TE Part # 1-2447917-0  
SLC-SLC-MP-136



TE Part # 1-2447917-1  
SLC-SLC-MP-144



TE Part # 1-2447917-2  
SLC-SLC-MP-151



TE Part # 1-2447917-3  
SLC-SLC-MP-166



TE Part # 1-2447917-4  
SLC-SLC-MP-181



TE Part # 1-2447920-0  
SLC-PS-135



TE Part # 1-2447920-1  
SLC-PS-150



## Documents

### Product Drawings

[SLC4-F14-076](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2437979-7\\_B2.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2437979-7\\_B2.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2437979-7\\_B2.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[Safety Light Curtains](#)

English

[Safety Products Training](#)

English

### Product Specifications

[Manuals & User Guides](#)

English

[Manuals & User Guides](#)

English

### Agency Approvals

[UL Report](#)

English