

Description

The P528 incorporates Kavlico's 4th generation ceramic capacitive sense element with the latest state of the art proprietary ASIC. Available in brass or stainless steel housings, this multi-purpose sensor is rugged by design. Highly reliable, the P528 is ideal for measuring a broad range of process media including hydrocarbon based fluids, air, and gases. The P528 package has a built-in Metri-Pack 150 series sealed electrical connector and is available with popular pressure connection thread options. The sensor is offered with seal materials suitable for diverse applications. Standard pressure ranges are available in PSI or Bar.



Features

- Small Size (3/4" Hex)
- External Hex for Easy Installation
- Linear Amplified Output
- Temperature Compensated
- Superior Long-Term Stability
- Low Power Consumption
- Minimum Life Expectancy: Ten Million Cycles

Applications

- Compressors
- Process Controls
- Instruments & Test Equipment
- Sterilizers
- Air Pressure
- Oil & Fuel Pressure
- Coolant Pressure
- Agricultural Equipment
- CNG & Natural Gas Engines



MAIN FEATURES

Pressure Ranges	0 - 6 up to 0 - 70 Bar and 0 - 100 up to 0 - 1000 PSI				
Electrical Connection	Packard Electric Metri-Pack 150 Series				
Pressure Connection	1/4"SAE Female Flare w/ Schrader Deflator 7/16"-20 UNF-2A external threads 1/4"-18 NPT 1/8"-27 NPT (external threads)				
Housing Material	Brass (up to 300 psi) and stainless steel (above 300 psi)				
Output Voltage	0.5 to 4.5 Vdc				



Sensata

Technologies



Pressure Ranges

Bar A, S or G	0 - 1	0 - 1.6	0 - 2.5	0 - 4	0 - 6	0 - 10	0 - 16	0 - 25	0 - 40	0 - 50	0 - 70	
PSI A, S or G	0 - 15	0 - 20	0 - 30	0 - 50	0 - 75	0 - 100	0 - 150	0 - 200	0 - 300	0 - 500	0 - 750	0 - 1000

For custom pressure ranges consult Kavlico Pressure Sensors.

Physical

Durability/Service Life	10 million full pressure cycles (minimum)			
Proof Pressure	3X FS Pressure (upto 14 Bar / 200 PSI) 2X FS Pressure (above 14 Bar / 200 PSI)			
Burst Pressure	1500 PSI (upto 24 Bar / 300 PSI) 2500 PSI (above 24 Bar / 300 PSI)			
Humidity	93 +/- 3% RH			
Vibration	10 g's peak to peak sine (10 - 2000 Hz)			
Shock	75 g's, 1/2 Sine Wave			
Drop Test	1 meter drop on concrete as per SAE J1455			
Weight	< 50 gm			
Ingress Protection	IP67			

Performance

Linearity Error	\leq +/- 0.5% of span			
Total Error Band	+/-1.5% of span (0 \le T \le 85 C°) +/-2.0% of span (T < 0 C°,T < 85 C°)			
Stability Coefficient	+/-0.3 % of Full span over 1 year			
Operating Temperature	-40 C° to 125 C° (Seal material dependent. See Ordering Options)			
Storage Temperature	-40 C° to 125 C° (Seal material dependent. See Ordering Options)			



Electrical

Supply Voltage	5.0 Vdc +/- 0.5
Output Voltage	0.5 to 4.5 Vdc
Supply Current	\leq 5 mA
Output Impedance	\leq 100 Ω
Output load	\geq 10 K Ω
Output response time	\leq 2 ms to 63 % of final output voltage with step change in input pressure
Overvoltage protection	36 Vdc
Reverse Voltage	-36 Vdc
Short Circuit protected	Output to supply, Output to Ground: Indefinite
Isolation Voltage	$R \geq$ 100 $M\Omega,$ 500 Vdc / 1 min
Warmup time	3 mSec Max.
EMC	Meets ISO 7637-3, ISO 11452-4, ISO 11452-2, CISPR 25, MIL-STD 461 E
ESD	IEC 1000-4.2 (8kV contact, 15kV air), ISO 10605 (8kV contact, 25kV air)





Pressure Sensor with Electrical Connection



Pressure Connections and Recommended Installation Torque







Name	1/4 - 18 NPT	1/8 - 27 NPT	Schrader deflator
Thread	External	External	Internal
Torque	25 Nm	14 Nm	15 Nm



Name	7/16 – 20 UNF 2A
Thread	External
Torque	16 Nm

Note: Recommended torque may varify according to material and specific application.



Example: P528-16B-A-C1A

P528 Sensor, 0 - 16 Bar Absolute, Fluorosilicone Seal Material, 1/4 - 18 NPT Pressure Connection,

	P528 – 16B –	A <mark>-</mark> C 1 /	A
Family	<u> </u>	Γ T T $-$	
P528			
Pressure Ranges			
6B: 0 - 6 Bar 100: 0 - 100 PSI 1000: 0 - 7 10B: 0 - 10 Bar 150: 0 - 150 PSI 168: 0 - 16 Bar 16B: 0 - 16 Bar 300: 0 - 300 PSI 258: 0 - 25 Bar 40B: 0 - 40 Bar 500: 0 - 500 PSI 400: 0 - 500 PSI 50B: 0 - 50 Bar 600: 0 - 600 PSI 70B: 0 - 70 Bar	1000 PSI		
Reference			
A: Absolute G: Gage S: Sealed Gage (Referenced to 14.7 PSIA)			
Seal Material			
C: Neoprene (-30° to 120°C) F: Ethylene Propylene (-40° to 120°C) H: HNBR (-20° to 125°C)			
Pressure Connection (Port)			
1: 1/4 - 18 NPT (External Threads) 2: 1/4 SAE Female flare w/schrader deflator 3: 7/16 - 20 UNF 2A (External threads) 4: 1/8 - 27 NPT (External threads)			
Built-in Electrical Connection			1
A: With Mating Connector, w/12", 18 AWG Leads C: Without Mating Connector			



EN 61326-1, 2006

IEC 61000-4-2, 2001 IEC 61000-4-3, 2006 IEC 61000-4-8, 2001

CE RoHS

2002/95/EC RoHS Directive



File # SA10552

Page 6

Revised 2/7/18

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS, OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE OF SENSATA DATA SHEETS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

Americas

+1 (800) 350 2727 sensors@sensata.com switches@sensata.com

Europe, Middle East & Africa +359 (2) 809 1826 pressure-info.eu@sensata.com

Asia Pacific

sales.isasia@list.sensata.com China +86 (21) 2306 1500 Japan +81 (45) 277 7117 Korea +82 (31) 601 2004 India +91 (80) 67920890 Rest of Asia +886 (2) 27602006 ext 2808