



PRODUCT-DETAILS

XT5H-D 400 MCS 3p F F UL/CSA

XT5H-D 400 MCS 3p F F UL/CSA



General Information	
Extended Product Type	XT5H-D 400 MCS 3p F F UL/CSA
Product ID	1SDA102663R1
EAN	8056221023573
Catalog Description	XT5H-D 400 MCS 3p F F UL/CSA
Long Description	SWITCH-DISCONNECTOR TMAX XT5H-D 400 MCS UL/CSA FIXED THREE-POLE WITH FRONT TERMINALS

ABB EcoSolutions	
ABB EcoSolutions	Yes

Circular Value	
Circular Design Principles Recyclability Rate	Design for Closing Resource Loops - Standard EN45555 - 59.6 %
Conflict Minerals Reporting Template	9AKK108467A5658

(CMRT)

End of Life Instructions	9AKK108468A2353
Group Waste to Landfill Target	UL 2799 Zero Waste To Landfill Validation available
Toxic Substances Control Act - TSCA	9AKK108467A8326

Eco Transparency

Environmental Product Declaration - EPD	9AKK108468A1893
---	-----------------

Environmental

Environmental Information	9AKK108467A6707
REACH Declaration	9AKK108466A1425
RoHS Information	9AKK108466A1424
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Ordering

Order Code US and Canada	XT5HU340ADFF000XXX
EAN	8056221023573
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	140 mm
Product Net Height	205 mm
Product Net Depth / Length	103.5 mm
Product Net Weight	4.304 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	248 mm
Package Level 1 Height	240 mm
Package Level 1 Depth / Length	285 mm
Package Level 1 Gross Weight	4.53 kg
Package Level 1 EAN	8056221023573

Additional Information

Mechanical Durability	240 cycles per hour 20000 cycle
Number of Poles	3
Order Multiple	1 piece

Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	Switch Disconnecter
Rated Current (I _n)	400 A
Rated Operational Current AC-23A (I _e)	(400 V) 400 A (690 V) 400 A
Rated Operational Voltage	600 V AC 600 V DC
Rated Uninterrupted Current (I _u)	400 A
Short-Circuit Performance Level	H
Standards	UL489
Sub-type	XT5
Suitable for Product Class	SACE Tmax XT
Terminal Connection Type	Front
Version	F
CAD Dimensional Drawing	1SDH002065A1115 1SDH002065A1131

Technical UL/CSA

Interrupting Rating acc. to UL489	(240 V AC) 150 kA (480 V AC) 65 kA (600 V AC) 35 kA (250 V DC) 2 Poles in Series 70 kA (500 V DC) 2 Poles in Series 50 kA (600 V DC) 3 Poles in Series 35 kA
-----------------------------------	---

Certificates and Declarations

Data Sheet, Technical Information	1SDC210200D0206 1SDC210199D0206
Declaration of Conformity - CE	9AKK107680A2824
Mechanical Drawings	1SDH002011A1101
Wiring Diagram	1SDM000005A1001
Instructions and Manuals	1SDH002011A1002

Classifications

ETIM 7	EC000216 - Switch disconnecter
ETIM 8	EC000216 - Switch disconnecter
ETIM 9	EC000216 - Switch disconnecter (low voltage)
IDEA Granular Category Code (IGCC)	4927 >> Molded case circuit breakers
UNSPSC	39121616
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	V11.1 : 27371403

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

