

Features

- Made from antistatic polyethylene
- Printed in white with ESD caution logo and text
- Supplied in packs of 100
- Homogeneous, non-amine antistatic polythene film which is effective at low relative humidities (less than 12%)

RS PRO Antistatic Refuse Sacks – Black – 110 ltr – 130 Gauge

RS Stock No.: 75053292



RS Professionally Approved Products bring you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Our ESD refuse sacks are suitable to holding waste in an EPA. Specifically designed for the particular needs of the electronics industry. The special additives used do not affect the film clarity or quality.

General Specifications

STANDARD DOCUMENT	MEETS REQUIREMENTS OF:
ANSI/ESD S20.20	

Physical Properties

ITEM	TYPICAL VALUE	TEST PROCEDURES/METHOD
Thickness	130 Gauge - 32.5 microns	-
Tensile Strength	1500 to 3000 psi	ASTM D 882
Tear Strength	65 to 450lbs/inch	ASTM D 1004
Elongation	MD: 550	ASTM D 882
Dart Impact	250-750 grams	ASTM D 3420
Burst (Mullen)	20 - 60 psi	ASTM D 3420
Heat Sealing	Temperature: 250-375°F	ASTM D 882
Time	.25 - 3.5 seconds	-
Pressure	30-60 psi	-
Surface Resistivity	(Inside/Outside) at 28.8°C and 12% RH 10^{11} Ohms/sq	-
Static Decay Rate	(5000 volts to 0 volts at 28.8°C and 12% RH) <math><2</math> seconds	-

Notes:

- Unless otherwise noted, tolerance $\pm 10\%$

Stock No.	Brand	Product Name	Size	Quantity (per pack)
75053292	RS PRO	Antistatic Refuse Sacks - Black	110 ltr	100