



# Technical Data Sheet

## *DELTA SOLAR*



**DELTA SOLAR** measures important electrical parameters like AC Current (TRMS), DC Current, AC Voltage(TRMS) and DC Voltage. It also features Capacitance, Ohm & Continuity, Frequency and Duty cycle and temperature measurement.

## Application

DELTA SOLAR measures important electrical parameters like AC Current (TRMS), DC Current, AC Voltage(TRMS) and DC Voltage. It also features Capacitance, Ohm & Continuity, Frequency and Duty cycle and temperature measurement.

## Product Features

### Unique Design

DELTA SOLAR is a highly innovative design for features those increases safety and comfort of user.

- Rotating clamp jaws facilitate the measurement at physically awkward positions, vertical bus bars, conductors placed at positions difficult to access.
- Clamp jaws can be opened or closed with the trigger placed at bottom side away from the jaws. This allows the user to place his/her hand at safer distance from live conductor. This greatly reduces exposure of human beings to electrical shocks
- Location and design of trigger eliminates fatigues caused by single finger operation. It allows spreading the force required to open the jaws over more than one finger to ensure comfortable operation.
- Comfortable operation of push buttons and function selector switch, in adverse field conditions.

### Large Jaw Opening

For DELTA SOLAR Jaw opening of 51mm for standard wire diameter of 50mm

### Narrow Body

Narrow housing for firm grip and easy to carry.

### High Accuracy for low current measurement

The clamp meter can measure accurately at not only the High currents but also Low current ranges.

### True Root Mean Square (TRMS) measurement

Clamp meter measures AC signal's root-mean-square value accurately irrespective of the shape of input waveform.

### Measurement on Variable Frequency Drives

The clamp meter can measure accurately on variable frequency drives (VFD) and UPS.

### User selectable Backlit : (Optional)

It is possible to conduct measurement using the clamp meter during night time in darkness with the help of Backlit. The back lit can be switched ON or OFF by pressing a single key.

### Temperature measurement

Temperatures from -200 to 800 °C using Pt 100 and Pt 1000 sensors.

### AUTO POWER OFF

In order to save the power of the Batteries, the clamp meter will automatically shut OFF if it detects no activity for 10 minutes.

### Analog Scale

Analog scale that updates at the rate 20 times/sec to observe fluctuations in input.

### CONTINOUS ON MODE

In this mode, AUTO POWER OFF is disabled

### DATAHold Function

By pressing DATA HOLD button, reading on the display can be latched for Hands free operation.

### MIN,MAX Function

By pressing MIN/MAX button, the clamp meter will start recording latest Minimum and Maximum readings

### NULZERO Correction for Resistance

For Low ohm measurement, the lead resistance can be compensated by pressing the shift key (Yellow Key)

### NULZERO Correction for Capacitance

Null zero correction for capacitance. For nF range, stray capacitance can be compensated by shift key (Yellow Key)

## Product Features

### AUTO and MANUAL ranging modes

range with best resolution depending on the applied input. In MANUAL ranging mode range is user selectable using MAN Key

### Diode Measurement

For testing diode and transistors, diode measurement function is available.

### Protection from dust and water

Ip20 for terminals as per IEC60529

### Applicable International Safety standards

600 V CAT IV/1000V CAT III as per International Safety standard IEC 61010-1- 2010

### Double molded Cover for soft touch and firm grip of the Instrument

## Technical Specifications

Measuring function	Measuring range	Resolution	Input impedance	Intrinsic error of digital display ± (...% of rdg + ...digit) at reference condition	Over load capacity <sup>1)</sup>	
					Over load value	Overload duration
V dc	30.00 mV	10 µV	>10 GΩ // <40pF	0.5 + 3 <sup>2)</sup>	1500 V DC 1000 V AC eff / rms Sine wave	Continuously
	300.0 mV	100 µV	>10 GΩ // <40pF	0.5 + 3		
	3.000 V	1 mV	11 MΩ // <40pF	0.25 + 3		
	30.00 V	10 mV	10 MΩ // <40pF	0.25 + 3		
	300.0 V	100 mV	10 MΩ // <40pF	0.25 + 3		
	1000 V	1 V	10 MΩ // <40pF	0.35 + 3		
	1500 V	1 V	10 MΩ // <40pF	0.5 + 3		
V ~	3.000 V	1 mV	11 MΩ // <40pF	0.75 + 2 (10....300 Digit) 0.75 + 1 (> 300 Digit)	1500 V DC 1000 V AC eff / rms Sine wave	Continuously
	30.00 V	10 mV	10 MΩ // <40pF			
	300.0 V	100 mV	10 MΩ // <40pF			
	1000 V	1V	10 MΩ // <40pF			
Ω	No load voltage				1500 V DC 1000 V AC eff / rms Sine wave	10 Sec
	30.00 Ω	10 mΩ	Max. 3.2 V	0.5 + 3 <sup>2)</sup>		
	300.0 Ω	100 mΩ	Max. 3.2 V	0.5 + 3		
	3.000 KΩ	1Ω	Max. 1.25 V	0.4 + 1		
	30.00 KΩ	10 Ω	Max. 1.25 V	0.4 + 1		
	300.0 KΩ	100 Ω	Max. 1.25 V	0.4 + 1		
	3.000 MΩ	1 KΩ	Max. 1.25 V	0.6 + 1		
	30.00 MΩ	10 KΩ	Max. 1.25 V	2.0 + 1		
►	2.000 V	1 mV	Max. 3.2 V	0.2 + 3	1600 A	Continuously
A AC/DC	2 to 300.0 A	0.1 A	-----	2 % + 0.5 A		
	300 to 1200 A	1 A	-----	2 % + 5 A		
	1200 to 1500 A	1 A	-----	2.2 % + 5 A		

## Technical Specifications

Measuring function	Measuring range	Resolution	Discharge resistance	U0 max.	Intrinsic error of digital display ± (...% of rdg + ...digit) at reference condition	Over load capacity <sup>1)</sup>			
						Overload value	Overload duration		
F	30.00 nF	10 pF	250 KΩ	0.5 + 3 <sup>2)</sup>	1.0 + 3 <sup>2)</sup>	1500 V DC 1000 V AC eff / rms Sine wave	10 Sec		
	300.0 nF	100 pF	250 KΩ		1.0 + 3				
	3.000 µF	1 nF	25 KΩ		1.0 + 3				
	30.00 µF	10 nF	25 KΩ		3.0 + 3				
	300.0 µF	10 nF	15 KΩ		5.0 + 6				
			f min V dc	f min V ~					
Hz	300.0 Hz	0.1 Hz	1 Hz	45 Hz	0.5 + 3 <sup>3)</sup>	3 kHz 1000 V 30 kHz; 300 V 100 kHz 30 V	Continuously		
	3.000 KHz	1 Hz	1 Hz	45 Hz	0.5 + 1 <sup>3)</sup>				
	30.00 KHz	10 Hz	10 Hz	45 Hz					
	100.0 KHz	100 Hz	100 Hz	100 Hz					
%	2.0....98.0%	0.1 %	2 Hz	-	2 Hz... 1kHz ± 5 Digit <sup>4)</sup> 1 kHz ... 10 kHz; ± 5 Digit/kHz <sup>4)</sup>				
°C	Pt 100 -200.0... +200.0 °C	0.1 °C	-	-	2 Kelvin + 5 Digit <sup>5)</sup>	1500 V DC 1000 V AC eff / rms Sine wave	10 Sec		
	+200.0... +850.0 °C	0.1 °C			1.0 + 5 <sup>5)</sup>				
	Pt 100 -100.0... +200.0 °C	0.1 °C	-	-	2 Kelvin + 5 Digit <sup>5)</sup>				
	+200.0... +850.0 °C	0.1 °C			1.0 + 2 <sup>5)</sup>				

1) At 0° .... + 40 °C

2) With zero adjustment, without zero adjustment + 35 digits

3) Range :

3 V ac/dc: Ue = 1.5 V eff/rms ... 100 V eff/rms

30 V ac/dc: Ue = 15 V eff/rms ... 300 V eff/rms

300 V ac/dc: Ue = 150 V eff/rms ... 1000 V eff/rms

4) On the range 3 V dc, square – wave signal positive on one side

5 ... 15 V, f = const., not 163.84 Hz or integral multiple.

5) Without sensor

### Reference conditions for Accuracy

Reference temperature	23°C ± 2K
Relative Humidity	45%...55% RH
Waveform of measured quantity	Sinusoidal
Input frequency	50 or 60 Hz ±2%
Battery Voltage	8 V ± 0.1 V

### Battery

- Battery Voltage 9 V DC
- Battery type Manganese Dioxide Cell as per IEC6F22 , alkaline manganese cell as per IEC 6LR 61
- Battery Life Minimum 220 hours on Vdc, Adc, 80 hours on Vac, Aac.

### Environmental

● Operating temperature	-10 to +55°C
● Storage temperature	-20 to +70°C
● Relative humidity	0... 90% non condensing
● Terminal Protection	IP50 for Housing and Ip20 for terminals

### Display

- Number of digits 3 ¾ digits.
- Maximum count 3100 counts
- Over range indication "OL" is displayed
- Polarity indication "—" sign is displayed for DC functions, if positive pole is at "L"

## Influence Quantities and Variations

Influence Quantity	Range of Influence	Measured Quantity/ Measuring Range	Variation <sup>1)</sup> ± (....% of rdg. + ....digits)
<b>Temperature</b>	0 °C +21 °C and +25 °C...+40°C	30/300 mV dc	1.0 + 3
		3...300 V dc	0.15 + 1
		1000 V dc	0.2 + 1
		V ~	0.4 + 2
		30 Ω <sup>2)</sup>	0.15 + 2
		300 Ω	0.25 + 2
		3 KΩ – 3 MΩ	0.15 + 1
		30 MΩ	1.0 + 1
		30 nF – 3 μF	0.5 + 2
		30 μF	2.0 + 2
		Hz	0.5 + 1
		%	± 5 digits
		-200...+200 °C	0.5 K + 2
		+200...+850°C	0.5 + 2
		DELTA SOLAR	300 A ~ / A DC      0.2 X Specified accuracy 1500 A ~ / A DC      0.1 X Specified accuracy
<b>Frequency of the measured quantity</b>	> 65 Hz...400 Hz	3...300 V ~	2.0 + 3
	>400 Hz...1 KHz		
	>65 Hz ... 1 KHz	1000 V ~	3.0 + 3
	15Hz ...<45 Hz	A ~	1.0 % of range + 1
	>66 Hz... 400 Hz		

## Influence Quantities and Variations

Influence Quantity	Range of Influence		Measured Quantity/ Measuring Range	Variation <sup>1)</sup> ± ....% of rdg. + ....digits
Wave form of the measured quantity	Crest factor CF	1....3 1....5	V ~ <sup>4)</sup>	± 1 % of rdg ± 3 % of rdg
Battery Voltage	 <sup>5)</sup> ... < 7.9 V ... > 8.1 V ... 10.0 V		V DC V ~ AAC/ADC 30Ω / 300Ω / °C 3 kΩ - 30MΩ nF, μF Hz %	2 Digit 4 Digit 8 Digit 4 Digit 3 Digit 10 Digit 10 Digit 10 Digit
Relative Humidity	75% 3 Days Meter off		V~,VDC A~, ADC Ω F Hz % C	1 x intrinsic error
HOLD	-		-	± 1 digits
MIN / MAX	-		V ac/dc , A ~ , ADC	± 2 digits

### Applicable Standards

EMC	IEC/EN 61326-1: 2012 Class B
Immunity	IEC/EN 61326-1: 2012
	IEC 61000-4-2
	8 KV atmosphere discharge, 4 KV contact discharge.
	IEC 61000-4-3 : 3 V/m
	IEC 61000-4-8 : 3 A/m

### Standard Scope of supply

1 Cable Set
1 Battery Set
1 Operating Instructions Manual
1 Leather carrying case

### Safety

IP for water & dust	IEC60529
Pollution degree	2
Installation category	III 1000V, IV 600V
High Voltage Test	6.7 kV AC, 50Hz for 1 minute between housing and input. 3.7 kV AC, 50Hz for 1 minute between housing with jaws and input
Weight	0.6 Kg

### Warranty

1 years

## Ordering Information

**DT40-1NZ0000000000 - DELTA SOLAR METER WITH NT**

**DT40-1FZ0000000000 - DELTA SOLAR METER WITH FT**



**sifam tinsley**  
PRECISION INSTRUMENTATION

**Sifam Tinsley Instrumentation Inc.**  
3105, Creekside Village Drive,  
Suite No. 801, Kennesaw,  
GA 30144 (USA)  
**E-mail Id :** psk@sifamtinsley.com  
**Web :** www.sifamtinsley.com  
**Contact No. :** +1 404 736 4903

**Sifam Tinsley Instrumentation Ltd**  
Unit 1 Warner Drive,  
Springwood Industrial Estate  
Braintree, Essex, UK, CM72YW  
**E-mail:** sales@sifamtinsley.com  
**Web:** www.sifamtinsley.com/uk  
**Contact:** +44(0)1803615139