## WWW.PHIHONG.COM



# 12W Wall Plug Adapter







## **Features**

- Double Insulated
- Class B EMI
- < 0.075W No-Load Current

- DOE Level VI
- Over-Voltage & Short-Circuit protections

### **Applications**

- Wireless Communications
- Networking

- Portable Equipment
- Peripherals

## **Safety Approvals**

• UL/cUL 62638-1

### **Mechanical Characteristics**

• Length: 71.2mm (2.80in)

• Width: 34mm (1.34in)

## • Height: 46mm (1.81in)

• Weight: 85g (3.00oz) Ref

## **Output Specifications**

Model	Prong Style	DC Lo		ad	Ripple <sup>1</sup>	Regulation
		Output Voltage	Min.	Max.		Line & Load
PSAA12A-120L6-R	US	12V	0A	1A	240mV	±5%

## Notes:

 Measured with by-pass capacitors 0.1uf /10uf at output connector terminal and oscilloscope set at 20 MHz (tested by oscilloscope) after 30 minutes warm-up

### PSAA12A-120L6-R Characteristics<sup>1</sup>

### WWW.PHIHONG.COM

**Input:** 

**AC Input Voltage Rating** 

100 to 240 V AC

**AC Input Voltage Range** 

90 to 264V AC

**AC Input Frequency** 

47 to 63Hz

**Input Current** 

0.5A (RMS) max at 100VAC, max load

**Leakage Current** 

0.25mA max

**Inrush Current** 

60A @230VAC, 25°C, at max load

**Input Power Saving** 

<0.075W at 230Vac, no load

**Output:** 

Efficiency<sup>2</sup>

DOE Level VI

**Hold-up Time** 

10mS Min. at Max load and 120Vac 60Hz

**Short Circuit Protection** 

Units protected against a continuous short circuit and over current condition over the operating range.

**Over-Voltage Protection** 

Output voltage shall not exceed 20V

**Over-Current Protection** 

2A max

**Environmental:** 

**Temperature** 

Operation  $0^{\circ}\text{C}$  to  $+40^{\circ}\text{C}$ Non-operation  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ Humidity  $90^{\circ}\text{RH}$  Max

**Emissions** 

Complies with FCC Part 15 Class B

**Immunity** 

EN50082-1:

EN 61000 -4-2 Level 4 EN 61000 -4-5

Level 3 EN61000-3-2

EN61000-3-3 EN

55024

IEC610004-2

IEC610004-3

IEC610004-4

IEC610004-5

IEC610004-6

IEC610004-8

IEC610004-11

Dielectric Withstand (Hi-pot) Test Primary to

Secondary: 3000V AC for 1 min., 10mA

**DC Output Connector** 

The output dc cord shall be 1200mm 26AWG in length


. Matte black PVC insulation. DC plug: (-) GND

outside; (+) Output inside

### Notes:

- 1. The characteristics defined are at ambient temperature of 25°C unless otherwise specified
- 2. Efficiency is measured after 30 minutes burn-in

# Dimension Diagram Unit: mm





# Supplier's Declaration of Conformity 47 CFR § 2.1077 Compliance Information

Phihong USA Corporation 47800 Fremont Boulevard Fremont, CA 94538 Telephone: (510) 445-0100

www.phihong.com

This device complies with/The devices in this product series comply with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.