

Indicator 22 mm

82-6151.0134



<https://eao.com/p/82-6151.0134>

Your product:



82-6151.0134 Indicator 22 mm

FRONT

Front bezel material: Stainless steel

MOUNTING

Mounting cut-out: Ø 22 mm

OPERATING-/INDICATION PART

Lens colour: Silver

Shape of illumination: Ring

Lens shape: flush

Lens optics: opaque

Lens illumination: illuminative

Lens material: Stainless steel

Illumination colour: Green

ELECTRICAL CHARACTERISTICS

Electrical lifetime: 50 000 cycles of operation

Pollution degree: 2, according to EN IEC 60947-1

Rated Operational Voltage U_e : 250 VAC

Rated insulation voltage U_i : 250 V

Thermal current I_{th} : 5 A

Electric strength: 1500 VAC, 50 Hz 1 minute between life terminals and ground

Operating voltage: 24 V AC/DC

MECHANICAL CHARACTERISTIC

Weight:	0.018 kg
Terminal:	Soldering terminal, 2.8 x 0.5 mm
Tightening torque:	0.5 ... 0.6 Nm

AMBIENT CONDITION


Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
Storage temperature:	- 40 °C ... + 80 °C
Operating temperature:	- 30 °C ... + 70 °C
Climate resistance:	Damp heat, 21 days according to IEC 60512-11
Shock resistance:	Max. 500 m / s ² as per IEC 60068-2-27

CERTIFICATE


Approbations:	CB, CCC, C UL, UL
----------------------	-------------------

OTHER


Short Description:	Indicator 22 mm, 24 V AC/DC, Soldering terminal, 2.8 x 0.5 mm, Stainless steel, Green, Silver
Kind of illumination:	Single-LED
Wiring diagrams:	



Dimension drawings:



Mounting cut-outs:



Component layouts:

