

Keysight 11878A 50 Ohm 3.5 mm Adapter Kit

Notices

Copyright Notice

© Keysight Technologies 1989 - 2019

No part of this manual may be reproduced in any form or by any means (including electronic storage and retrieval or translation into a foreign language) without prior agreement and written consent from Keysight Technologies as governed by United States and international copyright laws.

Manual Part Number

11878-90001

Edition

Edition 2, February 8, 2019

Printed in:

Printed in Malaysia

Published by:

Keysight Technologies
Bayan Lepas Free Industrial Zone,
11900 Penang, Malaysia

Technology Licenses

The hardware and/or software described in this document are furnished under a license and may be used or copied only in accordance with the terms of such license.

Declaration of Conformity

Declarations of Conformity for this product and for other Keysight products may be downloaded from the Web. Go to <http://www.keysight.com/go/conformity>. You can then search by product number to find the latest Declaration of Conformity.

U.S. Government Rights

The Software is "commercial computer software," as defined by Federal Acquisition Regulation ("FAR") 2.101. Pursuant to FAR 12.212 and 27.405-3 and Department of Defense FAR Supplement ("DFARS") 227.7202, the U.S. government acquires commercial computer software under the same terms by which the software is customarily provided to the public. Accordingly, Keysight provides the Software to U.S. government customers under its standard commercial license, which is embodied in its End User License Agreement (EULA), a copy of which can be found at <http://www.keysight.com/find/sweula>. The license set forth in the EULA represents the exclusive authority by which the U.S. government may use, modify, distribute, or disclose the Software. The EULA and the license set forth therein, does not require or permit, among other things, that Keysight: (1) Furnish technical information related to commercial computer software or commercial computer software documentation that is not customarily provided to the public; or (2) Relinquish to, or otherwise provide, the government rights in excess of these rights customarily provided to the public to use, modify, reproduce, release, perform, display, or disclose commercial computer software or commercial computer software documentation. No additional government requirements beyond those set forth in the EULA shall apply, except to the extent that those terms, rights, or licenses are explicitly required from all providers of commercial computer software pursuant to the FAR and the DFARS and are set forth specifically in writing elsewhere in the EULA. Keysight shall be under no obligation to update, revise or otherwise modify the Software. With respect to any technical data as defined by FAR 2.101, pursuant to FAR 12.211 and 27.404.2 and DFARS 227.7102, the U.S. government acquires no greater than Limited Rights as defined in FAR 27.401 or DFAR 227.7103-5 (c), as applicable in any technical data.

Warranty

THE MATERIAL CONTAINED IN THIS DOCUMENT IS PROVIDED "AS IS," AND IS SUBJECT TO BEING CHANGED, WITHOUT NOTICE, IN FUTURE EDITIONS. FURTHER, TO THE MAXIMUM EXTENT PERMITTED BY APPLICABLE LAW, KEYSIGHT DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED, WITH REGARD TO THIS MANUAL AND ANY INFORMATION CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. KEYSIGHT SHALL NOT BE LIABLE FOR ERRORS OR FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IN CONNECTION WITH THE FURNISHING, USE, OR PERFORMANCE OF THIS DOCUMENT OR OF ANY INFORMATION CONTAINED HEREIN. SHOULD KEYSIGHT AND THE USER HAVE A SEPARATE WRITTEN AGREEMENT WITH WARRANTY TERMS COVERING THE MATERIAL IN THIS DOCUMENT THAT CONFLICT WITH THESE TERMS, THE WARRANTY TERMS IN THE SEPARATE AGREEMENT SHALL CONTROL.

Safety Information

CAUTION

A CAUTION notice denotes a hazard. It calls attention to an operating procedure, practice, or the like that, if not correctly performed or adhered to, could result in damage to the product or loss of important data. Do not proceed beyond a CAUTION notice until the indicated conditions are fully understood and met.

WARNING

A WARNING notice denotes a hazard. It calls attention to an operating procedure, practice, or the like that, if not correctly performed or adhered to, could result in personal injury or death. Do not proceed beyond a WARNING notice until the indicated conditions are fully understood and met.

Waste Electrical and Electronic Equipment (WEEE) Directive

This instrument complies with the WEEE Directive marking requirement. This affixed product label indicates that you must not discard this electrical or electronic product in domestic household waste.

Product category:

With reference to the equipment types in the WEEE directive Annex 1, this instrument is classified as a “Monitoring and Control Instrument” product.

The affixed product label is as shown below.



Do not dispose in domestic household waste.

To return this unwanted instrument, contact your nearest Keysight Service Center, or visit <http://about.keysight.com/en/companyinfo/environment/takeback.shtml> for more information.

Sales and Technical Support

To contact Keysight for sales and technical support, refer to the support links on the following Keysight websites:

- www.keysight.com/find/adapters
(product-specific information and support, software and documentation updates)
- www.keysight.com/find/assist
(worldwide contact information for repair and service)

THIS PAGE HAS BEEN INTENTIONALLY LEFT BLANK.

Table of Contents

Waste Electrical and Electronic Equipment (WEEE) Directive	3
Product category:	3
Sales and Technical Support	3
List of Tables	7
General Information	9
Description	9
Contents	9
General Characteristics	9
Equipment and Supplies	10
Mating 11878A Adapters with Precision 3.5 mm Devices	10
Mating 11878A Adapters with SMA Devices	11
Cleaning Connectors	12

THIS PAGE HAS BEEN INTENTIONALLY LEFT BLANK.

List of Tables

Table 1 Equipment and supplies 10

THIS PAGE HAS BEEN INTENTIONALLY LEFT BLANK.

General Information

- To obtain optimum performance from this adapter kit, observe these simple precautions:
- Keep the protective plastic end-caps on the adapters when not in use.
- Make connections carefully to avoid misalignment and connector damage, which will result in inaccurate measurements.
- Keep the connectors free of dirt and any particles.
- When you clean the connectors, try using compressed air first. Do not use abrasives. If further cleaning is required, refer to the *Connector Care for RF and Microwave Coaxial Connectors* document. It can be viewed online by searching for part number 08510-90064 at www.keysight.com.
- Periodically gage the adapter connectors using the instructions provided in the *Connector Care for RF and Microwave Coaxial Connectors* document. The mechanical tolerance for 3.5 mm center connector recession (male and female) is 0.0 to 0.003 inch.
- Read and follow the directions provided later in this document when mating these adapters with SMA connectors.

Description

The 11878A 50 ohm 3.5 mm adapter kit contains four type-N to precision 3.5 mm adapters. The kit is useful for testing 3.5 mm devices on a network analyzer equipped with type-N test port connectors.

Contents

The 11878A kit contains the following:

- Test port adapter, 3.5 mm (m) to type-N (m) (Keysight part number 1250-1743)
- Test port adapter, 3.5 mm (f) to type-N (m) (Keysight part number 1250-1744)
- Test port adapter, 3.5 mm (f) to type-N (f) (Keysight part number 1250-1745)
- Test port adapter, 3.5 mm (m) to type-N (f) (Keysight part number 1250-1750)
- Storage box, (Keysight part number 9211-1582)
- Storage box foam pad, (Keysight part number 11878-80003)
- *Operating and Service Manual* (Keysight part number 11878-90001)

General Characteristics

Weight

Net: 0.8 kg (1 lb. 12 oz.)

Shipping: 1.3 kg (2 lb. 12 oz.)

Equipment and Supplies

The following equipment and supplies are required for the maintenance and use of, but are not supplied with, your 11878A adapter kit.

Table 1 Equipment and supplies

Item	Part number	Recommended use
3.5 mm gage sets (part of the 85052B calibration kits)	11752-60105 (f) 11752-60106 (m)	Periodic gaging of connectors. Gage <i>every</i> SMA connector before use.
Torque wrench, 5/16", 96 N-cm (8 in-lb) (part of the 85052B calibration kit)	8710-1765	Mating two precision 3.5 mm connectors.
Torque wrench, open-end, 5/16", 60 N-cm (5 in-lb)	8710-1582	Mating a precision 3.5 mm connector to an SMA connector.
Document: <i>Connector Care for RF and Microwave Coaxial Connectors</i>	08510-90064	Following instructions on using and maintaining coaxial connectors.

Mating 11878A Adapters with Precision 3.5 mm Devices

The adapters in this kit are precision 3.5 mm connectors, and are best used with other precision 3.5 mm devices. When mating connectors, observe the following precautions:

- Push them straight together.
- Make sure the male contact pin is precisely aligned with the female.
- Do not overtighten the connectors.
- NEVER rotate either center conductor (by turning the device body).
- Only turn the outer nut of the male connector.
- Torque to 8 in-lb (96 N-cm) for the final connection.

An 8 in-lb torque wrench is available from Keysight Technologies. Refer to [“Equipment and Supplies”](#) on page 10 for the part number.

Mating 11878A Adapters with SMA Devices

CAUTION

SMA connectors are not precision devices, and are often out of mechanical tolerances even when new. Out of tolerance SMA connectors will likely ruin a precision 3.5 mm connector on the first mating. Gage SMA connectors before use.

Each adapter in this kit has a type-N connector on one end and a precision 3.5 mm connector on the other. SMA connectors will mate with precision 3.5 mm connectors. However, caution is necessary to prevent accidental damage due to worn or out-of-tolerance SMA connectors. Such connectors can destroy a precision 3.5 mm connector even on the first connection. Keysight Technologies recommends that you remember the following important information:

- SMA connectors are not precision mechanical devices.
- They are not designed for repeated connections.
- They are very susceptible to mechanical wear.
- SMA connectors are often out of mechanical tolerances when new.

Before mating an SMA connector (even a new one) to a precision 3.5 mm connector, inspect the SMA connector carefully both visually and mechanically. To measure the mechanical tolerances, use a precision connector gage. A male SMA connector pin which is too long can smash or break the delicate fingers on the precision 3.5 mm female connector, damaging it beyond possibility of repair. Gaging SMA connectors is the most important step in preventing damage to your equipment, and it takes very little time. Gaging instructions and gage part numbers are provided in the *Connector Care for RF and Microwave Coaxial Connectors* document. It can be viewed online by searching for part number 08510-90064 at www.keysight.com.

Use the following precautions when mating SMA and precision 3.5 mm connectors:

- Push them straight together.
- Make sure the male contact pin is precisely aligned with the female.
- Do not overtighten the connectors.
- NEVER rotate either center conductor (by turning the device body).
- Only turn the outer nut of the male connector.
- Torque to 5 in-lb (50 N-cm) for the final connection.

Note that the torque listed above is less than when mating two precision 3.5 mm connectors. A 5 in-lb torque wrench is available from Keysight. For the part number, refer to “[Equipment and Supplies](#)” on page 10.

Significant structural and dimensional differences exist between these two type of connectors. Precision 3.5 mm connectors use an air dielectric. Only air exists between the center and outer conductors. The male or female center conductor is supported by a plastic bead, deep within the body of the connector. In SMA connectors, a plastic dielectric supports the entire length of the center conductor. In addition, the diameters of both the inner and outer conductors differ between SMA and precision 3.5 connectors.

Using only precision 3.5 mm connectors will provide superior SWR and insertion loss. It will also extend the life of your adapters (and other test equipment connectors) by reducing mechanical wear.

Cleaning Connectors

For information on cleaning connectors, refer to the *Connector Care for RF and Microwave Coaxial Connectors* document. It can be viewed online by searching for part number 08510-90064 at www.keysight.com.



This information is subject to change without notice. Always refer to the Keysight website for the latest revision.

© Keysight Technologies 1989 - 2019
Edition 2, February 8, 2019

Printed in Malaysia



11878-90001

www.keysight.com