

# Illuminated pushbutton Ø 22 mm silver contact

82-6152.2114.B002



<https://eao.com/p/82-6152.2114.B002>

Your product:

---



## 82-6152.2114.B002

### Illuminated pushbutton Ø 22 mm silver contact

#### FRONT

**Front bezel material:** Stainless steel

#### MOUNTING

**Mounting cut-out:** Ø 22 mm

#### OPERATING-/INDICATION PART

**Illumination colour:** Red

**Shape of illumination:** Ring

**Lens shape:** flush

**Lens illumination:** illuminative

**Lens colour:** Silver

**Lens optics:** opaque

**Lens material:** Stainless steel

#### ELECTRICAL CHARACTERISTICS

**Rated Operational Voltage U<sub>e</sub>:** 250 VAC

**Operating voltage:** 24 V AC/DC

**Pollution degree:** 2, according to EN IEC 60947-1

**Electric strength:** 1500 VAC, 50 Hz 1 minute between life terminals and ground

**Contacts:** 1 C

**Rated insulation voltage U<sub>i</sub>:** 250 V

**Switching voltage and switching current:**

according to IEC 60947-5-1 (Silver contacts)

Service categorie AC-15

Voltage

24 VAC

35 VAC

110 VAC

220 VAC

Current

1 A

1 A (M12 version)

1 A

0.5 A

Switch rating DC service categorie DC-13 (Silver contacts)

Voltage

24 VDC

35 VDC

110 VDC

220 VDC

Current

0.7 A

0.5 A (M12 version)

0.2 A

0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$  0,75 ... 0,8

Voltage

120 VAC

240 VAC

24 VAC

Current

5 A

3 A

1 A

**Thermal current I<sub>th</sub>:** 5 A

**Electrical lifetime:** 50 000 cycles of operation

### MECHANICAL CHARACTERISTIC

**Terminal:** Screw terminal

**Switching action:** Maintained

**Operating Travel:** ca. 3 mm

**Tightening torque:** 0.5 ... 0.6 Nm, Screw terminal 0.1 Nm

**Contact material:** Silver

**Weight:** 0.018 kg

**Switching system:** Snap-action switching element

**Operating force:** 4 N ... 7 N

**Mechanical lifetime:** 500 000 cycles of operation

### AMBIENT CONDITION

**Climate resistance:** Damp heat, 21 days according to IEC 60512-11

**Storage temperature:** - 40 °C ... + 80 °C

**Shock resistance:** Max. 500 m / s<sup>2</sup> as per IEC 60068-2-27

**Vibration resistance:** 10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

**Operating temperature:** - 30 °C ... + 70 °C

**CERTIFICATE**

**Conformities:** CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)  
**Approbations:** CB, CCC, C UL, UL


**OTHER**

**Short Description:** Illuminated pushbutton Ø 22 mm silver contact, Maintained, 24 V AC/DC, 1 C, Screw terminal, Stainless steel, Red, Standby, Silver


**Kind of illumination:** Single-LED

**Symbol:** Standby


**Wiring diagrams:**



**Dimension drawings:**



**Mounting cut-outs:**



**Component layouts:**

