

PRODUCT-DETAILS

ACS180-04S-09A4-4

LV AC machinery drive module, IEC: Pn 4 kW, 9.4 A (ACS180-04S-09A4-4)



General Information

Global Commercial Alias	ACS180-04S-09A4-4
Product ID	3AXD50000662623
ABB Type Designation	ACS180-04S-09A4-4
Catalog Description	LV AC machinery drive module, IEC: Pn 4 kW, 9.4 A (ACS180-04S-09A4-4)

Long Description

The ACS180 is a compact, robust, and adaptable variable speed drive (VSD) for applications such as pumps, fans, compressors, conveyors, winders and mixers. This easy-to-use compact VSD offers excellent performance and quality at superior value with all essential machinery application features embedded. And as a member of ABB's all-compatible drives portfolio, it shares the same architecture and user interfaces for ease of use.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS180-04S-09A4-4 PN: 4kW, IN: 9.4A
Made To Order	No
Minimum Order Quantity	1 piece

Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	2.2 dm ³
--------------	---------------------

Dimensions

Product Net Weight	1.24 kg
Product Net Depth / Length	143 mm
Product Net Height	220 mm
Product Net Width	70 mm
Package Level 1 Depth / Length	225 mm
Package Level 1 Height	115 mm
Package Level 1 Width	220 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	7.2 A
Output Current, Light-Overload Use (I_{LD})	8.9 A
Output Current, Normal Use (I_n)	9.4 A
Output Power, Heavy-Duty Use (P_{HD})	3 kW
Output Power, Light-Overload Use (P_{LD})	4 kW
Output Power, Normal Use (P_n)	4 kW
Apparent Power Output	6.5 kV·A
Efficiency Level	IE2

Complete Drive Module
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	50 W	0.8 %	87.2 %
0 / 50 %	60 W	0.9 %	91.7 %
0 / 100 %	87 W	1.3 %	93.4 %
50 / 25 %	53 W	0.8 %	93.1 %
50 / 50 %	66 W	1.0 %	95.5 %
50 / 100 %	99 W	1.5 %	96.3 %
90 / 50 %	74 W	1.1 %	97.1 %
90 / 100 %	119 W	1.8 %	97.5 %

Temperature Rating

Maximum 40 °C

Additional Information

Product Name

FREQUENCY CONVERTER

Classifications

UNSPSC

39122001

Environmental

SCIP

5d07f008-496e-4abd-8f50-616cb485c791 Finland (FI)

WEEE Category

5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS180 - Machinery Drive

ACS180-04S-09A4-4

