



Figure similar

Data sheet for SIMOTICS M-1PH8

Article No. : 1PH8226-1DD20-0EA1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Engineering data

		P _N [kW]	M _N [Nm]	I _N [A]	U _N [V]	f _N [Hz]	n _N [rpm]	M _{max} [Nm]	I _{max} [A]	n _{max} [rpm]	M ₀ [Nm]	I ₀ [A]	η	cos φ	I _μ [A]
Y	ALM 400V	131.0	1,088.0	230.0	390	38.9	1,150	2,176	460.0	4,500	1,088.0	230	0.945	0.890	87.0
	BLM/SLM 400V	115.0	1,098.0	235.0	340	33.9	1,000	2,197	470.0	4,500	1,098.0	235	0.938	0.890	87.0
	ALM/BLM/SLM 480V	150.0	1,061.0	225.0	460	45.5	1,350	2,122	450.0	4,500	1,061.0	225	0.951	0.880	88.0

Mechanical data

Motor type	Squirrel cage asynchronous motor
Shaft height	225
Cooling	Water cooling
Vibration severity grade	A
Shaft and flange accuracy	N
Degree of protection	IP55
Design acc. to Code I	IM B3 (IM B6, IM B7, IM B8, IM V6)
Temperature monitoring	Pt1000 temperature sensor in the stator winding
Color	Standard (Anthracite RAL 7016)
Type of the bearing	Increased cantilever forces
Shaft end	Plain shaft
Encoder system	Incremental encoder 22 bit with commutation position 11 bit, max. encoder speed = 12000 rpm

Cooling water specification

pH value	6 ... 9
Total hardness	1.7 mmol/l
Electrical conductivity	2,000 μS/cm
Chloride ions	250 mg/l
Sulfate ions	240 mg/l
Nitrate ions	50 mg/l
Dissolved substances	340 mg/l
Maximum particle size	100 μm
Antifreeze/corrosion protection	20 ... 30 %

¹⁾ at a rated frequency of 2 kHz or 4 kHz and a speed range of up to 4500 rpm

Physical constants

Thermal time constant	32 min
Moment of inertia	18,950 kgcm ²
Weight (approx.)	740 kg

Connection

Type of electrical connection	Terminal box
Position of the connection	NDE top
Power connection	right
Signal connection	DE
Terminal box designation	1XB7422-P06

Cooling data and sound pressure level

Flow rate, min.	20 l/min
Sound pressure level L _{pA} (1m) motor rated load, tolerance + 3dB	70 dB ¹⁾
Pressure drop	0.6 bar
NDE thread connection	0.375 Inches