

LC1G6304LSEN

Contacteur, high power, TeSys Giga, 4P(4NO), AC-1, <=440V 1050A, standard version, 200-500V AC/DC wide band coil



Main

Range	TeSys
Range of Product	TeSys Giga
Product or Component Type	Contacteur
Device short name	LC1G
Contacteur application	Power switching
Utilisation category	AC-3 AC-3e AC-1 AC-5a AC-5b AC-6a AC-6b DC-1 DC-3 DC-5
Poles description	4P
[Ue] rated operational voltage	<= 1000 V AC 50/60 Hz <= 460 V DC
[Ie] rated operational current	630 A (at <140.0000000000 °F (60 °C)) at <= 440 V AC-3 1050 A (at <104.0000000000 °F (40 °C)) at <= 1000 V AC-1
[Uc] control circuit voltage	200...500 V AC 50/60 Hz 200...500 V DC
Control circuit voltage limits	Operational: 0.8 Uc Min...1.1 Uc Max (at <140.0000000000 °F (60 °C)) Drop-out: 0.1 Uc Max...0.45 Uc Min (at <140.0000000000 °F (60 °C))

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overtoltage category	III
[Ith] conventional free air thermal current	1050 A (at 104.0000000000 °F (40 °C))
Rated breaking capacity	5550 A at 440 V
[Icw] rated short-time withstand current	5.05 KA - 10 s 4.4 KA - 30 s 3.4 KA - 1 min 2.2 KA - 3 min 1.6 kA - 10 min
Associated fuse rating	630 A aM at <= 440 V for motor 500 A aM at <= 690 V for motor 1250 A gG at <= 690 V
Average impedance	0.000065 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	70 W AC-1 - Ith 1050 A 26 W AC-3 - Ith 630 A
Compatibility code	LC1G
Pole contact composition	4 NO
Auxiliary contact composition	1 NO + 1 NC
Irms rated making capacity	7220 A at 440 V
Coil technology	Built-in bidirectional peak limiting

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Safety reliability level	B10d = 100000 cycles contactor with nominal load EN/ISO 13849-1 B10d = 1800000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	5 Mcycles
Inrush power in VA (50/60 Hz, AC)	670 VA
Inrush power in W (DC)	390 W
Hold-in power consumption in VA (50/60 Hz, AC)	17.0 VA
Hold-in power consumption in W (DC)	11 W
Operating time	40...70 ms closing 15...50 ms opening
Maximum operating rate	600 Cyc/H AC-3 600 Cyc/H AC-3e 300 cyc/h AC-1
Connections - terminals	Power circuit: bar 2 - busbar cross section: 52 x 20 mm Power circuit: lugs-ring terminals 1 0.3 in ² (185 mm ²) Control circuit: push-in 1 0.0003...0.004 in ² (0.2...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 1 0.0004...0.004 in ² (0.25...2.5 mm ²) - cable stiffness: flexible with cable end Control circuit: push-in 2 0.0008...0.002 in ² (0.5...1.0 mm ²) with cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: flexible with cable end
Connection pitch	2.8 in (70 mm)
Mounting Support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1 UL 60335-1 UL 60335-2-40:Annex JJ
Product Certifications	CB Scheme[RETURN]CCC[RETURN]cULus[RETURN]EAC[RETURN]CE[RETURN]UKCA[RETURN] RO-MR by DNV-GL
Tightening torque	513.3 lbf.in (58 N.m)
Height	11.2 in (284 mm)
Width	11.06 in (281 mm)
Depth	10.5 in (266 mm)
Net Weight	39.7 lb(US) (18 kg)

Environment

IP degree of protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Ambient Air Temperature for Operation	-13.0000000000...140.0000000000 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76.0000000000...176.0000000000 °F (-60...80 °C)
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Color	Dark grey
Protective treatment	TH
Permissible ambient air temperature around the device	-40.0000000000...158.0000000000 °F (-40...70 °C) at Uc

Ordering and shipping details

Category	US10I1222329
Discount Schedule	0I12
GTIN	3606486392072
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.6 in (34.5 cm)
Package 1 Width	14.6 in (37 cm)
Package 1 Length	19.7 in (50 cm)
Package 1 Weight	45.4 lb(US) (20.6 kg)
Unit Type of Package 2	S06
Number of Units in Package 2	2
Package 2 Height	33.5 in (85 cm)
Package 2 Width	23.6 in (60 cm)
Package 2 Length	31.5 in (80 cm)
Package 2 Weight	113.10 lb(US) (51.3 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information