

LC1G5004LSEN

Contacteur, high power, TeSys Giga, 4P(4NO), AC-1, <=440V 700A, standard version, 200-500V AC/DC wide band coil



Main

Range	TeSys
Range of Product	TeSys Giga
Product or Component Type	Contacteur
Device short name	LC1G
Contacteur application	Power switching
Utilisation category	AC-3 AC-3e AC-1 AC-5a AC-5b AC-6a AC-6b DC-1 DC-3 DC-5
Poles description	4P
[Ue] rated operational voltage	<= 1000 V AC 50/60 Hz <= 460 V DC
[Ie] rated operational current	500 A (at <140.0000000000 °F (60 °C)) at <= 440 V AC-3 700 A (at <104.0000000000 °F (40 °C)) at <= 1000 V AC-1
[Uc] control circuit voltage	200...500 V AC 50/60 Hz 200...500 V DC
Control circuit voltage limits	Operational: 0.8 Uc Min...1.1 Uc Max (at <140.0000000000 °F (60 °C)) Drop-out: 0.1 Uc Max...0.45 Uc Min (at <140.0000000000 °F (60 °C))

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overtension category	III
[Ith] conventional free air thermal current	700 A (at 104.0000000000 °F (40 °C))
Rated breaking capacity	4600 A at 440 V
[Icw] rated short-time withstand current	4.0 kA - 10 s 2.8 kA - 30 s 2.2 kA - 1 min 1.5 kA - 3 min 1.2 kA - 10 min
Associated fuse rating	500 A aM at <= 440 V for motor 400 A aM at <= 690 V for motor 800 A aG at <= 690 V
Average impedance	0.00008 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	40 W AC-1 - Ith 700 A 20 W AC-3 - Ith 500 A
Compatibility code	LC1G
Pole contact composition	4 NO
Auxiliary contact composition	1 NO + 1 NC
Irms rated making capacity	5090 A at 440 V
Coil technology	Built-in bidirectional peak limiting

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Safety reliability level	B10d = 400000 cycles contactor with nominal load EN/ISO 13849-1 B10d = 3000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	8 Mcycles
Inrush power in VA (50/60 Hz, AC)	535 VA
Inrush power in W (DC)	300 W
Hold-in power consumption in VA (50/60 Hz, AC)	15.4 VA
Hold-in power consumption in W (DC)	8.6 W
Operating time	40...70 ms closing 15...50 ms opening
Maximum operating rate	600 Cyc/H AC-3 600 Cyc/H AC-3e 300 cyc/h AC-1
Connections - terminals	Power circuit: bar 2 - busbar cross section: 32 x 10 mm Power circuit: lugs-ring terminals 1 0.3 in ² (185 mm ²) Control circuit: push-in 1 0.0003...0.004 in ² (0.2...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 1 0.0004...0.004 in ² (0.25...2.5 mm ²) - cable stiffness: flexible with cable end Control circuit: push-in 2 0.0008...0.002 in ² (0.5...1.0 mm ²) with cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: flexible with cable end
Connection pitch	1.8 in (45 mm)
Mounting Support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1 UL 60335-1 UL 60335-2-40:Annex JJ
Product Certifications	CB Scheme[RETURN]CCC[RETURN]cULus[RETURN]EAC[RETURN]CE[RETURN]UKCA[RETURN] RO-MR by DNV-GL
Tightening torque	309.8 lbf.in (35 N.m)
Height	8.9 in (225 mm)
Width	7.3 in (185 mm)
Depth	8.9 in (226 mm)
Net Weight	18.08 lb(US) (8.2 kg)

Environment

IP degree of protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Ambient Air Temperature for Operation	-13.0000000000...140.0000000000 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76.0000000000...176.0000000000 °F (-60...80 °C)
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Color	Dark grey
Protective treatment	TH
Permissible ambient air temperature around the device	-40.0000000000...158.0000000000 °F (-40...70 °C) at Uc

Ordering and shipping details

Category	US10I1222329
Discount Schedule	0I12
GTIN	3606486392065
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.8 in (30 cm)
Package 1 Width	10.4 in (26.5 cm)
Package 1 Length	14.6 in (37 cm)
Package 1 Weight	21.396 lb(US) (9.705 kg)
Unit Type of Package 2	S06
Number of Units in Package 2	4
Package 2 Height	28.9 in (73.5 cm)
Package 2 Width	23.6 in (60 cm)
Package 2 Length	31.5 in (80 cm)
Package 2 Weight	115.644 lb(US) (52.455 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information