



Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or Component Type	Suitable enclosure
Version	PLA
Nominal height	59.06 in (1500 mm)
Nominal width	49.21 in (1250 mm)
Nominal depth	16.54 in (420 mm)
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel

Complementary

Body type	Sealed top and bottom part assembled with side parts
Door type	Solid front
Number of doors	2
Door opening side	Right and left 120 °)
Lock type	4 points lock, 5 mm double-bar
Accessibility for operation	Rear Front
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208 UL 508 A
NEMA Degree of Protection	NEMA 1 NEMA 2 NEMA 13 NEMA 12
Product Certifications	DNV Marine Veritas UL/cUL listed
Electrical Insulation Class	Class II

Environment

IP degree of protection	IP65 IEC 60529 completely sealed)
IK degree of protection	IK10 IEC 62262 plain door)
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature for Storage	-31...194 °F (-35...90 °C)

Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480774737
Returnability	Yes
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.32 in (44.0 cm)
Package 1 Width	50.00 in (127.0 cm)
Package 1 Length	59.06 in (150.0 cm)
Package 1 Weight	206.45 lb(US) (93.644 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile