

## Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	90 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

## Complementary

Maximum Horse Power Rating	7.5 Hp 115 V AC, 1 phase 20 Hp 230 V AC, 1 phase 30 Hp 230 V AC, 3 phase 50 Hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Locked rotor rated current	540 A 277 V AC 450 A 460 V AC 360 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical Connection	Quick connect terminals Box lugs
Height	5.26 in (133.60 mm) 5.3 in (134 mm)
Width	3.39 in (86.11 mm) 3.4 in (86 mm)
Depth	4.67 in (118.62 mm)
Net Weight	3.70 Lb(US) (1.68 kg) 3.7 lb(US) (1.7 kg)

## Environment

Product Certifications	UL Recognized[RETURN]CSA
------------------------	--------------------------

## Ordering and shipping details

Category	US1CP1B21349
Discount Schedule	CP1B
GTIN	785901118398
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0000000000 in (15.240 cm)
Package 1 Width	5.600 in (14.224 cm)
Package 1 Length	7.200 in (18.288 cm)
Package 1 Weight	3.680 lb(US) (1.669 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------