

10S40FSS

Low voltage transformer, encapsulated dry type, 1 phase, 10kVA, 480V primary, 120/240V secondary, Type 3R SS



Main

Product or Component Type	Dry Sealed Transformer
Primary to Secondary Voltage	480 V 120/240 V
Full Capacity Taps	2 5 % FCBN

Complementary

Enclosure Code	13B
Phase	1 phase
Power Rating	10 kVA
Temperature rise	115 °C
Height	14.75 in (374.65 mm)
Width	9.75 in (247.65 mm)
Depth	11.75 in (298.45 mm)
Enclosure mounting	Wall mounted
Net Weight	165 Lb(US) (74.84 kg) 164.99 lb(US) (74.84 kg)
Enclosure Material	Stainless Steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product Certifications	UL Listed CULus CSA

Ordering and shipping details

Category	16277-RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	785901777694
Nbr. of units in pkg.	1
Package weight(Lbs)	165.00 lb(US) (74.843 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.22 in (28.499 cm)
Package 1 width	10.24 in (26.01 cm)
Package 1 Length	13.23 in (33.604 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------