

# Product data sheet

## Characteristics

# 1.5S1FSS

Low voltage transformer, encapsulated dry type, 1 phase, 1.5kVA, 240x480V primary, 120/240V sec, Type 3R SS

### Main

|                              |                        |
|------------------------------|------------------------|
| Product or Component Type    | Dry Sealed Transformer |
| Primary to Secondary Voltage | 240 x 480 V 120/240 V  |
| Full Capacity Taps           | 0                      |

### Complementary

|                    |                     |
|--------------------|---------------------|
| Enclosure Code     | 8A                  |
| Phase              | 1 phase             |
| Power Rating       | 1.5 kVA             |
| Temperature rise   | 115 °C              |
| Height             | 8.25 in (209.55 mm) |
| Width              | 8.68 in (220.47 mm) |
| Depth              | 6.56 in (166.62 mm) |
| Enclosure mounting | Wall mounted        |
| Enclosure Material | Stainless Steel     |

### Environment

|                        |                           |
|------------------------|---------------------------|
| Enclosure Type         | NEMA 3R                   |
| Insulation temperature | 356 °F (180 °C)           |
| Product Certifications | UL Listed<br>CULus<br>CSA |

### Ordering and shipping details

|                       |                        |
|-----------------------|------------------------|
| Category              | 16277-RESIN LVGP XFMR  |
| Discount Schedule     | PE2                    |
| GTIN                  | 785901140894           |
| Nbr. of units in pkg. | 1                      |
| Package weight(Lbs)   | 30.1 lb(US) (13.65 kg) |
| Returnability         | No                     |
| Country of origin     | US                     |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| PVC free                   | Yes   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|