



## Main

Product	Double Throw Safety Switch
Duty Rating	Heavy duty
Disconnect Type	Fusible disconnect
Factory Installed Neutral	None
Number of Poles	3
Current Rating	30 A
Voltage Rating	600 V AC 600 V DC
Enclosure Rating	NEMA 1
Motor power hp	5 Hp at 480 V AC 50-60 Hz for 3 phase motors 15 Hp at 480 V AC 50-60 Hz for 3 phase motors 7.5 Hp at 600 V AC 50-60 Hz for 1 phase motors 20 Hp at 600 V AC 50-60 Hz for 3 phase motors 5 Hp at 250 V DC 15 hp at 600 V DC

## Complementary

Short-circuit current	10 KA H or K 200 kA R or J
Fuse type	H or K R or J
Mounting Type	Surface
Wire Size	AWG 12...AWG 2 aluminium AWG 14...AWG 2 copper
Tightening torque	35 Lbf.In (4.0 N.m) 0.003...0.008 in <sup>2</sup> (2.08...5.26 mm <sup>2</sup> ) (AWG 14...AWG 10) 40 Lbf.In (4.5 N.m) 0.01 in <sup>2</sup> (8.37 mm <sup>2</sup> ) (AWG 8) 45 Lbf.In (5.08 N.m) 0.02...0.03 in <sup>2</sup> (13.3...21.15 mm <sup>2</sup> ) (AWG 6...AWG 4) 50 lbf.in (5.6 N.m) 0.04...0.05 in <sup>2</sup> (26.67...33.62 mm <sup>2</sup> ) (AWG 3...AWG 2)
Depth	6.75 in (171.45 mm)
Width	11.5 in (292.1 mm)
Height	38 in (965.2 mm)
Net Weight	45.0 lb(US) (20.4 kg)

## Environment

Certifications	UL Listed
----------------	-----------

## Ordering and shipping details

Category	US10DE100033
Discount Schedule	0DE1
GTIN	785901308447
Returnability	Yes
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	40.0000000000 in (101.6 cm)
Package 1 Width	10.0000000000 in (25.4 cm)
Package 1 Length	12.125 in (30.797 cm)
Package 1 Weight	45.0008 lb(US) (20.412 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------