



Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Surface cover

Complementary

Tightening Torque	Main lugs 35 lb.in, AWG 14...AWG 10, aluminium/copper Main lugs 35 lb.in, AWG 12...AWG10, aluminium/copper
PoN Convertible Mains (lugs)	Fixed Mains (lugs)
Rated Current	30 A
Number of Spaces	2
Max Short Circuit Current Rating	10 kA
Maximum Number of Single Pole Circuits	2
Maximum Number of Tandem Breakers	0
Number of Phases	1 phase 3 wires
Voltage Rating	120/240 V AC
Wire Size	AWG 14...AWG 10 copper AWG 12...AWG10 aluminium
Ground Bar	Grounding bar (ordered separately)
Electrical Connection	Lugs
Busbar Material	Tin plated aluminium: busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel Gray
Box Number	1
Height	6.7 in (171 mm)
Width	3.8 in (97 mm)

Environment

Enclosure Rating	NEMA 1 indoor enclosure
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

Ordering and shipping details

Category	US1DE3A00101
Discount Schedule	DE3A
GTIN	785901785071
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.100 in (10.414 cm)
Package 1 Width	4.350 in (11.049 cm)
Package 1 Length	7.600 in (19.304 cm)
Package 1 Weight	33.599 oz (952.543 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	388
Package 2 Height	40.0000000000 in (101.600 cm)
Package 2 Width	40.0000000000 in (101.600 cm)
Package 2 Length	48.0000000000 in (121.920 cm)
Package 2 Weight	819.0003 lb(US) (371.492 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------