

product type designation



RF260R reader IO-Link

SIMATIC RF200 reader RF260R IO-Link interface V1.1; IP67, -25 to +70 °C; 75x 75x 40 mm; with integrated antenna 32 Byte IO; 230 Kbit/s

suitability for operation

ISO 15693 transponder (MDS Dxxx), for connecting to IO-Link Master V1.1

radio frequencies

operating frequency / rated value	13.56 MHz
range / maximum	135 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964
protocol / with radio transmission	ISO 15693, ISO 18000-3
transfer rate / with radio transmission / maximum	26.5 kbit/s
product feature / multitag-capable	No

electrical data

transfer rate / at the point-to-point connection / serial / maximum	230 kbit/s
transmission time / for user data	
• for write access / per byte / typical	3.3 ms
• for read access / per byte / typical	2.4 ms
data volume / of the address range of the inputs / total	32 byte
data volume / of the address range of the outputs / total	32 byte

interfaces

standard for interfaces / for communication	IO-Link V1.1
type of electrical connection	M12, 4-pin

mechanical data

material	PA6.6
color	anthracite
tightening torque / of the screw for securing the equipment / maximum	1.5 N·m
mounting distance / relating to metal surfaces / recommended / minimum	0 mm

supply voltage, current consumption, power loss

supply voltage / at DC	
• rated value	24 V
•	20.4 ... 28.8 V
consumed current / at DC	
• at 24 V / typical	0.05 A

ambient conditions

ambient temperature	
• during operation	-20 ... +70 °C
• during storage	-25 ... +80 °C
• during transport	-25 ... +80 °C
protection class IP	IP67
shock resistance	EN 60721-3-7 Class 7 M2
shock acceleration	500 m/s ²
vibrational acceleration	200 m/s ²

design, dimensions and weights	
width	75 mm
height	41 mm
depth	75 mm
net weight	0.2 kg
fastening method	2 x M5 screws
wire length	
<ul style="list-style-type: none"> • between master and IO-Link device / maximum 	20 m

product features, product functions, product components / general	
display version	3-color LED
product feature / silicon-free	Yes

standards, specifications, approvals	
certificate of suitability	Radio according to R&TTE guidelines EN300 330 and EN 301489, FCC, cULus
certificate of suitability	
<ul style="list-style-type: none"> • IECEx 	No
MTBF	480 a
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	BYB

standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
Global Warming Potential [CO2 eq]	
<ul style="list-style-type: none"> • total 	124.25 kg
<ul style="list-style-type: none"> • during manufacturing 	11.24 kg
<ul style="list-style-type: none"> • during operation 	112.71 kg
<ul style="list-style-type: none"> • after end of life 	0.3 kg

further information / internet links	
internet link	
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to web page: RFID country approval • to web page: identification and localization systems • to web page: SiePortal • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/rfid-approvals https://www.siemens.com/ident https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com

security information	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>

Approvals / Certificates		
General Product Approval	Radio Equipment Type Approval Certificate	Environment



[Miscellaneous](#)



last modified:

8/18/2024 