

### **Article Information Sheet**

Copyright, 2021, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

This Article Information Sheet is provided as a courtesy in response to a customer request. A Safety Data Sheet (SDS) has not been prepared for these product(s) because they are articles. Articles are not subject to the Occupational Safety and Health Administration's Hazard Communication Standard (29 CFR 1910.1200(b)(6)(v)). As defined in this standard: "Article" means a manufactured item other than a fluid or particle: (i) which is formed to a specific shape or design during manufacture; (ii) which has end use function(s) dependent in whole or in part upon its shape or design during end use; and (iii) which under normal conditions of use does not release more than very small quantities, e.g., minute or trace amounts of a hazardous chemical, and does not pose a physical hazard or health risk to employees.

 Document Group:
 29-6614-1
 Version Number:
 1.04

 Issue Date:
 04/30/21
 Supercedes Date:
 08/29/17

## **SECTION 1: Identification**

#### 1.1. Product identifier

3M<sup>TM</sup> Scotchlok<sup>TM</sup> Aluminum Compression Connectors, 20000 Series

#### 1.2. Recommended use and restrictions on use

#### Recommended use

Electrical

#### 1.3. Supplier's details

MANUFACTURER: 3M

**DIVISION:** Electrical Markets Division

**ADDRESS:** 3M Center, St. Paul, MN 55144-1000, USA **Telephone:** 1-888-3M HELPS (1-888-364-3577)

#### 1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

## **SECTION 2: Hazard identification**

This product is exempt from hazard classification according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

# **SECTION 3: Composition/information on ingredients**

Ingredient	C.A.S. No.	% by Wt
Aluminum with Tin Plating	Mixture	100

## **SECTION 4: First aid measures**

#### 4.1. Description of first aid measures

Page 1 of 4

#### **Inhalation:**

No need for first aid is anticipated.

#### **Skin Contact:**

No need for first aid is anticipated.

#### **Eve Contact:**

No need for first aid is anticipated.

#### If Swallowed:

No need for first aid is anticipated.

# **SECTION 5: Fire-fighting measures**

In case of fire: Use a carbon dioxide or dry chemical extinguisher to extinguish.

## **SECTION 6: Accidental release measures**

#### 6.1. Personal precautions, protective equipment and emergency procedures

Not applicable.

## 6.2. Environmental precautions

Not applicable.

### 6.3. Methods and material for containment and cleaning up

Not applicable.

# **SECTION 7: Handling and storage**

#### 7.1. Precautions for safe handling

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions.

### 7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

# **SECTION 8: Exposure controls/personal protection**

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions. No engineering controls or personal protective equipment (PPE) are necessary.

# **SECTION 9: Physical and chemical properties**

### 9.1. Information on basic physical and chemical properties

**Appearance** 

Physical stateSolidColorGray

Odor Metallic
Odor threshold Not Applicable
pH Not Applicable

Melting point Not Applicable **Boiling Point** Not Applicable Flash Point No flash point **Evaporation rate** Not Applicable Flammability (solid, gas) Not Classified Flammable Limits(LEL) Not Applicable Flammable Limits(UEL) Not Applicable Vapor Pressure Not Applicable **Density** No Data Available **Specific Gravity** No Data Available

Solubility in Water Nil

Autoignition temperatureNot ApplicableDecomposition temperatureNot ApplicableViscosityNot ApplicableVolatile Organic CompoundsNo Data AvailablePercent volatileNo Data AvailableVOC Less H2O & Exempt SolventsNo Data Available

## **SECTION 10: Stability and reactivity**

This material is considered to be non reactive under normal use conditions.

# **SECTION 11: Toxicological information**

#### Inhalation:

No health effects are expected

#### **Skin Contact:**

No health effects are expected

### **Eye Contact:**

No health effects are expected

#### **Ingestion:**

No health effects are expected

#### **Additional Information:**

This product, when used under reasonable conditions and in accordance with the directions for use, should not present a health hazard. However, use or processing of the product in a manner not in accordance with the product's directions for use may affect the performance of the product and may present potential health and safety hazards.

# **SECTION 12: Ecological information**

This article is expected to present a low environmental risk either because use and disposal are unlikely to result in a significant release of components to the environment or because those components that may be released are expected to have insignificant environmental impact.

# **SECTION 13: Disposal considerations**

Dispose of contents/container in accordance with the local/regional/national/international regulations.

# **SECTION 14: Transport Information**

For Transport Information, please visit http://3M.com/Transportinfo or call 1-800-364-3577 or 651-737-6501.

## **SECTION 15: Regulatory information**

#### **Chemical Inventories**

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory requirements.

### **SECTION 16: Other information**

 Document Group:
 29-6614-1
 Version Number:
 1.04

 Issue Date:
 04/30/21
 Supercedes Date:
 08/29/17

DISCLAIMER: The information in this Article Information Sheet (AIS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the AIS available directly from 3M

3M USA AISs are available at www.3M.com