

# ST

Technical Data Sheet

# VA8040

*Environmental Meter  
Moisture meter*



## Product Features

<b>Material</b>	Ideal for total 7 building materials:
	1(Hard wood): 8.9~95.7%
	2(Soft wood): 7.1~80.0%
	3(Cement): 1.0~2.5%
	4(Anhydrite plane): 0.0~3.3%
	5(Cement mortar): 0.7~3.8%
	6(Lime mortar): 0.58~7.4%
7(Bricks): 0.0~23.4%	
<b>Power supply</b>	3x1.5V AAA battery
<b>Dimension</b>	121 x 60 x 30 mm (4.76x2.36x1.18 inch)

## Product Specifications

<b>Measurement Range</b>	0.0%~95.7%, -10~+50°C / °F
<b>Accuracy</b>	Conductivity measurement: $\pm 2\%$ Temperature: $\pm 1^\circ\text{C}$ , $\pm 1^\circ\text{F}$
<b>Resolution</b>	0.1%, 0.1°C, 0.1°F
<b>Probe type</b>	Insert



**sifam tinsley**  
PRECISION INSTRUMENTATION

**Sifam Tinsley Instrumentation Inc.**  
2105 Barrett Park Drive, Unit 105  
Kennesaw, GA 30144 (USA)  
**E-mail Id :** [psk@sifamtinsley.com](mailto:psk@sifamtinsley.com)  
**Web :** [www.sifamtinsley.com](http://www.sifamtinsley.com)  
**Contact No. :** +1 678 881 0008 / 800 879 6171