


Power Terminal Block

145x606

Replace "x" with 1, 2 or 3 for number of poles.



Wire Range

- Line: 1/2 - 13 X 1 5/16 stud
- Load: 1/2 - 13 X 1 5/16 stud

Electrical Ratings

- 410 Amps
- 600V per UL 1953 & CSA 22.2 No.158, Class B & C requirements
- SCCR of 10,000 A (default for terminal blocks).
- Factory & Field Wiring


Agency Compliance

- cULus - UL Listed, investigated to UL 1953, UL File QPOS.E309401 and UL evaluated to CSA 22.2 No 158 File no. QPOS7.309401
- CSA - certified to C22.2 No. 158, File No. LR19766


Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: copper, tin plated
- Threaded stud: steel, tin plated
- Hex nut: brass, tin plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

Termination Specifications

Line Side	Termination Type	Torque	Stud Length	Maximum Lug/Bar Width
	Listed lugs on 1/2 - 13 stud	47.7 N·m (422 lbf·in)	1 5/16" (33mm)	2.25" (57mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.
- Hex nut provided: 9/16 across flats

Load Side	Termination Type	Torque	Stud Length	Maximum Lug/Bar Width
	Listed lugs on 1/2 - 13 stud	47.7 N·m (422 lbf·in)	1 5/16" (33mm)	2.25" (57mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.
- Hex nut provided: 9/16 across flats

Installation & Accessories

- Mounting (Panel):
 - For use with 1/4 fastener.
 - Mounting torque to be determined in end use application not to exceed 40 lbf-in (4.5 Nm)

- Covers:
 - Snap on cover available upon request
 - Catalog number:
 - For 3 pole (1453xxx), CC1453
 - For 2 pole (1452xxx), CC1452
 - For 1 pole (1451xxx), CC1451
 - Cover is black thermoplastic

Drawing

