


Actuator

51-
252.026



<https://eao.com/p/51-252.026>

Your product:



51-252.026 Actuator

FRONT

Front dimension: Ø 24,5 mm

MOUNTING

Design: raised

OPERATING-/INDICATION PART

Lens shape: mushroom-head

Lens illumination: non illuminative

Lens material: Plastic

Lens colour: Red

Lens optics: opaque

ELECTRICAL CHARACTERISTICS

Switching voltage and switching current: 100 mA at 42 VAC/VDC

Contacts: 2 NC

MECHANICAL CHARACTERISTIC

Mechanical lifetime: 1 Mio. cycles of operation

Operating Travel: 3 mm

Operating force: 1,8 ... 3,5 N

Contact material: Gold

Switching system: This low-level switching element was designed for switching low powers in electronic circuits. The mechanism assures reliable switching of loads ranging from

a few $\mu\text{A}/\mu\text{V}$ up to 100 mA/ 42 VAC/DC.

Single-break momentary contact, as normally open or normally closed with 4 independent points of contact. 2 momentary contacts per switching element; combination of normally open and normally closed is possible.

Special features are the long life, extremely short rebound time and stable contact resistance.


Tightening torque:	Fixing nut max. 0.5 Nm
Switching action:	Maintained
Terminal:	Universal terminal, 2 x 0.5 mm
Switching system:	Low-level element
Weight:	0.011 kg

AMBIENT CONDITION


Storage temperature:	- 40 °C ... + 85 °C
IP front protection:	IP65, according to DIN EN 60529
Operating temperature:	- 25 °C ... + 55 °C

OTHER

Housing colour:	Black
Short Description:	Actuator, \varnothing 24,5 mm, mushroom-head, non illuminative, Red, Plastic, opaque, 2 NC, Maintained, Universal terminal, 2 x 0.5 mm, IP65, according to DIN EN 60529
Hints:	Marking arrows
Mounting cut-outs:	



Dimension drawings:



Wiring diagrams:

