

Data sheet for SIMOTICS S-1FK7

MLFB-Ordering data

1FK7080-2AH71-1BA2



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data			
Rated speed (100 K)	4500 rpm	Motor type	Permanent-magnet synchronous motor		
Number of poles	8	Motor type	Compact		
Rated torque (100 K)	4.5 Nm	Shaft height	80		
Rated current	4.8 A	Cooling	Natural cooling		
Static torque (60 K)	6.60 Nm	Radial runout tolerance	0.050 mm		
Static torque (100 K)	8.00 Nm	Concentricity tolerance	0.10 mm		
Stall current (60 K)	6.00 A	Axial runout tolerance	0.10 mm		
Stall current (100 K)	7.40 A	Vibration severity grade	Grade A		
Moment of inertia	14.200 kgcm ²	Connector size	1		
Efficiency	92.0 %	Degree of protection	IP65 and DE flange IP67		
<th colspan="2">Physical constants</th>		Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)
		Torque constant	1.08 Nm/A	Temperature monitoring	Pt1000 temperature sensor
		Voltage constant at 20° C	68.5 V/1000*min ⁻¹	Electrical connectors	Connectors for signals and power rotatable
		Winding resistance at 20° C	0.42 Ω	Color of the housing	Standard (Anthracite RAL 7016)
		Rotating field inductance	7.3 mH	Holding brake	without holding brake
		Electrical time constant	17.30 ms	Shaft end	Feather key
		Mechanical time constant	1.54 ms	Encoder system	Encoder AS24DQI: absolute encoder single-turn 24 bits
		Thermal time constant	40 min		
		Shaft torsional stiffness	120000 Nm/rad		
		Net weight of the motor	10.3 kg		



Figure similar

MLFB-Ordering data

1FK7080-2AH71-1BA2

Optimum operating point		Recommended Motor Module	
Optimum speed	4000 rpm	Rated inverter current	9 A
Optimum power	2.4 kW	Maximum inverter current	27 A
Limiting data		Maximum torque	24.70 Nm
Max. permissible speed (mech.)	6000 rpm		
Max. permissible speed (inverter)	6000 rpm		
Maximum torque	25.0 Nm		
Maximum current	27.5 A		