

LC1G330LSEN

Contacteur, high power, TeSys Giga, 3P(3NO), AC-3, <=440V 330A, standard version, 200-500V AC/DC wide band coil



Main

Range	TeSys
Range of Product	TeSys Giga
Product or Component Type	Contacteur
Device short name	LC1G
Contacteur application	Power switching Motor control
Utilisation category	AC-1 AC-3 AC-3e AC-4 AC-5a AC-5b AC-6a AC-6b AC-8a AC-8b DC-1 DC-3 DC-5
Poles description	3P
[Ue] rated operational voltage	<= 1000 V AC 50/60 Hz <= 460 V DC
[Ie] rated operational current	440 A (at <104.0000000000 °F (40 °C)) at <= 1000 V AC-1 330 A (at <140.0000000000 °F (60 °C)) at <= 440 V AC-3
[Uc] control circuit voltage	200...500 V AC 50/60 Hz 200...500 V DC
Control circuit voltage limits	Operational: 0.8 Uc Min...1.1 Uc Max (at <140.0000000000 °F (60 °C)) Drop-out: 0.1 Uc Max...0.45 Uc Min (at <140.0000000000 °F (60 °C))

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	440 A (at 104.0000000000 °F (40 °C))
Rated breaking capacity	2940 A at 440 V
[Icw] rated short-time withstand current	2.65 kA - 10 s 1.8 kA - 30 s 1.3 kA - 1 min 0.9 kA - 3 min 0.75 kA - 10 min
Associated fuse rating	400 A aM at <= 440 V for motor 250 A aM at <= 690 V for motor 500 A gG at <= 690 V
Average impedance	0.000144 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	30 W AC-1 - Ith 440 A 16 W AC-3 - Ith 330 A
Compatibility code	LC1G
Pole contact composition	3 NO

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Auxiliary contact composition	1 NO + 1 NC
Motor power kW	90 KW at 230 V AC 50/60 Hz (AC-3e) 160 KW at 400 V AC 50/60 Hz (AC-3e) 160 KW at 415 V AC 50/60 Hz (AC-3e) 185 KW at 440 V AC 50/60 Hz (AC-3e) 200 KW at 500 V AC 50/60 Hz (AC-3e) 220 KW at 690 V AC 50/60 Hz (AC-3e) 185 KW at 1000 V AC 50/60 Hz (AC-3e) 90 KW at 230 V AC 50/60 Hz (AC-3) 160 KW at 400 V AC 50/60 Hz (AC-3) 160 KW at 415 V AC 50/60 Hz (AC-3) 200 KW at 440 V AC 50/60 Hz (AC-3) 200 KW at 500 V AC 50/60 Hz (AC-3) 220 KW at 690 V AC 50/60 Hz (AC-3) 185 KW at 1000 V AC 50/60 Hz (AC-3) 90 KW at 230 V AC 50/60 Hz (AC-4) 160 KW at 400 V AC 50/60 Hz (AC-4) 160 KW at 415 V AC 50/60 Hz (AC-4) 185 KW at 440 V AC 50/60 Hz (AC-4) 200 KW at 500 V AC 50/60 Hz (AC-4) 220 KW at 690 V AC 50/60 Hz (AC-4) 185 kW at 1000 V AC 50/60 Hz (AC-4)
Maximum Horse Power Rating	100 Hp at 200/208 V 60 Hz 125 Hp at 230/240 V 60 Hz 250 Hp at 460/480 V 60 Hz 300 hp at 575/600 V 60 Hz
Irms rated making capacity	3830 A at 440 V
Coil technology	Built-in bidirectional peak limiting
Safety reliability level	B10d = 400000 cycles contactor with nominal load EN/ISO 13849-1 B10d = 3000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	8 Mcycles
Inrush power in VA (50/60 Hz, AC)	530 VA
Inrush power in W (DC)	300 W
Hold-in power consumption in VA (50/60 Hz, AC)	16.1 VA
Hold-in power consumption in W (DC)	9 W
Operating time	40...70 ms closing 15...50 ms opening
Maximum operating rate	600 Cyc/H AC-3 600 Cyc/H AC-3e 300 Cyc/H AC-1 150 cyc/h AC-4
Connections - terminals	Power circuit: bar 2 - busbar cross section: 32 x 10 mm Power circuit: lugs-ring terminals 1 0.3 in ² (185 mm ²) Power circuit: bolted connection Control circuit: push-in 1 0.0003...0.004 in ² (0.2...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 1 0.0004...0.004 in ² (0.25...2.5 mm ²) - cable stiffness: flexible with cable end Control circuit: push-in 2 0.0008...0.002 in ² (0.5...1.0 mm ²) with cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: flexible with cable end
Connection pitch	1.8 in (45 mm)
Mounting Support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1 IEC 60335-1:Clause 30.2 IEC 60335-2-40:Annex JJ UL 60335-1 UL 60335-2-40:Annex JJ
Product Certifications	CB Scheme[RETURN]CCC[RETURN]cULus[RETURN]EAC[RETURN]CE[RETURN]UKCA[RETURN] RO-MR by DNV-GL
Tightening torque	309.8 lbf.in (35 N.m)
Height	8.9 in (225 mm)
Width	5.5 in (140 mm)

Depth	8.9 in (226 mm)
Net Weight	16.5 lb(US) (7.5 kg)

Environment

IP degree of protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Ambient Air Temperature for Operation	-13.0000000000...140.0000000000 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76.0000000000...176.0000000000 °F (-60...80 °C)
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Color	Dark grey
Protective treatment	TH
Permissible ambient air temperature around the device	-40.0000000000...158.0000000000 °F (-40...70 °C) at Uc

Ordering and shipping details

Category	US10I1222329
Discount Schedule	0I12
GTIN	3606486391945
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.8 in (30 cm)
Package 1 Width	8.7 in (22 cm)
Package 1 Length	14.6 in (37 cm)
Package 1 Weight	16.42 lb(US) (7.45 kg)
Unit Type of Package 2	S06
Number of Units in Package 2	4
Package 2 Height	28.9 in (73.5 cm)
Package 2 Width	23.6 in (60 cm)
Package 2 Length	31.5 in (80 cm)
Package 2 Weight	95.758 lb(US) (43.435 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information