

LC1G8004KUEN

Contactor, high power, TeSys Giga 800, standard version, 4 pole/NO, AC-1 $\leq 440V$ 1050A, 100-250VAC/DC coil



Main

Range	TeSys
Range of Product	TeSys Giga
Product or Component Type	Contacteur
Device short name	LC1G
Contacteur application	Power switching
Utilisation category	AC-3 AC-3e AC-1 AC-5a AC-5b AC-6a AC-6b DC-1 DC-3 DC-5
Poles description	4P
[Ue] rated operational voltage	≤ 1000 V AC 50/60 Hz ≤ 460 V DC
[Ie] rated operational current	800 A (at <140.0000000000 °F (60 °C)) at ≤ 440 V AC-3 1050 A (at <104.0000000000 °F (40 °C)) at ≤ 1000 V AC-1
[Uc] control circuit voltage	100...250 V AC 50/60 Hz 100...250 V DC
Control circuit voltage limits	Operational: 0.8 Uc Min...1.1 Uc Max (at <140.0000000000 °F (60 °C)) Drop-out: 0.1 Uc Max...0.45 Uc Min (at <140.0000000000 °F (60 °C))

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overtoltage category	III
[Ith] conventional free air thermal current	1050 A (at 104.0000000000 °F (40 °C))
Rated breaking capacity	5870 A at 440 V
[Icw] rated short-time withstand current	5.5 kA - 10 s 4.6 kA - 30 s 3.6 kA - 1 min 2.6 kA - 3 min 1.7 kA - 10 min
Associated fuse rating	800 A aM at ≤ 440 V for motor 630 A aM at ≤ 690 V for motor 1250 A gG at ≤ 690 V
Average impedance	0.000065 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	70 W AC-1 - Ith 1050 A 42 W AC-3 - Ith 800 A
Compatibility code	LC1G
Pole contact composition	4 NO
Auxiliary contact composition	1 NO + 1 NC
Irms rated making capacity	7640 A at 440 V
Coil technology	Built-in bidirectional peak limiting

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Safety reliability level	B10d = 100000 cycles contactor with nominal load EN/ISO 13849-1 B10d = 1800000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	5 Mcycles
Inrush power in VA (50/60 Hz, AC)	800 VA
Inrush power in W (DC)	680 W
Hold-in power consumption in VA (50/60 Hz, AC)	15.0 VA
Hold-in power consumption in W (DC)	9.5 W
Operating time	40...70 ms closing 15...50 ms opening
Maximum operating rate	600 Cyc/H AC-3 600 Cyc/H AC-3e 300 cyc/h AC-1
Connections - terminals	Power circuit: bar 2 - busbar cross section: 52 x 20 mm Power circuit: lugs-ring terminals 1 0.3 in ² (185 mm ²) Power circuit: bolted connection Control circuit: push-in 1 0.0003...0.004 in ² (0.2...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 1 0.0004...0.004 in ² (0.25...2.5 mm ²) - cable stiffness: flexible with cable end Control circuit: push-in 2 0.0008...0.002 in ² (0.5...1.0 mm ²) with cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: solid stranded without cable end Control circuit: push-in 0.001...0.004 in ² (0.75...2.5 mm ²) - cable stiffness: flexible with cable end
Connection pitch	2.8 in (70 mm)
Mounting Support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1 UL 60335-1 UL 60335-2-40:Annex JJ
Product Certifications	CB Scheme[RETURN]CCC[RETURN]cULus[RETURN]EAC[RETURN]CE[RETURN]UKCA[RETURN] RO-MR by DNV-GL
Tightening torque	513.3 lbf.in (58 N.m)
Height	11.2 in (284 mm)
Width	11.06 in (281 mm)
Depth	10.5 in (266 mm)
Net Weight	39.7 lb(US) (18 kg)

Environment

IP degree of protection	IP2X front face with shrouds IEC 60529 IP2X front face with shrouds VDE 0106
Ambient Air Temperature for Operation	-13.0000000000...140.0000000000 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76.0000000000...176.0000000000 °F (-60...80 °C)
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Color	Dark grey
Protective treatment	TH
Permissible ambient air temperature around the device	-40.0000000000...158.0000000000 °F (-40...70 °C) at Uc

Ordering and shipping details

Category	US10I1222329
Discount Schedule	0I12
GTIN	3606481922212
Returnability	Yes
Country of origin	SG

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.780 in (35.000 cm)
Package 1 Width	14.567 in (37.000 cm)
Package 1 Length	20.079 in (51.000 cm)
Package 1 Weight	45.834 lb(US) (20.790 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	2
Package 2 Height	29.528 in (75.000 cm)
Package 2 Width	31.496 in (80.000 cm)
Package 2 Length	25.591 in (65.000 cm)
Package 2 Weight	119.050 lb(US) (54.000 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product