

NDX.Q | Square end-caps for tubes

Technopolymer

INCH

RoHS

PA

+212 °F
-22 °F

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

MATERIAL

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.


STANDARD EXECUTION

Nickel-plated brass boss with threaded pass-through hole.



NDX.Q - 20 - 25 - 30 - 35 - 40

NDX.Q - 50 - 60



INCH

Code	Description	L	d	h	H	h1	l	Tube external diameter	Tube internal diameter	Thickness	Tube size	Max. static load* [lbf]	⚖️
90320082	NDX.Q-1-1/2x0,065-B 3/8-16	1.5	3/8-16	0.39	1.5	0.31	1.37	1.5	1.37	0.06	1 - 1/2'	1344	0.1
90320083	NDX.Q-1-1/2x0,065-B 1/2-13	1.5	1/2-13	0.39	1.5	0.31	1.37	1.5	1.37	0.06	1 - 1/2'	1344	0.1
90320085	NDX.Q-1-1/2x0,065-B 5/8-11	1.5	5/8-11	0.59	1.5	0.31	1.37	1.5	1.37	0.06	1 - 1/2'	1344	0.11
90320086	NDX.Q-1-1/2x0,065-B 3/4-10	1.5	3/4-10	0.79	1.5	0.31	1.37	1.5	1.37	0.06	1 - 1/2'	1792	0.11
90320102	NDX.Q-1-1/2x0,120-B 3/8-16	1.5	3/8-16	0.39	1.5	0.31	1.26	1.5	1.26	0.12	1 - 1/2'	1344	0.1
90320103	NDX.Q-1-1/2x0,120-B 1/2-13	1.5	1/2-13	0.39	1.5	0.31	1.26	1.5	1.26	0.12	1 - 1/2'	1344	0.1
90320105	NDX.Q-1-1/2x0,120-B 5/8-11	1.5	5/8-11	0.59	1.5	0.31	1.26	1.5	1.26	0.12	1 - 1/2'	1344	0.11
90320106	NDX.Q-1-1/2x0,120-B 3/4-10	1.5	3/4-10	0.79	1.5	0.31	1.26	1.5	1.26	0.12	1 - 1/2'	1792	0.11
90320122	NDX.Q-2x0,065-B 3/8-16	2	3/8-16	0.39	1.77	0.39	1.88	2.01	1.88	0.06	2"	1344	0.16
90320123	NDX.Q-2x0,065-B 1/2-13	2	1/2-13	0.39	1.77	0.39	1.88	2.01	1.88	0.06	2"	1344	0.16
90320125	NDX.Q-2x0,065-B 5/8-11	2	5/8-11	0.59	1.77	0.39	1.88	2.01	1.88	0.06	2"	1344	0.16
90320126	NDX.Q-2x0,065-B 3/4-10	2	3/4-10	0.79	1.77	0.39	1.88	2.01	1.88	0.06	2"	1904	0.16
90320132	NDX.Q-2x0,109-B 3/8-16	2	3/8-16	0.39	1.77	0.39	1.77	2.01	1.77	0.11+0.12	2"	1344	0.16
90320133	NDX.Q-2x0,109-B 1/2-13	2	1/2-13	0.39	1.77	0.39	1.77	2.01	1.77	0.11+0.12	2"	1344	0.16
90320135	NDX.Q-2x0,109-B 5/8-11	2	5/8-11	0.59	1.77	0.39	1.77	2.01	1.77	0.11+0.12	2"	1344	0.16
90320136	NDX.Q-2x0,109-B 3/4-10	2	3/4-10	0.79	1.77	0.39	1.77	2.01	1.77	0.11+0.12	2"	1904	0.16

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

Levelling elements and supports