

## Main

Range of Product	PowerPact M PowerPact P
Product or Component Type	Mechanical lug
Accessory / separate part category	Connection accessory
Circuit breaker name	PowerPact M or P
Quantity per Set	Set of 3
Circuit breaker type	Standard

## Complementary

Line Rated Current	800 A
Material	Copper
Mounting Mode	Unit mount I-Line
Location of connection	Downstream Upstream
AWG gauge	AWG 3/0...500 kcmil copper
Kcmil size	500 kcmil
Tightening torque	442.5 lbf.in (50 N.m) 0.1...0.4 in <sup>2</sup> (95...240 mm <sup>2</sup> ) (AWG 3/0...500 kcmil)

## Environment

Product Certifications	UL[RETURN]CSA
------------------------	---------------

## Ordering and shipping details

Category	US10DE201250
Discount Schedule	0DE2
GTIN	785901837749
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 in (7.6 cm)
Package 1 Width	5.2 in (13.2 cm)
Package 1 Length	12.5 in (31.8 cm)
Package 1 Weight	5.00009 lb(US) (2.268 kg)

## Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------