



Figure similar

MLFB-Ordering data

1FK7080-2AH71-1QG2

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Engineering data

Rated speed (100 K) 4500 rpm

Number of poles 8

Rated torque (100 K) 4.5 Nm

Rated current 4.8 A

Static torque (60 K) 6.60 Nm

Static torque (100 K) 8.00 Nm

Stall current (60 K) 6.00 A

Stall current (100 K) 7.40 A

Moment of inertia 14.200 kgcm<sup>2</sup>

Efficiency 92.0 %

### Physical constants

Torque constant 1.08 Nm/A

Voltage constant at 20° C 68.5 V/1000\*min<sup>-1</sup>

Winding resistance at 20° C 0.42 Ω

Rotating field inductance 7.3 mH

Electrical time constant 17.30 ms

Mechanical time constant 1.54 ms

Thermal time constant 40 min

Shaft torsional stiffness 120000 Nm/rad

Net weight of the motor 10.3 kg

### Mechanical data

Motor type Permanent-magnet synchronous motor

Motor type Compact

Shaft height 80

Cooling Natural cooling

Radial runout tolerance 0.050 mm

Concentricity tolerance 0.10 mm

Axial runout tolerance 0.10 mm

Vibration severity grade Grade A

Connector size 1

Degree of protection IP65 and DE flange IP67

Design acc. to Code I IM B5 (IM V1, IM V3)

Temperature monitoring Pt1000 temperature sensor

Electrical connectors Connectors for signals and power rotatable

Color of the housing Standard (Anthracite RAL 7016)

Holding brake without holding brake

Shaft end Plain shaft

Encoder system Encoder AS20DQI: absolute encoder single-turn 20 bits



Figure similar

MLFB-Ordering data

1FK7080-2AH71-1QG2

### Optimum operating point

Optimum speed	4000 rpm
Optimum power	2.4 kW

### Limiting data

Max. permissible speed (mech.)	6000 rpm
Max. permissible speed (inverter)	6000 rpm
Maximum torque	25.0 Nm
Maximum current	27.5 A

### Recommended Motor Module

Rated inverter current	9 A
Maximum inverter current	27 A
Maximum torque	24.70 Nm