

Passive Components - Resistive Solutions for Wind Turbines

TE Connectivity (TE) can help you to become part of the leading force in alternative energy with improved technical developments and higher power ratings, plus an ever increasing pressure on quality, the alternative energy industry faces many challenges. Whether process control, motion control and drives, robotics, electrical or any other related areas, such as, designing a turbine, control systems, inverters, drives, the same challenges are being faced throughout this complex market. For 50-plus years, TE has worked with industry leaders to lower costs and develop systems to increase reliability, and to devise new and innovative ways to implement technically advanced products for the energy markets. Find more information at te.com/wind

Power electronics design in wind turbine applications presents unique environmental, mechanical and electrical challenges in the selection of power resistor components and assemblies. The selection of resistors must be engineered to take these factors into account. Resistors must be carefully chosen to meet the specific performance requirements including factors like power rating, power density, accuracy, stability, short-term overload capacity, capacitance and inductance and thermal de-rating. In addition, heat dissipation, electrical isolation and other requirements often call for specialized packaging solutions. TE's experienced design team works closely with our customers' engineering personnel to design advanced products meeting their exact requirements. We offer 3D modeling of the product so our customers' engineers have an understanding of what the product will look like from the start of the project.

Our customization and development programme includes in-house product testing in our own R&D laboratory. Tests can be designed in conjunction with customer specifications to include cyclic rated power and overload testing, adiabatic (single shot and frequency) testing, environmental, mechanical

TE Connectivity's Passives Core Product Offering for Wind Turbines Include:

Power Resistors

- Power ratings from 0.25W to > 300kW
- Range of applications
 - Balancing
 - Braking
 - Capacitor Pre-charge / discharge
 - Chopper
 - Crowbar
 - Current sense
 - Filter
 - Inrush limiting
 - Snubber
- Range of technologies
 - Carbon composition
 - Ceramic composition
 - Foil
 - Thick film
 - Thin film
 - Wire-wound
- In-house design and test facilities for development of specification driven products
- Customization capabilities of standard products
- Supported by wide range of commodity power resistors

and repetitive pulse testing. Qualification testing is carried out to a proven procedure and the product development stages are well documented and approved by a design approval team.


About Turbines


Wind turbines are a prime example of a complete power conversion system that combines adjustable speed drives, rectifiers, inverters and intricate control systems. Manufacturers of wind turbine systems are faced with challenges to respond both to rapidly-changing market conditions and to technology developments.

This application calls into play a range of requirements for resistors of nearly all types: wire-wound, thick film, thin film, foil, metal plate, carbon composition and ceramic. Advances in wind turbine design call for innovative application of resistive elements – particularly in specialized packaging and integrated solutions.


Application Guide

Below is a typical frequency convertor schematic used in wind turbine applications. The diagram shows all the different applications where resistive components are required. Page 5 provides a cross reference of TE's resistive solutions for each application shown.





| Family | Technology | Key Features | Pre-Charge / Discharge | Inrush Limiting | Crowbar | Balancing | Current Sense | Braking | Snubber | Chopper | Filter | Heater | Page No. |
|-----------|------------------|---------------------------------|------------------------|-----------------|---------|-----------|---------------|---------|---------|---------|--------|--------|----------|
| BDF | Foil | 400W Isotop | | | | | | | • | | • | | 17 |
| BDS | Thick Film | 100W - 600W Isotop | | | | • | | | • | | • | | 17 |
| C | Wire-wound | 3 - 4W Vitreous | • | • | | • | • | | | | | | 23 |
| CBT/CCR | Carbon/Ceramic | 1/4 - 2W Pulse Withstand | | • | | | | | | | | | 34 |
| CFH | Wire-wound | 350 - 2200W Aluminium Housed | | • | • | | | • | | | | | 10 |
| CJS | Wire-wound | 175 - 1000W Mineral Filled | | | • | | | • | | | | • | 7 |
| CJT | Wire-wound | 60 - 2000W Aluminium Housed | • | | • | | | • | | • | • | | 8 |
| ER/ES | Wire-wound | 0.5 - 14W Silicone | • | • | | • | • | • | | | | | 25 |
| HB | Thick Film | High Voltage Planar | | | | • | | | • | | | | 29 |
| HH/HJ | Thick Film | High Voltage | | | | • | | | | | | • | 30 |
| HS | Wire-wound | 5 - 300W Aluminium Housed | • | • | • | | | • | | | • | | 12 |
| HVR | Thick Film | Up to 50kV High Voltage Tubular | | | | • | | | | | | | 28 |
| Load Bank | Wire-wound | Customised Load Bank | | | • | | | • | | • | | | 6 |
| MPC | Thick Film | 3 - 10W Planar | | • | | • | | | • | | | | 20 |
| MPR | Thin Film | 20W T0220 Radial | | | | • | | | • | | | | 19 |
| MPT | Thick Film | 20 - 100W Radial | | • | | • | | | • | | | | 18 |
| R5000 | Wire-wound/Foil | 250W Low Profile | | | | | • | • | • | | | | 11 |
| RGP | Thick Film | 0.25W High Ohmic | | | | • | | | • | | | | 31 |
| RR | Metal Film | 1, 2 & 3W Power | • | | | • | | | • | | | | 32 |
| ROX | Metal Oxide | 0.5 - 5W Oxide Power | • | | | • | | | • | | | | 33 |
| SBC | Wire-wound | 4 - 40W Ceramic Cased | • | • | | | | • | | | • | | 24 |
| SBL | Foil | 4 - 5W Low Ohmic | | | | | • | | | | | | 26 |
| SQ | Wire-wound/Oxide | 2 - 40W Ceramic Cased | • | • | | | • | • | | | • | | 21-22 |
| TE | Wire-wound | 50 - 2500W Tubular | • | • | • | | | | | • | • | • | 15 |
| THS | Wire-wound | 5 - 50W Aluminium Housed | • | • | • | | | • | | | • | • | 14 |
| TT | Wire-wound | 10 - 1000W Tubular | • | • | • | | | | | • | • | • | 16 |
| YP | Wire-wound | 8 - 10W Capacitor Discharge | • | | | | | | | | | | 27 |



Foil Technology



Wire-wound Technology



Thick Film Technology

Offered in a wide range of package styles, including IP sealing and in a variety of resistive configurations, TE's resistor banks are the result of over 40 years attention to power dissipation, pulse energy absorption and resistive technology developments. High power resistor banks are used in a wide variety of applications, such as testing of engine generator sets, periodic exercising of stand-by engine generator sets, battery system testing, ground power testing, load optimization in prime power applications, factory testing of turbines etc

Key Features

- 0.5 - 300kW power dissipation
- 0.5 - 10kV rated voltage
- Up to 30kV dielectric strength
- Up to 250A rated current
- IP20 - IP23 environmental protection
- Custom design solutions
- Modular design

Applications

- Crowbar
- Braking



Characteristics - Electrical

Case Mounted - LBR



| | |
|--------------------------|-----------------------|
| Power Range: | 0.5kW - 10kW |
| Operating Voltage Range: | 0.5kV - 3kV |
| Resistance Range: | 1R0 - 1K0 |
| Voltage Withstand: | 2.5kV - 5kV/1min 50Hz |
| IP Class: | IP20 |
| Vibration: | 0.5g |
| Rated Temperature Rise: | 375°C |
| Temperature Drift: | 80 - 1260ppm/°C |

Open Frame - TEBR



| | |
|--------------------------|-----------------------|
| Power Range: | 1kW - 500kW |
| Operating Voltage Range: | 0.5kV - 3kV |
| Resistance Range: | 1R0 - 1K0 |
| Voltage Withstand: | 2.5kV - 5kV/1min 50Hz |
| IP Class: | IP20 |
| Vibration: | 0.5g |
| Rated Temperature Rise: | 375°C |
| Temperature Drift: | 80 - 1260ppm/°C |

Cabinet Mounted - LBR



| | |
|--------------------------|------------------------|
| Power Range: | 11kW - 300kW |
| Power Factor Range: | 0.1 - 1 adjustable |
| Operating Voltage Range: | 0.5kV - 10kV |
| Resistance Range: | R50 - 100R |
| Dielectric Strength: | 2.5kV - 30kV/1min 50Hz |
| IP Protection: | IP20 - IP23 |
| Vibration: | 0.5g |
| Temperature Rise: | 375°C |
| Air Flow: | 7000m³/h |
| Temperature Coefficient: | 80 - 1260ppm/°C |

The CJS is a mineral filled, aluminium housed resistor designed for both braking of drives and for high power loads. The case can be internally earthed for extra safety.

Key Features



- Designed for dynamic braking
- Fully insulated and sealed
- Low inductance possible
- FASTON or wire leads
- Custom designs welcome
- UL approved




Characteristics - Electrical

| | CJS 275 | CJS 300 | CJS 550 | CJS 600 | CJS 700 | CJS 1000 |
|--------------------------------|--|---------|---------|---------|---------|----------|
| Power on Heatsink (W): | 275 | 300 | 550 | 600 | 700 | 1000 |
| Power Free Air (W): | 175 | 225 | 325 | 450 | 525 | 525 |
| Resistance Range: | 5R0-7K5 | 10R-13K | 20R-26K | 20R-32K | 20R-32K | 20R-36K |
| Standard Resistance Tolerance: | ±5% (others by request) | | | | | |
| Long Term Stability: | < 5% over 1000 hours - 1.5 hours on 0.5 hours off | | | | | |
| Temperature Coefficient: | ±150ppm/°C | | | | | |
| Insulation Voltage: | 5.0kV or AC peak | | | | | |
| Insulation Resistance: | 100MΩ at 250V | | | | | |
| Element Voltage: | 3 kV AC, RMS max (do not exceed when applying pulse overload) | | | | | |
| Short Time Overload: | 100 x 1 second, 20 x 5 seconds, 10 x 10 seconds (not 275 and 1000) | | | | | |

Pulse Energy Versus Resistance



Dimensions



| | L1 | L2 | H | W | D |
|----------|-----|-----|-----|-----|----|
| CJS 275 | 200 | 190 | 55 | 58 | - |
| CJS 300 | 280 | 270 | 55 | 58 | - |
| CJS 550 | 280 | 270 | 55 | 84 | 40 |
| CJS 600 | 340 | 330 | 54 | 84 | 40 |
| CJS 700 | 400 | 390 | 52 | 103 | 40 |
| CJS 1000 | 400 | 385 | 103 | 52 | 30 |


TE supplies standard and custom-designed power resistors for industrial, control and general-purpose applications. The CJT Series of resistors are advantageous to conventional ceramic resistors in the terms of weatherproofing, oscillation-resistance and safety. They are widely applied to a range of electrical circuits including power supplies, inverters and servo systems. With easy airtight fitting and the ability to fit a heatsink the resistor is highly suited to challenging environmental conditions.

Key Features

- Up to 2000W power rating
- Aluminium enclosure
- Vibration resistant

Applications


- Power supplies
- Inverters
- Servo systems
- Electrical systems in difficult environments




Characteristics - Electrical

| Type: | CJT60 | CJT80 | CJT100 | CJT120 | CJT150 | CJT200 | CJT300 | CJT400 | CJT500 | CJT800 | CJT1000 | CJT1200 | CJT1500 | CJT2000 |
|---|------------------------------------|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| Rated Power in Free Air (W): | 60 | 80 | 100 | 120 | 150 | 200 | 300 | 400 | 500 | 800 | 1000 | 1200 | 1500 | 2000 |
| Ohmic Value - min/max: | 1R0 to 2K7 (standard tolerance 5%) | | | | | | | | | | | | | |
| Temp. Coefficient of Resistance: | 440ppm | | | | | | | | | | | | | |
| Resistor Element max. Working Voltage: | 1kV | | | | | | | | | | | | | |
| Dielectric Voltage: | AC2.5kV / 1min 50Hz | | | | | | | | | | | | | |
| Insulation Resistance (MΩ): | R≥100MΩ | | | | | | | | | | | | | |
| Max. Surface Temp at Rated Power Free Air (°C): | 206°C | 221°C | 254°C | 267°C | 286°C | 306°C | 334°C | 370°C | 358°C | 311°C | 372°C | 406°C | 419°C | 453°C |
| Weight: | 150g | 185g | 240g | 280g | 300g | 445g | 600g | 765g | 965g | 1.18kg | 3.46kg | 3.885kg | 4.31kg | 4.89kg |
| Terminal Creep Distance: | N/A | | | | | | | | | | 30mm | 42mm | 42mm | 42mm |


Temperature Rise



Derating Curve




Dimensions - CJT



| Rated Power (Watt) | Dimensions | | | |
|-----------------------|------------|-----|----|----|
| | A | B | C | D |
| 60 | 115 | 98 | 40 | 20 |
| 80 | 140 | 123 | 40 | 20 |
| 100 | 165 | 148 | 40 | 20 |
| 120 | 190 | 173 | 40 | 20 |
| 150 | 215 | 197 | 40 | 20 |
| 200 | 165 | 147 | 60 | 30 |
| 300 | 215 | 197 | 60 | 30 |

| Rated Power (Watt) | Dimensions | | | |
|-----------------------|------------|-----|----|-----|
| | A | B | C | D |
| 400 | 265 | 247 | 60 | 30 |
| 500 | 335 | 317 | 60 | 30 |
| 800 | 400 | 382 | 61 | 59 |
| 1000 | 400 | 384 | 50 | 107 |
| 1200 | 450 | 434 | 50 | 107 |
| 1500 | 485 | 470 | 50 | 107 |
| 2000 | 550 | 532 | 50 | 107 |

Dimensions - CJTM



| Type | Rated Power (Watt) | Resistance (Ω) | | Dimensions (mm) | | | | | | Connecting Wire (mm ²) | Lead Length (mm) |
|--------|-----------------------|----------------|------|-----------------|-----|-----|-----|----|----|---------------------------------------|---------------------|
| | | Min | Max | A | A1 | B | B1 | G | H | | |
| CJTM1U | 200 | 1 | 2K7 | 268 | 253 | 64 | 30 | 20 | 54 | 2.5 | 500 |
| CJTM1U | 300 | 1 | 2K7 | 318 | 303 | 64 | 30 | 20 | 54 | 2.5 | 500 |
| CJTM1U | 400 | 1 | 2K7 | 368 | 353 | 64 | 30 | 20 | 54 | 2.5 | 500 |
| CJTM1U | 500 | 1 | 2K7 | 438 | 423 | 64 | 30 | 20 | 54 | 2.5 | 500 |
| CJTM1U | 600 | 1 | 2K7 | 503 | 488 | 64 | 30 | 20 | 54 | 2.5 | 500 |
| CJTM2U | 800 | 2 | 5K4 | 372 | 355 | 84 | 49 | 20 | 84 | 2.5 | 500 |
| CJTM2U | 1000 | 2 | 5K4 | 442 | 425 | 84 | 49 | 20 | 84 | 2.5 | 500 |
| CJTM2U | 1200 | 2 | 5K4 | 507 | 490 | 84 | 49 | 20 | 84 | 2.5 | 500 |
| CJTM3U | 1200 | 3 | 8K1 | 372 | 355 | 134 | 75 | 20 | 84 | 2.5 | 500 |
| CJTM3U | 1500 | 3 | 8K1 | 442 | 425 | 134 | 75 | 20 | 84 | 2.5 | 500 |
| CJTM3U | 1800 | 3 | 8K1 | 507 | 490 | 134 | 75 | 20 | 84 | 2.5 | 500 |
| CJTM4U | 1600 | 4 | 10K8 | 372 | 355 | 184 | 125 | 20 | 84 | 2.5 | 500 |
| CJTM4U | 2000 | 4 | 10K8 | 442 | 425 | 184 | 125 | 20 | 84 | 4 | 500 |
| CJTM4U | 2400 | 4 | 10K8 | 507 | 490 | 184 | 125 | 20 | 84 | 4 | 500 |
| CJTM5U | 2000 | 5 | 13K5 | 372 | 355 | 234 | 175 | 20 | 84 | 4 | 500 |
| CJTM5U | 2500 | 5 | 13K5 | 442 | 425 | 234 | 175 | 20 | 84 | 4 | 500 |
| CJTM5U | 3000 | 5 | 13K5 | 507 | 490 | 234 | 175 | 20 | 84 | 4 | 500 |


The CFH is a high quality range of aluminium housed power resistors offering environmental protection to IP55, 6kV dielectric strength, 1.8kW power dissipation, and the ability to absorb electrical pulses of up to 24kJ. The use of advanced materials in the construction of this device enables operating temperatures of up to 450°C giving very high power density.

Key Features

- 2200W in a 72cm² footprint
- Impressive pulse capability
- No heatsink required
- Slimline casing
- Environmental protection to IP55

Applications


- Braking
- Balancing
- Capacitor charging & discharging
- Crowbar
- Filter
- Inrush limiting




Characteristics - Electrical

| | CFH350 | CFH500 | CFH750 | CFH1100 |
|--|---|------------------|--------------------|--------------------|
| Dissipation @ 25°C with Heatsink (Watts): | 650 | 850 | 1300 | 1800 |
| Without Heatsink: | 350 | 500 | 750 | 1100 |
| With Water Cooled Heatsink (40°C): | 750 | 1000 | 1500 | 2200 |
| Overload Rating (5s): | 4000 | 5600 | 8000 | 12000 |
| Ohmic Value (Ohms): | R50 to 10K | R50 to 18K | R50 to 27K | R50 to 27K |
| Tolerance: | ±5% Standard | | | |
| Maximum Working Voltage (DC/ACrms) Volts: | 1500 | 2500 | 3500 | 4000 |
| Insulation Resistance (Volts): | ≥10000MΩ | | | |
| Dielectric Strength (AC peak) Volts: | 4500 standard and 6000 special | | | |
| Inductance (Henries): | 5-50μH at 1000Hz | 7-70μH at 1000Hz | 10-100μH at 1000Hz | 20-200μH at 1000Hz |
| Standard Heatsink Area (mm ²): | 1600 | 1600 | 1600 | 1600 |
| Thickness (mm): | 135 | 135 | 135 | 135 |
| Protection Grade (IP): | IP55 | | | |
| Heat Dissipation: | Although the use of proprietary heat sinks with lower thermal resistance is acceptable, up rating is not recommended. The use of proprietary heat sink compound to improve thermal conductivity is essential. | | | |


Derating Curve



Surface Temperature Rise



Dimensions



| Type | CFH350 | CFH500 | CFH750 | CFH1100 |
|------|--------|--------|--------|---------|
| L | 110mm | 160mm | 220mm | 320mm |
| P | 60mm | 110mm | 140mm | 240mm |

The R5000 by TE is a high specification flat resistor module with flying leads, designed for braking and snubbing applications where size and weight are at a premium. With a height of 13mm, an overall weight of 150g, and a rated power of 250W, this resistor offers unbeatable performance in terms of power density. Advanced construction methods and high performance materials give a rugged and resilient device capable of high pulse energy absorption, low inductance, high stability, and a low TCR. This device can be fused to offer circuit protection and is available in a wide range of resistance values.

Key Features

- 250W in a 77cm² footprint
- Special fuse option available
- Low inductance for the fastest switching speeds
- High quality aluminium construction - just 150g
- UL approved

Applications


- Braking
- Snubbing
- Filter
- Power supplies
- Electrical machinery




Characteristics - Electrical

| | |
|--|---|
| Dissipation @ 20°C with Heatsink (Watts): | 250 |
| Ohmic Value - Foil / Wire-wound (Ohms): | R05 - 20R / 10R - 10K (± 10% Tolerance) |
| Limiting Element Voltage (DC/ACrms) Volts: | 500V DC or AC Peak |
| Dielectric Strength (AC peak) Volts: | 500V (Can be uprated) |
| Inductance - Foil Element (Henries): | <1 µH |
| Capacitance (F): | 440pF |
| TCR (ppm/°C): | 20ppm/°C - 150ppm/°C (to design) |
| Stability (1000h/250W): | ΔR < 5% |
| Terminal Strength: | 5kg pull strength |
| Temperature Range: | -50°C to 125°C |
| Humidity (Silicon-sealed Option): | 96% RH @ 40°C - 56days. ΔR <1% |
| Orientation: | Vertical |
| Number of Mounting Holes: | 2 |
| Cable Length: | 130mm ± 10mm |
| Heat Dissipation: | Although the use of proprietary heat sinks with lower thermal resistance is acceptable, up rating is not recommended. The use of proprietary heat sink compound to improve thermal conductivity is essential. |


Derating Curve



Pulse Energy (Foil Element)



Dimensions



TE supplies standard and custom designed aluminium housed resistors for general-purpose use, power supplies, power generation and the traction industry. The HS is a range of extremely stable, high quality wire-wound resistors capable of dissipating high power in a limited space with relatively low surface temperature. The power is rapidly dissipated as heat through the aluminium housing to a specified heatsink. The resistors are made from quality materials for optimum reliability and stability. TE can test resistors to conform to relevant international, MIL or customer specifications. TE is happy to advise on the use of resistors for pulse applications and to supply information for high voltage use and low-ohmic value, alternative mountings and termination type.

Key Features

- Established product with proven reliability
- 5 - 300W
- Versatile product
- Custom designs
- Low resistance, low inductance and higher voltage versions available

Applications


- Braking resistor
- Balancing resistor
- Filter
- Crowbar
- Capacitor charging & discharging




Characteristics - Electrical

| | HSA5 | HSA10 | HSA25 | HSA50 | HSC75 | HSC100 | HSC150 | HSC200 | HSC250 | HSC300 |
|---|---------|---------|---------|----------|---------|----------|----------|---------|---------|---------|
| Dissipation @ 25°C with/without Heatsink (Watts): | 10/5.5 | 16/8 | 25/12.5 | 50/20 | 75/45 | 100/50 | 150/55 | 200/50 | 250/60 | 300/75 |
| Ohmic Value min/max (Ohms): | R01/10K | R01/15K | R01/36K | R01/100K | R05/50K | R05/100K | R10/100K | R10/50K | R10/68K | R10/82K |
| Max. Working Voltage (DC or ACrms) Volts: | 160 | 265 | 550 | 1250 | 1400 | 1900 | 2500 | 1900 | 2200 | 2500 |
| Dielectric Strength (AC peak) Volts: | 1400 | 1400 | 2500 | 2500 | 5000 | 5000 | 5000 | 5600 | 5600 | 5600 |
| Stability (% resistance change, 1000 hours) (%): | 1 | 1 | 1 | 1 | 2 | 2 | 2 | 3 | 3 | 3 |
| Standard Heatsink Area (mm²): | 41500 | 41500 | 53500 | 53500 | 99500 | 99500 | 99500 | 375000 | 476500 | 578000 |
| Thickness (mm): | 1 | 1 | 1 | 1 | 3 | 3 | 3 | 3 | 3 | 3 |
| Number of Mounting Holes: | 2 hole | 2 hole | 2 hole | 2 hole | 4 hole | 4 hole | 4 hole | 6 hole | 6 hole | 6 hole |


Pulse Energy HSA5 to HSC75




Pulse Energy HSC100 to HSC300




Surface Temperature Rise




Dimensions - HSA5 - HSA50



HSC75 - HSC150




HSC200+




| Type | H±0.3 | J±0.3 | K±0.2 | L Max | M Max | N Max | P Max | R Min | T±0.5 | U Max |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| HSA5 | 11.3 | 12.4 | 2.4 | 17.0 | 30.0 | 17.0 | 9.0 | 1.9 | 3.4 | 2.5 |
| HSA10 | 14.3 | 15.9 | 2.4 | 21.0 | 36.5 | 21.0 | 11.0 | 1.9 | 5.2 | 3.2 |
| HSA25 | 18.3 | 19.8 | 3.3 | 29.0 | 51.8 | 28.0 | 15.0 | 2.8 | 7.2 | 3.2 |
| HSA50 | 39.7 | 21.4 | 3.3 | 51.0 | 72.5 | 30.0 | 17.0 | 2.8 | 7.9 | 3.2 |
| HSC75 | 29.0 | 37.0 | 4.4 | 49.0 | 71.0 | 47.5 | 26.0 | 5.0 | 11.5 | 3.5 |
| HSC100 | 35.0 | 37.0 | 4.4 | 65.5 | 87.5 | 47.5 | 26.0 | 5.0 | 11.5 | 3.5 |
| HSC150 | 58.0 | 37.0 | 4.4 | 98.0 | 122.0 | 47.5 | 26.0 | 5.0 | 11.5 | 3.5 |
| HSC200 | 35.0 | 57.2 | 5.3 | 90.0 | 143.0 | 73.0 | 45.0 | 5.6 | 22.2 | 6.75 |
| HSC250 | 44.5 | 57.2 | 5.3 | 109.0 | 163.0 | 73.0 | 45.0 | 5.6 | 22.2 | 6.75 |
| HSC300 | 52.0 | 59.0 | 6.5 | 128.0 | 180.0 | 73.0 | 45.0 | 6.0 | 22.2 | 6.75 |

HSA5 - HSA50



HSC200-HSC300



| Type | L |
|-----------------|----|
| HSA5, 10 | 7 |
| HSA25, 50 | 10 |
| HSC75, 100, 150 | 8 |


The THS is a range of extremely stable, high quality wire-wound resistors capable of dissipating high power in a limited space with relatively low surface temperature. The power is rapidly dissipated as heat through the aluminium housing to a specified heatsink. The resistors are made from quality materials for optimum reliability and stability. TE can test resistors to conform to relevant international, MIL or customer specifications.

Key Features

- Established product with proven reliability
- 10 - 75W
- Versatile product

Applications


- Braking resistor
- Balancing resistor
- Filter
- Crowbar
- Capacitor charging & discharging




Characteristics - Electrical

| | THS10 | THS15 | THS25 | THS50 | THS75 |
|--|-----------|-----------|-----------|-----------|-----------|
| Dissipation @ 25°C with / without Heatsink (Watts): | 10 / 5.5 | 15 / 8 | 25 / 12.5 | 50 / 20 | 75 / 40 |
| Ohmic Value min/max (Ohms): | R01-10K | R01-15K | R01-36K | R01-50K | R05-50K |
| Max. Working Voltage (DC or ACrms) Volts: | 160 | 265 | 550 | 1250 | 1400 |
| Dielectric Strength (AC Peak) Volts: | 1400 | 1400 | 2500 | 2500 | 5000 |
| Stability (% resistance change, 1000 hours) (%): | 1 | 1 | 1 | 1 | 2 |
| Standard Heatsink Area-mm ² / Thickness mm: | 41500 / 1 | 41500 / 1 | 53500 / 1 | 53500 / 1 | 99500 / 3 |
| Number of Mounting Holes: | 2 hole | 2 hole | 2 hole | 2 hole | 4 hole |


Derating Curve




Pulse Energy THS10 to THS75




Surface Temperature Rise




Dimensions - THS10 - THS50



THS75



| Type | H±0.3 | J±0.3 | L Max | M Max | N Max | P Max | R Min | T±0.5 | U Max |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| THS10 | 11.3 | 12.4 | 17.0 | 30.0 | 17.0 | 9.0 | 1.9 | 3.4 | 2.5 |
| THS15 | 14.3 | 15.9 | 21.0 | 36.5 | 21.0 | 11.0 | 1.9 | 5.2 | 3.2 |
| THS25 | 18.3 | 19.8 | 29.0 | 51.8 | 28.0 | 15.0 | 2.8 | 7.2 | 3.2 |
| THS50 | 39.7 | 21.4 | 51.0 | 72.5 | 30.0 | 17.0 | 2.8 | 7.9 | 3.2 |
| THS75 | 29.0 | 37.0 | 49.0 | 71.0 | 47.5 | 26.0 | 5.0 | 11.5 | 3.5 |



| Type | L |
|-----------|----|
| THS10, 15 | 7 |
| THS25, 50 | 10 |
| THS75 | 8 |


The TE range of mullite coated tubular ceramic core resistors have a corrugated ribbon element for rapid cooling effect to enable up to 2500W power handling capability. Designed for heavy duty machinery, electrical equipment, motor control etc. requiring stability and reliability.

Key Features

- Mullite coated
- Up to 2500W power rating
- Corrugated ribbon element for rapid cooling
- 3x overload for 5 seconds
- Custom terminations/ leads available
- Flameproof construction

Applications

- Capacitor charging & discharging
- Load test simulation
- Motor start/stop cycles
- Dynamic braking
- Equipment discharge




Characteristics - Electrical

| | |
|--|--|
| Temperature Coefficient of Resistance: | Within $\pm 440\text{ppm}/^\circ\text{C}$ |
| Rated Power Free Air: | 50 - 2500W |
| Operating Temperature Range : | -25°C to $+225^\circ\text{C}$ |
| Resistance Range (Ohms): | See resistance range chart below |
| Selection Series: | E12 |
| Tolerance: | $\pm 5\%$, $\pm 10\%$ as per resistance range chart below |


| Type | Resistance Value | Tolerance |
|------|------------------|-----------|
| 50W | R10 – R99 | 10% |
| | 1R0 – 2K7 | 5% |
| 60W | R10 – R99 | 10% |
| | 1R0 – 2K7 | 5% |
| 80W | R10 – R99 | 10% |
| | 1R0 – 2K7 | 5% |
| 100W | 1R0 – 2K7 | 5% |
| 120W | 1R0 – 2K7 | 5% |
| 150W | 1R0 – 2K7 | 5% |
| 200W | 1R0 – 2K7 | 5% |

| Type | Resistance Value | Tolerance |
|-------|------------------|-----------|
| 300W | 1R0 – 2K7 | 5% |
| 400W | 1R0 – 2K7 | 5% |
| 500W | 1R0 – 2K7 | 5% |
| 600W | 1R0 – 2K7 | 5% |
| 750W | 1R0 – 2K7 | 5% |
| 1000W | 1R0 – 2K7 | 5% |
| 1200W | 1R0 – 2K7 | 5% |
| 1500W | 1R0 – 2K7 | 5% |
| 2000W | 1R0 – 2K7 | 5% |
| 2500W | 1R0 – 2K7 | 5% |


Derating Curve



TE Temperature Rise



Dimensions



| Rated Power | Dimensions | | | |
|-------------|------------|------|-----|------|
| | L1±2 | L2±5 | D±2 | H1±3 |
| 50 | 102 | 124 | 28 | 61 |
| 60 | 102 | 124 | 28 | 61 |
| 80 | 152 | 174 | 28 | 61 |
| 100 | 182 | 204 | 28 | 61 |
| 120 | 182 | 204 | 28 | 61 |
| 150 | 195 | 217 | 40 | 81 |
| 200 | 195 | 217 | 40 | 81 |
| 300 | 282 | 304 | 40 | 81 |
| 400 | 282 | 304 | 40 | 81 |

| Rated Power | Dimensions | | | |
|-------------|------------|------|-----|------|
| | L1±2 | L2±5 | D±2 | H1±3 |
| 500 | 316 | 338 | 50 | 101 |
| 600 | 345 | 367 | 40 | 81 |
| 750 | 316 | 338 | 50 | 101 |
| 1000 | 300 | 325 | 60 | 119 |
| 1200 | 415 | 440 | 60 | 119 |
| 1500 | 415 | 440 | 60 | 119 |
| 2000 | 510 | 535 | 60 | 119 |
| 2500 | 600 | 625 | 60 | 119 |

These high power tubular resistors have a high resistance to heat, and a small resistance to temperature co-efficient. Relatively small in size, their ability to take a large load make them ideal for use in heavy electrical machinery. Available as standard wire-wound resistor coated with flameproof enamel paint or ribbon style also coated with flameproof enamel paint.

Key Features

- High resistance to heat
- Small resistance temperature coefficient
- Small in size
- Adjustable version available
- Ribbon version available

Applications


- Braking
- Crowbar
- Inrush limiting
- Balancing
- Filter
- Electrical machinery
- Capacitor charging & discharging




Characteristics - Electrical

| | |
|----------------------------------|---|
| Resistance Values: | R20 to 70K |
| Resistance Tolerance: | 5%, 10% |
| Temp. Coefficient of Resistance: | within $\pm 400\text{ppm}/^\circ\text{C}$ |
| Rated Power @ 70°C: | 10 - 1000W nominal |
| Operating Temperature Range: | -55°C to +200°C |

Derating Curve




Dimensions - TTR Series




| Power Rating | Dimensions (mm) | | | | Resistance Range (Ohms) |
|--------------|-----------------|-------------|-------------|-------------|-------------------------|
| | D ± 1.0 | E ± 2.0 | F ± 1.0 | K ± 2.0 | |
| 90W | 33 | 15 | 26 | 90 | R2 - 7R5 |
| 120W | 33 | 15 | 26 | 115 | R2 - 10R |
| 150W | 33 | 15 | 26 | 140 | R3 - 12R |
| 180W | 33 | 15 | 26 | 165 | R3 - 15R |
| 225W | 33 | 15 | 26 | 195 | R43 - 18R |
| 300W | 33 | 15 | 26 | 254 | R51 - 20R |
| 450W | 48 | 25 | 42 | 254 | R82 - 25R |
| 600W | 48 | 25 | 42 | 330 | 1R - 30R |
| 1000W | 48 | 25 | 42 | 420 | 2R - 33R |

TTH Series



| Power Rating | Dimensions (mm) | | | | Resistance Range (Ohms) | |
|--------------|-----------------|-------------|-------------|-------------|-------------------------|-----------|
| | A ± 1.0 | B ± 2.0 | C ± 3.0 | D ± 2.0 | TTH | TTHA |
| 10W | 12 | 45 | 16 | 5 | 1R - 1K | 1R - 470R |
| 15W | 15 | 45 | 17 | 7 | 1R - 2K | 1R - 1K |
| 20W | 19 | 50 | 19 | 9 | 1R - 3K | 1R - 1K5 |
| 25W | 19 | 60 | 19 | 9 | 2R - 3K9 | 2R - 2K |
| 30W | 19 | 75 | 19 | 9 | 2R - 4K3 | 2R - 2K2 |
| 40W | 19 | 90 | 19 | 9 | 2R - 5K6 | 2R - 3K |
| 50W | 26 | 75 | 31 | 15 | 3R - 7K5 | 3R - 3K6 |
| 60W | 28 | 90 | 31 | 15 | 3R - 10K | 3R - 4K7 |
| 80W | 28 | 115 | 31 | 15 | 3R - 12K | 3R - 5K6 |
| 100W | 28 | 140 | 31 | 15 | 4R3 - 15K | 4R3 - 7K5 |
| 120W | 28 | 165 | 31 | 15 | 4R3 - 20K | 4R3 - 10K |
| 150W | 28 | 195 | 31 | 15 | 5R1 - 22K | 5R1 - 11K |
| 200W | 28 | 254 | 31 | 15 | 5R1 - 30K | 5R1 - 15K |
| 300W | 42 | 254 | 48 | 25 | 5R1 - 39K | 5R1 - 20K |
| 400W | 42 | 330 | 48 | 25 | 10R - 47K | 10R - 24K |
| 600W | 42 | 420 | 48 | 25 | 10R - 68K | 10R - 33K |

TTHA Series



The BDS is a non-inductive thick film power resistor offering continuous powers up to 400 Watts (on a suitable heatsink). A modern functional package, with high voltage insulation and an excellent partial discharge rating.

Key Features

- Values R47 - 1M Ω
- Voltage single shot 12kV
- Options for internal circuitry
- Non-inductive for fast switching
- Low partial discharge

Applications



- Snubbing (low inductance)
- Balancing resistor (multi resistor package)
- Filter (low inductance)
- High voltage
- High frequency



Characteristics - Electrical

| | 250 / 400W | 100W (T0 227) |
|---|---|---|
| Resistance Range: | 0R47-1M (4 terminal below 1R) | 0R20-1M (4 terminal below 1R) |
| Resistance Tolerance: | $\pm 10\%$, 5% (tighter by discussion) | $\pm 10\%$, 5% (tighter by discussion) |
| TCR - R > 1 Ohm: | 250ppm $^{\circ}$ C | 250ppm $^{\circ}$ C |
| TCR - R < 1 Ohm: | 150ppm $^{\circ}$ C | 150ppm $^{\circ}$ C |
| Rated Power Heatsink Temperature at 100 $^{\circ}$ C: | 250W (400W) at 70 $^{\circ}$ C | 100W at 60 $^{\circ}$ C max heatsink |
| Parallel Capacitance: | 40pf | 40pf |
| Capacitance to Earth: | 120pf | 120pf |
| Series Inductance: | 40nH maximum | 40nH maximum |
| Limiting Element Voltage: | 5kV max DC/AC rms | 2.5kV DC/AC rms |
| Isolation Voltage (Terminal to Heatsink): | 7kV DC/AC rms | 2.5kV DC/AC rms |
| Single Shot 1.5/50 μ s: | up to 12kV | 4.0kV |
| Insulation Resistance at 500V DC: | > 100g Ohms | > 100g Ohms |
| Partial Discharge: | < 5pC at 7kV | < 10pC at 2.5 kv |
| Endurance (Rated Power): | 2000 cycles at rated power 30m/30m | ΔR 0.25% typically |
| Humidity Load Life: | 56 days, 40 $^{\circ}$ C, 95%rh | ΔR 0.25% typically (i.r. 10g Ω) |
| Temperature Cycling: | -55 $^{\circ}$ C to +125 $^{\circ}$ C, 5 cycles | ΔR 0.25% typically |
| Operating / Storage Temperature: | -55 $^{\circ}$ C to +125 $^{\circ}$ C | |
| *Short Term Overload: | 3 times rated power, 10 seconds | ΔR 0.25% typically *(4 times to order) |
| Vibration: | 10/500 hz | ΔR 0.25% typically |
| Bump: | 40g 4000 | ΔR 0.25% typically |

Dimensions




The MPT resistor series are a range of T0220 packaged, low inductance thick film power resistors which complement the thin film MPR series. This small size, high power device packaged in five case sizes are ideally suited to applications where high power dissipation yet small size are key design requirements. The MPT resistor series are the ideal solution for small snubber circuits, the output side of high speed pulse generators and low inductive resistor requirements in switch mode power supplies.

Key Features

- High power density
- Non inductive
- High power up to 100W
- Isolated moulded case
- Easy to mount

Applications


- Balancing
- Snubber
- Current sense
- In rush limiting



Characteristics - Electrical

| | MPT20 | MPT30 | MPT35 | MPT50 | MPT100 |
|-------------------------------------|-----------------|-----------|-----------|-----------|-----------------|
| Resistance Range: | R10 - 10K | R10 - 10K | R10 - 10K | R10 - 10K | R10 - 10K |
| Selection Series: | E24 | | | | |
| Rated Power with Suitable Heatsink: | 20W | 30W | 35W | 50W | 100W |
| Rated Power without Heatsink: | 3W | 2.25W | 2.5W | 3W | 3.5W |
| Maximum Operating Voltage: | 350V | | | | |
| Dielectric Strength: | 1800VAC | | | | |
| Insulation Resistance: | 10G min. | | | | |
| Operating Temperature Range: | -65°C to +150°C | | | | -65°C to +175°C |


Derating Curve




TCR / Tolerance Value Chart

| | MPT 20 / 30 / 35 / 50 | | MPT100 |
|------------------------------|-----------------------|--------|---------------|
| Resistance Range / Tolerance | 1% / 5% / 10% | 0.5% | 1% / 5% / 10% |
| R10 - 2R7 | 300ppm | - | 300ppm |
| 3R - 10R | 100ppm | - | 100ppm |
| 3R - 10R | 200ppm | - | 200ppm |
| 11R - 10K | 50ppm | 50ppm | 50ppm |
| 11R - 10K | 100ppm | 100ppm | 100ppm |
| 11R - 10K | 200ppm | 200ppm | 200ppm |

Dimensions




MPT30




Mounting Detail

MPT35



MPT100



| | a | b | c | d | e | f | g | h | i | j |
|--------|-------------|-------------|-------------|------------|------------|-------------|-----------|------------|-------------|--------------|
| MPT20 | 10.41 ±0.26 | 16.26 ±0.26 | 12.7 ±1.27 | 3.3 ±0.76 | 1.27 ±0.13 | 5.08 ±0.26 | 0.76 ±0.1 | 3.18 ±0.26 | 0.5 ±0.1 | 1.78 ±0.26 |
| MPT30 | 10.41 ±0.26 | 16.26 ±0.26 | 12.7 ±1.27 | 3.3 ±0.76 | 1.27 ±0.13 | 5.08 ±0.26 | 0.76 ±0.1 | 3.18 ±0.26 | 0.5 ±0.1 | 1.78 ±0.26 |
| MPT35 | 10.16 ±0.25 | 14.75 ±0.25 | 13.70 ±1.0 | 4.0 | 1.27 ±0.1 | 5.08 ±0.25 | 0.78 ±0.8 | 4.44 ±0.38 | 0.625 ±0.07 | 2.285 ±0.235 |
| MPT50 | 10.41 ±0.26 | 16.26 ±0.26 | 12.7 ±1.27 | 3.3 ±0.76 | 1.27 ±0.13 | 5.08 ±0.26 | 0.76 ±0.1 | 3.18 ±0.26 | 0.5 ±0.1 | 1.78 ±0.26 |
| MPT100 | 15.75 ±0.26 | 20.7 ±0.26 | 14.48 ±1.27 | 2.79 ±0.76 | 3.63 ±0.18 | 10.16 ±0.26 | 1.52 ±0.1 | 4.95 ±0.26 | 0.81 ±0.26 | 2.41 ±0.26 |


This small size non-inductive, high power resistor is an innovative and significant first for TE. Occupying a standard T0220 package it is ideally suited to positions where high power dissipation, small size and tight tolerance are key design requirements. This series is an ideal solution for the output side of high speed pulse generators, a surge absorption resistor in switch mode power supplies and for monitors, display terminals, scientific workstations and other brown and white goods.

Key Features

- Small size (T0220 package)
- Non inductive
- High frequency range up to 300MHz
- High power 20W with suitable heatsink
- Voltage proof 2000V DC

Applications

- Balancing
- Snubber




Characteristics - Electrical

| | | | |
|--|---|-----------|-----------|
| Resistance Range: | R22 - R91 | 1R0 - 9R1 | 10R - 51K |
| Resistance Tolerance: | 5% | 5% | 1% / 5% |
| Temp. Coefficient of Resistance (TCR): | 250ppm/°C | 100ppm/°C | 50ppm/°C |
| Rated Power (on Suitable Heatsink): | 20W | | |
| Rated Power (with/without Heatsink): | 2W * (See note below) | | |
| Equivalent Parallel Capacitance: | 1.0pF | | |
| Maximum Operating Voltage: | 500V DC | | |
| Withstand Voltage: | 2000V DC (Between terminals and heatsink) | | |
| Operating Temperature Range: | -55°C to +155°C | | |
| Rated Ambient Temperature: | -25°C to +40°C | | |


* With a 5.8°C Watt heatsink or better at a 25°C ambient temperature, 20 Watts can be dissipated. A larger heatsink will allow the resistor to run at a lower temperature.

Derating Curve




Load Life in High Temperature & Humidity


(70°C 95% DC Rated Power x 0.1) Continuous



Dimensions



PCB Piercing Plan




A range of non inductive thick film power resistors complementing the T0220 packaged MPR series (20W heat sink styles), being vertically mounted and suitable to dissipate power from 3W up to 10W. Available in values from 1R0 to 200K Ohms they are the idea solution for small snubber circuits, the output side of high speed pulse generators and low inductive resistor requirements in switch mode power supplies.

Key Features

- High power density
- Non inductive
- High power up to 10W
- Voltage proof 5000V DC
- Stable at 100ppm/°C

Applications


- Balancing
- Snubber
- Current sense
- Inrush limiting




Characteristics - Electrical

| | |
|--|--|
| Resistance Values: | R10 to 200K |
| Resistance Tolerance: | 1%, 5% |
| Temp. Coefficient of Resistance: | ±100ppm/°C |
| Rated Power @ 70°C: | 3 - 10W nominal |
| Equivalent Parallel Capacitance (100 MHz): | 1.0pf |
| Maximum Operating Voltage: | 300V AC |
| Withstanding Voltage: | 5000V |
| Overload Current: | 20 x rated current up to 8ms (ΔR ± 0.5%) |


Derating Curve



Overload Characteristics



Dimensions



| Size | MPC3 | MPC5 | MPC7 | MPC10 |
|------|-------|------|-------|-------|
| A | 10.16 | 12.7 | 19.05 | 25.4 |
| B | 5.08 | 5.08 | 12.70 | 20.32 |

This flexible range of power wire-wound resistors either have wire or power oxide film elements. The SQ series resistors are wound or deposited on a fine non - alkali ceramic core then embodied in a ceramic case and sealed with an inorganic silica filler. This design provides a resistor with high insulation resistance, low surface temperature, excellent TCR, and entirely fire proof construction. These resistors are ideally suited to a range of areas where low cost, and efficient thermal performance are important design criteria. Metal film cores adjusted by laser spiral are used where the resistor value is above that suited to wire. Similar performance is obtained although short time overload is slightly derated.

Key Features

- Choice of styles
- Bracketed types available
- Stable TCR 300ppm/°C
- Custom designs welcome
- Inorganic flame proof construction

Applications


- Capacitor pre-charge
- Capacitor discharge
- Inrush limiting
- Braking




Characteristics - Electrical

| | Test Condition | Performance |
|-------------------------------|--|-------------|
| Resistance Temp. Coefficient: | -55°C ~ 155°C | ± 300ppm/°C |
| *Short Time Overload: | 10 times rated power for 5 seconds | ± 2% |
| Rated Load: | Rated power for 30 minutes | ± 1% |
| Voltage Withstand: | 1000V AC 1 minute | no change |
| Insulation Resistance: | 500V megger | 1000meg |
| Temperature Cycle: | -30°C ~ 85°C for 5 cycles | ± 1% |
| Load Life: | 70°C on-off cycle for 1000 hours | ± 5% |
| Moisture-proof Load Life: | 40°C 95% RH on-off cycle 1000 hours | ± 5% |
| Incombustibility: | 16 times rated wattage for 5 minutes | No flame |
| Max. Overload Voltage: | 2 times max. working voltage | |
| *Metal Film Elements: | Short time overload 5 times rated power, 5 seconds | |

Derating Curve




Load Against Temperature



Dimensions -

Type SQP - Horizontal




| Power Rating | Dimensions | | | | | Resistance Range | | Max. Working Voltage |
|--------------|------------|------|-------|--------|------|------------------|-------------|----------------------|
| | W±1 | H±1 | L±1.5 | d±0.05 | ±0.3 | Wire | Metal Film | |
| 2W | 7 | 7 | 18 | 0.65 | 23 | R10 - 82R | 83R - 10K | 150V |
| 3W | 8 | 8 | 22 | 0.8 | 35 | R10 - 180R | 181R - 33K | 350V |
| 5W | 10 | 9 | 22 | 0.8 | 35 | R10 - 180R | 181R - 100K | 350V |
| 7W | 10 | 9 | 35 | 0.8 | 35 | R10 - 430R | 431R - 100K | 500V |
| 10W | 10 | 9 | 48 | 0.8 | 35 | R10 - 470R | 471R - 100K | 750V |
| 15W | 12.5 | 11.5 | 48 | 0.8 | 35 | R50 - 600R | 601R - 150K | 1000V |
| 20-25W | 14 | 13.5 | 60 | 0.8 | 35 | R50 - 1K0 | 1.1K - 150K | 1000V |

Rated Continuous Working Voltage (RCWV)


RCWV: $\sqrt{\text{Rated Power} \times \text{Resistance Value}}$ or Maximum Working Voltage listed above whichever is lower

Type SQH - Horizontal with Solder Lugs




| Power Rating | Dimensions | | | | | | Resistance Range | |
|--------------|------------|------|--------|-------|-------|--|------------------|------------|
| | W ±1 | H ±1 | L ±1.5 | P | H1 ±1 | | Wire | Metal Film |
| 10W | 10 | 10 | 48 | 32 ±1 | 21 | | R50 - 600R | 601R - 50K |
| 15W | 12.5 | 11.5 | 48 | 32 ±1 | 21 | | 1R0 - 600R | 601R - 50K |
| 20W | 14.5 | 13.5 | 60 | 42 ±1 | 24 | | 1R0 - 1K0 | 1K1 - 50K |
| 30W | 19 | 19 | 75 | 55 ±2 | 31 | | 1R0 - 2K0 | — |
| 40W | 19 | 19 | 90 | 67 ±2 | 31 | | 1R0 - 2K0 | — |

Type SQB - Horizontal with Solder Lugs & Bracket



| Power Rating | Dimensions | | | |
|--------------|------------|--------|--------|--------|
| | A ±0.5 | B ±0.5 | C ±0.5 | G ±0.5 |
| 10W | 8.0 | 5.0 | 12.0 | 3.0 |
| 15W | 8.0 | 5.5 | 12.0 | 3.0 |
| 20W | 8.0 | 5.5 | 12.0 | 3.0 |
| 30W | 10.5 | 8.0 | 18.0 | 3.5 |
| 40W | 10.5 | 8.0 | 18.0 | 3.5 |


Type SQZ - Horizontal Pluggable



| Power Rating | Dimensions | | | | | | | | | | | Resistance Range | |
|--------------|------------|------|--------|--------|-----|----|----|-----|-------|-------|--|------------------|-------------|
| | W ±1 | H ±1 | L ±1.5 | P ±1.5 | P1 | P2 | P3 | P4 | H1 ±1 | H2 ±1 | | Wire | Metal Film |
| 5W | 10 | 10 | 28 | 15 | 4.2 | 2 | 5 | 1.5 | 25 | 10.5 | | R10 - 130R | 131R - 100K |
| 7W | 10 | 10 | 36 | 20 | 4.2 | 2 | 5 | 1.5 | 25 | 10.5 | | R10 - 430R | 431R - 100K |
| 10W | 10 | 10 | 48 | 32 | 4.2 | 2 | 5 | 1.5 | 25 | 10.5 | | R20 - 470R | 471R - 100K |
| 15W | 12.5 | 12 | 48 | 32 | 4.2 | 2 | 5 | 1.5 | 26 | 10.5 | | 1R0 - 600R | 601R - 150K |
| 20W-25W* | 15 | 13 | 60 | 42 | 7 | 6 | 10 | 2.7 | 36 | 15.0 | | 1R0 - 1K0 | 1K1 - 150K |

*NB: 20W & 25W Devices Terminations are not crimped


Type SQM - Vertical



| Power Rating | Dimensions | | | | Resistance Range | |
|--------------|------------|------|--------|--------|------------------|-------------|
| | W ±1 | H ±1 | S ±1.5 | P ±2.0 | Wire | Metal Film |
| 2W | 11 | 20 | 7 | 5 | R10 - 82R | 83R - 10K |
| 3W | 12 | 25 | 8 | 5 | R10 - 180R | 181R - 33K |
| 5W | 13 | 25 | 9 | 5 | R10 - 180R | 181R - 100K |
| 7W | 13 | 39 | 9 | 5 | R10 - 430R | 431R - 100K |
| 10W | 13 | 51 | 9 | 5 | R10 - 470R | 471R - 100K |
| 10WS | 16 | 35 | 12 | 7.5 | R10 - 360R | 361R - 100K |

N.B. Custom design versions in wire at low tolerances, better TCR, and higher ohmic values are available to special order. Please enquire.

Type SPS - Vertical Mounting with Stabilising Bracket



| Power Rating | Dimension | | Resistance Range | |
|--------------|-----------|--------|------------------|-------------|
| | L ±1.5 | K ±0.5 | Wire | Metal Film |
| 7W | 48 | 8.5 | R10 - 430R | 431R - 100K |
| 10W | 60 | 20 | R10 - 470R | 471R - 100K |


TE has offered the C Series of vitreous enamelled wire-wound resistors for more than 25 years and as a result of continuous development and investment in the latest production equipment now supplies a product with a proven record of reliability and quality. These economically priced resistors are capable of dissipating high power from a relatively small size in harsh environmental conditions. The resistors are manufactured from quality materials for optimum reliability and stability.

Key Features

- Vitreous enamel coated
- Up to 14W power
- All welded construction
- Overload 10 x 5 seconds
- Ammo packed or reeled (3 - 7W)

Applications


- Capacitor pre-charge
- Capacitor discharge
- Inrush limiting
- Balancing




Characteristics - Electrical

| | C3A | C7 | C10 | C14 |
|--|--|-----|-----|------|
| Wattage at 40°C: | 4 | 7 | 10 | 14 |
| Ohmic Value (min): | R10 | R10 | R10 | R10 |
| (max): | 10K | 27K | 47K | 100K |
| Limiting Element Voltage (DC/AC rms): | 200 | 350 | 500 | 650 |
| Resistance Tolerance: | 10%, 5%, 2% (1% by request on a limited value range) | | | |
| Temperature Coefficient of Resistance (Ohmic Value): | Above 1R0 90ppm/°C | | | |
| Overload Resistance Change (up to 10x Rated Wattage for 5 Secs): | ΔR less than 1% | | | |
| Load Life Stability at Rated Wattage (resistance change): | 1000 hours ΔR less than 3% 8000 hours ΔR less than 5% | | | |
| Shelf life stability (Resistance Change): | 2 years ΔR less than 0.25% | | | |
| Power Derating: | Derate from 40°C linearly to zero at 350°C | | | |

Surface Temperature v Power Dissipation



Dimensions



| Type | L | D | d | I | Measuring Distance |
|------|------|-----|-----|------|--------------------|
| C3A | 13.0 | 5.7 | 0.8 | 35.0 | 30.7 |
| C7 | 22.0 | 8.5 | 0.8 | 35.0 | 37.7 |
| C10 | 38.1 | 8.5 | 0.8 | 35.0 | 52.8 |
| C14 | 53.3 | 8.5 | 0.8 | 35.0 | 69.5 |


This range of power wire-wound resistors are wound on continuous glass fiber elements or have a ceramic core depending on resistance value. The element is housed in a ceramic case and sealed with an inorganic silica filler. Their construction gives a resistor with high insulation resistance and low surface temperature, capable of withstanding high overload currents. These resistors are ideally suited to a variety of applications within industrial and commercial environments, where performance and reliability are of prime importance. Applications include fan force ovens, cooker hoods, power supplies and triac based speed controls. Custom design variants in value and style are welcomed.

Key Features

- Vertical or axial mount
- Up to 17W
- Customer specials invited
- Fusible styles
- Widely available from distribution

Applications


- Pre-charge
- Discharge
- Braking
- In rush limiting
- Pulse withstand




Characteristics - Electrical

| | |
|--|---|
| Resistance Values: | Series E24 5% E12 10% (see tables for value limits per style) |
| Resistance Tolerance: | ±5% ±10% |
| Maximum Continuous Voltage: | $\sqrt{P \times R}$ |
| Load Life: | $\Delta R < \pm 3\%$ 1000 hours at 70°C |
| Power Rating: | See Surface Temperature Curve (below) |
| Temperature Coefficient of Resistance: | 200ppm/°C (400ppm/°C below 18R) |
| Dielectric Strength: | 2000V RMS |

Surface Temperature Rise Curve




Derating Curve




Dimensions


Type SBC (No Flutes in Ceramic)




Type SBCH (Flutes in Ceramic)



Type SBCLF (Externally Fused Style)



Type SBCV (Vertical Mount Style)



Ceramic Styles



| Model | Power Max | Ohmic Values | | Dimensions | | |
|----------|-----------|--------------|-----|------------|-----|----|
| | | Min | Max | A | B | L |
| SBC-2 | 4W | R20 | 6K8 | 6.4 | 6.4 | 20 |
| SBC-4 | 5W | R30 | 10K | 6.4 | 6.4 | 25 |
| SBC-6 | 7W | R47 | 22K | 6.4 | 6.4 | 38 |
| SBC-8 | 9W | 1R0 | 8K2 | 9 | 9 | 38 |
| SBC-11 | 11W | 1R0 | 22K | 9 | 9 | 50 |
| SBC-15 | 17W | 1R0 | 22K | 9 | 9 | 75 |
| SBCH-4 | 4W | R20 | 6K8 | 7 | 8 | 20 |
| SBCH-5 | 5W | R30 | 10K | 7 | 8 | 25 |
| SBCH-6 | 7W | R47 | 22K | 7 | 8 | 38 |
| SBCH-7 | 7W | R33 | 10K | 9 | 10 | 25 |
| SBCH-8 | 9W | 1R0 | 8K2 | 9 | 10 | 38 |
| SBCH-11 | 11W | 1R0 | 22K | 9 | 10 | 50 |
| SBCH-15 | 17W | 1R0 | 22K | 9 | 10 | 75 |
| SBCLF-4 | 4W | 2R2 | 2K2 | 10 | 9 | 25 |
| SBCLF-5 | 5.5W | 2R2 | 5K6 | 10 | 9 | 38 |
| SBCLF-7 | 7W | 3R3 | 8K2 | 10 | 9 | 50 |
| SBCLF-10 | 10W | 4R7 | 12K | 10 | 9 | 75 |
| SBCV-6 | 7W | R47 | 22K | 9 | 10 | 25 |
| SBCV-8 | 9W | 1R0 | 8K2 | 9 | 10 | 38 |
| SBCV-11 | 11W | 1R0 | 22K | 9 | 10 | 50 |
| SBCV-15 | 17W | 1R0 | 22K | 9 | 10 | 75 |

A silicone coated power resistor. The ER series is suited to a wide range of industrial, control, medical and consumer applications and is available in a vertical mounting style. While very slightly larger than the ER series and manufactured to a marginally different specification, the ES series is suited to volume requirements in power supplies, process control instruments, communication equipment and other industrial positions.

Key Features

- Tough silicone coating
- Special pulse styles available
- 0.5% tolerance available
- Resistant to most solvents
- Vertical mount styles available
- Custom designs welcomed
- 0.5W - 10W sizes

Applications

- Capacitor pre-charge
- Capacitor discharge
- Inrush limiting
- Balancing
- Braking




Characteristics - Electrical


| | ES0.5W | ES1W | ES2W | ES3W | ES3WY | ES5W | ES6W | ES7W | ES8W | ES10W | ER74 | ER58 | ER16 | ER17 | ERV74 | ERV58 | ERV16 |
|-------------------------------|---------|----------|----------|----------|-----------|----------|---------|---------|---------|---------|---------|---------|---------|----------|---------|---------|---------|
| Power Rating at 20°C (W): | 1/2 | 1 | 2 | 3 | 3 | 5 | 6 | 7 | 8 | 10 | - | - | - | - | 3* | 7* | 11* |
| Power Rating at 40°C (W): | - | - | - | - | - | - | - | - | - | - | 3 | 7 | 11 | 14 | - | - | - |
| Power Rating at 70°C (W): | - | - | - | - | - | - | - | - | - | - | 2.5 | 6 | 9 | 12 | 1.5* | 3* | 5* |
| Resistance Range: | R05-68R | R05-100R | R05-150R | R05-200R | 201R-470R | R10-390R | R10-1K0 | R10-1K5 | R10-2K2 | R10-3K3 | R03-10K | R05-20K | R13-68K | R20-100K | R10-3K9 | R10-6K8 | R15-27K |
| Dielectric Withstand Voltage: | 350V | 500V | 500V | 500V | 500V | 500V | 500V | 500V | 800V | 1000V | - | - | - | - | - | - | - |
| Max. Element Volts: | - | - | - | - | - | - | - | - | - | - | 100V | 200V | 500V | 700V | 100V | 200V | 500V |

* When mounted in the horizontal and vertical plane only - inverted mounting may result in heat damage of the PCB - Please contact your local Product Information Center or go to te.com/help


Power Ratings Dissipation / Ambient Temperature




Power Ratings Hot Spot Temperature @ 40°C




Surface Temperature Vs Power



Dimensions



| Type | ES0.5W | ES1W | ES2W | ES3W | ES3WY | ES5W | ES6W | ES7W | ES8W | ES10W | ER74 | ER58 | ER16 | ER17 |
|------|------------|------------|------------|------------|------------|------------|------------|------------|------------|------------|------|------|------|------|
| D | 3.0 ±1.0 | 4.0 ±1.0 | 5.0 ±1.0 | 5.5 ±1.0 | 6.0 ±1.0 | 6.5 ±1.0 | 8.5 ±1.0 | 8.5 ±1.0 | 8.5 ±1.0 | 8.5 ±1.0 | 6.0 | 8.0 | 8.0 | 8.0 |
| L | 9.0 ±1.5 | 9.0 ±1.5 | 11.0 ±1.5 | 13.0 ±1.5 | 17.0 ±1.5 | 20.0 ±1.5 | 25.0 ±1.5 | 32.0 ±1.5 | 41.0 ±1.5 | 53.0 ±1.5 | 13.5 | 22.2 | 38.1 | 53.5 |
| I | 30.0 ±3.0 | 30.0 ±3.0 | 30.0 ±3.0 | 38.0 ±3.0 | 38.0 ±3.0 | 38.0 ±3.0 | 38.0 ±3.0 | 38.0 ±3.0 | 38.0 ±3.0 | 33.0 ±3.0 | 38.0 | 38.0 | 38.0 | 38.0 |
| d | 0.65 ±0.05 | 0.65 ±0.05 | 0.80 ±0.05 | 0.80 ±0.05 | 0.80 ±0.05 | 0.80 ±0.05 | 0.80 ±0.05 | 0.80 ±0.05 | 0.80 ±0.05 | 0.80 ±0.05 | 0.8 | 0.8 | 0.8 | 0.8 |



| Type | A | B | C |
|-------|------|-----|------|
| ERV74 | 19.0 | 5.6 | 9.7 |
| ERV58 | 29.0 | 8.0 | 10.6 |
| ERV16 | 43.0 | 8.0 | 10.6 |

- Resistance measured 6mm either side of body.
- Supplied in standard packs in arrays of 5 resistors with snap links for handling.


The SBL series is a low ohmic non-inductive resistor with a low temperature coefficient in a fully insulated ceramic housing. It is ideal for applications in power supply regulation, motor control current monitoring, feedback control loops, overload sensors and radio frequency applications. The solid metal element has welded copper terminals and is encapsulated in a ceramic housing, filled with compressed silica sand.

Key Features

- 4W & 5W versions
- Solid metal element
- Non-inductive
- Low temperature coefficient
- 4W device available in distribution

Applications


- Current sense




Characteristics - Electrical

| | |
|-------------------------|---|
| Resistance Values (4W): | R005, R01, R015, R018, R022, R033, R047, R051 |
| Resistance Values (5W): | R01, R015, R018, R022, R033, R047, R051 |
| Resistance Tolerance: | ± 5% |
| Rated Dissipation (4W): | 4W at 70°C |
| Rated Dissipation (5W): | 5W at 70°C |
| Dielectric Strength: | 2000V |


Temperature Co-Efficient of Resistance




Temperature Rise



Derating Curve



Dimensions



The YP series resistors are coated a multilayer silicone and the terminals are designed for quick and easy mounting on capacitors and have a mounting pitch of 22.2 and 31.8 mm. These are wire-wound ceramic core resistors designed for voltage balancing of series connected aluminium electrolytic capacitors. These resistors are also suitable for capacitor voltage discharge safety applications in high voltage circuits. Ideally suited for industrial grade capacitors.

Key Features

- Flameproof silicone coating
- Stainless steel mounting terminals for direct mounting on capacitors
- Direct mounting onto capacitors
- Custom designs possible
- Innovative design

Applications


- Capacitor pre-charge
- Capacitor discharge
- Inrush limiting



Characteristics - Electrical

| | |
|--------------------------|--|
| Resistance Values: | 2K, 10K, 18K, 27K, 47K. Other values on request and to order |
| Resistance Tolerance: | ±5% |
| Temperature Coefficient: | ±30ppm/°C (typ.), ±100ppm/°C (maximum) |
| Maximum Voltage: | 825V DC or AC rms for YP10, 570V for YP8 |
| Derating: | Derated linearly to zero at 350°C |
| Power Rating: | 10W @ 70°C for YP10 and 8W @ 70°C for YP8 |
| Stability: | 70°C, 1000hr - R/R @ 100% load <±5% |
| Standard: | Performance as per BS - CECC 40201-002 |
| Marking: | Type, resistance value, tolerance |

Dimensions



| Type | A ±1mm | B max. | C ±1mm | D ±1mm | E ±1mm |
|------|--------|--------|--------|--------|--------|
| YP8 | 22.2 | 40 | 15 | 21 | 9.5 |
| YP10 | 31.8 | 50 | 15 | 21 | 9.5 |

TE supplies high specification power resistors for specialist applications. The HVR range consists of high power, high voltage resistors capable of operating up to 50kV (continuous) and dissipating 50W in air or 100W oil. The thick film resistor element is designed to minimize inductance and capacitance giving optimum performance at MHz frequencies, and resistance to high voltage surges.

Key Features

- Highly versatile product
- 50kV continuous operating voltage
- Low inductance and capacitance
- Established product

Applications


- High frequency switching (MHz)
- Balancing
- Voltage divider
- High voltage




Characteristics - Electrical

| | HVR10 | HVR20 | HVR30 | HVR50 |
|--|--------------------|--------------------|--------------------|-------------|
| Ohmic Value min/max (Ω): | 2K0-1G0 | 2K0-1G0 | 2K0-1G0 | 2K0-1G0 |
| Resistor Tolerance - standard (%): | 10% | 10% | 10% | 10% |
| Options (R<400M): | 5%, 1% | 5%, 1% | 5%, 1% | 5%, 1% |
| Power Dissipation at 20°C (W): | 5W | 15W | 25W | 50W |
| At 70°C: | 3W | 10W | 15W | 25W |
| In Oil at 20°C: | 10W | 30W | 50W | 100W |
| Continuous Operating Voltage max (V): | 10kV | 20kV | 30kV | 50kV |
| Temperature Coefficient of Resistance 20°C to 70°C (ppm/°C): | < ± 300 ppm/°C | < ± 300 ppm/°C | < ± 300 ppm/°C | < 300ppm/°C |
| Voltage Coefficient of Resistance - V > 100V (%): | < $\pm 2\%$ | < $\pm 2\%$ | < $\pm 2\%$ | < $\pm 2\%$ |
| Stability ΔR - 1000h load life (%): | < $\pm 2\%$ | < $\pm 2\%$ | < $\pm 2\%$ | < $\pm 2\%$ |


Derating Curve




Surface Temperature Rise




Dimensions Style B



Style D



Style C



Style B

| Type | A | E | L | N | P |
|-------|------|------|-------|-------|------|
| HVR10 | 6.3 | 12.0 | 60.0 | 53.2 | 18.2 |
| HVR20 | 10.0 | 22.6 | 120.0 | 109.0 | 27.0 |
| HVR30 | 17.5 | 30.6 | 120.0 | 109.0 | 34.0 |
| HVR50 | 17.5 | 30.6 | 240.0 | 229.0 | 34.0 |

Style C

| Type | A | E | L | N | P |
|-------|------|------|-------|---|---|
| HVR10 | 6.3 | 10.5 | 60.0 | - | - |
| HVR20 | 10.0 | 20.2 | 120.0 | - | - |
| HVR30 | 17.5 | 28.2 | 120.0 | - | - |
| HVR50 | 17.5 | 28.2 | 240.0 | - | - |

Style D

| Type | A | E | L | N | P |
|-------|------|------|-------|---|---|
| HVR10 | 6.3 | 10.0 | 70.0 | - | - |
| HVR20 | 10.0 | 21.5 | 140.0 | - | - |
| HVR30 | 17.5 | 30.0 | 140.0 | - | - |
| HVR50 | 17.5 | 30.0 | 260.0 | - | - |


TE supplies standard and custom designed high value/high voltage resistors for high voltage, industrial, control, medical and general-purpose use. The HB is a tough epoxy coated high voltage resistor, with axial or radial leads, values up to 1GΩ and an operational voltage to 20kV as standard and 30kV to order. The resistors are made from quality materials for optimum reliability and stability. TE can test resistors to conform to relevant international, MIL or customer specifications. TE offers advice on the use of resistors for high frequency applications and to supply information for high voltage use. Please contact your local Product Information Center or go to te.com/help

Key Features

- Up to 15kV element voltage
- High ratio of size to power
- 1k0Ω to 1G0Ω
- Low inductance
- Established proven reliability

Applications


- High voltage divider
- Surge
- Filter
- Balancing
- Inrush limiting




Characteristics - Electrical

| | HBA | HB1 | HB3 |
|--|------------------------------------|---------------------|------------------------------------|
| Power Dissipation - Power @ 20°C (70°C) (W): | 0.8 (0.4) | 2.0 (1.0) | 4.0 (2.0) |
| Ohmic Value - min/max (Ohms): | 1K-120M | 10K-1G | 10K-1G |
| Resistance Tolerance (%) (Tighter by Request): | 1%, 2%, 5% | 1%, 2%, 5% | 1%, 2%, 5% |
| Maximum Working Voltage - DC or ACrms (Volts): | 1kV | 7.5kV | 15kV |
| Insulation Resistance - Epoxy Coated, @500V DC (Ohms): | >10 ⁹ MΩ | >10 ⁹ MΩ | >10 ⁹ MΩ |
| Temperature Coefficient (ppm/°C): | ±100ppm/°C | ±100ppm/°C | ±100ppm/°C |
| (±20ppm/°C Available to Special Order) | | | |
| Voltage Coefficient: | Negligible up to 100K | | Negligible up to 200K |
| | Increasing to 0.02ppm/Volt at 800K | | Increasing to 0.01ppm/Volt at 1M0 |
| | Increasing to 1.0ppm/Volt at 5M0 | | Increasing to 1.0ppm/Volt at 10M |
| | Increasing to 2.0ppm/Volt at 50M | | Increasing to 2.0ppm/Volt at 100M |
| | Increasing to 8.0ppm/Volt at 100M | | Increasing to 8.0ppm/Volt at 1000M |
| Ambient Temperature Range (°C): | -55 to 125 | -55 to 125 | -55 to 125 |
| Encapsulation: | Epoxy coating (Optional) | | |


Derating Curve



Surface Temperature Rise



Dimensions



| Type | | A | B | C | D | E | F | G | H | I |
|------|--------------|------|------|------|------|------|------|------|-----|-----|
| HBA | Uncoated | 10.2 | 7 | 1.75 | 60.2 | 5.0 | — | — | — | — |
| | Epoxy Coated | 12.5 | 8 | 2.6 | 60.5 | 5.0 | — | — | — | — |
| HB01 | Uncoated | 8.4 | 26 | 1.5 | 33.8 | 22.9 | 26 | 66 | 1.5 | 8.4 |
| | Epoxy Coated | 10.4 | 26.5 | 3.0 | 35.8 | 22.9 | 26.3 | 66 | 3 | 9.2 |
| HB03 | Uncoated | 8.4 | 51.1 | 1.5 | 33.8 | 48.3 | 51.1 | 91.1 | 1.5 | 8.4 |
| | Epoxy Coated | 10.4 | 52 | 3.0 | 35.8 | 48.3 | 53.5 | 91.1 | 3 | 9.6 |

Lead Length: minimum 20mm

Lead Diameter: Nominal 0.6 ±0.05mm


The HH type resistors offers a very stable high voltage resistor in a compact package with excellent pulse withstand capability. These are used mainly in physical and chemical measuring instruments, X-ray apparatus, electron microscopes and other high voltage industrial applications. The HJ type resistors have higher reliability when they are mounted on board, and excellent long-term stability. These are used mainly in semiconductor equipments, X-ray apparatus, and many other measuring instruments.

Key Features

- Low TCR's
- Close resistance tolerances
- Small compact size
- Excellent long-term stability
- High resistance to pulse voltages
- Special coatings for high humidity
- High thermal shock resistance

Applications


- Balancing




Characteristics - Electrical

| Type | Power Rating @ 25°C (Watt) | Max. Working Voltage DC (kV) | Impulse Voltage (kV) 1.2 x 50 Microseconds | Resistance Range (Ohms) | Resistance Tolerance (%) | Temperature Coefficient (ppm) |
|-------|----------------------------------|------------------------------------|--|-------------------------------|--------------------------------|-------------------------------------|
| HJ55 | 0.25W | 0.75 | 1.5 | 100K-100M | 0.1, 0.25 | ±25, ±50, ±100 |
| HJ60 | 0.5W | 1.5 | 3.0 | 100K-100M | 0.1, 0.25 | ±25, ±50, ±100 |
| HJ65 | 1.0W | 2.0 | 4.0 | 100K-100M | 0.1, 0.25 | ±25, ±50, ±100 |
| HJ70 | 2.0W | 5.0 | 10.0 | 100K-100M | 0.1, 0.25 | ±25, ±50, ±100 |
| HJ80 | 3.0W | 10.0 | 20.0 | 1M-100M | 0.1, 0.25 | ±25, ±50, ±100 |
| HH55 | 0.5W | 1.5 | 3.0 | 100K-100M | 1.0, 2.0, 5.0, 10 | ±25, ±50, ±100 |
| HH60 | 1.0W | 2.0 | 4.0 | 100K-500M | 1.0, 2.0, 5.0, 10 | ±25, ±50, ±100 |
| HH65 | 2.0W | 5.0 | 10.0 | 100K-500M | 1.0, 2.0, 5.0, 10 | ±25, ±50, ±100 |
| HH70 | 3.0W | 10.0 | 20.0 | 100K-500M | 1.0, 2.0, 5.0, 10 | ±25, ±50, ±100 |
| HH80 | 4.0W | 15.0 | 30.0 | 100K-500M | 1.0, 2.0, 5.0, 10 | ±50 |
| | | | | 100K-2G0 | | ±100 |
| HH120 | 6.0W | 20.0 | 40.0 | 100K-500M | 1.0, 2.0, 5.0, 10 | ±50 |
| | | | | 100K-2G0 | | ±100 |

Derating Curve



Dimensions



| Style | D±1.0 | L±1.0 | d±0.05 | I min |
|-------|-------|-------|--------|-------|
| HH55 | 4.5 | 13.0 | 0.8 | 38.0 |
| HH60 | 4.5 | 14.5 | 0.8 | 38.0 |
| HH65 | 5.5 | 26.5 | 1.0 | 38.0 |
| HH70 | 5.5 | 42.0 | 1.0 | 38.0 |
| HH80 | 8.5 | 52.0 | 1.0 | 38.0 |
| HH120 | 8.5 | 77.0 | 1.0 | 38.0 |

| Style | D±1.0 | L±1.0 | d±0.05 | I min |
|-------|-------|-------|--------|-------|
| HJ55 | 3.0 | 9.0 | 0.6 | 38.0 |
| HJ60 | 4.5 | 13.0 | 0.8 | 38.0 |
| HJ65 | 4.5 | 14.5 | 0.8 | 38.0 |
| HJ70 | 5.5 | 26.5 | 1.0 | 38.0 |
| HJ80 | 8.5 | 42.0 | 1.0 | 38.0 |

Metal glaze resistors are manufactured using thick film techniques. The ceramic slugs have the thick film applied, the film is fired and end caps are forced onto the slugs, the resistive element is spiralled to value and lead wires are welded onto the end caps. Four layers of coating are applied - the first being a phenolic resin, the other three being epoxy.

Key Features

- Stable thick film elements
- High working voltages
- High ohmic values

Applications


- Balancing
- Snubber




Characteristics - Electrical

| | RGP0207CH | RGP50 | RGP100 | RGP200 | RGP300 | RGP400 |
|---------------------------------|-------------|-------|--------|--------|--------|--------|
| Rated Power @ 70°C (W): | 0.25 | 0.5 | 1 | 2 | 3 | 4 |
| Resistance Range (Ohms) min: | 1M0 | 1M0 | 1M0 | 1M0 | 1M0 | 1M0 |
| max: | 1G0 | 3G0 | 5G0 | 5G0 | 10G | 10G |
| Tolerance (%): | 5 10 | | | | | |
| Code Letter: | J K | | | | | |
| Temp. Coefficient max (ppm/°C): | ±350 | | | | | |
| Selection Series: | E24 | | | | | |
| Limiting Element Voltage (V): | 750 | 1K0 | 1K5 | 5K0 | 10K | 15K |
| Maximum Overload Voltage (V): | 1K0 | 1K5 | 2K5 | 7K5 | 15K | 20K |
| Operating Temp. Range (°C): | -55 to +155 | | | | | |
| Climatic Category: | 55/155/56 | | | | | |
| Voltage Coefficient (±%/V): | 0.005 | | | | | |
| Typical Noise at 47MΩ: | 0.75 | | | | | |
| Dielectric Strength (V): | 300 | | | | | |
| Insulation Resistance (MΩ): | 1000 | | | | | |

Derating Curve



Dimensions



| Style | L ± 1 | D ± 0.5 | d ± 0.1 | l ± 2 |
|-----------|-------|---------|---------|-------|
| RGP0207CH | 6.5 | 2.5 | 0.6 | 28 |
| RGP50 | 13.0 | 4.5 | 0.8 | 38 |
| RGP100 | 14.5 | 5.5 | 0.8 | 38 |
| RGP200 | 27.0 | 7.0 | 0.8 | 38 |
| RGP300 | 42.0 | 7.0 | 0.8 | 38 |
| RGP400 | 52.0 | 8.0 | 1.0 | 38 |

The RR Series is manufactured by depositing a homogeneous film of metal alloy onto a high-grade ceramic body. After a helical groove has been cut in the resistive layer, tinned connecting wires of electrolytic copper are welded to the end-caps. The resistors are coated with a red, non-flammable lacquer, which provides electrical, mechanical and climatic protection.

Key Features

- Metal film technology
- High power, small package
- Excellent long-term stability
- High surge/overload capability
- High stability/reliability

Applications


- Pre-charge
- Discharge
- Snubbing
- Balancing
- Pulse withstand



Characteristics - Electrical


| | RR01 1W | | RR02 2W | | RR03 3W | |
|-------------------------------|------------|--------------|------------|--------------|------------|--------------|
| Resistance Range: | 0.22Ω-1MΩ | 10R - 1M0 | 0.33Ω-1MΩ | 10R - 1M0 | 0.33Ω-1MΩ | 10R - 1M0 |
| Tolerance and Series: | ±5%, E24 | ±1%, E24/E96 | ±5%, E24 | ±1%, E24/E96 | ±5%, E24 | ±1%, E24/E96 |
| Temperature Coefficient: | ±300ppm/°C | | | | | |
| Limiting Voltage (DC or RMS): | 350V | | 500V | | 750V | |

Derating Curve




Maximum dissipation (Pmax) in percentage of rated power as a function of ambient temperature (Tamb)

Fusing Characteristics




Pulse Characteristics




Maximum permissible peak pulse power (Pmax) as a function of pulse duration (Tt)

— 1W — 2W — 3W

Dimensions



| | L ±1 | øD ±0.5 | ød ±0.1 | l ±3 |
|------|------|---------|---------|------|
| RR01 | 6.8 | 2.6 | 0.65 | 30 |
| RR02 | 9.0 | 3.5 | 0.8 | 30 |
| RR03 | 15.0 | 5.0 | 0.8 | 30 |



Condition test: Resistance change ≤±5% with pulse 1000 cycles as like the figure (reference only).

1. Added power and added voltage are within the lower territory of this graph.

2. Added in normal temperature and humidity.


The resistive element comprises a metal oxide film deposited on a ceramic former. The element is protected by a flameproof coating which will withstand overload conditions without flame or mechanical damage. They are recommended for use in applications such as line protection.

Key Features

- High power, small size
- Complete flameproof construction
- High surge/overload capability
- Special lead formations possible
- Custom lead forming

Applications


- Capacitor pre-charge
- Capacitor discharge
- Balancing
- Snubber




Characteristics - Electrical

| | ROX05 | ROX1 | ROX2 | ROX05S | ROX1SS | ROX1S | ROX2S | ROX3S | ROX5S |
|--|-----------------|------------|------------|------------|-----------------------------|------------|------------|------------|------------|
| Rated Power @ 70°C (W): | 0.5 | 1 | 2 | 0.5 | 1 | 1 | 2 | 3 | 5 |
| Resistance Range min/max(Ω) | 0.1 - 330K | 0.1 - 470K | 0.1 - 560K | 0.1 - 100K | 0.1 - 200R | 0.1 - 270K | 0.1 - 470K | 0.1 - 560K | 0.1 - 560K |
| Tolerance and Code Letter: | 2% (G) / 5% (J) | | | | 1% (F) available on request | | | | |
| Temp. Coefficient max (ppm/°C): | ± 350 | | | | | | | | |
| Limiting Element Voltage (V): | 250 | 350 | 350 | 250 | 350 | 350 | 350 | 350 | 500 |
| Maximum Overload Voltage (V): | 400 | 600 | 600 | 400 | 400 | 600 | 600 | 600 | 800 |
| Max Intermittent Overload Voltage (V): | 500 | 750 | 750 | 500 | 500 | 750 | 750 | 750 | 1500 |
| Dielectric Strength (V): | 250 | 350 | 350 | 250 | 350 | 350 | 350 | 350 | 500 |


Derating Curve



Heat Rise Chart



Dimensions



Standard Range Ledged

| Style | D max | L Max | l±3 | d±0.05 |
|-------|-------|-------|-----|--------|
| ROX05 | 3.5 | 10 | 28 | 0.54 |
| ROX1 | 5 | 12 | 25 | 0.7 |
| ROX2 | 5.5 | 16 | 28 | 0.7 |

Standard Range Pre-formed

| Style | P1 ±0.5 | P2 ±2 | H1 | H2 | h max |
|-------|---------|-------|----------|--------|-------|
| ROX05 | 12.5 | 12.5 | 7.5 ±1.5 | 3.5 ±1 | 2.0 |
| ROX1 | 15 | 15 | 7.5 ±1.5 | 3.5 ±1 | 2.0 |
| ROX2 | 20 | 20 | 7.5 ±2.0 | 3.5 ±1 | 3.0 |

"S" Range Ledged

| Style | D max | L Max | l±/3 | d±/-0.05 |
|--------|-------|-------|------|----------|
| ROX05S | 2.5 | 7.5 | 28 | 0.54 |
| ROX1SS | 2.5 | 7.5 | 28 | 0.54 |
| ROX1S | 3.5 | 10 | 28 | 0.54 |
| ROX2S | 5 | 12 | 25 | 0.7 |
| ROX3S | 5.5 | 16 | 28 | 0.7 |
| ROX5S | 8 | 25 | 38 | 0.75 |

"S" Range Pre-formed

| Style | P1 ±0.5 | P2 ±2 | H1 | H2 | h max |
|--------|---------|-------|----------|--------|-------|
| ROX05S | 10 | 10 | 7.5 ±1.5 | 3.5 ±1 | 2.0 |
| ROX1SS | 10 | 10 | 7.5 ±1.5 | 3.5 ±1 | 2.0 |
| ROX1S | 12.5 | 12.5 | 7.5 ±0.5 | 3.5 ±1 | 2.0 |
| ROX2S | 15 | 15 | 7.5 ±1.5 | 3.5 ±1 | 2.9 |
| ROX3S | 20 | 20 | 7.5 ±2.0 | 3.5 ±1 | 3.0 |
| ROX5S | 30 | 30 | 7.5 ±2.0 | 3.5 ±1 | 3.0 |


The CBT and CCR Series of resistors are constructed utilising solid carbon or ceramic composition, which is the traditional medium for absorbing high energy pulses, in cases of high inrush current. These resistors have evolved over many years to have excellent pulse withstand capabilities, whilst remaining very stable. These improved characteristics have been achieved by prudent selection of materials of optimum physical properties and by advances in manufacturing process.

Key Features

- Ceramic or carbon element
- Designed for pulse withstand
- Solid element construction
- High performance
- 0.25W to 2.0W dissipation

Applications

- R-C Snubber circuits
- HV power supplies
- Inrush limiting
- Surge protection





Characteristics - Electrical

| | CBT25 | CBT50 | CCR1/2 | CCR1 | CCR2 |
|-----------------------------------|--|------------------------------|------------------------------|----------------------------|----------------------------|
| Power at 70°C Ambient: | 0.25W derating to 0 at +125°C | 0.5W derating to 0 at +125°C | 0.5W derating to 0 at +200°C | 1W derating to 0 at +200°C | 2W derating to 0 at +200°C |
| Maximum Voltage: | 250 V | 350 V | 200V | 300V | 400V |
| Resistance Range: | 1R0 - 5M6 | 1R0 - 22M | 10R - 100K | 3R3 - 390K | 3R3 - 390K |
| Resistance Values: | 5% E24 Series/10% E12 Series/20% E6 Series | 10% E12 series | 10% E12 series | 10% E12 series | 10% E12 series |
| Voltage Coefficient: | ± 0.035%/V | ± 0.035%/V | — | — | — |
| Limiting Element Voltage: | 250 V | 350 V | — | — | — |
| Maximum Overload Voltage: | 400 V | 700 V | 400V | 600V | 800V |
| Dielectric Withstand Voltage: | — | — | 500 V | 500 V | 700 V |
| Impulse Withstanding Voltage*: | — | — | 10 Kv | 14 Kv | 20 Kv |
| Temperature Coefficient (ppm/°C): | — | — | <100R: -900 to ±300 | >100R: -1300 to ±300 | |


NB *: Please refer to Resistance to Pulse Circuit

Pulse Withstand Characteristics


Charging and discharging a 2000pF Capacitor for 100 Cycles




Resistance to Pulse Circuit




Resistance to Pulse Graphs - CCR1



CCR2



Dimensions



| Style | L | D | d (nom) | I |
|--------|------------|-----------|---------|---------|
| CBT25 | 6.3 ± 0.7 | 2.4 ± 0.1 | 0.6 | 27 min. |
| CBT50 | 9.5±0.8 | 3.6±0.2 | 0.7 | 25 min. |
| CCR1/2 | 9.0 ± 1.0 | 3.5 ± 0.5 | 0.7 | 30 ± 3 |
| CCR1 | 16.5 ± 1.0 | 5.5 ± 1.0 | 0.8 | 38 ± 3 |
| CCR2 | 19.0 ± 1.0 | 7.0 ± 1.0 | 0.8 | 38 ± 3 |

Wire-wound

Traditional design, consisting of resistance wire wrapped around a ceramic core. Robust, cheap, and with a relatively high element mass, wire-wound elements provide excellent value due to their ability for withstanding high currents and absorption of large energy pulses. These resistors are available in a variety of sizes and are suited to applications where high short term overload capacity or very high power ratings are required.

Suitable Applications:

- Braking
- Inrush limiting
- Crowbar
- Pre-charge
- Capacitor discharge

Preferred Product Types:

C • CFH • CJB • CJS • ER • ES • HS/THS
LOAD BANK • R5000 • SBC • SQ • TT/TE • YP

Thick Film

Thick film resistive elements consist of a metal and glass films printed onto a flat or tubular ceramic surface. Offering very low inductance values, these elements can be manufactured with a wide resistance range then laser trimmed to a high degree of accuracy. Benefits of this technology are the high thermal efficiencies allowing the resistor to have a higher power density compared with conventional wire-wound elements.

Suitable Applications:

- Balancing resistors
- Snubbing

Preferred Product Types:

BDS • HB • HH • HJ • HVR • MPC • MPT • RGP

Thin Film

A sputtered film of metal alloy deposited onto a ceramic surface. Commonly used in the manufacturing of precision resistors. Suited to high specification or technically demanding circuits whilst offering excellent thermal efficiency.

Suitable Applications:

- Inrush limiting
- Snubbing

Preferred Product Types:

MPR • RGP • RR • ROX

Foil

The element is formed by etching or punching a metal alloy into a serpentine shape which is then enclosed into a resistor package. This technology has a high element mass enabling it to withstand high energy pulses whilst offering good thermal efficiency and low inductance. Foil elements offer a robust solution but are limited in resistance value.

Suitable Applications:

- Braking
- Inrush limiting
- Snubbing

Preferred Product Types:

BDF • R5000

Carbon Composition / Ceramic Composition

Consisting of either a bulk carbon or ceramic core, this technology is used when protection is required from high energy pulses.

Suitable Applications:

- Inrush limiting
- Protection

Preferred Product Types:

CBT • CCR

Pre-Charge Resistor

This is used on system start up to charge the DC coupling capacitor. The resistor limits the inrush current during charging of the DC coupling capacitor. This capacitor sits across the DC voltage source to keep the line voltage constant when the input voltage drops low. The resistor must be able to absorb high energy from a single pulse, over a short time.

- **Key Feature:** Short-term overload capability

Capacitor Discharge Resistor

The resistor is fitted across the capacitor terminals to provide a safety function. When the voltage to the capacitor is removed, the resistor discharges any residual voltage in the capacitor making it safe to touch. The resistor must handle continuous power as it dissipates power continuously when the capacitor is connected to a voltage source.

- **Key Feature:** Continuous power dissipation

Inrush Limiting Resistor

Similar to precharge resistor, but offers protection to the rectifier section of circuit.

- **Key Feature:** Short-term overload capability

Braking Resistor

The resistor is used in a variable speed drive to absorb the energy created when the motor decelerates quickly. These can be fitted internally or externally to the drive. The rate that the motor decelerates is controlled by the amount of energy dumped into the resistor. During the braking cycle (deceleration) lots of little pulses of energy are dissipated by the resistor over a short period of time.

- **Key Feature:** Dissipation of repetitive energy pulses

Crowbar Resistor

The resistor is used to drop the voltage to earth safely, generating a zero voltage in the circuit when a fault has been detected.

- **Key Feature:** Ability to absorb large short-term energy and voltage overloads, with a high insulation resistance

Balancing Resistor

The resistor is used to balance the voltage across critical components (such as IGBTs) when they are connected in series. This is to ensure that each component has equal voltage stress during operation.

- **Key Feature:** Tight tolerance, low power and high ohmic value

Current Sense Resistor

A low ohmic resistor creates a small voltage drop in the circuit. As the current in the circuit changes the voltage drop will vary. The change in voltage drop is used to measure the current to or from the circuit. This current can be monitored allowing an action in the control software.

- **Key Feature:** Low ohmic value, high accuracy


Snubber Resistor

The resistor is used to absorb transient high voltage spikes produced by switching a solid state switch (like relays, IGBTs, GTOs, etc.). It is connected in series with a capacitor across the switch. These switching operations can be very high frequency therefore the resistor must have a low inductance, so that the transient spike is not transferred back into the switch.

- **Key Feature:** Dissipation of repetitive energy pulses, low inductance

Note: Partial Discharge

A resistor with low partial discharge is a requirement of many of the applications above. Partial discharge is a form of high voltage test that can be used to measure the life of the component. It measures the amount and size of voids in the insulation and therefore the quality of it.



Related Literature

Passive Components - Literature No. 1309350

Passive Components Resistors - Literature No. 1773442-9

Passive Components Capacitors - Literature No. 4-1773449-3

FOR MORE INFORMATION

te.com/passives

te.com/wind

For email, phone or live chat, go to: te.com/help

TE Connectivity Customer Support:

| | |
|-------------------|-----------------------|
| USA: | +1 (800) 522-6752 |
| Canada: | +1 (905) 475-6222 |
| Mexico: | +52 (0) 55-1106-0800 |
| Latin/S. America: | +54 (0) 11-4733-2200 |
| Germany: | +49 (0) 6251-133-1999 |
| UK: | +44 (0) 800-267666 |
| France: | +33 (0) 1-3420-8686 |
| Netherlands: | +31 (0) 73-6246-999 |
| China: | +86 (0) 400-820-6015 |

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.

*as defined te.com/leadfree

te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.
4-1773455-8 CIS BI 05/2011

FASTON, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks of the TE Connectivity Ltd family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

