

## **2021** | **Industrial Power Solutions**

IEC /EN / UL 62368-1 Approved

AC/DC Power Supplies & DC/DC Converters



## Company Profile

TRACO Electronic AG is a Swiss company with headquarters based in Baar, Switzerland. As a leading power supply specialist with more than 40 years experience we are dedicated to the design and manufacturing of high quality DC/DC and AC/DC power conversion products.

TRACO markets its products worldwide under the registered trademark TRACO POWER. Our mission is to provide our customers with optimal power supply solutions in terms of performance, quality and cost for their individual application.

## The varying levels of industrial power supplies

All power supplies designed for use in non-medical application are required to meet the international safety standards of IEC/EN/UL 62368-1. Industrial grade power supplies are subjected to increased requirements which vary depending upon their environment, typically divided into 2 categories, one for office /manufacturing environments and another for harsh/hazardous environments.

For power supplies in household applications, there are virtually no differences when it comes to insulation and operational safety. However, stronger electromagnetic and conducted disturbances are expected to arise in industrial environments, and electrical power supplies must be resistant to these. EMC immunity tests according to the generic standard IEC 61000-6-2 „immunity for industrial environments“ is the common denominator for a power supply being classified as industrial-grade.

### The right product for the application and environment / standard products

Traco Power offers a wide selection of standard industrial power supplies that are manufactured and tested according to the varying environments and applicable safety standards, allowing our customers to choose the power solution that is most cost-effective for their application and environmental requirements.

### All our industrial rated power supplies provide following features as standard:

- Safety approval according IEC/EN/UL 62368-1 (for 3000 VAC I/O isolation)
- EMC immunity according IEC 61000-6-2
- EMC emission according EN 55032 class B
- Protection against short circuit, overload and output over-voltage

### Customer specific applications / customized solutions

It is often not possible to find a standard power supply that fully complies with the respective requirements or without unnecessary features making the application more expensive. With our design company **TRACO POWER SOLUTIONS** we have a center of competence to develop and optimize power supplies for customer-specific requirements. The motto from our design team is “Reduced to the Max” and develop or modify a solution specific to your needs at the lowest cost of ownership.

# INDEX

EACH PRODUCT CATEGORY INCLUDES A DETAILED INDEX ON THE FIRST PAGE

Category	Power Range	Pages
----------	-------------	-------

## DC/DC Converters

### Non-Isolated / Point-of-Load Regulators

SIP .....	0.5 ~ 3 Amp .....	3 ~ 8
Surface Mount.....	0.5 ~ 1 Amp .....	9 ~ 10

### Isolated

Surface Mount.....	1 ~ 5 Watt.....	11 ~ 20
SIP.....	1 ~ 9 Watt.....	21 ~ 38
DIP .....	1 ~ 60 Watt .....	39 ~ 80
Brick.....	40 ~ 240 Watt.....	81 ~ 86
Chassis Mount .....	6 ~ 300 Watt .....	87 ~ 99

<b>Surge Filter</b> .....	20 ~ 300 Watt.....	100
---------------------------	--------------------	-----

## AC/DC Power Supplies

### Encapsulated

Chassis Mount .....	5 ~ 100 Watt .....	101 ~ 108
PCB Mount.....	3 ~ 100 Watt .....	109 ~ 122

<b>Open Frame</b> .....	15 ~ 850 Watt.....	123 ~ 134
-------------------------	--------------------	-----------

<b>Enclosed</b> .....	15 ~ 960 Watt.....	135 ~ 150
-----------------------	--------------------	-----------

<b>IP67 / 68 External Mount</b> .....	6 ~ 120 Watt .....	151 ~ 154
---------------------------------------	--------------------	-----------

## DIN Rail Power

<b>AC/DC Power</b> .....	6 ~ 600 Watt .....	155 ~ 159
--------------------------	--------------------	-----------






<b>DC/DC Power</b> .....	20 ~ 60 Watt .....	160
--------------------------	--------------------	-----

<b>Function Modules</b> .....		161-165
-------------------------------	--	---------

<b>Alphanumeric Index</b> .....		166
---------------------------------	--	-----

## ICONS USED THROUGHOUT CATALOG

All isolated products >5 watts in this in catalog are **IEC/EN/UL 62368-1** approved for ITE/IoT/ industrial applications. The icons listed below are used to highlight products with additional safety approvals.

-  IEC/EN/ES 60601-1 3rd Edition (BF rated | 2xMOPP)
-  EN60335-1 Approved (household appliance)
-  EN50155 / EN61373 (railway / ruggedized applications)
-  UL508 LISTED (industrial / DIN rail applications)
-  HAZARDOUS LOCATION (ATEX / UL HazLoc Class I Div 2)



# Non-Isolated / Point-of-Load Regulators (SIP-3 / TO-220 Pinout)


Our SIP-3 non-isolated / point-of-load regulators provide output currents up to 3 Amps with high-efficiency operation. Convection-cooled operation combined with the standard SIP 3 / TO-220 pinout, make these true alternatives to less efficient linear regulators.

SERIES	AMPS	DESCRIPTION	STATUS	PAGE
<b>TSR 0.5</b>	0.5	SIP-3 package, 4.75-32 Vin, pos.-pos. circuit, LM78 compatible	ACTIVE	4
<b>TSR 0.6WI</b>	0.6	SIP-3 package, 9-72 Vin, pos.-pos. circuit, LM78 compatible	<b>NEW</b>	4
<b>TSN 1</b>	1	SIP-3 package, -7.0 to -32 Vin, neg.-neg. circuit, LM78 compatible	ACTIVE	5
<b>TSR 1</b>	1	SIP-3 package, 4.6-36 Vin, pos.-pos. circuit, LM78 compatible	ACTIVE	5
<b>TSR 1E</b>	1	SIP-3 package, 6-36 Vin, pos.-pos. circuit, cost efficient, LM78 compatible	<b>NEW</b>	6
<b>TSR 1WI</b>	1	SIP-3 package, 9-72 Vin, pos.-pos. circuit, LM78 compatible	<b>NEW</b>	6
<b>TSRN 1</b>	1	SIP-3 package, 4.6-42 Vin, pos.-neg. circuit, LM78 compatible	ACTIVE	7
<b>TSR 2</b>	2	SIP-3 package, 3.0-36 Vin, pos.-pos. circuit, LM78 compatible	ACTIVE	7
<b>TSR 3</b>	3	SIP-3 package, 2.5-30 Vin, pos.-pos. circuit, open frame, LM78 compatible	ACTIVE	8



# DC/DC: Non-Isolated / Point-of-Load Regulators (SIP-3 / TO-220 Pinout)

## TSR 0.5 0.5 Amp




- 0.45 x 0.40 x 0.30" SIP-3 package
- Very high efficiency up to 97%
- Excellent line/load regulation
- Low standby current
- Temperature range -40 to 90°C
- Over-temperature protection
- Short circuit protection
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSR 0.5-2415	4.75 - 32 VDC	1.5 VDC	500 mA	73 %
TSR 0.5-2418		1.8 VDC		82 %
TSR 0.5-2425		2.5 VDC		87 %
TSR 0.5-2433		3.3 VDC		91 %
TSR 0.5-2450		5 VDC		94 %
TSR 0.5-2465	8 - 32 VDC	6.5 VDC	95 %	
TSR 0.5-2490	11 - 32 VDC	9 VDC	96 %	
TSR 0.5-24120	15 - 32 VDC	12 VDC	97 %	
TSR 0.5-24150	18 - 32 VDC	15 VDC	97 %	

Pinout	
Pin	Function
1	+Vin
2	GND
3	+Vout

## TSR 0.6WI NEW! 0.6 Amp




- 0.53 x 0.47 x 0.34" SIP-3 Package
- Ultra-wide 8:1 input range: 9-72 VDC
- Covers a majority of standard bus- and battery voltages
- Up to 94% efficiency - No heatsink required
- Pin compatible with LMxx linear regulators
- Temperature range -40 to +85°C
- Low standby current
- Excellent line/load regulation
- Protection against short circuit, overvoltage and overtemperature
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TSR 0.6-4833WI	9 - 72 VDC	3.3 VDC	600 mA	85 %	
TSR 0.6-4850WI		5 VDC		89 %	
TSR 0.6-4865WI		6.5 VDC		91 %	
TSR 0.6-4890WI		14 - 72 VDC		9 VDC	92 %
TSR 0.6-48120WI		17 - 72 VDC		12 VDC	93 %
TSR 0.6-48150WI	20 - 72 VDC	15 VDC	94 %		
TSR 0.6-48240WI	33 - 72 VDC	24 VDC	400 mA	94 %	

Pinout	
Pin	Function
1	+Vin
2	GND
3	+Vout

**TSN 1** 1 Amp




- 0.55 x 0.45 x 0.30" SIP-3 Package
- Non-isolated converter for negative output
- Pin compatible with LM79xx linear regulators
- No heatsink required
- High efficiency up to 96%
- Operation temp. range -40°C to +85°C
- Overload, short circuit and over-temperature protection
- Fixed switching frequency
- Wide input range up to -32 VDC
- Excellent line / load regulation
- Low standby current
- 3 year product warranty

Pinout	
Pin	Single
1	GND
2	-Vin
3	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSN 1-2450	-7.0 - -32 VDC	-5.0 VDC	-1.0 A	91.5 %
TSN 1-2452	-7.0 - -32 VDC	-5.2 VDC		92.0 %
TSN 1-2460	-8.0 - -32 VDC	-6.0 VDC		92.5 %
TSN 1-2480	-10.5 - -32 VDC	-8.0 VDC		94.0 %
TSN 1-2490	-11.5 - -32 VDC	-9.0 VDC		94.5 %
TSN 1-24120	-15 - -32 VDC	-12.0 VDC		96.0 %
TSN 1-24150	-18 - -32 VDC	-15.0 VDC		96.0 %

**TSR 1** 1 Watt



- 0.46 x 0.40 x 0.30" SIP 3 package
- Up to 96% efficiency – No heat-sink required
- Pin compatible with LMxx linear regulators
- SIP-package fits existing TO-220 footprint
- Built in filter capacitors
- Operation temp. range -40°C to +85°C
- Short circuit protection
- Wide input operating range
- Excellent line / load regulation
- Low standby current
- 3 year product warranty

Pinout	
Pin	Single
1	+Vin
2	GND
3	+Vout


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSR1-2412	4.6 - 36 VDC	1.2 VDC	1 Amp	74%
TSR1-2415		1.5 VDC		78%
TSR1-2418		1.8 VDC		82%
TSR1-2425		2.5 VDC		87%
TSR1-2433		3.3 VDC		91%
TSR1-2450		5 VDC		94%
TSR1-2465		6.5 VDC		93%
TSR1-2490		9 VDC		95%
TSR1-2412		12 VDC		95%
TSR1-2415		15 VDC		96%

## DC/DC: Non-Isolated / Point-of-Load Regulators (SIP-3 / TO-220 Pinout)

TSR 1E

**NEW!**

1 Amp



- 0.45 x 0.40 x 0.30" SIP-3 package
- Cost efficient design
- Up to 92% efficiency - No heat-sink required
- Pin compatible with LMxx linear regulators
- Built in filter capacitors
- Operation temp. range -40°C to +85°C
- Short circuit protection
- Wide input operating range
- Excellent line / load regulation
- Low standby current
- 3 year product warranty


Pinout	
Pin	Function
1	+ Vin
2	GND
3	+ Vout

Model	Input Voltage Range	Output Voltage	Output Current max.	Efficiency
TSR 1-2433E	6-36 VDC	3.3 VDC	1000 mA	88 %
TSR 1-2450E	7-36 VDC	5 VDC	1000 mA	92 %

TSR 1WI

**NEW!**

1 Amp



- 0.69 x 0.48 x 0.34" SIP-3 package
- Ultra-wide 8:1 input range: 9-72 VDC
- Covers a majority of standard bus and battery voltages
- Up to 93% efficiency - No heatsink required
- Pin compatible with LMxx linear regulators
- Temperature range -40 to +80°C
- Low standby current
- Excellent line/load regulation
- Protection against short circuit, overvoltage and overtemperature
- 3 year product warranty


Pinout	
Pin	Function
1	+Vin
2	GND
3	+Vout
4	Case pin
5	Case pin

Model	Input Voltage Range	Output Vnom	Output Imax	Efficiency
TSR 1-4833WI	9 - 72 VDC	3.3 VDC	1000 mA	83 %
TSR 1-4850WI		5 VDC		87 %
TSR 1-4865WI		6.5 VDC		88 %
TSR 1-4890WI	14 - 72 VDC	9 VDC		90 %
TSR 1-48120WI	17 - 72 VDC	12 VDC		93 %
TSR 1-48150WI	21 - 72 VDC	15 VDC	93 %	
TSR 1-48240WI	33 - 72 VDC	24 VDC	700 mA	92 %



TSRN 1

1 Amp




- 0.46 x 0.40 x 0.30 SIP-3 package
- Fits existing TO-220 footprint
- Suitable for positive & negative output circuit
- Pin compatible with LMxx linear regulators
- Built in filter capacitors
- Operation temp. range -40°C to +85°C
- No heat-sink required
- Over-temperature & short circuit protection
- Wide input range up to 42 VDC
- Excellent line/load regulation
- 3 year product warranty

Pinout	
Pin	Function
1	+Vin
2	GND
3	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSRN 1-2415	4.6 - 42 VDC	1.5 VDC	1000 mA	77 %
TSRN 1-2418		1.8 VDC		81 %
TSRN 1-2425		2.5 VDC		84 %
TSRN 1-2433		3.3 VDC		88 %
TSRN 1-2450		5 VDC		92 %
TSRN 1-2465	6.5 - 42 VDC	6.5 VDC	1000 mA	93 %
TSRN 1-2490	8 - 42 VDC	9 VDC		95 %
TSRN 1-24120	10.5 - 42 VDC	12 VDC		95 %
TSRN 1-24150	13.5 - 42 VDC	15 VDC		95 %
TSRN 1-24150	16.5 - 42 VDC	15 VDC		95 %

TSR 2


2 Amp



- 0.55 x 0.30 x 0.40" SIP-3 Package
- Up to 96% efficiency - No heat-sink required
- Pin compatible with LMxx linear regulators
- Built in filter capacitors
- Temperature range -40°C to +85°C
- Excellent line / load regulation
- Short circuit protection
- 3 year product warranty

Pinout	
Pin	Function
1	+Vin
2	GND
3	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSR 2-0512	3 - 5.5 VDC	1.2 VDC	2000 mA	90%
TSR 2-0515		1.5 VDC		91%
TSR 2-0518		1.8 VDC		92%
TSR 2-0525	3.8 - 5.5 VDC	2.5 VDC	2000 mA	95%
TSR 2-2412	4.6 - 36 VDC	1.2 VDC		84%
TSR 2-2415		1.5 VDC		86%
TSR 2-2418		1.8 VDC		87%
TSR 2-2425		2.5 VDC		89%
TSR 2-2433		3.3 VDC		91%
TSR 2-2450	4.75 - 36 VDC	5 VDC		94%
TSR 2-2465	6.5 - 36 VDC	6.5 VDC		94%
TSR 2-2490	9 - 36 VDC	9 VDC		95%
TSR 2-24120	12 - 36 VDC	12 VDC		95%
TSR 2-24150	15 - 36 VDC	15 VDC	96%	



Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TSR 3-0533	2.5 - 5.5 VDC	0.6 - 3.3V	3.00 A	95%
TSR 3-1250	4.5 - 14 VDC	0.6 - 6.0 V		93%
TSR3-2450	10 - 30 VDC	3.0 - 6.0 V		91%
TSR 3-24150	10 - 30 VDC	5.0 - 15 V		95%

- High performance
- 3Amp switching regulator
- Suitable for positive & negative output
- High efficiency up to 95%
- Adjustable output voltages
- Wide input voltage ranges
- Short circuit protection
- Remote On/Off
- Low output ripple & noise
- 3 year product warranty

Pinout		
Pin	positive	negative
1	Remote On/Off	
2	+Vin (Vcc)	
3	GND	-Vout
4	+Vout	GND
5	Trim	


# Non-Isolated / Point-of-Load Regulators (Surface Mount)

Our SMD non-isolated / point of load regulators provide output currents up to 1 Amp with high efficiency operation. Convection-cooled operation surface mount packaging make these ideal power solutions for a broad range of applications.

SERIES	AMPS	DESCRIPTION	STATUS	PAGE
TSR 0.5SM	0.5	SMD (DIP-10) package, 4.75-32 VDC input, pos.-pos. circuit	ACTIVE	9
TSR 1SM	1	SMD (DIP-10) package, 3.0-36 VDC input, pos.-pos. circuit	ACTIVE	10
TSRN 1SM	1	SMD (DIP-10) package, 3.0-42 VDC input, pos.-neg. circuit	ACTIVE	10

## TSR 0.5SM

0.5 Amp



Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSR 0.5-2415SM	4.75 - 32 VDC	1.5 VDC	500 mA	73 %
TSR 0.5-2418SM		1.8 VDC		82 %
TSR 0.5-2425SM		2.5 VDC		87 %
TSR 0.5-2433SM		3.3 VDC		91 %
TSR 0.5-2450SM	6.5 - 32 VDC	5 VDC	94 %	
TSR 0.5-2465SM	8 - 32 VDC	6.5 VDC	95 %	
TSR 0.5-2490SM	11 - 32 VDC	9 VDC	96 %	
TSR 0.5-24120SM	15 - 32 VDC	12 VDC	97 %	
TSR 0.5-24150SM	18 - 32 VDC	15 VDC	97 %	


- 0.60 x 0.49 x 0.49" SMD package
- Very high efficiency up to 97%
- Excellent line / load regulation
- Low standby current
- Operating temperature range -40 to 90°C
- Over-temperature and short circuit protection
- Remote On/Off input
- Adjustable output voltage
- Moisture sensitivity level 2 as per IPC J-STD-033C
- 3 year product warranty

Pinout	
Pin	Function
1	+Vin
2	+Vin
3	GND
4	+Vout
5	+Vout
6	Trim
7	GND
8	GND
9	GND
10	Remote On/Off



# DC/DC: Non-Isolated / Point-of-Load Regulators (Surface Mount)

## TSR 1SM 1 Amp




- 0.60 x 0.47 x 0.30" SMD package
- Up to 96% efficiency
- No thermal layer required
- Built in filter capacitors
- Operation temp. range -40°C to +85°C
- Short circuit protection
- Wide input operating range
- Excellent line / load regulation
- Low standby current
- 3 year product warranty

Pinout	
Pin	Function
1	+Vin
5	+Vout
6	Trim
7	GND
9	GND
10	Remote On/Off

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSR 1-0512SM	3 - 5.5 VDC	1.2 VDC	1000 mA	91 %
TSR 1-0515SM		1.5 VDC		92 %
TSR 1-0518SM		1.8 VDC		93 %
TSR 1-0525SM	3.8 - 5.5 VDC	2.5 VDC		95 %
TSR 1-2412SM	4.6 - 36 VDC	1.2 VDC		74 %
TSR 1-2415SM		1.5 VDC		79 %
TSR 1-2418SM		1.8 VDC		82 %
TSR 1-2425SM		2.5 VDC		87 %
TSR 1-2433SM		3.3 VDC		91 %
TSR 1-2450SM	4.75 - 36 VDC	5 VDC		94 %
TSR 1-2465SM	6.5 - 36 VDC	6.5 VDC	94 %	
TSR 1-2490SM	9 - 36 VDC	9 VDC	95 %	
TSR 1-24120SM	12 - 36 VDC	12 VDC	95 %	
TSR 1-24150SM	15 - 36 VDC	15 VDC	96 %	

## TSRN 1SM 1 Amp



- 0.60 x 0.46 x 0.30" SMD package
- Positive & negative output circuit
- Adjustable output voltage
- Wide input up to 42 VDC
- Remote On/Off input
- Built in filter capacitors
- Operation temp. range -40°C to +85°C
- Excellent line/load regulation
- Low standby current
- 3 year product warranty

Pinout	
Pin	Function
1	+Vin
5	+Vout
6	Trim
7	GND
9	GND
10	Remote On/Off

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TSRN 1-0525SM	3 - 5.5 VDC	2.5 VDC	1000 mA	96 %
TSRN 1-2433SM	4.6 - 42 VDC	3.3 VDC		88 %
TSRN 1-2450SM	6.5 - 42 VDC	5 VDC		92 %
TSRN 1-2490SM	10.5 - 42 VDC	9 VDC		95 %
TSRN 1-2490SM	13.5 - 42 VDC	12 VDC		95 %
TSRN 1-24150SM	16.5 - 42 VDC	15 VDC		96 %

# DC/DC: Isolated Surface Mount Package


TRACO POWER's range of isolated DC/DC converters in SMD package consists of products from 1 to 5W with unregulated or regulated outputs. All models provide high pin accuracy and are qualified for automated pick-and-place machines and withstand lead-free reflow solder processes and comply with IPC J-STD-020D standard.

SERIES	DESCRIPTION		STATUS	WATTS	PAGE
<b>TDN 1WISM</b>	4:1 input, regulated, high power density, encapsulated		ACTIVE	1	12
<b>TES 1</b>	DIP-10, ±10% input, unregulated		ACTIVE	1	12
<b>TES 1V</b>	DIP-12, ±10% input, unregulated, 3000 VDC I/O-isolation, plastic case		ACTIVE	1	13
<b>TMR 1SM</b>	DIP-14, 2:1 input, regulated		ACTIVE	1	13
<b>TRN 1SM</b>	2:1 input, regulated, cost efficient, encapsulated		ACTIVE	1	14
<b>TDR 2SM</b>	DIP-14, 2:1 input, regulated, overmold (washable)		ACTIVE	2	14
<b>TDR 2WISM</b>	DIP-14, 4:1 input, regulated, overmold (washable)		ACTIVE	2	15
<b>TES 2H</b>	DIP-10, ±10% input, unregulated		ACTIVE	2	15
<b>TES 2M</b>	DIP-16, ±10% input, unregulated, 4000 VAC I/O-isolation (reinforced)	⊕	ACTIVE	2	16
<b>TIM 2SM</b>	DIP-16, 2:1 input, 5000 VAC I/O-isolation, encapsulated	⊕	<b>NEW</b>	2	16
<b>TRS 2</b>	2:1 input, regulated, cost efficient, encapsulated		ACTIVE	2	17
<b>TDN 3WISM</b>	4:1 input, regulated, high power density, encapsulated		ACTIVE	3	17
<b>TDR 3SM</b>	DIP-14, 2:1 input, regulated, overmold (washable)		ACTIVE	3	18
<b>TDR 3WISM</b>	DIP-14, 4:1 input, regulated, overmold (washable)		ACTIVE	3	18
<b>TRN 3SM</b>	2:1 input, regulated, cost efficient, encapsulated		ACTIVE	3	19
<b>TIM 3.5SM</b>	DIP-16, 2:1 input, 5000 VAC I/O-isolation, encapsulated	⊕	<b>NEW</b>	3.5	19
<b>TDN 5WISM</b>	4:1 input, regulated, high power density, encapsulated		ACTIVE	5	20

**APPS KEY:** ⊕ = IEC/EN/ES 60601-1 (2×MOPP Approved)

# DC/DC: Isolated / Surface Mount Package

## TDN 1WISM 1 Watt




- 0.56 x 0.36 x 0.40" SMD package
- Fully regulated outputs
- I/O-isolation 1600 VDC
- Temperature range -40°C to +90°C without derating
- Short circuit protection
- Remote On/Off
- 3 year product warranty
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	On/Off	On/Off
5	no con.	-Vout
6	-Vout	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDN 1-1210WISM	4.5 - 18 VDC (12 VDC nominal)	3.3 VDC	300 mA	77 %
TDN 1-1211WISM		5.0 VDC	200 mA	79 %
TDN 1-1219WISM		9.0 VDC	112 mA	79 %
TDN 1-1212WISM		12 VDC	90 mA	81 %
TDN 1-1213WISM		15 VDC	70 mA	81 %
TDN 1-1215WISM		24 VDC	45 mA	80 %
TDN 1-1221WISM		± 5.0 VDC	±100 mA	77 %
TDN 1-1222WISM		±12 VDC	±45 mA	80 %
TDN 1-1223WISM		±15 VDC	±35 mA	81 %
TDN 1-2410WISM		9 - 36 VDC (24 VDC nominal)	3.3 VDC	300 mA
TDN 1-2411WISM	5.0 VDC		200 mA	78 %
TDN 1-2419WISM	9.0 VDC		112 mA	79 %
TDN 1-2412WISM	12 VDC		90 mA	81 %
TDN 1-2413WISM	15 VDC		70 mA	81 %
TDN 1-2415WISM	24 VDC		45 mA	80 %
TDN 1-2421WISM	± 5.0 VDC		±100 mA	77 %
TDN 1-2422WISM	±12 VDC		±45 mA	80 %
TDN 1-2423WISM	±15 VDC	±35 mA	81 %	
TDN 1-4810WISM	18 - 75 VDC (48 VDC nominal)	3.3 VDC	300 mA	75 %
TDN 1-4811WISM		5.0 VDC	200 mA	78 %
TDN 1-4819WISM		9.0 VDC	112 mA	79 %
TDN 1-4812WISM		12 VDC	90 mA	81 %
TDN 1-4813WISM		15 VDC	70 mA	81 %
TDN 1-4815WISM		24 VDC	45 mA	80 %
TDN 1-4821WISM		± 5.0 VDC	±100 mA	77 %
TDN 1-4822WISM		±12 VDC	±45 mA	80 %
TDN 1-4823WISM		±15 VDC	±35 mA	81 %

## TES 1 1 Watt



- 0.54 x 0.43 x 0.26" Single Outputs
- 0.64 x 0.43 x 0.26" Dual Outputs
- I/O isolation 1500 VDC
- Unregulated device
- Single and dual output models
- Input voltage 5, 12 and 24 VDC
- High efficiency up to 80%
- Temperature range -40°C to +90°C
- High accuracy of pin co-planarity
- Qualified for leadfree reflow solder process according IPC/JEDEC (J-STD-020C)
- Available in tape and reel package
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TES 1-0510	5 VDC ±10% (nominal 5 VDC)	3.3 VDC	300 mA	73 %	
TES 1-0511		5 VDC	200 mA	78 %	
TES 1-0519		9 VDC	110 mA	78 %	
TES 1-0512		12 VDC	85 mA	78 %	
TES 1-0513		15 VDC	65 mA	79 %	
TES 1-0521		±5 VDC	±100 mA	74 %	
TES 1-0522		±12 VDC	±40 mA	78 %	
TES 1-0523		±15 VDC	±35 mA	78 %	
TES 1-1211		12 VDC ±10% (nominal 12 VDC)	5 VDC	200 mA	76 %
TES 1-1219			9 VDC	110 mA	78 %
TES 1-1212	12 VDC		85 mA	79 %	
TES 1-1213	15 VDC		65 mA	80 %	
TES 1-1221	±5 VDC		±100 mA	74 %	
TES 1-1222	±12 VDC		±40 mA	78 %	
TES 1-1223	±15 VDC		±35 mA	79 %	
TES 1-2411	24 VDC ±10% (nominal 24 VDC)		5 VDC	200 mA	78 %
TES 1-2419		9 VDC	110 mA	77 %	
TES 1-2412		12 VDC	85 mA	79 %	
TES 1-2413		15 VDC	65 mA	79 %	
TES 1-2421		±5 VDC	±100 mA	73 %	
TES 1-2422		±12 VDC	±40 mA	78 %	
TES 1-2423		±15 VDC	±35 mA	78 %	


Pinout			
Pin	Single	Pin	Dual
1	-Vin (GND)	1	-Vin (GND)
2	+Vin (Vcc)	2	+Vin (Vcc)
4	-Vout	4	Common
5	+Vout	5	-Vout
8	*NC	7	+Vout
-		10	*NC

\* Pin to be isolated from circuitry



TES 1V

1 Watt




- 0.64 x 0.31 x 0.31" SMD package
- I/O isolation voltage 3000 VDC
- Unregulated device
- Single and dual output models
- High efficiency up to 80%
- Temperature range -40°C to +85°C
- High accuracy of pin co-planarity
- Qualified for leadfree reflow solder according IPC/JEDEC J-STD-020D
- Available in tape and reel package
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin	+Vin
3	No con.	No con.
5	-Vout	Common
6	No con.	-Vout
7	No con.	No con.
8	+Vout	+Vout
10	No con.	No con.
11	No con.	No con.
12	No con.	No con.

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TES 1-0510V	5 VDC ±10% (nominal 5 VDC)	3.3 VDC	260 mA	72 %
TES 1-0511V		5.0 VDC	200 mA	75 %
TES 1-0512V		12 VDC	84 mA	79 %
TES 1-0513V		15 VDC	67 mA	80 %
TES 1-0521V		±5 VDC	±100 mA	75 %
TES 1-0522V		±12 VDC	±42 mA	79 %
TES 1-0523V	±15 VDC	±34 mA	80 %	
TES 1-1210V	12 VDC ±10% (nominal 12 VDC)	3.3 VDC	260 mA	73 %
TES 1-1211V		5.0 VDC	200 mA	76 %
TES 1-1212V		12 VDC	84 mA	80 %
TES 1-1213V		15 VDC	67 mA	81 %
TES 1-1221V		±5 VDC	±100 mA	76 %
TES 1-1222V		±12 VDC	±42 mA	80 %
TES 1-1223V	±15 VDC	±34 mA	80 %	
TES 1-2410V	24 VDC ±10% (nominal 24 VDC)	3.3 VDC	260 mA	70 %
TES 1-2411V		5.0 VDC	200 mA	73 %
TES 1-2412V		12 VDC	84 mA	79 %
TES 1-2413V		15 VDC	67 mA	79 %
TES 1-2421V		±5 VDC	±100 mA	73 %
TES 1-2422V		±12 VDC	±42 mA	79 %
TES 1-2423V	±15 VDC	±34 mA	79 %	

TMR 1SM

1 Watt



- 0.74 x 0.54 x 0.33" SMD package
- Wide 2:1 input voltage range
- Fully regulated outputs
- Cost optimised design
- No minimum load required
- Continuous short circuit protection
- Temperature range -40°C to +85°C
- I/O isolation 1500 VDC
- Remote On/Off control
- 3 year product warranty


Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	Remote	Remote
6	NTC	Common
7	NTC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin	+Vin

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 1-0511SM	4.5 - 9 VDC (5 VDC nom.)	5 VDC	200 mA	78 %
TMR 1-0512SM		12 VDC	83 mA	79 %
TMR 1-0513SM		15 VDC	67 mA	81 %
TMR 1-0522SM		+12 VDC	42 mA	79 %
TMR 1-0523SM		+15 VDC	33 mA	80 %
TMR 1-1211SM	9 - 18 VDC (12 VDC nom.)	5 VDC	200 mA	79 %
TMR 1-1212SM		12 VDC	83 mA	79 %
TMR 1-1213SM		15 VDC	67 mA	82 %
TMR 1-1222SM		+12 VDC	42 mA	81 %
TMR 1-1223SM		+15 VDC	33 mA	80 %
TMR 1-2411SM	18 - 36 VDC (24 VDC nom.)	5 VDC	200 mA	79 %
TMR 1-2412SM		12 VDC	83 mA	82 %
TMR 1-2413SM		15 VDC	67 mA	82 %
TMR 1-2422SM		+12 VDC	42 mA	82 %
TMR 1-2423SM		+15 VDC	33 mA	82 %
TMR 1-4811SM	36 - 75 VDC (48 VDC nom.)	5 VDC	200 mA	79 %
TMR 1-4812SM		12 VDC	83 mA	80 %
TMR 1-4813SM		15 VDC	67 mA	80 %
TMR 1-4822SM		+12 VDC	42 mA	81 %
TMR 1-4823SM		+15 VDC	33 mA	81 %

# DC/DC: Isolated / Surface Mount Package

## TRN 1SM

1 Watt




- 0.47 x 0.31 x 0.45" SMD package
- Fully regulated outputs
- 2:1 Input Voltage range
- I/O-isolation 1600 VDC
- Temperature range -40°C to +90°C without derating
- Short circuit protection
- 3 year product warranty
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	+Vout	+Vout
4	no pin	common
5	-Vout	-Vout
6	NC	NC
7	NC	NC

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRN 1-0510SM	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	300 mA	77 %
TRN 1-0511SM		5.0 VDC	200 mA	79 %
TRN 1-0512SM		12 VDC	90 mA	81 %
TRN 1-0513SM		15 VDC	70 mA	82 %
TRN 1-0515SM		24 VDC	45 mA	83 %
TRN 1-0521SM		± 5.0 VDC	±100 mA	79 %
TRN 1-0522SM		±12 VDC	±45 mA	83 %
TRN 1-0523SM	±15 VDC	±35 mA	80 %	
TRN 1-1210SM	9 - 18 VDC (12 VDC nominal)	3.3 VDC	300 mA	77 %
TRN 1-1211SM		5.0 VDC	200 mA	80 %
TRN 1-1212SM		12 VDC	90 mA	81 %
TRN 1-1213SM		15 VDC	70 mA	83 %
TRN 1-1215SM		24 VDC	45 mA	83 %
TRN 1-1221SM		± 5.0 VDC	±100 mA	79 %
TRN 1-1222SM		±12 VDC	±45 mA	83 %
TRN 1-1223SM	±15 VDC	±35 mA	80 %	
TRN 1-2410SM	18 - 36 VDC (24 VDC nominal)	3.3 VDC	300 mA	77 %
TRN 1-2411SM		5.0 VDC	200 mA	81 %
TRN 1-2412SM		12 VDC	90 mA	82 %
TRN 1-2413SM		15 VDC	70 mA	83 %
TRN 1-2415SM		24 VDC	45 mA	82 %
TRN 1-2421SM		± 5.0 VDC	±100 mA	79 %
TRN 1-2422SM		±12 VDC	±45 mA	82 %
TRN 1-2423SM	±15 VDC	±35 mA	80 %	
TRN 1-4810SM	36 - 75 VDC (48 VDC nominal)	3.3 VDC	300 mA	77 %
TRN 1-4811SM		5.0 VDC	200 mA	78 %
TRN 1-4812SM		12 VDC	90 mA	80 %
TRN 1-4813SM		15 VDC	70 mA	81 %
TRN 1-4815SM		24 VDC	45 mA	81 %
TRN 1-4821SM		± 5.0 VDC	±100 mA	78 %
TRN 1-4822SM		±12 VDC	±45 mA	81 %
TRN 1-4823SM	±15 VDC	±35 mA	79 %	

## TDR 2SM

2 Watt




- 0.74 x 0.50 x 0.35" SMD package
- Wide 2:1 input voltage range
- Fully regulated outputs
- Low ripple and noise
- No minimum load required
- Temperature range -40°C to +85°C without derating
- I/O isolation 1600 VDC
- Continuous short-circuit protection
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDR 2-0511SM	4.5 - 9.0 VDC (5 VDC nominal)	5.0 VDC	400 mA	80 %
TDR 2-0512SM		12 VDC	167 mA	81 %
TDR 2-0513SM		15 VDC	134 mA	83 %
TDR 2-0522SM		±12 VDC	±83 mA	81 %
TDR 2-0523SM		±15 VDC	±67 mA	82 %
TDR 2-1211SM	9 - 18 VDC (12 VDC nominal)	5.0 VDC	400 mA	81 %
TDR 2-1212SM		12 VDC	167 mA	81 %
TDR 2-1213SM		15 VDC	134 mA	84 %
TDR 2-1222SM		±12 VDC	±83 mA	83 %
TDR 2-1223SM		±15 VDC	±67 mA	82 %
TDR 2-2411SM	18 - 36 VDC (24 VDC nominal)	5.0 VDC	400 mA	81 %
TDR 2-2412SM		12 VDC	167 mA	84 %
TDR 2-2413SM		15 VDC	134 mA	84 %
TDR 2-2422SM		±12 VDC	±83 mA	84 %
TDR 2-2423SM		±15 VDC	±67 mA	84 %
TDR 2-4811SM	36 - 75 VDC (48 VDC nominal)	5.0 VDC	400 mA	81 %
TDR 2-4812SM		12 VDC	167 mA	82 %
TDR 2-4813SM		15 VDC	134 mA	82 %
TDR 2-4822SM		±12 VDC	±83 mA	83 %
TDR 2-4823SM		±15 VDC	±67 mA	83 %

TDR 2WISM

2 Watt




- 0.74 x 0.50 x 0.35" DIP package
- Ultra-wide 4:1 input voltage range
- Fully regulated outputs
- Low ripple and noise 30mV pk-pk
- No minimum load required
- Temperature range -40°C to +85°C without derating
- I/O isolation 1600 VDC
- Continuous short-circuit protection
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDR 2-1211WISM	4.5 - 18 VDC (12 VDC nominal)	5.0 VDC	400 mA	79 %
TDR 2-1212WISM		12 VDC	167 mA	80 %
TDR 2-1213WISM		15 VDC	134 mA	81 %
TDR 2-1222WISM		±12 VDC	±83 mA	81 %
TDR 2-1223WISM		±15 VDC	±67 mA	81 %
TDR 2-2411WISM	9 - 36 VDC (24 VDC nominal)	5.0 VDC	400 mA	79 %
TDR 2-2412WISM		12 VDC	167 mA	80 %
TDR 2-2413WISM		15 VDC	134 mA	82 %
TDR 2-2422WISM		±12 VDC	±83 mA	81 %
TDR 2-2423WISM		±15 VDC	±67 mA	81 %
TDR 2-4811WISM	18 - 75 VDC (48 VDC nominal)	5.0 VDC	400 mA	78 %
TDR 2-4812WISM		12 VDC	167 mA	81 %
TDR 2-4813WISM		15 VDC	134 mA	82 %
TDR 2-4822WISM		±12 VDC	±83 mA	81 %
TDR 2-4823WISM		±15 VDC	±67 mA	81 %

TES 2H

2 Watt



- Singles: 0.54 x 0.37 x 0.35" package
- Duals: 0.64 x 0.37 x 0.35" package
- I/O isolation voltage 1500 VDC
- Unregulated device
- Single and dual output models
- Input voltage 5, 12 and 24 VDC
- High efficiency up to 80%
- Operating Temperature range -40 to +85°C
- High accuracy of pin co-planarity
- Qualified for leadfree reflow solder process according IPC/JEDEC J-STD-020D
- Available in tape and reel package
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TES 2-0510H	5 VDC ±10% (5 VDC nominal)	3.3 VDC	500 mA	70 %
TES 2-0511H		5.0 VDC	400 mA	73 %
TES 2-0512H		12 VDC	165 mA	77 %
TES 2-0521H		±5 VDC	±200 mA	74 %
TES 2-0522H		±12 VDC	±83 mA	76 %
TES 2-0523H	±15 VDC	±66 mA	76 %	
TES 2-1210H	12 VDC ±10% (12 VDC nominal)	3.3 VDC	500 mA	72 %
TES 2-1211H		5.0 VDC	400 mA	75 %
TES 2-1212H		12 VDC	165 mA	79 %
TES 2-1222H		±12 VDC	±83 mA	80 %
TES 2-1223H		±15 VDC	±66 mA	80 %
TES 2-2410H	24 VDC ±10% (24 VDC nominal)	3.3 VDC	500 mA	72 %
TES 2-2411H		5.0 VDC	400 mA	75 %
TES 2-2412H		12 VDC	165 mA	79 %
TES 2-2422H		±12 VDC	±83 mA	79 %
TES 2-2423H		±15 VDC	±66 mA	79 %

Pinout			
Pin	Single	Pin	Dual
1	-Vin (GND)	1	-Vin (GND)
2	+Vin (Vcc)	2	+Vin (Vcc)
4	-Vout	4	Common
5	+Vout	5	-Vout
8	*NC	7	+Vout
-		10	*NC


\* Pin to be isolated from circuitry

## DC/DC: Isolated / Surface Mount Package

TES 2M

2 Watt

⊕ IEC/EN/ES 60601-1 (2xMOOP)



- 0.94 x 0.54 x 0.35" SMD package
- Supplementary and reinforced insulation
- I/O isolation 4000 VACrms rated for 300 Vrms working voltage
- Unregulated device
- 2xMOOP
- Industrial safety to UL/IEC/EN 60950-1
- Ultracompact SMD-package
- Operating temp. range -25°C to +80°C
- Qualified for lead-free reflow solder process
- Available in tape & reel package
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TES 2-0511M	5.0 VDC ±10% (nominal 05 VDC)	5 VDC	400 mA	66 %
TES 2-0512M		12 VDC	165 mA	66 %
TES 2-0513M		15 VDC	133 mA	66 %
TES 2-0522M		±12 VDC	±83 mA	72 %
TES 2-0523M		±15 VDC	±66 mA	73 %
TES 2-1211M	12.0 VDC ±10% (nominal 12 VDC)	5 VDC	400 mA	66 %
TES 2-1212M		12 VDC	165 mA	66 %
TES 2-1213M		15 VDC	133 mA	66 %
TES 2-1222M		±12 VDC	±83 mA	74 %
TES 2-1223M		±15 VDC	±66 mA	75 %
TES 2-2411M	24 VDC ±10% (nominal 24 VDC)	5 VDC	400 mA	66 %
TES 2-2412M		12 VDC	165 mA	66 %
TES 2-2413M		15 VDC	133 mA	66 %
TES 2-2422M		±12 VDC	±83 mA	74 %
TES 2-2423M		±15 VDC	±66 mA	75 %


Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin	+Vin

TIM 2SM

**NEW!**

2 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 0.95 x 0.57 x 0.40" SMD-16-package
- I/O isolation 5000 VAC rated for 250 VAC working voltage
- Certification according to IEC/EN/ES 60601-1 3rd edition (2 x MOPP)
- Low leakage current < 2 μA
- Extended operating temperature range -40°C to 95°C.
- EMC compliance to IEC 60601-1-2 4th edition and EN 55032 class A
- 5 year product warranty


Pinout / Connection		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	Remote	Remote
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TIM 2-0910SM	4.5 - 12 VDC (9 VDC nom.)	3.3 VDC	600 mA	75 %
TIM 2-0911SM		5 VDC	400 mA	78 %
TIM 2-0919SM		9 VDC	222 mA	78 %
TIM 2-0912SM		12 VDC	167 mA	82 %
TIM 2-0913SM		15 VDC	134 mA	82 %
TIM 2-0915SM		24 VDC	83 mA	82 %
TIM 2-0922SM		±12 VDC	83 mA	82 %
TIM 2-0923SM		±15 VDC	67 mA	80 %
TIM 2-1210SM		9 - 18 VDC (12 VDC nom.)	3.3 VDC	600 mA
TIM 2-1211SM	5 VDC		400 mA	78 %
TIM 2-1219SM	9 VDC		222 mA	79 %
TIM 2-1212SM	12 VDC		167 mA	82 %
TIM 2-1213SM	15 VDC		134 mA	82 %
TIM 2-1215SM	24 VDC		83 mA	81 %
TIM 2-1222SM	±12 VDC		83 mA	81 %
TIM 2-1223SM	±15 VDC		67 mA	81 %
TIM 2-2410SM	18 - 36 VDC (24 VDC nom.)		3.3 VDC	600 mA
TIM 2-2411SM		5 VDC	400 mA	79 %
TIM 2-2419SM		9 VDC	222 mA	80 %
TIM 2-2412SM		12 VDC	167 mA	81 %
TIM 2-2413SM		15 VDC	134 mA	81 %
TIM 2-2415SM		24 VDC	83 mA	81 %
TIM 2-2422SM		±12 VDC	83 mA	81 %
TIM 2-2423SM		±15 VDC	67 mA	81 %
TIM 2-4810SM		36 - 75 VDC (48 VDC nom.)	3.3 VDC	600 mA
TIM 2-4811SM	5 VDC		400 mA	78 %
TIM 2-4819SM	9 VDC		222 mA	79 %
TIM 2-4812SM	12 VDC		167 mA	80 %
TIM 2-4813SM	15 VDC		134 mA	82 %
TIM 2-4815SM	24 VDC		83 mA	81 %
TIM 2-4822SM	±12 VDC		83 mA	81 %
TIM 2-4823SM	±15 VDC		67 mA	81 %



TRS 2

2 Watt




- Most compact package - 0.47 x 0.44 x 0.31"
- Cost-efficient design
- 1600 VDC I/O isolation (functional)
- High efficiency for low thermal loss
- Temperature range -40°C to +90°C
- Designed to met UL 62368-1
- No minimum load required
- Protection against short circuit
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
3	NC	Common
4	NC	-Vout
5	+Vout	+Vout
6	-Vout	Common
7	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRS 2-0910	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	500 mA	77 %
TRS 2-0911		5.0 VDC	400 mA	80 %
TRS 2-0919		9.0 VDC	222 mA	80 %
TRS 2-0912		12 VDC	167 mA	83 %
TRS 2-0913		15 VDC	134 mA	82 %
TRS 2-0915		24 VDC	83 mA	82 %
TRS 2-0921		±5.0 VDC	±200 mA	78 %
TRS 2-0922		±12 VDC	±83 mA	82 %
TRS 2-0923		±15 VDC	±67 mA	80 %
TRS 2-1210		9 - 18 VDC (12 VDC nominal)	3.3 VDC	500 mA
TRS 2-1211	5.0 VDC		400 mA	80 %
TRS 2-1219	9.0 VDC		222 mA	80 %
TRS 2-1212	12 VDC		167 mA	84 %
TRS 2-1213	15 VDC		134 mA	83 %
TRS 2-1215	24 VDC		83 mA	83 %
TRS 2-1221	±5.0 VDC		±200 mA	79 %
TRS 2-1222	±12 VDC		±83 mA	83 %
TRS 2-1223	±15 VDC	±67 mA	81 %	
TRS 2-2410	18 - 36 VDC (24 VDC nominal)	3.3 VDC	500 mA	77 %
TRS 2-2411		5.0 VDC	400 mA	78 %
TRS 2-2419		9.0 VDC	222 mA	80 %
TRS 2-2412		12 VDC	167 mA	84 %
TRS 2-2413		15 VDC	134 mA	84 %
TRS 2-2415		24 VDC	83 mA	82 %
TRS 2-2421		±5.0 VDC	±200 mA	80 %
TRS 2-2422		±12 VDC	±83 mA	83 %
TRS 2-2423	±15 VDC	±67 mA	82 %	
TRS 2-4810	36 - 75 VDC (48 VDC nominal)	3.3 VDC	500 mA	76 %
TRS 2-4811		5.0 VDC	400 mA	79 %
TRS 2-4819		9.0 VDC	222 mA	80 %
TRS 2-4812		12 VDC	167 mA	83 %
TRS 2-4813		15 VDC	134 mA	83 %
TRS 2-4815		24 VDC	83 mA	82 %
TRS 2-4821		±5.0 VDC	±200 mA	78 %
TRS 2-4822		±12 VDC	±83 mA	82 %
TRS 2-4823	±15 VDC	±67 mA	80 %	

TDN 3WISM

3 Watt



- 0.52 x 0.36 x 0.40" SMD package
- I/O-isolation 1600 VDC
- Fully regulated outputs
- Operating temperature range -40°C to +70°C without derating
- Short circuit protection
- Remote On/Off
- 3 year product warranty
- Designed to meet UL 62368-1
- 3 year product warranty


Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	On/Off	On/Off
5	no con.	-Vout
6	-Vout	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDN 3-1210WISM	4.5 - 18 VDC (12 VDC nominal)	3.3 VDC	700 mA	76 %
TDN 3-1211WISM		5.0 VDC	600 mA	80 %
TDN 3-1219WISM		9.0 VDC	333 mA	81 %
TDN 3-1212WISM		12 VDC	250 mA	83 %
TDN 3-1213WISM		15 VDC	200 mA	84 %
TDN 3-1215WISM		24 VDC	125 mA	82 %
TDN 3-1221WISM		± 5.0 VDC	±300 mA	80 %
TDN 3-1222WISM		±12 VDC	±125 mA	82 %
TDN 3-1223WISM		±15 VDC	±100 mA	82 %
TDN 3-2410WISM		9 - 36 VDC (24 VDC nominal)	3.3 VDC	700 mA
TDN 3-2411WISM	5.0 VDC		600 mA	80 %
TDN 3-2419WISM	5.0 VDC		333 mA	81 %
TDN 3-2412WISM	12 VDC		250 mA	83 %
TDN 3-2413WISM	15 VDC		200 mA	83 %
TDN 3-2415WISM	24 VDC		125 mA	82 %
TDN 3-2421WISM	± 5.0 VDC		±300 mA	80 %
TDN 3-2422WISM	±12 VDC		±125 mA	82 %
TDN 3-2423WISM	±15 VDC	±100 mA	82 %	
TDN 3-4810WISM	18 - 75 VDC (48 VDC nominal)	3.3 VDC	700 mA	77 %
TDN 3-4811WISM		5.0 VDC	600 mA	80 %
TDN 3-4819WISM		9.0 VDC	333 mA	81 %
TDN 3-4812WISM		12 VDC	250 mA	83 %
TDN 3-4813WISM		15 VDC	200 mA	83 %
TDN 3-4815WISM		24 VDC	125 mA	82 %
TDN 3-4821WISM		± 5.0 VDC	±300 mA	80 %
TDN 3-4822WISM		±12 VDC	±125 mA	82 %
TDN 3-4823WISM	±15 VDC	±100 mA	82 %	

## DC/DC: Isolated / Surface Mount Package

TDR 3SM

3 Watt





- Compact design in SMD or DIP package
- Wide 2:1 input voltage range
- Fully regulated outputs
- Low ripple and noise
- No minimum load required
- Temperature range -40°C to +85°C
- I/O isolation 1600 VDC
- Continuous short-circuit protection
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDR 3-0511SM TDR 3-0512SM TDR 3-0513SM TDR 3-0522SM TDR 3-0523SM	4.5 - 9.0 VDC (5 VDC nominal)	5.0 VDC 12 VDC 15 VDC ±12 VDC ±15 VDC	600 mA 250 mA 200 mA ±125 mA ±100 mA	79 % 80 % 81 % 80 % 81 %
TDR 3-1211SM TDR 3-1212SM TDR 3-1213SM TDR 3-1222SM TDR 3-1223SM	9 - 18 VDC (12 VDC nominal)	5.0 VDC 12 VDC 15 VDC ±12 VDC ±15 VDC	600 mA 250 mA 200 mA ±125 mA ±100 mA	81 % 82 % 82 % 82 % 83 %
TDR 3-2411SM TDR 3-2412SM TDR 3-2413SM TDR 3-2422SM TDR 3-2423SM	18 - 36 VDC (24 VDC nominal)	5.0 VDC 12 VDC 15 VDC ±12 VDC ±15 VDC	600 mA 250 mA 200 mA ±125 mA ±100 mA	81 % 82 % 83 % 83 % 83 %
TDR 3-4811SM TDR 3-4812SM TDR 3-4813SM TDR 3-4822SM TDR 3-4823SM	36 - 75 VDC (48 VDC nominal)	5.0 VDC 12 VDC 15 VDC ±12 VDC ±15 VDC	600 mA 250 mA 200 mA ±125 mA ±100 mA	81 % 82 % 82 % 83 % 83 %

TMR 3WISM

3 Watt




- 0.86 x 0.44 x 0.36" SMD package
- Ultra-wide 4:1 Input
- I/O-isolation 1500 VDC
- Fully regulated outputs
- Temperature range -40°C to +80°C
- Short circuit and overload protection
- Remote On/Off
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	Remote	Remote
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 3-0511WISM TMR 3-0512WISM TMR 3-0513WISM TMR 3-0515WISM TMR 3-0522WISM TMR 3-0523WISM	4.5 - 12 VDC (9 VDC nom.)	5 VDC 12 VDC 15 VDC 24 VDC +12 VDC +15 VDC	600 mA 250 mA 200 mA 125 mA 125 mA 100 mA	81 % 84 % 84 % 84 % 83 % 83 %
TMR 3-2411WISM TMR 3-2412WISM TMR 3-2413WISM TMR 3-2415WISM TMR 3-2422WISM TMR 3-2423WISM	9 - 36 VDC (24 VDC nom.)	5 VDC 12 VDC 15 VDC 24 VDC +12 VDC +15 VDC	600 mA 250 mA 200 mA 125 mA 125 mA 100 mA	80 % 85 % 85 % 85 % 84 % 84 %
TMR 3-4811WISM TMR 3-4812WISM TMR 3-4813WISM TMR 3-4815WISM TMR 3-4822WISM TMR 3-4823WISM	18 - 75 VDC (48 VDC nom.)	5 VDC 12 VDC 15 VDC 24 VDC +12 VDC +15 VDC	600 mA 250 mA 200 mA 125 mA 125 mA 100 mA	80 % 84 % 84 % 85 % 83 % 82 %

TRN 3SM

3 Watt



- 0.47 x 0.30 x 0.44" SMD package
- Fully regulated outputs
- 2:1 Input Voltage range
- I/O-isolation 1600 VDC
- Temperature range -40°C to +85°C
- Short circuit protection
- 3 year product warranty
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	+Vout	+Vout
4	no pin	common
5	-Vout	-Vout
6	NC	NC
7	NC	NC


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRN 3-0510SM TRN 3-0511SM TRN 3-0512SM TRN 3-0513SM TRN 3-0515SM TRN 3-0521SM TRN 3-0522SM TRN 3-0523SM	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC 5.0 VDC 12 VDC 15 VDC 24 VDC ± 5.0 VDC ± 12 VDC ± 15 VDC	700 mA 600 mA 250 mA 200 mA 125 mA ±300 mA ±125 mA ±100 mA	75 % 78 % 82 % 80 % 80 % 77 % 80 % 80 %
TRN 3-1210SM TRN 3-1211SM TRN 3-1212SM TRN 3-1213SM TRN 3-1215SM TRN 3-1221SM TRN 3-1222SM TRN 3-1223SM	9 - 18 VDC (12 VDC nominal)	3.3 VDC 5.0 VDC 12 VDC 15 VDC 24 VDC ± 5.0 VDC ± 12 VDC ± 15 VDC	700 mA 600 mA 250 mA 200 mA 125 mA ±300 mA ±125 mA ±100 mA	76 % 79 % 84 % 83 % 82 % 78 % 82 % 81 %
TRN 3-2410SM TRN 3-2411SM TRN 3-2412SM TRN 3-2413SM TRN 3-2415SM TRN 3-2421SM TRN 3-2422SM TRN 3-2423SM	18 - 36 VDC (24 VDC nominal)	3.3 VDC 5.0 VDC 12 VDC 15 VDC 24 VDC ± 5.0 VDC ± 12 VDC ± 15 VDC	700 mA 600 mA 250 mA 200 mA 125 mA ±300 mA ±125 mA ±100 mA	76 % 78 % 84 % 84 % 83 % 79 % 83 % 82 %
TRN 3-4810SM TRN 3-4811SM TRN 3-4812SM TRN 3-4813SM TRN 3-4815SM TRN 3-4821SM TRN 3-4822SM TRN 3-4823SM	36 - 75 VDC (48 VDC nominal)	3.3 VDC 5.0 VDC 12 VDC 15 VDC 24 VDC ± 5.0 VDC ± 12 VDC ± 15 VDC	700 mA 600 mA 250 mA 200 mA 125 mA ±300 mA ±125 mA ±100 mA	75 % 79 % 83 % 83 % 82 % 77 % 82 % 80 %

TIM 3.5SM

NEW!

3.5 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 0.95 x 0.57 x 0.40" SMD-16-package
- I/O isolation 5000 VAC rated for 250 VAC working voltage
- IEC/EN/ES 60601-1 3rd ed. (2xMOPP)
- Low leakage < 2 μA for BF-applications
- Temperature range -40°C to 90°C.
- EMC compliance to IEC 60601-1-2 4th edition and EN 55032 class A
- 3 year product warranty

Pinout / Connection		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	Remote	Remote
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TIM 3.5-0911SM TIM 3.5-0919SM TIM 3.5-0912SM TIM 3.5-0913SM TIM 3.5-0915SM TIM 3.5-0922SM TIM 3.5-0923SM	4.5 - 12 VDC (9 VDC nom.)	5 VDC 9 VDC 12 VDC 15 VDC 24 VDC ± 12 VDC ± 15 VDC	700 mA 389 mA 292 mA 234 mA 146 mA 146 mA 117 mA	77 % 78 % 82 % 82 % 82 % 82 % 81 %
TIM 3.5-1211SM TIM 3.5-1219SM TIM 3.5-1212SM TIM 3.5-1213SM TIM 3.5-1215SM TIM 3.5-1222SM TIM 3.5-1223SM	9 - 18 VDC (12 VDC nom.)	5 VDC 9 VDC 12 VDC 15 VDC 24 VDC ± 12 VDC ± 15 VDC	700 mA 389 mA 292 mA 234 mA 146 mA 146 mA 117 mA	79 % 79 % 82 % 82 % 82 % 82 % 82 %
TIM 3.5-2411SM TIM 3.5-2419SM TIM 3.5-2412SM TIM 3.5-2413SM TIM 3.5-2415SM TIM 3.5-2422SM TIM 3.5-2423SM	18 - 36 VDC (24 VDC nom.)	5 VDC 9 VDC 12 VDC 15 VDC 24 VDC ± 12 VDC ± 15 VDC	700 mA 389 mA 292 mA 234 mA 146 mA 146 mA 117 mA	79 % 80 % 83 % 83 % 82 % 82 % 82 %

**TDN 5WISM** **5 Watt**



- 0.52 x 0.36 x 0.39" SMD package
- I/O-isolation 1600 VDC
- Fully regulated outputs
- Temperature range -40°C to +75°C
- Short circuit protection
- Remote On/Off
- 3 year product warranty
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	On/Off	On/Off
5	NC	-Vout
6	-Vout	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDN 5-0910WISM	4.5 - 13.2 VDC (9 VDC nom.)	3.3 VDC	1000 mA	76 %
TDN 5-0911WISM		5.0 VDC	1000 mA	80 %
TDN 5-0919WISM		9.0 VDC	555 mA	81 %
TDN 5-0912WISM		12 VDC	420 mA	83 %
TDN 5-0913WISM		15 VDC	333 mA	83 %
TDN 5-0915WISM		24 VDC	210 mA	83 %
TDN 5-0921WISM		±5.0 VDC	±500 mA	80 %
TDN 5-0922WISM		±12 VDC	±210 mA	83 %
TDN 5-0923WISM		±15 VDC	±168 mA	83 %
TDN 5-2410WISM		9 - 36 VDC (24 VDC nom.)	3.3 VDC	1000 mA
TDN 5-2411WISM	5.0 VDC		1000 mA	80 %
TDN 5-2419WISM	9.0 VDC		555 mA	81 %
TDN 5-2412WISM	12 VDC		420 mA	83 %
TDN 5-2413WISM	15 VDC		333 mA	83 %
TDN 5-2415WISM	24 VDC		210 mA	83 %
TDN 5-2421WISM	±5.0 VDC		±500 mA	80 %
TDN 5-2422WISM	±12 VDC		±210 mA	83 %
TDN 5-2423WISM	±15 VDC		±168 mA	84 %
TDN 5-4810WISM	18 - 75 VDC (48 VDC nom.)		3.3 VDC	1000 mA
TDN 5-4811WISM		5.0 VDC	1000 mA	81 %
TDN 5-4819WISM		9.0 VDC	555 mA	81 %
TDN 5-4812WISM		12 VDC	420 mA	83 %
TDN 5-4813WISM		15 VDC	333 mA	83 %
TDN 5-4815WISM		24 VDC	210 mA	83 %
TDN 5-4821WISM		±5.0 VDC	±500 mA	80 %
TDN 5-4822WISM		±12 VDC	±210 mA	83 %
TDN 5-4823WISM		±15 VDC	±168 mA	84 %



# DC/DC: Isolated SIP Package

TRACO POWER's SIP package isolated DC/DC Converters provides a complete range of compact products from 1 to 9 watts with non-regulated, semi-regulated and fully regulated outputs.


SERIES	WATTS	DESCRIPTION	APPS	STATUS	PAGE
TBA 1	1	SIP-4 package, ±10% input, unregulated, short circuit protection, encapsulated		NEW	22
TBA 1E	1	SIP-7 package, ±10% input, unregulated, short circuit protection, encapsulated		NEW	22
TBA 1HI	1	SIP-7 package, ±10% input, unregulated, short circuit protection, 3000 VDC I/O iso.		NEW	23
TEA 1	1	SIP-4 package, ±10% input, unregulated, cost optimized design, encapsulated		NEW	2
TEA 1E	1	SIP-7 package, ±10% input, unregulated, cost optimized design, encapsulated		NEW	24
TEA 1HI	1	SIP-7 package, ±10% input, unregulated, 4000 VDC I/O isolation, encapsulated		NEW	24
TMAP	1	SIP-7 package, ±10% input, unregulated, short circuit protection, 3000 VDC I/O iso.		ACTIVE	25
TMR 1	1	SIP-6 package, 2:1 input, regulated, encapsulated		ACTIVE	25
TMV-EN	1	SIP-7 package, ±10% input, unregulated, 3000 VAC I/O isolation(reinforced), encapsulated		ACTIVE	26
TMV-HI	1	SIP-7 package, ±10% input, unregulated, 5200 VDC I/O isolation, encapsulated		ACTIVE	26
TRN 1	1	SIP-5 package, 2:1 input, regulated, cost efficient, compact, encapsulated		ACTIVE	27
TRV 1M	1	SIP-7 package, ±10% input, semi-regulated, 5000 VAC isolation, encapsulated	⊕	NEW	27
TBA 2	2	SIP-7 package, ±10% input, unregulated, short circuit protection, encapsulated		NEW	28
TEC 2	2	SIP-8 package, 2:1 input, regulated, cost efficient, encapsulated		ACTIVE	28
TEC 2WI	2	SIP-8 package, 4:1 input, regulated, cost efficient, encapsulated		ACTIVE	29
TMR 2	2	SIP-8 package, 2:1 input, regulated, encapsulated		ACTIVE	29
TMR 2WIN	2	SIP-8 package, 4:1 input, regulated, encapsulated		ACTIVE	30
TMV 2HI	2	SIP-7 package, 10% input, unregulated, 5200 VDC I/O-isolation, encapsulated		ACTIVE	30
TEC 3	3	SIP-8 package, 2:1 input, regulated, cost efficient, encapsulated		ACTIVE	31
TEC 3WI	3	SIP-8 package, 4:1 input, regulated, cost efficient, encapsulated		ACTIVE	31
TMR 3	3	SIP-8 package, 2:1 input, regulated, encapsulated		ACTIVE	32
TMR 3HI	3	SIP-8 package, 2:1 input, regulated, 3000 VDC I/O-isolation (functional), encapsulated		ACTIVE	32
TMR 3WI	3	SIP-8 package, 4:1 input, regulated, encapsulated		ACTIVE	33
TMR 3WIR	3	SIP-8 package, 2:1 input, regulated, 3000 VDC I/O-isolation, railway, metal case	🚂	NEW	33
TRN 3	3	SIP-5 package, 2:1 input, regulated, cost efficient, compact, encapsulated		ACTIVE	34
TVN 3	3	SIP-8 package, 2:1 input, regulated, ultra low ripple & noise, metal case		ACTIVE	34
TMR 4	4	SIP-8 package, 2:1 input, regulated, encapsulated		NEW	35
TMR 4WI	4	SIP-8 package, 4:1 input, regulated, encapsulated		NEW	35
TMR 6	6	SIP-8 package, 2:1 input, regulated, encapsulated		ACTIVE	36
TMR 6WI	6	SIP-8 package, 4:1 input, regulated, encapsulated		ACTIVE	36
TMR 6WIR	6	SIP-8 package, 2:1 input, regulated, 3000 VDC I/O-isolation, railway, metal case	🚂	NEW	37
TMR 9	9	SIP-8 package, 2:1 input, regulated, ultra compact, encapsulated		ACTIVE	37
TMR 9WI	9	SIP-8 package, 4:1 input, regulated, ultra compact, encapsulated			38

APPS KEY: ⊕ = UL/EN60601-1 (2xMOPP) Approved    🚂 = EN50155 /EN61373 Approved

TBA 1

**NEW!**

1 Watt



- 0.45 x 0.38 x 0.24" SIP-4 package
- Cost-efficient design
- Continuous short circuit protection
- I/O isolation: 1500 VDC
- Temperature range -40 to +85 °C without derating
- ±10% input voltage ranges
- High efficiency up to 82%
- Unregulated outputs
- 3 year product warranty


Pinout	
Pin	Function
1	-Vin (GND)
2	+Vin (Vcc)
3	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TBA 1-0310	2.97 - 3.63 VDC	3.3 VDC	260 mA	73 %
TBA 1-0311	(3.3 VDC nom.)	5 VDC	200 mA	76 %
TBA 1-0510	4.5 - 5.5 VDC (5 VDC nom.)	3.3 VDC	260 mA	75 %
TBA 1-0511		5 VDC	200 mA	79 %
TBA 1-0519		9 VDC	110 mA	80 %
TBA 1-0512		12 VDC	80 mA	82 %
TBA 1-0513		15 VDC	65 mA	82 %
TBA 1-1211	10.8 - 13.2 VDC (12 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-1219		9 VDC	110 mA	79 %
TBA 1-1212		12 VDC	80 mA	80 %
TBA 1-1213		15 VDC	65 mA	80 %
TBA 1-2411	21.6 - 26.4 VDC (24 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-2419		9 VDC	110 mA	80 %
TBA 1-2412		12 VDC	80 mA	82 %
TBA 1-2413		15 VDC	65 mA	82 %

TBA 1E

**NEW!**

1 Watt



- 0.75 x 0.37 x 0.24" SIP-7 package
- Cost-efficient design
- Continuous short circuit protection
- I/O isolation: 1500 VDC
- Operating temperature range -40 to +85 °C without derating
- ±10% input voltage ranges
- High efficiency up to 82%
- Unregulated outputs
- 3 year product warranty


Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	-Vout	-Vout
5	No pin	Common
6	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TBA 1-0511E	4.5 - 5.5 VDC (5 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-0512E		12 VDC	84 mA	82 %
TBA 1-0513E		15 VDC	66 mA	82 %
TBA 1-0521E		±5 VDC	100 mA	79 %
TBA 1-0522E		±12 VDC	41 mA	82 %
TBA 1-0523E	±15 VDC	33 mA	82 %	
TBA 1-1211E	10.8 - 13.2 VDC (12 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-1212E		12 VDC	84 mA	80 %
TBA 1-1213E		15 VDC	66 mA	80 %
TBA 1-1221E		±5 VDC	100 mA	79 %
TBA 1-1222E		±12 VDC	41 mA	80 %
TBA 1-1223E		±15 VDC	33 mA	80 %
TBA 1-2411E	21.6 - 26.4 VDC (24 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-2412E		12 VDC	84 mA	82 %
TBA 1-2413E		15 VDC	66 mA	82 %
TBA 1-2421E		±5 VDC	100 mA	79 %
TBA 1-2422E		±12 VDC	41 mA	82 %
TBA 1-2423E		±15 VDC	33 mA	82 %

TBA 1HI

**NEW!**

1 Watt



- 0.75 x 0.37 x 0.24" SIP-7 package
- Cost-efficient design
- Continuous short circuit protection
- I/O isolation: 3000 VDC
- Operating temperature range -40 to +85 °C without derating
- ±10% input voltage ranges
- High efficiency up to 82%
- Unregulated outputs
- 3 year product warranty


Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
5	-Vout	-Vout
6	No pin	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TBA 1-0511HI	4.5 - 5.5 VDC (5 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-0519HI		9 VDC	111 mA	80 %
TBA 1-0512HI		12 VDC	84 mA	82 %
TBA 1-0513HI		15 VDC	66 mA	82 %
TBA 1-0521HI		±5 VDC	100 mA	79 %
TBA 1-0522HI		±12 VDC	41 mA	82 %
TBA 1-0523HI	±15 VDC	33 mA	82 %	
TBA 1-1211HI	10.8 - 13.2 VDC (12 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-1219HI		9 VDC	111 mA	79 %
TBA 1-1212HI		12 VDC	84 mA	80 %
TBA 1-1213HI		15 VDC	66 mA	80 %
TBA 1-1221HI		±5 VDC	100 mA	79 %
TBA 1-1222HI		±12 VDC	41 mA	80 %
TBA 1-1223HI	±15 VDC	33 mA	80 %	
TBA 1-2411HI	21.6 - 26.4 VDC (24 VDC nom.)	5 VDC	200 mA	79 %
TBA 1-2419HI		9 VDC	111 mA	80 %
TBA 1-2412HI		12 VDC	84 mA	82 %
TBA 1-2413HI		15 VDC	66 mA	82 %
TBA 1-2421HI		±5 VDC	100 mA	79 %
TBA 1-2422HI		±12 VDC	41 mA	82 %
TBA 1-2423HI	±15 VDC	33 mA	82 %	

TEA 1

**NEW!**

1 Watt



- 0.46 x 0.36 x 0.24" SIP-4 package
- Cost-efficient design
- I/O isolation: 1500 VDC
- Operating temperature range -40 to +85 °C without derating
- Extremely cost-efficient design
- High efficiency up to 82%
- Unregulated outputs
- 3 year product warranty

Pinout	
Pin	Single
1	-Vin
2	+Vin
3	-Vout
4	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEA 1-0505	4.5 - 5.5 VDC	5 VDC	200 mA	78 %




## DC/DC: Isolated / SIP Package

TEA 1E

**NEW!**

1 Watt



- 0.75 x 0.37 x 0.24" SIP-7 package
- Cost-efficient design
- I/O isolation: 1500 VDC
- Operating temperature range -40 to +85 °C without derating
- Extremely cost-efficient design
- High efficiency up to 82%
- Unregulated outputs
- 3 year product warranty


Pinout	
Pin	Single
1	+Vin
2	-Vin
4	-Vout
5	No pin
6	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEA 1-0505E	4.5 - 5.5 VDC	5 VDC	200 mA	78 %

TEA 1HI

**NEW!**

1 Watt



- 0.75 x 0.37 x 0.24" SIP-7 package
- Cost-efficient design
- I/O isolation: 3000 VDC
- Operating temperature range -40 to +85 °C without derating
- High efficiency up to 82%
- Extremely cost-efficient design
- Unregulated outputs
- 3 year product warranty


Pinout	
Pin	Single
1	+Vin
2	-Vin
5	-Vout
7	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEA 1-0505HI	4.5 - 5.5 VDC	5 VDC	200 mA	78 %



TMAP

1 Watt




- 0.77 x 0.40 x 0.28" SIP-7 package
- Overload and short circuit protection
- I/O isolation 3000 VDC (functional)
- Extended operating temperature range -40°C to 85°C without derating
- High efficiency up to 84% typ.
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	-Vout	-Vout
5	No Pin	Common
6	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMAP 0505S	4.5 - 5.5 VDC (5 VDC nominal)	5.0 VDC	200 mA	78 %
TMAP 0509S		9.0 VDC	110 mA	81 %
TMAP 0512S		12 VDC	84 mA	82 %
TMAP 0515S		15 VDC	68 mA	83 %
TMAP 0505D		±5.0 VDC	±100 mA	81 %
TMAP 0512D		±12 VDC	±42 mA	81 %
TMAP 0515D	±15 VDC	±34 mA	81 %	
TMAP 1205S	10.8 - 13.2 VDC (12 VDC nominal)	5.0 VDC	200 mA	80 %
TMAP 1209S		9.0 VDC	110 mA	82 %
TMAP 1212S		12 VDC	84 mA	84 %
TMAP 1215S		15 VDC	68 mA	83 %
TMAP 1205D		±5.0 VDC	±100 mA	81 %
TMAP 1212D		±12 VDC	±42 mA	82 %
TMAP 1215D	±15 VDC	±34 mA	82 %	
TMAP 2405S	21.6 - 26.4 VDC (24 VDC nominal)	5.0 VDC	200 mA	81 %
TMAP 2409S		9.0 VDC	110 mA	79 %
TMAP 2412S		12 VDC	84 mA	82 %
TMAP 2415S		15 VDC	68 mA	82 %
TMAP 2405D		±5.0 VDC	±100 mA	80 %
TMAP 2412D		±12 VDC	±42 mA	81 %
TMAP 2415D	±15 VDC	±34 mA	80 %	

TMR 1

1 Watt





- 0.67 x 0.40 x 0.30" SIP-6 package
- Wide 2:1 input voltage range
- Fully regulated outputs
- Cost optimised design
- No minimum load required
- Continuous short circuit protection
- Temperature range -40°C to +95°C
- I/O isolation 1500 VDC
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
4	+Vout	+Vout
5	No pin	Common
6	-Vout	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 1-0511	4.5 - 9 VDC (5 VDC nom.)	5 VDC	200 mA	76 %
TMR 1-0512		12 VDC	83 mA	77 %
TMR 1-0513		15 VDC	67 mA	79 %
TMR 1-0515		24 VDC	42 mA	76 %
TMR 1-0522		+12 VDC	42 mA	77 %
TMR 1-0523		+15 VDC	33 mA	78 %
TMR 1-1211	9 - 18 VDC (12 VDC nom.)	5 VDC	200 mA	77 %
TMR 1-1212		12 VDC	83 mA	77 %
TMR 1-1213		15 VDC	67 mA	80 %
TMR 1-1215		24 VDC	42 mA	77 %
TMR 1-1222		+12 VDC	42 mA	79 %
TMR 1-1223		+15 VDC	33 mA	78 %
TMR 1-2411	18 - 36 VDC (24 VDC nom.)	5 VDC	200 mA	77 %
TMR 1-2412		12 VDC	83 mA	80 %
TMR 1-2413		15 VDC	67 mA	80 %
TMR 1-2415		24 VDC	42 mA	77 %
TMR 1-2422		+12 VDC	42 mA	80 %
TMR 1-2423		+15 VDC	33 mA	80 %
TMR 1-4811	36 - 75 VDC (48 VDC nom.)	5 VDC	200 mA	77 %
TMR 1-4812		12 VDC	83 mA	78 %
TMR 1-4813		15 VDC	67 mA	78 %
TMR 1-4815		24 VDC	42 mA	76 %
TMR 1-4822		+12 VDC	42 mA	79 %
TMR 1-4823		+15 VDC	33 mA	79 %

TMV-EN

1 Watt





- 0.87 x 0.49 x 0.30" SIP package
- I/O isolation voltage 3000 VACrms
- Reinforced insulation, rated for 300 VAC working voltage
- Unregulated device
- IEC/EN/UL 60950-1 approved
- Safety barrier 100 % production test
- Low coupling capacity
- Single-in-line package (SIP)
- Lead-free design, RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
5	-Vout	-Vout
6	No pin	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMV 0505 EN	5 VDC ±10 %	5 VDC	200 mA	66 %
TMV 0512 EN		12 VDC	80 mA	66 %
TMV 0515 EN		15 VDC	65 mA	66 %
TMV 0505D EN		±5 VDC	±100 mA	66 %
TMV 0512D EN		±12 VDC	±40 mA	72 %
TMV 0515D EN		±15 VDC	±35 mA	73 %
TMV 1205 EN	12 VDC ±10 %	5 VDC	200 mA	66 %
TMV 1212 EN		12 VDC	80 mA	66 %
TMV 1215 EN		15 VDC	65 mA	66 %
TMV 1205D EN		±5 VDC	±100 mA	66 %
TMV 1212D EN		±12 VDC	±40 mA	74 %
TMV 1215D EN		±15 VDC	±35 mA	75 %

TMV-HI

1 Watt




- 0.77 x 0.30 x 0.40" SIP-7 package
- Ultra compact SIP-7 package
- Very high I/O-isolation 5200 VDC
- Unregulated device
- Dedicated for IGBT applications
- Operating temperature range -40°C to +95°C
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
5	-Vout	-Vout
6	No pin	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMV 0503SHI	5 VDC ±10 %	3.3 VDC	303 mA	70 %
TMV 0505SHI		5.0 VDC	200 mA	70 %
TMV 0509SHI		9.0 VDC	111 mA	75 %
TMV 0512SHI		12 VDC	84 mA	77 %
TMV 0515SHI		15 VDC	66 mA	78 %
TMV 0505DHI		±5.0 VDC	±100 mA	71 %
TMV 0509DHI		±9.0 VDC	±56 mA	75 %
TMV 0512DHI		±12 VDC	±42 mA	77 %
TMV 0515DHI		±15 VDC	±33 mA	78 %
TMV 05159HI		+15/-9 VDC	+33/-55 mA	76 %
TMV 1203SHI	12 VDC ±10 %	3.3 VDC	303 mA	71 %
TMV 1205SHI		5.0 VDC	200 mA	71 %
TMV 1209SHI		9.0 VDC	111 mA	76 %
TMV 1212SHI		12 VDC	84 mA	78 %
TMV 1215SHI		15 VDC	66 mA	79 %
TMV 1205DHI		±5.0 VDC	±100 mA	72 %
TMV 1209DHI		±9.0 VDC	±56 mA	76 %
TMV 1212DHI		±12 VDC	±42 mA	78 %
TMV 1215DHI		±15 VDC	±33 mA	79 %
TMV 12159HI		+15/-9 VDC	+33/-55 mA	77 %
TMV 1503SHI	15 VDC ±10 %	3.3 VDC	303 mA	70 %
TMV 1505SHI		5.0 VDC	200 mA	70 %
TMV 1509SHI		9.0 VDC	111 mA	75 %
TMV 1512SHI		12 VDC	84 mA	75 %
TMV 1515SHI		15 VDC	66 mA	79 %
TMV 1505DHI		±5.0 VDC	±100 mA	71 %
TMV 1509DHI		±9.0 VDC	±56 mA	75 %
TMV 1512DHI		±12 VDC	±42 mA	78 %
TMV 1515DHI		±15 VDC	±33 mA	79 %
TMV 15159HI		+15/-9 VDC	+33/-55 mA	76 %
TMV 2403SHI	24 VDC ±10 %	3.3 VDC	303 mA	70 %
TMV 2405SHI		5.0 VDC	200 mA	70 %
TMV 2409SHI		9.0 VDC	111 mA	75 %
TMV 2412SHI		12 VDC	84 mA	78 %
TMV 2415SHI		15 VDC	66 mA	80 %
TMV 2405DHI		±5.0 VDC	±100 mA	71 %
TMV 2409DHI		±9.0 VDC	±56 mA	75 %
TMV 2412DHI		±12 VDC	±42 mA	77 %
TMV 2415DHI		±15 VDC	±33 mA	78 %
TMV 24159HI		+15/-9 VDC	+33/-55 mA	75 %

TRN 1

1 Watt



- 0.47 x 0.32 x 0.43" SIP-5 package
- Fully regulated outputs
- Input Voltage range 4.5-13.2, 9-18, 18-36, 36-75 VDC
- I/O-isolation 1600 VDC
- Operating temperature range -40°C to +90°C without derating
- Short circuit protection
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	+Vout	+Vout
4	no pin	common
5	-Vout	-Vout


Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TRN 1-0510	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	300 mA	77 %
TRN 1-0511		5.0 VDC	200 mA	79 %
TRN 1-0512		12 VDC	90 mA	81 %
TRN 1-0513		15 VDC	70 mA	82 %
TRN 1-0515		24 VDC	45 mA	83 %
TRN 1-0521		± 5.0 VDC	±100 mA	79 %
TRN 1-0522		±12 VDC	±45 mA	83 %
TRN 1-0523		±15 VDC	±35 mA	80 %
TRN 1-1210		9 - 18 VDC (12 VDC nominal)	3.3 VDC	300 mA
TRN 1-1211	5.0 VDC		200 mA	80 %
TRN 1-1212	12 VDC		90 mA	81 %
TRN 1-1213	15 VDC		70 mA	83 %
TRN 1-1215	24 VDC		45 mA	83 %
TRN 1-1221	± 5.0 VDC		±100 mA	79 %
TRN 1-1222	±12 VDC		±45 mA	83 %
TRN 1-1223	±15 VDC		±35 mA	80 %
TRN 1-2410	18 - 36 VDC (24 VDC nominal)		3.3 VDC	300 mA
TRN 1-2411		5.0 VDC	200 mA	81 %
TRN 1-2412		12 VDC	90 mA	82 %
TRN 1-2413		15 VDC	70 mA	83 %
TRN 1-2415		24 VDC	45 mA	82 %
TRN 1-2421		± 5.0 VDC	±100 mA	79 %
TRN 1-2422		±12 VDC	±45 mA	82 %
TRN 1-2423		±15 VDC	±35 mA	80 %
TRN 1-4810		36 - 75 VDC (48 VDC nominal)	3.3 VDC	300 mA
TRN 1-4811	5.0 VDC		200 mA	78 %
TRN 1-4812	12 VDC		90 mA	80 %
TRN 1-4813	15 VDC		70 mA	81 %
TRN 1-4815	24 VDC		45 mA	81 %
TRN 1-4821	± 5.0 VDC		±100 mA	78 %
TRN 1-4822	±12 VDC		±45 mA	81 %
TRN 1-4823	±15 VDC		±35 mA	79 %

TRV 1M

NEW!

1 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 0.77 x 0.49 x 0.39 SIP-7 package
- Semi regulated
- 2x MOPP / BF Compliant
- 5000 VAC I/O-isolation (reinforced)
- Operating temperature: -40°C to 95°C w/o derating
- ±10% Input 5 to 24 VDC
- 3.3 to 15 VDC output voltage
- 3 year product warranty

Pinout / Connection		
Pin	Single Output	Dual Output
1	+Vin	+Vin
2	-Vin	-Vin
7	-Vout	-Vout
8	No pin	Common
9	+Vout	+Vout


Model	Input	Vout	I <sub>out</sub>	Efficiency	
TRV 1-0510M	5 ± 10 VDC	3.3 VDC	303 mA	80 %	
TRV 1-0511M		5 VDC	200 mA	82 %	
TRV 1-0512M		12 VDC	83 mA	85 %	
TRV 1-0513M		15 VDC	67 mA	84 %	
TRV 1-0521M		±5 VDC	±100 mA	85 %	
TRV 1-0522M		±12 VDC	±42 mA	85 %	
TRV 1-0523M		±15 VDC	±34 mA	84 %	
TRV 1-1210M		12 ± 20 VDC	3.3 VDC	303 mA	80 %
TRV 1-1211M			5 VDC	200 mA	82 %
TRV 1-1212M	12 VDC		83 mA	84 %	
TRV 1-1213M	15 VDC		67 mA	83 %	
TRV 1-1221M	±5 VDC		±100 mA	82 %	
TRV 1-1222M	±12 VDC		±42 mA	83 %	
TRV 1-1223M	±15 VDC		±34 mA	83 %	
TRV 1-1510M	15 ± 20 VDC		3.3 VDC	303 mA	79 %
TRV 1-1511M			5 VDC	200 mA	83 %
TRV 1-1512M		12 VDC	83 mA	84 %	
TRV 1-1513M		15 VDC	67 mA	84 %	
TRV 1-1521M		±5 VDC	±100 mA	82 %	
TRV 1-1522M		±12 VDC	±42 mA	83 %	
TRV 1-1523M		±15 VDC	±34 mA	83 %	

## DC/DC: Isolated / SIP Package

TBA 2

**NEW!**

2 Watt




- 0.77 x 0.40 x 0.30" SIP-7 package
- Continuous short circuit protection
- I/O isolation: 1500 VDC
- Operating temperature range -40 to +80 °C without derating
- ±10% input voltage ranges
- High efficiency up to 84%
- Unregulated outputs
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	-Vout	-Vout
5	No pin	Common
6	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TBA 2-0511	4.5 - 5.5 VDC (5 VDC nom.)	5 VDC	400 mA	78 %
TBA 2-0512		12 VDC	165 mA	82 %
TBA 2-0513		15 VDC	130 mA	82 %
TBA 2-0521		±5 VDC	200 mA	79 %
TBA 2-0522		±12 VDC	80 mA	82 %
TBA 2-0523	±15 VDC	65 mA	82 %	
TBA 2-1211	10.8 - 13.2 VDC (12 VDC nom.)	5 VDC	400 mA	79 %
TBA 2-1212		12 VDC	165 mA	82 %
TBA 2-1213		15 VDC	130 mA	84 %
TBA 2-1221		±5 VDC	200 mA	79 %
TBA 2-1222		±12 VDC	80 mA	83 %
TBA 2-1223	±15 VDC	65 mA	84 %	
TBA 2-2411	21.6 - 26.4 VDC (24 VDC nom.)	5 VDC	400 mA	78 %
TBA 2-2412		12 VDC	165 mA	84 %
TBA 2-2413		15 VDC	130 mA	84 %
TBA 2-2421		±5 VDC	200 mA	80 %
TBA 2-2422		±12 VDC	80 mA	84 %
TBA 2-2423	±15 VDC	65 mA	84 %	

TEC 2

2 Watt



- 0.86 x 0.36 x 0.44" SIP-8 package
- I/O-isolation voltage 1600 VDC
- Fully regulated outputs
- Operating temperature range -40°C to +95°C
- Short circuit protection
- Remote On/Off
- Designed to meet UL 62368-1
- 3 year product warranty


Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (VCC)	+Vin (VCC)
3	On/Off	On/Off
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEC 2-0910	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	500 mA	78 %
TEC 2-0911		5.0 VDC	400 mA	81 %
TEC 2-0919		9.0 VDC	222 mA	84 %
TEC 2-0912		12 VDC	167 mA	84 %
TEC 2-0913		15 VDC	134 mA	84 %
TEC 2-0915		24 VDC	83 mA	85 %
TEC 2-0921		±5.0 VDC	±200 mA	81 %
TEC 2-0922		±12 VDC	±83 mA	85 %
TEC 2-0923		±15 VDC	±67 mA	84 %
TEC 2-1210		9 - 18 VDC (12 VDC nominal)	3.3 VDC	500 mA
TEC 2-1211	5.0 VDC		400 mA	82 %
TEC 2-1219	9.0 VDC		222 mA	84 %
TEC 2-1212	12 VDC		167 mA	85 %
TEC 2-1213	15 VDC		134 mA	85 %
TEC 2-1215	24 VDC		83 mA	85 %
TEC 2-1221	±5.0 VDC		±200 mA	82 %
TEC 2-1222	±12 VDC		±83 mA	85 %
TEC 2-1223	±15 VDC		±67 mA	84 %
TEC 2-2410	18 - 36 VDC (12 VDC nominal)		3.3 VDC	500 mA
TEC 2-2411		5.0 VDC	400 mA	83 %
TEC 2-2419		9.0 VDC	222 mA	85 %
TEC 2-2412		12 VDC	167 mA	86 %
TEC 2-2413		15 VDC	134 mA	85 %
TEC 2-2415		24 VDC	83 mA	85 %
TEC 2-2421		±5.0 VDC	±200 mA	83 %
TEC 2-2422		±12 VDC	±83 mA	85 %
TEC 2-2423		±15 VDC	±67 mA	86 %
TEC 2-4810		36 - 75 VDC (48 VDC nominal)	3.3 VDC	500 mA
TEC 2-4811	5.0 VDC		400 mA	80 %
TEC 2-4819	9.0 VDC		222 mA	82 %
TEC 2-4812	12 VDC		167 mA	84 %
TEC 2-4813	15 VDC		134 mA	85 %
TEC 2-4815	24 VDC		83 mA	85 %
TEC 2-4821	±5.0 VDC		±200 mA	80 %
TEC 2-4822	±12 VDC		±83 mA	85 %
TEC 2-4823	±15 VDC		±67 mA	83 %



TEC 2WI

2 Watt




- 0.86 x 0.36 x 0.44" SIP-8 package
- I/O-isolation voltage 1600 VDC
- Ultra-wide 4:1 input voltage range
- Fully regulated outputs
- Operating temperature range -40°C to +93°C
- Continuous short circuit protection
- Remote On/Off
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (VCC)	+Vin (VCC)
3	On/Off	On/Off
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEC 2-1210WI	4.5 - 18 VDC (12 VDC nominal)	3.3 VDC	500 mA	75 %
TEC 2-1211WI		5.0 VDC	400 mA	80 %
TEC 2-1219WI		9.0 VDC	222 mA	81 %
TEC 2-1212WI		12 VDC	167 mA	81 %
TEC 2-1213WI		15 VDC	134 mA	82 %
TEC 2-1215WI		24 VDC	83 mA	82 %
TEC 2-1221WI		±5.0 VDC	±200 mA	80 %
TEC 2-1222WI		±12 VDC	±83 mA	82 %
TEC 2-1223WI		±15 VDC	±67 mA	81 %
TEC 2-2410WI		9 - 36 VDC (24 VDC nominal)	3.3 VDC	500 mA
TEC 2-2411WI	5.0 VDC		400 mA	80 %
TEC 2-2419WI	9.0 VDC		222 mA	80 %
TEC 2-2412WI	12 VDC		167 mA	82 %
TEC 2-2413WI	15 VDC		134 mA	82 %
TEC 2-2415WI	24 VDC		83 mA	82 %
TEC 2-2421WI	±5.0 VDC		±200 mA	79 %
TEC 2-2422WI	±12 VDC		±83 mA	82 %
TEC 2-2423WI	±15 VDC		±67 mA	80 %
TEC 2-4810WI	18 - 75 VDC (48 VDC nominal)		3.3 VDC	500 mA
TEC 2-4811WI		5.0 VDC	400 mA	79 %
TEC 2-4819WI		9.0 VDC	222 mA	81 %
TEC 2-4812WI		12 VDC	167 mA	82 %
TEC 2-4813WI		15 VDC	134 mA	81 %
TEC 2-4815WI		24 VDC	83 mA	81 %
TEC 2-4821WI		±5.0 VDC	±200 mA	79 %
TEC 2-4822WI		±12 VDC	±83 mA	81 %
TEC 2-4823WI		±15 VDC	±67 mA	81 %

TMR 2

2 Watt




- 0.86 x 0.36 x 0.44" SIP-8 package
- Wide 2:1 input voltage range
- Small footprint
- Remote On/Off control
- Temperature range -40° to +85°C
- High efficiency
- Excellent load and line regulation
- Indefinite short-circuit protection
- I/O isolation 1500 VDC
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 0510	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	500 mA	76 %
TMR 0511		5 VDC	400 mA	80 %
TMR 0512		12 VDC	167 mA	81 %
TMR 0521		+5 VDC	200 mA	79 %
TMR 0522		+12 VDC	83 mA	82 %
TMR 0523		+15 VDC	67 mA	81 %
TMR 1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	500 mA	77 %
TMR 1211		5 VDC	400 mA	81 %
TMR 1212		12 VDC	167 mA	83 %
TMR 1221		+5 VDC	200 mA	81 %
TMR 1222		+12 VDC	83 mA	83 %
TMR 1223		+15 VDC	67 mA	84 %
TMR 2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	500 mA	78 %
TMR 2411		5 VDC	400 mA	81 %
TMR 2412		12 VDC	167 mA	83 %
TMR 2421		+5 VDC	200 mA	80 %
TMR 2422		+12 VDC	83 mA	83 %
TMR 2423		+15 VDC	67 mA	82 %
TMR 4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	500 mA	76 %
TMR 4811		5 VDC	400 mA	78 %
TMR 4812		12 VDC	167 mA	83 %
TMR 4821		+5 VDC	200 mA	80 %
TMR 4822		+12 VDC	83 mA	81 %
TMR 4823		+15 VDC	67 mA	81 %

**TMR 2WIN** **2 Watt**




- 1.02 x 0.36 x 0.49" SIP-8 package
- Ultra-wide 4:1 input range
- Temperature range -40 to +90°C (up to +75°C at full load)
- High efficiency of 82%
- Excellent load and line regulation
- Continuous short-circuit protection
- Overload protection
- I/O isolation 1500 VDC
- Remote On/Off control
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TMR 2-1210WIN	4.5 - 18 VDC (12 VDC nom.)	3.3 VDC	500 mA	75 %
TMR 2-1211WIN		5 VDC	400 mA	80 %
TMR 2-1212WIN		12 VDC	167 mA	82 %
TMR 2-1213WIN		15 VDC	134 mA	82 %
TMR 2-1221WIN		+5 VDC	200 mA	80 %
TMR 2-1222WIN		+12 VDC	83 mA	82 %
TMR 2-1223WIN	+15 VDC	67 mA	82 %	
TMR 2-2410WIN	9 - 36 VDC (24 VDC nom.)	3.3 VDC	500 mA	75 %
TMR 2-2411WIN		5 VDC	400 mA	80 %
TMR 2-2412WIN		12 VDC	167 mA	82 %
TMR 2-2413WIN		15 VDC	134 mA	82 %
TMR 2-2421WIN		+5 VDC	200 mA	80 %
TMR 2-2422WIN		+12 VDC	83 mA	82 %
TMR 2-2423WIN	+15 VDC	67 mA	82 %	
TMR 2-4810WIN	18 - 75 VDC (48 VDC nom.)	3.3 VDC	500 mA	74 %
TMR 2-4811WIN		5 VDC	400 mA	80 %
TMR 2-4812WIN		12 VDC	167 mA	82 %
TMR 2-4813WIN		15 VDC	134 mA	82 %
TMR 2-4821WIN		+5 VDC	200 mA	80 %
TMR 2-4822WIN		+12 VDC	83 mA	82 %
TMR 2-4823WIN	+15 VDC	67 mA	82 %	

**TMV 2HI** **2 Watt**




- 0.77 x 0.30 x 0.40" SIP-7 package
- I/O-isolation 5200 VDC (5700 Vpk)
- Unregulated device
- Dedicated for IGBT applications
- Operating temperature range -40°C to +85°C
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
5	-Vout	-Vout
6	No pin	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency	
TMV 2-0503SHI	5 VDC ± 10 %	3.3 VDC	500 mA	74 %	
TMV 2-0505SHI		5.0 VDC	400 mA	80 %	
TMV 2-0509SHI		9.0 VDC	222 mA	81 %	
TMV 2-0512SHI		12 VDC	168 mA	82 %	
TMV 2-0515SHI		15 VDC	132 mA	79 %	
TMV 2-0505DHI		+5.0 VDC	±200 mA	78 %	
TMV 2-0509DHI		±9.0 VDC	±112 mA	80 %	
TMV 2-0512DHI		±12 VDC	±84 mA	80 %	
TMV 2-0515DHI		±15 VDC	±66 mA	79 %	
TMV 2-05159HI		+15/-9 VDC	+66/-110 mA	80 %	
TMV 2-1203SHI		12 VDC ± 10 %	3.3 VDC	500 mA	76 %
TMV 2-1205SHI			5.0 VDC	400 mA	79 %
TMV 2-1209SHI	9.0 VDC		222 mA	81 %	
TMV 2-1212SHI	12 VDC		168 mA	83 %	
TMV 2-1215SHI	15 VDC		132 mA	82 %	
TMV 2-1205DHI	±5.0 VDC		±200 mA	79 %	
TMV 2-1209DHI	±9.0 VDC		±112 mA	81 %	
TMV 2-1212DHI	±12 VDC		±84 mA	82 %	
TMV 2-1215DHI	±15 VDC		±66 mA	83 %	
TMV 2-12159HI	+15/-9 VDC		+66/-110 mA	81 %	
TMV 2-1503SHI	15 VDC ± 10 %		3.3 VDC	500 mA	77 %
TMV 2-1505SHI			5.0 VDC	400 mA	79 %
TMV 2-1509SHI		9.0 VDC	222 mA	83 %	
TMV 2-1512SHI		12 VDC	168 mA	83 %	
TMV 2-1515SHI		15 VDC	132 mA	85 %	
TMV 2-1505DHI		±5.0 VDC	±200 mA	81 %	
TMV 2-1509DHI		±9.0 VDC	±112 mA	84 %	
TMV 2-1512DHI		±12 VDC	±84 mA	82 %	
TMV 2-1515DHI		±15 VDC	±66 mA	82 %	
TMV 2-15159HI		+15/-9 VDC	+66/-110 mA	83 %	
TMV 2-2403SHI		24 VDC ± 10 %	3.3 VDC	500 mA	76 %
TMV 2-2405SHI			5.0 VDC	400 mA	77 %
TMV 2-2409SHI	9.0 VDC		222 mA	81 %	
TMV 2-2412SHI	12 VDC		168 mA	82 %	
TMV 2-2415SHI	15 VDC		132 mA	82 %	
TMV 2-2405DHI	±5.0 VDC		±200 mA	77 %	
TMV 2-2409DHI	±9.0 VDC		±112 mA	81 %	
TMV 2-2412DHI	±12 VDC		±84 mA	81 %	
TMV 2-2415DHI	±15 VDC		±66 mA	80 %	
TMV 2-24159HI	+15/-9 VDC		+66/-110 mA	81 %	

TEC 3

3 Watt




- 0.86 x 0.36 x 0.44" SIP-8 package
- I/O-isolation 1600 VDC
- Fully regulated outputs
- Operating temperature range -40°C to +90°C
- Short circuit protection
- Remote On/Off
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (VCC)	+Vin (VCC)
3	On/Off	On/Off
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEC 3-0910	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	700 mA	75 %
TEC 3-0911		5.0 VDC	600 mA	78 %
TEC 3-0919		9.0 VDC	333 mA	81 %
TEC 3-0912		12 VDC	250 mA	83 %
TEC 3-0913		15 VDC	200 mA	84 %
TEC 3-0915		24 VDC	125 mA	82 %
TEC 3-0921		±5.0 VDC	±300 mA	79 %
TEC 3-0922		±12 VDC	±125 mA	82 %
TEC 3-0923		±15 VDC	±100 mA	82 %
TEC 3-1210		9 - 18 VDC (12 VDC nominal)	3.3 VDC	700 mA
TEC 3-1211	5.0 VDC		600 mA	81 %
TEC 3-1219	9.0 VDC		333 mA	82 %
TEC 3-1212	12 VDC		250 mA	84 %
TEC 3-1213	15 VDC		200 mA	85 %
TEC 3-1215	24 VDC		125 mA	85 %
TEC 3-1221	±5.0 VDC		±300 mA	81 %
TEC 3-1222	±12 VDC		±125 mA	85 %
TEC 3-1223	±15 VDC		±100 mA	83 %
TEC 3-2410	18 - 36 VDC (24 VDC nominal)		3.3 VDC	700 mA
TEC 3-2411		5.0 VDC	600 mA	82 %
TEC 3-2419		9.0 VDC	333 mA	83 %
TEC 3-2412		12 VDC	250 mA	85 %
TEC 3-2413		15 VDC	200 mA	86 %
TEC 3-2415		24 VDC	125 mA	84 %
TEC 3-2421		±5.0 VDC	±300 mA	82 %
TEC 3-2422		±12 VDC	±125 mA	84 %
TEC 3-2423		±15 VDC	±100 mA	85 %

TEC 3WI

3 Watt




- 0.86 x 0.36 x 0.44" SIP-8 package
- I/O-isolation 1600 VDC
- Ultra-wide 4:1 input voltage range
- Fully regulated outputs
- Operating temperature range -40°C to +90°C
- Short circuit protection
- Remote On/Off
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (VCC)	+Vin (VCC)
3	On/Off	On/Off
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEC 3-1210WI	4.5 - 18 VDC (12 VDC nominal)	3.3 VDC	700 mA	75 %
TEC 3-1211WI		5.0 VDC	600 mA	79 %
TEC 3-1219WI		9.0 VDC	333 mA	81 %
TEC 3-1212WI		12 VDC	250 mA	82 %
TEC 3-1213WI		15 VDC	200 mA	83 %
TEC 3-1215WI		24 VDC	125 mA	82 %
TEC 3-1221WI		±5.0 VDC	±300 mA	80 %
TEC 3-1222WI		±12 VDC	±125 mA	82 %
TEC 3-1223WI		±15 VDC	±100 mA	81 %
TEC 3-2410WI		9 - 36 VDC (24 VDC nominal)	3.3 VDC	700 mA
TEC 3-2411WI	5.0 VDC		600 mA	80 %
TEC 3-2419WI	9.0 VDC		333 mA	81 %
TEC 3-2412WI	12 VDC		250 mA	83 %
TEC 3-2413WI	15 VDC		200 mA	83 %
TEC 3-2415WI	24 VDC		125 mA	81 %
TEC 3-2421WI	±5.0 VDC		±300 mA	79 %
TEC 3-2422WI	±12 VDC		±125 mA	81 %
TEC 3-2423WI	±15 VDC		±100 mA	81 %
TEC 3-4810WI	18 - 75 VDC (48 VDC nominal)		3.3 VDC	700 mA
TEC 3-4811WI		5.0 VDC	600 mA	80 %
TEC 3-4819WI		9.0 VDC	333 mA	81 %
TEC 3-4812WI		12 VDC	250 mA	82 %
TEC 3-4813WI		15 VDC	200 mA	83 %
TEC 3-4815WI		24 VDC	125 mA	82 %
TEC 3-4821WI		±5.0 VDC	±300 mA	80 %
TEC 3-4822WI		±12 VDC	±125 mA	82 %
TEC 3-4823WI		±15 VDC	±100 mA	82 %

TMR 3

3 Watt




- 0.86 x 0.44 x 0.36" - SIP-8 package
- Wide 2:1 input voltage range
- Fully regulated output voltage
- 1600 VDC I/O isolation
- Small footprint
- Temperature range -40° to +85°C
- High efficiency up to 85%
- Short-circuit protection
- Remote On/Off control
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 3-0510	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	700 mA	75 %
TMR 3-0511		5 VDC	600 mA	79 %
TMR 3-0512		12 VDC	250 mA	81 %
TMR 3-0513		15 VDC	200 mA	82 %
TMR 3-0521		+5 VDC	300 mA	78 %
TMR 3-0522	+12 VDC	125 mA	81 %	
TMR 3-0523	+15 VDC	100 mA	81 %	
TMR 3-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	700 mA	77 %
TMR 3-1211		5 VDC	600 mA	81 %
TMR 3-1212		12 VDC	250 mA	83 %
TMR 3-1213		15 VDC	200 mA	83 %
TMR 3-1221		+5 VDC	300 mA	82 %
TMR 3-1222	+12 VDC	125 mA	83 %	
TMR 3-1223	+15 VDC	100 mA	83 %	
TMR 3-2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	700 mA	76 %
TMR 3-2411		5 VDC	600 mA	82 %
TMR 3-2412		12 VDC	250 mA	83 %
TMR 3-2413		15 VDC	200 mA	84 %
TMR 3-2421		+5 VDC	300 mA	80 %
TMR 3-2422	+12 VDC	125 mA	83 %	
TMR 3-2423	+15 VDC	100 mA	85 %	
TMR 3-4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	700 mA	74 %
TMR 3-4811		5 VDC	600 mA	79 %
TMR 3-4812		12 VDC	250 mA	81 %
TMR 3-4813		15 VDC	200 mA	82 %
TMR 3-4821		+5 VDC	300 mA	79 %
TMR 3-4822	+12 VDC	125 mA	82 %	
TMR 3-4823	+15 VDC	100 mA	83 %	

TMR 3HI

3 Watt



- 0.86 x 0.44 x 0.36" SIP-8 package
- Wide 2:1 input voltage range
- Fully regulated output voltage
- 3000 VDC I/O isolation
- Small footprint
- Temperature range -40° to +85°C
- High efficiency up to 85%
- Short-circuit protection
- Remote On/Off control
- 3 year product warranty


Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 3-0510HI	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	700 mA	75 %
TMR 3-0511HI		5 VDC	600 mA	79 %
TMR 3-0512HI		12 VDC	250 mA	81 %
TMR 3-0513HI		15 VDC	200 mA	82 %
TMR 3-0521HI		+5 VDC	300 mA	78 %
TMR 3-0522HI	+12 VDC	125 mA	81 %	
TMR 3-0523HI	+15 VDC	100 mA	81 %	
TMR 3-1210HI	9 - 18 VDC (12 VDC nom.)	3.3 VDC	700 mA	77 %
TMR 3-1211HI		5 VDC	600 mA	81 %
TMR 3-1212HI		12 VDC	250 mA	83 %
TMR 3-1213HI		15 VDC	200 mA	83 %
TMR 3-1221HI		+5 VDC	300 mA	82 %
TMR 3-1222HI	+12 VDC	125 mA	83 %	
TMR 3-1223HI	+15 VDC	100 mA	83 %	
TMR 3-2410HI	18 - 36 VDC (24 VDC nom.)	3.3 VDC	700 mA	76 %
TMR 3-2411HI		5 VDC	600 mA	82 %
TMR 3-2412HI		12 VDC	250 mA	83 %
TMR 3-2413HI		15 VDC	200 mA	84 %
TMR 3-2421HI		+5 VDC	300 mA	80 %
TMR 3-2422HI	+12 VDC	125 mA	83 %	
TMR 3-2423HI	+15 VDC	100 mA	85 %	
TMR 3-4810HI	36 - 75 VDC (48 VDC nom.)	3.3 VDC	700 mA	74 %
TMR 3-4811HI		5 VDC	600 mA	79 %
TMR 3-4812HI		12 VDC	250 mA	81 %
TMR 3-4813HI		15 VDC	200 mA	82 %
TMR 3-4821HI		+5 VDC	300 mA	79 %
TMR 3-4822HI	+12 VDC	125 mA	82 %	
TMR 3-4823HI	+15 VDC	100 mA	83 %	



TMR 3WI

3 Watt



- 0.86 x 0.44 x 0.36" SIP-8 package
- Ultra-wide 4:1 input range
- Small footprint: 21.8 x 9.2 mm
- Temperature range -40° to +85°C
- High efficiency up to 82%
- Excellent load and line regulation
- Short-circuit protection
- I/O isolation 1600 VDC
- Remote On/Off control
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 3-1210WI	4.5 - 18 VDC (12 VDC nom.)	3.3 VDC	700 mA	74 %
TMR 3-1211WI		5 VDC	600 mA	78 %
TMR 3-1212WI		12 VDC	250 mA	80 %
TMR 3-1213WI		15 VDC	200 mA	80 %
TMR 3-1221WI		+5 VDC	300 mA	80 %
TMR 3-1222WI		+12 VDC	125 mA	80 %
TMR 3-1223WI	+15 VDC	100 mA	80 %	
TMR 3-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	700 mA	75 %
TMR 3-2411WI		5 VDC	600 mA	80 %
TMR 3-2412WI		12 VDC	250 mA	82 %
TMR 3-2413WI		15 VDC	200 mA	82 %
TMR 3-2421WI		+5 VDC	300 mA	79 %
TMR 3-2422WI		+12 VDC	125 mA	81 %
TMR 3-2423WI	+15 VDC	100 mA	81 %	
TMR 3-4810WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	700 mA	74 %
TMR 3-4811WI		5 VDC	600 mA	80 %
TMR 3-4812WI		12 VDC	250 mA	81 %
TMR 3-4813WI		15 VDC	200 mA	81 %
TMR 3-4821WI		+5 VDC	300 mA	79 %
TMR 3-4822WI		+12 VDC	125 mA	81 %
TMR 3-4823WI	+15 VDC	100 mA	81 %	

TMR 3WIR

NEW!

3 Watt

EN50155 / EN61373 Approved




- x 0.44 x 0.38" SIP-8 metal case
- Ultra-wide 4:1 Input
- I/O-isolation 3'000 VDC
- Fully regulated outputs
- Operating temperature range -40°C to +90°C
- Short circuit protection and current limitation
- Remote On/Off
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout
9, 10	Case	Case

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 3-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	700 mA	76 %
TMR 3-2411WIR		5 VDC	600 mA	81 %
TMR 3-2419WIR		9VDC	333 mA	81 %
TMR 3-2412WIR		12 VDC	250 mA	83 %
TMR 3-2413WIR		15 VDC	200 mA	83 %
TMR 3-2415WIR		24 VDC	125 mA	82 %
TMR 3-2421WIR	18 - 75 VDC (48 VDC nom.)	± 5 VDC	300 mA	80 %
TMR 3-2422WIR		±12 VDC	125 mA	82 %
TMR 3-2423WIR		±15 VDC	100 mA	82 %
TMR 3-4810WIR		3.3 VDC	700 mA	75 %
TMR 3-4811WIR		5 VDC	600 mA	81 %
TMR 3-4819WIR		9VDC	333 mA	81 %
TMR 3-4812WIR	12 VDC	250 mA	82 %	
TMR 3-4813WIR	15 VDC	200 mA	82 %	
TMR 3-4815WIR	24 VDC	125 mA	82 %	
TMR 3-4821WIR	18 - 75 VDC (48 VDC nom.)	± 5 VDC	300 mA	80 %
TMR 3-4822WIR		±12 VDC	125 mA	82 %
TMR 3-4823WIR		±15 VDC	100 mA	82 %

**TRN 3** **3 Watt**




- 0.47 x 0.32 x 0.43" SIP-5 package
- Fully regulated outputs
- Input Voltage range 4.5-13.2, 9-18, 18-36, 36-75 VDC
- I/O-isolation 1600 VDC
- Operating temperature range -40°C to +85°C
- Short circuit protection
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	+Vout	+Vout
4	no pin	common
5	-Vout	-Vout

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TRN 3-0510	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	700 mA	75 %	
TRN 3-0511		5.0 VDC	600 mA	78 %	
TRN 3-0512		12 VDC	250 mA	82 %	
TRN 3-0513		15 VDC	200 mA	80 %	
TRN 3-0515		24 VDC	125 mA	80 %	
TRN 3-0521		± 5.0 VDC	±300 mA	77 %	
TRN 3-0522		±12 VDC	±125 mA	80 %	
TRN 3-0523		±15 VDC	±100 mA	80 %	
TRN 3-1210		9 - 18 VDC (12 VDC nominal)	3.3 VDC	700 mA	76 %
TRN 3-1211			5.0 VDC	600 mA	79 %
TRN 3-1212	12 VDC		250 mA	84 %	
TRN 3-1213	15 VDC		200 mA	83 %	
TRN 3-1215	24 VDC		125 mA	82 %	
TRN 3-1221	± 5.0 VDC		±300 mA	78 %	
TRN 3-1222	±12 VDC		±125 mA	82 %	
TRN 3-1223	±15 VDC		±100 mA	81 %	
TRN 3-2410	18 - 36 VDC (24 VDC nominal)		3.3 VDC	700 mA	76 %
TRN 3-2411			5.0 VDC	600 mA	78 %
TRN 3-2412		12 VDC	250 mA	84 %	
TRN 3-2413		15 VDC	200 mA	84 %	
TRN 3-2415		24 VDC	125 mA	83 %	
TRN 3-2421		± 5.0 VDC	±300 mA	79 %	
TRN 3-2422		±12 VDC	±125 mA	83 %	
TRN 3-2423		±15 VDC	±100 mA	82 %	
TRN 3-4810		36 - 75 VDC (48 VDC nominal)	3.3 VDC	700 mA	75 %
TRN 3-4811			5.0 VDC	600 mA	79 %
TRN 3-4812	12 VDC		250 mA	83 %	
TRN 3-4813	15 VDC		200 mA	83 %	
TRN 3-4815	24 VDC		125 mA	82 %	
TRN 3-4821	± 5.0 VDC		±300 mA	77 %	
TRN 3-4822	±12 VDC		±125 mA	82 %	
TRN 3-4823	±15 VDC		±100 mA	80 %	

**TVN 3** **3 Watt**



- 0.86 x 0.44 x 0.38" SIP-8 package
- Compact SIP-8 package
- Ultra-low ripple and noise
- Fully regulated outputs
- I/O-isolation 1600 VDC
- Operating temperature range -40°C to +90°C
- Short circuit protection
- No minimum load required
- 3 year product warranty


Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	On/Off	On/Off
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout
9/10	Case	Case

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TVN 3-0910	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	700 mA	75 %
TVN 3-0911		5.0 VDC	600 mA	79 %
TVN 3-0919		9.0 VDC	333 mA	80 %
TVN 3-0912		12 VDC	250 mA	83 %
TVN 3-0913		15 VDC	200 mA	83 %
TVN 3-0915		24 VDC	125 mA	82 %
TVN 3-0921		± 5.0 VDC	±300 mA	78 %
TVN 3-0922		±12 VDC	±125 mA	82 %
TVN 3-0923		±15 VDC	±100 mA	81 %
TVN 3-1210		9 - 18 VDC (12 VDC nominal)	3.3 VDC	700 mA
TVN 3-1211	5.0 VDC		600 mA	81 %
TVN 3-1219	9.0 VDC		333 mA	80 %
TVN 3-1212	12 VDC		250 mA	85 %
TVN 3-1213	15 VDC		200 mA	84 %
TVN 3-1215	24 VDC		125 mA	84 %
TVN 3-1221	± 5.0 VDC		±300 mA	82 %
TVN 3-1222	±12 VDC		±125 mA	84 %
TVN 3-1223	±15 VDC		±100 mA	83 %
TVN 3-2410	18 - 36 VDC (24 VDC nominal)		3.3 VDC	700 mA
TVN 3-2411		5.0 VDC	600 mA	82 %
TVN 3-2419		9.0 VDC	333 mA	82 %
TVN 3-2412		12 VDC	250 mA	85 %
TVN 3-2413		15 VDC	200 mA	85 %
TVN 3-2415		24 VDC	125 mA	84 %
TVN 3-2421		± 5.0 VDC	±300 mA	80 %
TVN 3-2422		±12 VDC	±125 mA	84 %
TVN 3-2423		±15 VDC	±100 mA	85 %

TMR 4

**NEW!**

4 Watt



- 0.86 x 0.44 x 0.37" SIP-8 package
- Wide 2:1 input voltage range
- Fully regulated output voltage
- 1600 VDC I/O isolation
- Small footprint
- Temperature range -40° to +85°C
- High efficiency up to 85%
- Short-circuit protection
- Remote On/Off control
- 3 year product warranty


Pinout		
Pin	Single	Dual
1	-Vin	-Vin
2	+Vin	+Vin
3	Remote On/Off	Remote On/Off
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 4-1211	9 -18 VDC (12 VDC nom.)	5 VDC	800 mA	78 %
TMR 4-1212		12 VDC	333 mA	82 %
TMR 4-1213		15 VDC	266 mA	82 %
TMR 4-1215		24 VDC	166 mA	82 %
TMR 4-1222		±12 VDC	±166 mA	82 %
TMR 4-1223		±15 VDC	±133 mA	82 %
TMR 4-2411	18 -36 VDC (24 VDC nom.)	5 VDC	800 mA	79 %
TMR 4-2412		12 VDC	333 mA	83 %
TMR 4-2413		15 VDC	266 mA	83 %
TMR 4-2415		24 VDC	166 mA	83 %
TMR 4-2422		±12 VDC	±166 mA	83 %
TMR 4-2423		±15 VDC	±133 mA	83 %
TMR 4-4811	18 -75 VDC (48 VDC nom.)	5 VDC	800 mA	78 %
TMR 4-4812		12 VDC	333 mA	82 %
TMR 4-4813		15 VDC	266 mA	82 %
TMR 4-4815		24 VDC	166 mA	82 %
TMR 4-4822		±12 VDC	±166 mA	82 %
TMR 4-4823		±15 VDC	±133 mA	82 %

TMR 4WI

**NEW!**

4 Watt




- 0.86 x 0.44 x 0.37" SIP-8 package
- Ultra-wide 4:1 input range
- Small footprint: 21.8 x 9.2 mm
- Temperature range -40° to +85°C
- High efficiency up to 82%
- Excellent load and line regulation
- Short-circuit protection
- I/O isolation 1600 VDC
- Remote On/Off control
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin	-Vin
2	+Vin	+Vin
3	Remote On/Off	Remote On/Off
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 4-2411WI	9 -36 VDC (24 VDC nom.)	5 VDC	211 mA	79 %
TMR 4-2412WI		12 VDC	201 mA	83 %
TMR 4-2413WI		15 VDC	200 mA	83 %
TMR 4-2415WI		24 VDC	200 mA	83 %
TMR 4-2422WI		±12 VDC	200 mA	83 %
TMR 4-2423WI		±15 VDC	200 mA	83 %
TMR 4-4811WI	18 -75 VDC (48 VDC nom.)	5 VDC	107 mA	78 %
TMR 4-4812WI		12 VDC	102 mA	82 %
TMR 4-4813WI		15 VDC	101 mA	82 %
TMR 4-4815WI		24 VDC	101 mA	82 %
TMR 4-4822WI		±12 VDC	101 mA	82 %
TMR 4-4823WI		±15 VDC	101 mA	82 %

**TMR 6** **6 Watt**




- 0.86 x 0.44 x 0.36" SIP-8 package
- Wide 2:1 input voltage range
- Continuous short-circuit protection
- Temperature range -40° to +78°C
- High efficiency up to 86%
- I/O isolation 1600 VDC
- Remote On/Off control
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 6-0510	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	1'300 mA	77 %
TMR 6-0511		5 VDC	1'200 mA	81 %
TMR 6-0519		9 VDC	666 mA	83 %
TMR 6-0512		12 VDC	500 mA	84 %
TMR 6-0513		15 VDC	400 mA	84 %
TMR 6-0515		24 VDC	250 mA	84 %
TMR 6-0521		+5 VDC	600 mA	81 %
TMR 6-0522		+12 VDC	250 mA	84 %
TMR 6-0523		+15 VDC	200 mA	84 %
TMR 6-1210		9 - 18 VDC (12 VDC nom.)	3.3 VDC	1'300 mA
TMR 6-1211	5 VDC		1'200 mA	83 %
TMR 6-1219	9 VDC		666 mA	85 %
TMR 6-1212	12 VDC		500 mA	85 %
TMR 6-1213	15 VDC		400 mA	85 %
TMR 6-1215	24 VDC		250 mA	84 %
TMR 6-1221	+5 VDC		600 mA	82 %
TMR 6-1222	+12 VDC		250 mA	84 %
TMR 6-1223	+15 VDC		200 mA	85 %
TMR 6-2410	18 - 36 VDC (24 VDC nom.)		3.3 VDC	1'300 mA
TMR 6-2411		5 VDC	1'200 mA	83 %
TMR 6-2419		9 VDC	666 mA	85 %
TMR 6-2412		12 VDC	500 mA	86 %
TMR 6-2413		15 VDC	400 mA	86 %
TMR 6-2415		24 VDC	250 mA	85 %
TMR 6-2421		+5 VDC	600 mA	82 %
TMR 6-2422		+12 VDC	250 mA	85 %
TMR 6-2423		+15 VDC	200 mA	85 %
TMR 6-4810		36 - 75 VDC (48 VDC nom.)	3.3 VDC	1'300 mA
TMR 6-4811	5 VDC		1'200 mA	82 %
TMR 6-4819	9 VDC		666 mA	84 %
TMR 6-4812	12 VDC		500 mA	85 %
TMR 6-4813	15 VDC		400 mA	86 %
TMR 6-4815	24 VDC		250 mA	84 %
TMR 6-4821	+5 VDC		600 mA	82 %
TMR 6-4822	+12 VDC		250 mA	84 %
TMR 6-4823	+15 VDC		200 mA	85 %

**TMR 6WI** **6 Watt**



- 0.86 x 0.44 x 0.36" SIP-8 package
- Wide 4:1 input voltage range
- Ultra-compact SIP-8 package
- Smallest footprint 6 W converter
- Temperature range -40° to +84°C
- High efficiency up to 88%
- Indefinite short-circuit protection
- I/O isolation 1600 VDC
- Remote On/Off control
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
5	NC	NC
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 6-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	1'500 mA	81 %
TMR 6-2411WI		5 VDC	1'200 mA	84 %
TMR 6-2419WI		9 VDC	666 mA	86 %
TMR 6-2412WI		12 VDC	500 mA	87 %
TMR 6-2413WI		15 VDC	400 mA	88 %
TMR 6-2415WI		24 VDC	250 mA	87 %
TMR 6-2421WI		+5 VDC	600 mA	84 %
TMR 6-2422WI		+12 VDC	250 mA	87 %
TMR 6-2423WI		+15 VDC	200 mA	87 %
TMR 6-4810WI		18 - 75 VDC (48 VDC nom.)	3.3 VDC	1'500 mA
TMR 6-4811WI	5 VDC		1'200 mA	84 %
TMR 6-4819WI	9 VDC		666 mA	85 %
TMR 6-4812WI	12 VDC		500 mA	87 %
TMR 6-4813WI	15 VDC		400 mA	87 %
TMR 6-4815WI	24 VDC		250 mA	87 %
TMR 6-4821WI	+5 VDC		600 mA	84 %
TMR 6-4822WI	+12 VDC		250 mA	87 %
TMR 6-4823WI	+15 VDC		200 mA	87 %




TMR 6WIR

**NEW!**

6 Watt

EN50155 / EN61373 Approved




- 0.86 x 0.44 x 0.38" SIP-8 package
- EN 50155 railway approval
- Ultra-wide 4:1 Input: 9-36, 18-75 and 43-160 VDC
- I/O-isolation 3'000 VDC
- Fully regulated outputs
- Operating temperature range -40°C to +80°C
- Short circuit protection and current limitation
- Remote On/Off
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout
9, 10	Case	Case

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 6-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	1500 mA	81 %
TMR 6-2411WIR		5 VDC	1200 mA	84 %
TMR 6-2419WIR		9 VDC	666 mA	86 %
TMR 6-2412WIR		12 VDC	500 mA	87 %
TMR 6-2413WIR		15 VDC	400 mA	88 %
TMR 6-2415WIR		24 VDC	250 mA	87 %
TMR 6-2421WIR		± 5 VDC	600 mA	84 %
TMR 6-2422WIR		± 12 VDC	250 mA	87 %
TMR 6-2423WIR		± 15 VDC	200 mA	87 %
TMR 6-4810WIR		18 - 75 VDC (48 VDC nom.)	3.3 VDC	1500 mA
TMR 6-4811WIR	5 VDC		1200 mA	84 %
TMR 6-4819WIR	9 VDC		666 mA	85 %
TMR 6-4812WIR	12 VDC		500 mA	87 %
TMR 6-4813WIR	15 VDC		400 mA	87 %
TMR 6-4815WIR	24 VDC		250 mA	87 %
TMR 6-4821WIR	± 5 VDC		600 mA	84 %
TMR 6-4822WIR	± 12 VDC		250 mA	87 %
TMR 6-4823WIR	± 15 VDC		200 mA	87 %

TMR 9

9 Watt




- 0.86 x 0.44 x 0.38" SIP-8 package
- Wide 2:1 input voltage range
- Temperature range -40° to +85°C
- High efficiency up to 89%
- Indefinite short-circuit protection
- I/O isolation 1600 VDC
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout
9	Case	Case
10	Stand Off	Stand Off
11	Stand Off	Stand Off
12	Case	Case

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 9-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	2'000 mA	81 %
TMR 9-1211		5 VDC	1'600 mA	85 %
TMR 9-1219		9 VDC	1'000 mA	87 %
TMR 9-1212		12 VDC	750 mA	88 %
TMR 9-1213		15 VDC	600 mA	89 %
TMR 9-1215		24 VDC	375 mA	89 %
TMR 9-1221		+5 VDC	800 mA	85 %
TMR 9-1222		+12 VDC	375 mA	88 %
TMR 9-1223		+15 VDC	300 mA	89 %
TMR 9-2410		18 - 36 VDC (24 VDC nom.)	3.3 VDC	2'000 mA
TMR 9-2411	5 VDC		1'600 mA	85 %
TMR 9-2419	9 VDC		1'000 mA	88 %
TMR 9-2412	12 VDC		750 mA	89 %
TMR 9-2413	15 VDC		600 mA	90 %
TMR 9-2415	24 VDC		375 mA	90 %
TMR 9-2421	+5 VDC		800 mA	86 %
TMR 9-2422	+12 VDC		375 mA	89 %
TMR 9-2423	+15 VDC		300 mA	87 %
TMR 9-4810	36 - 75 VDC (48 VDC nom.)		3.3 VDC	2'000 mA
TMR 9-4811		5 VDC	1'600 mA	85 %
TMR 9-4819		9 VDC	1'000 mA	88 %
TMR 9-4812		12 VDC	750 mA	89 %
TMR 9-4813		15 VDC	600 mA	89 %
TMR 9-4815		24 VDC	375 mA	89 %
TMR 9-4821		+5 VDC	800 mA	86 %
TMR 9-4822		+12 VDC	375 mA	87 %
TMR 9-4823		+15 VDC	300 mA	87 %

TMR 9WI 9 Watt



- 0.86 x 0.44 x 0.38" SIP-8 package
- Ultra-wide 4:1 input voltage range
- Temperature range -40° to +85°C
- High efficiency up to 89%
- Indefinite short-circuit protection
- I/O isolation 1600 VDC
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
3	Remote	Remote
6	+Vout	+Vout
7	-Vout	Common
8	NC	-Vout
9	Case	Case
10	Stand Off	Stand Off
11	Stand Off	Stand Off
12	Case	Case

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMR 9-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2'000 mA	82 %
TMR 9-2411WI		5 VDC	1'600 mA	85 %
TMR 9-2419WI		9 VDC	1'000 mA	88 %
TMR 9-2412WI		12 VDC	750 mA	88 %
TMR 9-2413WI		15 VDC	600 mA	89 %
TMR 9-2415WI		24 VDC	375 mA	89 %
TMR 9-2421WI		+5 VDC	800 mA	86 %
TMR 9-2422WI		+12 VDC	375 mA	88 %
TMR 9-2423WI		+15 VDC	300 mA	88 %
TMR 9-4810WI		18 - 75 VDC (48 VDC nom.)	3.3 VDC	2'000 mA
TMR 9-4811WI	5 VDC		1'600 mA	85 %
TMR 9-4819WI	9 VDC		1'000 mA	89 %
TMR 9-4812WI	12 VDC		750 mA	89 %
TMR 9-4813WI	15 VDC		600 mA	89 %
TMR 9-4815WI	24 VDC		375 mA	89 %
TMR 9-4821WI	+5 VDC		800 mA	85 %
TMR 9-4822WI	+12 VDC		375 mA	88 %
TMR 9-4823WI	+15 VDC		300 mA	87 %

# DC/DC: Isolated DIP Package

TRACO POWER's DIP package isolated DC/DC Converters provide a complete range of compact products from 1 to 60 watts with non-regulated, semi-regulated and fully regulated outputs.

SERIES	WATTS	DESCRIPTION	APPS	STATUS	PAGE
TDN 1WI	1	DIP package, 4:1 input, regulated, encapsulated		ACTIVE	41
TDR 2	2	DIP-14 package, 2:1 input, regulated, overmold (washable), plastic case		ACTIVE	41
TDR 2WI	2	DIP-14 package, 4:1 input, regulated, overmold (washable), plastic case		ACTIVE	42
THI 2M	2	DIP-16 package, $\pm 10\%$ input, unregulated, 2 $\times$ MOOP, encapsulated		ACTIVE	42
TIM 2	2	DIP-16 package, 2 :1 input, regulated, 5000 VAC I/O-isolation, 2 xMOPP medical, encapsulated	⊕	NEW	43
TDN 3WI	3	DIP package, 4:1 input, regulated, high power density, encapsulated		ACTIVE	43
TDR 3	3	DIP-14 package, 2:1 input, regulated, overmold (washable), plastic case		ACTIVE	44
TDR 3WI	3	DIP-14 package, 4:1 input, regulated, overmold (washable), plastic case		ACTIVE	44
TEM 3N	3	DIP-24 package, $\pm 10\%$ input, regulated, cost efficient, encapsulated		ACTIVE	45
TEN 3N	3	DIP-24 package, 2:1 input, regulated, cost efficient, encapsulated		ACTIVE	45
TEN 3WIN	3	DIP-24 package, 4:1 input, regulated, cost efficient, encapsulated		ACTIVE	46
THI 3	3	DIP-24 package, 10% input, regulated, 4000 VAC isolation, 2 $\times$ MOOP medical, encapsulated	⊕	ACTIVE	46
THM 3	3	DIP-24 package, 2:1 input, regulated, 5000 VAC isolation, 2 $\times$ MOPP medical, encapsulated	⊕	ACTIVE	47
THM 3WI	3	DIP-24 package, 4:1 input, regulated, 5000 VAC isolation, 2 $\times$ MOPP medical, encapsulated	⊕	ACTIVE	47
THP 3	3	DIP-24 package, 4:1 input, regulated, 3000 VAC isolation, 2 $\times$ MOOP medical, encapsulated	⊕	ACTIVE	48
THR 3WI	3	DIP-24 package, 4:1 input, regulated, 3000 VAC isolation (reinforced), encapsulated		COMING SOON	48
TIM 3.5	3.5	DIP-16 package, 2 :1 input, regulated, 5000 VAC I/O isolation, 2 xMOPP medical, encapsulated	⊕	NEW	49
TRI 3	3.5	DIP-24 package, 2:1 input, regulated, 5000 VAC I/O isolation, encapsulated		NEW	49
TDN 5WI	5	DIP package, 4:1 input, regulated, highest power density, encapsulated		ACTIVE	50
TEL 5	5	DIP-24 package, 2:1 input, regulated, cost optimized, encapsulated		ACTIVE	50
TVN 5WI	5	DIP-24 package, 4:1 input, regulated, ultra low ripple & noise, encapsulated, metal case		ACTIVE	51
TEN 6N	6	DIP-24 package, 2:1 input, regulated, cost efficient, encapsulated		ACTIVE	51
TEN 6WIN	6	DIP-24 package, 4:1 input, regulated, cost efficient, encapsulated		ACTIVE	52
THM 6	6	DIP-24 package, 2:1 input, regulated, 5000 VAC isolation, 2 $\times$ MOPP medical, encapsulated	⊕	ACTIVE	52
THM 6WI	6	DIP-24 package, 4:1 input, regulated, 5000 VAC isolation, 2 $\times$ MOPP medical, encapsulated	⊕	ACTIVE	53
TRI 6	6	DIP-24 package, 2:1 input, regulated, 5000 VAC I/O isolation, encapsulated		NEW	53
TEL 8	8	DIP-16 package, 2:1 input, regulated, high power density, encapsulated, metal case		ACTIVE	54
TEL 8WI	8	DIP-16 package, 4:1 input, regulated, high power density, encapsulated, metal case		ACTIVE	54
TEN 8	8	DIP-24 package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	55
TEN 8WI	8	DIP-24 package, 4:1 input, regulated, encapsulated, railway, metal case	🚂	ACTIVE	55
TEL 10	10	DIP-16 package, 2:1 input, regulated, high power density, encapsulated, metal case		NEW	56
TEL 10WI	10	DIP-16 package, 4:1 input, regulated, high power density, encapsulated, metal case		ACTIVE	56
THD 10N	10	DIP-24 package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	57
THD 10WIN	10	DIP-24 package, 4:1 input, regulated, encapsulated, metal case		ACTIVE	57
THL 10	10	1" x 1" package, 2:1 input, regulated, cost efficient, encapsulated, metal case		ACTIVE	58
THM 10	10	DIP-24 package, 2:1 input, regulated, 5000 VAC isolation, 2 $\times$ MOPP medical, encapsulated	⊕	ACTIVE	58
THM 10WI	10	DIP-24 package, 4:1 input, regulated, 5000 VAC isolation, 2 $\times$ MOPP medical, encapsulated	⊕	ACTIVE	59
THN 10WIR	10	1" x 1" package, 4:1 input, regulated, 3000 VDC isolation, railway, encapsulated, metal case	🚂	NEW	59
THR 10WI	10	2 $\times$ 1" package, 4:1 input, regulated, 3000 VAC isolation (reinforced), encapsulated		COMING SOON	60
TRI 10	10	DIP-24 package, 2:1 input, regulated, 5000 VAC I/O isolation, encapsulated		NEW	60

APPS KEY: ⊕ = UL/EN60601-1 (2 $\times$ MOPP) Approved

🚂 = EN50155 /EN61373 Approved




SERIES	WATTS	DESCRIPTION	APPS	STATUS	PAGE
TEL 12	12	DIP-16 package, 2:1 input, regulated, high power density, encapsulated, metal case		NEW	61
TEL 12WI	12	DIP-16 package, 4:1 input, regulated, high power density, encapsulated, metal case		NEW	61
THD 12	12	DIP-24 package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	62
THD 12WI	12	DIP-24 package, 4:1 input, regulated, encapsulated, metal case		ACTIVE	62
THD 15N	15	DIP-24 package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	63
THD 15WIN	15	DIP-24 package, 4:1 input, regulated, encapsulated, metal case		ACTIVE	63
THL 15WI	15	1" x 1" package, 4:1 input, regulated, cost optimized, encapsulated, metal case		NEW	64
THM 15	15	1.6" x 1" package, 2:1 input, regulated, 5000 VAC isolation, 2 × MOPP medical, encapsulated	⊕	ACTIVE	64
THM 15WI	15	1.6" x 1" package, 4:1 input, regulated, 5000 VAC isolation, 2 × MOPP medical, encapsulated	⊕	ACTIVE	65
THN 15	15	1" x 1" package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	65
THN 15N	15	1" x 1" package, 2:1 input, regulated, encapsulated, metal case, integrated EN 55032 Class A filter		ACTIVE	66
THN 15WI	15	1" x 1" package, 4:1 input, regulated, encapsulated, metal case		NEW models	66
THN 15WIR	15	1" x 1" package, 4:1 input, regulated, 3000 VDC isolation, railway, encapsulated, metal case	🚂	ACTIVE	67
TRI 15	15	2" x 1" package, 2:1 input, regulated, 1000 VAC working voltage, encapsulated		NEW	67
TEN 20WIR	20	2" x 1" package, 4:1 input, regulated, 2250 VDC isolation, railway, encapsulated	🚂	ACTIVE	68
THM 20	20	1.6" x 1" package, 2:1 input, regulated, 5000 VAC isolation, 2 × MOPP medical, encapsulated	⊕	ACTIVE	68
THM 20WI	20	1.6" x 1" package, 4:1 input, regulated, 5000 VAC isolation, 2 × MOPP medical, encapsulated	⊕	ACTIVE	69
THN 20	20	1" x 1" package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	69
THN 20WI	20	1" x 1" package, 4:1 input, regulated, encapsulated, metal case		NEW models	70
THN 20WIR	20	1" x 1" package, 4:1 input, regulated, 3000 VDC isolation, railway, encapsulated	🚂	NEW	70
THR 20WI	20	2" x 1" package, 4:1 input, regulated, 3000 VAC isolation (reinforced), encapsulated		COMING SOON	71
TRI 20	20	2" x 1" package, 2:1 input, regulated, 1000 VAC working voltage, encapsulated		NEW	71
THL 25	25	1" x 1" package, 2:1 input, regulated, cost optimized, encapsulated, metal case		ACTIVE	72
THL 25WI	25	1" x 1" package, 4:1 input, regulated, cost optimized, encapsulated, metal case		ACTIVE	72
TEN 30	30	2" x 1" package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	73
TEN 30WIN	30	2" x 1" package, 4:1 input, regulated, encapsulated, metal case		ACTIVE	73
THM 30	30	2" x 1" package, 2:1 input, regulated, 5000 VAC isolation, 2 × MOPP medical, encapsulated	⊕	ACTIVE	74
THM 30WI	30	2" x 1" package, 4:1 input, regulated, 5000 VAC isolation, 2 × MOPP medical, encapsulated	⊕	ACTIVE	74
THN 30	30	1" x 1" package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	75
THN 30WI	30	1" x 1" package, 4:1 input, regulated, encapsulated, metal case		NEW models	75
THN 30WIR	30	1" x 1" package, 4:1 input, regulated, 3000 VDC isolation, railway, encapsulated	🚂	COMING SOON	76
TEN 40E	40	2" x 1" package, 2:1 input, regulated, cost efficient, encapsulated, metal case		NEW	76
TEN 40WIE	40	2" x 1" package, 4:1 input, regulated, cost efficient, encapsulated, metal case		NEW	77
TEN 40WIR	40	2" x 1" package, 4:1 input, regulated, 2250 VDC isolation, railway, encapsulated	🚂	ACTIVE	77
THR 40WI	40	2" x 1" package, 4:1 input, regulated, 3000 VAC isolation (reinforced), encapsulated		COMING SOON	78
TEN 50	50	2" x 1" package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	78
TEN 50WI	50	2" x 1" package, 4:1 input, regulated, encapsulated, metal case		ACTIVE	79
TEN 60N	60	2" x 1" package, 2:1 input, regulated, encapsulated, metal case		ACTIVE	79
TEN 60WIN	60	2" x 1" package, 4:1 input, regulated, encapsulated, metal case		ACTIVE	80
TEN 60WIR	60	2" x 1" package, 4:1 input, regulated, 3000 VDC isolation, railway, encapsulated	🚂	NEW	80

APPS KEY: ⊕ = UL/EN60601-1 (2×MOPP) Approved    🚂 = EN50155 /EN61373 Approved



TDN 1WI

1 Watt




- 0.52 x 0.36 x 0.40" package
- Ultra-wide 4 : 1 input range
- Fully regulated outputs
- I/O-isolation 1600 VDC
- Operating temperature range -40°C to +90°C without derating
- Short circuit protection
- Remote On/Off
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	On/Off	On/Off
5	no con.	-Vout
6	-Vout	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDN 1-1210WI	4.5 - 18 VDC (12 VDC nominal)	3.3 VDC	300 mA	77 %
TDN 1-1211WI		5.0 VDC	200 mA	79 %
TDN 1-1219WI		9.0 VDC	112 mA	79 %
TDN 1-1212WI		12 VDC	90 mA	81 %
TDN 1-1213WI		15 VDC	70 mA	81 %
TDN 1-1215WI		24 VDC	45 mA	80 %
TDN 1-1221WI		± 5.0 VDC	±100 mA	77 %
TDN 1-1222WI		±12 VDC	±45 mA	80 %
TDN 1-1223WI		±15 VDC	±35 mA	81 %
TDN 1-2410WI		9 - 36 VDC (24 VDC nominal)	3.3 VDC	300 mA
TDN 1-2411WI	5.0 VDC		200 mA	78 %
TDN 1-2419WI	9.0 VDC		112 mA	79 %
TDN 1-2412WI	12 VDC		90 mA	81 %
TDN 1-2413WI	15 VDC		70 mA	81 %
TDN 1-2415WI	24 VDC		45 mA	80 %
TDN 1-2421WI	± 5.0 VDC		±100 mA	77 %
TDN 1-2422WI	±12 VDC		±45 mA	80 %
TDN 1-2423WI	±15 VDC		±35 mA	81 %
TDN 1-4810WI	18 - 75 VDC (48 VDC nominal)		3.3 VDC	300 mA
TDN 1-4811WI		5.0 VDC	200 mA	78 %
TDN 1-4819WI		9.0 VDC	112 mA	79 %
TDN 1-4812WI		12 VDC	90 mA	81 %
TDN 1-4813WI		15 VDC	70 mA	81 %
TDN 1-4815WI		24 VDC	45 mA	80 %
TDN 1-4821WI		± 5.0 VDC	±100 mA	77 %
TDN 1-4822WI		±12 VDC	±45 mA	80 %
TDN 1-4823WI		±15 VDC	±35 mA	81 %

TDR 2

2 Watt




- 0.74 x 0.50 x 0.35" package
- Wide 2:1 input voltage range
- Fully regulated outputs
- Low ripple and noise
- No minimum load required
- Temperature range -40°C to +85°C without derating
- I/O isolation 1600 VDC
- Continuous short-circuit protection
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDR 2-0511	4.5 - 9.0 VDC (5 VDC nominal)	5.0 VDC	400 mA	80 %
TDR 2-0512		12 VDC	167 mA	81 %
TDR 2-0513		15 VDC	134 mA	83 %
TDR 2-0522		±12 VDC	±83 mA	81 %
TDR 2-0523		±15 VDC	±67 mA	82 %
TDR 2-1211	9 - 18 VDC (12 VDC nominal)	5.0 VDC	400 mA	81 %
TDR 2-1212		12 VDC	167 mA	81 %
TDR 2-1213		15 VDC	134 mA	84 %
TDR 2-1222		±12 VDC	±83 mA	83 %
TDR 2-1223		±15 VDC	±67 mA	82 %
TDR 2-2411	18 - 36 VDC (24 VDC nominal)	5.0 VDC	400 mA	81 %
TDR 2-2412		12 VDC	167 mA	84 %
TDR 2-2413		15 VDC	134 mA	84 %
TDR 2-2422		±12 VDC	±83 mA	84 %
TDR 2-2423		±15 VDC	±67 mA	84 %
TDR 2-4811	36 - 75 VDC (48 VDC nominal)	5.0 VDC	400 mA	81 %
TDR 2-4812		12 VDC	167 mA	82 %
TDR 2-4813		15 VDC	134 mA	82 %
TDR 2-4822		±12 VDC	±83 mA	83 %
TDR 2-4823		±15 VDC	±67 mA	83 %

**TDR 2WI** **2 Watt**




- 0.74 x 0.50 x 0.35" package
- Ultra-wide 4:1 input voltage range
- Fully regulated outputs
- Low ripple and noise 30mV pk-pk
- No minimum load required
- Temperature range -40°C to +85°C without derating
- I/O isolation 1600 VDC
- Continuous short-circuit protection
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDR 2-1211WI	4.5 - 18 VDC (12 VDC nominal)	5.0 VDC	400 mA	79 %
TDR 2-1212WI		12 VDC	167 mA	80 %
TDR 2-1213WI		15 VDC	134 mA	81 %
TDR 2-1222WI		±12 VDC	±83 mA	81 %
TDR 2-1223WI		±15 VDC	±67 mA	81 %
TDR 2-2411WI	9 - 36 VDC (24 VDC nominal)	5.0 VDC	400 mA	79 %
TDR 2-2412WI		12 VDC	167 mA	80 %
TDR 2-2413WI		15 VDC	134 mA	82 %
TDR 2-2422WI		±12 VDC	±83 mA	81 %
TDR 2-2423WI		±15 VDC	±67 mA	81 %
TDR 2-4811WI	18 - 75 VDC (48 VDC nominal)	5.0 VDC	400 mA	78 %
TDR 2-4812WI		12 VDC	167 mA	81 %
TDR 2-4813WI		15 VDC	134 mA	82 %
TDR 2-4822WI		±12 VDC	±83 mA	81 %
TDR 2-4823WI		±15 VDC	±67 mA	81 %

**THI 2M** **2 Watt**





- 0.94 x 0.54 x 0.34" DIP-16 package
- I/O isolation 3000 VACrms rated for 300 Vrms working voltage
- IEC/EN/UL 60601-1 3rd edition, 2 x MOOP
- IEC/EN/UL 62368-1
- Temp. range -40°C to +71°C
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	No con.	No con.
8	No con.	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin	+Vin

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THI 2-0511M	5.0 VDC ± 10% (nominal 5 VDC)	5 VDC	400 mA	66 %
THI 2-0512M		12 VDC	165 mA	66 %
THI 2-0513M		15 VDC	133 mA	66 %
THI 2-0522M		±12 VDC	±83 mA	72 %
THI 2-0523M		±15 VDC	±66 mA	73 %
THI 2-1211M	12.0 VDC ± 10% (nominal 12 VDC)	5 VDC	400 mA	66 %
THI 2-1212M		12 VDC	165 mA	66 %
THI 2-1213M		15 VDC	133 mA	66 %
THI 2-1222M		±12 VDC	±83 mA	74 %
THI 2-1223M		±15 VDC	±66 mA	75 %
THI 2-2411M	24 VDC ± 10% (nominal 24 VDC)	5 VDC	400 mA	66 %
THI 2-2412M		12 VDC	165 mA	66 %
THI 2-2413M		15 VDC	133 mA	66 %
THI 2-2422M		±12 VDC	±83 mA	74 %
THI 2-2423M		±15 VDC	±66 mA	75 %

**TIM 2** **NEW!** **2 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 0.95 x 0.57 x 0.40" DIP-16 package
- I/O isolation 5000 VAC rated for 250 VAC working voltage
- 2 x MOPP / BF Compliant
- Low leakage current < 2 μA
- Extended operating temperature range -40°C to 95°C
- EMC compliance to IEC 60601-1-2 4th edition and EN 55032 class A
- 5 year product warranty

Pinout / Connection		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	Remote	Remote
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TIM 2-0910	4.5 - 12 VDC (9 VDC nom.)	3.3 VDC	600 mA	75 %	
TIM 2-0911		5 VDC	400 mA	78 %	
TIM 2-0919		9 VDC	222 mA	78 %	
TIM 2-0912		12 VDC	167 mA	82 %	
TIM 2-0913		15 VDC	134 mA	82 %	
TIM 2-0915		24 VDC	83 mA	82 %	
TIM 2-0922	9 - 18 VDC (12 VDC nom.)	±12 VDC	83 mA	82 %	
TIM 2-0923		±15 VDC	67 mA	80 %	
TIM 2-1210		3.3 VDC	600 mA	76 %	
TIM 2-1211	18 - 36 VDC (24 VDC nom.)	5 VDC	400 mA	78 %	
TIM 2-1219		9 VDC	222 mA	79 %	
TIM 2-1212		12 VDC	167 mA	82 %	
TIM 2-1213		15 VDC	134 mA	82 %	
TIM 2-1215		24 VDC	83 mA	81 %	
TIM 2-1222		±12 VDC	83 mA	81 %	
TIM 2-1223	±15 VDC	67 mA	81 %		
TIM 2-2410	36 - 75 VDC (48 VDC nom.)	3.3 VDC	600 mA	76 %	
TIM 2-2411		5 VDC	400 mA	78 %	
TIM 2-2419		9 VDC	222 mA	80 %	
TIM 2-2412		12 VDC	167 mA	81 %	
TIM 2-2413		15 VDC	134 mA	81 %	
TIM 2-2415		24 VDC	83 mA	81 %	
TIM 2-2422	9 - 18 VDC (12 VDC nom.)	±12 VDC	83 mA	81 %	
TIM 2-2423		±15 VDC	67 mA	81 %	
TIM 2-4810		18 - 75 VDC (48 VDC nom.)	3.3 VDC	600 mA	76 %
TIM 2-4811			5 VDC	400 mA	78 %
TIM 2-4819			9 VDC	222 mA	79 %
TIM 2-4812			12 VDC	167 mA	80 %
TIM 2-4813	15 VDC		134 mA	82 %	
TIM 2-4815	24 VDC		83 mA	81 %	
TIM 2-4822	9 - 18 VDC (12 VDC nom.)	±12 VDC	83 mA	81 %	
TIM 2-4823		±15 VDC	67 mA	81 %	

**TDN 3WI** **3 Watt**





- 0.52 x 0.36 x 0.40 package
- Ultra-wide 4 : 1 input range
- I/O-isolation 1600 VDC
- Fully regulated outputs
- Operating temperature range -40°C to +70°C without derating
- Short circuit protection
- Remote On/Off
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	On/Off	On/Off
5	no con.	-Vout
6	-Vout	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TDN 3-1210WI	4.5 - 18 VDC (12 VDC nominal)	3.3 VDC	700 mA	76 %	
TDN 3-1211WI		5.0 VDC	600 mA	80 %	
TDN 3-1219WI		9.0 VDC	333 mA	81 %	
TDN 3-1212WI		12 VDC	250 mA	83 %	
TDN 3-1213WI		15 VDC	200 mA	84 %	
TDN 3-1215WI		24 VDC	125 mA	82 %	
TDN 3-1221WI	9 - 36 VDC (24 VDC nominal)	±5.0 VDC	±300 mA	80 %	
TDN 3-1222WI		±12 VDC	±125 mA	82 %	
TDN 3-1223WI		±15 VDC	±100 mA	82 %	
TDN 3-2410WI		18 - 75 VDC (48 VDC nominal)	3.3 VDC	700 mA	77 %
TDN 3-2411WI			5.0 VDC	600 mA	80 %
TDN 3-2419WI			9.0 VDC	333 mA	81 %
TDN 3-2412WI	12 VDC		250 mA	83 %	
TDN 3-2413WI	15 VDC		200 mA	83 %	
TDN 3-2415WI	24 VDC		125 mA	82 %	
TDN 3-2421WI	9 - 18 VDC (12 VDC nominal)	±5.0 VDC	±300 mA	80 %	
TDN 3-2422WI		±12 VDC	±125 mA	82 %	
TDN 3-2423WI		±15 VDC	±100 mA	82 %	
TDN 3-4810WI		18 - 75 VDC (48 VDC nominal)	3.3 VDC	700 mA	77 %
TDN 3-4811WI			5.0 VDC	600 mA	80 %
TDN 3-4819WI			9.0 VDC	333 mA	81 %
TDN 3-4812WI	12 VDC		250 mA	83 %	
TDN 3-4813WI	15 VDC		200 mA	83 %	
TDN 3-4815WI	24 VDC		125 mA	82 %	
TDN 3-4821WI	9 - 18 VDC (12 VDC nominal)	±5.0 VDC	±300 mA	80 %	
TDN 3-4822WI		±12 VDC	±125 mA	82 %	
TDN 3-4823WI		±15 VDC	±100 mA	82 %	

TDR 3

3 Watt





- 0.74 x 0.50 x 0.35" DIP 14 package
- Wide 2:1 input voltage range
- Fully regulated outputs
- Low ripple and noise
- No minimum load required
- Temperature range -40°C to +85°C
- I/O isolation 1600 VDC
- Continuous short-circuit protection
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDR 3-0511	4.5 - 9.0 VDC (5 VDC nominal)	5.0 VDC	600 mA	79 %
TDR 3-0512		12 VDC	250 mA	80 %
TDR 3-0513		15 VDC	200 mA	81 %
TDR 3-0522		±12 VDC	±125 mA	80 %
TDR 3-0523		±15 VDC	±100 mA	81 %
TDR 3-1211	9 - 18 VDC (12 VDC nominal)	5.0 VDC	600 mA	81 %
TDR 3-1212		12 VDC	250 mA	82 %
TDR 3-1213		15 VDC	200 mA	82 %
TDR 3-1222		±12 VDC	±125 mA	82 %
TDR 3-1223		±15 VDC	±100 mA	83 %
TDR 3-2411	18 - 36 VDC (24 VDC nominal)	5.0 VDC	600 mA	81 %
TDR 3-2412		12 VDC	250 mA	82 %
TDR 3-2413		15 VDC	200 mA	83 %
TDR 3-2422		±12 VDC	±125 mA	83 %
TDR 3-2423		±15 VDC	±100 mA	83 %
TDR 3-4811	36 - 75 VDC (48 VDC nominal)	5.0 VDC	600 mA	81 %
TDR 3-4812		12 VDC	250 mA	82 %
TDR 3-4813		15 VDC	200 mA	82 %
TDR 3-4822		±12 VDC	±125 mA	83 %
TDR 3-4823		±15 VDC	±100 mA	83 %

TDR 3WI

3 Watt



- 0.74 x 0.50 x 0.35" DIP 14 package
- Ultra-wide 4:1 input voltage range
- Fully regulated outputs
- Low ripple and noise
- No minimum load required
- Temperature range -40°C to +85°C
- I/O isolation 1600 VDC
- Continuous short-circuit protection
- Remote On/Off control
- Fully RoHS compliant
- 3 year product warranty


Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
2	Remote On/Off	Remote On/Off
6	NC	Common
7	NC	-Vout
8	+Vout	+Vout
9	-Vout	Common
14	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDR 3-1211WI	4.5 - 18 VDC (12 VDC nominal)	5.0 VDC	600 mA	81 %
TDR 3-1212WI		12 VDC	250 mA	82 %
TDR 3-1213WI		15 VDC	200 mA	82 %
TDR 3-1222WI		±12 VDC	±125 mA	82 %
TDR 3-1223WI		±15 VDC	±100 mA	81 %
TDR 3-2411WI	9 - 36 VDC (24 VDC nominal)	5.0 VDC	600 mA	80 %
TDR 3-2412WI		12 VDC	250 mA	82 %
TDR 3-2413WI		15 VDC	200 mA	82 %
TDR 3-2422WI		±12 VDC	±125 mA	82 %
TDR 3-2423WI		±15 VDC	±100 mA	81 %
TDR 3-4811WI	18 - 75 VDC (48 VDC nominal)	5.0 VDC	600 mA	80 %
TDR 3-4812WI		12 VDC	250 mA	83 %
TDR 3-4813WI		15 VDC	200 mA	82 %
TDR 3-4822WI		±12 VDC	±125 mA	82 %
TDR 3-4823WI		±15 VDC	±100 mA	81 %



TEM 3N

3 Watt




- 1.26 x 0.80 x 0.40" DIP-24 package
- Fully regulated output
- Output ripple & noise 30 mVp-p typ.
- Short circuit protection
- Operating temperature range -40°C to +75°C at full load
- I/O isolation 1500 VDC
- Input filter meet EN 55032, class A
- No minimum load required
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	ntc.	-Vout
3	ntc.	Common
10	-Vout	Common
11	+Vout	+Vout
12	-Vin (GND)	-Vin (GND)
13	-Vin (GND)	-Vin (GND)
14	+Vout	+Vout
15	-Vout	Common
22	ntc.	Common
23	ntc.	-Vout
24	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEM 3-0511N	5 VDC ±10%	5 VDC	600 mA	70 %
TEM 3-0512N		12 VDC	250 mA	78 %
TEM 3-0513N		15 VDC	200 mA	78 %
TEM 3-0522N		±12 VDC	±125 mA	78 %
TEM 3-0523N		±15 VDC	±100 mA	78 %
TEM 3-1211N	12 VDC ±10%	5 VDC	600 mA	74 %
TEM 3-1212N		12 VDC	250 mA	80 %
TEM 3-1213N		15 VDC	200 mA	80 %
TEM 3-1222N		±12 VDC	±125 mA	81 %
TEM 3-1223N		±15 VDC	±100 mA	82 %
TEM 3-2411N	24 VDC ±10%	5 VDC	600 mA	75 %
TEM 3-2412N		12 VDC	250 mA	80 %
TEM 3-2413N		15 VDC	200 mA	80 %
TEM 3-2422N		±12 VDC	±125 mA	81 %
TEM 3-2423N		±15 VDC	±100 mA	82 %

TEN 3N

3 Watt




- 1.25 x 0.80 x 0.40" DIP-24 package
- Wide 2 : 1 input range
- EN 55032 class A and FCC level A without external components
- Temperature range -40°C to +85°C
- Models with 1500 VDC and 3000 VDC I/O isolation (functional insulation)
- High reliability, MTBF >1.0 Mio. h
- 3 year product warranty

Pinout		
Pin	Single	Dual
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	ntc	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TEN 3-0510N	4.5 - 9.0 VDC (nominal 5 VDC)	3.3 VDC	750 mA	77 %	
TEN 3-0511N		5.0 VDC	600 mA	80 %	
TEN 3-0512N		12 VDC	250 mA	82 %	
TEN 3-0513N		15 VDC	200 mA	82 %	
TEN 3-0515N		24 VDC	125 mA	81 %	
TEN 3-0521N		±5.0 VDC	±250 mA	80 %	
TEN 3-0522N		±12 VDC	±125 mA	82 %	
TEN 3-0523N		±15 VDC	±100 mA	82 %	
TEN 3-1210N		9 - 18 VDC (nominal 12 VDC)	3.3 VDC	750 mA	79 %
TEN 3-1211N			5.0 VDC	600 mA	81 %
TEN 3-1212N	12 VDC		250 mA	85 %	
TEN 3-1213N	15 VDC		200 mA	85 %	
TEN 3-1215N	24 VDC		125 mA	84 %	
TEN 3-1221N	±5.0 VDC		±250 mA	80 %	
TEN 3-1222N	±12 VDC		±125 mA	84 %	
TEN 3-1223N	±15 VDC		±100 mA	84 %	
TEN 3-2410N	18 - 36 VDC (nominal 24 VDC)		3.3 VDC	750 mA	79 %
TEN 3-2411N			5.0 VDC	600 mA	81 %
TEN 3-2412N		12 VDC	250 mA	85 %	
TEN 3-2413N		15 VDC	200 mA	85 %	
TEN 3-2415N		24 VDC	125 mA	84 %	
TEN 3-2421N		±5.0 VDC	±250 mA	80 %	
TEN 3-2422N		±12 VDC	±125 mA	84 %	
TEN 3-2423N		±15 VDC	±100 mA	84 %	
TEN 3-4810N		36 - 75 VDC (nominal 48 VDC)	3.3 VDC	750 mA	79 %
TEN 3-4811N			5.0 VDC	600 mA	81 %
TEN 3-4812N	12 VDC		250 mA	85 %	
TEN 3-4813N	15 VDC		200 mA	85 %	
TEN 3-4815N	24 VDC		125 mA	84 %	
TEN 3-4821N	±5.0 VDC		±250 mA	80 %	
TEN 3-4822N	±12 VDC		±125 mA	84 %	
TEN 3-4823N	±15 VDC		±100 mA	84 %	

TEN 3WIN 3 Watt




- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultra-wide 4 : 1 input range
- EN 55032 Class A and FCC level A without external components
- Temperature range -40°C to 85°C
- Models with 1500 VDC and 3000 VDC I/O isolation (functional insulation)
- High reliability, MTBF >1.0 Mio. h
- 3 year product warranty

Pinout		
Pin	Single	Dual
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	ntc	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output Vnom	Output Imax	Efficiency
TEN 3-2410WIN	9.0 - 36 VDC (nominal 24 VDC)	3.3 VDC	750 mA	77 %
TEN 3-2411WIN		5.0 VDC	600 mA	79 %
TEN 3-2412WIN		12 VDC	250 mA	82 %
TEN 3-2413WIN		15 VDC	200 mA	83 %
TEN 3-2415WIN		24 VDC	125 mA	81 %
TEN 3-2421WIN		±5.0 VDC	±250 mA	80 %
TEN 3-2422WIN	±12 VDC	±125 mA	82 %	
TEN 3-2423WIN	±15 VDC	±100 mA	82 %	
TEN 3-4810WIN	18 - 75 VDC (nominal 48 VDC)	3.3 VDC	750 mA	77 %
TEN 3-4811WIN		5 VDC	600 mA	80 %
TEN 3-4812WIN		12 VDC	250 mA	83 %
TEN 3-4813WIN		15 VDC	200 mA	84 %
TEN 3-4815WIN		24 VDC	125 mA	82 %
TEN 3-4821WIN		±5.0 VDC	±250 mA	80 %
TEN 3-4822WIN	±12 VDC	±125 mA	82 %	
TEN 3-4823WIN	±15 VDC	±100 mA	82 %	

THI 3 3 Watt

⊕ IEC/EN/ES 60601-1 (2×MOPP)




- 1.25 x 0.80 x 0.40" DIP-24 package
- Supplementary & reinforced insulation
- I/O isolation 4000 VACrms
- 300 VACrms working voltage
- 2 x MOOP / BF compliant
- Industrial safety to IEC/EN 60950-1
- Fully regulated output voltage
- EN 55032 class A and FCC, level A
- Operating temp. range -40°C to +75°C
- Low leakage current
- Short circuit protection
- 5 year product warranty

Model	Input Voltage Range	Output Vnom	Output Imax	Efficiency
THI 3-0511	5.0 VDC ± 10%	5 VDC	600 mA	60 %
THI 3-0512		12 VDC	250 mA	62 %
THI 3-0513		15 VDC	200 mA	62 %
THI 3-0522		±12 VDC	±125 mA	60 %
THI 3-0523	±15 VDC	±100mA	60 %	
THI 3-1211	12.0 VDC ± 10%	5 VDC	600 mA	60 %
THI 3-1212		12 VDC	250 mA	62 %
THI 3-1213		15 VDC	200 mA	62 %
THI 3-1222		±12 VDC	±125 mA	60 %
THI 3-1223	±15 VDC	±100 mA	60 %	
THI 3-2411	24 VDC ± 10%	5 VDC	600 mA	60 %
THI 3-2412		12 VDC	250 mA	64 %
THI 3-2413		15 VDC	200 mA	64 %
THI 3-2422		±12 VDC	±125 mA	60 %
THI 3-2423	±15 VDC	±100 mA	60 %	

Pinout		
Pin	Single	Dual
1	+Vin (VCC)	+Vin (VCC)
2	+Vin (VCC)	+Vin (VCC)
10	No pin	Common
11	No pin	Common
12	-Vout	No pin.
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)

**THM 3** **3 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 1.25 x 0.80 x 0.40" DIP-24 package
- I/O isolation 5000 VAC rated for 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- Low leakage current < 2 μA
- Operating temperature: -40°C to 90°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	No pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 3-0510	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	1000 mA	81 %
THM 3-0511		5 VDC	600 mA	85 %
THM 3-0512		12 VDC	250 mA	86 %
THM 3-0513		15 VDC	200 mA	88 %
THM 3-0515		24 VDC	125 mA	86 %
THM 3-0521		±5 VDC	300 mA	83 %
THM 3-0522	±12 VDC	125 mA	86 %	
THM 3-0523	±15 VDC	100 mA	86 %	
THM 3-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	1000 mA	82 %
THM 3-1211		5 VDC	600 mA	85 %
THM 3-1212		12 VDC	250 mA	87 %
THM 3-1213		15 VDC	200 mA	87 %
THM 3-1215		24 VDC	125 mA	87 %
THM 3-1221		±5 VDC	300 mA	84 %
THM 3-1222	±12 VDC	125 mA	88 %	
THM 3-1223	±15 VDC	100 mA	87 %	
THM 3-2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	1000 mA	82 %
THM 3-2411		5 VDC	600 mA	85 %
THM 3-2412		12 VDC	250 mA	87 %
THM 3-2413		15 VDC	200 mA	87 %
THM 3-2415		24 VDC	125 mA	87 %
THM 3-2421		±5 VDC	300 mA	83 %
THM 3-2422	±12 VDC	125 mA	87 %	
THM 3-2423	±15 VDC	100 mA	86 %	
THM 3-4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	1000 mA	81 %
THM 3-4811		5 VDC	600 mA	84 %
THM 3-4812		12 VDC	250 mA	87 %
THM 3-4813		15 VDC	200 mA	87 %
THM 3-4815		24 VDC	125 mA	87 %
THM 3-4821		±5 VDC	300 mA	83 %
THM 3-4822	±12 VDC	125 mA	86 %	
THM 3-4823	±15 VDC	100 mA	86 %	

**THM 3WI** **3 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultra-wide 4:1 input voltage 3
- I/O isolation 5000 VAC rated for 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current < 2 μA
- Operating temp.: -40°C to 90°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- Operating up to 5000m altitude
- 5 year product warranty

Pinout / Connection		
Pin	Single	Dual
1	No pin*/Remote	No pin*/Remote
2	-Vin (GND)	-Vin (GND)
10	No pin*/Trim	No pin*/Trim
11	No pin*/NC **	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 3-0510WI	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	1000 mA	81 %
THM 3-0511WI		5 VDC	600 mA	85 %
THM 3-0512WI		12 VDC	250 mA	86 %
THM 3-0513WI		15 VDC	200 mA	88 %
THM 3-0515WI		24 VDC	125 mA	86 %
THM 3-0521WI		±5 VDC	300 mA	83 %
THM 3-0522WI	±12 VDC	125 mA	86 %	
THM 3-0523WI	±15 VDC	100 mA	86 %	
THM 3-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	1000 mA	82 %
THM 3-2411WI		5 VDC	600 mA	85 %
THM 3-2412WI		12 VDC	250 mA	87 %
THM 3-2413WI		15 VDC	200 mA	87 %
THM 3-2415WI		24 VDC	125 mA	87 %
THM 3-2421WI		±5 VDC	300 mA	83 %
THM 3-2422WI	±12 VDC	125 mA	87 %	
THM 3-2423WI	±15 VDC	100 mA	86 %	
THM 3-4810WI	36 - 75 VDC (48 VDC nom.)	3.3 VDC	1000 mA	81 %
THM 3-4811WI		5 VDC	600 mA	84 %
THM 3-4812WI		12 VDC	250 mA	87 %
THM 3-4813WI		15 VDC	200 mA	87 %
THM 3-4815WI		24 VDC	125 mA	87 %
THM 3-4821WI		±5 VDC	300 mA	83 %
THM 3-4822WI	±12 VDC	125 mA	86 %	
THM 3-4823WI	±15 VDC	100 mA	86 %	

**THP 3** **3 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultra-wide 4 : 1 input range
- Supplementary and reinforced insulation (3000 VACrms / 1000 Vrms working voltage)
- 2xMOPP / BF compliant
- Industrial safety to IEC/EN/UL 62368-1
- Temperature range -40°C to 85°C max.
- EN 55032 class A without ext. components
- Continuous short circuit protection
- High reliability, MTBF >1 Mio. hours
- Lead free design, RoHS compliant
- 5 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
THP 3-2411	9 - 40 VDC (24 VDC nominal)	5 VDC	600 mA	78 %
THP 3-2412		12 VDC	250 mA	83 %
THP 3-2422		±12 VDC	±125 mA	83 %
THP 3-2423		±15 VDC	±100 mA	83 %
THP 3-4811	18 - 80 VDC (48 VDC nominal)	5 VDC	600 mA	78 %
THP 3-4812		12 VDC	250 mA	83 %
THP 3-4822		±12 VDC	±125 mA	83 %
THP 3-4823		±15 VDC	±100 mA	83 %
THP 3-7211	36 - 160 VDC (72 VDC nominal)	5 VDC	600 mA	78 %
THP 3-7212		12 VDC	250 mA	83 %
THP 3-7222		±12 VDC	±125 mA	83 %
THP 3-7223		±15 VDC	±100 mA	83 %

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	No pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)

**THR 3WI** **NEW - under development** **3 Watt**



- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultra-wide 4 : 1 input range
- Reinforced I/O-isolation 3000 VAC
- Input filter to meet EN 55032, Class A
- High efficiency up to 85%
- Temperature range -40°C to 90°C
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
THR 3-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	600 mA	80 %
THR 3-2412WI		12 VDC	250 mA	84 %
THR 3-2413WI		15 VDC	200 mA	85 %
THR 3-2422WI		±12 VDC	±125 mA	83 %
THR 3-2423WI	±15 VDC	±100 mA	84 %	
THR 3-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	600 mA	80 %
THR 3-4812WI		12 VDC	250 mA	83 %
THR 3-4813WI		15 VDC	200 mA	84 %
THR 3-4822WI		±12 VDC	±125 mA	83 %
THR 3-4823WI	±15 VDC	±100 mA	83 %	
THR 3-7211WI	40 - 160 VDC (110 VDC nom.)	5 VDC	600 mA	80 %
THR 3-7212WI		12 VDC	250 mA	84 %
THR 3-7213WI		15 VDC	200 mA	84 %
THR 3-7222WI		±12 VDC	±125 mA	83 %
THR 3-7223WI	±15 VDC	±100 mA	85 %	

Pinout		
Pin	Single	Dual
1	+Vin	+Vin
11	No Pin	Common
12	-Vout	No Pin
13	+Vout	-Vout
15	No Pin	+Vout
23	-Vin	-Vin
24	-Vin	-Vin




TIM 3.5

**NEW!**

3.5 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 0.95 x 0.57 x 0.40" DIP-16 package
- I/O isolation 5000 VAC rated for 250 VAC working voltage
- 2xMOPP / BF compliant
- Low leakage < 2 μA for BF-applications
- Temperature range -40°C to 90°C.
- EMC compliance to IEC 60601-1-2 4th edition and EN 55032 class A
- 5 year product warranty


Pinout / Connection		
Pin	Single Output	Dual Output
1	-Vin (GND)	-Vin (GND)
2	Remote	Remote
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TIM 3.5-0911	4.5 - 12 VDC (9 VDC nom.)	5 VDC	700 mA	77 %
TIM 3.5-0919		9 VDC	389 mA	78 %
TIM 3.5-0912		12 VDC	292 mA	82 %
TIM 3.5-0913		15 VDC	234 mA	82 %
TIM 3.5-0915		24 VDC	146 mA	82 %
TIM 3.5-0922		±12 VDC	146 mA	82 %
TIM 3.5-0923	±15 VDC	117 mA	81 %	
TIM 3.5-1211	9 - 18 VDC (12 VDC nom.)	5 VDC	700 mA	79 %
TIM 3.5-1219		9 VDC	389 mA	79 %
TIM 3.5-1212		12 VDC	292 mA	82 %
TIM 3.5-1213		15 VDC	234 mA	82 %
TIM 3.5-1215		24 VDC	146 mA	82 %
TIM 3.5-1222		±12 VDC	146 mA	82 %
TIM 3.5-1223	±15 VDC	117 mA	82 %	
TIM 3.5-2411	18 - 36 VDC (24 VDC nom.)	5 VDC	700 mA	79 %
TIM 3.5-2419		9 VDC	389 mA	80 %
TIM 3.5-2412		12 VDC	292 mA	83 %
TIM 3.5-2413		15 VDC	234 mA	83 %
TIM 3.5-2415		24 VDC	146 mA	82 %
TIM 3.5-2422		±12 VDC	146 mA	82 %
TIM 3.5-2423	±15 VDC	117 mA	82 %	
TIM 3.5-4811	36 - 75 VDC (48 VDC nom.)	5 VDC	700 mA	79 %
TIM 3.5-4819		9 VDC	389 mA	80 %
TIM 3.5-4812		12 VDC	292 mA	82 %
TIM 3.5-4813		15 VDC	234 mA	82 %
TIM 3.5-4815		24 VDC	146 mA	82 %
TIM 3.5-4822		±12 VDC	146 mA	82 %
TIM 3.5-4823	±15 VDC	117 mA	82 %	

TRI 3

**NEW!**

3.5 Watt




- 1.25 x 0.80 x 0.41" DIP-24 package
- Reinforced I/O-isolation 7071 VDC rated for 1000 VAC working voltage
- Isolation peak voltage 9000 VDC (1s)
- Common Mode Transient Immunity (dv/dt) 15 kV/μs
- Temperature range -40 to +90°C
- no-load power 96 - 192 mW
- Internal EN 55032 class A filter
- High efficiency up to 87%
- 2:1 input voltage range
- Protection against overload, overvoltage and short circuit
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	No pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRI 3-0511	4.5 - 9 VDC (5 VDC nom.)	5 VDC	700 mA	82 %
TRI 3-0512		12 VDC	290 mA	83 %
TRI 3-0513		15 VDC	235 mA	84 %
TRI 3-0515		24 VDC	146 mA	83 %
TRI 3-0522		±12 VDC	145 mA	84 %
TRI 3-0523		±15 VDC	115 mA	84 %
TRI 3-1211	9 - 18 VDC (12 VDC nom.)	5 VDC	700 mA	82 %
TRI 3-1212		12 VDC	290 mA	86 %
TRI 3-1213		15 VDC	235 mA	87 %
TRI 3-1215		24 VDC	146 mA	86 %
TRI 3-1222		±12 VDC	145 mA	87 %
TRI 3-1223		±15 VDC	115 mA	87 %
TRI 3-2411	18 - 36 VDC (24 VDC nom.)	5 VDC	700 mA	82 %
TRI 3-2412		12 VDC	290 mA	85 %
TRI 3-2413		15 VDC	235 mA	87 %
TRI 3-2415		24 VDC	146 mA	86 %
TRI 3-2422		±12 VDC	145 mA	87 %
TRI 3-2423		±15 VDC	115 mA	86 %
TRI 3-4811	36 - 75 VDC (48 VDC nom.)	5 VDC	700 mA	82 %
TRI 3-4812		12 VDC	290 mA	85 %
TRI 3-4813		15 VDC	235 mA	85 %
TRI 3-4815		24 VDC	146 mA	83 %
TRI 3-4822		±12 VDC	145 mA	84 %
TRI 3-4823		±15 VDC	115 mA	84 %

**TDN 5WI** **5 Watt**




- 0.52 x 0.36 x 0.39" DIP-8 package
- Ultra-wide 4 : 1 input range
- I/O-isolation 1600 VDC
- Fully regulated outputs
- Temperature range -40°C to +75°C
- Short circuit protection
- Remote On/Off
- 3 year product warranty
- Designed to meet UL 62368-1
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
4	On/Off	On/Off
5	no con.	-Vout
6	-Vout	Common
7	+Vout	+Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TDN 5-0910WI	4.5 - 13.2 VDC (9 VDC nominal)	3.3 VDC	1000 mA	76 %
TDN 5-0911WI		5.0 VDC	1000 mA	80 %
TDN 5-0919WI		9.0 VDC	555 mA	81 %
TDN 5-0912WI		12 VDC	420 mA	83 %
TDN 5-0913WI		15 VDC	333 mA	83 %
TDN 5-0915WI		24 VDC	210 mA	83 %
TDN 5-0921WI		± 5.0 VDC	±500 mA	80 %
TDN 5-0922WI		±12 VDC	±210 mA	83 %
TDN 5-0923WI		±15 VDC	±168 mA	83 %
TDN 5-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	1000 mA	76 %
TDN 5-2411WI		5.0 VDC	1000 mA	80 %
TDN 5-2419WI		9.0 VDC	555 mA	81 %
TDN 5-2412WI		12 VDC	420 mA	83 %
TDN 5-2413WI		15 VDC	333 mA	83 %
TDN 5-2415WI		24 VDC	210 mA	83 %
TDN 5-2421WI		± 5.0 VDC	±500 mA	80 %
TDN 5-2422WI		±12 VDC	±210 mA	83 %
TDN 5-2423WI		±15 VDC	±168 mA	84 %
TDN 5-4810WI	18 - 75 VDC (48 VDC nominal)	3.3 VDC	1000 mA	76 %
TDN 5-4811WI		5.0 VDC	1000 mA	81 %
TDN 5-4819WI		9.0 VDC	555 mA	81 %
TDN 5-4812WI		12 VDC	420 mA	83 %
TDN 5-4813WI		15 VDC	333 mA	83 %
TDN 5-4815WI		24 VDC	210 mA	83 %
TDN 5-4821WI		± 5.0 VDC	±500 mA	80 %
TDN 5-4822WI		±12 VDC	±210 mA	83 %
TDN 5-4823WI		±15 VDC	±168 mA	84 %

**TEL 5** **5 Watt**




- 1.25 x 0.80 x 0.41" DIP-24 package
- Wide 2:1 input range
- High power density
- High efficiency up to 86%
- Regulated outputs
- I/O isolation 1500 VDC
- EN 55032, Class A and FCC level A without external components
- Indefinite short-circuit protection
- High reliability, MTBF >1 Mio. h
- Lead free design, RoHS compliant
- 3 year product warranty

Pinout		
Pin	Single	Dual
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	No con.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEL 5-1210	9 - 18 VDC (nominal 12 VDC)	3.3 VDC	1200 mA	77 %
TEL 5-1211		5 VDC	1000 mA	81 %
TEL 5-1212		12 VDC	500 mA	84 %
TEL 5-1222		±12 VDC	±250 mA	84 %
TEL 5-1223		±15 VDC	±200 mA	84 %
TEL 5-2410	18 - 36 VDC (nominal 24 VDC)	3.3 VDC	1200 mA	79 %
TEL 5-2411		5 VDC	1000 mA	83 %
TEL 5-2412		12 VDC	500 mA	86 %
TEL 5-2422		±12 VDC	±250 mA	86 %
TEL 5-2423		±15 VDC	±200 mA	86 %

TVN 5WI

5 Watt




- 1.26 x 0.79 x 0.40" DIP-24 Package
- Ultra low ripple and noise 10 mVp-p typ.
- 6-side shielded DIP-24 metal package
- Input filter to meet EN 55032, class B
- Ultra-wide 4:1 input voltage range
- Temperature range -40°C to +90°C
- Undervoltage lockout
- I/O isolation 1600 VDC
- Adjustable output voltage
- No minimum load required
- Remote On/Off
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	
2	+Vin (Vcc)	
3	Case	
10	No pin	Common
11	No pin	+Vout 1
12	Case	
13	TRIM	
14	-Vout	-Vout 2
15	+Vout	Common
22	Remote On / Off	
23	-Vin	
24	-Vin	

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TVN 5-0910WI	4.5 - 12 VDC (9 VDC nominal)	3.3 VDC	1515 mA	79 %
TVN 5-0911WI		5.0 VDC	1000 mA	82 %
TVN 5-0912WI		12 VDC	416 mA	87 %
TVN 5-0913WI		15 VDC	333 mA	87 %
TVN 5-0915WI		24 VDC	208 mA	88 %
TVN 5-0921WI		±5.0 VDC	±500 mA	84 %
TVN 5-0922WI		±12 VDC	±208 mA	85 %
TVN 5-0923WI		±15 VDC	±166 mA	86 %
TVN 5-0925WI		±24 VDC	±104 mA	87 %
TVN 5-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	1515 mA	81 %
TVN 5-2411WI		5.0 VDC	1000 mA	83 %
TVN 5-2412WI		12 VDC	416 mA	88 %
TVN 5-2413WI		15 VDC	333 mA	88 %
TVN 5-2415WI		24 VDC	208 mA	89 %
TVN 5-2421WI		±5.0 VDC	±500 mA	84 %
TVN 5-2422WI		±12 VDC	±208 mA	85 %
TVN 5-2423WI		±15 VDC	±166 mA	86 %
TVN 5-2425WI		±24 VDC	±104 mA	87 %
TVN 5-4810WI	18 - 75 VDC (48 VDC nominal)	3.3 VDC	1515 mA	80 %
TVN 5-4811WI		5.0 VDC	1000 mA	83 %
TVN 5-4812WI		12 VDC	416 mA	86 %
TVN 5-4813WI		15 VDC	333 mA	87 %
TVN 5-4815WI		24 VDC	208 mA	88 %
TVN 5-4821WI		±5.0 VDC	±500 mA	83 %
TVN 5-4822WI		±12 VDC	±208 mA	85 %
TVN 5-4823WI		±15 VDC	±166 mA	86 %
TVN 5-4825WI		±24 VDC	±104 mA	87 %

TEN 6N

6 Watt




- 1.25 x 0.80 x 0.40" DIP-24 package
- 2:1 input voltage range
- High efficiency
- Temperature range -40°C to +85°C
- No minimum load required
- Input filter meets EN 55032, class A
- Overload protection
- I/O-isolation 1500 VDC
- DIP-24 plastic package
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	No function	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 6-1210N	9 - 18 VDC (12 VDC nominal)	3.3 VDC	1200 mA	75 %
TEN 6-1211N		5 VDC	1200 mA	78 %
TEN 6-1212N		12 VDC	500 mA	82 %
TEN 6-1213N		15 VDC	400 mA	82 %
TEN 6-1215N		24 VDC	250 mA	84 %
TEN 6-1221N		±5 VDC	±500 mA	78 %
TEN 6-1222N		±12 VDC	±250 mA	82 %
TEN 6-1223N		±15 VDC	±200 mA	82 %
TEN 6-2410N		18 - 36 VDC (24 VDC nominal)	3.3 VDC	1200 mA
TEN 6-2411N	5 VDC		1200 mA	80 %
TEN 6-2412N	12 VDC		500 mA	84 %
TEN 6-2413N	15 VDC		400 mA	84 %
TEN 6-2415N	24 VDC		250 mA	84 %
TEN 6-2421N	±5 VDC		±500 mA	80 %
TEN 6-2422N	±12 VDC		±250 mA	84 %
TEN 6-2423N	±15 VDC		±200 mA	84 %
TEN 6-4810N	36 - 75 VDC (48 VDC nominal)		3.3 VDC	1200 mA
TEN 6-4811N		5 VDC	1200 mA	80 %
TEN 6-4812N		12 VDC	500 mA	84 %
TEN 6-4813N		15 VDC	400 mA	84 %
TEN 6-4815N		24 VDC	250 mA	84 %
TEN 6-4821N		±5 VDC	±500 mA	80 %
TEN 6-4822N		±12 VDC	±250 mA	84 %
TEN 6-4823N		±15 VDC	±200 mA	84 %

TEN 6WIN 6 Watt




- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultra-wide 4 : 1 input range
- High efficiency
- Temperature range -40°C to +85°C
- No minimum load required
- 1500 VDC I/O Isolation
- 3000 VDC I/O isolation (HI option)
- Input filter meets EN 55032, class A
- Overload protection
- DIP-24 plastic package
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	No function	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TEN 6-2410WIN	9 - 36 VDC (24 VDC nominal)	3.3 VDC	1200 mA	77 %	
TEN 6-2411WIN		5 VDC	1200 mA	80 %	
TEN 6-2412WIN		12 VDC	500 mA	84 %	
TEN 6-2413WIN		15 VDC	400 mA	84 %	
TEN 6-2415WIN		24 VDC	250 mA	84 %	
TEN 6-2421WIN		±5 VDC	±500 mA	80 %	
TEN 6-2422WIN		±12 VDC	±250 mA	84 %	
TEN 6-2423WIN		±15 VDC	±200 mA	84 %	
TEN 6-4810WIN		18 - 75 VDC (48 VDC nominal)	3.3 VDC	1200 mA	77 %
TEN 6-4811WIN			5 VDC	1200 mA	80 %
TEN 6-4812WIN	12 VDC		500 mA	84 %	
TEN 6-4813WIN	15 VDC		400 mA	84 %	
TEN 6-4815WIN	24 VDC		250 mA	84 %	
TEN 6-4821WIN	±5 VDC		±500 mA	80 %	
TEN 6-4822WIN	±12 VDC		±250 mA	84 %	
TEN 6-4823WIN	±15 VDC		±200 mA	84 %	

THM 6 6 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 1.25 x 0.80 x 0.40" DIP-24 package
- Wide 2:1 input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current < 2 μA
- Operating temp.: -40°C to 90°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 3 year product warranty

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	Mo pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)


Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
THM 6-0510	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	1800 mA	82 %	
THM 6-0511		5 VDC	1200 mA	86 %	
THM 6-0512		12 VDC	500 mA	86 %	
THM 6-0513		15 VDC	400 mA	88 %	
THM 6-0515		24 VDC	250 mA	87 %	
THM 6-0521		±5 VDC	600 mA	84 %	
THM 6-0522		±12 VDC	250 mA	87 %	
THM 6-0523		±15 VDC	200 mA	88 %	
THM 6-1210		9 - 18 VDC (12 VDC nom.)	3.3 VDC	1800 mA	84 %
THM 6-1211			5 VDC	1200 mA	86 %
THM 6-1212	12 VDC		500 mA	89 %	
THM 6-1213	15 VDC		400 mA	89 %	
THM 6-1215	24 VDC		250 mA	89 %	
THM 6-1221	±5 VDC		600 mA	85 %	
THM 6-1222	±12 VDC		250 mA	89 %	
THM 6-1223	±15 VDC		200 mA	88 %	
THM 6-2410	18 - 36 VDC (24 VDC nom.)		3.3 VDC	1800 mA	83 %
THM 6-2411			5 VDC	1200 mA	86 %
THM 6-2412		12 VDC	500 mA	89 %	
THM 6-2413		15 VDC	400 mA	89 %	
THM 6-2415		24 VDC	250 mA	89 %	
THM 6-2421		±5 VDC	600 mA	85 %	
THM 6-2422		±12 VDC	250 mA	89 %	
THM 6-2423		±15 VDC	200 mA	89 %	
THM 6-4810		36 - 75 VDC (48 VDC nom.)	3.3 VDC	1800 mA	83 %
THM 6-4811			5 VDC	1200 mA	87 %
THM 6-4812	12 VDC		500 mA	88 %	
THM 6-4813	15 VDC		400 mA	89 %	
THM 6-4815	24 VDC		250 mA	88 %	
THM 6-4821	±5 VDC		600 mA	85 %	
THM 6-4822	±12 VDC		250 mA	88 %	
THM 6-4823	±15 VDC		200 mA	87 %	



THM 6WI

6 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultrawide 4:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF Compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current < 2 μA
- Operating temp.: -40°C to 90°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Pinout / Connection		
Pin	Single	Dual
1	No pin*/Remote	No pin*/Remote
2	-Vin (GND)	-Vin (GND)
10	No pin*/Trim	No pin*/Trim
11	No pin/NC **	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 6-0510WI THM 6-0511WI THM 6-0512WI THM 6-0513WI THM 6-0515WI	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	1800 mA	82 %
		5 VDC	1200 mA	86 %
		12 VDC	500 mA	86 %
		15 VDC	400 mA	88 %
		24 VDC	250 mA	87 %
THM 6-0521WI THM 6-0522WI THM 6-0523WI	±5 VDC ±12 VDC ±15 VDC	600 mA	84 %	
		250 mA	87 %	
		200 mA	88 %	
THM 6-2410WI THM 6-2411WI THM 6-2412WI THM 6-2413WI THM 6-2415WI THM 6-2421WI THM 6-2422WI THM 6-2423WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	1800 mA	83 %
		5 VDC	1200 mA	86 %
		12 VDC	500 mA	89 %
		15 VDC	400 mA	89 %
		24 VDC	250 mA	89 %
		±5 VDC	600 mA	85 %
		±12 VDC	250 mA	89 %
		±15 VDC	200 mA	89 %
THM 6-4810WI THM 6-4811WI THM 6-4812WI THM 6-4813WI THM 6-4815WI THM 6-4821WI THM 6-4822WI THM 6-4823WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	1800 mA	83 %
		5 VDC	1200 mA	87 %
		12 VDC	500 mA	88 %
		15 VDC	400 mA	89 %
		24 VDC	250 mA	88 %
		±5 VDC	600 mA	85 %
		±12 VDC	250 mA	88 %
		±15 VDC	200 mA	87 %

NC: No connection


\* If Remote or Trim is not selected there is no pin on corresponding number.

\*\* If Trim is selected there is no pin on the corresponding pin number.

TRI 6

NEW!

6 Watt




- 1.25 x 0.80 x 0.40" DIP-24 package
- Reinforced I/O-isolation 7071 VDC rated for 1000 VAC working voltage
- Peak voltage 9000 VDC (1s)
- Common Mode Transient Immunity (dv/dt) 15 kV/μs
- Temperature range -40 to +85°C
- No-load power 120 - 240 mW
- Internal EN 55032 class A filter
- High efficiency up to 89%
- 2:1 input voltage range: Protection against overload, overvoltage and short circuit
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	No pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRI 6-1211 TRI 6-1212 TRI 6-1213	9 - 18 VDC (12 VDC nom.)	5 VDC	1'200 mA	83 %
		12 VDC	500 mA	86 %
		15 VDC	400 mA	86 %
TRI 6-1222 TRI 6-1223	+12 VDC +15 VDC	250 mA	87 %	
		200 mA	87 %	
TRI 6-2411 TRI 6-2412 TRI 6-2413 TRI 6-2422 TRI 6-2423	18 - 36 VDC (24 VDC nom.)	5 VDC	1'200 mA	83 %
		12 VDC	500 mA	86 %
		15 VDC	400 mA	87 %
		+12 VDC	250 mA	86 %
		+15 VDC	200 mA	87 %
TRI 6-4811 TRI 6-4812 TRI 6-4813 TRI 6-4822 TRI 6-4823	36 - 75 VDC (48 VDC nom.)	5 VDC	1'200 mA	83 %
		12 VDC	500 mA	86 %
		15 VDC	400 mA	89 %
		+12 VDC	250 mA	87 %
		+15 VDC	200 mA	88 %

TEL 8 8 Watt




- 0.95 x 0.55 x 0.33" DIP-16 package
- Temperature range -40°C to +80°C
- Wide 2:1 input range
- Built-in EN 55032 class A filter
- Protection against short circuit
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEL 8-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	1'600 mA	78 %
TEL 8-1211		5 VDC	1'600 mA	81 %
TEL 8-1212		12 VDC	665 mA	84 %
TEL 8-1213		15 VDC	535 mA	84 %
TEL 8-1215		24 VDC	335 mA	85 %
TEL 8-1222		±12 VDC	335 mA	85 %
TEL 8-1223	±15 VDC	265 mA	84 %	
TEL 8-2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	1'600 mA	78 %
TEL 8-2411		5 VDC	1'600 mA	82 %
TEL 8-2412		12 VDC	665 mA	85 %
TEL 8-2413		15 VDC	535 mA	85 %
TEL 8-2415		24 VDC	335 mA	86 %
TEL 8-2422		±12 VDC	335 mA	85 %
TEL 8-2423	±15 VDC	265 mA	86 %	
TEL 8-4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	1'600 mA	78 %
TEL 8-4811		5 VDC	1'600 mA	81 %
TEL 8-4812		12 VDC	665 mA	85 %
TEL 8-4813		15 VDC	535 mA	85 %
TEL 8-4815		24 VDC	335 mA	86 %
TEL 8-4822		±12 VDC	335 mA	86 %
TEL 8-4823	±15 VDC	265 mA	86 %	

TEL 8WI 8 Watt




- 0.95 x 0.55 x 0.33" DIP-16 package
- Temperature range -40°C to +80°C
- Ultra-wide 4:1 input range
- Built-in EN 55032 class A filter
- Protection against short circuit
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEL 8-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2000 mA	78 %
TEL 8-2411WI		5 VDC	1600 mA	82 %
TEL 8-2412WI		12 VDC	665 mA	85 %
TEL 8-2413WI		15 VDC	535 mA	85 %
TEL 8-2415WI		24 VDC	335 mA	86 %
TEL 8-2422WI		±12 VDC	335 mA	85 %
TEL 8-2423WI	±15 VDC	265 mA	86 %	
TEL 8-4810WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	2000 mA	78 %
TEL 8-4811WI		5 VDC	1600 mA	81 %
TEL 8-4812WI		12 VDC	665 mA	85 %
TEL 8-4813WI		15 VDC	535 mA	85 %
TEL 8-4815WI		24 VDC	335 mA	86 %
TEL 8-4822WI		±12 VDC	335 mA	86 %
TEL 8-4823WI	±15 VDC	265 mA	86 %	

TEN 8

8 Watt



- 1.26 x 0.80 x 0.40" DIP-24 package
- Wide 2:1 input voltage range
- Input filter meets EN 55032, class A
- Extended operating temperature range: -40°C to +85°C
- Remote On/Off
- Shielded metal casing with insulated baseplate
- Lead free design, RoHS compliant
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 8-1210	9 - 18 VDC (12 VDC nominal)	3.3 VDC	2000 mA	80 %
TEN 8-1211		5 VDC	1500 mA	83 %
TEN 8-1212		12 VDC	665 mA	88 %
TEN 8-1213		15 VDC	535 mA	87 %
TEN 8-1221		±5 VDC	±800 mA	83 %
TEN 8-1222		±12 VDC	±335 mA	87 %
TEN 8-1223	±15 VDC	±265 mA	85 %	
TEN 8-2410	18 - 36 VDC (24 VDC nominal)	3.3 VDC	2000 mA	80 %
TEN 8-2411		5 VDC	1500 mA	83 %
TEN 8-2412		12 VDC	665 mA	86 %
TEN 8-2413		15 VDC	535 mA	85 %
TEN 8-2421		±5 VDC	±800 mA	82 %
TEN 8-2422		±12 VDC	±335 mA	86 %
TEN 8-2423	±15 VDC	±265 mA	85 %	
TEN 8-4810	36 - 75 VDC (48 VDC nominal)	3.3 VDC	2000 mA	80 %
TEN 8-4811		5 VDC	1500 mA	83 %
TEN 8-4812		12 VDC	665 mA	86 %
TEN 8-4813		15 VDC	535 mA	86 %
TEN 8-4821		±5 VDC	±800 mA	85 %
TEN 8-4822		±12 VDC	±335 mA	87 %
TEN 8-4823	±15 VDC	±265 mA	87 %	

Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No con.	Common
11	No con.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

TEN 8WI

8 Watt

EN50155 /EN61373 Approved




- 1.26 x 0.80 x 0.40" DIP-24 package
- Ultra-wide 4:1 input voltage range
- High efficiency up to 88 %
- No minimum load required
- Operating temperature range -40°C to +85°C
- Remote On/Off
- Under voltage lock-out circuit
- Shielded metal case with insulated base plate
- Lead free design, RoHS compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 8-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2400 mA	85 %
TEN 8-2411WI		5 VDC	1600 mA	87 %
TEN 8-2412WI		12 VDC	666 mA	86 %
TEN 8-2413WI		15 VDC	533 mA	86 %
TEN 8-2421WI		±5 VDC	±800 mA	84 %
TEN 8-2422WI		±12 VDC	±333 mA	86 %
TEN 8-2423WI	±15 VDC	±267 mA	86 %	
TEN 8-4810WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	2400 mA	85 %
TEN 8-4811WI		5 VDC	1600 mA	87 %
TEN 8-4812WI		12 VDC	666 mA	87 %
TEN 8-4813WI		15 VDC	533 mA	88 %
TEN 8-4821WI		±5 VDC	±800 mA	84 %
TEN 8-4822WI		±12 VDC	±333 mA	87 %
TEN 8-4823WI	±15 VDC	±267 mA	87 %	
TEN 8-7210WI	43 - 160 VDC (110 VDC nom.)	3.3 VDC	2400 mA	84 %
TEN 8-7211WI		5 VDC	1600 mA	85 %
TEN 8-7212WI		12 VDC	666 mA	86 %
TEN 8-7213WI		15 VDC	533 mA	86 %
TEN 8-7221WI		±5 VDC	±800 mA	82 %
TEN 8-7222WI		±12 VDC	±333 mA	85 %
TEN 8-7223WI	±15 VDC	±267 mA	85 %	

Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	ntc	Common
11	ntc	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

TEL 10 **NEW!** 10 Watt




- 0.94 x 0.54 x 0.31" DIP-16 package
- Highest power density of 3.83 W/cm<sup>3</sup>
- 6-side shielded metal case with insulated base plate
- Wide 2:1 input voltage range
- High efficiency for low thermal loss
- Operating temperature range of -40°C to +88°C
- Built-in EN 55032 class A filter
- Current limitation and protection against short circuit
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEL 10-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	2'700 mA	79 %
TEL 10-1211		5.1 VDC	2'000 mA	82 %
TEL 10-1212		12 VDC	833 mA	86 %
TEL 10-1213		15 VDC	666 mA	87 %
TEL 10-1215		24 VDC	416 mA	87 %
TEL 10-1222		±12 VDC	416 mA	86 %
TEL 10-1223	±15 VDC	333 mA	86 %	
TEL 10-2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	2'700 mA	80 %
TEL 10-2411		5.1 VDC	2'000 mA	83 %
TEL 10-2412		12 VDC	833 mA	87 %
TEL 10-2413		15 VDC	666 mA	88 %
TEL 10-2415		24 VDC	416 mA	88 %
TEL 10-2422		±12 VDC	416 mA	87 %
TEL 10-2423	±15 VDC	333 mA	87 %	
TEL 10-4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	2'700 mA	80 %
TEL 10-4811		5.1 VDC	2'000 mA	83 %
TEL 10-4812		12 VDC	833 mA	87 %
TEL 10-4813		15 VDC	666 mA	88 %
TEL 10-4815		24 VDC	416 mA	88 %
TEL 10-4822		±12 VDC	416 mA	87 %
TEL 10-4823	±15 VDC	333 mA	87 %	

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)

TEL 10WI 10 Watt



- 0.94 x 0.54 x 0.31" DIP-16 package
- Highest power density of 3.83 W/cm<sup>3</sup>
- 6-side shielded metal case with insulated base plate
- Ultra-wide 4:1 input voltage range
- High efficiency for low thermal loss
- Operating temperature range of -40°C to +88°C
- Built-in EN 55032 class A filter
- Protection against short circuit and overload
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEL 10-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2'700 mA	80 %
TEL 10-2411WI		5.1 VDC	2'000 mA	83 %
TEL 10-2412WI		12 VDC	833 mA	87 %
TEL 10-2413WI		15 VDC	666 mA	88 %
TEL 10-2415WI		24 VDC	416 mA	88 %
TEL 10-2422WI		±12 VDC	416 mA	87 %
TEL 10-2423WI	±15 VDC	333 mA	87 %	
TEL 10-4810WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	2'700 mA	80 %
TEL 10-4811WI		5.1 VDC	2'000 mA	83 %
TEL 10-4812WI		12 VDC	833 mA	87 %
TEL 10-4813WI		15 VDC	666 mA	88 %
TEL 10-4815WI		24 VDC	416 mA	88 %
TEL 10-4822WI		±12 VDC	416 mA	87 %
TEL 10-4823WI	±15 VDC	333 mA	87 %	

Pinout		
Pin	Single	Dual
1	-Vin (GND)	-Vin (GND)
7	NC	NC
8	NC	Common
9	+Vout	+Vout
10	-Vout	-Vout
16	+Vin (Vcc)	+Vin (Vcc)



THD 10N

10 Watt





Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THD 10-1210N	9 - 18 VDC (12 VDC nominal)	3.3 VDC	2700 mA	86 %
THD 10-1211N		5.1 VDC	2000 mA	85 %
THD 10-1212N		12 VDC	833 mA	88 %
THD 10-1213N		15 VDC	666 mA	89 %
THD 10-1222N		±12 VDC	±416 mA	88 %
THD 10-1223N		±15 VDC	±333 mA	89 %
THD 10-2410N	18 - 36 VDC (24 VDC nominal)	3.3 VDC	2700 mA	86 %
THD 10-2411N		5.1 VDC	2000 mA	85 %
THD 10-2412N		12 VDC	833 mA	89 %
THD 10-2413N		15 VDC	666 mA	89 %
THD 10-2422N		±12 VDC	±416 mA	88 %
THD 10-2423N		±15 VDC	±333 mA	89 %
THD 10-4810N	36 - 75 VDC (48 VDC nominal)	3.3 VDC	2700 mA	86 %
THD 10-4811N		5.1 VDC	2000 mA	85 %
THD 10-4812N		12 VDC	833 mA	87 %
THD 10-4813N		15 VDC	666 mA	88 %
THD 10-4822N		±12 VDC	±416 mA	87 %
THD 10-4823N		±15 VDC	±333 mA	88 %

- 1.25 x 0.8 x 0.4" DIP-24 Package
- Wide 2:1 input voltage range
- EN 55032, class A
- High efficiency up to 89%
- Temperature range -40°C to +85°C
- No minimum load required
- I/O isolation 1500 VDC
- Overload protection
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	No function	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

THD 10WIN

10 Watt




Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THD 10-2410WIN	9 - 36 VDC (24 VDC nominal)	3.3 VDC	2700 mA	86 %
THD 10-2411WIN		5.1 VDC	2000 mA	85 %
THD 10-2412WIN		12 VDC	833 mA	87 %
THD 10-2413WIN		15 VDC	666 mA	87 %
THD 10-2415WIN		24 VDC	416 mA	87 %
THD 10-2422WIN		±12 VDC	±416 mA	87 %
THD 10-2423WIN	±15 VDC	±333 mA	87 %	
THD 10-4810WIN	18 - 75 VDC (48 VDC nominal)	3.3 VDC	2700 mA	86 %
THD 10-4811WIN		5.1 VDC	2000 mA	85 %
THD 10-4812WIN		12 VDC	833 mA	87 %
THD 10-4813WIN		15 VDC	666 mA	87 %
THD 10-4815WIN		24 VDC	416 mA	87 %
THD 10-4822WIN		±12 VDC	±416 mA	87 %
THD 10-4823WIN	±15 VDC	±333 mA	87 %	

- 1.25 x 0.8 x 0.4" DIP-24 Package
- Ultra wide 4:1 input voltage range
- EN 55032 class A
- High efficiency up to 87%
- Temperature range -40°C to +85°C
- No minimum load required
- I/O isolation 1500 VDC
- Overload protection
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	No pin	Common
11	No function	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

**THL 10** **10 Watt**




- 1.00 x 1.00 x 0.40" package
- Metal case + isolated baseplate
- Wide 2:1 input voltage ranges
- Temp. range -40°C to +80°C and up to +85°C with heat-sink
- I/O isolation voltage 1500 VDC
- Input filter meets EN 55032 class A without external components
- Cost optimized design
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+ Vout	+ Vout
4	No pin	Common
5	-Vout	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THL 10-1210	9 - 18 VDC (12 VDC nominal)	3.3 VDC	2500 mA	82 %
THL 10-1211		5.1 VDC	2000 mA	85 %
THL 10-1212		12 VDC	830 mA	87 %
THL 10-1213		15 VDC	670 mA	88 %
THL 10-1221		±5.0 VDC	±1000 mA	84 %
THL 10-1222		±12 VDC	±416 mA	87 %
THL 10-1223	±15 VDC	±333 mA	87 %	
THL 10-2410	18 - 36 VDC (24 VDC nominal)	3.3 VDC	2500 mA	83 %
THL 10-2411		5.1 VDC	2000 mA	85 %
THL 10-2412		12 VDC	830 mA	87 %
THL 10-2413		15 VDC	670 mA	89 %
THL 10-2421		±5.0 VDC	±1000 mA	85 %
THL 10-2422		±12 VDC	±416 mA	88 %
THL 10-2423	±15 VDC	±333 mA	89 %	
THL 10-4810	36 - 75 VDC (48 VDC nominal)	3.3 VDC	2500 mA	83 %
THL 10-4811		5.1 VDC	2000 mA	85 %
THL 10-4812		12 VDC	830 mA	89 %
THL 10-4813		15 VDC	670 mA	89 %
THL 10-4821		±5.0 VDC	±1000 mA	86 %
THL 10-4822		±12 VDC	±416 mA	87 %
THL 10-4823	±15 VDC	±333 mA	88 %	

**THM 10** **10 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 1.25 x 0.80 x 0.40" DIP-24 package
- Wide 2:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current < 2 μA
- Operating temp.: -40°C to 90°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	No pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 10-0510	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	2500 mA	80 %
THM 10-0511		5 VDC	2000 mA	84 %
THM 10-0512		12 VDC	830 mA	87 %
THM 10-0513		15 VDC	670 mA	87 %
THM 10-0515		24 VDC	416 mA	86 %
THM 10-0521		±5 VDC	1000 mA	83 %
THM 10-0522	±12 VDC	416 mA	86 %	
THM 10-0523	±15 VDC	333 mA	87 %	
THM 10-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	2500 mA	83 %
THM 10-1211		5 VDC	2000 mA	86 %
THM 10-1212		12 VDC	830 mA	88 %
THM 10-1213		15 VDC	670 mA	89 %
THM 10-1215		24 VDC	416 mA	89 %
THM 10-1221		±5 VDC	1000 mA	84 %
THM 10-1222	±12 VDC	416 mA	89 %	
THM 10-1223	±15 VDC	333 mA	88 %	
THM 10-2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	2500 mA	83 %
THM 10-2411		5 VDC	2000 mA	87 %
THM 10-2412		12 VDC	830 mA	89 %
THM 10-2413		15 VDC	670 mA	89 %
THM 10-2415		24 VDC	416 mA	89 %
THM 10-2421		±5 VDC	1000 mA	85 %
THM 10-2422	±12 VDC	416 mA	89 %	
THM 10-2423	±15 VDC	333 mA	88 %	
THM 10-4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	2500 mA	83 %
THM 10-4811		5 VDC	2000 mA	87 %
THM 10-4812		12 VDC	830 mA	89 %
THM 10-4813		15 VDC	670 mA	89 %
THM 10-4815		24 VDC	416 mA	89 %
THM 10-4821		±5 VDC	1000 mA	85 %
THM 10-4822	±12 VDC	416 mA	88 %	
THM 10-4823	±15 VDC	333 mA	88 %	


THM 10WI

10 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultrawide 4:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current < 2 μA
- Operating temp.: -40°C to 90°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty



Pinout / Connection		
Pin	Single	Dual
1	No pin*/Remote	No pin*/Remote
2	-Vin (GND)	NC -Vin (GND)
10	No pin*/Trim	No pin*/Trim
11	NC	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 10-0510WI	4.5 - 9 VDC (5 VDC nom.)	3.3 VDC	2500 mA	80 %
THM 10-0511WI		5 VDC	2000 mA	84 %
THM 10-0512WI		12 VDC	830 mA	87 %
THM 10-0513WI		15 VDC	670 mA	87 %
THM 10-0515WI		24 VDC	416 mA	86 %
THM 10-0521WI		±5 VDC	1000 mA	83 %
THM 10-0522WI		±12 VDC	416 mA	86 %
THM 10-0523WI	±15 VDC	333 mA	87 %	
THM 10-2410WI	9 - 36 VDC (24 VDC nom.)	3.3 VDC	2500 mA	83 %
THM 10-2411WI		5 VDC	2000 mA	87 %
THM 10-2412WI		12 VDC	830 mA	89 %
THM 10-2413WI		15 VDC	670 mA	89 %
THM 10-2415WI		24 VDC	416 mA	89 %
THM 10-2421WI		±5 VDC	1000 mA	85 %
THM 10-2422WI		±12 VDC	416 mA	89 %
THM 10-2423WI	±15 VDC	333 mA	88 %	
THM 10-4810WI	18 - 75 VDC (48 VDC nom.)	3.3 VDC	2500 mA	83 %
THM 10-4811WI		5 VDC	2000 mA	87 %
THM 10-4812WI		12 VDC	830 mA	89 %
THM 10-4813WI		15 VDC	670 mA	89 %
THM 10-4815WI		24 VDC	416 mA	89 %
THM 10-4821WI		±5 VDC	1000 mA	85 %
THM 10-4822WI		±12 VDC	416 mA	88 %
THM 10-4823WI	±15 VDC	333 mA	88 %	

NC: No connection

\* If Remote or Trim is not selected there is no pin on corresponding number.

THN 10WIR


NEW!

10 Watt

EN50155 /EN61373 Approved




- 1.00 x 1.00 x 0.40" package
- Ultra-wide 4:1 input voltage range
- Qualification for fire behaviour according to EN 45545-2
- I/O-isolation 3'000 VDC
- High efficiency up to 90%
- Temperature range -40°C to +90°C
- Under-voltage lock out circuit
- Adjustable output voltage & Remote On/Off
- 3 year product warranty



Pinout / Connection		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Ctrl	Ctrl
4	+Vout	+Vout
5	Trim	Common
6	-Vout	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 10-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	3000 mA	87 %
THN 10-2411WIR		5 VDC	2000 mA	89 %
THN 10-2412WIR		12 VDC	830 mA	89 %
THN 10-2413WIR		15 VDC	670 mA	90 %
THN 10-2415WIR		24 VDC	420 mA	90 %
THN 10-2421WIR		±5 VDC	±1000 mA	86 %
THN 10-2422WIR		±12 VDC	±416 mA	89 %
THN 10-2423WIR	±15 VDC	±333 mA	89 %	
THN 10-2425WIR	±24 VDC	±210 mA	90 %	
THN 10-4810WIR	18 - 75 VDC (48 VDC nom.)	3.3 VDC	3000 mA	87 %
THN 10-4811WIR		5 VDC	2000 mA	89 %
THN 10-4812WIR		12 VDC	830 mA	89 %
THN 10-4813WIR		15 VDC	670 mA	90 %
THN 10-4815WIR		24 VDC	420 mA	90 %
THN 10-4821WIR		±5 VDC	±1000 mA	86 %
THN 10-4822WIR		±12 VDC	±416 mA	89 %
THN 10-4823WIR	±15 VDC	±333 mA	89 %	
THN 10-4825WIR	±24 VDC	±210 mA	90 %	
THN 10-7210WIR	36 - 160 VDC (110 VDC nom.)	3.3 VDC	3000 mA	87 %
THN 10-7211WIR		5 VDC	2000 mA	88 %
THN 10-7212WIR		12 VDC	830 mA	89 %
THN 10-7213WIR		15 VDC	670 mA	89 %
THN 10-7215WIR		24 VDC	420 mA	89 %
THN 10-7221WIR		±5 VDC	±1000 mA	85 %
THN 10-7222WIR		±12 VDC	±416 mA	89 %
THN 10-7223WIR	±15 VDC	±333 mA	89 %	
THN 10-7225WIR	±24 VDC	±210 mA	89 %	

**THR 10WI** **NEW - under development** **10 Watt**




- 2.00 x 1.00 x 0.43" package
- Ultra-wide 4 : 1 input range
- Reinforced I/O-isolation 3000 VAC
- Input filter meets EN 55032 Class A
- High efficiency up to 85%
- Temperature range -40°C to 90°C
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Remote On/Off	Remote On/Off
4	+Vout	+Vout
5	Trim	Common
6	-Vout	-Vout

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THR 10-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	2000 mA	84 %
THR 10-2412WI		12 VDC	835 mA	86 %
THR 10-2413WI		15 VDC	670 mA	87 %
THR 10-2415WI		24 VDC	417 mA	88 %
THR 10-2422WI		±12 VDC	±417 mA	86 %
THR 10-2423WI	±15 VDC	±335 mA	87 %	
THR 10-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	2000 mA	85 %
THR 10-4812WI		12 VDC	835 mA	87 %
THR 10-4813WI		15 VDC	670 mA	87 %
THR 10-4815WI		24 VDC	417 mA	86 %
THR 10-4822WI		±12 VDC	±417 mA	89 %
THR 10-4823WI	±15 VDC	±335 mA	88 %	
THR 10-7211WI	40 - 160 VDC (110 VDC nom.)	5 VDC	2000 mA	82 %
THR 10-7212WI		12 VDC	835 mA	85 %
THR 10-7213WI		15 VDC	670 mA	85 %
THR 10-7215WI		24 VDC	417 mA	85 %
THR 10-7222WI		±12 VDC	±417 mA	86 %
THR 10-7223WI	±15 VDC	±335 mA	86 %	

**TRI 10** **NEW!** **10 Watt**



- 1.25 x 0.80 x 0.40" DIP-24 package
- Reinforced I/O-isolation 7071 VDC rated for 1000 VAC working voltage
- Peak isolation of 9000 VDC (1s)
- Common Mode Transient Immunity (dv/dt) 15 kV/μs
- Temperature range -40 to +85°C
- No-load power 144 - 288 mW
- Internal EN 55032 class A filter
- High efficiency up to 88%
- 2:1 input voltage range: Protection against overload, overvoltage and short circuit
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	No pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRI 10-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	2'700 mA	81 %
TRI 10-1211		5.1 VDC	2'000 mA	83 %
TRI 10-1212		12 VDC	833 mA	86 %
TRI 10-1213		15 VDC	666 mA	88 %
TRI 10-1215		24 VDC	416 mA	88 %
TRI 10-1222	±12 VDC	416 mA	88 %	
TRI 10-1223	±15 VDC	333 mA	87 %	
TRI 10-2410	18 - 36 VDC (24 VDC nom.)	3.3 VDC	2'700 mA	81 %
TRI 10-2411		5.1 VDC	2'000 mA	84 %
TRI 10-2412		12 VDC	833 mA	87 %
TRI 10-2413		15 VDC	666 mA	88 %
TRI 10-2415		24 VDC	416 mA	88 %
TRI 10-2422	±12 VDC	416 mA	88 %	
TRI 10-2423	±15 VDC	333 mA	87 %	
TRI 10-4810	36 - 75 VDC (48 VDC nom.)	3.3 VDC	2'700 mA	81 %
TRI 10-4811		5.1 VDC	2'000 mA	84 %
TRI 10-4812		12 VDC	833 mA	87 %
TRI 10-4813		15 VDC	666 mA	88 %
TRI 10-4815		24 VDC	416 mA	87 %
TRI 10-4822	±12 VDC	416 mA	87 %	
TRI 10-4823	±15 VDC	333 mA	87 %	



TEL 12

**NEW - under development**

12 Watt



- 0.94 x 0.54 x 0.31" DIP-16 package
- Highest power density of 3.61 W/cm<sup>3</sup>
- Shielded metal case with insulated base plate
- Wide 2:1 input range
- High efficiency for low thermal loss
- Temperature range of -40°C to +85°C
- Built-in EN 55032 class A filter
- Protection against short circuit and overload
- 3 year product warranty


	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEL 12-1211	9 - 18VDC (12 VDC nominal)	5.1 VDC	2400 mA	83 %
TEL 12-1212		12 VDC	1000 mA	87 %
TEL 12-1213		15 VDC	800 mA	88 %
TEL 12-1215		24 VDC	500 mA	88 %
TEL 12-1222		±12 VDC	±500 mA	87 %
TEL 12-1223		±15 VDC	±400 mA	87 %
TEL 12-2411	18 - 36 VDC (24 VDC nominal)	5.1 VDC	2400 mA	83 %
TEL 12-2412		12 VDC	1000 mA	87 %
TEL 12-2413		15 VDC	800 mA	88 %
TEL 12-2415		24 VDC	500 mA	88 %
TEL 12-2422		±12 VDC	±500 mA	87 %
TEL 12-2423		±15 VDC	±400 mA	87 %
TEL 12-4811	36 - 75 VDC (48 VDC nominal)	5.1 VDC	2400 mA	83 %
TEL 12-4812		12 VDC	1000 mA	87 %
TEL 12-4813		15 VDC	800 mA	88 %
TEL 12-4815		24 VDC	500 mA	88 %
TEL 12-4822		±12 VDC	±500 mA	87 %
TEL 12-4823		±15 VDC	±400 mA	87 %

Pinout		
Pin	Single	Dual
1	-Vin	-Vin
8	NC	Common
9	+Vout.	+Vout
10	-Vout.	-Vout
16	+Vin	+Vin

TEL 12WI

**NEW - under development**

12 Watt




- 0.94 x 0.54 x 0.31" DIP-16 package
- Highest power density of 3.61 W/cm<sup>3</sup>
- Shielded metal case with insulated base plate
- Ultra-wide 4:1 input range
- High efficiency for low thermal loss
- Temperature range of -40°C to +85°C
- Built-in EN 55032 class A filter
- Protection against short circuit and overload
- 3 year product warranty

	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEL 12-2411WI	9 - 36 VDC (24 VDC nominal)	5.1 VDC	2400 mA	83 %
TEL 12-2412WI		12 VDC	1000 mA	87 %
TEL 12-2413WI		15 VDC	800 mA	88 %
TEL 12-2415WI		24 VDC	500 mA	88 %
TEL 12-2422WI		±12 VDC	±500 mA	87 %
TEL 12-2423WI		±15 VDC	±400 mA	87 %
TEL 12-4811WI	18 - 75 VDC (48 VDC nominal)	5.1 VDC	2400 mA	83 %
TEL 12-4812WI		12 VDC	1000 mA	87 %
TEL 12-4813WI		15 VDC	800 mA	88 %
TEL 12-4815WI		24 VDC	500 mA	88 %
TEL 12-4822WI		±12 VDC	±500 mA	87 %
TEL 12-4823WI		±15 VDC	±400 mA	87 %

Pinout		
Pin	Single	Dual
1	-Vin	-Vin
8	NC	Common
9	+Vout.	+Vout
10	-Vout.	-Vout
16	+Vin	+Vin

**THD 12** **12 Watt**




- 1.25 x 0.80 x 0.40" DIP-24 package
- High power density
- Wide 2:1 input range
- Very high efficiency up to 88%
- I/O isolation 1500V
- Input filter to meet EN 55032, class A
- Remote On/Off
- Under voltage lock-out circuit
- Shielded metal case with insulated Baseplate
- Continuous short-circuit protection
- Operating temp. range -40°C to +85°C (with derating)
- Lead free design, RoHS compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THD 12-1209	9 - 18 VDC (nominal 12 VDC)	2.5 VDC	3500 mA	82 %
THD 12-1210		3.3 VDC	3500 mA	84 %
THD 12-1211		5.1 VDC	2400 mA	86 %
THD 12-1212		12 VDC	1000 mA	86 %
THD 12-1222		±12 VDC	±500 mA	87 %
THD 12-1223	±15 VDC	±400 mA	87 %	
THD 12-2409	18 - 36 VDC (nominal 24 VDC)	2.5 VDC	3500 mA	83 %
THD 12-2410		3.3 VDC	3500 mA	85 %
THD 12-2411		5.1 VDC	2400 mA	87 %
THD 12-2412		12 VDC	1000 mA	87 %
THD 12-2422		±12 VDC	±500 mA	88 %
THD 12-2423	±15 VDC	±400 mA	88 %	
THD 12-4809	36 - 75 VDC (nominal 48 VDC)	2.5 VDC	3500 mA	83 %
THD 12-4810		3.3 VDC	3500 mA	85 %
THD 12-4811		5.1 VDC	2400 mA	87 %
THD 12-4812		12 VDC	1000 mA	87 %
THD 12-4822		±12 VDC	±500 mA	88 %
THD 12-4823	±15 VDC	±400 mA	88 %	

Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	ntc.	Common
11	ntc.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

**THD 12WI** **12 Watt**




- 1.25 x 0.80 x 0.40" DIP-24 package
- Ultra-wide 4:1 input range
- Very high efficiency up to 85%
- I/O isolation 1500V
- Input filter meets EN 55032A
- Remote On/Off
- Under voltage lock-out circuit
- Shielded metal case with insulated baseplate
- Continuous short-circuit protection
- Operating temp. range -40°C to +85°C
- Lead free design, RoHS compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THD 12-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	3500 mA	84 %
THD 12-2411WI		5.1 VDC	2400 mA	85 %
THD 12-2412WI		12 VDC	1000 mA	85 %
THD 12-2413WI		15 VDC	800 mA	85 %
THD 12-2421WI		±5 VDC	±1200 mA	82 %
THD 12-2422WI	±12 VDC	±500 mA	85 %	
THD 12-2423WI	±15 VDC	±400 mA	85 %	
THD 12-4810WI	18 - 75 VDC (48 VDC nominal)	3.3 VDC	3500 mA	84 %
THD 12-4811WI		5.1 VDC	2400 mA	85 %
THD 12-4812WI		12 VDC	1000 mA	85 %
THD 12-4813WI		15 VDC	800 mA	85 %
THD 12-4821WI		±5 VDC	±1200 mA	82 %
THD 12-4822WI	±12 VDC	±500 mA	85 %	
THD 12-4823WI	±15 VDC	±400 mA	85 %	

Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	ntc.	Common
11	ntc.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

THD 15N

15 Watt





- 1.25 x 0.80 x 0.40" DIP-24 package
- Shielded metal case with isolated baseplate
- Very high efficiency up to 91%
- Wide 2:1 input ranges
- No minimum load required
- EN 55032 class A without external components
- I/O isolation voltage 1500 VDC
- Operating temp. range: -40°C to +85°C
- Remote On/Off control
- Industry standard pinout
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
THD 15-1210N	9 - 18 VDC (12 VDC nominal)	3.3 VDC	4000 mA	87 %
THD 15-1211N		5.1 VDC	3000 mA	90 %
THD 15-1212N		12 VDC	1250 mA	90 %
THD 15-1213N		15 VDC	1000 mA	90 %
THD 15-1221N		±5 VDC	±1500 mA	86 %
THD 15-1222N		±12 VDC	±625 mA	90 %
THD 15-1223N	±15 VDC	±500 mA	90 %	
THD 15-2410N	18 - 36 VDC (24 VDC nominal)	3.3 VDC	4000 mA	88 %
THD 15-2411N		5.1 VDC	3000 mA	90 %
THD 15-2412N		12 VDC	1250 mA	91 %
THD 15-2413N		15 VDC	1000 mA	91 %
THD 15-2421N		±5 VDC	±1500 mA	87 %
THD 15-2422N		±12 VDC	±625 mA	90 %
THD 15-2423N	±15 VDC	±500 mA	90 %	
THD 15-4810N	36 - 75 VDC (48 VDC nominal)	3.3 VDC	4000 mA	88 %
THD 15-4811N		5.1 VDC	3000 mA	90 %
THD 15-4812N		12 VDC	1250 mA	90 %
THD 15-4813N		15 VDC	1000 mA	91 %
THD 15-4821N		±5 VDC	±1500 mA	87 %
THD 15-4822N		±12 VDC	±625 mA	90 %
THD 15-4823N	±15 VDC	±500 mA	90 %	

Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	NC	Common
11	NC.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

THD 15WIN

15 Watt



- 1.25 x 0.80 x 0.40" DIP-24 package
- Shielded metal case with isolated baseplate
- Very high efficiency up to 90%
- Ultra-wide 4:1 input ranges
- No minimum load required
- EN 55032 class A without external components
- I/O isolation voltage 1500 VDC
- Operating temp. range: -40°C to +85°C
- Remote On/Off control
- Industry standard pinout
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
THD 15-2410WIN	9 - 36 VDC (24 VDC nominal)	3.3 VDC	4000 mA	88 %
THD 15-2411WIN		5.1 VDC	3000 mA	90 %
THD 15-2412WIN		12 VDC	1250 mA	90 %
THD 15-2413WIN		15 VDC	1000 mA	90 %
THD 15-2421WIN		±5 VDC	±1500 mA	86 %
THD 15-2422WIN		±12 VDC	±625 mA	89 %
THD 15-2423WIN	±15 VDC	±500 mA	90 %	
THD 15-4810WIN	18 - 75 VDC (48 VDC nominal)	3.3 VDC	4000 mA	89 %
THD 15-4811WIN		5.1 VDC	3000 mA	89 %
THD 15-4812WIN		12 VDC	1250 mA	90 %
THD 15-4813WIN		15 VDC	1000 mA	90 %
THD 15-4821WIN		±5 VDC	±1500 mA	86 %
THD 15-4822WIN		±12 VDC	±625 mA	89 %
THD 15-4823WIN	±15 VDC	±500 mA	90 %	


Pinout		
Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-Vin (GND)	-Vin (GND)
3	-Vin (GND)	-Vin (GND)
9	NC	Common
11	NC.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

## DC/DC: Isolated / DIP Package

THL 15WI

**NEW**

15 Watt



- 1.00 x 1.00 x 0.40" metal package
- Cost efficient design
- Ultra-wide 4:1 input voltage range
- Temperature range -40 to +70 °C without derating
- Internal EN 55032 class A filter
- 1500 VDC I/O-isolation
- Protection against overload, overvoltage and short circuit
- Remote On/Off and Trim function
- Optional heatsink for increased temperature capabilities
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THL 15-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	3400 mA	86 %
THL 15-2411WI		5.0 VDC	3000 mA	88 %
THL 15-2412WI		12 VDC	1250 mA	88 %
THL 15-2413WI		15 VDC	1000 mA	89 %
THL 15-2415WI		24 VDC	625 mA	91 %
THL 15-2422WI		±12 VDC	±625 mA	89 %
THL 15-2423WI	±15 VDC	±500 mA	89 %	
THL 15-4810WI	18 - 75 VDC (48 VDC nominal)	3.3 VDC	3400 mA	86 %
THL 15-4811WI		5.0 VDC	3000 mA	88 %
THL 15-4812WI		12 VDC	1250 mA	88 %
THL 15-4813WI		15 VDC	1000 mA	89 %
THL 15-4815WI		24 VDC	625 mA	91 %
THL 15-4822WI		±12 VDC	±625 mA	90 %
THL 15-4823WI	±15 VDC	±500 mA	89 %	

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

THM 15

15 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)



- 1.60 x 1.00 x 0.40" package
- Wide 2:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current <2.5 μA
- Operating temp.: -40°C to 85°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 15-1211	9 - 18 VDC (12 VDC nom.)	5 VDC	3000 mA	89 %
THM 15-1212		12 VDC	1250 mA	89 %
THM 15-1213		15 VDC	1000 mA	89 %
THM 15-1215		24 VDC	625 mA	89 %
THM 15-1221		±5 VDC	1500 mA	86 %
THM 15-1222		±12 VDC	625 mA	89 %
THM 15-1223	±15 VDC	500 mA	89 %	
THM 15-2411	18 - 36 VDC (24 VDC nom.)	5 VDC	3000 mA	90 %
THM 15-2412		12 VDC	1250 mA	90 %
THM 15-2413		15 VDC	1000 mA	90 %
THM 15-2415		24 VDC	625 mA	90 %
THM 15-2421		±5 VDC	1500 mA	86 %
THM 15-2422		±12 VDC	625 mA	90 %
THM 15-2423	±15 VDC	500 mA	90 %	
THM 15-4811	36 - 75 VDC (48 VDC nom.)	5 VDC	3000 mA	90 %
THM 15-4812		12 VDC	1250 mA	88 %
THM 15-4813		15 VDC	1000 mA	89 %
THM 15-4815		24 VDC	625 mA	89 %
THM 15-4821		±5 VDC	1500 mA	86 %
THM 15-4822		±12 VDC	625 mA	89 %
THM 15-4823	±15 VDC	500 mA	89 %	


Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	-Vout	Common
5	Trim	-Vout
6	No pin*/Remote	No pin*/Remote



THM 15WI

15 Watt

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 1.60 x 1.00 x 0.40" package
- Ultra-Wide 4:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current <2.5 μA
- Operating temp.: -40°C to 85°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	-Vout	Common
5	Trim	-Vout
6	No pin*/Remote	No pin*/Remote

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 15-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	3000 mA	88 %
THM 15-2412WI		12 VDC	1250 mA	89 %
THM 15-2413WI		15 VDC	1000 mA	89 %
THM 15-2415WI		24 VDC	625 mA	88 %
THM 15-2421WI		±5 VDC	1500 mA	86 %
THM 15-2422WI		±12 VDC	625 mA	88 %
THM 15-2423WI		±15 VDC	500 mA	89 %
THM 15-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	3000 mA	90 %
THM 15-4812WI		12 VDC	1250 mA	88 %
THM 15-4813WI		15 VDC	1000 mA	89 %
THM 15-4815WI		24 VDC	625 mA	89 %
THM 15-4821WI		±5 VDC	1500 mA	86 %
THM 15-4822WI		±12 VDC	625 mA	89 %
THM 15-4823WI		±15 VDC	500 mA	89 %

THN 15

15 Watt




- 1.0" x 1.0" x 0.4" package
- Wide 2:1 input ranges
- Output voltage Trim
- I/O isolation voltage 1600 VDC
- Very high efficiency up to 88%
- -40°C to +85°C operating temp.
- Remote On/Off control
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+ Vout	+ Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 15-1210	9 - 18 VDC (12 VDC nominal)	3.3 VDC	4000 mA	84 %
THN 15-1211		5.0 VDC	3000 mA	88 %
THN 15-1212		12 VDC	1300 mA	86 %
THN 15-1213		15 VDC	1000 mA	88 %
THN 15-1215		24 VDC	625 mA	90 %
THN 15-1221		±5 VDC	±1500 mA	85 %
THN 15-1222		±12 VDC	±625 mA	87 %
THN 15-1223	±15 VDC	±500 mA	88 %	
THN 15-1225	±24 VDC	±315 mA	90 %	
THN 15-2410	18 - 36 VDC (24 VDC nominal)	3.3 VDC	4000 mA	86 %
THN 15-2411		5.0 VDC	3000 mA	88 %
THN 15-2412		12 VDC	1300 mA	87 %
THN 15-2413		15 VDC	1000 mA	88 %
THN 15-2415		24 VDC	625 mA	90 %
THN 15-2421		±5 VDC	±1500 mA	85 %
THN 15-2422		±12 VDC	±625 mA	88 %
THN 15-2423	±15 VDC	±500 mA	88 %	
THN 15-2425	±24 VDC	±315 mA	90 %	
THN 15-4810	36 - 75 VDC (48 VDC nominal)	3.3 VDC	4000 mA	86 %
THN 15-4811		5.0 VDC	3000 mA	88 %
THN 15-4812		12 VDC	1300 mA	88 %
THN 15-4813		15 VDC	1000 mA	88 %
THN 15-4815		24 VDC	625 mA	91 %
THN 15-4821		±5 VDC	±1500 mA	85 %
THN 15-4822		±12 VDC	±625 mA	89 %
THN 15-4823	±15 VDC	±500 mA	88 %	
THN 15-4825	±24 VDC	±315 mA	91 %	

**THN 15N** **15 Watt**




- 1.00 x 1.00 x 0.39" metal package
- Wide 2:1 input voltage
- Internal EN 55032 class A filter
- Operating temperature range -40 to +70 °C without derating
- Low no-load power 96 - 336 mW
- High efficiency up to 91%
- I/O-isolation voltage 1600 VDC
- Protection against overload, overvoltage and short circuit
- Remote On/Off and Trim function
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	Remote On/Off

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 15-1210N	9 - 18 VDC (nominal 12 VDC)	3.3 VDC	4500 mA	88 %
THN 15-1211N		5 VDC	3000 mA	90 %
THN 15-1212N		12 VDC	1300 mA	89 %
THN 15-1213N		15 VDC	1000 mA	90 %
THN 15-1215N		24 VDC	625 mA	91 %
THN 15-1221N		±5 VDC	±1500 mA	86 %
THN 15-1222N		±12 VDC	±625 mA	89 %
THN 15-1223N		±15 VDC	±500 mA	90 %
THN 15-1225N		±24 VDC	±315 mA	90 %
THN 15-2410N		18 - 36 VDC (nominal 24 VDC)	3.3 VDC	4500 mA
THN 15-2411N	5 VDC		3000 mA	90 %
THN 15-2412N	12 VDC		1300 mA	89 %
THN 15-2413N	15 VDC		1000 mA	90 %
THN 15-2415N	24 VDC		625 mA	91 %
THN 15-2421N	±5 VDC		±1500 mA	86 %
THN 15-2422N	±12 VDC		±625 mA	90 %
THN 15-2423N	±15 VDC		±500 mA	90 %
THN 15-2425N	±24 VDC	±315 mA	90 %	
THN 15-4810N	36 - 75 VDC (nominal 48 VDC)	3.3 VDC	4500 mA	87 %
THN 15-4811N		5 VDC	3000 mA	89 %
THN 15-4812N		12 VDC	1300 mA	89 %
THN 15-4813N		15 VDC	1000 mA	89 %
THN 15-4815N		24 VDC	625 mA	90 %
THN 15-4821N		±5 VDC	±1500 mA	85 %
THN 15-4822N		±12 VDC	±625 mA	89 %
THN 15-4823N		±15 VDC	±500 mA	89 %
THN 15-4825N	±24 VDC	±315 mA	89 %	

**THN 15WI** **NEW models** **15 Watt**



- 1.00 x 1.00 x 0.39" metal package
- Metal case with isolated baseplate
- Ultrawide 4:1 input ranges
- Output voltage Trim
- -A1 models have 5VDC adjustment to 6VDC for LDO Regulators
- I/O isolation voltage 1500 VDC
- Very high efficiency up to 87%
- Temp. range: -40°C to +85°C
- Remote On/Off control
- Industry standard pinout
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+ Vout	+ Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 15-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	4000 mA	86 %
THN 15-2411WI		5.0 VDC	3000 mA	86 %
THN 15-2411WI-A1		5.0 VDC *1	3000 mA	86 %
THN 15-2412WI		12 VDC	1300 mA	87 %
THN 15-2413WI		15 VDC	1000 mA	87 %
THN 15-2415WI		24 VDC	625 mA	90 %
THN 15-2421WI		±5 VDC	±1500 mA	85 %
THN 15-2422WI		±12 VDC	±625 mA	87 %
THN 15-2423WI		±15 VDC	±500 mA	88 %
THN 15-2425WI		±24 VDC (48 VDC)*2	±315 mA	91 %
THN 15-4810WI	18 - 75 VDC (48 VDC nominal)	3.3 VDC	4000 mA	86 %
THN 15-4811WI		5.0 VDC	3000 mA	87 %
THN 15-4811WI-A1		5.0 VDC*1	3000 mA	87 %
THN 15-4812WI		12 VDC	1300 mA	87 %
THN 15-4813WI		15 VDC	1000 mA	87 %
THN 15-4815WI		24 VDC	625 mA	91 %
THN 15-4821WI		±5 VDC	±1500 mA	85 %
THN 15-4822WI		±12 VDC	±625 mA	86 %
THN 15-4823WI	±15 VDC	±500 mA	87 %	
THN 15-4825WI	±24 VDC (48 VDC)*2	±315 mA	90 %	

\*1 Adjustable output up to 6 VDC, suitable for low ripple & noise applications in conjunction with an LDO line regulator  
 \*2 The outputs can also be used in serial circuit for single 48 VDC operation

THN 15WIR

15 Watt

EN50155 /EN61373 Approved



- 1.00 x 1.00 x 0.39" metal package
- Ultra-wide 4:1 input voltage range
- Qualification for fire behaviour according to EN 45545-2
- I/O-isolation 3'000 VDC
- High efficiency up to 91%
- Temperature range -40°C to +90°C
- Under-voltage lock out circuit
- Adjustable output voltage & Remote On/Off
- 3 year product warranty


Pinout / Connection		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	On/Off	On/Off

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 15-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	4500 mA	88 %
THN 15-2411WIR		5 VDC	3000 mA	89 %
THN 15-2412WIR		12 VDC	1300 mA	89 %
THN 15-2413WIR		15 VDC	1000 mA	89 %
THN 15-2415WIR		24 VDC	625 mA	90 %
THN 15-2421WIR		± 5 VDC	±1500 mA	86 %
THN 15-2422WIR		±12 VDC	±625 mA	89 %
THN 15-2423WIR		±15 VDC	±500 mA	89 %
THN 15-2425WIR		±24 VDC	±315 mA	91 %
THN 15-4810WIR		18 - 75 VDC (48 VDC nom.)	3.3 VDC	4500 mA
THN 15-4811WIR	5 VDC		3000 mA	89 %
THN 15-4812WIR	12 VDC		1300 mA	89 %
THN 15-4813WIR	15 VDC		1000 mA	89 %
THN 15-4815WIR	24 VDC		625 mA	91 %
THN 15-4821WIR	± 5 VDC		±1500 mA	86 %
THN 15-4822WIR	±12 VDC		±625 mA	90 %
THN 15-4823WIR	±15 VDC		±500 mA	89 %
THN 15-4825WIR	±24 VDC		±315 mA	90 %
THN 15-7210WIR	36 - 160 VDC (110 VDC nom.)		3.3 VDC	4500 mA
THN 15-7211WIR		5 VDC	3000 mA	89 %
THN 15-7212WIR		12 VDC	1300 mA	89 %
THN 15-7213WIR		15 VDC	1000 mA	89 %
THN 15-7215WIR		24 VDC	625 mA	90 %
THN 15-7221WIR		± 5 VDC	±1500 mA	85 %
THN 15-7222WIR		±12 VDC	±625 mA	89 %
THN 15-7223WIR		±15 VDC	±500 mA	89 %
THN 15-7225WIR		±24 VDC	±315 mA	90 %

TRI 15

NEW!

15 Watt



- 2.00 x 1.00 x 0.47" package
- Reinforced I/O-isolation 5940 VDC
- rated for 1000 VAC working voltage
- Ultra-high isolation peak voltage 8000 VDC (1s)
- Common Mode Transient Immunity (dv/dt) 15 kV/μs
- Operating temperature range -40 to +85°C
- Low no-load power consumption 240 - 480 mW
- Internal EN 55032 class A filter
- High efficiency up to 90%
- 2:1 input voltage range
- Protection against overload, overvoltage and short circuit
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRI 15-1211	9 - 18 VDC (12 VDC nom.)	5.1 VDC	3'000 mA	85 %
TRI 15-1212		12 VDC	1'250 mA	88 %
TRI 15-1213		15 VDC	1'000 mA	88 %
TRI 15-1215		24 VDC	625 mA	88 %
TRI 15-1222		±12 VDC	625 mA	88 %
TRI 15-1223	±15 VDC	500 mA	89 %	
TRI 15-2411	18 - 36 VDC (24 VDC nom.)	5.1 VDC	3'000 mA	87 %
TRI 15-2412		12 VDC	1'250 mA	88 %
TRI 15-2413		15 VDC	1'000 mA	89 %
TRI 15-2415		24 VDC	625 mA	90 %
TRI 15-2422		±12 VDC	625 mA	90 %
TRI 15-2423	±15 VDC	500 mA	89 %	
TRI 15-4811	36 - 75 VDC (48 VDC nom.)	5.1 VDC	3'000 mA	87 %
TRI 15-4812		12 VDC	1'250 mA	87 %
TRI 15-4813		15 VDC	1'000 mA	90 %
TRI 15-4815		24 VDC	625 mA	89 %
TRI 15-4822		±12 VDC	625 mA	89 %
TRI 15-4823	±15 VDC	500 mA	88 %	


Pinout		
Pin	Single Output	Dual Output
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	No pin	Common
5	-Vout	-Vout

## DC/DC: Isolated / DIP Package

### TEN 20WIR

20 Watt

EN50155 /EN61373 Approved



- 2.00 x 1.00 x 0.40" package
- Ultra-wide 4:1 input voltage range
- EN 55032 class B without external components
- High efficiency up to 89%
- No minimum load required
- Operating temperature range -40°C to +85°C
- Under voltage lock-out circuit
- Remote On/Off
- Output voltage adjustable
- Lead free design, RoHS compliant
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 20-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	4500 mA	85 %
TEN 20-2411WIR		5 VDC	4000 mA	88 %
TEN 20-2412WIR		12 VDC	1670 mA	89 %
TEN 20-2413WIR		15 VDC	1330 mA	88 %
TEN 20-2422WIR		±12 VDC	±833 mA	88 %
TEN 20-2423WIR	±15 VDC	±667 mA	99 %	
TEN 20-4810WIR	18 - 75 VDC (48 VDC nom.)	3.3 VDC	4500 mA	85 %
TEN 20-4811WIR		5 VDC	4000 mA	88 %
TEN 20-4812WIR		12 VDC	1670 mA	89 %
TEN 20-4813WIR		15 VDC	1330 mA	89 %
TEN 20-4822WIR		±12 VDC	±833 mA	88 %
TEN 20-4823WIR	±15 VDC	±667 mA	89 %	
TEN 20-7210WIR	43 - 160 VDC (110 VDC nom.)	3.3 VDC	4500 mA	85 %
TEN 20-7211WIR		5 VDC	4000 mA	87 %
TEN 20-7212WIR		12 VDC	1670 mA	88 %
TEN 20-7213WIR		15 VDC	1330 mA	88 %
TEN 20-7222WIR		±12 VDC	±833 mA	88 %
TEN 20-7223WIR	±15 VDC	±667 mA	89 %	

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	Remote On/Off

### THM 20

20 Watt

IEC/EN/ES 60601-1 (2xMOPP)



- 1.60 x 1.00 x 0.40" package
- Wide 2:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current <2.5 μA
- Operating temp.: -40°C to 80°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 20-1211	9 - 18 VDC (12 VDC nom.)	5 VDC	4000 mA	89 %
THM 20-1212		12 VDC	1670 mA	89 %
THM 20-1213		15 VDC	1330 mA	89 %
THM 20-1215		24 VDC	833 mA	89 %
THM 20-1221		±5 VDC	2000 mA	86 %
THM 20-1222		±12 VDC	833 mA	89 %
THM 20-1223	±15 VDC	667 mA	89 %	
THM 20-2411	18 - 36 VDC (24 VDC nom.)	5 VDC	4000 mA	90 %
THM 20-2412		12 VDC	1670 mA	90 %
THM 20-2413		15 VDC	1330 mA	90 %
THM 20-2415		24 VDC	833 mA	90 %
THM 20-2421		±5 VDC	2000 mA	86 %
THM 20-2422		±12 VDC	833 mA	90 %
THM 20-2423	±15 VDC	667 mA	90 %	
THM 20-4811	36 - 75 VDC (48 VDC nom.)	5 VDC	4000 mA	90 %
THM 20-4812		12 VDC	1670 mA	89 %
THM 20-4813		15 VDC	1330 mA	89 %
THM 20-4815		24 VDC	833 mA	89 %
THM 20-4821		±5 VDC	2000 mA	86 %
THM 20-4822		±12 VDC	833 mA	89 %
THM 20-4823	±15 VDC	667 mA	89 %	

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	-Vout	Common
5	Trim	-Vout
6	No pin*/Remote	No pin*/Remote



**THM 20WI** **20 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 1.60 x 1.00 x 0.40" package
- Ultra-Wide 4:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current <2.5 μA
- Operating temp.: -40°C to 80°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 20-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	4000 mA	89 %
THM 20-2412WI		12 VDC	1670 mA	89 %
THM 20-2413WI		15 VDC	1330 mA	89 %
THM 20-2415WI		24 VDC	833 mA	89 %
THM 20-2421WI		±5 VDC	2000 mA	86 %
THM 20-2422WI		±12 VDC	833 mA	89 %
THM 20-2423WI	±15 VDC	667 mA	89 %	
THM 20-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	4000 mA	90 %
THM 20-4812WI		12 VDC	1670 mA	89 %
THM 20-4813WI		15 VDC	1330 mA	89 %
THM 20-4815WI		24 VDC	833 mA	89 %
THM 20-4821WI		±5 VDC	2000 mA	86 %
THM 20-4822WI		±12 VDC	833 mA	89 %
THM 20-4823WI	±15 VDC	667 mA	89 %	

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	-Vout	Common
5	Trim	-Vout
6	No pin*/Remote	No pin*/Remote

**THN 20** **20 Watt**




- 1.0" x 1.0" x 0.4" package
- Shielded metal case with isolated baseplate
- Wide 2:1 input voltage ranges
- Very high efficiency up to 90%
- Output voltage adjustable
- Remote On/Off control
- Temp. range -40°C to +75°C (85 °C with heat-sink)
- I/O isolation voltage 1500 VDC
- EN 55032 class A without external components
- No minimum load required
- Lead free design, RoHS compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 20-1210	9 - 18 VDC (12 VDC nominal)	3.3 VDC	4500 mA	86 %
THN 20-1211		5.0 VDC	4000 mA	90 %
THN 20-1212		12 VDC	1670 mA	89 %
THN 20-1213		15 VDC	1330 mA	89 %
THN 20-1222		±12 VDC	±833 mA	89 %
THN 20-1223		±15 VDC	±667 mA	89 %
THN 20-2410	18 - 36 VDC (24 VDC nominal)	3.3 VDC	4500 mA	86 %
THN 20-2411		5.0 VDC	4000 mA	90 %
THN 20-2412		12 VDC	1670 mA	90 %
THN 20-2413		15 VDC	1330 mA	90 %
THN 20-2422		±12 VDC	±833 mA	90 %
THN 20-2423		±15 VDC	±667 mA	90 %
THN 20-4810	36 - 75 VDC (48 VDC nominal)	3.3 VDC	4500 mA	86 %
THN 20-4811		5.0 VDC	4000 mA	90 %
THN 20-4812		12 VDC	1670 mA	90 %
THN 20-4813		15 VDC	1330 mA	90 %
THN 20-4822		±12 VDC	±833 mA	90 %
THN 20-4823		±15 VDC	±667 mA	90 %

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

# DC/DC: Isolated / DIP Package

## THN 20WI **NEW models** 20 Watt



- 1.0" x 1.0" x 0.4" package
- Shielded metal case with isolated baseplate
- Ultrawide 4:1 input voltage ranges
- Very high efficiency up to 90%
- Output voltage adjustable
- -A1 models have 5VDC adjustment to 6VDC for LDO Regulators"
- Remote On/Off control
- Temp. range -40°C to +75°C (85 °C with heat-sink)
- I/O isolation voltage 1500 VDC
- EN 55032 class A without external components
- No minimum load required
- Lead free design, RoHS compliant
- 3 year product warranty


Model	Input Voltage Range	Output Vnom	Imax	Efficiency
THN 20-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	4500 mA	86 %
THN 20-2411WI		5.0 VDC	4000 mA	89 %
THN 20-2411WI-A1		5.0 VDC <sup>1</sup>	4000 mA	89 %
THN 20-2412WI		12 VDC	1670 mA	89 %
THN 20-2413WI		15 VDC	1330 mA	89 %
THN 20-2415WI		24 VDC	833 mA	91 %
THN 20-2422WI		±12 VDC	±833 mA	89 %
THN 20-2423WI		±15 VDC	±667 mA	89 %
THN 20-2425WI		±24 VDC (48 VDC) <sup>2</sup>	±417 mA	91 %
THN 20-4810WI		18 - 75 VDC (48 VDC nominal)	3.3 VDC	4500 mA
THN 20-4811WI	5.0 VDC		4000 mA	89 %
THN 20-4811WI-A1	5.0 VDC <sup>1</sup>		4000 mA	89 %
THN 20-4812WI	12 VDC		1670 mA	89 %
THN 20-4813WI	15 VDC		1330 mA	90 %
THN 20-4815WI	24 VDC		833 mA	91 %
THN 20-4822WI	±12 VDC		±833 mA	89 %
THN 20-4823WI	±15 VDC		±667 mA	89 %
THN 20-4825WI	±24 VDC (48 VDC) <sup>2</sup>		±417 mA	91 %

<sup>1</sup> Adjustable output up to 6 VDC  
<sup>2</sup> The outputs can also be used in serial circuit for single 48 VDC operation

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+ Vout	+ Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

## THN 20WIR **NEW** 20 Watt

EN50155 /EN61373 Approved




- 1.00 x 1.00 x 0.40" package
- Ultra-wide 4:1 input voltage range
- Qualification for fire behaviour according to EN 45545-2
- I/O-isolation 3'000 VDC
- High efficiency up to 91%
- Temperature range -40°C to +90°C
- Under-voltage lock out circuit
- Adjustable output voltage & Remote On/Off
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	Imax	Efficiency	
THN 20-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	5500 mA	88 %	
THN 20-2411WIR		5 VDC	4000 mA	89 %	
THN 20-2412WIR		12 VDC	1670 mA	89 %	
THN 20-2413WIR		15 VDC	1330 mA	89 %	
THN 20-2415WIR		24 VDC	833 mA	91 %	
THN 20-2422WIR		±12 VDC	±833 mA	89 %	
THN 20-2423WIR		±15 VDC	±667 mA	90 %	
THN 20-2425WIR		±24 VDC	±417 mA	91 %	
THN 20-4810WIR		18 - 75 VDC (48 VDC nom.)	3.3 VDC	5500 mA	89 %
THN 20-4811WIR			5 VDC	4000 mA	90 %
THN 20-4812WIR	12 VDC		1670 mA	89 %	
THN 20-4813WIR	15 VDC		1330 mA	90 %	
THN 20-4815WIR	24 VDC		833 mA	91 %	
THN 20-4822WIR	±12 VDC		±833 mA	89 %	
THN 20-4823WIR	±15 VDC		±667 mA	90 %	
THN 20-4825WIR	±24 VDC		±417 mA	91 %	
THN 20-7210WIR	36 - 160 VDC (110 VDC nom.)		3.3 VDC	5500 mA	89 %
THN 20-7211WIR			5 VDC	4000 mA	90 %
THN 20-7212WIR		12 VDC	1670 mA	90 %	
THN 20-7213WIR		15 VDC	1330 mA	90 %	
THN 20-7215WIR		24 VDC	833 mA	91 %	
THN 20-7222WIR		±12 VDC	±833 mA	90 %	
THN 20-7223WIR		±15 VDC	±667 mA	90 %	
THN 20-7225WIR		±24 VDC	±417 mA	91 %	

Pinout / Conecction		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Ctrl	Ctrl
4	+Vout	+Vout
5	Trim	Common

**THR 20WI** **NEW - under development** **20 Watt**




Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THR 20-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	4000 mA	87 %
THR 20-2412WI		12 VDC	1670 mA	87 %
THR 20-2413WI		15 VDC	1330 mA	87 %
THR 20-2415WI		24 VDC	833 mA	87 %
THR 20-2422WI		±12 VDC	±833 mA	86 %
THR 20-2423WI	±15 VDC	±667 mA	86 %	
THR 20-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	4000 mA	87 %
THR 20-4812WI		12 VDC	1670 mA	88 %
THR 20-4813WI		15 VDC	1330 mA	88 %
THR 20-4815WI		24 VDC	833 mA	88 %
THR 20-4822WI		±12 VDC	±833 mA	87 %
THR 20-4823WI	±15 VDC	±667 mA	87 %	
THR 20-7211WI	40 - 160 VDC (110 VDC nom.)	5 VDC	4000 mA	84 %
THR 20-7212WI		12 VDC	1670 mA	86 %
THR 20-7213WI		15 VDC	1330 mA	86 %
THR 20-7215WI		24 VDC	833 mA	86 %
THR 20-7222WI		±12 VDC	±833 mA	86 %
THR 20-7223WI	±15 VDC	±667 mA	86 %	

- 2.00 x 1.00 x 0.40" package
- Ultra-wide 4 : 1 input range
- Reinforced I/O-isolation 3000 VAC
- Input filter to meet EN 55032, Class A
- High efficiency up to 85%
- Temperature range -40°C to 88°C
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Remote On/Off	Remote On/Off
4	+Vout	+Vout
5	Trim	Common
6	-Vout	-Vout

**TRI 20** **NEW!** **20 Watt**





Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TRI 20-1211	9 - 18 VDC (12 VDC nom.)	5.1 VDC	4'000 mA	85 %
TRI 20-1212		12 VDC	1'670 mA	88 %
TRI 20-1213		15 VDC	1'333 mA	88 %
TRI 20-1215		24 VDC	840 mA	89 %
TRI 20-1222		±12 VDC	840 mA	89 %
TRI 20-1223	±15 VDC	670 mA	89 %	
TRI 20-2411	18 - 36 VDC (24 VDC nom.)	5.1 VDC	4'000 mA	87 %
TRI 20-2412		12 VDC	1'670 mA	88 %
TRI 20-2413		15 VDC	1'333 mA	89 %
TRI 20-2415		24 VDC	840 mA	90 %
TRI 20-2422		±12 VDC	840 mA	90 %
TRI 20-2423	±15 VDC	670 mA	90 %	
TRI 20-4811	36 - 75 VDC (48 VDC nom.)	5.1 VDC	4'000 mA	87 %
TRI 20-4812		12 VDC	1'670 mA	88 %
TRI 20-4813		15 VDC	1'333 mA	90 %
TRI 20-4815		24 VDC	840 mA	89 %
TRI 20-4822		±12 VDC	840 mA	89 %
TRI 20-4823	±15 VDC	670 mA	90 %	

- 2.00 x 1.00 x 0.41" package
- Reinforced I/O-isolation 5940 VDC rated for 1000 VAC working voltage
- Peak voltage 8000 VDC (1s)
- Common Mode Transient Immunity (dv/dt) 15 kV/μs
- Operating temperature range -40 to +76°C
- Low no-load power consumption 240 - 480 mW
- Internal EN 55032 class A filter
- High efficiency up to 90%
- 2:1 input voltage range
- Protection against overload, overvoltage and short circuit
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	No pin	Common
5	-Vout	-Vout

**THL 25** **25 Watt**




- 1.00 x 1.00 x 0.40" package
- Shielded metal case with isolated baseplate
- Wide 2:1 input voltage ranges
- Very high efficiency up to 90%
- Output voltage adjustable
- Remote On/Off control
- Temp. range -40°C to +80°C (+85°C with heat-sink)
- I/O isolation voltage 1500 VDC
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THL 25-1210	9 - 18 VDC (12 VDC nominal)	3.3 VDC	6000 mA	87 %
THL 25-1211		5.0 VDC	5000 mA	89 %
THL 25-1212		12 VDC	2090 mA	89 %
THL 25-1213		15 VDC	1670 mA	89 %
THL 25-1222		±12 VDC	±1040 mA	89 %
THL 25-1223	±15 VDC	±840 mA	89 %	
THL 25-2410	18 - 36 VDC (24 VDC nominal)	3.3 VDC	6000 mA	88 %
THL 25-2411		5.0 VDC	5000 mA	90 %
THL 25-2412		12 VDC	2090 mA	90 %
THL 25-2413		15 VDC	1670 mA	90 %
THL 25-2422		±12 VDC	±1040 mA	89 %
THL 25-2423	±15 VDC	±840 mA	89 %	
THL 25-4810	36 - 75 VDC (48 VDC nominal)	3.3 VDC	6000 mA	88 %
THL 25-4811		5.0 VDC	5000 mA	90 %
THL 25-4812		12 VDC	2090 mA	90 %
THL 25-4813		15 VDC	1670 mA	90 %
THL 25-4822		±12 VDC	±1040 mA	89 %
THL 25-4823	±15 VDC	±840 mA	89 %	

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

**THL 25WI** **25 Watt**



- 1.00" x 1.00" x 0.40" package
- Shielded metal case with isolated baseplate
- Ultra-wide 4 : 1 input voltage ranges
- Very high efficiency up to 90%
- Output voltage adjustable
- Remote On/Off control
- Temp. range -40°C to +80°C (+85°C with heat-sink)
- I/O isolation voltage 1500 VDC
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THL 25-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	6000 mA	87 %
THL 25-2411WI		5.0 VDC	5000 mA	89 %
THL 25-2412WI		12 VDC	2090 mA	89 %
THL 25-2413WI		15 VDC	1670 mA	90 %
THL 25-2422WI		±12 VDC	±1040 mA	89 %
THL 25-2423WI	±15 VDC	±840 mA	89 %	
THL 25-4810WI	18 - 75 VDC (48 VDC nominal)	3.3 VDC	6000 mA	88 %
THL 25-4811WI		5.0 VDC	5000 mA	90 %
THL 25-4812WI		12 VDC	2090 mA	90 %
THL 25-4813WI		15 VDC	1670 mA	90 %
THL 25-4822WI		±12 VDC	±1040 mA	89 %
THL 25-4823WI	±15 VDC	±840 mA	89 %	

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	



TEN 30

30 Watt




Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 30-1210	9 - 18 VDC (nominal 12 VDC)	3.3 VDC	8000 mA	85 %
TEN 30-1211		5.1 VDC	6000 mA	87 %
TEN 30-1212		12 VDC	2500 mA	89 %
TEN 30-1213		15 VDC	2000 mA	89 %
TEN 30-1221		±5 VDC	±3000 mA	87 %
TEN 30-1222		±12 VDC	±1250 mA	87 %
TEN 30-1223	±15 VDC	±1000 mA	87 %	
TEN 30-2410	18 - 36 VDC (nominal 24 VDC)	3.3 VDC	8000 mA	87 %
TEN 30-2411		5.1 VDC	6000 mA	90 %
TEN 30-2412		12 VDC	2500 mA	91 %
TEN 30-2413		15 VDC	2000 mA	91 %
TEN 30-2421		±5 VDC	±3000 mA	90 %
TEN 30-2422		±12 VDC	±1250 mA	89 %
TEN 30-2423	±15 VDC	±1000 mA	90 %	
TEN 30-4810	36 - 75 VDC (nominal 48 VDC)	3.3 VDC	7500 mA	87 %
TEN 30-4811		5.1 VDC	6000 mA	89 %
TEN 30-4812		12 VDC	2500 mA	91 %
TEN 30-4813		15 VDC	2000 mA	91 %
TEN 30-4821		±5 VDC	±3000 mA	90 %
TEN 30-4822		±12 VDC	±1250 mA	88 %
TEN 30-4823	±15 VDC	±1000 mA	89 %	

- Smallest encapsulated 30 W converter
- 2" x 1" x 0.4" shielded metal package with isolated baseplate
- Single- and dual output models
- I/O isolation voltage 1500 VDC
- Excellent efficiency up to 91 %
- Operating temperature range -40°C to +85°C
- Remote On/Off
- Over-temperature protection
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	
4	+Vout	+Vout
5	-Vout	Common
6	Trim	-Vout

TEN 30WIN

30 Watt




Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TEN 30-2410WIN	9 - 36 VDC (24 VDC nominal)	3.3 VDC	7.5 A	86 %	
TEN 30-2411WIN		5.1 VDC	6 A	88 %	
TEN 30-2412WIN		12 VDC	2.5 A	89 %	
TEN 30-2413WIN		15 VDC	2 A	89 %	
TEN 30-2421WIN		±5 VDC	3 A	88 %	
TEN 30-2422WIN		±12 VDC	1.25 A	87 %	
TEN 30-2423WIN	±15 VDC	1 A	87 %		
TEN 30-2433WIN	18 - 75 VDC (48 VDC nominal)	3.3 / ±12 VDC	5 / 0.416 A	86 %	
TEN 30-2434WIN		3.3 / ±15 VDC	5 / 0.333 A	86 %	
TEN 30-2431WIN		5 / ±12 VDC	4 / 0.416 A	88 %	
TEN 30-2432WIN		5 / ±15 VDC	4 / 0.333 A	88 %	
TEN 30-4810WIN		18 - 75 VDC (48 VDC nominal)	3.3 VDC	7.5 A	86 %
TEN 30-4811WIN			5.1 VDC	6 A	88 %
TEN 30-4812WIN	12 VDC		2.5 A	90 %	
TEN 30-4813WIN	15 VDC		2 A	91 %	
TEN 30-4821WIN	±5 VDC		3 A	88 %	
TEN 30-4822WIN	±12 VDC		1.25 A	88 %	
TEN 30-4823WIN	±15 VDC	1 A	88 %		
TEN 30-4833WIN	18 - 75 VDC (48 VDC nominal)	3.3 / ±12 VDC	5 / 0.416 A	86 %	
TEN 30-4834WIN		3.3 / ±15 VDC	5 / 0.333 A	86 %	
TEN 30-4831WIN		5 / ±12 VDC	4 / 0.416 A	88 %	
TEN 30-4832WIN		5 / ±15 VDC	4 / 0.333 A	88 %	

- 2.00" x 1.00" x 0.40" shielded metal package with isolated baseplate
- Single- and dual output models
- I/O isolation voltage 1500 VDC
- Excellent efficiency up to 91 %
- Operating temperature range -40°C to +85°C
- Remote On/Off
- Over-temperature protection
- 3 year product warranty

Pinout			
Pin	Single	Dual	Triple
1	+Vin (Vcc)	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)	-Vin (GND)
3	Remote On/Off	Remote On/Off	Remote On/Off
4	+Vout 1	Output 1	Output 2
5	-Vout 1	Common	Output 3
6	Trim	Output 2	Common
7	No pin	No pin	Output 1

**THM 30** **30 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 2.00 x 1.00 x 0.40" package
- Wide 2:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current <2.5 μA
- Operating temp.: -40°C to 80°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 30-1211	9 - 18 VDC (12 VDC nom.)	5 VDC	6000 mA	89 %
THM 30-1212		12 VDC	2500 mA	89 %
THM 30-1213		15 VDC	2000 mA	90 %
THM 30-1215		24 VDC	1250 mA	89 %
THM 30-1221		± 5 VDC	3000 mA	86 %
THM 30-1222		±12 VDC	1250 mA	89 %
THM 30-1223	±15 VDC	1000 mA	89 %	
THM 30-2411	18 - 36 VDC (24 VDC nom.)	5 VDC	6000 mA	89 %
THM 30-2412		12 VDC	2500 mA	89 %
THM 30-2413		15 VDC	2000 mA	91 %
THM 30-2415		24 VDC	1250 mA	90 %
THM 30-2421		± 5 VDC	3000 mA	86 %
THM 30-2422		±12 VDC	1250 mA	90 %
THM 30-2423	±15 VDC	1000 mA	90 %	
THM 30-4811	36 - 75 VDC (48 VDC nom.)	5 VDC	6000 mA	89 %
THM 30-4812		12 VDC	2500 mA	89 %
THM 30-4813		15 VDC	2000 mA	90 %
THM 30-4815		24 VDC	1250 mA	89 %
THM 30-4821		± 5 VDC	3000 mA	87 %
THM 30-4822		±12 VDC	1250 mA	90 %
THM 30-4823	±15 VDC	1000 mA	90 %	

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	-Vout	Common
5	Trim	-Vout
6	No pin*/Remote	No pin*/Remote

**THM 30WI** **30 Watt**

⊕ IEC/EN/ES 60601-1 (2xMOPP)




- 2.00 x 1.00 x 0.40" package
- Ultra-Wide 4:1 Input range
- I/O isolation 5000 VAC rated for
- 250 VAC working voltage
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- Low leakage current <2.5 μA
- Operating temp.: -40°C to 80°C
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- 5 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 30-2411WI	9 - 36 VDC (24 VDC nom.)	5 VDC	6000 mA	89 %
THM 30-2412WI		12 VDC	2500 mA	89 %
THM 30-2413WI		15 VDC	2000 mA	91 %
THM 30-2415WI		24 VDC	1250 mA	90 %
THM 30-2421WI		± 5 VDC	3000 mA	86 %
THM 30-2422WI		±12 VDC	1250 mA	90 %
THM 30-2423WI	±15 VDC	1000 mA	90 %	
THM 30-4811WI	18 - 75 VDC (48 VDC nom.)	5 VDC	6000 mA	89 %
THM 30-4812WI		12 VDC	2500 mA	89 %
THM 30-4813WI		15 VDC	2000 mA	90 %
THM 30-4815WI		24 VDC	1250 mA	89 %
THM 30-4821WI		± 5 VDC	3000 mA	87 %
THM 30-4822WI		±12 VDC	1250 mA	90 %
THM 30-4823WI	±15 VDC	1000 mA	90 %	

Pinout / Connection		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	-Vout	Common
5	Trim	-Vout
6	No pin*/Remote	No pin*/Remote

THN 30

30 Watt



- 1.00 x 1.00 x 0.40" package
- Shielded metal case with isolated baseplate
- Wide 2:1 input voltage range
- Up to 92% efficiency across full load range
- Over temperature protection
- Temp. range -40°C to +80°C (85 °C with heat-sink)
- Ultra low no load input current
- Remote On/Off control
- Output voltage adjustable
- I/O isolation voltage 1500 VDC
- RoHS 2011/65/EU compliant
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 30-1210	9 - 18 VDC (12 VDC nominal)	3.3 VDC	7000 mA	86 %
THN 30-1211		5.0 VDC	6000 mA	89 %
THN 30-1212		12 VDC	2500 mA	89 %
THN 30-1213		15 VDC	2000 mA	89 %
THN 30-1215		24 VDC	1250 mA	89 %
THN 30-1222		±12 VDC	±1250 mA	89 %
THN 30-1223	±15 VDC	±1000 mA	90 %	
THN 30-2410	18 - 36 VDC (24 VDC nominal)	3.3 VDC	7000 mA	87 %
THN 30-2411		5.0 VDC	6000 mA	90 %
THN 30-2412		12 VDC	2500 mA	91 %
THN 30-2413		15 VDC	2000 mA	91 %
THN 30-2415		24 VDC	1250 mA	91 %
THN 30-2422		±12 VDC	±1250 mA	91 %
THN 30-2423	±15 VDC	±1000 mA	91 %	
THN 30-4810	36 - 75 VDC (48 VDC nominal)	3.3 VDC	7000 mA	87 %
THN 30-4811		5.0 VDC	6000 mA	89 %
THN 30-4812		12 VDC	2500 mA	90 %
THN 30-4813		15 VDC	2000 mA	91 %
THN 30-4815		24 VDC	1250 mA	91 %
THN 30-4822		±12 VDC	±1250 mA	91 %
THN 30-4823	±15 VDC	±1000 mA	92 %	

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

THN 30WI

NEW models

30 Watt



- 1.00 x 1.00 x 0.40" package
- Shielded metal case with isolated baseplate
- Ultrawide 4:1 input voltage range
- Very high efficiency across full load range
- No minimum load required
- Remote On/Off control
- -A1 models have 5VDC adjustment to 6VDC for LDO Regulators"
- Temp. range -40°C to +80°C (85 °C with heat-sink)
- Over temperature protection
- Output voltage adjustable
- I/O isolation voltage 1500 VDC
- RoHS 2011/65/EU compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THN 30-2410WI	9 - 36 VDC (24 VDC nominal)	3.3 VDC	7000 mA	86 %
THN 30-2411WI		5.0 VDC	6000 mA	89 %
THN 30-2411WI-A1		5.0 VDC <sup>*1</sup>	6000 mA	89 %
THN 30-2412WI		12 VDC	2500 mA	89 %
THN 30-2413WI		15 VDC	2000 mA	89 %
THN 30-2415WI		24 VDC	1250 mA	89 %
THN 30-2425WI <sup>*2</sup>	48 VDC	625 mA	91 %	
THN 30-2422WI	±12 VDC	±1250 mA	89 %	
THN 30-2423WI	±15 VDC	±1000 mA	91 %	
THN 30-2425WI	±24 VDC	±625 mA	91 %	
THN 30-4810WI	18 - 75 VDC (48 VDC nominal)	3.3 VDC	7000 mA	87 %
THN 30-4811WI		5.0 VDC	6000 mA	90 %
THN 30-4811WI-A1		5.0 VDC <sup>*1</sup>	6000 mA	90 %
THN 30-4812WI		12 VDC	2500 mA	90 %
THN 30-4813WI		15 VDC	2000 mA	91 %
THN 30-4815WI		24 VDC	1250 mA	91 %
THN 30-4825WI <sup>*2</sup>	48 VDC	625 mA	91 %	
THN 30-4822WI	±12 VDC	±1250 mA	91 %	
THN 30-4823WI	±15 VDC	±1000 mA	92 %	
THN 30-4825WI	±24 VDC	±625 mA	92 %	

\*1 Adjustable output up to 6 VDC

\*2 This dual ±24 VDC converter can be used as single 48 VDC converter (open common contact)

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	


## DC/DC: Isolated / DIP Package

THN 30WIR

**NEW** - under development

30 Watt

EN50155 /EN61373 Approved



- 1.00 x 1.00 x 0.40" package
- Ultra-wide 4:1 input voltage range
- Qualification for fire behaviour according to EN 45545-2
- I/O-isolation 3'000 VDC
- High efficiency up to 92%
- Operating temperature range -40°C to +90°C
- Under-voltage lock out circuit
- Adjustable output voltage & Remote On/Off
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
THN 30-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	7000 mA	88 %	
THN 30-2411WIR		5 VDC	6000 mA	89 %	
THN 30-2412WIR		12 VDC	2500 mA	89 %	
THN 30-2413WIR		15 VDC	2000 mA	89 %	
THN 30-2415WIR		24 VDC	1250 mA	90 %	
THN 30-2422WIR		±12 VDC	±1250 mA	89 %	
THN 30-2423WIR		±15 VDC	±1000 mA	91 %	
THN 30-2425WIR		±24 VDC	±625 mA	91 %	
THN 30-4810WIR		18 - 75 VDC (48 VDC nom.)	3.3 VDC	7000 mA	88 %
THN 30-4811WIR			5 VDC	6000 mA	90 %
THN 30-4812WIR	12 VDC		2500 mA	90 %	
THN 30-4813WIR	15 VDC		2000 mA	91 %	
THN 30-4815WIR	24 VDC		1250 mA	92 %	
THN 30-4822WIR	±12 VDC		±1250 mA	91 %	
THN 30-4823WIR	±15 VDC		±1000 mA	91 %	
THN 30-4825WIR	±24 VDC		±625 mA	92 %	
THN 30-7210WIR	36 - 160 VDC (110 VDC nom.)	3.3 VDC	7000 mA	88 %	
THN 30-7211WIR		5 VDC	6000 mA	90 %	
THN 30-7212WIR		12 VDC	2500 mA	90 %	
THN 30-7213WIR		15 VDC	2000 mA	90 %	
THN 30-7215WIR		24 VDC	1250 mA	91 %	
THN 30-7222WIR		±12 VDC	±1250 mA	90 %	
THN 30-7223WIR		±15 VDC	±1000 mA	90 %	
THN 30-7225WIR		±24 VDC	±625 mA	91 %	


### Pinout / Connection

Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Ctrl	Ctrl
4	+Vout	+Vout
5	Trim	Common
6	-Vout	-Vout

TEN 40E

**NEW**

40 Watt



- 2.00 x 1.00 x 0.40" package
- Developed to maximize quality in a cost efficient design
- Wide 2:1 input range
- Excellent temperature capabilities
- Operating temperature range -40 to +85°C
- 1600 VDC I/O-isolation
- Remote On/Off and Trim function
- Protection against short circuit, overvoltage and overtemperature
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TEN 40-1210E	9 - 18 VDC (12 VDC nominal)	3.3 VDC	12'200 mA	89 %	
TEN 40-1211E		5 VDC	8'000 mA	90 %	
TEN 40-1212E		12 VDC	3'333 mA	91 %	
TEN 40-1213E		15 VDC	2'666 mA	91 %	
TEN 40-1215E		24 VDC	1'666 mA	90 %	
TEN 40-1222E		±12 VDC	1'666 mA	90 %	
TEN 40-1223E		±15 VDC	1'333 mA	90 %	
TEN 40-1225E		±24 VDC	833 mA	91 %	
TEN 40-2410E		18 - 36 VDC (24 VDC nominal)	3.3 VDC	12'200 mA	90 %
TEN 40-2411E			5 VDC	8'000 mA	92 %
TEN 40-2412E	12 VDC		3'333 mA	92 %	
TEN 40-2413E	15 VDC		2'666 mA	93 %	
TEN 40-2415E	24 VDC		1'666 mA	91 %	
TEN 40-2422E	±12 VDC		1'666 mA	91 %	
TEN 40-2423E	±15 VDC		1'333 mA	91 %	
TEN 40-2425E	±24 VDC		833 mA	91 %	
TEN 40-4810E	36 - 75 VDC (48 VDC nominal)	3.3 VDC	12'200 mA	90 %	
TEN 40-4811E		5 VDC	8'000 mA	91 %	
TEN 40-4812E		12 VDC	3'333 mA	92 %	
TEN 40-4813E		15 VDC	2'666 mA	92 %	
TEN 40-4815E		24 VDC	1'666 mA	92 %	
TEN 40-4822E		±12 VDC	1'666 mA	91 %	
TEN 40-4823E		±15 VDC	1'333 mA	91 %	
TEN 40-4825E		±24 VDC	833 mA	92 %	

### Pinout / Connection


Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	
4	+Vout	+Vout
5	-Vout	Common
6	Trim	-Vout



TEN 40WIE

**NEW**

40 Watt



- 2.00 x 1.00 x 0.40" package
- Developed to maximize quality in a cost efficient design
- Ultra-wide 4:1 input range
- Excellent temperature capabilities
- Operating temperature range -40 to +85°C
- 1600 VDC I/O-isolation
- Remote On/Off and Trim function
- Protection against short circuit, overvoltage and overtemperature
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 40-2410WIE	9 - 36 VDC (24 VDC nominal)	3.3 VDC	12'200 mA	90 %
TEN 40-2411WIE		5 VDC	8'000 mA	92 %
TEN 40-2412WIE		12 VDC	3'333 mA	92 %
TEN 40-2413WIE		15 VDC	2'666 mA	93 %
TEN 40-2415WIE		24 VDC	1'666 mA	91 %
TEN 40-2422WIE		±12 VDC	1'666 mA	91 %
TEN 40-2423WIE	±15 VDC	1'333 mA	91 %	
TEN 40-2425WIE	±24 VDC	833 mA	91 %	
TEN 40-4810WIE	18 - 75 VDC (48 VDC nominal)	3.3 VDC	12'200 mA	90 %
TEN 40-4811WIE		5 VDC	8'000 mA	91 %
TEN 40-4812WIE		12 VDC	3'333 mA	92 %
TEN 40-4813WIE		15 VDC	2'666 mA	92 %
TEN 40-4815WIE		24 VDC	1'666 mA	92 %
TEN 40-4822WIE		±12 VDC	1'666 mA	91 %
TEN 40-4823WIE	±15 VDC	1'333 mA	91 %	
TEN 40-4825WIE	±24 VDC	833 mA	92 %	

Pinout / Conecction		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	
4	+Vout	+Vout
5	-Vout	Common
6	Trim	-Vout

TEN 40 WIR

40 Watt

EN50155 /EN61373 Approved




- 2.00 x 1.00 x 0.40" package
- Ultra-wide 4:1 input voltage range
- EN 50155 approval for railway applications
- Thermal shock and vibration resistant (EN 61373)
- High efficiency up to 92%
- No minimum load required
- Operating temperature range -40°C to +85°C
- Under voltage lock-out circuit
- Remote On/Off
- Output voltage adjustable
- Lead free design, RoHS compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 40-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	10'000 mA	90 %
TEN 40-2411WIR		5 VDC	8000 mA	91 %
TEN 40-2412WIR		12 VDC	3333 mA	92 %
TEN 40-2413WIR		15 VDC	2666 mA	92 %
TEN 40-2415WIR		24 VDC	1666 mA	91 %
TEN 40-2422WIR		±12 VDC	±1666 mA	90 %
TEN 40-2423WIR	±15 VDC	±1333 mA	90 %	
TEN 40-2425WIR	±24 (48*) VDC	±833 mA	91 %	
TEN 40-4810WIR	18 - 75 VDC (48 VDC nom.)	3.3 VDC	10'000 mA	90 %
TEN 40-4811WIR		5 VDC	8000 mA	91 %
TEN 40-4812WIR		12 VDC	3333 mA	92 %
TEN 40-4813WIR		15 VDC	2666 mA	92 %
TEN 40-4815WIR		24 VDC	1666 mA	91 %
TEN 40-4822WIR		±12 VDC	±1666 mA	90 %
TEN 40-4823WIR	±15 VDC	±1333 mA	90 %	
TEN 40-4825WIR	±24 (48*) VDC	±833 mA	91 %	
TEN 40-7210WIR	43 - 160 VDC (110 VDC nom.)	3.3 VDC	10'000 mA	88 %
TEN 40-7211WIR		5 VDC	8000 mA	89 %
TEN 40-7212WIR		12 VDC	3333 mA	90 %
TEN 40-7213WIR		15 VDC	2666 mA	91 %
TEN 40-7215WIR		24 VDC	1666 mA	90 %
TEN 40-7222WIR		±12 VDC	±1666 mA	89 %
TEN 40-7223WIR	±15 VDC	±1333 mA	89 %	
TEN 40-7225WIR	±24 (48*) VDC	±833 mA	91 %	

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	Remote On/Off
4	+Vout	+Vout
5	-Vout	Common
6	trim	-Vout

**THR 40WI** **NEW - under development** **40 Watt**




Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THR 40-7211WI	36 - 160 VDC (110 VDC nom.)	5 VDC	8000 mA	88 %
THR 40-7212WI		12 VDC	3330 mA	89 %
THR 40-7213WI		15 VDC	2670 mA	89 %
THR 40-7215WI		24 VDC	1670 mA	89 %
THR 40-7222WI		±12 VDC	±1670 mA	89 %
THR 40-7223WI		±15 VDC	±1330 mA	89 %

- 2.00 x 1.00 x 0.43" package
- Ultra-wide 4 : 1 input range
- Reinforced I/O-isolation 3000 VAC
- Input filter to meet EN 55032, Class A
- High efficiency up to 85%
- Temperature range -40°C to 90°C
- 3 year product warranty

Pinout		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Remote On/Off	Remote On/Off
4	+Vout	+Vout
5	-Vout	Common
6	Trim	-Vout

**TEN 50** **50 Watt**




Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 50-1210	9 - 18 VDC (nominal 12 VDC)	3.3 VDC	10000 mA	89 %
TEN 50-1211		5.0 VDC	10000 mA	90 %
TEN 50-1212		12 VDC	4170 mA	91 %
TEN 50-1213		15 VDC	3330 mA	91 %
TEN 50-1215		24 VDC	2080 mA	91 %
TEN 50-2410	18 - 36 VDC (nominal 24 VDC)	3.3 VDC	10000 mA	89 %
TEN 50-2411		5.0 VDC	10000 mA	92 %
TEN 50-2412		12 VDC	4170 mA	92 %
TEN 50-2413		15 VDC	3330 mA	92 %
TEN 50-2415		24 VDC	2080 mA	91 %
TEN 50-4810	36 - 75 VDC (nominal 48 VDC)	3.3 VDC	10000 mA	89 %
TEN 50-4811		5.0 VDC	10000 mA	92 %
TEN 50-4812		12 VDC	4170 mA	92 %
TEN 50-4813		15 VDC	3330 mA	92 %
TEN 50-4815		24 VDC	2080 mA	91 %

- 2.00 x 1.00 x 0.40" package
- Excellent efficiency up to 92 %
- Operating temperature range -40°C to +85°C
- No minimum load required
- Output voltage adjustable
- Remote On/Off
- I/O isolation 1500 VDC
- 3 year product warranty

Pinout	
Pin	Single
1	+Vin (Vcc)
2	-Vin (GND)
3	Remote On/Off
4	+Vout
5	-Vout
6	Trim

TEN 50WI

50 Watt




- 2.00 x 1.00 x 0.40" package
- Wide 4:1 input range
- Excellent efficiency up to 92 %
- Operating temperature range -40°C to +80°C
- Protection against over-temperature
- No minimum load required
- Output voltage adjustable
- Remote On/Off
- I/O isolation 1500 VDC
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 50-2410WI	9 - 36 VDC (nominal 24 VDC)	3.3 VDC	10000 mA	90 %
TEN 50-2411WI		5.0 VDC	10000 mA	91 %
TEN 50-2412WI		12 VDC	4170 mA	92 %
TEN 50-2413WI		15 VDC	3330 mA	92 %
TEN 50-2415WI		24 VDC	2080 mA	91 %
TEN 50-4810WI	18 - 75 VDC (nominal 48 VDC)	3.3 VDC	10000 mA	90 %
TEN 50-4811WI		5.0 VDC	10000 mA	91 %
TEN 50-4812WI		12 VDC	4170 mA	92 %
TEN 50-4813WI		15 VDC	3330 mA	92 %
TEN 50-4815WI		24 VDC	2080 mA	91 %

Pinout	
Pin	Single
1	+Vin (Vcc)
2	-Vin (GND)
3	Remote On/Off
4	+Vout
5	-Vout
6	Trim

TEN 60N

60 Watt




- 2.00 x 1.00 x 0.40" package
- Wide 2:1 input voltage range
- High efficiency up to 92%
- Adjustable output voltage
- No minimum load required
- Operating temperature range -40°C to +85°C
- Input filter to meet EN55032, class A
- Remote On/Off
- Under voltage lockout
- Lead free design, RoHS compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 60-1211N	9 - 18 VDC (12 VDC nominal)	5.0 VDC	12000 mA	90.5 %
TEN 60-1212N		12 VDC	5000 mA	90.5 %
TEN 60-1213N		15 VDC	4000 mA	91.5 %
TEN 60-1215N		24 VDC	2500 mA	91.5 %
TEN 60-1222N		±12 VDC	±2500 mA	90 %
TEN 60-1223N	±15 VDC	±2000 mA	90 %	
TEN 60-1225N	±24 VDC	±1250 mA	91 %	
TEN 60-2411N	18 - 36 VDC (24 VDC nominal)	5.0 VDC	12000 mA	92 %
TEN 60-2412N		12 VDC	5000 mA	92 %
TEN 60-2413N		15 VDC	4000 mA	92 %
TEN 60-2415N		24 VDC	2500 mA	92 %
TEN 60-2422N		±12 VDC	±2500 mA	90 %
TEN 60-2423N	±15 VDC	±2000 mA	90 %	
TEN 60-2425N	±24 VDC	±1250 mA	91 %	
TEN 60-4811N	36 - 75 VDC (48 VDC nominal)	5.0 VDC	12000 mA	92 %
TEN 60-4812N		12 VDC	5000 mA	92 %
TEN 60-4813N		15 VDC	4000 mA	92 %
TEN 60-4815N		24 VDC	2500 mA	92 %
TEN 60-4822N		±12 VDC	±2500 mA	91 %
TEN 60-4823N	±15 VDC	±2000 mA	91 %	
TEN 60-4825N	±24 VDC	±1250 mA	91 %	

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	
4	+Vout	+Vout
5	-Vout	Common
6	TRIM	-Vout

# DC/DC: Isolated / DIP Package

## TEN 60WIN 60 Watt




- 2.00 x 1.00 x 0.40" package
- Wide 4:1 input voltage range
- High efficiency up to 92%
- Adjustable output voltage
- No minimum load required
- Operating temperature range -40°C to +85°C
- Input filter to meet EN 55032, class A
- Remote On/Off
- Under voltage lockout
- Lead free design, RoHS compliant
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 60-2411WIN	9 - 36 VDC (24 VDC nominal)	5.0 VDC	12000 mA	92 %
TEN 60-2412WIN		12 VDC	5000 mA	92 %
TEN 60-2413WIN		15 VDC	4000 mA	92 %
TEN 60-2415WIN		24 VDC	2500 mA	92 %
TEN 60-2422WIN		±12 VDC	±2500 mA	91 %
TEN 60-2423WIN		±15 VDC	±2000 mA	91 %
TEN 60-2425WIN	±24 VDC	±1250 mA	91 %	
TEN 60-4811WIN	18 - 75 VDC (48 VDC nominal)	5.0 VDC	12000 mA	92 %
TEN 60-4812WIN		12 VDC	5000 mA	92 %
TEN 60-4813WIN		15 VDC	4000 mA	92 %
TEN 60-4815WIN		24 VDC	2500 mA	91 %
TEN 60-4822WIN		±12 VDC	±2500 mA	91 %
TEN 60-4823WIN		±15 VDC	±2000 mA	91 %
TEN 60-4825WIN	±24 VDC	±1250 mA	91 %	

Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	
4	+Vout	+Vout
5	-Vout	Common
6	TRIM	-Vout

## TEN 60WIR **NEW!** 60 Watt

EN50155 / EN61373 Approved



- 2.00 x 1.60 x 1.00" package with heatsink
- Ultra-wide 4:1 input voltage range
- Qualification for fire behaviour according to EN 45545-2
- I/O-isolation 3'000 VDC
- High efficiency up to 91%
- Full load operation from -40°C to +70°C
- Under-voltage lock out circuit
- Adjustable output voltage & Remote On/Off
- 3 year product warranty









Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEN 60-2411WIR	9 - 36 VDC	5 VDC	12 A	91 %
TEN 60-2412WIR		12 VDC	5 A	93 %
TEN 60-2413WIR		15 VDC	4 A	93 %
TEN 60-2415WIR		24 VDC	2.5 A	90.5 %
TEN 60-2418WIR		48 VDC	1.25 A	91.5 %
TEN 60-2422WIR		±12 VDC	±2.5 A	90.5 %
TEN 60-2423WIR	±15 VDC	±2 A	90.5 %	
TEN 60-2425WIR	±24 VDC	±1.25 A	91.5 %	
TEN 60-4811WIR	18 - 75 VDC	5 VDC	12 A	91.5 %
TEN 60-4812WIR		12 VDC	5 A	92.5 %
TEN 60-4813WIR		15 VDC	4 A	94 %
TEN 60-4815WIR		24 VDC	2.5 A	91.5 %
TEN 60-4818WIR		48 VDC	1.25 A	92 %
TEN 60-4822WIR		±12 VDC	±2.5 A	91.5 %
TEN 60-4823WIR	±15 VDC	±2 A	91.5 %	
TEN 60-4825WIR	±24 VDC	±1.25 A	92 %	
TEN 60-7211WIR	36 - 160 VDC	5 VDC	12 A	91 %
TEN 60-7212WIR		12 VDC	5 A	92 %
TEN 60-7213WIR		15 VDC	4 A	92 %
TEN 60-7215WIR		24 VDC	2.5 A	90.5 %
TEN 60-7218WIR		48 VDC	1.25 A	91 %
TEN 60-7222WIR		±12 VDC	±2.5 A	90.5 %
TEN 60-7223WIR	±15 VDC	±2 A	90.5 %	
TEN 60-7225WIR	±24 VDC	±1.25 A	91 %	


Pinout		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Ctrl	Ctrl
4	+Vout	+Vout
5	-Vout	Common
6	Trim	-Vout



# DC/DC: High-Power PCB Mount Brick Converters

TRACO POWER's high-power brick DC/DC converter products range in power from 40 ~ 240 watts in the industry standard quarter brick & half brick packages with either 2:1 or 4:1 input ranges.

SERIES	WATTS	DESCRIPTION	STATUS	APPS	PAGE
<b>TEP 40UIR</b>	40	1/4-Brick package, 12:1 input, 3000 VAC isolation	<b>NEW!</b>		82
<b>TEP 60UIR</b>	60	1/4-Brick package, 12:1 input, 3000 VAC isolation	<b>NEW!</b>		82
<b>THM 60WI</b>	60	2.28 × 1.45" package, 4:1 input, regulated, 5000 VAC isolation	<b>NEW!</b>		83
<b>TEP 75WI</b>	75	1/2-Brick package, 4:1 input, 2250 VDC isolation	ACTIVE		83
<b>TEP 100</b>	100	1/2-Brick package, 2:1 input, 2250 VDC isolation	ACTIVE		84
<b>TEP 100UIR</b>	100	1/4-Brick package, 12:1 input, 3000 VAC isolation	<b>COMING SOON!</b>		84
<b>TEP 100WIR</b>	100	1/2-Brick package, 4:1 input, 2250 VDC isolation	ACTIVE		85
<b>TEP 160</b>	160	1/2-Brick package, 2:1 input, 2250 VDC isolation	ACTIVE		85
<b>TEP 160WIR</b>	160	1/2-Brick package, 4:1 input, 2250 VDC isolation	ACTIVE		86
<b>TEP 200WIR</b>	180-240	1/2-Brick package, 4:1 input, 2250 VDC isolation	ACTIVE		86

**APPS KEY:**  = EN50155 / EN61373 Approved  = IEC/EN/ES 60601-1 (2xMOPP Approved)


# DC/DC: High Power PCB Mount Brick Converters

TEP 40UIR

**NEW**

40 Watt

EN 50155 / EN 61373 Approved



Pin (4, 8): 1.5 (0.06), Pin (other): 1.0 (0.04)

- 1/4 Brick package (2.30 x 1.45 x 0.50")
- Ultra-wide 12:1 input voltage range
- Qualification for fire behavior according to EN 45545-2
- IEC/EN/UL 62368-1 approved
- I/O isolation 3'000 VAC
- High efficiency up to 92%
- Operating temperature range -40°C to +85°C
- Under-voltage lock out circuit
- Vtrim (+10/-20%) , remote on/off & sense functions
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 40-3611UIR	9 - 75 VDC	5VDC	8 A	89 %
TEP 40-3612UIR		12 VDC	3.33 A	91 %
TEP 40-3613UIR		15 VDC	2.67 A	90 %
TEP 40-3615UIR		24 VDC	1.67 A	90 %
TEP 40-3618UIR		48VDC	0.83 A	92 %
TEP 40-7211UIR	14 - 160 VDC	5 VDC	8 A	89 %
TEP 40-7212UIR		12 VDC	3.33 A	90 %
TEP 40-7213UIR		15 VDC	2.67 A	90 %
TEP 40-7215UIR		24 VDC	1.67 A	90 %
TEP 40-7218UIR		48VDC	0.83 A	90 %

### Pin Connection


Pin	Function
1	-Vin
2	Ctrl
3	+Vin
4	-Vout
5	-Sense
6	Trim
7	+Sense
8	+Vout

TEP 60UIR

**NEW**

60 Watt

EN 50155 / EN 61373 Approved



Pin (4, 8): 1.5 (0.06)  
Pin (other): 1.0 (0.04)

- 1/4 Brick package (2.3 x 1.45 x 0.50")
- Ultra-wide 12:1 input voltage range
- Qualification for fire behavior according to EN 45545-2
- IEC/EN/UL 62368-1 approved
- I/O isolation 3'000 VAC
- High efficiency up to 92%
- Operating temperature range -40°C to +85°C
- Under-voltage lock out circuit
- Vtrim (+10/-20%) , remote on/off & sense functions
- 3 year product warranty


Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 60-3611UIR	9 - 75 VDC	5VDC	12 A	89 %
TEP 60-3612UIR		12 VDC	5 A	89 %
TEP 60-3613UIR		15 VDC	4 A	89 %
TEP 60-3615UIR		24 VDC	2.5 A	90 %
TEP 60-3618UIR		48VDC	1.25 A	92 %
TEP 60-7211UIR	14 - 160 VDC	5 VDC	12 A	89 %
TEP 60-7212UIR		12 VDC	5 A	89 %
TEP 60-7213UIR		15 VDC	4 A	89 %
TEP 60-7215UIR		24 VDC	2.5 A	90 %
TEP 60-7218UIR		48VDC	1.25 A	90 %

### Pin Connection

Pin	Function
1	-Vin
2	Ctrl
3	+Vin
4	-Vout
5	-Sense
6	Trim
7	+Sense
8	+Vout

THM 60WI
NEW
60 Watt

+ IEC/EN/ES 60601-1 (2xMOPP Approved)




- 1/4 Brick package (2.30 x 1.45 x 0.50")
- Ultra-wide 4:1 input voltage
- Reinforced I/O isolation 5000 VAC
- 2xMOPP / BF compliant
- ISO 14971 risk management file
- IEC/EN/UL 62368-1 approved
- Low leakage current <2.5 µA
- Operating temp.: -40°C to +80°C
- Vtrim (+10/-20%) , remote on/off & sense functions
- IEC 60601-1-2 4th edition & EN55032 class A (EMC)
- 5 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
THM 60-2411WI	<b>9 - 36 VDC</b> (24 VDC nom.)	5.0 VDC	12.0 A	89 %
THM 60-2412WI		12.0 VDC	5.0 A	90 %
THM 60-2413WI		15.0 VDC	4.0 A	90 %
THM 60-2415WI		24.0 VDC	2.5 A	91 %
THM 60-2422WI		±12.0 VDC	±2.5 A	91 %
THM 60-2423WI	±15.0 VDC	±2.0 A	91 %	
THM 60-4811WI	<b>18 - 75 VDC</b> (48 VDC nom.)	5.0 VDC	12.0 A	89 %
THM 60-4812WI		12.0 VDC	5.0 A	90 %
THM 60-4813WI		15.0 VDC	4.0 A	90 %
THM 60-4815WI		24.0 VDC	2.5 A	91 %
THM 60-4822WI		±12.0 VDC	±2.5 A	91 %
THM 60-4823WI	±15.0 VDC	±2.0 A	92 %	

Pinout / Connection		
Pin	Single	Dual
1	-Vin	-Vin
2	Ctrl	Ctrl
3	+Vin	+Vin
4	-Vout	-Vout
5	-Sense	-Sense
6	Trim	Common
7	+Sense	+Sense
8	+Vout	+Vout

TEP 75WI
75 Watt

+ EN 50155 / EN 61373 Approved




- 2.40 x 2.28 x 0.50" half brick package
- Ultra-wide 4:1 input voltage range
- Full load operation up to +60°C (convection)
- Soft start, under voltage lockout & reverse input protection
- Vtrim (+10/-20%) , remote on/off & sense functions
- 2,250 VDC I/O Isolation
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEP 75-2411WI	<b>9 - 36 VDC</b> (24 VDC nom.)	5 VDC	15'000 mA	88 %
TEP 75-2412WI		12 VDC	6300 mA	88 %
TEP 75-2413WI		15 VDC	5000 mA	88 %
TEP 75-2415WI		24 VDC	3200 mA	87 %
TEP 75-2416WI		28 VDC	2700 mA	87 %
TEP 75-2418WI	48 VDC	1600 mA	87 %	
TEP 75-4811WI	<b>18 - 75 VDC</b> (48 VDC nom.)	5 VDC	15'000 mA	90 %
TEP 75-4812WI		12 VDC	6300 mA	90 %
TEP 75-4813WI		15 VDC	5000 mA	89 %
TEP 75-4815WI		24 VDC	3200 mA	88 %
TEP 75-4816WI		28 VDC	2700 mA	88 %
TEP 75-4818WI	48 VDC	1600 mA	87 %	
TEP 75-7211WI	<b>43 - 160 VDC</b> (110 VDC nom.)	5 VDC	15'000 mA	91 %
TEP 75-7212WI		12 VDC	6300 mA	91 %
TEP 75-7213WI		15 VDC	5000 mA	91 %
TEP 75-7215WI		24 VDC	3200 mA	90 %
TEP 75-7216WI		28 VDC	2700 mA	90 %
TEP 75-7218WI	48 VDC	1600 mA	90 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	Case
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

TEP 100 100 Watt




Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 100-1210	9 - 18 VDC (12 VDC nom.)	3.3 VDC	25'000 mA	90 %
TEP 100-1211		5 VDC	20'000 mA	91 %
TEP 100-1212		12 VDC	8'400 mA	91 %
TEP 100-1213		15 VDC	6'700 mA	91 %
TEP 100-1215		24 VDC	4'200 mA	90 %
TEP 100-1216		28 VDC	3'600 mA	90 %
TEP 100-1218		48 VDC	2'100 mA	90 %
TEP 100-2410		18 - 36 VDC (24 VDC nom.)	3.3 VDC	25'000 mA
TEP 100-2411	5 VDC		20'000 mA	93 %
TEP 100-2412	12 VDC		8'400 mA	93 %
TEP 100-2413	15 VDC		6'700 mA	93 %
TEP 100-2415	24 VDC		4'200 mA	92 %
TEP 100-2416	28 VDC		3'600 mA	92 %
TEP 100-2418	48 VDC		2'100 mA	92 %
TEP 100-4810	36 - 75 VDC (48 VDC nom.)		3.3 VDC	25'000 mA
TEP 100-4811		5 VDC	20'000 mA	93 %
TEP 100-4812		12 VDC	8'400 mA	93 %
TEP 100-4813		15 VDC	6'700 mA	93 %
TEP 100-4815		24 VDC	4'200 mA	92 %
TEP 100-4816		28 VDC	3'600 mA	92 %
TEP 100-4818		48 VDC	2'100 mA	92 %

- 2.40 x 2.28 x 0.50" half brick package
- Wide 2:1 input voltage range
- Full load operation up to +60°C (convection)
- Soft start, under voltage lockout & reverse input protection
- Vtrim (+10/-20%) , remote on/off & sense functions
- 2,250 VDC I/O Isolation
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Pinout	
Pin	Function
1	-Vin (GND)
2	Case
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

TEP 100UIR **NEW - under development** 100 Watt

EN 50155 / EN 61373 Approved



Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 100-3611UIR	9 - 75 VDC	5VDC	20 A	87 %
TEP 100-3612UIR		12 VDC	8.35 A	88 %
TEP 100-3613UIR		15 VDC	6.7 A	88 %
TEP 100-3615UIR		24 VDC	4.2 A	88 %
TEP 100-3618UIR		48 VDC	2.1 A	89 %
TEP 100-7211UIR	14 - 160 VDC	5 VDC	20 A	87 %
TEP 100-7212UIR		12 VDC	8.35 A	88 %
TEP 100-7213UIR		15 VDC	6.7 A	88 %
TEP 100-7215UIR		24 VDC	4.2 A	88 %
TEP 100-7218UIR		48 VDC	2.1 A	89 %


- 1/4 Brick package (2.30x1.45 x 0.50")
- Ultra-wide 12:1 input range
- EN 45545-2 (fire behavior)
- IEC/EN/UL 62368-1 approved
- I/O isolation 3'000 VAC
- High efficiency up to 92%
- Operating temperature range -40°C to +85°C
- Under-voltage lockout circuit
- Vtrim (+10/-20%) , remote on/off & sense functions
- 3 year product warranty

Pin Connection	
Pin	Function
1	-Vin
2	Ctrl
3	+Vin
4	-Vout
5	-Sense
6	Trim
7	+Sense
8	+Vout
9	Bus (option)
10	UVLO (option)



TEP 100WIR 100 Watt

EN 50155 / EN 61373 Approved




- 2.40 x 2.28 x 0.50" half brick package
- Ultra-wide 4:1 input voltage range
- Full load operation up to +60°C (convection)
- Adjustable output voltage +10/-20%
- Soft start, under voltage lockout & reverse input protection
- Vtrim (+10/-20%) , remote on/off & sense functions
- 2,250 VDC I/O Isolation
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 100-2411WIR	9 - 36 VDC (24 VDC nom.)	5 VDC	20'000 mA	93 %
TEP 100-2412WIR		12 VDC	8400 mA	90 %
TEP 100-2415WIR		24 VDC	4200 mA	90 %
TEP 100-2416WIR		28 VDC	3600 mA	90 %
TEP 100-2418WIR	48 VDC	2100 mA	90 %	
TEP 100-4812WIR	18 - 75 VDC (48 VDC nom.)	12 VDC	8400 mA	90 %
TEP 100-4815WIR		24 VDC	4200 mA	90 %
TEP 100-4816WIR		28 VDC	3600 mA	92 %
TEP 100-4818WIR		48 VDC	2100 mA	91 %
TEP 100-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	8400 mA	90 %
TEP 100-7215WIR		24 VDC	4200 mA	90 %
TEP 100-7216WIR		28 VDC	3600 mA	90 %
TEP 100-7218WIR	48 VDC	2100 mA	91 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	Case
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

TEP 160 160 Watt



- 2.40 x 2.28 x 0.50" half brick package
- Wide 2:1 input (16.5-36, 33-75 VDC)
- Full load operation up to +60°C (convection)
- Adjustable output voltage +10/-20%
- Soft start, under voltage lockout & reverse input protection
- Vtrim (+10/-20%) , remote on/off & sense functions
- 2,250 VDC I/O Isolation
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 160-2412	16.5 - 36 VDC (24 VDC nom.)	12 VDC	13'000 mA	92 %
TEP 160-2413		15 VDC	10'000 mA	92 %
TEP 160-2415		24 VDC	6'500 mA	93 %
TEP 160-2416		28 VDC	5'500 mA	93 %
TEP 160-2418	48 VDC	3'300 mA	92 %	
TEP 160-4812	33 - 75 VDC (48 VDC nom.)	12 VDC	16'000 mA	92 %
TEP 160-4813		15 VDC	13'000 mA	93 %
TEP 160-4815		24 VDC	8'000 mA	92 %
TEP 160-4816		28 VDC	7'000 mA	92 %
TEP 160-4818	48 VDC	4'000 mA	92 %	
TEP 160-48153	53 VDC	3'700 mA	92 %	


Pinout	
Pin	Function
1	-Vin (GND)
2	Case
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

# DC/DC: High Power PCB Mount Brick Converters

## TEP 160WIR

160 Watt

EN 50155 / EN 61373 Approved



- 2.40 x 2.28 x 0.50" half brick package
- Ultra-wide 4:1 input voltage range
- Full load operation up to +60°C (convection)
- Adjustable output voltage +10/-20%
- Soft Start, Under voltage lockout & reverse input protection
- Vtrim (+10/-20%) , remote on/off & sense functions
- 2,250 VDC I/O Isolation
- IEC/EN/UL 62368-1 approved
- 3 year product warranty


Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 160-2412WIR	9 - 36 VDC (24 VDC nom.)	12 VDC	12'000 mA	90 %
TEP 160-2413WIR		15 VDC	9500 mA	91 %
TEP 160-2415WIR		24 VDC	6000 mA	90 %
TEP 160-2416WIR		28 VDC	5000 mA	90 %
TEP 160-2418WIR	48 VDC	3000 mA	90 %	
TEP 160-4812WIR	18 - 75 VDC (48 VDC nom.)	12 VDC	13'000 mA	91 %
TEP 160-4813WIR		15 VDC	10'000 mA	91 %
TEP 160-4815WIR		24 VDC	6500 mA	91 %
TEP 160-4816WIR		28 VDC	5500 mA	91 %
TEP 160-4818WIR	48 VDC	3200 mA	91 %	
TEP 160-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	15'000 mA	90 %
TEP 160-7213WIR		15 VDC	12'000 mA	90 %
TEP 160-7215WIR		24 VDC	7500 mA	90 %
TEP 160-7216WIR		28 VDC	6500 mA	90 %
TEP 160-7218WIR	48 VDC	3800 mA	90 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	Case
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

## TEP 200WIR

240 Watt

EN 50155 / EN 61373 Approved



- 2.40 x 2.28 x 0.50" half brick package
- Ultra-wide 4:1 input voltage range
- Full load operation up to +60°C (convection)
- Adjustable output voltage +10/-20%
- Soft start, under voltage lockout & reverse input protection
- Vtrim (+10/-20%) , remote on/off & sense functions
- 2,250 VDC I/O Isolation
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEP 200-2412WIR	9 - 36 VDC (24 VDC nom.)	12 VDC	15'000 mA	89 %
TEP 200-2413WIR		15 VDC	12'000 mA	90 %
TEP 200-2415WIR		24 VDC	7500 mA	90 %
TEP 200-2416WIR		28 VDC	6500 mA	90 %
TEP 200-2418WIR	48 VDC	3700 mA	89 %	
TEP 200-4812WIR	18 - 75 VDC (48 VDC nom.)	12 VDC	18'000 mA	90 %
TEP 200-4813WIR		15 VDC	14'000 mA	91 %
TEP 200-4815WIR		24 VDC	9000 mA	90 %
TEP 200-4816WIR		28 VDC	7500 mA	91 %
TEP 200-4818WIR	48 VDC	4500 mA	90 %	
TEP 200-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	20'000 mA	89 %
TEP 200-7213WIR		15 VDC	16'000 mA	90 %
TEP 200-7215WIR		24 VDC	10'000 mA	89 %
TEP 200-7216WIR		28 VDC	8500 mA	90 %
TEP 200-7218WIR	48 VDC	5000 mA	89 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	Case
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

# DC/DC: Isolated Chassis Mount

SERIES	WATTS	DESCRIPTION	STATUS	APPS	PAGE
TMDC 06	6	2.09 × 1.34 × 1.04", 4:1 input, harsh EMC compliance	NEW		88
TMDC 06H	6	2.09 × 1.34 × 1.04", 2:1 input, harsh EMC compliance, 3000 VAC isolation, 80~160Vin Range	NEW		88
TMDC 10	10	3.11 × 1.34 × 0.87", 4:1 input, harsh EMC compliance	NEW		89
TMDC 10H	10	3.11 × 1.34 × 0.87", 2:1 input, harsh EMC compliance, 3000 VAC isolation , 80~160Vin Range	NEW		89
TEQ 20WIR	20	4.00 × 2.30 × 1.03" package, 4:1 input, regulated, 2250 VDC isolation, railway, encased	ACTIVE		90
TMDC 20	20	3.78 × 1.81 × 0.92", 4:1 input, harsh EMC compliance	ACTIVE		90
TMDC 20H	20	3.78 × 1.81 × 0.92", 2:1 input, harsh EMC compliance, 3000 VAC isolation , 80~160Vin Range	NEW		91
TEQ 40WIR	40	4.00 × 2.30 × 1.03" package, 4:1 input, regulated, 2250 VDC isolation, encased	ACTIVE		91
TMDC 40	40	4.41 × 2.51 × 1.01", 4:1 input, harsh EMC compliance	ACTIVE		92
TMDC 40H	40	4.41 × 2.51 × 1.01", 2:1 input, harsh EMC compliance, 3000 VAC isolation , 80~160Vin Range	NEW		92
TMDC 60	60	4.41 × 2.67 × 1.50", 4:1 input, harsh EMC compliance	ACTIVE		93
TMDC 60H	60	4.41 × 2.67 × 1.50", 2:1 input, harsh EMC compliance, 3000 VAC isolation , 80~160Vin Range	NEW		93
TEP 75WICMF	75	3.35 × 2.40 × 1.53", 4:1 input, 2250 VDC isolation, with filter	ACTIVE		94
TEP 100CMF	100	3.35 × 2.40 × 1.53", 2:1 input, 2250 VDC isolation, with filter	ACTIVE		94
TEP 100WIRCMF	100	3.35 × 2.40 × 1.53", 4:1 input, 2250 VDC isolation, with filter	ACTIVE		95
TEQ 100WIR	100	3.00 × 4.00 × 3.50" package, 4:1 input, 2250 VDC isolation, rugged design	ACTIVE		95
TEP 150WI	150	3.86 × 2.56 × 1.60" package, 4:1 input, 2250 VDC isolation, rugged design	ACTIVE		96
TEP 160CMF	160	3.35 × 2.40 × 1.53", 2:1 input, 2250 VDC isolation, with filter	ACTIVE		96
TEP 160WIRCMF	160	3.35 × 2.40 × 1.53", 4:1 input, 2250 VDC isolation, with filter	ACTIVE		97
TEQ 160WIR	160	3.00 × 4.00 × 3.50" package, 4:1 input, 2250 VDC isolation, rugged design	ACTIVE		97
TEP 200WIRCMF	200	3.35 × 2.40 × 1.53", 4:1 input, 2250 VDC isolation, with filter	ACTIVE		98
TEQ 200WIR	200	3.00 × 4.00 × 3.50" package, 4:1 input, 2250 VDC isolation, rugged design	ACTIVE		98
TEQ 300WIR	300	6.00 × 4.00 × 1.50" package, 4:1 input, 2250 VDC isolation, rugged design	ACTIVE		99

APPS KEY:  = EN50155 /EN61373 Approved




## DC/DC: Isolated Chassis Mount

TMDC 06

**NEW!**

6 Watt



- 2.09 x 1.34 x 1.04" package
- EN 55035 (EMC) & EN 55032 class A (EMI)
- Ultra-wide 4:1 input (9-36 & 18-75 VDC)
- -40 to +80 °C without derating
- I/O isolation 3000 VDC
- Protection overload, under voltage & short circuit
- DC-OK (LED) & Remote On/Off function
- IEC/EN/UL 62368-1 approved
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 06-2411	9 - 36 VDC (24 VDC nom.)	5.1 VDC	1'200 mA	81 %
TMDC 06-2412		12 VDC	500 mA	84 %
TMDC 06-2413		15 VDC	400 mA	84 %
TMDC 06-2415		24 VDC	250 mA	85 %
TMDC 06-2418		48 VDC	125 mA	83 %
TMDC 06-2422		+12 VDC	250 mA	84 %
TMDC 06-2423		+15 VDC	200 mA	85 %
TMDC 06-2425		+24 VDC	125 mA	84 %
TMDC 06-4811	18 - 75 VDC (48 VDC nom.)	5.1 VDC	1'200 mA	80 %
TMDC 06-4812		12 VDC	500 mA	84 %
TMDC 06-4813		15 VDC	400 mA	84 %
TMDC 06-4815		24 VDC	250 mA	85 %
TMDC 06-4818		48 VDC	125 mA	83 %
TMDC 06-4822		+12 VDC	250 mA	85 %
TMDC 06-4823		+15 VDC	200 mA	85 %
TMDC 06-4825		+24 VDC	125 mA	84 %

Pinout		
Pin	Single Output	Dual Output
1	Remote	Remote
2	-Vin (GND)	-Vin (GND)
3	+Vin (Vcc)	+Vin (Vcc)
4	-Vout	-Vout
5	NC	Common
6	+Vout	+Vout

TMDC 06H

**NEW!**

6 Watt



- 2.09 x 1.34 x 1.04" package
- Wide 2:1 input range (80-160 VDC)
- 3,000 VAC Isolation (250VAC Working Voltage)
- EN 55035 (EMC) & EN 55032 class A (EMI)
- Wide 2:1 input range (80-160V)
- Operating temperature range -40 to +80 °C without derating
- I/O isolation 3,000 VAC reinforced
- Protection against overload, under voltage & short circuit
- IEC/EN/UL 62368-1 approved
- DC-OK (LED) & Remote On/Off function
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 06-7211H	80 - 160 VDC (110 VDC nom.)	5.1 VDC	1'200 mA	79 %
TMDC 06-7212H		12 VDC	500 mA	83 %
TMDC 06-7213H		15 VDC	400 mA	83 %
TMDC 06-7215H		24 VDC	250 mA	84 %
TMDC 06-7218H		48 VDC	125 mA	82 %
TMDC 06-7222H		±12 VDC	±250 mA	84 %
TMDC 06-7223H		±15 VDC	±200 mA	84 %
TMDC 06-7225H		±24 VDC	±125 mA	83 %


Pinout		
Pin	Single Output	Dual Output
1	Remote	Remote
2	-Vin (GND)	-Vin (GND)
3	+Vin (Vcc)	+Vin (Vcc)
4	-Vout	-Vout
5	NC	Common
6	+Vout	+Vout



TMDC 10

**NEW!**

10 Watt



Model	Input Voltage Range	Output		Efficiency	
		Vnom	I <sub>max</sub>		
TMDC 10-2411	9 - 36 VDC (24 VDC nom.)	5.1 VDC	2'000 mA	84 %	
TMDC 10-2412		12 VDC	833 mA	86 %	
TMDC 10-2413		15 VDC	666 mA	86 %	
TMDC 10-2415		24 VDC	416 mA	86 %	
TMDC 10-2418		48 VDC	208 mA	84 %	
TMDC 10-2422		±12 VDC	416 mA	86 %	
TMDC 10-2423		±15 VDC	333 mA	86 %	
TMDC 10-2425		±24 VDC	208 mA	85 %	
TMDC 10-4811		18 - 75 VDC (48 VDC nom.)	5.1 VDC	2'000 mA	84 %
TMDC 10-4812			12 VDC	833 mA	86 %
TMDC 10-4813	15 VDC		666 mA	86 %	
TMDC 10-4815	24 VDC		416 mA	86 %	
TMDC 10-4818	48 VDC		208 mA	84 %	
TMDC 10-4822	±12 VDC		416 mA	86 %	
TMDC 10-4823	±15 VDC		333 mA	86 %	
TMDC 10-4825	±24 VDC	208 mA	85 %		


- 3.11 x 1.34 x 0.87" package
- EN 55035 (EMC) & EN 55032 class A (EMI)
- Ultra-wide 4:1 input (9-36 & 18-75 VDC)
- Operating temperature range -40 to +80°C without derating
- I/O isolation 3000 VDC
- Protection against overload, under voltage & short circuit
- DC-OK (LED) & remote on/off
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	Remote	Remote
2	-Vin (GND)	-Vin (GND)
3	+Vin (Vcc)	+Vin (Vcc)
4	-Vout	-Vout
5	NC	Common
6	+Vout	+Vout

TMDC 10H

**NEW!**

10 Watt



Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 10-7211H	80 - 160 VDC (110 VDC nom.)	5.1 VDC	2000 mA	83 %
TMDC 10-7212H		12 VDC	833 mA	85 %
TMDC 10-7213H		15 VDC	666 mA	85 %
TMDC 10-7215H		24 VDC	416 mA	85 %
TMDC 10-7218H		48 VDC	208 mA	83 %
TMDC 10-7222H		±12 VDC	±416 mA	85 %
TMDC 10-7223H		±15 VDC	±333 mA	85 %
TMDC 10-7225H		±24 VDC	±208 mA	84 %


- 3.11 x 1.34 x 0.87" package
- Wide 2:1 input range (80-160 VDC)
- EN 55035 (EMC) & EN 55032 class A (EMI)
- Wide 2:1 input range
- Operating temperature range -40 to +87°C without derating
- Reinforced I/O isolation 3,000 VAC
- Protection against overload, under voltage & short circuit
- IEC/EN/UL 62368-1 approved
- DC-OK (LED) & remote on/off function
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	Remote	Remote
2	-Vin (GND)	-Vin (GND)
3	+Vin (Vcc)	+Vin (Vcc)
4	-Vout	-Vout
5	NC	Common
6	+Vout	+Vout

# DC/DC: Isolated Chassis Mount

## TEQ 20WIR 20 Watt

EN 50155 / EN 61373 Approved




- 4.06 x 2.25 x 1.03" package
- Temperature range -40°C to +93°C
- Ultra-wide 4:1 input voltage range
- Excellent efficiency up to 88%
- Input filter meet EN 55032 class B
- IEC/EN/UL 62368-1 approved
- I/O isolation 2250 VDC
- Under voltage lock-out circuit
- High power block with excellent thermal convection
- Protection against overload, under voltage & short circuit
- Output LED indicator
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEQ 20-2411WIR	9 - 36 VDC (24 VDC nom.)	5 VDC	4000 mA	87 %
TEQ 20-2412WIR		12 VDC	1670 mA	88 %
TEQ 20-2413WIR		15 VDC	1330 mA	87 %
TEQ 20-2415WIR		24 VDC	833 mA	87 %
TEQ 20-2422WIR		±12 VDC	833 mA	87 %
TEQ 20-2423WIR	±15 VDC	667 mA	88 %	
TEQ 20-4811WIR	18 - 75 VDC (48 VDC nom.)	5 VDC	4500 mA	87 %
TEQ 20-4812WIR		12 VDC	1670 mA	88 %
TEQ 20-4813WIR		15 VDC	1330 mA	88 %
TEQ 20-4815WIR		24 VDC	833 mA	87 %
TEQ 20-4822WIR		±12 VDC	833 mA	87 %
TEQ 20-4823WIR	±15 VDC	667 mA	88 %	
TEQ 20-7211WIR	43 - 160 VDC (110 VDC nom.)	5 VDC	4500 mA	86 %
TEQ 20-7212WIR		12 VDC	1670 mA	87 %
TEQ 20-7213WIR		15 VDC	1330 mA	87 %
TEQ 20-7215WIR		24 VDC	833 mA	87 %
TEQ 20-7222WIR		±12 VDC	833 mA	87 %
TEQ 20-7223WIR	±15 VDC	667 mA	88 %	

Pinout		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin (GND)	-Vin (GND)
3	NC	NC
4	NC	-Vout
5	-Vout	Common
6	+Vout	Common
7	NC	+Vout


## TMDC 20 20 Watt




- 3.78 x 1.81 x 0.92" package
- Ultra-wide 4:1 input voltage range
- Temperature range -40°C to +90°C
- I/O isolation 2500 VDC
- Excellent efficiency up to 91 %
- EN 55032 class B filter
- Optional DIN-Rail mount adapter
- No minimum load required
- DC-OK (LED) & Remote On/Off
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Pinout	
Pin	Function
1	Remote
2	-Vin (GND)
3	+Vin (Vcc)
4	NC
5	-Vout
6	NC
7	+Vout
8	NC

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 20-2411	9 - 36 VDC (24 VDC nom.)	5.1 VDC	4'000 mA	90 %
TMDC 20-2412		12 VDC	1'670 mA	91 %
TMDC 20-2415		24 VDC	835 mA	91 %
TMDC 20-2418		48 VDC	420 mA	89 %
TMDC 20-4811	18 - 75 VDC (48 VDC nom.)	5.1 VDC	4'000 mA	90 %
TMDC 20-4812		12 VDC	1'670 mA	91 %
TMDC 20-4815		24 VDC	835 mA	91 %
TMDC 20-4818		48 VDC	420 mA	89 %




**TMDC 20H** **NEW!** **20 Watt**



Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TMDC 20-7211H	80 - 160 VDC (110 VDC nom.)	5.1 VDC	4000 mA	87 %
TMDC 20-7212H		12 VDC	1670 mA	88 %
TMDC 20-7213H		15 VDC	1340 mA	88 %
TMDC 20-7215H		24 VDC	830 mA	88 %
TMDC 20-7218H		48 VDC	420 mA	86 %
TMDC 20-7222H		±12 VDC	±830 mA	87 %
TMDC 20-7223H		±15 VDC	±670 mA	87 %
TMDC 20-7225H		±24 VDC	±420 mA	87 %


- 3.78 x 2.13 x 0.92" package
- Wide 2:1 input range (80-160 VDC)
- EN 55035 (EMC) & EN 55032 class A (EMI)
- Wide 2:1 input range
- Operating temperature range -40 to +95 °C
- Reinforced I/O isolation 3,000 VAC
- Protection against overload, under voltage & short circuit
- IEC/EN/UL 62368-1 approved
- DC-OK (LED) & remote on/off function
- 3 year product warranty

Pinout	
Pin	Function
1	Remote
2	-Vin (GND)
3	+Vin (Vcc)
4	NC
5	-Vout
6	NC
7	+Vout
8	NC



**TEQ 40WIR** **40 Watt**

EN 50155 / EN 61373 Approved




Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency
TEQ 40-2411WIR	9 - 36 VDC (24 VDC nom.)	5 VDC	8000 mA	90 %
TEQ 40-2412WIR		12 VDC	3330 mA	91 %
TEQ 40-2413WIR		15 VDC	2670 mA	91 %
TEQ 40-2415WIR		24 VDC	1670 mA	90 %
TEQ 40-2422WIR		±12 VDC	1670 mA	89 %
TEQ 40-2423WIR		±15 VDC	1330 mA	89 %
TEQ 40-2425WIR	±24 VDC	830 mA	90 %	
TEQ 40-4811WIR	18 - 75 VDC (48 VDC nom.)	5 VDC	8000 mA	90 %
TEQ 40-4812WIR		12 VDC	3330 mA	91 %
TEQ 40-4813WIR		15 VDC	2670 mA	91 %
TEQ 40-4815WIR		24 VDC	1670 mA	90 %
TEQ 40-4822WIR		±12 VDC	1670 mA	89 %
TEQ 40-4823WIR		±15 VDC	1330 mA	89 %
TEQ 40-4825WIR	±24 VDC	830 mA	90 %	
TEQ 40-7211WIR	43 - 160 VDC (110 VDC nom.)	5 VDC	8000 mA	88 %
TEQ 40-7212WIR		12 VDC	3330 mA	90 %
TEQ 40-7213WIR		15 VDC	2670 mA	90 %
TEQ 40-7215WIR		24 VDC	1670 mA	89 %
TEQ 40-7222WIR		±12 VDC	1670 mA	88 %
TEQ 40-7223WIR		±15 VDC	1330 mA	88 %
TEQ 40-7225WIR		±24 VDC	830 mA	90 %

- 4.06 x 2.25 x 1.03" package
- -40°C to +92° operating temperature
- Ultra-wide 4:1 input voltage range
- IEC/EN/UL 62368-1 approved
- Excellent efficiency up to 91%
- Input filter meet EN 55032, class B
- I/O isolation of 3,000 VDC
- Under voltage lock-out circuit
- High power block with excellent thermal convection
- Protection against overvoltage, overtemperature & short circuit
- Output LED indicator
- 3 year product warranty

Pinout		
Pin	Single Output	Dual Output
1	+Vin	+Vin
2	-Vin (GND)	-Vin (GND)
3	NC	NC
4	NC	-Vout
5	-Vout	Common
6	+Vout	Common
7	NC	+Vout


**TMDC 40** **40 Watt**




- 4.41 x 2.51 x 1.01" package
- Ultra-wide 4 : 1 input voltage range
- Temperature range -40°C to +85°C
- I/O isolation 2500 VDC
- Excellent efficiency up to 92 %
- EN 55032 class A filter
- Optional DIN-Rail mount adapter
- No minimum load required
- DC OK LED & remote on/off function
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Pinout	
Pin	Function
1	Remote
2	-Vin (GND)
3	+Vin (Vcc)
4	+Vout
5	NC
6	-Vout
7	NC
8	NC

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 40-2411	9 - 36 VDC (24 VDC nom.)	5.1 VDC	8'000 mA	90 %
TMDC 40-2412		12 VDC	3'330 mA	90 %
TMDC 40-2415		24 VDC	1'670 mA	90 %
TMDC 40-2418		48 VDC	835 mA	89 %
TMDC 40-4811	18 - 75 VDC (48 VDC nom.)	5.1 VDC	8'000 mA	89 %
TMDC 40-4812		12 VDC	3'330 mA	91 %
TMDC 40-4815		24 VDC	1'670 mA	92 %
TMDC 40-4818		48 VDC	835 mA	90 %




**TMDC 40H** NEW! **40 Watt**



- 4.41 x 2.51 x 1.01" package
- Wide 2:1 input range (80-160 VDC)
- EN 55035 (EMC & EN 55032 class B (EMI))
- Temperature range -40 to +90 °C
- Reinforced I/O isolation 3,000 VAC
- Overload, under voltage & short circuit protection
- IEC/EN/UL 62368-1 approved
- DC-OK (LED) & remote on/off function
- Optional DIN-Rail mount adapter
- 3 year product warranty

Pinout	
Pin	Function
1	Remote
2	-Vin (GND)
3	+Vin (Vcc)
4	+Vout
5	NC
6	-Vout
7	NC
8	NC


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 40-7211H	80 - 160 VDC (110 VDC nom.)	5.1 VDC	8000 mA	87 %
TMDC 40-7212H		12 VDC	3330 mA	89 %
TMDC 40-7213H		15 VDC	2670 mA	89 %
TMDC 40-7215H		24 VDC	1670 mA	89 %
TMDC 40-7218H		48 VDC	840 mA	87 %
TMDC 40-7222H		±12 VDC	±1670 mA	89 %
TMDC 40-7223H		±15 VDC	±1330 mA	89 %
TMDC 40-7225H		±24 VDC	±830 mA	87 %





TMDC 60


60 Watt



Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 60-2411	9 - 36 VDC (24 VDC nom.)	5.1 VDC	12'000 mA	90 %
TMDC 60-2412		12 VDC	5'000 mA	91 %
TMDC 60-2415		24 VDC	2'500 mA	91 %
TMDC 60-2418		48 VDC	1'250 mA	91 %
TMDC 60-4811	18 - 75 VDC (48 VDC nom.)	5.1 VDC	12'000 mA	91 %
TMDC 60-4812		12 VDC	5'000 mA	92 %
TMDC 60-4815		24 VDC	2'500 mA	91 %
TMDC 60-4818		48 VDC	1'250 mA	91 %

- 4.41 x 2.67 x 1.50" package
- Ultra-wide 4:1 input voltage range
- Operating temperature range -40°C to +85°C
- I/O isolation 2500 VDC
- Excellent efficiency up to 92 %
- EN 55032 class A filter
- Optional DIN-Rail mount adapter
- DC-OK (LED) & remote on/off function
- IEC/EN/UL 62368-1 approved
- 3 year product warranty


Pinout	
Pin	Function
1	Remote
2	-Vin (GND)
3	+Vin (Vcc)
4	NC
5	+Vout
6	NC
7	-Vout
8	NC



TMDC 60H

NEW!


60 Watt



Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TMDC 60-7211H	80 - 160 VDC (110 VDC nom.)	5.1 VDC	12000 mA	88 %
TMDC 60-7212H		12 VDC	5000 mA	89 %
TMDC 60-7213H		15 VDC	4000 mA	89 %
TMDC 60-7215H		24 VDC	2500 mA	88 %
TMDC 60-7218H		48 VDC	1250 mA	88 %
TMDC 60-7222H		±12 VDC	±2500 mA	88 %
TMDC 60-7223H		±15 VDC	±2000 mA	88 %
TMDC 60-7225H		±24 VDC	±1250 mA	88 %

- 4.41 x 2.67 x 1.50" package
- Wide 2:1 input range (80-160 VDC)
- EN 55035 (EMC) & EN 55032 class B (EMI)
- Temperature range -40 to +90 °C
- Reinforced I/O isolation 3,000 VAC
- Overload, under voltage & short circuit protection
- IEC/EN/UL 62368-1 approved
- DC-OK (LED) & remote on/off function
- Optional DIN-Rail mount adapter
- 3 year product warranty


Pinout	
Pin	Function
1	Remote
2	-Vin (GND)
3	+Vin (Vcc)
4	NC
5	+Vout
6	NC
7	-Vout
8	NC



# DC/DC: Isolated Chassis Mount

## TEP 75WICMF 75 Watt

EN 50155 / EN61373 Approved




- Compact 3.35 x 2.40 x 1.53" package
- Ultra-wide 4:1 input voltage ranges
- EN 50155 railway approved
- IEC/EN/UL 62368-1 approved
- 2,250 VDC I/O Isolation
- Very high efficiency up to 90%
- No minimum load & soft start
- Under voltage lock-out circuit
- Integrated Class A EMI filter
- Option DIN Rail Clip (TEP-MK1)
- Vtrim (+10/-20%), sense, remote on/off
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEP 75-2411WICMF	9 - 36 VDC (24 VDC nom.)	5 VDC	15'000 mA	88 %
TEP 75-2412WICMF		12 VDC	6300 mA	88 %
TEP 75-2413WICMF		15 VDC	5000 mA	88 %
TEP 75-2415WICMF		24 VDC	3200 mA	87 %
TEP 75-2416WICMF		28 VDC	2700 mA	87 %
TEP 75-2418WICMF		48 VDC	1600 mA	87 %
TEP 75-4811WICMF	18 - 75 VDC (48 VDC nom.)	5 VDC	15'000 mA	90 %
TEP 75-4812WICMF		12 VDC	6300 mA	90 %
TEP 75-4813WICMF		15 VDC	5000 mA	89 %
TEP 75-4815WICMF		24 VDC	3200 mA	88 %
TEP 75-4816WICMF		28 VDC	2700 mA	88 %
TEP 75-4818WICMF		48 VDC	1600 mA	87 %
TEP 75-7211WICMF	43 - 160 VDC (110 VDC nom.)	5 VDC	15'000 mA	91 %
TEP 75-7212WICMF		12 VDC	6300 mA	91 %
TEP 75-7213WICMF		15 VDC	5000 mA	91 %
TEP 75-7215WICMF		24 VDC	3200 mA	90 %
TEP 75-7216WICMF		28 VDC	2700 mA	90 %
TEP 75-7218WICMF		48 VDC	1600 mA	90 %

Pinout	
Pin	Function
1	-Vin (GND)
2	NC
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

## TEP 100CMF 100 Watt





- Compact 3.35 x 2.40 x 1.53" package
- Wide 2:1 input voltage ranges
- IEC/EN/UL 62368-1 approved
- EN 61373 thermal shock & vibration
- 2,250 VDC I/O Isolation
- Very high efficiency up to 90%
- No minimum load & soft start
- Under voltage lock-out circuit
- Integrated Class A EMI filter
- Option DIN Rail Clip (TEP-MK1)
- Vtrim (+10/-20%), sense, remote on/off
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEP 100-1210CMF	9 - 18 VDC (12VDC nom.)	3.3 VDC	25'000mA	90 %
TEP 100-1211CMF		5 VDC	20'000 mA	91 %
TEP 100-1212CMF		12 VDC	8'400 mA	91 %
TEP 100-1213CMF		15 VDC	6'700 mA	91 %
TEP 100-1215CMF		24 VDC	4'200 mA	90 %
TEP 100-1216CMF		28 VDC	3'600 mA	90 %
TEP 100-1218CMF	48 VDC	2'100 mA	90 %	
TEP 100-2410CMF	9 - 36 VDC (24 VDC nom.)	3.3 VDC	25'000mA	91 %
TEP 100-2411CMF		5 VDC	20'000 mA	93 %
TEP 100-2412CMF		12 VDC	8'400 mA	93 %
TEP 100-2413CMF		15 VDC	6'700 mA	93 %
TEP 100-2415CMF		24 VDC	4'200 mA	92 %
TEP 100-2416CMF		28 VDC	3'600 mA	92 %
TEP 100-2418CMF	48 VDC	2'100 mA	92 %	
TEP 100-4810CMF	18 - 75 VDC (48 VDC nom.)	3.3 VDC	25'000mA	91 %
TEP 100-4811CMF		5 VDC	20'000 mA	93 %
TEP 100-4812CMF		12 VDC	8'400 mA	93 %
TEP 100-4813CMF		15 VDC	6'700 mA	93 %
TEP 100-4815CMF		24 VDC	4'200 mA	92 %
TEP 100-4816CMF		28 VDC	3'600 mA	92 %
TEP 100-4818CMF	48 VDC	2'100 mA	92 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	NC
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

**TEP 100WIRCMF** **100 Watt**

EN 50155 / EN 61373 Approved





- Compact 3.35 x 2.40 x 1.53" package
- Ultra-wide 4:1 input voltage ranges
- IEC/EN/UL 62368-1 approved
- 2,250 VDC I/O Isolation
- Very high efficiency up to 91%
- No minimum load & soft start
- Under voltage lock-out circuit
- Vtrim (+10/-20%), sense, remote on/off
- Integrated Class A EMI filter
- Optional DIN Rail Clip (TEP-MK1)
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Eff
TEP 100-2411WIRCMF	9 - 36 VDC (24 VDC nom.)	5 VDC	20'000 mA	93 %
TEP 100-2412WIRCMF		12 VDC	8400 mA	90 %
TEP 100-2415WIRCMF		24 VDC	4200 mA	90 %
TEP 100-2416WIRCMF		28 VDC	3600 mA	90 %
TEP 100-2418WIRCMF	48 VDC	2100 mA	90 %	
TEP 100-4812WIRCMF	18 - 75 VDC (48 VDC nom.)	12 VDC	8400 mA	90 %
TEP 100-4815WIRCMF		24 VDC	4200 mA	90 %
TEP 100-4816WIRCMF		28 VDC	3600 mA	92 %
TEP 100-4818WIRCMF		48 VDC	2100 mA	91 %
TEP 100-7212WIRCMF	43 - 160 VDC (110 VDC nom.)	12 VDC	8400 mA	90 %
TEP 100-7215WIRCMF		24 VDC	4200 mA	90 %
TEP 100-7216WIRCMF		28 VDC	3600 mA	90 %
TEP 100-7218WIRCMF		48 VDC	2100 mA	91 %

Pinout	
Pin	Function
1	-Vin (GND)
2	NC
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

**TEQ 100WIR** **100 Watt**

EN 50155 / EN 61373 Approved



- 4.06 x 3.45 x 3.11" package
- -40°C to +85°C without derating
- Shock & vibration resistant
- Ultra-wide 4:1 input voltage range
- IEC/EN/UL 62368-1 approved
- High power block, excellent thermal convection
- Input filter meet EN 55032, class A
- I/O isolation 1591 VAC
- Under voltage lock-out & soft start circuit
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency typ.
TEQ 100-2412WIR	10 - 36 VDC (24 VDC nom.)	12 VDC	8400 mA	90 %
TEQ 100-2415WIR		24 VDC	4200 mA	90 %
TEQ 100-2416WIR		28 VDC	3600 mA	90 %
TEQ 100-2418WIR		48 VDC	2100 mA	90 %
TEQ 100-4812WIR	19 - 75 VDC (48 VDC nom.)	12 VDC	8400 mA	90 %
TEQ 100-4815WIR		24 VDC	4200 mA	90 %
TEQ 100-4816WIR		28 VDC	3600 mA	90 %
TEQ 100-4818WIR		48 VDC	2100 mA	90 %
TEQ 100-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	8400 mA	89 %
TEQ 100-7215WIR		24 VDC	4200 mA	90 %
TEQ 100-7216WIR		28 VDC	3600 mA	90 %
TEQ 100-7218WIR		48 VDC	2100 mA	90 %

Pin Connection	
Terminal	Pin Function
1, 2	-Vin
3	NC
4	On/Off Ctrl
5, 6	+Vin
7, 8	-Vout
9	-Sense*
10	+Sense*
11, 12	+Vout

\* Sense line to be connected to the output either at the module or at the load under regard of polarity.  
 • The current rating of the terminal block is 15 A/pole.  
 • Using 2 poles in parallel if the peak output current can exceed 15 A.  
 • Wire size shall be selected to Withstand the peak output current (I<sub>out max</sub> + Current limitation).

# DC/DC: Isolated Chassis Mount

## TEP 150WI 150 Watt

EN 50155 / EN 61373 Approved




- 3.86 x 2.56 x 1.60" package
- Ultra-wide 4:1 input voltage ranges
- IEC/EN/UL 62368-1 approved
- Very high efficiency up to 89%
- Constant current output characteristic for battery load applications
- Optional EN 55032 class B filter
- -40°C to +75°C temperature range:
- Under voltage lock-out, overtemperature & reverse input protection
- Easy chassis & wall mounting
- 3 year product warranty

Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEP 150-2412WI	9 - 36 VDC (24 VDC nom.)	12 VDC	12'500 mA	86 %
TEP 150-2413WI		15 VDC	10'000 mA	86 %
TEP 150-2415WI		24 VDC	6300 mA	87 %
TEP 150-2416WI		28 VDC	5400 mA	87 %
TEP 150-2418WI	48 VDC	3200 mA	86 %	
TEP 150-4812WI	18 - 36 VDC (24 VDC nom.)	12 VDC	12'500 mA	88 %
TEP 150-4813WI		15 VDC	10'000 mA	89 %
TEP 150-4815WI		24 VDC	6300 mA	89 %
TEP 150-4816WI		28 VDC	5400 mA	89 %
TEP 150-4818WI	48 VDC	3200 mA	88 %	
TEP 150-7212WI	36 - 75 VDC (48 VDC nom.)	12 VDC	12'500 mA	88 %
TEP 150-7213WI		15 VDC	10'000 mA	89 %
TEP 150-7215WI		24 VDC	6300 mA	89 %
TEP 150-7216WI		28 VDC	5400 mA	89 %
TEP 150-7218WI	48 VDC	3200 mA	88 %	

Pinout	
Pin	Function
1	+ Vin
2	+ Vin
3	- Vin
4	- Vin
5	Remote
6	+ Vout
7	- Vout
8	Trim
9	Trim

## TEP 160CMF 160 Watt



- Compact 3.35 x 2.40 x 1.53" package
- Wide 2:1 input voltage ranges
- IEC/EN/UL 62368-1 approved
- EN 61373 thermal shock & vibration
- 2,250 VDC I/O Isolation
- Very high efficiency up to 90%
- No minimum load & soft start
- Under voltage lock-out circuit
- Integrated Class A EMI filter
- Option DIN Rail Clip (TEP-MK1)
- Vtrim (+10/-20%), sense, remote on/off
- 3 year product warranty


Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TEP 160-2412CMF	16.5 - 36 VDC (24 VDC nom.)	12 VDC	13'000 mA	92 %
TEP 160-2413CMF		15 VDC	10'000 mA	92 %
TEP 160-2415CMF		24 VDC	6'500 mA	93 %
TEP 160-2416CMF		28 VDC	5'500 mA	93 %
TEP 160-2418CMF	48 VDC	3'300 mA	92 %	
TEP 160-4812CMF	36 - 75 VDC (48 VDC nom.)	12 VDC	16'000 mA	92 %
TEP 160-4813CMF		15 VDC	13'000 mA	93 %
TEP 160-4815CMF		24 VDC	8'000 mA	92 %
TEP 160-4816CMF		28 VDC	7'000 mA	92 %
TEP 160-4818CMF	48 VDC	4'000 mA	92 %	
TEP 160-48153CMF	53 VDC	3'700 mA	92 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	NC
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout



**TEP 160WIRCMF** **144~182 Watt**

EN 50155 / EN 61373 Approved




- Compact 3.35 x 2.40 x 1.53" package
- Ultra-wide 4:1 input voltage ranges
- IEC/EN/UL 62368-1 approved
- 2,250 VDC I/O Isolation
- Very high efficiency up to 91%
- No minimum load & soft start
- Under voltage lock-out circuit
- Vtrim (+10/-20%), sense, remote on/off
- Integrated Class A EMI filter
- Optional DIN Rail Clip (TEP-MK1)
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Eff
TEP 160-2412WIRCMF	9 - 36 VDC (24 VDC nom.)	12 VDC	12'000 mA	90 %
TEP 160-2413WIRCMF		15 VDC	9500 mA	91 %
TEP 160-2415WIRCMF		24 VDC	6000 mA	90 %
TEP 160-2416WIRCMF		28 VDC	5000 mA	90 %
TEP 160-2418WIRCMF	48 VDC	3000 mA	90 %	
TEP 160-4812WIRCMF	18 - 75 VDC (48 VDC nom.)	12 VDC	13'000 mA	91 %
TEP 160-4813WIRCMF		15 VDC	10'000 mA	91 %
TEP 160-4815WIRCMF		24 VDC	6500 mA	91 %
TEP 160-4816WIRCMF		28 VDC	5500 mA	91 %
TEP 160-4818WIRCMF	48 VDC	3200 mA	91 %	
TEP 160-7212WIRCMF	43 - 160 VDC (110 VDC nom.)	12 VDC	15'000 mA	90 %
TEP 160-7213WIRCMF		15 VDC	12'000 mA	90 %
TEP 160-7215WIRCMF		24 VDC	7500 mA	90 %
TEP 160-7216WIRCMF		28 VDC	6500 mA	90 %
TEP 160-7218WIRCMF	48 VDC	3800 mA	90 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	NC
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

**TEQ 160WIR** **160 Watt**

EN 50155 / EN 61373 Approved



- 4.06 x 3.45 x 3.11" package
- -40°C to +85°C without derating
- Shock & vibration resistant
- Ultra-wide 4:1 input voltage range
- IEC/EN/UL 62368-1 approved
- High power block, excellent thermal convection
- Input filter meet EN 55032, class A
- I/O isolation 1591 VAC
- Under voltage lock-out & soft start circuit
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency typ.
TEQ 160-4812WIR	19 - 75 VDC (48 VDC nom.)	12 VDC	13'000 mA	90 %
TEQ 160-4815WIR		24 VDC	6500 mA	90 %
TEQ 160-4816WIR		28 VDC	5500 mA	90 %
TEQ 160-4818WIR		48 VDC	3200 mA	90 %
TEQ 160-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	15'000 mA	89 %
TEQ 160-7215WIR		24 VDC	7500 mA	89 %
TEQ 160-7216WIR		28 VDC	6500 mA	89 %
TEQ 160-7218WIR		48 VDC	3800 mA	89 %

Pin Connection	
Terminal	Pin Function
1, 2	-Vin
3	NC
4	On/Off Ctrl
5, 6	+Vin
7, 8	-Vout
9	-Sense*
10	+Sense*
11, 12	+Vout


\* Sense line to be connected to the output either at the module or at the load under regard of polarity.  
 • The current rating of the terminal block is 15 A/pole.  
 • Using 2 poles in parallel if the peak output current can exceed 15 A.  
 • Wire size shall be selected to Withstand the peak output current (I<sub>out max</sub> + Current limitation).

## DC/DC: Isolated Chassis Mount

### TEP 200WIRCMF

180~240 Watt

EN 50155 / EN 61373 Approved



- Compact 3.35 x 2.40 x 1.53" package
- Ultra-wide 4:1 input voltage ranges
- IEC/EN/UL 62368-1 approved
- 2,250 VDC I/O Isolation
- Very high efficiency up to 91%
- No minimum load & soft start
- Under voltage lock-out circuit
- Vtrim (+10/-20%), sense, remote on/off
- Integrated Class A EMI filter
- Optional DIN Rail Clip (TEP-MK1)
- 3 year product warranty


Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Eff
TEP 200-2412WIRCMF	9 - 36 VDC (24 VDC nom.)	12 VDC	15'000 mA	89 %
TEP 200-2413WIRCMF		15 VDC	12'000 mA	90 %
TEP 200-2415WIRCMF		24 VDC	7500 mA	90 %
TEP 200-2416WIRCMF		28 VDC	6500 mA	90 %
TEP 200-2418WIRCMF	48 VDC	3700 mA	89 %	
TEP 200-4812WIRCMF	18 - 75 VDC (48 VDC nom.)	12 VDC	18'000 mA	90 %
TEP 200-4813WIRCMF		15 VDC	14'000 mA	91 %
TEP 200-4815WIRCMF		24 VDC	9000 mA	90 %
TEP 200-4816WIRCMF		28 VDC	7500 mA	91 %
TEP 200-4818WIRCMF	48 VDC	4500 mA	90 %	
TEP 200-7212WIRCMF	43 - 160 VDC (110 VDC nom.)	12 VDC	20'000 mA	89 %
TEP 200-7213WIRCMF		15 VDC	16'000 mA	90 %
TEP 200-7215WIRCMF		24 VDC	10'000 mA	89 %
TEP 200-7216WIRCMF		28 VDC	8500 mA	90 %
TEP 200-7218WIRCMF	48 VDC	5000 mA	89 %	

Pinout	
Pin	Function
1	-Vin (GND)
2	NC
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense*
7	Trim
8	+Sense*
9	+Vout

### TEQ 200WIR

200 Watt

EN 50155 / EN 61373 Approved



- 4.06 x 3.45 x 3.11" package
- -40°C to +85°C without derating
- Shock & vibration resistant
- Ultra-wide 4:1 input voltage range
- IEC/EN/UL 62368-1 approved
- High power block, excellent thermal convection
- Input filter meet EN 55032, class A
- I/O isolation 1591 VAC
- Under voltage lock-out & soft start circuit
- 3 year product warranty

Model	Input Voltage Range	Output Vnom	I <sub>max</sub>	Efficiency typ.
TEQ 200-4812WIR	19 - 75 VDC (48 VDC nom.)	12 VDC	18'000 mA	89 %
TEQ 200-4815WIR		24 VDC	9000 mA	89 %
TEQ 200-4816WIR		28 VDC	7500 mA	90 %
TEQ 200-4818WIR		48 VDC	4500 mA	89 %
TEQ 200-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	20'000 mA	88 %
TEQ 200-7215WIR		24 VDC	10'000 mA	88 %
TEQ 200-7216WIR		28 VDC	8500 mA	89 %
TEQ 200-7218WIR		48 VDC	5000 mA	88 %


Pin Connection	
Terminal	Pin Function
1, 2	-Vin
3	NC
4	On/Off Ctrl
5, 6	+Vin
7, 8	-Vout
9	-Sense*
10	+Sense*
11, 12	+Vout

\* Sense line to be connected to the output either at the module or at the load under regard of polarity.  
 • The current rating of the terminal block is 15 A/pole.  
 • Using 2 poles in parallel if the peak output current can exceed 15 A.  
 • Wire size shall be selected to Withstand the peak output current (I<sub>out max</sub> + Current limitation).

TEQ 300WIR

300 Watt

EN 50155 / EN 61373 Approved



- 6.00 x 4.00 x 1.52" package
- Temperature range -40°C to +80°C
- Shock & vibration resistant
- Ultra-wide 4:1 input voltage range
- EN 50155 / EN 61373 approval railway applications
- IEC/EN/UL 62368-1 approved
- High power block, excellent thermal convection
- Constant current characteristic for battery loads
- Power sharing (up to 3 pcs in parallel)
- Input filter meet EN 55032, class A
- Under voltage lock-out circuit

Model	Input Voltage Range	Output		Efficiency typ.
		Vnom	I <sub>max</sub>	
TEQ 300-4812WIR	19 - 75 VDC (48 VDC nom.)	12 VDC	25'000 mA	89 %
TEQ 300-4815WIR		24 VDC	12'500 mA	92 %
TEQ 300-4816WIR		28 VDC	10'800 mA	91 %
TEQ 300-4818WIR		48 VDC	6300 mA	92 %
TEQ 300-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	25'000 mA	89 %
TEQ 300-7215WIR		24 VDC	12'500 mA	91 %
TEQ 300-7216WIR		28 VDC	10'800 mA	91 %
TEQ 300-7218WIR		48 VDC	6300 mA	92 %

Pin Connection

Terminal	Pin Function
1, 2	+Vin
3, 4	-Vin (GND)
5	On/Off Ctrl
6, 7	+Vout
8, 9	-Vout
10	+Sense*
11	LS (Loadshare)
12	-Sense*

\* Sense line to be connected to the output either at the module or at the load under regard of polarity.  
 • Wire size shall be selected to Withstand the peak current (I<sub>out max</sub> + Current limitation).



# Surge | Filter for Railway Systems

RIA12 - More aggressive than EN 50155,  
1.5x for up to 1s - 3.5x for up to 20ms



Protection from potential surge sources such as:

- Switchover between neutral & energized zones
- Arcing from momentary loss of contact
- Change from coasting to traction mode
- Lightning strikes
- Opening/Closing main switch
- Operations on the electrical grid



**TFI** **NEW!** **20-300 Watt (RIA12 Surge | Filter Modules)**


EN 50155 / EN 61373 Approved



Pin-Out	
Pin	Function
1	+Vin
2	+Vin
10	+Vout
11	+Vout
12	+Vout
13	- Vout
14	- Vout
23	- Vin
24	- Vin

- Clamps over voltage transients (up to 385 VDC) at 168 VDC
- Use with any DC/DC converter
- Complies with RIA12, NF F 01-510 Surge susceptibilities
- Wide 43-160 VDC input range
- Brownout voltage 36 VDC min.
- -40°C to +95°C temperature range
- 3 year product warranty

Model	Input voltage	Power max.
TFI 20	43-160 VDC	20 W
TFI 150	43-160 VDC	150 W
TFI 300	43-160 VDC	300 W



Pinout			
Pin	Function	Pin	Function
1	+Vin	4	+Vout
2	NC	6	- Vout
3	- Vin		




# AC/DC: Encapsulated Chassis Mount

SERIES	WATTS	DESCRIPTION	STATUS	APPS	PAGE
TMPW 5-J	5	2.17 × 1.08 × 0.91" package, 90-305 VAC input, 4000 VAC isolation	NEW	🏠	101
TMPW 10-J	10	2.17 × 1.08 × 0.91" package, 90-305 VAC input, 4000 VAC isolation	NEW	🏠	102
TMP 15-C	15	4.41 × 2.51 × 1.01" package, 85-264 VAC input, 3'000 VAC isolation	ACTIVE	⚙️	102
TPP 15-J	15	2.82 × 1.14 × 0.82" package, 4000 VAC isolation	ACTIVE	⊕ 🏠	103
TML 20-C	20	3.78 × 2.15 × 1.09" package, 90-264 VAC input, 3'000 VAC isolation	ACTIVE		103
TMM 24-C	24	3.78 × 2.13 × 0.92" package, 85-264 VAC input, 4'000 VAC isolation	ACTIVE	⊕ ⚙️	104
TMPW 25-J	25	3.48 × 1.50 × 0.95" package, 90-305 VAC input, 4000 VAC isolation	NEW	🏠	104
TMP 30-C	30	4.41 × 2.51 × 1.01" package, 85-264 VAC input, 3'000 VAC isolation	ACTIVE	⚙️	105
TPP 30-J	30	3.95 × 1.50 × 1.00" package, 4000 VAC isolation	ACTIVE	⊕ 🏠	105
TML 40-C	40	4.41 × 2.50 × 1.25" package, 90-264 VAC input, 3'000 VAC isolation	ACTIVE		106
TMM 40-C	40	4.41 × 2.51 × 1.34" package, 85-264 VAC input, 4'000 VAC isolation	ACTIVE	⊕ ⚙️	106
TMPW 50-J	50	3.81 × 1.90 × 1.00" package, 90-305 VAC input, 4,000 VAC isolation	NEW	🏠	107
TMM 60-C	60	4.41 × 2.67 × 1.50" package, 85-264 VAC input, 4'000 VAC isolation	ACTIVE	⊕ ⚙️	107
TMP 60-C	60	4.41 × 2.67 × 1.50" package, 85-264 VAC input, 3'000 VAC isolation	ACTIVE	⚙️	108
TML 100C	100	5.50 × 2.36 × 1.48" package, 3000 VAC isolation, active PFC	ACTIVE		108

APPS KEY: 🏠 = EN 60335-1 Approved    ⊕ = UL/EN 60601-1 (2xMOPP) Approved    ⚙️ = UL/cUL 508 Listed

## TMPW 5-J NEW! 5 Watt

🏠 EN 60335-1 Approved



- 2.17 x 1.70 x 0.91" package
- Wide 90-305 VAC input voltage range
- IEC/EN/UL 62368-1 approved
- I/O isolation 4000 VAC
- Temperature range -40°C to +70°C
- No load input power <0.1W (ErP ready)
- EMI meets EN 55032 class B
- High efficiency up to 89%
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- 3 year product warranty


Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 5-103-J	3.3 VDC	1515 mA	73 %
TMPW 5-105-J	5 VDC	1000 mA	77 %
TMPW 5-112-J	12 VDC	420 mA	81 %
TMPW 5-124-J	24 VDC	210 mA	83 %

Pin Connections	
Pin	Single
1	AC (L)
2	AC (N)
3	-Vout
4	NC
5	+Vout

# AC/DC: Encapsulated Chassis Mount

## TMPW 10-J **NEW!** 10 Watt

EN 60335-1 Approved




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 10-105-J	5 VDC	2000 mA	81 %
TMPW 10-112-J	12 VDC	833 mA	85 %
TMPW 10-115-J	15 VDC	667 mA	86 %
TMPW 10-124-J	24 VDC	417 mA	86 %

- 2.17 x 1.70 x 0.91" package
- Wide 90-305 VAC input voltage range
- IEC/EN/UL 62368-1 approved
- I/O isolation 4000 VAC
- Temperature range -40°C to +70°C
- No load input power <0.1W (ErP ready)
- EMI meets EN 55032 class B
- High efficiency up to 89%
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- 3 year product warranty

Pin Connections	
Pin	Single
1	AC (L)
2	AC (N)
3	-Vout
4	NC
5	+Vout

## TMP 15C 15 Watt

UL/cUL 508 Listed



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMP 15105C	5 VDC	3000 mA	75%
TMP 15112C	12 VDC	1250 mA	79%
TMP 15115C	15 VDC	1000 mA	79%
TMP 15124C	24 VDC	625 mA	79%
TMP 15148C	48 VDC	310 mA	79%
TMP 15212C	±12 VDC	±650 mA	79%
TMP 15215C	±15 VDC	±500 mA	79%
TMP 15252C	5 / 12 VDC	1500 mA / 625 mA	72%
TMP 15512C	5 / ±12 VDC	2000 mA / +200 mA	74%
TMP 15515C	5 / ±15 VDC	2000 mA / ±150 mA	74%


- 4.41 x 2.51 x 1.01" package
- Fully encapsulated (pollution/dust)
- Single-, dual- & triple output models
- DIN-rail mount adaptor (optional)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II prepared
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- UI/cUL 508 Listed (single outputs only)
- Overtemperature protection
- Protection against short circuit & overload
- 3 year product warranty

Pin Connections				
Pin	Single	Dual (sym)	Dual (asym)	Triple
1	AC (L)	AC (L)	AC (L)	AC (L)
2	AC (N)	AC (N)	AC (N)	AC (N)
3	NC	NC	NC	Vout 3
4	-Vout	Vout 2	-Vout 2	Comm
5	NC	Comm	+Vout 2	Vout 2
6	+Vout	Vout 1	-Vout 1	-Vout 1
7	NC	NC	+Vout 1	+Vout 1

TPP 15-J

15 Watt

- EN 60335-1 Approved
- IEC/EN/ES 60601-1 Approved




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPP 15-103-J	3.3 VDC	4'000 mA	84 %
TPP 15-105-J	5 VDC	3'000 mA	86 %
TPP 15-109-J	9 VDC	1'670 mA	86 %
TPP 15-112-J	12 VDC	1'250 mA	87 %
TPP 15-115-J	15 VDC	1'000 mA	87 %
TPP 15-124-J	24 VDC	625 mA	88 %
TPP 15-136-J	36 VDC	417 mA	88 %
TPP 15-148-J	48 VDC	313 mA	89 %

- 2.82 x 1.14 x 0.82" package
- 2xMOPP / BF Compliant
- <75 µA Leakage (BF Rated)
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance to IPC-A-610 Level 3
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- ErP Ready (no load power <75 mW)
- 5 year product warranty

Pin Connectors			
Input		Output	
Pin	Function	Pin	Function
1	Line	1	-Vout
3	Neutral	2	+Vout

TML 20C

20 Watt



Model	Output Voltage nom.	Output Current max.
TML 20103C	3.3 VDC	4500 mA
TML 20105C	5.0 VDC	4000 mA
TML 20112C	12 VDC	1670 mA
TML 20115C	15 VDC	1340 mA
TML 20124C	24 VDC	840 mA
TML 20205C	±5 VDC	±2000 mA
TML 20212C	±12 VDC	±833 mA
TML 20215C	±12 VDC	±833 mA
TML 20512C	5 VDC / ±12 VDC	2800 mA / ±250 mA
TML 20515C	5 VDC / ±15 VDC	2800 mA / ±200 mA


- 3.78 x 2.15 x 1.09" package
- Single, dual & triple output models
- Universal input 90-264 VAC, 47-440 Hz
- EN 55022, class B & FCC, level B
- IEC/EN/UL 62368-1 approved
- Short circuit & overload protection
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Pin Connections			
Pin	Single	Dual	Triple
1	FG	FG	FG
2	AC (N)	AC (N)	AC (N)
3	AC (Line)	AC (Line)	AC (Line)
4	NC	NC	Vout3
5	-Vout	Vout2	Comm
6	NC	Comm	Vou2
7	+Vout	Vout1 1	-Vout1
8	NC	NC	+Vout1

# AC/DC: Encapsulated Chassis Mount

## TMM 24C 24 Watt

- ⊕ IEC/EN/ES 60601-1 Approved
- ⚙️ UL/cUL 508 Listed




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMM 24105C	5 VDC	3'000 mA	77%
TMM 24112C	12 VDC	2'000 mA	83%
TMM 24115C	15 VDC	1'600 mA	82%
TMM 24124C	24 VDC	1'000 mA	85%
TMM 24212C	+12 VDC / -12 VDC	1'000 mA	84%
TMM 24215C	+15 VDC / -15 VDC	800 mA	84%

- 3.78 x 2.13 x 0.92" package
- 2xMOPP / BF Compliant
- IEC/EN/UL 62368-1 approved
- IEC/EN/UL 60950-1 approved
- UL 508 (Listed)
- ErP compliant <0.3 W no load power
- Protection class II prepared
- Protection against over-temperature, over-load & short circuit
- 3 year product warranty

Pin Connections		
Pin	Single	Dual
1	AC (N)	AC (N)
2	AC (L)	AC (L)
3	NC	NC
4	-Vout	-Vout
5	NC	Comm
6	+Vout	+Vout

## TMPW 25-J NEW! 25 Watt

- 🏠 EN 60335-1 Approved



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 25-105-J	5.1 VDC	3922 mA	84 %
TMPW 25-112-J	12 VDC	2083 mA	88 %
TMPW 25-115-J	15 VDC	1666 mA	88 %
TMPW 25-124-J	24 VDC	1042 mA	87 %

- 3.48 x 1.50 x 0.95" package
- Wide 90-305 VAC input voltage range
- IEC/EN/UL 62368-1 approved
- I/O isolation 4000 VAC
- Temperature range -40° to +70°C
- No load input power <0.1W (Erp Ready)
- EMI meets EN 55032 class B
- High efficiency up to 89%
- Protection class II prepared
- 3 year product warranty


Pin Connections	
Pin	Single
1	AC (L)
2	AC (N)
3	-Vout
4	NC
5	+Vout



TMP 30C

30 Watt

UL/cUL 508 Listed



- 4.41 x 2.51 x 1.01" package
- Fully encapsulated (pollution/dust)
- Screw terminal block
- Optional pin-connector on request
- DIN-rail mount adaptor (optional)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II prepared
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- UL/cUL 508 listed (single outputs only)
- Over-temperature protection
- Protection against short circuit & overload
- 3 year product warranty


Model	Output Voltage nom.	Output Current max.	Eff typ.
TMP 30105C	5 VDC	6000 mA	78%
TMP 30112C	12 VDC	2500 mA	80%
TMP 30115C	15 VDC	2000 mA	80%
TMP 30124C	24 VDC	1250 mA	80%
TMP 30148C	48 VDC	625 mA	80%
TMP 30212C	±12 VDC	±1300 mA	80%
TMP 30215C	±15 VDC	±1000 mA	80%
TMP 30252C	5.0 VDC / ±12 VDC	3000 mA / ±1250 mA	76%
TMP 30316C	3.3 / +5 / +12 VDC	4000 / 1500 / 250 mA	71%
TMP 30317C	5 / +3.3 / +12 VDC	4500 / 1000 / 250 mA	71%
TMP 30512C	5 / ±12 VDC	3000 / ±600 mA	76%
TMP 30515C	5 / ±15 VDC	3000 / ±500 mA	76%
TMP 30522C	5 / ±12 VDC	3000 / +1000 / -250 mA	76%

Pin Connections				
Pin	Single	Dual (sym)	Dual (asym)	Triple
1	AC (L)	AC (L)	AC (L)	AC (L)
2	AC (N)	AC (N)	AC (N)	AC (N)
3	+Vout	Vout 1	+Vout 2	Vout2
4	NC	NC	+Vout 1	+Vout 1
5	-Vout	Comm	-Vout2	Comm
6	NC	NC	-Vout 1	-Vout 1
7	NC	Vout 2	NC	Vout 3

TPP 30-J

30 Watt

EN 60335-1 Approved  
IEC/EN/ES 60601-1 Approved



- 3.95 x 1.50 x 1.00" package
- 2xMOPP / BF Compliant
- <75 µA Leakage (BF rated)
- IEC 60601-1-2 4th edition EMC
- IEC/EN/UL 62368-1 approved
- Protection class II
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- Operating up to 5000 m altitude
- ErP Ready (no load power <60 mW)
- 5 year product warranty


Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 30-103-J	3.3 VDC (2.97 - 3.63 VDC)	6'000 mA	84 %
TPP 30-105-J	5 VDC (4.5 - 5.5 VDC)	6'000 mA	87 %
TPP 30-109-J	9 VDC (8.1 - 9.9 VDC)	3'340 mA	88 %
TPP 30-112-J	12 VDC (10.8 - 13.2 VDC)	2'500 mA	91 %
TPP 30-115-J	15 VDC (13.5 - 16.5 VDC)	2'000 mA	91 %
TPP 30-124-J	24 VDC (21.6 - 26.4 VDC)	1'250 mA	90 %
TPP 30-136-J	36 VDC (32.4 - 39.6 VDC)	840 mA	90 %
TPP 30-148-J	48 VDC (43.2 - 52.8 VDC)	630 mA	92 %

Pin Connectors			
Input		Output	
Pin	Function	Pin	Function
1	Line	1	+Vout
3	Neutral	2	-Vout

# AC/DC: Encapsulated Chassis Mount

## TML 40C

40 Watt



Model	Output Voltage nom.	Output Current max.
TML 40103C	3.3 VDC	8000 mA
TML 40105C	5.0 VDC	8000 mA
TML 40112C	12 VDC	3333 mA
TML 40115C	15 VDC	2666 mA
TML 40124C	24 VDC	1667 mA
TML 40205C	±5 VDC	±4000 mA
TML 40212C	±12 VDC	±1666 mA
TML 40215C	±15 VDC	±1333 mA
TML 40252C	5 / 12 VDC	5000 mA / 1250 mA
TML 40254C	5 / 24 VDC	5000 mA / 625 mA
TML 40512C	5 / ±12 VDC	5000 mA / ±600 mA
TML 40515C	5 / ±15	5000 mA / ±500 mA


- 4.41 x 2.50 x 1.25" package
- Single, dual & triple outputs
- 90-264 VAC input, 47-440 Hz
- EMI meets EN 55022, class B & FCC, level B
- IEC/EN/UL 62368-1 approved
- Protection class II
- Short circuit & overload protection
- 3 year product warranty

Pin Connections				
Pin	Single	Dual (sym)	Dual asym	Triple
1	NC	NC	NC	NC
2	AC (L)	AC (L)	AC (L)	AC (L)
3	AC (N)	AC (N)	AC (N)	AC (N)
4	+Vout	Vout 1	Vout 2	Vout 2
5	NC	NC	Vout 1	Vout 1
6	-Vout	Comm	-Vout 2	Comm
7	NC	NC	-Vout 1	-Vout 1
8	NC	Vout 2	NC	Vout 3

## TMM 40C

40 Watt

- ⊕ IEC/EN/ES 60601-1 Approved
- ⚙ UL/cUL 508 Listed




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMM 40105C	5 VDC	8'000 mA	81%
TMM 40112C	12 VDC	3'330 mA	84%
TMM 40115C	15 VDC	2'660 mA	85%
TMM 40124C	24 VDC	1'660 mA	84%
TMM 40212C	+12 VDC / -12 VDC	1'660 mA	84%
TMM 40215C	+15 VDC / -15 VDC	1'330 mA	85%

- 4.41 x 2.51 x 1.34" package
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Safety class II prepared
- ErP compliant <0.3 W no load power
- Protection against over-temperature, overload & short circuit
- 3 year product warranty

Pin Connections		
Pin	Single	Dual
1	AC (N)	AC (N)
2	AC (L)	AC (L)
3	+Vout	+Vout
4	NC	NC
5	-Vout	Common
6	NC	NC
7	NC	-Vout

**TMPW 50-J** **NEW!** **50 Watt**

EN 60335-1 Approved




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 50-112-J	12 VDC	4167 mA	89 %
TMPW 50-115-J	15 VDC	3333 mA	88 %
TMPW 50-124-J	24 VDC	2083 mA	88 %

- 3.82 x 1.90 x 1.00" package
- 90-305 VAC input range
- IEC/EN/UL 62368-1 approved
- I/O isolation 4,000VAC
- -40°C to +70°C temperature range
- <0.1W no load power (ErP compliant)
- High efficiency up to 89%
- Internal EN55032 class B filter
- Protection class II prepared
- 3 year product warranty

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	-Vout
4	NC
5	+Vout

**TMM 60C** **60 Watt**

IEC/EN/ES 60601-1 Approved  
UL/cUL 508 Listed



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMM 60105C	5.1 VDC	10'000 mA	84%
TMM 60112C	12 VDC	5'000 mA	87%
TMM 60115C	15 VDC	4'000 mA	87%
TMM 60124C	24 VDC	2'500 mA	87%
TMM 60148C	48 VDC	1'250 mA	88%

- 4.41 x 2.67 x 1.50" package
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- <0.5 W no load power (ErP Ready)
- Safety class II prepared
- Protection against over-temperature, overload & short circuit
- 3 year product warranty

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	NC
4	+Vout
5	NC
6	-Vout
7	NC


# AC/DC: Encapsulated Chassis Mount

## TMP 60C 60 Watt

UL/cUL 508 Listed



TMP 60 models for chassis mount:




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMP 60112C	12 VDC	5'000 mA	82%
TMP 60105C	5.1 VDC	10'000 mA	79%
TMP 60115C	15 VDC	4'000 mA	83%
TMP 60124C	24 VDC	2'500 mA	84%
TMP 60136C	36 VDC	1'665 mA	84%
TMP 60148C	48 VDC	1'250 mA	84%

- 4.41 x 2.67 x 1.50" package
- Optional pin-connector on request
- DIN-rail mount adaptor (optional)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- Over-temperature protection
- Protection against short circuit & overload
- 3 year product warranty

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	NC
4	-Vout
5	NC
6	-Vout
7	NC

## TML 100C 100 Watt



Model	Input Voltage Range	Output		Efficiency
		Vnom	I <sub>max</sub>	
TML 100-112C	85	12 VDC	7080 mA	90 %
TML 100-115C	85	15 VDC	5660 mA	90 %
TML 100-124C	100	24 VDC	4200 mA	92 %
TML 100-148C	100	48 VDC	2100 mA	93 %

- 5.50 x 2.36 x 1.48" package
- Active PFC, power factor >0.95 (230VAC), >0.99 (115 VAC)
- High efficiency up to 93% typ.
- Remote On/Off input
- Adjustable output voltage ±5%
- LED output indicator
- Universal input 100-240 VAC
- Low leakage current
- EMI meets EN 55032, class B
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- 3 year product warranty

Pinout	
Pin	Output
1	AC in (L)
2	AC in (N)
3	FG
4	Remote On/Off
5	+Vout
6	-Vout
7	Trim



# AC/DC Power Encapsulated PCB Mount

Traco Power offers a wide range of encapsulated power supplies with hundred of models available in PCB mount styles to suit a wide range of applications.


SERIES	POWER	DESCRIPTION	STATUS	APPS	PAGE
TMPS 03	3	1.00 × 1.00 × 0.64" package, 3000 VAC isolation, household	ACTIVE	🏠	110
TMLM 04	4	1.44 × 1.60 × 0.67" package, 85-264 VAC Input, 3000 VAC isolation	ACTIVE		110
TMPS 05	5	1.00 × 1.00 × 0.64" package, 3000 VAC isolation	ACTIVE	🏠	111
TMPW 5	5	1.46 × 1.08 × 0.69" package, 90-305 VAC input, 4000 VAC isolation	NEW!	🏠	111
TMG 07	7	1.07 × 1.07 × 0.74" package, 85-264 VAC input, 3000 VAC isolation	ACTIVE		112
TMP 07	7	2.00 × 1.00 × 0.77" package, 85-264 VAC Input, 3000 VAC isolation	ACTIVE		112
TMPM 10	10	2.06 × 1.07 × 0.93" package, 85-264 VAC Input, 3000 VAC isolation	ACTIVE		113
TMPS 10	10	1.50 × 1.00 × 0.62" package, 4000 VAC isolation	ACTIVE	🏠	113
TMPW 10	10	1.46 × 1.08 × 0.79" package, 90-305 VAC input, 4000 VAC isolation	NEW!	🏠	114
TMG 15	15	1.62 × 1.07 × 0.75" package, 85-264 VAC input, 3000 VAC isolation	ACTIVE		114
TMP 15	15	2.91 × 2.13 × 0.77" package, 85-264 VAC Input, 3000 VAC isolation	ACTIVE		115
TMPS 15	15	2.06 × 1.07 × 0.93" package, 3000 VAC isolation	NEW!	🏠	115
TPP 15-D	15	1.65 × 1.14 × 0.85" package, 4000 VAC isolation	ACTIVE	⊕ 🏠	116
TML 20	20	2.74 × 1.87 × 0.85" package, 85-264 VAC input, 3000 VAC isolation	ACTIVE		116
TMLM 20	20	2.06 × 1.07 × 0.93", 85-264 VAC Input, 3000 VAC isolation	ACTIVE		117
TMM 24	24	2.91 × 2.13 × 0.77" package, 85-264 VAC Input, 4000 VAC isolation	ACTIVE	⊕	117
TMPW 25	25	2.07 × 1.08 × 0.93" package, 90-305 VAC input, 4000 VAC isolation	NEW!	🏠	118
TMG 30	30	2.51 × 1.77 × 0.93" package, 85-264 VAC input, 3000 VAC isolation	ACTIVE		118
TMP 30	30	3.50 × 2.50 × 0.85" package, 85-264 VAC Input, 3000 VAC isolation	ACTIVE		119
TPP 30-D	30	2.89 × 1.50 × 1.00" package, 4000 VAC isolation	ACTIVE	⊕ 🏠	119
TML 40	40	3.20 × 2.52 × 0.98" package, 85-264 VAC input, 3000 VAC isolation	ACTIVE		120
TMM 40	40	3.50 × 2.50 × 1.18" package, 85-264 VAC Input, 4000 VAC isolation	ACTIVE	⊕	120
TMG 50	50	2.91 × 2.12 × 0.86" package, 85-264 VAC input, 3000 VAC isolation	ACTIVE		121
TMPW 50	50	2.92 × 1.85 × 0.91" package, 90-305 VAC input, 4000 VAC isolation	NEW!	🏠	121
TMM 60	60	3.50 × 2.66 × 1.34" package, 85-264 VAC Input, 4000 VAC isolation	ACTIVE	⊕	122
TMP 60	60	3.50 × 2.66 × 1.35" package, 85-264 VAC Input, 3000 VAC isolation	ACTIVE		122

APPS KEY: ⊕ = IEC/EN/ES 60601-1 (2×MOPP Approved) 🏠 = EN60335-1 Approved

# AC/DC: Encapsulated PCB Mount

## TMPS 03 3 Watt

EN 60335-1 Approved




- 1.00 x 1.00 x 0.64" package
- No load input power <150 mW, to comply with ErP directive
- Operating temperature range -25°C to +70°C
- EMI meets EN 55032, class B
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Output Current peak	Efficiency typ.
TMPS 03-103	3.3 VDC	900 mA	1170 mA	70 %
TMPS 03-105	5 VDC	600 mA	780 mA	72 %
TMPS 03-109	9 VDC	333 mA	430 mA	77 %
TMPS 03-112	12 VDC	250 mA	320 mA	78 %
TMPS 03-115	15 VDC	200 mA	260 mA	78 %
TMPS 03-124	24 VDC	125 mA	160 mA	78 %

Pin Connections	
Pin	Function
1	AC (N)
2	AC (L)
3	NC
4	-Vout
5	+Vout

## TMLM 04 4 Watt




- 1.44 x 1.06 x 0.67" package
- Fully encapsulated plastic case
- Universal input 90-264 VAC, 47-440 Hz
- High efficiency
- EMI meets EN 55022, class B & FCC, level B
- IEC/EN/UL 62368-1 approved
- Low ripple & noise
- Short circuit & overload protection
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMLM 04103	43.3 VDC	1200 mA	67%
TMLM 04105	5.0 VDC	800 mA	69%
TMLM 04109	9.0 VDC	444 mA	72%
TMLM 04112	12 VDC	333 mA	70%
TMLM 04115	15 VDC	267 mA	74%
TMLM 04124	24 VDC	167 mA	73%
TMLM 04253	+5.0 VDC / +3.3 VDC	600 mA / 150 mA	69%
TMLM 04225	+12 VDC / +5.0 VDC	250 mA / 120 mA	69%

Pin Connections		
Pin	Single	Dual
1	NC	NC
2	+Vout	Vout 1
3	-Vout	Common
4	NC	Vout 2
5	AC (L)	AC (L)
6	AC (N)	AC (N)
7	NC	NC

**TMPS 05** **5 Watt**

EN 60335-1 Approved



Model	Output Voltage nom.	Output Current max.	Output Current peak	Efficiency typ.
TMPS 05-103	3.3 VDC	1'515 mA	1'970 mA	74 %
TMPS 05-105	5 VDC	1'000 mA	1'300 mA	80 %
TMPS 05-109	9 VDC	555 mA	721 mA	82 %
TMPS 05-112	12 VDC	416 mA	540 mA	82 %
TMPS 05-115	15 VDC	333 mA	433 mA	83 %
TMPS 05-124	24 VDC	208 mA	270 mA	83 %
TMPS 05-148	48 VDC	104 mA	135 mA	85 %


- 1.00 x 1.00 x 0.64" package
- IEC/EN/UL 62368-1 approved
- <300 mW no load power (ErP directive)
- Temperature range -25°C to +70°C
- EMI meets EN 55032 class B
- EN 55014-1
- Protection class II prepared
- 3 year product warranty

Pin Connections	
Pin	Function
1	AC (N)
2	AC (L)
3	NC*
4	-Vout
5	+Vout

\* Internally not connected but keep it isolated from primary circuit

**TMPW 5** **NEW!** **5 Watt**

EN 60335-1 Approved





Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 5-103	3.3 VDC	1515 mA	73 %
TMPW 5-105	5 VDC	1000 mA	77 %
TMPW 5-112	12 VDC	420 mA	81 %
TMPW 5-124	24 VDC	210 mA	83 %

- 1.46 x 1.08 x 0.69" package
- Wide 90-305 VAC input voltage range
- I/O isolation 4000 VAC
- Temperature range: -40° to +70°C
- <0.1W no load power (ErP directive)
- EMI meets EN 55032 class B
- IEC/EN/UL 62368-1 approved
- High efficiency up to 89%
- Protection class II prepared
- 3 year product warranty

Pin Connections	
Pin	Single
1	NC
2	+Vout
3	GND
4	AC (L)
5	AC (N)

**TMG 07** **7 Watt**





Dimensions in mm  
Tolerances ±0.5 mm  
Pin tolerances ±0.1 mm

- 1.08 x 1.08 x 0.74" package
- Fully regulated outputs
- 3000 VAC I/O isolation
- High efficiency up to 80%
- Universal input range 90 to 264 VAC
- Temperature range: -40°C to +70°C
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- Short circuit over power & over voltage limitation
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMG 07105	5 VDC	1'260 mA	77%
TMG 07112	12 VDC	583 mA	80%
TMG 07115	15 VDC	466 mA	80%
TMG 07124	24 VDC	292 mA	80%

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	+Vout
5	-Vout

**TMP 07** **7 Watt**




- 2.00 x 1.00 x 0.77" package
- Fully encapsulated (pollution/dust)
- DIN-rail mount adaptor (optional)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II prepared
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- Over-temperature protection
- Protection against short circuit & overload
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMP 07103	3.3 VDC	1400 mA	70%
TMP 07105	5.0 VDC	1400 mA	73%
TMP 07112	12 VDC	583 mA	78%
TMP 07115	15 VDC	466 mA	78%
TMP 07124	24 VDC	291 mA	78%

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	+Vout
5	-Vout



**TMPM 10** **10 Watt**




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPM 10103	3.3 VDC	2500 mA	70%
TMPM 10105	5.0 VDC	2000 mA	72%
TMPM 10112	12 VDC	833 mA	76%
TMPM 10115	15 VDC	667 mA	75%
TMPM 10124	24 VDC	417 mA	72%

- 2.06 x 1.07 x 0.93” package
- Fully encapsulated (pollution/dust)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II prepared
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- Over-temperature protection
- Protection against short circuit & overload
- 3 year product warranty

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	+Vout
5	-Vout

**TMPS 10** **10 Watt**

EN 60335-1 Approved



Model	Output Voltage nom.	Output Current max.	Output Current peak	Efficiency typ.
TMPS 10-103	3.3 VDC	2'600 mA	3'380 mA	77 %
TMPS 10-105	5 VDC	2'000 mA	2'600 mA	80 %
TMPS 10-109	9 VDC	1'100 mA	1'440 mA	83 %
TMPS 10-112	12 VDC	830 mA	1'080 mA	84 %
TMPS 10-115	15 VDC	660 mA	860 mA	84 %
TMPS 10-124	24 VDC	410 mA	530 mA	86 %
TMPS 10-148	48 VDC	210 mA	270 mA	84 %

- 1.52 x 1.00 x 0.62” package
- IEC/EN/UL 62368-1 approved
- Reinforced I/O isolation 4000 VAC
- Temperature range -25°C to +70°C
- 130% peak current up to 30 s
- No load power <0.15 W (ErP directive)
- EN 55032 class B & EN 55014-1
- Protection class II prepared
- 3 year product warranty

Pin Connections	
Pin	Function
1	AC (N)
2	AC (L)
3	-Vout
4	+Vout


# AC/DC: Encapsulated PCB Mount

## TMPW 10 NEW! 10 Watt

 EN 60335-1 Approved



- 1.46 x 1.08 x 0.79" package
- 90-305 VAC input voltage range
- IEC/EN/UL 62368-1 approved
- I/O isolation 4000 VAC
- Temperature range: -40° to +70°C
- No load power <0.1 W (ErP directive)
- EMI meets EN 55032 class B
- High efficiency up to 89%
- Protection class II prepared
- 3 year product warranty




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 10-105	5 VDC	2000 mA	81 %
TMPW 10-112	12 VDC	833 mA	85 %
TMPW 10-115	15 VDC	667 mA	86 %
TMPW 10-124	24 VDC	417 mA	86 %

Pin Connections	
Pin	Single
1	NC
2	AC (N)
3	AC (L)
4	GND
5	+Vout

## TMG 15 15 Watt





- 1.62 x 1.08 x 0.75" package
- 4000 VAC I/O isolation
- High efficiency up to 85%
- Universal input range 90 to 264 VAC
- Operating temperature range: -40°C to +70°C max.
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- Protection against short-circuit, over-power & over-voltage
- 3 year product warranty



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMG 15105	5 VDC	2'700 mA	80%
TMG 15112	12 VDC	1'250 mA	84%
TMG 15115	15 VDC	1'000 mA	84%
TMG 15124	24 VDC	625 mA	85%

Pin Connections	
Pin	Single
1	AC (L)
2	AC (N)
3	-Vout
5	+Vout

**TMP 15** **15 Watt**



- 2.91 x 2.13 x 0.77" package
- Fully encapsulated (pollution/dust)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II prepared
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- Over-temperature protection
- Protection against short circuit & overload
- 3 year product warranty



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMP 15105	5 VDC	3000 mA	75%
TMP 15112	12 VDC	1250 mA	79%
TMP 15115	15 VDC	1000 mA	79%
TMP 15124	24 VDC	625 mA	79%
TMP 15148	48 VDC	310 mA	79%
TMP 15212	±12 VDC	±650 mA	79%
TMP 15215	±15 VDC	±500 mA	79%
TMP 15252	5 / 12 VDC	1500 mA / 625 mA	72%
TMP 15512	5 / ±12 VDC	2000 mA / +200 mA	74%
TMP 15515	5 / ±15 VDC	2000 mA / ±150 mA	74%

**Pin Connections**

Pin	Single	Dual (sym)	Dual (asym)	Triple
1	AC (L)	AC (L)	AC (L)	AC (L)
2	AC (N)	AC (N)	AC (N)	AC (N)
3	NC	NC	NC	Vout 3
4	-Vout	Vout 2	-Vout 2	Comm
5	NC	Comm	+Vout 2	Vout 2
6	+Vout	Vout 1	-Vout 1	-Vout 1
7	NC	NC	+Vout 1	+Vout 1

**TMPS 15** NEW! **15 Watt**

EN 60335-1 Approved



- 2.06 x 1.07 x 0.93" package
- EN 60335-1 for household appliance
- IEC/EN/UL 62368-1 approved
- I/O isolation 3000 VAC
- Temperature range -25°C to +70°C
- 130% peak current up to 30 s
- No load power <0.15 (ErP directive)
- EMI meets EN 55032 class B & EN 55014-1
- Protection class II prepared
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Output Current peak	Efficiency typ.
TMPS 15-103	3.3 VDC	3500 mA	4550 mA	75 %
TMPS 15-105	5 VDC	3000 mA	3900 mA	79 %
TMPS 15-112	12 VDC	1250 mA	1625 mA	82 %
TMPS 15-115	15 VDC	1000 mA	1300 mA	82 %
TMPS 15-124	24 VDC	625 mA	813 mA	84 %
TMPS 15-148	48 VDC	313 mA	407 mA	82 %


**Pin Connections**

Pin	Function
1	AC (N)
2	AC (L)
3	+Vout
4	-Vout

# AC/DC: Encapsulated PCB Mount

## TPP 15-D 15 Watt

- 🏠 EN 60335-1 Approved
- ⊕ IEC/EN/ES 60601-1 Approved





- 1.65 x 1.14 x 0.85" package
- 2xMOPP / BF Compliant
- <75 µA leakage
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <75 mW (ERP compliant)
- 5 year product warranty

Model	Output Voltage nom. *	*adjustable	Output Current max.	Efficiency typ.
TPP 15-103-D	3.3 VDC	2.97 - 3.63 VDC	4'000 mA	84 %
TPP 15-105-D	5 VDC	4.5 - 5.5 VDC	3'000 mA	86 %
TPP 15-109-D	9 VDC	8.1 - 9.9 VDC	1'670 mA	86 %
TPP 15-112-D	12 VDC	10.8 - 13.2 VDC	1'250 mA	87 %
TPP 15-115-D	15 VDC	13.5 - 16.5 VDC	1'000 mA	87 %
TPP 15-124-D	24 VDC	21.6 - 26.4 VDC	625 mA	88 %
TPP 15-136-D	36 VDC	32.4 - 39.6 VDC	417 mA	88 %
TPP 15-148-D	48 VDC	43.2 - 52.8 VDC	313 mA	89 %

Pin Connections	
Pin	Function
1	Neutral
2	Line
3	Trim
4	-Vout
5	+Vout

## TML 20 20 Watt



- 2.74 x 1.87 x 0.85" package
- Universal input 90-264 VAC, 47-440 Hz
- EMI meets EN 55022, class B & FCC, level B
- Short circuit & overload protection
- IEC/EN/UL 62368-1 approved
- 3 year product warranty


Model	Output Voltage nom.	Output Current max.
TML 20103	3.3 VDC	4500 mA
TML 20105	5.0 VDC	4000 mA
TML 20112	12 VDC	1670 mA
TML 20115	15 VDC	1340 mA
TML 20124	24 VDC	840 mA
TML 20205	±5.0 VDC	±2000 mA
TML 20212	±12 VDC	±833 mA
TML 20215	+12 VDC / -12 VDC	833 mA
TML 20512	5 VDC / ±12 VDC	2800 mA / ±250 mA
TML 20515	5 VDC / ±15 VDC	2800 mA / ±200 mA

Pin Connections			
Pin	Single	Dual	Triple
1	FG	FG	FG
2	AC (N)	AC (N)	AC (N)
3	AC(L)	AC(L)	AC(L)
4	NC	NC	Vout 3
5	-Vout	Vout 2	Comm
6	NC	Comm	Vout 2
7	+Vout	+Vout 1	-Vout 1
8	NC	NC	+Vout 1



TMLM 20

20 Watt



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMLM 20103	3.3 VDC	3600 mA	74%
TMLM 20105	5.0 VDC	3600 mA	78%
TMLM 20112	12 VDC	1660 mA	82%
TMLM 20115	15 VDC	1330 mA	83%
TMLM 20124	24 VDC	833 mA	83%


- 2.06 x 1.07 x 0.93" package
- Fully encapsulated plastic case
- Universal input 90-264 VAC, 47-440 Hz
- EMI meets EN 55022, class B & FCC, level B
- Protection class II prepared
- Low ripple & noise
- Protection against short circuit & overload
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Pin Connections	
Pin	Single
1	AC
2	AC
3	-Vout
4	+Vout

TMM 24

24 Watt

⊕ IEC/EN/ES 60601-1 Approved



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMM 24105	5 VDC	3'000 mA	77%
TMM 24112	12 VDC	2'000 mA	83%
TMM 24115	15 VDC	1'600 mA	82%
TMM 24124	24 VDC	1'000 mA	85%
TMM 24212	±12 VDC	±1'000 mA	84%
TMM 24215	±15 VDC	±800mA	84%

- 2.91 x 2.13 x 0.77" package
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- ErP Ready (<0.3 W no-load power consumption)
- -40°C start-up temperature
- Protection class II prepared
- Protection against over temperature, overload & short circuit
- 3 year product warranty

Pin Connections		
Pin	Single	Dual
1	AC (N)	AC (N)
2	AC (L)	AC (L)
4	-Vout	-Vout
5	NC	Comm
6	+Vout	+Vout

# AC/DC: Encapsulated PCB Mount

TMPW 25



**NEW!**

25 Watt

EN 60335-1 Approved



- 2.07 x 1.08 x 0.93" package
- 90-305 VAC input voltage range
- IEC/EN/UL 62368-1 approved
- I/O isolation 4000 VAC
- Temperature range: -40°C to +70°C
- No load power <0.1W (ErP directive)
- EMI meets EN 55032 class B
- High efficiency up to 89%
- Protection class II prepared
- 3 year product warranty



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 25-105	5.1 VDC	3922 mA	84 %
TMPW 25-112	12 VDC	2083 mA	88 %
TMPW 25-115	15 VDC	1666 mA	88 %
TMPW 25-124	24 VDC	1042 mA	87 %


Pin Connections	
Pin	Function
1	AC (L)
2	AC (N)
3	+Vout
4	-Vout

TMG 30

30 Watt



- 2.52 x 1.77 x 0.93" package
- Fully regulated outputs
- I/O isolation 3000 VAC
- High efficiency up to 89%
- Universal input range 90 to 305 VAC
- 40°C to +70°C temperature range
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- Protection against short circuit, over power & over voltage
- 3 year product warranty




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMG 30103	3.3 VDC	5'000 mA	80%
TMG 30105	5 VDC	5'000 mA	84%
TMG 30112	12 VDC	2'500 mA	89%
TMG 30115	15 VDC	2'000 mA	86%
TMG 30124	24 VDC	1'250 mA	86%

Pin Connections	
Pin	Function
1	AC (N)
2	AC (L)
3	-Vout
4	+Vout

TMP 30

30 Watt



- 3.50 x 2.50 x 0.85" package
- Optional pin-connector on request
- DIN-rail mount adaptor (optional)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II prepared
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- Over-temperature protection
- Protection against short circuit & overload
- 3 year product warranty


Model	Output Voltage nom.	Output Current max.	Eff typ.
TMP 30105	5 VDC	6000 mA	78%
TMP 30112	12 VDC	2500 mA	80%
TMP 30115	15 VDC	2000 mA	80%
TMP 30124	24 VDC	1250 mA	80%
TMP 30148	48 VDC	625 mA	80%
TMP 30212	±12 VDC	±1300 mA	80%
TMP 30215	±15 VDC	±1000 mA	80%
TMP 30252	5.0VDC / ±12 VDC	3000 mA2) / ±1250 mA	76%
TMP 30316	3.3 / +5 / +12VDC	4000 / 1500 / 250 mA	71%
TMP 30317	5 / +3.3 / +12 VDC	4500 / 1000 / 250 mA	71%
TMP 30512	5 / ±12 VDC	3000 / ±600 mA	76%
TMP 30515	5 / ±15 VDC	3000 / ±500 mA	76%
TMP 30522	5 / ±12 VDC	3000 / +1000 / -250 mA	76%

Pin Connections				
Pin	Single	Dual (sym)	Dual (asym)	Triple
1	AC (L)	AC (L)	AC (L)	AC (L)
2	AC (N)	AC (N)	AC (N)	AC (N)
3	+Vout	Vout 1	+Vout 2	Vout2
4	NC	NC	+Vout 1	+Vout 1
5	-Vout	Comm	-Vout2	Comm
6	NC	NC	-Vout 1	-Vout 1
7	NC	Vout 2	NC	Vout 3

TPP 30-D

30 Watt

- 🏠 EN 60335-1 Approved
- ⊕ IEC/EN/ES 60601-1 Approved



- 2.89 x 1.50 x 1.00" package
- 2xMOPP / BF Compliant
- <75 µA leakage
- IEC 60601-1-2 4th edition EMC
- IEC/EN/UL 62368-1 approved
- ISO 14971 risk management file
- IPC-A-610 Level 3 acceptance criteria
- Protection class II prepared
- Operating up to 5000 m altitude
- no load power <60 mW (ErP compliant)
- 5 year product warranty

Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 30-103-D	3.3 VDC (2.97 - 3.63 VDC)	6'000 mA	84 %
TPP 30-105-D	5 VDC (4.5 - 5.5 VDC)	6'000 mA	87 %
TPP 30-109-D	9 VDC (8.1 - 9.9 VDC)	3'340 mA	88 %
TPP 30-112-D	12 VDC (10.8 - 13.2 VDC)	2'500 mA	91 %
TPP 30-115-D	15 VDC (13.5 - 16.5 VDC)	2'000 mA	91 %
TPP 30-124-D	24 VDC (21.6 - 26.4 VDC)	1'250 mA	90 %
TPP 30-136-D	36 VDC (32.4 - 39.6 VDC)	840 mA	90 %
TPP 30-148-D	48 VDC (43.2 - 52.8 VDC)	630 mA	92 %

PCB Pinout	
Pin	Function
1	Neutral
2	Line
3	+Vout
4	-Vout
5	Trim






TMG 50

50 Watt



- 2.92 x 2.13 x 0.86" package
- Fully regulated outputs
- 3000 VAC I/O isolation
- High efficiency up to 90%
- Universal input range 90 to 264 VAC
- -40°C to +70°C temperature range
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- Protection against short circuit, over power & over voltage
- 3 year product warranty



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMG 50105	5 VDC	8'000 mA	86%
TMG 50112	12 VDC	4'167 mA	90%
TMG 50115	15 VDC	3'333 mA	87%
TMG 50124	24 VDC	2'083 mA	88%
TMG 50148	48 VDC	1'040 mA	89%

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	-Vout
4	+Vout

TMPW 50


**NEW!**

50 Watt

EN 60335-1 Approved



- 2.92 x 1.85 0.91" package
- Wide 90-305 VAC input voltage range
- EC/EN/UL 62368-1 approved
- I/O isolation 4000 VAC
- Temperature range: -40° to +70°C
- No load power <0.1W (ErP directive)
- EMI meets EN 55032 class B
- High efficiency up to 89%
- Protection class II prepared
- 3 year product warranty




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMPW 50-112	12 VDC	4167 mA	89 %
TMPW 50-115	15 VDC	3333 mA	88 %
TMPW 50-124	24 VDC	2083 mA	88 %

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	-Vout
4	+Vout

# AC/DC: Encapsulated PCB Mount

## TMM 60 60 Watt

⊕ IEC/EN/ES 60601-1 Approved




- 3.50 x 2.66 x 1.34" package
- 2xMOPP / BF compliant
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- IEC/EN/UL 60950-1 / 62368-1 approved
- <0.3 W no load power (ErP ready)
- Protection class II prepared
- Protection against over temperature, overload & short circuit
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMM 60105	5.1 VDC	10'000 mA	84%
TMM 60112	12 VDC	5'000 mA	87%
TMM 60115	15 VDC	4'000 mA	87%
TMM 60124	24 VDC	2'500 mA	87%
TMM 60148	48 VDC	1'250 mA	88%

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	+Vout
4	-Vout

## TMP 60 60 Watt



- 3.50 x 2.66 x 1.35" package
- Fully encapsulated (pollution/dust)
- Universal input 85-264 VAC, 47-440 Hz
- Protection class II prepared
- IEC/EN/UL 60950-1 approval
- IEC/EN/UL 62368-1 approval
- Over-temperature protection
- Protection against short circuit & overload
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMP 60112	12 VDC	5'000 mA	82%
TMP 60105	5.1 VDC	10'000 mA	79%
TMP 60115	15 VDC	4'000 mA	83%
TMP 60124	24 VDC	2'500 mA	84%
TMP 60136	36 VDC	1'665 mA	84%
TMP 60148	48 VDC	1'250 mA	84%

Pin Connections	
Pin	Single
1	AC (N)
2	AC (L)
3	NC
4	-Vout
5	NC
6	-Vout
7	NC

# AC/DC: Open-Frame Power Supplies


Traco Power offers a wide range of open-frame power supplies with hundreds of models available in PCB mount styles to suit a wide range of applications.

SERIES	POWER	DESCRIPTION	STATUS	APPS	PAGE
TPP 15A-D	15	1.50 × 1.00 × 1.02" open-frame package, 4000 VAC isolation, PCB mount	ACTIVE	⊕ 🏠	124
TPP 15A-J	15	2.60 × 1.00" × 0.72" open-frame package, 4000 VAC isolation	ACTIVE	⊕ 🏠	124
TPI 30A-J	30	3.34 × 1.36 × 0.77" open-frame package, 3000 VAC isolation, cost efficient	<b>NEW!</b>		125
TPP 30A-D	30	2.74 × 1.36 × 1.10" open-frame package, 4000 VAC isolation, PCB mount	ACTIVE	⊕ 🏠	125
TPP 30A-JP	30	3.34 × 1.34 × 0.88" open-frame package, 4000 VAC isolation	ACTIVE	⊕ 🏠	126
TPP 40A	40	3.00 × 2.00 × 0.94" open-frame package, 4000 VAC isolation	ACTIVE	⊕	126
TPI 65A-JP	65	3.00 × 2.00 × 0.94" open-frame package, 3000 VAC isolation, cost efficient	<b>NEW!</b>		127
TPP 65A	65	3.00 × 2.00 × 0.94" open-frame package, 4000 VAC isolation	ACTIVE	⊕	127
TPI 100A	100	3.00 × 2.00 × 1.16" open-frame package, 3000 VAC isolation	ACTIVE		128
TPP 100A-J	100	3.00 × 2.00 × 1.16" open-frame package, 4000 VAC isolation	ACTIVE	⊕	128
TXH 120	120	5.35 × 3.23 × 1.50" u-frame package, 4000 VAC isolation	ACTIVE		129
TPI 125A	125	3.00 × 2.00 × 1.16" open-frame package, 3000 VAC isolation	<b>NEW!</b>		129
TPI 150A	150	4.00 × 2.00 × 1.16" open-frame package, 3000 VAC isolation	ACTIVE		130
TPP 150A-J	150	4.00 × 2.00 × 1.16" open-frame package, 4000 VAC isolation	ACTIVE	⊕	130
TPP 180A	180	3.00 × 2.00 × 1.16" open-frame package, 4000 VAC isolation	<b>COMING SOON!</b>	⊕	131
TXH 240	240	5.91 × 4.17 × 1.38" u-frame package, 4000 VAC isolation	ACTIVE		131
TPP 250A	250	4.00 × 2.00 × 1.25" open-frame package, 4000 VAC isolation	<b>COMING SOON!</b>	⊕	132
TPP 300A	300	4.00 × 2.00 × 1.16" open-frame package, 4000 VAC isolation	<b>COMING SOON!</b>	⊕	132
TPP 450A-M	450	5.00 × 3.00 × 1.58" open-frame + baseplate package, 4000 VAC isolation	ACTIVE	⊕	133
TPP 600A	600	5.00 × 3.00 × 1.50" open-frame package, 4000 VAC isolation	<b>COMING SOON!</b>	⊕	133
TPP 850A	850	4.00 × 6.0 × 1.50" open-frame package, 4000 VAC isolation	<b>COMING SOON!</b>	⊕	134

**APPS KEY:** ⊕ = IEC/EN/ES 60601-1 (2×MOPP Approved) 🏠 = EN60335-1 Approved (Household Appliance)

**TPP 15A-D** **15 Watt**

EN 60335-1 Approved  
 IEC/EN/ES 60601-1 Approved




- 1.50 x 1.00 x 1.02" package
- 2 x MOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- Low leakage <75 µA
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria To IPC-A-610 Level 3
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <75 mW (ERP Ready)
- 5 year product warranty

PCB Pinout	
Pin	Function
1	Neutral
2	Line
3	Trim
4	-Vout
5	+Vout

Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 15-103A-D	3.3 VDC (2.97 - 3.63 VDC)	4'000 mA	84 %
TPP 15-105A-D	5 VDC (4.5 - 5.5 VDC)	3'000 mA	86 %
TPP 15-109A-D	9 VDC (8.1 - 9.9 VDC)	1'670 mA	86 %
TPP 15-112A-D	12 VDC (10.8 - 13.2 VDC)	1'250 mA	87 %
TPP 15-115A-D	15 VDC (13.5 - 16.5 VDC)	1'000 mA	87 %
TPP 15-124A-D	24 VDC (21.6 - 26.4 VDC)	625 mA	88 %
TPP 15-136A-D	36 VDC (32.4 - 39.6 VDC)	417 mA	88 %
TPP 15-148A-D	48 VDC (43.2 - 52.8 VDC)	313 mA	89 %

**TPP 15A-J** **15 Watt**

EN 60335-1 Approved  
 IEC/EN/ES 60601-1 Approved



- 2.61 x 1.00 x 0.72" package
- 2 x MOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- Low leakage <75 µA
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <75 mW (ERP Ready)
- 5 year product warranty

Pin Connectors			
Input		Output	
Pin	Function	Pin	Function
1	Line	1	-Vout
3	Neutral	2	+Vout


Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 15-103A-J	3.3 VDC (2.97 - 3.63 VDC)	4'000 mA	84 %
TPP 15-105A-J	5 VDC (4.5 - 5.5 VDC)	3'000 mA	86 %
TPP 15-109A-J	9 VDC (8.1 - 9.9 VDC)	1'670 mA	86 %
TPP 15-112A-J	12 VDC (10.8 - 13.2 VDC)	1'250 mA	87 %
TPP 15-115A-J	15 VDC (13.5 - 16.5 VDC)	1'000 mA	87 %
TPP 15-124A-J	24 VDC (21.6 - 26.4 VDC)	625 mA	88 %
TPP 15-136A-J	36 VDC (32.4 - 39.6 VDC)	417 mA	88 %
TPP 15-148A-J	48 VDC (43.2 - 52.8 VDC)	313 mA	89 %



TPI 30A-JP

**NEW!**

30 Watt



- 3.34 x 1.36 x 0.77" package
- I/O reinforced isolation 3000 VAC
- IEC/EN/UL 62368-1 approved
- 120% peak power for 5 secs
- < 0.3 W no load power (ErP ready)
- Efficiency up to 90%
- Protection class II prepared
- Operating up to 5000 m altitude
- Adjustable output voltage
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPI 30-103A-JP	3.3 VDC	6'000 mA	83 %
TPI 30-105A-JP	5 VDC	6'000 mA	86 %
TPI 30-109A-JP	9 VDC	3'340 mA	87 %
TPI 30-112A-JP	12 VDC	2'500 mA	88.5 %
TPI 30-115A-JP	15 VDC	2'000 mA	88.5 %
TPI 30-124A-JP	24 VDC	1'250 mA	88 %
TPI 30-136A-JP	36 VDC	840 mA	89 %
TPI 30-148A-JP	48 VDC	630 mA	90.5 %


**Connectors - Connection**

CON1 - Input Connector	
Pin 1	Line
Pin 3	Neutral
CON2 - Output Connector	
Pin 1	+Vout
Pin 2	-Vout

TPP 30A-D

30 Watt

- 🏠 EN 60335-1 Approved
- ⊕ IEC/EN/ES 60601-1 Approved



- 2.74 x 1.36 x 1.10" package
- 2 x MOPP / BF compliant
- Low leakage <75  $\mu$ A
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- Protection class II prepared
- No load power <60 mW (ERP Ready)
- 5 year product warranty


Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 30-103A-D	3.3 VDC (2.97 - 3.63 VDC)	6'000 mA	84 %
TPP 30-105A-D	5 VDC (4.5 - 5.5 VDC)	6'000 mA	87 %
TPP 30-109A-D	9 VDC (8.1 - 9.9 VDC)	3'340 mA	88 %
TPP 30-112A-D	12 VDC (10.8 - 13.2 VDC)	2'500 mA	91 %
TPP 30-115A-D	15 VDC (13.5 - 16.5 VDC)	2'000 mA	91 %
TPP 30-124A-D	24 VDC (21.6 - 26.4 VDC)	1'250 mA	90 %
TPP 30-136A-D	36 VDC (32.4 - 39.6 VDC)	840 mA	90 %
TPP 30-148A-D	48 VDC (43.2 - 52.8 VDC)	630 mA	92 %

**PCB Pinout**

Pin	Function
1	Neutral
2	Line
3	+Vout
4	-Vout
5	Trim

## TPP 30A-J 30 Watt

- 🏠 EN 60335-1 Approved
- ⊕ IEC/EN/ES 60601-1 Approved




- 3.34 x 1.34 x 0.88" package
- 2 x MOPP / BF compliant
- Low leakage <75  $\mu$ A
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <60 mW (ERP Ready)
- 5 year product warranty

Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 30-103A-J	3.3 VDC (2.97 - 3.63 VDC)	6'000 mA	84 %
TPP 30-105A-J	5 VDC (4.5 - 5.5 VDC)	6'000 mA	87 %
TPP 30-109A-J	9 VDC (8.1 - 9.9 VDC)	3'340 mA	88 %
TPP 30-112A-J	12 VDC (10.8 - 13.2 VDC)	2'500 mA	91 %
TPP 30-115A-J	15 VDC (13.5 - 16.5 VDC)	2'000 mA	91 %
TPP 30-124A-J	24 VDC (21.6 - 26.4 VDC)	1'250 mA	90 %
TPP 30-136A-J	36 VDC (32.4 - 39.6 VDC)	840 mA	90 %
TPP 30-148A-J	48 VDC (43.2 - 52.8 VDC)	630 mA	92 %

Pin Connectors			
Input		Output	
Pin	Function	Pin	Function
1	Line	1	+Vout
3	Neutral	2	-Vout

## TPP 40A 40 Watt

- ⊕ IEC/EN/ES 60601-1 Approved



- 3.00 x 2.00 x 0.94" package
- 2 x MOPP / BF compliant
- Low leakage <75  $\mu$ A
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <150 mW (ERP Ready)
- 5 year product warranty

Model	Output Voltage nom. (adjustable)	Output 2	Efficiency
TPP 40-105A-J	5 VDC (4.5 - 5.5 VDC)	8000 mA	90 %
TPP 40-112A-J	12 VDC (10.8 - 13.2 VDC)	3340 mA	92 %
TPP 40-124A-J	24 VDC (21.6 - 26.4 VDC)	1670 mA	92 %
TPP 40-148A-J	48 VDC (43.2 - 52.8 VDC)	840 mA	93 %

Note - Other output models are available on request.

Screw Terminal			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

\*Terminal rated for 7 A max. (at higher current connection has to be split)


**CON1:** JST series  
mates with JST crimp terminal: BVH-21T-P1.1  
& terminal housing: VHR-3N

**CON2:** JST series  
mates with JST crimp terminal: BVH-21T-P1.1  
& terminal housing: VHR-4N

TPI 65A-JP

**NEW!**

65 Watt



- 3.00 x 2.00 x 0.94" package
- I/O reinforced isolation 3000 VAC
- IEC/EN/UL 62368-1 approved
- 130% peak power up to 5 secs
- < 0.3 W no load power (Erp ready)
- Efficiency up to 93%
- Protection class II prepared
- Operating up to 5000 m altitude
- Adjustable output voltage
- 3 year product warranty


Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPI 65-105A-JP	5 VDC	10 A	90 %
TPI 65-109A-JP	9 VDC	7.23 A	91 %
TPI 65-112A-JP	12 VDC	5.42 A	92.5 %
TPI 65-115A-JP	15 VDC	4.34 A	93.5 %
TPI 65-124A-JP	24 VDC	2.71 A	93.5 %
TPI 65-136A-JP	36 VDC	1.81 A	92.5 %
TPI 65-148A-JP	48 VDC	1.36 A	93 %

Connectors - Connection			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

TPP 65A

65 Watt

⊕ IEC/EN/ES 60601-1 Approved



- 3.00 x 2.00 x 0.94" package
- 2xMOPP / BF compliant
- Low leakage <75 μA (BF rated)
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <150 mW (ERP Ready)
- 5 year product warranty

Model	Output Voltage nom. (adjustable)	Output 2	Efficiency
TPP 65-105A-J	5 VDC (4.5 - 5.5 VDC)	10000 mA	90 %
TPP 65-112A-J	12 VDC (10.8 - 13.2 VDC)	5420 mA	93 %
TPP 65-124A-J	24 VDC (21.6 - 26.4 VDC)	2710 mA	94 %
TPP 65-148A-J	48 VDC (43.2 - 52.8 VDC)	1360 mA	93 %

Note  
- Other output models are available on request.


Connectors - Connection			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

\*Terminal rated for 7 A max. (at higher current connection has to be split)

CON1: JST series  
mates with JST crimp terminal: BVH-21T-P1.1  
& terminal housing: VHR-3N

CON2: JST series  
mates with JST crimp terminal: BVH-21T-P1.1  
& terminal housing: VHR-4N

**TPI 100A** **100 Watt**



- 3.00 x 2.00 x 1.16" package
- I/O reinforced isolation 3000 VAC
- IEC/EN/UL 62368-1 approved
- < 0.3 W no load power (ErP ready)
- High efficiency 91% - 92%
- Active power factor correction > 95
- Protection class II prepared
- Operating up to 5000 m altitude
- Adjustable output voltage
- 3 year product warranty


Pin connectors			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1,2	-Vout
3	Neutral	3,4	+Vout

\*Terminal rated for 10 A max.  
(at higher current connection has to be split)

Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPI 100-112A-J	12 VDC (10.8 - 13.2 VDC)	8'340 mA	91 %
TPI 100-115A-J	15 VDC (13.5 - 16.5 VDC)	6'670 mA	92 %
TPI 100-124A-J	24 VDC (21.6 - 26.4 VDC)	4'170 mA	92 %
TPI 100-128A-J	28 VDC (25.2 - 30.8 VDC)	3'580 mA	92 %
TPI 100-136A-J	36 VDC (32.4 - 39.6 VDC)	2'780 mA	91 %
TPI 100-148A-J	48 VDC (43.2 - 52.8 VDC)	2'090 mA	91 %

**TPP 100A-J** **100 Watt**

⊕ IEC/EN/ES 60601-1 Approved



- 3.00 x 2.00 x 1.16" package
- 2xMOPP / BF compliant
- Low leakage <75 µA
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- Acceptance criteria. to IPC-A-610 Level 3
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <300 mW (ERP Ready)
- 5 year product warranty

Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 100-112A-J	12 VDC (10.8 - 13.2 VDC)	8340 mA	91 %
TPP 100-115A-J	15 VDC (13.5 - 16.5 VDC)	6670 mA	92 %
TPP 100-124A-J	24 VDC (21.6 - 26.4 VDC)	4170 mA	92 %
TPP 100-128A-J	28 VDC (25.2 - 30.8 VDC)	3580 mA	92 %
TPP 100-136A-J	36 VDC (32.4 - 39.6 VDC)	2780 mA	91 %
TPP 100-148A-J	48 VDC (43.2 - 52.8 VDC)	2090 mA	91 %

Screw Terminal			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

\*Terminal rated for 7 A max. (at higher current connection has to be split)


CON1: JST series  
mates with JST crimp terminal: BVH-21T-P1.1  
& terminal housing: VHR-3N

CON2: JST series  
mates with JST crimp terminal: BVH-21T-P1.1  
& terminal housing: VHR-4N



TXH 120

120 Watt



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXH 120-112	12 VDC	10'000 mA	90%
TXH 120-124	24 VDC	5'000 mA	93%
TXH 120-148	48 VDC	2'500 mA	93%

\* Optional Cover: TXH 120-COV


- 5.35 x 3.23 x 1.50" package
- U-bracket power supplies with optional cover
- Universal input range 90 to 264 VAC
- 4000 VAC I/O isolation
- IEC/EN/UL 62368-1 approved
- High efficiency up to 93 %
- Temperature range: -25°C to +70°C max.
- Features active power factor correction
- Protection against over current, short circuit & over voltage
- 3 year product warranty

Pin Connections	
Pin	Single
1	AC (L)
2	AC (N)
3	PE
4-5	+Vout
6-7	-Vout

TPI 125

**NEW!**

125 Watt




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPI 125-112A-J	12 VDC	10'420 mA	91 %
TPI 125-115A-J	15 VDC	8'340 mA	92 %
TPI 125-124A-J	24 VDC	5'210 mA	92 %
TPI 125-136A-J	36 VDC	3'480 mA	91 %
TPI 125-148A-J	48 VDC	2'610 mA	91 %

- 3.00 x 2.00 x 1.16" package
- Compact & cost efficient design
- Peak power function up to 120%
- I/O reinforced isolation 3000 VAC
- Temperature range -40°C to +85°C
- No load power <0.3W (ErP Ready)
- High efficiency up to 92%
- Internal EN 55032 class B filter
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- 3 year product warranty

Pin Connections	
Pin	Single
in 1	AC (L)
in 3	AC (N)
Out 1-2	-Vout
Out 3-4	+Vout

TPI 150A 150 Watt



Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPI 150-112A-J	12 VDC (10.8 - 13.2 VDC)	12'500 mA	91 %
TPI 150-115A-J	15 VDC (13.5 - 16.5 VDC)	10'000 mA	92 %
TPI 150-124A-J	24 VDC (21.6 - 26.4 VDC)	6'250 mA	92 %
TPI 150-128A-J	28 VDC (25.2 - 30.8 VDC)	5'360 mA	92 %
TPI 150-136A-J	36 VDC (32.4 - 39.6 VDC)	4'170 mA	92 %
TPI 150-148A-J	48 VDC (43.2 - 52.8 VDC)	3'130 mA	92 %


- 4.00 x 2.00 x 1.16" package
- I/O reinforced isolation 3000 VAC
- IEC/EN/UL 62368-1 approved
- < 0.3 W no load power (ErP Ready)
- High efficiency - 91-92%
- Active power factor correction > 95
- Protection class II prepared
- Operating up to 5000 m altitude
- Adjustable output voltage
- 3 year product warranty

Pin connectors					
Input (CON1)		Output (CON2)		Fan (CON3)	
Pin	Function	Pin*	Function	Pin	Function
1	Line	1-3	-Vout	1	-Fan
3	Neutral	4-6	+Vout	2	+Fan

\*Terminal rated for 10 A max. (at higher current connection has to be split)

TPP 150A-J 150 Watt

⊕ IEC/EN/ES 60601-1 Approved



Model	Output Voltage nom. (adjustable)	Output Current max. (Forced air cooling)	Efficiency typ.
TPP 150-112A-J	12 VDC (10.8 - 13.2 VDC)	12'500 mA	91 %
TPP 150-115A-J	15 VDC (13.5 - 16.5 VDC)	10'000 mA	92 %
TPP 150-124A-J	24 VDC (21.6 - 26.4 VDC)	6'250 mA	92 %
TPP 150-128A-J	28 VDC (25.2 - 30.8 VDC)	5'360 mA	92 %
TPP 150-136A-J	36 VDC (32.4 - 39.6 VDC)	4'170 mA	92 %
TPP 150-148A-J	48 VDC (43.2 - 52.8 VDC)	3'130 mA	92 %

Output Current max. (Natural convection):

- 8340 mA
- 7340 mA
- 4590 mA
- 3930 mA
- 3060 mA
- 2090 mA

\*Terminal rated for 7 A max. (at higher current connection has to be split)

- 4.00 x 2.00 x 1.16" package
- 2 x MOPP / BF compliant
- Low leakage <75 μA
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- IPC-A-610 Level 3 acceptance criteria
- IEC/EN/UL 62368-1 approved
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <300 mW (ERP Ready)
- 5 year product warranty

Pin connectors					
Input (CON1)		Output (CON2)		Input (CON3)	
Pin	Function	Pin*	Function	Pin	Function
1	Line	1-3	-Vout	1	-Fan
3	Neutral	4-6	+Vout	2	+Fan


CON1: JST series mates with JST crimp terminal: SVH-21T-P1.1 & terminal housing: VHR-3N

CON2: JST series mates with JST crimp terminal: SVH-21T-P1.1 & terminal housing: VHR-6N

CON3: Molex series mates with Molex crimp terminals: 2759 & Molex housing: 22-01-1022

**TPP 180A** **NEW - under development** **180 Watt**

⊕ IEC/EN/ES 60601-1 Approved




- 3.00 x 2.00 x 1.16" package
- 2xMOPP / BF compliant
- Low leakage <100 μA
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- IPC-A-610 Level 3 acceptance criteria
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <300 mW (ERP Ready)
- 5 year product warranty

Screw Terminal			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPP 180-112A-M	12 VDC	15 A	92%
TPP 180-115A-M	15 VDC	12 A	92%
TPP 180-124A-M	24 VDC	7.5 A	94%
TPP 180-128A-M	28 VDC	6.4 A	93%
TPP 180-136A-M	36 VDC	5 A	93%
TPP 180-148A-M	48 VDC	3.75 A	93%

**TXH 240** **240 Watt**



- 5.91 x 4.17 x 1.38" package
- U-frame style with optional cover
- Universal input range 90 to 264 VAC
- 4000 VAC I/O isolation
- IEC/EN/UL 62368-1 approved
- High efficiency up to 93 %
- Temperature range: -10°C to +70°C
- Active power factor correction
- Short circuit & over voltage protection


Pin Connections	
Pin	Single
1	AC (L)
2	AC (N)
3	PE
4-5	+Vout
6-7	-Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXH 240-112	12 VDC	20'000 mA	90%
TXH 240-124	24 VDC	10'000 mA	92%
TXH 240-148	48 VDC	5'000 mA	93%

\* Optional Cover: TXH 240-COV

**TPP 250** **NEW - under development** **250 Watt**

⊕ IEC/EN/ES 60601-1 Approved




- 4.00 x 2.00 x 1.25" package
- 2 x MOPP / BF compliant
- Low leakage <100 μA
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- IPC-A-610 Level 3 acceptance criteria
- Protection class I & II prepared
- Operating up to 5000 m altitude
- No load power <500mW (ERP Ready)
- 12V Fan Output
- 5 year product warranty

Pin Connections	
Pin	Single
1	AC (L)
2	AC (N)
3	-Vout
4	NC
5	+Vout

Model	Output Voltage nom.	Output Current max.
TPP 250-112A-M	12 VDC	20.8 A
TPP 250-115A-M	15 VDC	16.7 A
TPP 250-124A-M	24 VDC	10.4 A
TPP 250-128A-M	28 VDC	8.9 A
TPP 250-136A-M	36 VDC	6.9 A
TPP 250-148A-M	48 VDC	5.8 A

**TPP 300A** **NEW - under development** **300 Watt**

⊕ IEC/EN/ES 60601-1 Approved



- 4.00 x 2.00 x 1.16" package
- 2xMOPP / BF compliant
- Low leakage <100 μA
- IEC/EN/UL 62368-1 approved
- IEC 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- IPC-A-610 Level 3 acceptance criteria
- Protection class II prepared
- Operating up to 5000 m altitude
- No load power <300mW (ERP Ready)
- 5 year product warranty

Pin connectors			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1-3	-Vout
3	Neutral	4-6	+Vout
Input (CON3)			
Pin	Function		
1	-Fan		
2	+Fan		


Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPP 300-112A-M	12 VDC	25 A	91%
TPP 300-115A-M	15 VDC	20 A	91%
TPP 300-124A-M	24 VDC	12.5 A	92%
TPP 300-128A-M	28 VDC	10.7 A	92%
TPP 300-136A-M	36 VDC	8.3 A	93%
TPP 300-148A-M	48 VDC	6.25 A	93%



TPP 450A

450 Watt

⊕ IEC/EN/ES 60601-1 Approved



- 5.00 x 3.00 x 1.58" package
- Optional Class II operation (BA-M Models)
- Open-Frame with baseplate style
- 450 Watt with forced air cooling (320 Watt convection)
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 / 60950-1 approved
- IEC/EN 60601-1-2 4th edition EMC
- ISO 14971 risk management file
- IPC-A-610 class 3 Acceptance
- 5 V Standby output, 12 V fan output with variable fan speed, Remote On/Off, Power Good Signal
- 5 year product warranty


Model	Output Voltage nom. (adjustable)	Output Current max. (Forced air cooling)	Efficiency typ.
<b>Class I Safety Approved Models</b>			
TPP 450-112A-M	12 VDC (11.0 - 13.0 VDC)	37'500 mA	91 %
TPP 450-115A-M	15 VDC (13.8 - 16.2 VDC)	30'000 mA	92 %
TPP 450-124A-M	24 VDC (22.1 - 25.9 VDC)	18'750 mA	93 %
TPP 450-128A-M	28 VDC (25.8 - 30.2 VDC)	16'100 mA	93 %
TPP 450-136A-M	36 VDC (33.1 - 38.9 VDC)	12'500 mA	93 %
TPP 450-148A-M	48 VDC (44.2 - 51.8 VDC)	9'400 mA	94 %
TPP 450-153A-M	53 VDC (48.8 - 57.2 VDC)	8'550 mA	94 %
<b>Class II Safety Approved Models</b>			
TPP 450-112BA-M	12 VDC (11.0 - 13.0 VDC)	37'500 mA	91 %
TPP 450-115BA-M	15 VDC (13.8 - 16.2 VDC)	30'000 mA	92 %
TPP 450-124BA-M	24 VDC (22.1 - 25.9 VDC)	18'750 mA	93 %
TPP 450-128BA-M	28 VDC (25.8 - 30.2 VDC)	16'100 mA	93 %
TPP 450-136BA-M	36 VDC (33.1 - 38.9 VDC)	12'500 mA	93 %
TPP 450-148BA-M	48 VDC (44.2 - 51.8 VDC)	9'400 mA	94 %
TPP 450-153BA-M	53 VDC (48.8 - 57.2 VDC)	8'550 mA	94 %

Input		Auxiliary	
CON1		Pin	Function
Pin	Function	1	+Fan
1	AC (L)	2	+Sense
3	AC (N)	3	+Remote
CON2		4	PG
Output		5	+Standby
CON2		6	-Fan
Pin*	Function	7	-Sense
1-5	+Vout	8	-Remote
6-10	-Vout	9	No Pin
		10	-Standby

TPP 600A **NEW - under development**

600 Watt

⊕ IEC/EN/ES 60601-1 Approved



- 3.00 x 5.00 x 1.50" open frame
- 600W with forced air cooling
- Up to 300W convection cooled
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC/EN 60601-1-2 4th ed. (EMC)
- ISO 14971 risk management file
- Protection class I / II prepared
- Low leakage current <100 μA
- ErP compliant (<0.5 W no load)
- 5Vsb, 12V smart fan, Remote On/Off, & DC OK signals
- 5 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPP 600-124A-M	24 VDC	25.0 A	94%
TPP 600-128A-M	28 VDC	21.4 A	
TPP 600-136A-M	36 VDC	16.7 A	
TPP 600-148A-M	48 VDC	12.5 A	

Input J8		Auxiliary J3	
Pin	Function	Pin	Function
1	AC (L)	1	+5V
3	AC (N)	2	COMM
Output J5 / J6		3	+Remote
Pin*	Function	<b>Fan J4</b>	
RED	+Vout	Pin	Function
BLK	-Vout	1	+12V
		2	Return

**Input Connector:**  
 J8 = Molex KK 396, PCB Header 41791  
 (PE : J1) = (PE 6.3x0.8mm DIN 46244 Vertical Tab)

**Output Connector(s) :**  
 J5, J6 = Keystone 8199-X


**Signal Connector :**  
 J3 = TE MTA-100, PCB Header 640457-4

**FAN Connector**  
 J4 = Molex KK 254, PCB Header 22-27-2021

⊕ IEC/EN/ES 60601-1 Approved



- 4.00 x 6.00 1.50" open frame
- 850W with forced air cooling
- Up to 360W convection cooled
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC/EN 60601-1-2 4th ed. (EMC)
- ISO 14971 risk management file
- ErP compliant (<0.5 W no load)
- Protection class I / II prepared
- Class I Low leakage current <100 μA
- 5Vsb, 12V smart fan, Remote On/Off, & DC OK signals
- 5 year product warranty



Auxiliary	
J3	
Pin	Function
1	+5V
2	Common
3	PWM Fan
4	DC OK
5	Remote
6	Common
7	+5V

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPP 850-124A-M	24 VDC	35.4 A	94%
TPP 850-128A-M	28 VDC	30.3 A	
TPP 850-136A-M	36 VDC	23.6 A	
TPP 850-148A-M	48 VDC	17.7 A	

# AC/DC: Enclosed Power Supplies


Traco Power offers a wide range of encapsulated power supplies with hundred of models available in PCB mount styles to suit a wide range of applications.

SERIES	POWER	DESCRIPTION	STATUS	APPS	PAGE
TXM 015	15	3.11 × 2.01 × 1.13" package, 3000 VAC isolation	ACTIVE		136
TXLN 018	18	2.99 × 2.00 × 1.10" package, 3000 VAC isolation	COMING SOON!		136
TXL 025	25	3.11 × 2.01 × 1.12" package, 3000 VAC isolation	ACTIVE		137
TXM 025	25	3.11 × 2.01 × 1.13" package, 3000 VAC isolation	ACTIVE		137
TXL 035	35	3.90 × 3.23 × 1.38" package, 3000 VAC isolation	ACTIVE		138
TXM 035	35	4.02 × 2.52 × 1.30" package, 3000 VAC isolation	ACTIVE		138
TPP 40	40	3.53 × 2.38 × 1.31" package, 4000 VAC isolation, 4000 VAC isolation	ACTIVE	⊕	139
TXL 050/60	50	3.90 × 3.23 × 1.38" package, 3000 VAC isolation	ACTIVE		139
TXM 050	50	3.90 × 3.23 × 1.38" package, 3000 VAC isolation	ACTIVE		140
TXH 060	60	3.12 × 2.00 × 1.50" package, 3000 VAC isolation	ACTIVE		140
TPP 65	65	3.53 × 2.38 × 1.31" package, 4000 VAC isolation, 4000 VAC isolation	ACTIVE	⊕	141
TXM 075	75	5.08 × 3.90 × 1.50" package, 3000 VAC isolation	ACTIVE		141
TXLN 080	80	6.25 × 3.74 × 1.50" package, 3000 VAC isolation	COMING SOON!		142
TPP 100	100	3.6 × 2.44 × 1.20" package, 4000 VAC isolation, 4000 VAC isolation	ACTIVE	⊕	142
TXM 100	100	7.05 × 3.90 × 1.50" package, 3000 VAC isolation	ACTIVE		143
TXLN 110	110	6.26 × 3.74 × 1.50" package, 3000 VAC isolation	COMING SOON!		143
TPP 150	150	4.6 × 2.44 × 1.94" package, 4000 VAC isolation, 4000 VAC isolation, top-mount fan	ACTIVE	⊕	144
TXLN 150	150	7.40 × 3.90 × 1.18" package, 3000 VAC isolation	COMING SOON!		129
TXM 150	150	7.05 × 3.90 × 1.50" package, 3000 VAC isolation	ACTIVE		144
TXLN 200	200	8.74 × 4.52 × 1.18" package, 3000 VAC isolation	COMING SOON!		145
TXM 200	200	7.83 × 3.90 × 1.98", 3000 VAC isolation	ACTIVE		145
TPP 250	250	2.00 × 4.00 × 1.60", 4000 VAC isolation, 4000 VAC isolation, top-mount fan	COMING SOON!	⊕	146
TXLN 320	320	8.74 × 4.53 × 1.18", 3000 VAC isolation, top-mount fan	COMING SOON!		146
TPP 450	450	5.83 × 3.15 × 1.62" package, 4000 VAC isolation, standby power, end-mount fan	ACTIVE	⊕	147
TXLN 500	500	9.67 × 5.00 × 1.61" package, 3000 VAC isolation, end-mount fan	COMING SOON!		147
TPP 600	600	5.00 × 3.00 × 1.62" package, 4000 VAC isolation, top-mount fan	COMING SOON!	⊕	148
TPP 850	850	4.00 × 6.00 × 1.62" package, 4000 VAC isolation, top-mount-fan	COMING SOON!	⊕	148
TXLN 960	960	10.82 × 4.92 × 3.28" package, 3000 VAC isolation, end-mount fan	COMING SOON!		149

APPS KEY: ⊕ = IEC/EN/ES 60601-1 (2×MOPP Approved)



**TXM 015** **15 Watt**




- 3.19 x 2.01 x 1.13" package
- High operating temperature up to 70°C
- Low no load power consumption <0.5W
- Screw terminal block
- Universal AC input
- Withstand 300 VAC surge input for 5 sec.
- IEC/EN/UL 62368-1 approved
- Adjustable output voltage
- 3 year product warranty

Pin-Out	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4	- Vout
5	+ Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXM 015-103	3.3VDC	4.0 A	71%
TXM 015-105	5VDC	3.0 A	78%
TXM 015-112	12VDC	1.3 A	82%
TXM 015-115	15VDC	1.0 A	83%
TXM 015-124	24VDC	0.7 A	85%

**TXLN 018** NEW - under development **18 Watt**



Dimensions in mm  
 Tolerances:  
 0 - 8: ±0.2  
 8 - 25: ±0.3  
 25 - 80: ±0.5

- 2.99 x 2.00 x 1.10" package
- -20 °C to 70°C Operation
- Full-load convection operation to 50°C
- Screw terminal blocks
- 85-264 VAC universal AC input
- IEC/EN/UL 62368-1 approved
- EN 55032 class B emissions
- ±10% Adjustable output voltage
- 3 year product warranty


Screw Terminal	
Pin	Function
1	AC (L)
2	AC (N)
3	FG
4	-Vout
5	+Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXLN 018-103	3.3 VDC	3'000 mA	86%
TXLN 018-105	5 VDC	3'000 mA	86%
TXLN 018-112	12 VDC	1'500 mA	88%
TXLN 018-115	15 VDC	1'200 mA	88%
TXLN 018-124	24 VDC	750 mA	89%



TXL 025

25 Watt




- 3.66 x 2.01 x 1.12" package
- Universal input 85 - 264 Vac
- EN 61000-6-3 & 6-1 (EMI/EMC)
- Compliance to EN 61000-3-2
- IEC/EN/UL 62368-1 approved
- Short circuit & overvoltage protection
- International safety approvals
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXL 025-05S	5VDC	5.0 A	79%
TXL 025-12S	12VDC	2.1 A	84%
TXL 025-15S	15VDC	1.7 A	85%
TXL 025-24S	24VDC	1.1 A	86%
TXL 025-3.3S	3.3VDC	6.0 A	72%
TXL 025-48S	48VDC	0.57 A	88%

TXM 025

25 Watt



- 3.68 x 2.01 x 1.13" package
- High operating temperature up to 70°C
- Low no load power consumption <0.5W
- Screw terminal block
- No internal fan
- Universal AC input
- Withstand 300 VAC surge input for 5 sec.
- IEC/EN/UL 62368-1 approved
- Adjustable output voltage
- 3 year product warranty

Pin-Out	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4	- Vout
5	+ Vout


Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXM 025-103	3.3VDC	6.0 A	71%
TXM 025-105	5VDC	5.0 A	77%
TXM 025-112	12VDC	2.1 A	82%
TXM 025-115	15VDC	1.7 A	83%
TXM 025-124	24VDC	1.1 A	84%



TPP 40

40 Watt

⊕ IEC/EN/ES 60601-1 Approved



- 3.53 x 2.38 x 1.31" package
- ErP compliant, No load < 150mW
- Constant power characteristics at 2W (no current limitation)
- Suitable to drive relays, solenoids, capacitive loads & LED,s
- Auxiliary outputs 3.3 & 5 VDC
- Operating temperature -30°C to +70°C
- EMI meets EN 55032, class B & FCC, level B
- IEC/EN/UL 62368-1 approved
- Short circuit, overload protection
- 3 year product warranty

Screw Terminal (Single Output Models)

Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

Screw Terminal (Multi Output Models)

Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1	Vout 3
3	Neutral	2, 3	COM
		4, 5	Vout 2
		6	Vout 1

Model	Vout	Iout	Efficiency
TPP 40-105	5 VDC	8.00 A	90 %
TPP 40-112	12 VDC	3.34 A	92 %
TPP 40-115	15 VDC	2.67 A	92 %
TPP 40-124	24 VDC	1.67 A	92 %
TPP 40-221	+12/+5 VDC	3.34/6.00 A	89 %
TPP 40-231	+15/+5 VDC	2.67/6.00 A	89 %
TPP 40-251	+24/+5 VDC	1.67/6.00 A	86 %
TPP 40-321M2	+12/+5/-12 VDC	3.34/6.00/0.50 A	88 %
TPP 40-331M3	+15/+5/-15 VDC	2.67/6.00/0.50 A	88 %
TPP 40-3512	+24/+5/+12 VDC	1.67/6.00/0.50 A	96 %


Note  
 - Total Power must not exceed 40 W.  
 - Other output models are available on request.  
 - Multi output models have a common ground.

Note (Dimensions)  
 - Multi output models 102.4 (4.03) length, 34.5 (1.36) height

\* Terminal rated for 10 A max. (at higher current connection has to be split)

TXL 050/060

50/60 Watt




- 4.37 x 3.23 x 1.38" package
- Universal input 85 - 264 Vac
- EN 61000-6-3 & 6-1 (EMI/EMC)
- Compliance to EN 61000-3-2
- Short circuit & overvoltage protection
- IEC/EN/UL 62368-1 approved
- 3 year product warranty

Screw Terminal

Pin	Single
1	AC L
2	AC N
3	PE
4	- Vout
5	+ Vout

Model	Output Voltage nom.	Output Current max.	Eff typ.
TXL 050-05S	5 VDC	10 A	78%
TXL 060-3.3S	3.3 VDC	15 A	74%
TXL 060-05S	5 VDC	12 A	77%
TXL 060-12S	12 VDC	5 A	81%
TXL 060-15S	15 VDC	4 A	83%
TXL 060-24S	24 VDC	2.5 A	84%

**TXM 050** **50 Watt**




- 3.90 x 3.23 x 1.38" package
- High operating temperature up to 70°C
- Low no load power consumption <0.5W
- Screw terminal block
- No internal fan
- Universal AC input
- Withstand 300 VAC surge input for 5 sec.
- IEC/EN/UL 62368-1 approved
- Adjustable output voltage
- 3 year product warranty

Pin-Out	
Pin	Function
1	AC (N)
2	AC (L)
3	PE
4	- Vout
5	+ Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXM 050-105	5VDC	8.0 A	80%
TXM 050-112	12VDC	4.2 A	85%
TXM 050-115	15VDC	3.4 A	86%
TXM 050-124	24 VDC	2.2 A	88%
TXM 050-148	48 VDC	1.1 A	89%

**TXH 060** **60 Watt**



- 3.14 x 2.35 x 1.50" package
- Universal input range 90 to 264 VAC
- ErP compliant, < 0.3 W no load power
- Adjustable output voltage
- 4242 VDC I/O isolation
- High efficiency up to 88%
- -30°C to +70°C operating temperature
- IEC/EN/UL 62368-1 approved
- Short circuit & over voltage protection
- 3 year product warranty


Pin Connections	
Pin	Function
1	AC IN (N)
2	AC IN (L)
3	PE
4	+Vout
5	-Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXH 060-112	12 VDC	5'000 mA	87%
TXH 060-115	15 VDC	4'000 mA	87%
TXH 060-124	24 VDC	2'500 mA	88%
TXH 060-148	48 VDC	1'250 mA	88%



**TPP 65** **65 Watt**

⊕ IEC/EN/ES 60601-1 Approved



- 3.53 x 2.38 x 1.31" package
- IEC/EN/ES 60601-1 3rd ed. (2 x MOPP)
- <75 µA leakage (BF rated)
- IEC/EN/UL 62368-1 approved
- ISO 14971 risk management file
- Acceptance criteria to IPC-A-610 Level 3
- IEC 60601-1-2 ed. 4 EMC
- Protection class I & II
- Operating up to 5000 m altitude
- ErP ready (<0.15 W no load power)
- 5 year product warranty

**Screw Terminal (Single Output Models)**

Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

**Screw Terminal (Multi Output Models)**

Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1	Vout 3
3	Neutral	2, 3	COM
		4, 5	Vout 2
		6	Vout 1


Model	Vout	Iout	Efficiency
TPP 65-105	5 VDC	10.00 A	90 %
TPP 65-112	12 VDC	5.42 A	93 %
TPP 65-115	15 VDC	4.34 A	94 %
TPP 65-124	24 VDC	2.71 A	94 %
TPP 65-221	+12/+5 VDC	5.42/8.00 A	90 %
TPP 65-231	+15/+5 VDC	4.34/8.00 A	91 %
TPP 65-251	+24/+5 VDC	2.71/8.00 A	89 %
TPP 65-321M2	+12/+5/-12 VDC	5.42/8.00/0.60 A	89 %
TPP 65-331M3	+15/+5/-15 VDC	4.34/8.00/0.60 A	90 %
TPP 65-3512	+24/+5/+12 VDC	2.71/8.00/0.60 A	89 %

Note  
 - Total Power must not exceed 65 W.  
 - Other output models are available on request.  
 - Multi output models have a common ground.

Note (Dimensions)  
 - Multi output models 102.4 (4.03) length, 34.5 (1.36) height

\* Terminal rated for 10 A max. (at higher current connection has to be split)

**TXM 075** **75 Watt**




- 5.08 x 3.90 x 1.50" package
- High operating temperature up to 70°C
- Low no load power consumption <0.5W
- Screw terminal block
- No internal fan
- Universal AC input
- IEC/EN/UL 62368-1 approved
- Withstand 300 VAC surge input for 5 sec.
- Adjustable output voltage
- 3 year product warranty

Pin-Out	
Pin	Function
1	AC (N)
2	AC (L)
3	PE
4	- Vout
5	+ Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXM 075-105	5 VDC	12.0 A	80%
TXM 075-112	12VDC	6.0 A	85%
TXM 075-115	15VDC	5.0 A	86%
TXM 075-124	24VDC	3.2 A	88%
TXM 075-148	48VDC	1.6 A	89%

**TXLN 080** **NEW - under development** **80 Watt**




Model	Output Voltage nom.	Output Current max.	Eff typ.
TXLN 080-212	+5 / +12 VDC	9 / 4 A	79%
TXLN 080-215	+5 / +24 VDC	9 / 2 A	80%
TXLN 080-312M2	+5 / ±12 VDC	8 / 4 / 1 A	79%
TXLN 080-313M3	+5 / ±15 VDC	8 / 3.6 / 1 A	80%
TXLN 080-3125	+5 / +12 / +24 VDC	8 / 3.5 / 1.5 A	90%

- 6.26 x 3.74 x 1.50" metal case
- -20 °C to 70°C Operation
- Full-load convection operation to 45°C
- Screw terminal blocks
- 88-264 VAC universal AC input
- IEC/EN/UL 62368-1 Approved
- EN 55032 class B emissions
- ±10% Adjustable output voltage
- 3 year product warranty

Screw Terminal		
Pin	Dual	Triple
1	AC (N)	
2	AC (L)	
3	FG	
4	NC	-Vout3
5	NC	+Vout2
6	-Vout1	-Vout1
7	+Vout1	+Vout1
8	-Vout2	-Vout2
9	+Vout2	+Vout2

**TPP 100** **100 Watt**

⊕ IEC/EN/ES 60601-1 Approved




Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 100-112	12 VDC (10.8 - 13.2 VDC)	8340 mA	91 %
TPP 100-115	15 VDC (13.5 - 16.5 VDC)	6670 mA	92 %
TPP 100-124	24 VDC (21.6 - 26.4 VDC)	4170 mA	92 %
TPP 100-128	28 VDC (25.2 - 30.8 VDC)	3580 mA	92 %
TPP 100-136	36 VDC (32.4 - 39.6 VDC)	2780 mA	91 %
TPP 100-148	48 VDC (43.2 - 52.8 VDC)	2090 mA	91 %

- 3.60 x 2.44 x 1.20" package
- IEC/EN/ES 60601-1 3rd ed. (2xMOPP)
- <75 µA leakage (BF rated)
- ISO 14971 risk management file
- IPC-A-610 Level 3 acceptance
- Active power factor correction >0.95
- IEC/EN/UL 62368-1 approved
- Protection class I & II prepared
- Operating up to 5000 m altitude
- <0.3 W no load power (ErP Ready)
- 5 year product warranty

Screw Terminal			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1, 2	-Vout
3	Neutral	3, 4	+Vout

TXM 100

100 Watt



- 5.08 x 3.90 x 1.50" package
- Operating temperature up to 60°C
- Low no load power consumption <0.5W
- Screw terminal block
- No internal fan
- Universal AC input
- Active power factor correction >0.93
- Withstand 300 VAC surge input for 5 sec.
- IEC/EN/UL 62368-1 approved
- Adjustable output voltage
- 3 year product warranty


Pin-Out	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4	- Vout
5	+ Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXM 100-105	5VDC	20.0 A	84%
TXM 100-112	12VDC	8.5 A	87%
TXM 100-115	15VDC	7.0 A	87%
TXM 100-124	24VDC	4.2 A	88%
TXM 100-148	48VDC	2.2 A	88%

TXLN 110

NEW - under development

110 Watt




- 6.26 x 3.74 x 1.50" metal case
- -20 °C to 70°C Operation
- Full-load convection operation to 45°C
- Screw terminal blocks
- 88-264 VAC universal AC input
- IEC/EN/UL 62368-1 approved
- EN 55032 class B emissions
- ±10% Adjustable output voltage
- 3 year product warranty

Screw Terminal	
Pin	Function
1	AC (L)
2	AC (N)
3	FG
4-5	-Vout
6-7	+Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXLN 110-105	5 VDC	20'000 mA	86%
TXLN 110-112	12 VDC	9'200 mA	88%
TXLN 110-112	12 VDC	7'300 mA	88%
TXLN 110-124	24 VDC	4'800 mA	89%
TXLN 110-148	48 VDC	2'300 mA	90%

TPP 150 150 Watt

⊕ IEC/EN/ES 60601-1 Approved



- 4.60 x 2.44 x 1.94" package
- 2xMOPP / BF compliant
- Leakage current <100 µA
- IEC/EN/UL 62368-1 approved
- ISO 14971 risk management file
- IPC-A-610 Level 3 acceptance
- Active power factor correction >0.95
- Protection class I & II prepared
- Operating up to 5000 m altitude
- ErP ready ( <0.3 W no load power)
- 5 year product warranty

Pin connectors			
Input (CON1)		Output (CON2)	
Pin	Function	Pin*	Function
1	Line	1-3	-Vout
3	Neutral	4-6	+Vout
Input (CON3)			
Pin	Function		
1	-Fan		
2	+Fan		

Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 150-112	12 VDC (10.8 - 13.2 VDC)	12500 mA	91 %
TPP 150-115	15 VDC (13.5 - 16.5 VDC)	10000 mA	92 %
TPP 150-124	24 VDC (21.6 - 26.4 VDC)	6250 mA	92 %
TPP 150-128	28 VDC (25.2 - 30.8 VDC)	5360 mA	92 %
TPP 150-136	36 VDC (32.4 - 39.6 VDC)	4170 mA	92 %
TPP 150-148	48 VDC (43.2 - 52.8 VDC)	3130 mA	92 %


\*Terminal rated for 7 A max. (at higher current connection has to be split)

CON1: Screw Terminal

CON2: Screw Terminal

CON3: Molex series mates with Molex crimp terminals: 2759

TXLN 150 NEW - under development 150 Watt




- 7.40 x 3.90 x 1.18" metal case
- -30 °C to 70°C Operation
- Full-load convection operation to 50°C
- Screw terminal blocks
- 85-264 VAC universal AC input
- IEC/EN/UL 62368-1 Approved
- EN 55032 class B emissions
- ±10% Adjustable output voltage
- 3 year product warranty

Screw Terminal		JTS Connector	
Pin	Function	Pin	Function
1	AC (L)	1	+Remote
2	AC (N)	2	-Remote
3	FG		
4-5	-Vout		
6-7	+Vout		

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXLN 150-105	5 VDC	30'000 mA	86%
TXLN 150-112	12 VDC	12'500 mA	88%
TXLN 150-124	24 VDC	6'300 mA	89%
TXLN 150-148	48 VDC	3'200 mA	90%



**TXM 150** **150 Watt**




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXM 150-112	12VDC	12.5A	86%
TXM 150-115	15VDC	10.0A	87%
TXM 150-124	24VDC	6.3A	88%
TXM 150-148	48VDC	3.2A	88%

- 6.30 x 3.55 x 1.50" package
- High operating temperature up to 60°C
- Low no load power consumption <0.5W
- Screw terminal block
- No internal fan
- Universal AC input
- Active power factor correction >0.95
- IEC/EN/UL 62368-1 approved
- Withstand 300 VAC surge input for 5 sec.
- Adjustable output voltage
- 3 year product warranty

Pin-Out	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4	- Vout
5	- Vout
6	+ Vout
7	+ Vout

**TXLN 200** NEW - under development **200 Watt**




Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXLN 200-112	12 VDC	16'700 mA	89%
TXLN 200-124	24 VDC	8'400 mA	90%
TXLN 200-148	48 VDC	4'200 mA	90%

- 8.74 x 4.53 x 1.18" metal case
- -30 °C to 70°C Operation
- Full-load convection operation to 45°C
- Screw terminal blocks
- 85-264 VAC universal AC input
- IEC/EN/UL 62368-1 Approved
- EN 55032 class B emissions
- ±10% Adjustable output voltage
- 3 year product warranty

Screw Terminal	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4-6	-Vout
7-9	+Vout

**TXM 200** **200 Watt**





- 7.83 x 3.90 x 1.98" package
- Fully convection cooled power supplies
- Cost efficient design
- High operating temperature up to 65°C
- Universal AC input 90 - 264 VAC
- Active power factor correction >0.95
- IEC/EN/UL 62368-1 approved
- Withstand 300 VAC surge input for 5 sec.
- Adjustable output voltage
- Over current limit & short circuit protection
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXM 200-112	12VDC	16.7A	87%
TXM 200-124	24VDC	8.4A	88%
TXM 200-148	48VDC	4.2A	88.50%

Pin-Out	
Pin	Function
1	AC (N)
2	AC (L)
3	GND
4	-Vout
5	-Vout
6	-Vout
7	+Vout
8	+Vout
9	+Vout

**TPP 250** NEW - under development **250 Watt**


⊕ IEC/EN/ES 60601-1 Approved



- 2.00 x 4.00 x 2.56" with top-mount fan
- Operating Temperature Range -40°C to +70°C
- ErP compliant (<0.5 W no load)
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC/EN 60601-1-2 4th edition (EMC)
- High Reliability
- Class I & II prepared
- 5 year product warranty

Model	Output Voltage nom.	Output Current max.
TPP 250-112-M	12 VDC	20.8 A
TPP 250-124-M	24 VDC	10.4 A
TPP 250-128-M	28 VDC	8.9 A
TPP 250-136-M	36 VDC	6.9 A
TPP 250-148-M	48 VDC	5.2 A

**TXLN 320** **NEW - under development** **320 Watt**




- 8.74 x 4.53 x 1.18" metal case
- -20 °C to 70°C Operation
- Full-load convection operation to 45°C
- Embedded top-mount fan
- Screw terminal blocks
- 85-264 VAC universal AC input
- IEC/EN/UL 62368-1 approved
- EN 55032 class B emissions
- ±10% Adjustable output voltage
- 3 year product warranty

Screw Terminal	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4-6	-Vout
7-9	+Vout

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXLN 320-124	24 VDC	13'400 mA	89%
TXLN 320-148	48 VDC	6'700 mA	90%

**TPP 450** **450 Watt**

⊕ IEC/EN/ES 60601-1 Approved



- 3.15 x 5.83 x 1.60" package
- Optional Class II Operation (B-M Models)
- 450W up to 65°C without derating
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC/EN 60601-1-2 4th edition (EMC)
- ISO 14971 risk management file
- IPC-A-610 class 3 criteria
- 5 Vsb, 12 V fan, On/Off, Power Good Signal, variable fan speed
- Operating up to 5000m altitude
- 5 year product warranty

Model	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
<b>Class I Safety Approved Models</b>			
TPP 450-112-M	12 VDC (11.0 - 13.0 VDC)	37'500 mA	91 %
TPP 450-115-M	15 VDC (13.8 - 16.2 VDC)	30'000 mA	92 %
TPP 450-124-M	24 VDC (22.1 - 25.9 VDC)	18'750 mA	93 %
TPP 450-128-M	28 VDC (25.8 - 30.2 VDC)	16'100 mA	93 %
TPP 450-136-M	36 VDC (33.1 - 38.9 VDC)	12'500 mA	93 %
TPP 450-148-M	48 VDC (44.2 - 51.8 VDC)	9'400 mA	94 %
TPP 450-153-M	53 VDC (48.8 - 57.2 VDC)	8'550 mA	94 %
<b>Class II Safety Approved Models</b>			
TPP 450-112B-M	12 VDC (11.0 - 13.0 VDC)	37'500 mA	91 %
TPP 450-115B-M	15 VDC (13.8 - 16.2 VDC)	30'000 mA	92 %
TPP 450-124B-M	24 VDC (22.1 - 25.9 VDC)	18'750 mA	93 %
TPP 450-128B-M	28 VDC (25.8 - 30.2 VDC)	16'100 mA	93 %
TPP 450-136B-M	36 VDC (33.1 - 38.9 VDC)	12'500 mA	93 %
TPP 450-148B-M	48 VDC (44.2 - 51.8 VDC)	9'400 mA	94 %
TPP 450-153B-M	53 VDC (48.8 - 57.2 VDC)	8'550 mA	94 %


Input CON1	
Pin	Function
1	AC (L)
3	AC (N)

Output CON2	
Pin*	Function
1-5	+Vout
6-10	-Vout

Auxiliary CON3	
Pin	Function
1	+Fan
2	+Sense
3	+Remote
4	PG
5	+Standby
6	-Fan
7	-Sense
8	-Remote
9	No Pin
10	-Standby

**TXLN 500** **NEW - under development** **500 Watt**



- 9.68 x 5.00 x 1.61" metal case
- -30 °C to 70°C Operation
- Full-load convection operation to 45°C
- Embedded end-mount fan
- Screw terminal blocks
- Remote Sense Function
- 90-264 VAC universal AC input
- IEC/EN/UL 62368-1 approved
- EN 55032 class B emissions
- ±10% Adjustable output voltage
- 3 year product warranty

Input		Output	
<b>CN1</b>		<b>CN3</b>	
Pin	Function	Pin	Function
1	AC (L)	1-3	-Vout
2	AC (N)	4-6	+Vout
3	FG		


Auxiliary	
<b>CON2</b>	
Pin	Function
1	-Remote
2	-Sense
3	+Remote
4	+Sense

**CN1:** 3 pin, 9.5mm pitch with PC cover  
**CN11:** 6 pin, 11 mm pitch  
**CN3:** HRS DF11-04DP-2DS

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXLN 500-124	24 VDC	21'000 mA	89%
TXLN 500-148	48 VDC	10'500 mA	91%

**TPP 600** **NEW - under development** **600 Watt**

⊕ IEC/EN/ES 60601-1 Approved



- 3.00 x 5.00 x 2.54" package with top-mount fan
- 600W with top-mount fan
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC/EN 60601-1-2 4th ed. (EMC)
- ISO 14971 risk management file
- Protection class I / II prepared
- Class I Low leakage current <100 µA
- ErP compliant (<0.5 W no load)
- 5Vsb, 12V smart fan, Remote On/Off, DC OK signals
- 5 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPP 600-124-M	24 VDC	25.0 A	94%
TPP 600-128-M	28 VDC	21.4 A	
TPP 600-136-M	36 VDC	16.7 A	
TPP 600-148-M	48 VDC	12.5 A	

Input		Auxiliary	
<b>J8</b>		<b>J3</b>	
Pin	Function	Pin	Function
1	AC (L)	1	+5V
3	AC (N)	2	COMM
<b>Output</b>		3	+Remote
Pin*	Function	4	DC OK
RED	+Vout		
BLK	-Vout		

**Input Connector:**  
 J8 = Molex KK 396, PCB Header 41791  
 (PE : J1) = (PE 6.3x0.8mm DIN 46244 Vertical Tab)



**Output Connector(s) :**  
 J5, J6 = Keystone 8199-X

**Signal Connector :**  
 J3 = TE MTA-100, PCB Header 640457-4



**TPP 850** **NEW - under development** **850 Watt**

⊕ IEC/EN/ES 60601-1 Approved




- 4.00 x 6.00 x 2.55" package with top-mount fan
- 850W with top-mount fan
- 2xMOPP / BF compliant
- IEC/EN/UL 62368-1 approved
- IEC/EN 60601-1-2 4th ed. (EMC)
- ISO 14971 risk management file
- ErP compliant (<0.5 W no load)
- Protection class I / II prepared
- Class I Low leakage current <100  $\mu$ A
- 5Vsb, 12V smart fan, Remote On/Off, DC OK signals
- 5 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TPP 850-124-M	24 VDC	35.4 A	94%
TPP 850-128-M	28 VDC	30.3 A	
TPP 850-136-M	36 VDC	23.6 A	
TPP 850-148-M	48 VDC	17.7 A	

Auxiliary	
J3	
Pin	Function
1	+5V
2	Common
3	PWM Fan
4	DC OK
5	Remote
6	Common
7	+5V

**TXLN 960** **NEW - under development** **960 Watt**



- 10.83 x 4.92 x 2.48" package + end-mount fan
- -20 °C to 65°C Operation
- Full-load convection operation to 45°C
- Screw terminal blocks
- 90-264 VAC universal AC input
- Remote sense, power good and remote on/off functions
- 12VDC @ 300MA auxilliary output
- IEC/EN/UL 62368-1 approved
- EN 55032 class B emissions
- $\pm$ 10% Adjustable output voltage
- 3 year product warranty

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TXLN 960-124	24 VDC	40'000 mA	89%
TXLN 960-148	48 VDC	20'000 mA	89%

Input		Output	
CN1		CN3	
Pin	Function	Pin	Function
1	AC (L)	1-3	+Vout
2	AC (N)	4-6	-Vout
3	FG		

Auxiliary	
CON2	
Pin	Function
1	CS
2	PG
3	+Sense
4	-Sense
5	-Remote
6	+Remote
7	Standby
8	GND

## ENGINEERED TO STAY COOL


**High Performance, ultra-compact AC/DC power supplies with minimal heat dissipation**

**Features:**

- Industrial, medical and household approvals
- Ultra-compact / high-density footprints
- High efficiencies with minimal heat dissipation
- -40 to +85°C extended operating temperatures
- Isolation (4kVAC) and leakage current (< 100 µA)
- 5 year product warranty

 IEC/EN/UL 60601-1 (EMC 4th edition)

 IEC/EN/UL62368-1

 EN60335-1

 ERP Ready

### 15 - 450 WATT AC/DC POWER SUPPLIES

FAMILY	WATTS	PACKAGE	FOOTPRINT
<b>TPP 15A-D</b>	15	Open-Frame PCB Mount	1.50 x 1.00 x 0.80"
<b>TPP 15A-J</b>	15	Open-Frame	2.61 x 1.00 x 0.64"
<b>TPP 15-D</b>	15	Encapsulated PCB Mount	1.65 x 1.14 x 0.82"
<b>TPP15-J</b>	15	Encapsulated Chassis-Mount	2.82 x 1.14 x 0.85"
<b>TPP 30A-D</b>	30	Open-Frame PCB Mount	2.74 x 1.36 x 0.95"
<b>TPP 30A-J</b>	30	Open-Frame	3.34 x 1.36 x 0.81"
<b>TPP 30-D</b>	30	Encapsulated PCB Mount	2.89 x 1.50 x 1.00"
<b>TPP 30-J</b>	30	Encapsulated Chassis-Mount	3.95 x 1.50 x 1.00"
<b>TPP 40A-J</b>	40	Open-Frame	3.00 x 2.00 x 0.94"
<b>TPP 40</b>	40	Enclosed	3.53 x 2.38 x 1.31"
<b>TPP 65A-J</b>	65	Open-Frame	3.00 x 2.00 x 0.94"
<b>TPP 65</b>	65	Enclosed	3.53 x 2.38 x 1.31"
<b>TPP 100A-J</b>	100	Open-Frame	3.00 x 2.00 x 1.16"
<b>TPP 100</b>	100	Enclosed	3.60 x 2.44 x 1.54"
<b>TPP 150A-J</b>	150	Open-Frame	4.00 x 2.00 x 1.16"
<b>TPP 150</b>	150	Enclosed with Top Fan	4.60 x 2.44 x 1.94"
<b>TPP 180A-J</b>	180	Open-Frame	3.00 x 2.00 x 1.16"
<b>TPP 300A-J</b>	300	Open-Frame	4.00 x 2.00 x 1.22"
<b>TPP 450A-M</b>	450	Open-Frame	5.00 x 3.00 x 1.58"
<b>TPP 450</b>	450	Enclosed with End Fan	5.83 x 3.15 x 1.60"



# AC/DC: IP67/68 Rated External Power Supplies

TRACO POWER offers external application power supplies designed to meet the environmental challenges of operating in home/building/furniture construction, medical facilities & hazardous gaseous environments.

SERIES	POWER	DESCRIPTION	STATUS	APPS	PAGE
TIW 06	6	1.98 × 1.89 × 0.93", 90-264 VAC input, 3000 VAC isolation, IP67 enclosure	ACTIVE	🏠	152
TIW 12	12	1.98 × 1.89 × 0.93", 90-264 VAC input, 3000 VAC isolation, IP67 enclosure	ACTIVE	🏠	152.5
TIW 24	24	2.20 × 2.05 × 1.26", 90-264 VAC input, 3000 VAC isolation, IP67 enclosure	ACTIVE	🏠	153
TMW 24	24	2.09 × 2.00 × 1.32", 3000 VAC isolation, IP68 enclosure	COMING SOON!	⊕	153.5
TMW 36	36	2.09 × 2.00 × 1.32" package, 3000 VAC isolation, IP68 enclosure	COMING SOON!	⊕	154
TEX 120	120	6.85 × 3.66 × 2.20" package, 3000 VAC isolation, IP67 enclosure	ACTIVE	🏠 ⚙️	154.5

APPS KEY: 🏠 EN60335-1 Approved   ⊕ IEC/EN/ES 60601-1 Approved   🏠 ATEX certification (Class I, Zone 2)   ⚙️ UL/cUL 508 Listed




**TIW 6** **6 Watt**

EN60335-1 Approved



- 1.98 x 1.89 x 0.93" package
- High efficiency switching power supplies
- Easy installation into standard flush boxes
- Fully encapsulated plastic housing
- Dust & waterproof to IP 67
- Protection class II prepared
- Safety approval to IEC/EN 62368-1, EN 50178, EN 60335-1, UL 1310 class 2
- Approved for mounting on to wood or materials with unknown flammability
- Ready to meet ErP directive
- Universal input range 93 to 264 VAC
- Operating temp. range -25°C to +50°C
- Short circuit & overload protection
- 3 year product warranty



Pinout			
Pin	Wire	Color	Type
1	AC (N)	Blue	20AWG/0.52mm <sup>2</sup>
2	AC (L)	Brown	20AWG/0.52mm <sup>2</sup>
3	-Vout	Black	20AWG/0.52mm <sup>2</sup>


Model	Output Voltage	Output Current	Efficiency typ.
TIW 06-103	3.3 VDC	1.2 A	75 %
TIW 06-105	5 VDC	1.0 A	75 %
TIW 06-106	6 VDC	1.0 A	80 %

**TIW 12** **12 Watt**

EN60335-1 Approved



- 1.98 x 1.89 x 0.93" package
- High efficiency switching power supplies
- Easy installation into standard flush boxes
- Fully encapsulated plastic housing
- Dust & waterproof to IP 67
- Protection class II prepared
- Safety approval to IEC/EN 62368-1 EN 50178, EN 60335-1, UL 1310 class 2
- Approved for mounting on to wood or materials with unknown flammability
- Ready to meet ErP directive
- Universal input range 93 to 264 VAC
- Operating temp. range -25°C to +50°C
- Short circuit & overload protection
- 3 year product warranty



Pinout			
Pin	Wire	Color	Type
1	AC (N)	Blue	20AWG/0.52mm <sup>2</sup>
2	AC (L)	Brown	20AWG/0.52mm <sup>2</sup>
3	-Vout	Black	20AWG/0.52mm <sup>2</sup>
4	+Vout	Red	20AWG/0.52mm <sup>2</sup>

Model	Output Voltage	Output Current	Efficiency typ.
TIW 12-112	12 VDC	1.0 A	80 %
TIW 12-115	15 VDC	0.8 A	80 %
TIW 12-124	24 VDC	0.5 A	80 %




**TIW 24** **24 Watt**

EN60335-1 Approved



- 2.20 x 2.05 x 1.26" package
- High efficiency switching power supplies
- Easy installation into standard flush boxes
- Fully encapsulated plastic housing
- Dust & waterproof to IP 67
- Protection class II prepared
- Safety approval to IEC/EN 62368-1, EN 50178, EN 60335-1, UL 1310 class 2
- Approved for mounting onto wood or materials with unknown flammability
- Ready to meet ErP directive
- Universal input range 93 to 264 VAC
- Operating temp. range -25°C to +50°C
- Short circuit & overload protection
- 3 year product warranty



Pinout			
Pin	Wire	Color	Type
1	AC (N)	Blue	20AWG/0.52mm <sup>2</sup>
2	AC (L)	Brown	20AWG/0.52mm <sup>2</sup>
3	-Vout	Black	20AWG/0.52mm <sup>2</sup>
4	+Vout	Red	20AWG/0.52mm <sup>2</sup>


Model	Output Voltage	Output Current	Efficiency typ.
TIW 24-112	12 VDC	2.0 A	83 %
TIW 24-124	24 VDC	1.0 A	85 %

**TMW 24** **NEW - under development** **24 Watt**

IEC/EN/ES 60601-1 Approved



- 2.09 x 2.00 x 0.96" package
- Fully encapsulated IP68 casing
- IEC/EN/ES 60601-1 3rd ed. (2xMOPP)
- ISO 14971 risk management file
- Effortless flush box mounting
- Fire safety for furniture
- Leakage current <100 µA (BF rated)
- Operating temperature: -20°C to +80°C
- Protection against short-circuit, over load & over voltage
- Protection class II prepared
- 5 year product warranty



Pinout / Connection			
Pin	Wire	Color	Type
1	Vac IN (N)	Blue	20AWG/0.52mm <sup>2</sup>
2	Vac IN (L)	Brown	20AWG/0.52mm <sup>2</sup>
3	-Vout	Black	20AWG/0.52mm <sup>2</sup>
4	+Vout	Red	20AWG/0.52mm <sup>2</sup>

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMW 24-105	5 VDC	4 A	85 %
TMW 24-112	12 VDC	2 A	85 %
TMW 24-124	24 VDC	1 A	90 %


\* Also available as pin version: suffix -P

**TMW 36** **NEW - under development** **36 Watt**

⊕ IEC/EN/ES 60601-1 Approved



- 2.09 x 2.00 x 1.32" package
- Fully encapsulated IP68 casing
- IEC/EN/ES 60601-1 3rd ed. (2xMOPP)
- ISO 14971 risk management file
- Effortless flush box mounting
- Fire safety for furniture
- Leakage current <100 µA (BF rated)
- Operating temperature: -20°C to +80°C
- Protection against short-circuit, over load & over voltage
- Protection class II prepared
- 5 year product warranty



Pinout / Connection			
Pin	Wire	Color	Type
1	Vac IN (N)	Blue	20AWG/0.52mm <sup>2</sup>
2	Vac IN (L)	Brown	20AWG/0.52mm <sup>2</sup>
3	-Vout	Black	20AWG/0.52mm <sup>2</sup>
4	+Vout	Red	20AWG/0.52mm <sup>2</sup>

Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TMW 36-112	12 VDC	3.0 A	87 %
TMW 36-124	24 VDC	1.5 A	88 %


\* Also available as pin version: suffix -P

**TEX 120** **24 Watt**

⊕ ATEX & UL Hazloc certified  
 ⚙ UL/cUL 508 Listed




- 6.85 x 3.66 x 2.20" package
- Die-cast aluminium housing
- IP67 & NEMA 4X RATED (Dust, water, salt, ice & oil resistant enclosure)
- ATEX & UL Hazloc class 1, Div 2
- Waterproof I/O plug-connectors
- Shock & vibration proof construction
- Operating temp. -40°C to +85°C
- Universal input 85 to 264 VAC
- Output voltage adjustable
- Low ripple & noise
- 3 year product warranty



Model	Output Voltage nom.	Output Current max.	Efficiency typ.
TEX 120-112	12 VDC	8 A	87%
TEX 120-124	24 VDC	5 A	87%

\* Also available as pin version: suffix -P



Pinout / Connection			
Pin	Wire	Color	Type
1	Vac IN (N)	Blue	20AWG/0.52mm <sup>2</sup>
2	Vac IN (L)	Brown	20AWG/0.52mm <sup>2</sup>
3	-Vout	Black	20AWG/0.52mm <sup>2</sup>
4	+Vout	Red	20AWG/0.52mm <sup>2</sup>

# DIN Rail Mount: AC/DC Power Supplies

Traco Power offers a wide range of encapsulated power supplies with hundred of models available in PCB mount styles to suit a wide range of applications.


SERIES	POWER	DESCRIPTION	STATUS	APPS	PAGE
TBL	15-150	Low profile case (55mm depth), 85-264 VAC input, UL 1310, UL 508	ACTIVE	⚙️	155
TBLC	6-90	Low profile case (55mm depth), 85-264 VAC input, EN 60355-1, UL 1310, UL 508	ACTIVE	⚙️	156
TCL	24-240	Slim profile case, 85-264 VAC input, UL 508	ACTIVE	⚙️	156
TPC	30-120	Slim profile case, 85-264 VAC input, robust design, ErP ready, UL 508	ACTIVE	⚙️	157
TIB	80-480	Rugged metal case, 85-264 VAC input, cost efficient, UL 508	<b>NEW MODELS!</b>	⚙️	157
TIB-EX	80-480	Rugged metal case, 85-264 VAC input, ATEX & UL HazLoc approvals, UL 508	<b>NEW!</b>	⚙️ ⚠️	158
TSPC	50-480	Slim metal case, 85-264 VAC input, UL 508	ACTIVE	⚙️	158
TSP	72-600	Rugged meal case, 85-264 VAC input, for harsh environments, UPS module options	ACTIVE	⚙️ ⚠️	159
TSP-WR	180-600	Rugged metal case, wide range 100/230-500 VAC input, UL 508	ACTIVE	⚙️	159

APPS KEY: ⚙️ UL/cUL 508 Listed    ⚠️ ATEX Certification (Class I, Zone 2)

## TBL

## 15-150 Watt

⚙️ UL/cUL 508 Listed



- Low profile - depth only 55mm
- Used in building automation panels
- Safety class II product
- UL 1310 class II, NEC class 2 (up to 90 W)
- UL 508 listed
- -25°C to +70°C temperature range
- Adjustable output voltage
- Short circuit & overload protection
- DC-OK indicator
- Wall mounting bracket (included)
- 3 year product warranty


Model	Output Power (max.)	Output Voltage* (nom.)(adjust.)	Output Current (max.)	Efficiency (typ.)
TBL 015-105	12 W	5.0 VDC	2.4 A	73 %
TBL 015-112	15 W	12 VDC	1.25 A	79 %
TBL 015-124	15 W	24 VDC	0.63 A	81 %
TBL 030-112	30 W	12 VDC	2.5 A	81 %
TBL 030-124	30 W	24 VDC	1.25 A	83 %
TBL 060-112	54 W	12 VDC	4.5 A	83 %
TBL 060-124	60 W	24 VDC	2.5 A	85 %
TBL 090-112	72 W	12 VDC	6.0 A	84 %
TBL 090-124	90 W	24 VDC	3.75 A	86 %
TBL 150-112	120 W	12 VDC	10 A	84 %
TBL 150-124	150 W	24 VDC	6.25 A	87 %

Model	Dimension Table	Weight
TBL 015	26.3 mm	100
TBL 030	52.5 mm	160
TBL 060	70.0 mm	230
TBL 090	105 mm	340
TBL 150	175 mm	625

# DIN Rail Mount: AC/DC Power Supplies

## TBLC 6-90 Watt

UL/cUL 508 Listed



- Low profile, module depth only 55mm for mounting in domestic installation panels
- High efficiency & low Standby power (compliance to ECO-Standard)
- Low output ripples & spikes
- UL 1310 class II, NEC class 2 compliance
- UL 508 listed
- Operating temperature -25°C to +70°C
- Adjustable output voltage
- Short circuit & overload protection
- DC-OK indicator LED
- 3 year product warranty


Model	Output Power (max.)	Output Voltage* (nom.)(adjust.)	Output Current (max.)	Efficiency (typ.)
TBLC 06-105	6 W	5.0 VDC	1.2 A	74 %
TBLC 06-112	6 W	12 VDC	0.5 A	81 %
TBLC 06-124	6 W	24 VDC	0.25 A	79 %
TBLC 15-105	12 W	5.0 VDC	2.4 A	81 %
TBLC 15-112	15 W	12 VDC	1.25 A	85 %
TBLC 15-124	15 W	24 VDC	0.63 A	85 %
TBLC 25-105	20 W	5.0 VDC	4.0 A	82 %
TBLC 25-112	24 W	12 VDC	2.0 A	86 %
TBLC 25-124	25 W	24 VDC	1.05 A	87 %
TBLC 50-112	48 W	12 VDC	4.0 A	88 %
TBLC 50-124	50 W	24 VDC	2.1 A	89 %
TBLC 75-112	72 W	12 VDC	6.0 A	89 %
TBLC 75-124	75 W	24 VDC	3.1 A	89 %
TBLC 90-112	90 W	12 VDC	7.5 A	90 %
TBLC 90-124	90 W	24 VDC	3.75 A	90 %

\* Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

Dimension Table		Weight
TBLC 06	18 mm	60
TBLC 15	27 mm	80
TBLC 25	36 mm	110
TBLC 50	54 mm	180
TBLC 75	72 mm	220
TBLC 90	90 mm	280

## TCL 24-240 Watt

UL/cUL 508 Listed



- Ultracompact plastic housing
- Spring clamp terminals or detachable screw terminal block
- Adaptor for wall mounting
- Universal input 85-264 VAC, 50/60 Hz
- Models with 5, 12, 24 & 48 VDC output
- Output voltage adjustable
- Power OK signal
- Overload & short-circuit protection
- Parallel operation possible
- 3 year product warranty

Model	Input Voltage Ranges	Output Power max.	Output Voltage nom.	Output Current (max.)	Connection
TCL 024-105	85 - 264 VAC Universal Input 50/60 Hz	20 W	5 VDC	4.0 A	Detachable screw terminal blocks
TCL 024-112		24 W	12VDC	2.0 A	
TCL 024-124		24 W	24 VDC	1.0 A	
TCL 060-112	85 - 375 VDC	60 W	12 VDC	4.0 A	
TCL 060-124		60 W	24 VDC	2.5 A	
TCL 060-148		60 W	48 VDC	1.25 A	
TCL 120-112	85-132 / 187-264 VAC	120 W	12 VDC	8.0 A	Spring clamp terminals
TCL 120-124		120 W	24 VDC	5.0 A	
TCL 240-124		240 W	24 VDC	10.0 A	
TCL 024-124C	85 - 264 VAC Universal Input 50/60 Hz	24 W	24 VDC	1.0 A	
TCL 060-112C		60 W	12 VDC	4.0 A	
TCL 060-124C		60 W	24 VDC	2.5 A	
TCL 060-148C	85 - 375 VDC	60 W	48 VDC	1.25 A	
TCL 120-112C		120 W	12 VDC	8.0 A	
TCL 120-124C		120 W	24 VDC	5.0 A	

Dimension Table			
Model	Width [W]	Length[l]	Height[h]
TCL 024	27 mm	100 mm	75 mm
TCL 60	45 mm	100 mm	75 mm
TCL 120	85 mm	100 mm	75 mm
TCL 240	85 mm	125 mm	110 mm




**TPC** **30-120 Watt**

UL/cUL 508 Listed



- <0.3 W no load power (ErP Ready)
- High efficiency across full load range
- Optional all mounting bracket
- Universal input 85-264 VAC, 47-63 Hz
- Output voltage adjustable
- Power good signal
- Low ripple & noise
- Overload & short-circuit protection
- 3 year product warranty



Model	Input Voltage Ranges	Output Power max.	Output Voltage nom./ adj. range	Output Current (max.)
TPC 030-105	85-264 VAC Universal Input 47/63 Hz	20 W	5.0 VDC / 5.0-6.0 VDC	4.0 A
TPC 030-112		26 W	12 VDC / 12-15 VDC	2.2 A
TPC 030-124		30 W	24 VDC / 24-28.8 VDC	1.25 A
TPC 030-148		30 W	48 VDC / 48-56 VDC	0.6 A
TPC 055-112	90-375 VDC	42 W	12 VDC / 12-15 VDC	3.5 A
TPC 055-124		55 W	24 VDC / 24-28.8 VDC	2.3 A
TPC 055-148		55 W	48 VDC / 48-56 VDC	1.15 A
TPC 080-112		72 W	12 VDC / 12-15 VDC	6.0 A
TPC 080-124		80 W	24 VDC / 24-28.8 VDC	3.3 A
TPC 080-148		80 W	48 VDC / 48-56 VDC	1.7 A
TPC 120-112		96 W	12 VDC / 12-15 VDC	8.0 A
TPC 120-124		120 W	24 VDC / 24-28.8 VDC	5.0 A
TPC 120-148		120 W	48 VDC / 48-56 VDC	2.5 A


Dimension Table			
Model	Width [W]	Length [l]	Height [h]
TPC 30	26.5 mm	96.5 mm	90 mm
TPC 55	45 mm	96.5 mm	90 mm
TPC 80	63 mm	96.5 mm	90 mm
TPC 120	72 mm	96.5 mm	90 mm

**TIB** **NEW models** **80-480 Watt**

UL/cUL 508 Listed



- Slim profile, for DIN-rail mounting
- Alternative side-mounting for flat panels
- Active power factor correction
- IEC / EN / UL 62368-1 approved
- Very high efficiency up to 94%
- Back power immunity
- 150% peak current for 4s
- -40°C to +60°C full load operation
- Adjustable output voltage
- Short circuit & overload protection
- 3 year product warranty



Model	Output Voltage nom. Range	Output Current max.	Output Current peak	Efficiency
TIB 080-112	12 VDC	6'700 mA	10'050 mA	88 %
TIB 080-124	24 VDC	3'400 mA	5'100 mA	90 %
TIB 080-148	48 VDC	1'700 mA	2'550 mA	90 %
TIB 120-112	12 VDC	10'000 mA	15'000 mA	94 %
TIB 120-124	24 VDC	5'000 mA	7'500 mA	94 %
TIB 120-148	48 VDC	2'500 mA	3'750 mA	94 %
TIB 240-124	24 VDC	10'000 mA	15'000 mA	95 %
TIB 240-148	48 VDC	5'000 mA	7'500 mA	95 %
TIB 480-124	24 VDC	20'000 mA	30'000 mA	95 %
TIB 480-148	48 VDC	10'000 mA	15'000 mA	95 %

Dimension Table			
Model	Width [W]	Length [l]	Height [h]
TIB 080	32 mm	99 mm	114 mm
TIB 120	36 mm	119 mm	125 mm
TIB 240	48 mm	119 mm	125 mm
TIB 480	82 mm	119 mm	125 mm

# DIN Rail Mount: AC/DC Power Supplies

TIB-EX


**NEW!**

80-480 Watt

- ATEX / UL Hazloc Certified
- UL/cUL 508 Listed



- ATEX & UL Hazloc class 1, Div 2
- IEC / EN / UL 62368-1 approved
- SEMI F47 (voltage sag immunity)
- Optional side-mounting for flat panels
- Back power immunity
- 150% peak current for 4s
- Operating Temp -40°C to +70°C (full load up to 60°C)
- Adjustable output voltage
- MTBF 1 mill. hrs per IEC 61709
- Short circuit & overload protection
- 5 year product warranty



Model	Output Voltage nom. Range	Output Current max.	Output Current peak	Efficiency
TIB 080-112EX	12 VDC	6'700 mA	10'050 mA	88 %
TIB 080-124EX	24 VDC	3'400 mA	5'100 mA	90 %
TIB 080-148EX	48 VDC	1'700 mA	2'550 mA	90 %
TIB 120-112EX	12 VDC	10'000 mA	15'000 mA	94 %
TIB 120-124EX	24 VDC	5'000 mA	7'500 mA	94 %
TIB 120-148EX	48 VDC	2'500 mA	3'750 mA	94 %
TIB 240-124EX	24 VDC	10'000 mA	15'000 mA	95 %
TIB 240-148EX	48 VDC	5'000 mA	7'500 mA	95 %
TIB 480-124EX	24 VDC	20'000 mA	30'000 mA	95 %
TIB 480-148EX	48 VDC	10'000 mA	15'000 mA	95 %

Dimension Table			
TIB 080-EX	32 mm	99 mm	114 mm
TIB 120-EX	36 mm	119 mm	125 mm
TIB 240-EX	48 mm	119 mm	125 mm
TIB 480-EX	82 mm	119 mm	125 mm


TSPC

50-480 Watt

- UL/cUL 508 Listed



- Rugged metal case for harsh industrial environments
- 25°C to +70°C temperature range
- Overload & overtemperature protection
- Power boost up to 120 %
- Power-Good signal
- Shock & vibration proof
- International safety approval package
- ATEX certification (hazardous locations)
- Wall mounting (option)
- 3 year product warranty



Model	Output power nominal	Output voltage nominal	Output Current max.
TSPC 050-112	50 W	12 VDC	4.0 A
TSPC 050-124HL*	50 W	24 VDC	2.1 A
TSPC 050-124	50 W	24 VDC	2.1 A
TSPC 080-112	80 W	12 VDC	6.6 A
TSPC 080-124	80 W	24 VDC	3.3 A
TSPC 120-124	120 W	24 VDC	5.0 A
TSPC 120-148	120 W	48 VDC	2.5 A
TSPC 240-124	240 W	24 VDC	10 A
TSPC 240-148	240 W	48 VDC	5.0 A
TSPC 480-124	480 W	24 VDC	20 A
TSPC 480-148	480 W	48 VDC	10 A

\*Additionally complies with UL hazloc


Dimension Table			
Model	Width [W]	Length [L]	Height [h]
TSPC 050	35 mm	87 mm	110 mm
TSPC 080	40 mm	110 mm	110 mm
TSPC 120	46 mm	110 mm	110 mm
TSPC 240	60 mm	110 mm	110 mm
TSPC 480	150 mm	115 mm	115 mm

**TSP** **72-600 Watt**

- UL/cUL 508 Listed
- ATEX / UL Hazloc Certified (-EX option)



- For harsh environments
- Shock & vibration proof
- Worldwide Safety approval package.
- ATEX / UL Hazloc class I, div 2 (option -EX)
- TSP 090-124N meets NEC class 2
- Temperature range: -25°C to +70°C
- Adjustable output voltage
- Protection against short-circuit, overvoltage & over-temperature
- Power OK signal, Remote On/Off
- Wall mounting (opt.)
- 3 year product warranty



Model	Output Power (Pmax)	**Output Voltage (Vnom)	***Output Current (Imax)
TSP 070-112*	72 W	12 VDC	6.0 A
TSP 090-124*	90 W	24 VDC	3.75 A
TSP 090-124N	90 W	24 VDC	3.75 A
TSP 090-148*	96 W	48 VDC	2.0 A
TSP 140-112*	144 W	12 VDC	12.0 A
TSP 180-124*	180 W	24 VDC	7.5 A
TSP 180-148*	192 W	48 VDC	4.0 A
TSP 360-124*	360 W	24 VDC	15.0 A
TSP 360-148*	360 W	48 VDC	7.5 A
TSP 600-124*	600 W	24 VDC	25.0 A
TSP 600-136		36 VDC	16.5 A
TSP 600-148*		48 VDC	12.5 A

\* For ATEX compliant models add appendix -EX to order code.


Dimension Table			
Model	Width [W]	Length [L]	Height [H]
TSP 070/090	35 mm	110 mm	110 mm
TSP 140/180	54 mm	110 mm	110 mm
TSP 360	80 mm	125 mm	125 mm
TSP 600	165 mm	125 mm	125 mm

**TSP-WR** **180-600 Watt**

- ATEX / UL Hazloc Certified
- UL/cUL 508 Listed



- Single- & two phase wide-range input 100/230-500 VAC
- ATEX / UL Hazloc class I, div 2 (option -EX)
- Temperature range: -25°C to +70°C
- Power OK / Remote On/Off
- Shock & vibration-proof
- Indefinite short circuit, overvoltage & overtemperature protection
- Buffer module for power backup
- Battery controller module
- 3 year product warranty



Model	Output Voltage (Vnom)	*Output Current (Imax)	Output Power (Pmax)
TSP 180-124WR	24 VDC (adjustable 24-28 VDC)	7.5 A	180 W
TSP 360-124WR		15.0 A	360 W
TSP 600-124WR		25.0 A	600 W

Dimension Table			
Model	Width [W]	Length [L]	Height [H]
TSP 180-WR	54 mm	110 mm	110 mm
TSP 360-WR	80 mm	125 mm	125 mm
TSP 600-WR	190 mm	125 mm	125 mm




# DIN Rail Power DC/DC Power Modules

TCL-DC

24-60 Watt

UL/cUL 508 Listed



Model	Input VDC	Output Voltage	Output Current
TCL 012-124 DC	9.5 - 18	24 VDC	1.0 A
TCL 024-105 DC		5 VDC	5.0 A
TCL 024-112 DC	18 - 75	12 VDC	2.0 A
TCL 024-124 DC		24 VDC	1.0 A
TCL 060-112 DC	18 - 75	12 VDC	5.0 A
TCL 060-124 DC		24 VDC	2.5 A

- Ultra-wide input voltage range
- Output voltage adjustable
- Overload & short circuit protection
- Low ripple & noise
- I/O isolation 1500 VDC
- Compact, slim plastic case
- Bracket for wall mount included
- 3 year product warranty

Pinout		
Terminal	Output	Input
1	+ Vout	Functional Ground
2	- Vout	-Vin
3	-	+Vin

TMDC + DIN RAIL CLIP

20 / 40 / 60 Watt

- Encapsulated Chassis Mount DC/DC with DIN Rail Clip
- Ultra-wide 4 : 1 input voltage range
- Operating temperature: -40°C to +85°C, (TMDC 20 models operate up to +90°C)
- I/O isolation 2500 VDC
- Excellent efficiency up to 91%
- Input filter to meet EN 55022, class A
- Power good LED indicator
- Remote On/Off
- 3 year warranty



**SEE PAGES**

- TMDC 20 - Page 90
- TMDC 40 - Page 92
- TMDC 60 - Page 93



# DIN Rail Mount: Status & Control Modules

SERIES	DESCRIPTION	APPS	STATUS	PAGE
<b>TSPC 240-124UPS</b>	Compact universal power supply for uninterruptable 24 VDC output voltage	⚙️ ⚡	ACTIVE	161
<b>TSP-BCMU360</b>	Universal battery controller module for uninterruptable 24 VDC & 48 VDC bus	⚙️	ACTIVE	162
<b>TSP-BCM</b>	Battery controller modules compatible with the TSP series		ACTIVE	162
<b>TSP-BFM</b>	Buffering module to increase hold-up time compatible with the TSP series	⚙️	ACTIVE	163
<b>TSPC-DCM</b>	Decoupling module for redundant operation compatible with the TSPC series	⚙️	ACTIVE	163
<b>TCL-REM</b>	Redundancy module compatible with the TCL series	⚙️	ACTIVE	164
<b>TPC-REM</b>	Redundancy module compatible with the TPC series		ACTIVE	164
<b>TSP-REM</b>	Redundancy module compatible with the TSP series	⚙️ ⚡	ACTIVE	165

**APPS KEY:** ⚙️ UL/cUL 508 Listed    ⚡ ATEX Certification (Class I, Zone 2)

## INTEGRATED UPS SYSTEM: TSPC-240-124UPS

240 Watt


⚡ ATEX / UL Hazloc Certified  
⚙️ UL/cUL 508 Listed



- 240 watt/24VDC power supply + integrated UPS system
- ATEX / UL Hazloc class I, div 2
- Over-voltage, discharge, short-circuit & reverse connection protection
- Alarm outputs for input, output & battery condition
- Remote On/Off for UPS function & power supply
- Controlled end of charge voltage by battery temperature sensor
- International safety approval package
- Suitable for various external 12 VDC lead acid batteries
- 3 year product warranty

Model	Input Range	Output	Back up Battery
<b>TSPC 240-124 UPS</b>	Low Line: 85-132 VAC  High Line: 187-264 VAC	24 VDC  12 A	12V lead acid battery (purchase in local market or use TRACO POWER battery pack)

\* Maximum current at nominal Vout




## DIN Rail Mount: Status & Control Modules

### BATTERY CONTROL: TSP-BCMU360

360 Watt

UL/cUL 508 Listed



Model	Inputs	Input Voltage Range	Output Current max.*
TSP-BCMU360	2 × 360 W any single or two identical input sources	24-28 or 48-56 VDC (jumper-select)	24 VDC / 15 A 48 VDC / 7.5 A


\* Maximum current at nominal Vout

\*\* 12V lead acid battery (purchase locally or TRACO POWER battery pack)

- Battery controller module for uninterruptable 24 / 48 Vout
- Redundant inputs for two independent sources
- Over-voltage, discharge, short-circuit & reverse connection protection
- Alarm outputs for input, output & battery condition
- Remote On/Off for battery
- Controlled end of charge voltage by temperature sensor
- International safety approval package
- 3 year product warranty

### BATTERY CONTROLLER MODULES: TSP-BCM

12-48 VDC



Model	Input	Max. Power per Input	Output Voltage	Output Current max.	Output Power max.
TSP-BCM12	12 VDC	144 W	12 VDC	12.0 A	144 W
TSP-BCM24	24 VDC	360 W	24 VDC	15.0 A	360 W
TSP-BCM48	48 VDC	360 W	48 VDC	7.5 A	360 W
TSP-BCM24A	24 VDC	600 W	24 VDC	25.0 A	600 W
TSP-BCM48A	48 VDC	600 W	48 VDC	12.5 A	600 W


- Professional battery management system to charge & monitor an external lead-acid battery
- Over-voltage, discharge, short-circuit & reverse connection protection
- Alarm outputs for input, output & battery condition
- Remote On/Off for battery & power supply
- Controlled end of charge voltage by temperature sensor
- International safety approval package
- 3 year product warranty

Dimension Table

Model	W	L	H
TSP-BCM 144-360 Watt	35 mm	110 mm	110 mm
TSP-BCM 600 Watt	54 mm	110 mm	110 mm

**BUFFER MODULE TSP-BFM** 600 Watt

UL/cUL 508 Listed




- Capacitor bank for energy storage, no battery needed!
- Typical Hold-up-time ranging 200ms @ 25A through 4s @ 1.2A
- Output 24 to 28 VDC, 600W max.
- Active ready & inhibit signals
- Maintenance free, long lifetime
- Performance at low temperature
- 3 year product warranty

Model	Input	Buffer Time	Output Voltage adjust.	Output Current max.*	Output Power-max.
TSP-BFM24	24 VDC	200 ms typ. @ 25 A max. 4 s max. @ 1.2 A	24 VDC	25.0 A	600 W

\* Maximum current at nominal Vout

**DECOUPLING MODULE TSPC-DCM** 600 Watt

UL/cUL 508 Listed



- Module contains two diodes for redundant operation of two power supplies
- Hot swappable inputs
- International safety approval package
- 3 year product warranty



Model	Input Voltage	Input Current	Max reverse Voltage	Voltage drop across the diodes
TSPC-DCM600	5 - 28 VDC (24 VDC nom.)	20 mA min. 25 A max.	35 VDC	0.75 VDC typ. 1.2 VDC max.

## DIN Rail Mount: Status & Control Modules

### REDUNDANCY & CURRENT SHARE MODULES TCL-REM

480 Watt

UL/cUL 508 Listed




- Module enables redundant operation of any two TCL models
- Ultracompact plastic housing
- Spring clamp or detachable screw terminals
- Adaptor for wall mounting
- Output voltage adjustable
- Power OK signal
- Overload & short-circuit protection
- Parallel operation possible
- 3 year product warranty

Model	Nominal Input Voltage	Input Voltage Range	Max Power per Input	Output Voltage	Output Current max.
TCL-REM240	5...48 VDC	5...60 VDC	200 W	V <sub>in</sub> - 0.9 VDC	8 A

### REDUNDANCY & CURRENT SHARE MODULES TPC-REM

240 Watt






- Allows redundant operation for two TPC series power supplies with 24 VDC or 48 VDC, same model
- High efficiency across full load range
- Universal input 85-264 VAC, 47-63 Hz
- Output voltage adjustable
- Power good signal
- Overload & short-circuit protection
- 3 year product warranty

Model	Nominal Input Voltage	Max Power per Input	Output Voltage adjustable	Output Current max.
TPC-REM240-24	24 VDC	120 W	24 - 27 VDC	10 A
TPC-REM240-48	48 VDC		48 - 55 VDC	5 A



**REDUNDANCY & CURRENT SHARE MODULES TSP-REM** **360-600 Watt**

 ATEX / UL Hazloc Certified  
 UL/cUL 508 Listed



- Allows same two TSP models redundant operation (no additional components)
- Module for true current sharing
- Alarm outputs, redundancy OK signal
- Hot swappable inputs
- Remote On/Off
- International safety approval package
- 3 year product warranty

Dimension Table			
Model	Width [W]	Length [L]	Height [h]
TSP-REM360	35 mm	110 mm	110 mm
TSP-REM600	54 mm	110 mm	110 mm

Model	Input Voltage Range	Max Power per Input	Output Voltage adjust.	Output Current max. **
TSP-REM360*	2 × 24 VDC	2 × 360 W	24 VDC	15.0 A
TSP-REM600*	2 × Control input	2 × 600 W	(24-27 VDC)	25.0 A

\* For ATEX / IECEx compliant model add appendix -EX to order code.  
 \*\* Maximum current at nominal Vout

# ALPHANUMERIC INDEX

SERIES .....	PAGE	SERIES .....	PAGE	SERIES .....	PAGE	SERIES .....	PAGE	SERIES .....	PAGE
TBA 1	22	TEP 100WIRCMF	95	THN15	65	TMPW 5	111	TRI 20	72
TBA 1E	22	TEP 150WI	96	THP 3	48	TMPW 50	121	TRI 3	49
TBA 1HI	23	TEP 160	85	THR 10WI	60	TMPW 50-J	107	TRI 6	53
TBA 2	28	TEP 160CMF	96	THR 20WI	71	TMPW 5-J	101	TRN 1	27
TBL	155	TEP 160WIR	86	THR 3WI	48	TMR 1	25	TRN 1SM	14
TBLC	156	TEP 160WIRCMF	97	THR 40WI	78	TMR 1SM	13	TRN 3	34
TCL	156	TEP 200WIR	86	TIB	157	TMR 2	29	TRN 3SM	19
TCL-DC	160	TEP 200WIRCMF	98	TIB-EX	158	TMR 2WIN	30	TRS 2	17
TCL-REM	164	TEP 40UIR	82	TIM 2	43	TMR 3	32	TRV 1M	27
TDN 1WI	41	TEP 60UIR	82	TIM 2SM	16	TMR 3HI	32	TSN 1	5
TDN 1WISM	12	TEP 75WI	83	TIM 3.5	49	TMR 3WI	33	TSP	159
TDN 3WI	43	TEP 75WICMF	94	TIM 3.5SM	19	TMR 3WIR	33	TSP-BCM	162
TDN 3WISM	17	TEQ 100WIR	95	TIW 06	152	TMR 4	35	TSP-BCMU360	162
TDN 5WI	50	TEQ 160WIR	97	TIW 12	152	TMR 4WI	35	TSP-BFM	163
TDN 5WISM	20	TEQ 200WIR	98	TIW 24	153	TMR 6	36	TSPC	158
TDR 2	41	TEQ 20WIR	90	TMAP	25	TMR 6WI	36	TSPC 240UPS	161
TDR 2SM	14	TEQ 300WIR	99	TMDC 06	88	TMR 6WIR	37	TSPC-DCM	163
TDR 2WI	42	TEQ 40WIR	91	TMDC 06H	88	TMR 9	37	TSP-REM	165
TDR 2WISM	15	TES 1	12	TMDC 10	89	TMR 9WI	38	TSP-REM	165
TDR 3	44	TES 1V	13	TMDC 10H	89	TMV 2HI	30	TSP-WR	159
TDR 3SM	18	TES 2H	15	TMDC 20	90	TMV-EN	26	TSR 0.5	4
TDR 3WI	44	TES 2M	16	TMDC 20H	91	TMV-HI	26	TSR 0.5SM	9
TDR 3WISM	18	TEX 120	154	TMDC 40	92	TMW 24	153	TSR 0.6WI	4
TEA 1	23	TFI	100	TMDC 40H	92	TMW 36	154	TSR 1	5
TEA 1E	24	THD 10N	57	TMDC 60	93	TPC	157	TSR 1E	6
TEA 1HI	24	THD 10WIN	57	TMDC 60H	93	TPC-REM	164	TSR 1SM	10
TEC 2	28	THD 12	62	TMG 07	112	TPI 100A-J	128	TSR 1WI	6
TEC 2WI	29	THD 12WI	62	TMG 15	114	TPI 125A	129	TSR 2	7
TEC 3	31	THD 15N	63	TMG 30	118	TPI 150A	130	TSR 3	8
TEC 3WI	31	THD 15WIN	63	TMG 50	121	TPI 30A-JP	125	TSRN 1	7
TEL 10	56	THI 2M	42	TML 100C	108	TPI 65A-JP	127	TSRN 1SM	10
TEL 10WI	56	THI 3	46	TML 20	116	TPP 100	142	TVN 3	34
TEL 12	61	THL 10	58	TML 20-C	103	TPP 100A-J	128	TVN 5WI	51
TEL 12WI	61	THL 15WI	64	TML 40	120	TPP 150	143	TXH 060	140
TEL 5	50	THL 25	71	TML 40-C	106	TPP 150A-J	130	TXH 240	129
TEL 8	54	THL 25WI	73	TMLM 04	110	TPP 15A-D	124	TXH 240	131
TEL 8WI	54	THM 10	58	TMLM 20	117	TPP 15A-J	124	TXL 025	137
TEM 3N	45	THM 10WI	59	TMM 24	117	TPP 15-D	116	TXL 035	138
TEN 20WIR	67	THM 15	64	TMM 24-C	104	TPP 15-J	103	TXL 050/60	139
TEN 30	72	THM 15WI	65	TMM 40	120	TPP 180A	131	TXLN 018	136
TEN 30WIN	73	THM 20	68	TMM 40-C	106	TPP 250	132	TXLN 080	142
TEN 3N	45	THM 20WI	69	TMM 60	122	TPP 250	146	TXLN 110	144
TEN 3WIN	46	THM 3	47	TMM 60-C	107	TPP 300A	132	TXLN 150	144
TEN 40E	76	THM 30	74	TMP 07	112	TPP 30A-D	125	TXLN 200	145
TEN 40WIE	77	THM 30WI	74	TMP 15	115	TPP 30A-J	126	TXLN 320	147
TEN 40WIR	77	THM 3WI	47	TMP 15-C	102	TPP 30-D	119	TXLN 500	148
TEN 50	78	THM 6	52	TMP 30	119	TPP 30-J	105	TXLN 960	149
TEN 50WI	79	THM 6WI	83	TMP 30-C	105	TPP 40	139	TXM 015	136
TEN 60N	79	THM 6WI	53	TMP 60	122	TPP 40A-J	126	TXM 025	137
TEN 60WIN	80	THN 10WIR	59	TMP 60-C	108	TPP 450	147	TXM 035	138
TEN 60WIR	80	THN 15N	66	TMPM 10	113	TPP 450A-M	133	TXM 050	140
TEN 6N	51	THN 15WI	66	TMPS 03	110	TPP 600	148	TXM 075	141
TEN 6WIN	52	THN 15WIR	67	TMPS 05	111	TPP 600A	133	TXM 100	143
TEN 8	55	THN 20	69	TMPS 10	113	TPP 65	141	TXM 150	145
TEN 8WI	55	THN 20WI	70	TMPS 15	115	TPP 65A-J	127	TXM 200	146
TEP 100	84	THN 20WIR	70	TMPW 10	114	TPP 850	149		
TEP 100CMF	94	THN 30	75	TMPW 10-J	102	TPP 850A	134		
TEP 100UIR	84	THN 30WI	75	TMPW 25	118	TRI 10	60		
TEP 100WIR	85	THN 30WIR	76	TMPW 25-J	104	TRI 15	68		

# ALPHANUMERIC INDEX

SERIES .....	PAGE	SERIES .....	PAGE	SERIES .....	PAGE	SERIES .....	PAGE	SERIES .....	PAGE
TBA 1	22	TEP 100WIRCMF	95	THN15	65	TMPW 5	111	TRI 20	72
TBA 1E	22	TEP 150WI	96	THP 3	48	TMPW 50	121	TRI 3	49
TBA 1HI	23	TEP 160	85	THR 10WI	60	TMPW 50-J	107	TRI 6	53
TBA 2	28	TEP 160CMF	96	THR 20WI	71	TMPW 5-J	101	TRN 1	27
TBL	155	TEP 160WIR	86	THR 3WI	48	TMR 1	25	TRN 1SM	14
TBLC	156	TEP 160WIRCMF	97	THR 40WI	78	TMR 1SM	13	TRN 3	34
TCL	156	TEP 200WIR	86	TIB	157	TMR 2	29	TRN 3SM	19
TCL-DC	160	TEP 200WIRCMF	98	TIB-EX	158	TMR 2WIN	30	TRS 2	17
TCL-REM	164	TEP 40UIR	82	TIM 2	43	TMR 3	32	TRV 1M	27
TDN 1WI	41	TEP 60UIR	82	TIM 2SM	16	TMR 3HI	32	TSN 1	5
TDN 1WISM	12	TEP 75WI	83	TIM 3.5	49	TMR 3WI	33	TSP	159
TDN 3WI	43	TEP 75WICMF	94	TIM 3.5SM	19	TMR 3WIR	33	TSP-BCM	162
TDN 3WISM	17	TEQ 100WIR	95	TIW 06	152	TMR 4	35	TSP-BCMU360	162
TDN 5WI	50	TEQ 160WIR	97	TIW 12	152	TMR 4WI	35	TSP-BFM	163
TDN 5WISM	20	TEQ 200WIR	98	TIW 24	153	TMR 6	36	TSPC	158
TDR 2	41	TEQ 20WIR	90	TMAP	25	TMR 6WI	36	TSPC 240UPS	161
TDR 2SM	14	TEQ 300WIR	99	TMDC 06	88	TMR 6WIR	37	TSPC-DCM	163
TDR 2WI	42	TEQ 40WIR	91	TMDC 06H	88	TMR 9	37	TSP-REM	165
TDR 2WISM	15	TES 1	12	TMDC 10	89	TMR 9WI	38	TSP-REM	165
TDR 3	44	TES 1V	13	TMDC 10H	89	TMV 2HI	30	TSP-WR	159
TDR 3SM	18	TES 2H	15	TMDC 20	90	TMV-EN	26	TSR 0.5	4
TDR 3WI	44	TES 2M	16	TMDC 20H	91	TMV-HI	26	TSR 0.5SM	9
TDR 3WISM	18	TEX 120	154	TMDC 40	92	TMW 24	153	TSR 0.6WI	4
TEA 1	23	TFI	100	TMDC 40H	92	TMW 36	154	TSR 1	5
TEA 1E	24	THD 10N	57	TMDC 60	93	TPC	157	TSR 1E	6
TEA 1HI	24	THD 10WIN	57	TMDC 60H	93	TPC-REM	164	TSR 1SM	10
TEC 2	28	THD 12	62	TMG 07	112	TPI 100A-J	128	TSR 1WI	6
TEC 2WI	29	THD 12WI	62	TMG 15	114	TPI 125A	129	TSR 2	7
TEC 3	31	THD 15N	63	TMG 30	118	TPI 150A	130	TSR 3	8
TEC 3WI	31	THD 15WIN	63	TMG 50	121	TPI 30A-JP	125	TSRN 1	7
TEL 10	56	THI 2M	42	TML 100C	108	TPI 65A-JP	127	TSRN 1SM	10
TEL 10WI	56	THI 3	46	TML 20	116	TPP 100	142	TVN 3	34
TEL 12	61	THL 10	58	TML 20-C	103	TPP 100A-J	128	TVN 5WI	51
TEL 12WI	61	THL 15WI	64	TML 40	120	TPP 150	143	TXH 060	140
TEL 5	50	THL 25	71	TML 40-C	106	TPP 150A-J	130	TXH 240	129
TEL 8	54	THL 25WI	73	TMLM 04	110	TPP 15A-D	124	TXH 240	131
TEL 8WI	54	THM 10	58	TMLM 20	117	TPP 15A-J	124	TXL 025	137
TEM 3N	45	THM 10WI	59	TMM 24	117	TPP 15-D	116	TXL 035	138
TEN 20WIR	67	THM 15	64	TMM 24-C	104	TPP 15-J	103	TXL 050/60	139
TEN 30	72	THM 15WI	65	TMM 40	120	TPP 180A	131	TXLN 018	136
TEN 30WIN	73	THM 20	68	TMM 40-C	106	TPP 250	132	TXLN 080	142
TEN 3N	45	THM 20WI	69	TMM 60	122	TPP 250	146	TXLN 110	144
TEN 3WIN	46	THM 3	47	TMM 60-C	107	TPP 300A	132	TXLN 150	144
TEN 40E	76	THM 30	74	TMP 07	112	TPP 300A-D	125	TXLN 200	145
TEN 40WIE	77	THM 30WI	74	TMP 15	115	TPP 30A-D	125	TXLN 320	147
TEN 40WIR	77	THM 3WI	47	TMP 15-C	102	TPP 30A-J	126	TXLN 500	148
TEN 50	78	THM 6	52	TMP 30	119	TPP 30-D	119	TXLN 960	149
TEN 50WI	79	THM 6WI	83	TMP 30-C	105	TPP 30-J	105	TXM 015	136
TEN 60N	79	THM 6WI	53	TMP 60	122	TPP 40	139	TXM 025	137
TEN 60WIN	80	THN 10WIR	59	TMP 60-C	108	TPP 40A-J	126	TXM 035	138
TEN 60WIR	80	THN 15N	66	TMPM 10	113	TPP 450	147	TXM 050	140
TEN 6N	51	THN 15WI	66	TMPS 03	110	TPP 450A-M	133	TXM 075	141
TEN 6WIN	52	THN 15WIR	67	TMPS 05	111	TPP 600	148	TXM 100	143
TEN 8	55	THN 20	69	TMPS 10	113	TPP 600A	133	TXM 150	145
TEN 8WI	55	THN 20WI	70	TMPS 15	115	TPP 65	141	TXM 200	146
TEP 100	84	THN 20WIR	70	TMPW 10	114	TPP 65A-J	127		
TEP 100CMF	94	THN 30	75	TMPW 10-J	102	TPP 850	149		
TEP 100UIR	84	THN 30WI	75	TMPW 25	118	TPP 850A	134		
TEP 100WIR	85	THN 30WIR	76	TMPW 25-J	104	TRI 10	60		
						TRI 15	68		

# TRACO POWER

Traco Power product offering includes vertical market solutions with market-focused catalogs and a complete product overview Short Form

**TRACO POWER**


**2020-2021 | Medical Power Solutions**  
IEC /EN / ES 60601-1 3rd Edition Approved  
AC/DC Power Supplies & DC/DC Converters




www.tracopower.com 

**TRACO POWER**

**2020-2021 | Ruggedized DC/DC Converters**  
Railway Certified to EN 50155  
3 - 300 Watts



www.tracopower.com 

**TRACO POWER**

**2020-2021 | Short Form Selection Guide**  
**DC/DC Converters**  
**AC/DC Power Supplies**



www.tracopower.com    

**TRACO POWER**

**2020-2021 | Household / Building Automation**  
IoT / IIoT Solutions  
2 - 360 Watts



www.tracopower.com 

## International Office

Traco Electronic AG  
Sihlbruggstrasse 111  
6340 Baar  
Switzerland

P +41 43 311 45 11  
F +41 43 311 45 45  
info@tracopower.com

## German Office

Traco Electronic GmbH  
Oskar-Messter-Str. 20a  
85737 Ismaning/München  
Germany

P +49 89 96 11 82-0  
F +49 89 96 11 82-20  
info@tracopower.de

## French Office

Traco Power France  
17, rue de la Vanne  
92120 Montrouge  
France

M +33 (0)6 72 11 52 21  
info@tracopower.fr

## North America Office

Traco Power North America, Inc.  
2025 Gateway Place #330  
SAN JOSE, CA 95110  
USA

P +1 (408) 916-4570  
F +1 (408) 916-4571  
salesusa@tracopower.com

## Design & Development

Traco Power Solutions Ltd.  
Whitemill Industrial Estate  
Whitemill Road, Wexford  
Y35 YH66, Ireland

P +353 53 9167 700  
F +353 53 9167 701  
info@tracopower.ie