

Amplifier Built-in Compact Photoelectric Sensor

CX-400 SERIES Ver.2

# **World Standard**



# **Upgraded to Increase Usability**

Achieving low power consumption and high noise-resistance

2010.11 panasonic-electric-works.net/sunx

Panasonic Electric Works SUNX

# The world standard CX-400 series Sensors that are environmentally and user friendly.

The total lineup of 148 models covers through the inclusion of a newly developed custom integrated circuit. This **CX-400** series upgrade achieves a significantly higher reliability in the same package as the older model.



Providing stable detection with low power consumption Includes an analog CMOS processor ASIC



# Strong

Demonstrating stable detection, even in harsh environments

#### Resistant to oil and coolant liquids CX-41 a/42 a/49 a

Test Oil

Lubricant

Water-insoluble

Water-soluble

cutting oil

cutting oil

JIS Standard

2-5

2-11

W1-1

W2-1

1,000 hours; Immersion (depth 0 m); Insulation resistance 20 M $\Omega$ /250 V

Note: Yushiron and Yushiroken are registered trademarks of Yushiro Chemical Industry Co., Ltd.

The lens material is made of a strong acrylic that resists the harmful effects of coolants. These sensors can be used with confidence even around metal processing machine that disperse oil mists.



Product Name

Velocity Oil No. 3 Daphnecut AS-30D

Yushiron Oil No.2ac (Note)

Yushiron Lubic HWC68 (Note)

Yushiroken S50N (Note)

strongly resists oils and coolant fluids, and a polycarbonate indicator cover that strongly resists ethanol .The **CX-400** series is also characterized by strong resistance to noise, reciprocal interference and cold environments.

The CX-400 series incorporates an acrylic that

### Strongly ethanol resistant CX-44□/48□

Incorporates a polycarbonate indicator cover that strongly resists ethanol. This makes it compatible with food processors that spray ethanolbased cleaning fluids.





Upgrade

Reducing environmental burdens further

# Up to 60% less power consumption

The **CX-400** series achieves reductions in power consumption of up to 60%, averaging 44% reduction when upgrading due to its unique design. These sensors reduce carbon emissions and contribute to environmental friendliness.



#### Contributing to reduced carbon dioxide emissions

Electricity consumed by the **CX-400** series has been reduced on average 10.5 mA. Calculating 8 hours/day, 260 days (operating 5 days/week) for a total of 2,080 hours/year leads to:

The **CX-400** contributes

Approx. 84.6 t annually in carbon dioxide reductions to the world

#### Upgrade ∠

Stronger noise resistance

#### Stronger inverter countermeasures

The **CX-400** has a high noise resistance then its previons model. By incorporating an inverter countermeasure circuit that appropriately shifts with peak wavelength, the sensor now resists high-frequency noise from high-voltage inverter motors and inverter lights more effectively.

#### Upgrade 🍝

Stronger output short-circuit resistance

#### Stronger inverse wiring connection protection

Strengthening the output circuit inverse polarity protection prevents sensor damage caused by mistaken output or power supply wiring.

# High Performance

#### High performance For many applications



Thanks to its unique optics and specialized design, the **CX-400**'s electronic circuits allows for consistent sensing of minute 0.4 mm 0.016 in (the thickness of a business card) differences or 10  $\mu$ m 0.394 mil ultra-thin film.

# Save

Thoroughly eliminating unnecessary waste, Reducing many environmental burdens



The **CX-400** series have three different cable length types and uses very simple packaging to reduce waste. The bag is made of polyethylene and does not emit toxic gasses.

# Thru-beam type CX-411: 10 m 32.808 ft CX-412: 15 m 49.213 ft CX-413: 30 m 98.425 ft Strong infrared beam Strong in dust and dirt CX-412/413 CX-412/413 Remarkable penetrating ability enables The infrared light source is strong in dust applications such as package content and dirt compared to the red beam type. detection come into practice. (Note) Even the thru-beam type is strong at mutual interference CX-411 Two CX-411 sensors, with their red beam light source, can be installed close together by inserting an interference prevention filter. Note: When sensing utilizing penetrating power, make Interference prevention filter (Optional) sure to verify using the actual sensor.



### **Applications**

Detecting box collapsing within the rail of stacker crane



 Synchronizing sensor for image processing systems



### Long sensing range of 5 m 16.404 ft CX-493

A long 5 m 16.404 ft sensing range is possible with the red LED type that is easy to align with the beam axis. The sensors can be used for wide automatic door shutters.



#### Retroreflective type with polarizing filters CX-491

Built-in polarizing filters ensure stable sensing even on a mirror surface object.

#### Strong against extraneous light and noise CX-491

Hardly affected by extraneous lights or noises, these sensors provide stable sensing.

#### Two sensors can be mounted close together All models

The interference prevention function lets two sensors of any type to be mounted close together precisely.

# **Retroreflective type**



#### **Applications**

Detecting pins in the case



Passage confirmation on substrate conveyor equipment



#### Beam axis alignment made easy with a high luminance spot beam CX-423

These sensors have a high luminance red LED spot beam which provides bright visibility enabling the sensing position to be checked at a glance. Because it achieved small beam spot approx. ø2 mm ø0.079 in at setting distance 100 mm 3.937 in, approx. ø5 mm Ø0.197 in at setting distance 200 mm 7.874 in, even the minutest object can be accurately detected.

#### Reduction of volume adjustment labor All models

Because these sensors possess many variations depending on the sensing range, they enable you to make optimal volume adjustment easily.



Great visibility approx. ø2 mm ø0.079 in high luminance spot beam (at setting distance 100 mm 3.937 in)

#### Introducing transparent object sensing type sensor CX-48

Our unique optical system and transparent object sensing circuit provide stable sensing of thinner transparent objects than the conventional models.



#### Transparent objects detectable with CX-48 (Typical examples)

Sensing object	Sensing object size	ze (mm in)
Glass sheet	<b>□50 □1.969</b>	t=0.7 t=0.028
Cylindrical glass	ø50 ø1.969 l =50 l =1.969	t=1.3 t=0.051
Acrylic board	<b>□50 □1.969</b>	t=1.0 t=0.039
Styrol (Floppy case)	<b>□50 □1.969</b>	t=0.9 t=0.035
Food wrapping film	□50 □1.969	t=10 µm t=0.394 mil
Cigarette case film	□50 □1.969	t=20 µm t=0.787 mil
Vinyl bag	<b>□50 □1.969</b>	t=30 µm t=1.181 mil
Pet bottle (500ml)	ø66 ø2.598	

Reflector setting range CX-481: 300 to 500 mm 11.811 to 19.685 in CX-482: 1 to 2 m 3.281 to 6.562 ft 9.370 in

CX-483: 500 to 1,000 mm 19.685 to 3

[with the RF-230 reflector at the optimum condition (Note)] Each object should pass across the beam at the center between the sensor and the reflector. { : Length of cylindrical glasses

t : Thickness of sensing object

Note: The optimum condition is defined as the condition in which the sensitivity level is set such that the stability indicator just lights up when the object is absent.

#### **Applications**

Detecting glossy electric appliances



Passage confirmation of object on a conveyor belt



Detecting plastic bottles stacked on pallets



Detecting transparent film



# Adjustable range reflective type



#### High precision type CX-441/443

#### Can sense height differences as small as 0.4 mm 0.016 in, with hysteresis of 2 % or less

An advanced optical system provides sensing performance that is approx. 2.5 times than conventional models. Even ultra-small differences of 0.4 mm 0.016 in can be detected accurately.



#### Hardly affected by colors

Both black and white objects can be sensed at the same distances. No adjuster control is needed, even when products of different colors are moving along the production line.



The difference in sensing range 1% or less between non-glossy white paper with a setting distance of 50 mm 1.969 in and non-glossy gray paper with a brightness level of 5.

# Select from 2 spot diameters as per application

Within the choice of 50 mm 1.969 in sensing range sensors, we offer small spot type of approx. Ø2 mm Ø0.079 in optimal for detecting minute objects and large spot type of approx. Ø6.5 mm Ø0.256 in capable of sensing objects covered with holes and grooves.



Spot diameter: ø2 mm ø0.079 in approx. [Positioning] Detects minute holes. Spot diameter: ø6.5 mm ø0.256 in approx. [Detection of presence /] labsence of objects Ignores minute holes and accurately detects objects.

#### The bright spot makes beam axis alignment easy All models

These sensors have a high luminance red spot that provides bright visibility. The sensing position can be checked at a glance. Because the **CX-441** sensor has a small spot beam, at approx.  $\emptyset 2 \text{ mm } \emptyset 0.079 \text{ in}$ , even the minutest object can be accurately detected.



# Can be used for sensing minute differences All models

Equipped with a 5-turn adjuster so that even challenging range settings can be handled with ease.



# BGS / FGS functions make even the most challenging settings possible!

#### The BGS function is best suited for the following case

#### Background not present

When object and background are separated



BGS

Not affected if the background color changes or someone passes behind the convevor.



#### BGS (Background suppression) function

The sensor judges that an object is present when light is received at position A of the light-receiving element (2-segment element). This is useful if the object and background are far apart. The distance adjustment method is the same as the conventional adjustment method for adjustable range reflective type sensors.



#### The FGS function is best suited for the following case



Background present

When object and background are close together When the object is glossy or uneven



Caution: Please use the FGS function together with a conveyor or other background unit.

#### FGS (Foreground suppression) function

The sensor judges that an object is present when no light is received at position B of the light-receiving element (2-segment element). Accordingly, even objects that are glossy can be sensed. This is useful if the object and background are close together, or if the object being sensed is glossy.



#### **Applications**

Small tablet detection

Detects minute objects unaffected by glossy background objects. Uses FGS function.



Biscuit detection

Stable sensing even for thin objects. Uses FGS function.



Passage confirmation

Not affected by color variations in objects and background objects. Uses BGS function.



# ORDER GUIDE

#### **Standard type**

т	me	Appearance	Sensing range	Model No	o. (Note 1)	Output	Emitting
	ype	Арреанансе		NPN output	PNP output	operation	element
E			10 m 32.808 ft	CX-411	CX-411-P		Red LED
hru-bea	ensing Ige		15 m 49.213 ft	CX-412	СХ-412-Р		Infrared
F	Long s rar		30 m 98.425 ft	NEW CX-413	NEW CX-413-P		LED
Mith polarizing			3 m 9.843 ft (Note 2)	CX-491	CX-491-P		DedUED
Retroreflective	Long sensing range		5 m 16.404 ft (Note 2)	CX-493	СХ-493-Р		Red LED
	ent g		50 to 500 mm 1.969 to 19.685 in (Note 2)	CX-481	CX-481-P		
	ranspare ct sensin		50 to 1,000mm 1.969 to 39.37 in (Note 2)	NEW CX-483	NEW CX-483-P		Infrared LED
	For th object		0.1 to 2 m 0.328 to 6.562 ft (Note 2)	CX-482	CX-482-P	Switchable	
			100 mm 3.937 in	CX-424	CX-424-P	or Dark-ON	
eflective			300 mm 11.811 in	CX-421	CX-421-P		Infrared LED
Diffuse re			800 mm 31.496 in	CX-422	СХ-422-Р		
	Narrow-view		70 to 300 mm 2.756 to 11.811 in	CX-423	СХ-423-Р		Red LED
ctive	Small spot		2 to 50 mm 0 070 to 1 060 in	CX-441	CX-441-P		
nge refle				CX-443	СХ-443-Р		Rod L ED
stable ranç			15 to 100 mm 0.591 to 3.937 in	CX-444	СХ-444-Р		INGU LED
Adjus			20 to 300 mm 0.787 to 11.811 in	CX-442	CX-442-P		

NOTE: Mounting bracket is not supplied with the sensor. Please select from the range of optional sensor mounting brackets.

Notes: 1) The model No. with "E" shown on the label affixed to the thru-beam type sensor is the emitter, "D" shown on the label is the receiver.

(e.g.) Emitter of CX-411: CX-411E, Receiver of CX-411: CX-411D
 The sensing range of the retroreflective type sensor is specified for the RF-230 reflector. The sensing range represents the actual sensing range of the sensor. The sensing ranges itemized in "A" of the table below may vary depending on the shape of sensing object. Be sure to check the operation with the actual sensing object.

Sensing range: A		$\square$	CX-491□	CX-493□	CX-481□	CX-483□	CX-482□
Sensing	$\square$	А	0 to 3 m 0 to 9.843 ft	0 to 5 m 0 to 16.404 ft	50 to 500 mm 1.969 to 19.685 in	50 to 1,000 mm 1.969 to 39.37 in	0.1 to 2 m 0.328 to 6.562 ft
Setting range of the reflector: B		В	0.1 to 3 m 0.328 to 9.843 ft	0.1 to 5 m 0.328 to 16.404 ft	100 to 500 mm 3.937 to 19.685 in	100 to 1,000 mm 3.937 to 39.37 in	0.8 to 2 m 2.625 to 6.562 ft
Sensor	Reflector						

## ORDER GUIDE

### NEW

Basic type (Without operation mode switch and sensitivity adjuster. Cable is 0.5 m 0.02 in long)

т	VDO	Appoarance	Sonsing range	Model No	o.(Note 1)	Output	Emitting
'	ype	Appearance	Sensing range	NPN output	PNP output	operation	element
			)) 10 m 32 808 ft	CX-411A-C05	CX-411A-P-C05	Light-ON	Pod LED
Thru-beam	ensing Ige		CX-4	CX-411B-C05	CX-411B-P-C05	Dark-ON	Red LLD
			)) 15 m 49 213 ft	CX-412A-C05	CX-412A-P-C05	Light-ON	Infrared
	Long s rar			CX-412B-C05	CX-412B-P-C05	Dark-ON	LED
eflective	olarizing ers		) 3 m 9.843 ff (Note 3)	CX-491A-C05-Y	CX-491A-P-C05-Y	Light-ON	Pod LED
With po	With pc filte	Optional (Note 2)		CX-491B-C05-Y	CX-491B-P-C05-Y	Dark-ON	Neu LED

NOTE: Mounting bracket is not supplied with the sensor. Please select from the range of optional sensor mounting brackets.

Notes: 1) The model No. with "E" shown on the label affixed to the thru-beam type sensor is the emitter, "D" shown on the label is the receiver. (e.g.) Emitter of CX-411A-C05: CX-411E, Receiver of CX-411A-C05: CX-411AD

2) The reflector is sold separately.

3) The sensing range of the retroreflective type sensor is specified for the RF-230 (optional) reflector. The sensing range represents the actual sensing range of the sensor. The sensing ranges itemized in "A" of the table below may vary depending on the shape of sensing object. Be sure to check the operation with the actual sensing object.



### ORDER GUIDE

#### 0.5 m 1.640 ft / 5 m 16.4 ft cable length types

0.5 m 1.640 ft / 5 m 16.404 ft cable length types (standard: 2 m 6.562 ft, basic: 0.5 m 1.640 in) are also available. When ordering this type, suffix "-**C05**" for the 0.5 m 1.640 ft cable length type, "-**C5**" for the 5 m 16.404 ft cable length type to the model No.

(Excluding CX-44 and basic type.)

(e.g.) 0.5 m 1.640 ft cable length type of CX-411-P is "CX-411-P-C05"

5 m 16.404 ft cable length type of CX-411-P is "CX-411-P-C5"

#### M8 plug-in connector type, M12 pigtailed type

M8 plug-in connector type and M12 pigtailed type are also available. When ordering this type, suffix "-Z" for the M8 connector type, "-J" for the M12 pigtailed type to the model No. (Please note that M12 pigtailed type is not available for **CX-44**□. Excluding basic type.) (e.g.) M8 connector type of **CX-411-P** is "**CX-411-P-Z**"

M12 pigtailed type of CX-411-P is "CX-411-P-J"

	Туре	Model No.	Cable length	Description	
M8 plug-in nector type	Straight	CN-24A-C2	2 m 6.562 ft		
		CN-24A-C5	5 m 16.404 ft		
	Elbow	CN-24AL-C2	2 m 6.562 ft	Can be used with all models	
Fol		CN-24AL-C5	5 m 16.404 ft		
ailed	2 0070	CN-22-C2	2 m 6.562 ft	For thru-beam type emitter	
pigta	2-core	CN-22-C5	5 m 16.404 ft	(2-core)	
M12	4	CN-24-C2	2 m 6.562 ft	Can be used with all models	
For	4-core	CN-24-C5	5 m 16.404 ft	Can be used with all models	

#### • Mating cables (2 cables are required for the thru-beam type.)



• CN-24AL-C2 CN-24AL-C5 • CN-22-C2, CN-22-C5 CN-24-C2, CN-24-C5





#### Package without reflector

NPN output type: CX-491-Y PNP output type: CX-491-P-Y

#### Accessory

• RF-230 (Reflector)



# **OPTIONS**

	Mode	el No.	0.11	Sensin	g range	Min. sensing object		
Designation	Slit mask	Sensor	Slit size	Slit on one side	Slit on both sides	Slit on one side	Slit on both sides	
		CX-411□		400 mm 15.748 in	20 mm 0.787 in		ø0.5 mm ø0.020 in	
	OS-CX-05	CX-412□	ø0.5 mm ø0.020 in	600 mm 23.622 in	30 mm 1.181 in	ø12 mm ø0.472 in		
		CX-413□		1,200 mm 47.242 in	60 mm 2.362 in			
Round slit mask		CX-411□	ø1 mm	900 mm 35.433 in	100 mm 3.937 in		ø1 mm ø0.039 in	
For thru- beam type	OS-CX-1	CX-412□		1.35 m 4.429 ft	150 mm 5.906 in	ø12 mm ø0.472 in	ø1.5 mm ø0.059 in	
sensor only		CX-413□		2.7 m 8.857 ft	300 mm 11.811 in			
		CX-411□	ø2 mm ø0.079 in	2 m 6.562 ft	400 mm 15.748 in	ø12 mm ø0.472 in	ø2 mm ø0.079 in	
	OS-CX-2	CX-412□		3 m 9.843 ft	600 mm 23.622 in		ø3 mm ø0 118 in	
		CX-413□		6 m 19.685 ft	1,200 mm 47.242 in		Ø3 IIIII Ø0. 116 III	
		CX-411□		2 m 6.562 ft	400 mm 15.748 in	ø12 mm ø0.472 in	0.5×6 mm	
	OS-CX-05×6	CX-412□	0.5×6 mm 0.020×0.236 in	3 m 9.843 ft	600 mm 23.622 in			
		CX-413□		6 m 19.685 ft	1,200 mm 47.242 in			
Rectangular slit mask		CX-411□		3 m 9.843 ft	1 m 3.281 ft			
For thru-	OS-CX-1×6	CX-412□	1×6 mm 0.039×0.236 in	4.5 m 14.764 ft	1.5 m 4.921 ft	ø12 mm ø0.472 in	1×6 mm 0.039×0.236 in	
sensor only		CX-413□		9 m 29.528 ft	3 m 9.843 ft			
		CX-411□		5 m 16.404 ft	2 m 6.562 ft			
	OS-CX-2×6	CX-412□	2×6 mm 0.079×0.236 in	7.5 m 24.606 ft	3 m 9.843 ft	ø12 mm ø0.472 in	2×6 mm 0.079×0.236 in	
		CX-413□		15 m 49.213 ft	6 m 19.685 ft	-		

Designation	Mode	el No.	Sensing range	Min. sensing object	
Interference prevention filter	<b>PF-CX4-V</b> (Vertical, Silver)	2 pcs. per set	5 m 16 404 ft (Note 1)	ø12 mm ø0.472 in	
(For <b>CX-411</b> □ only	PF-CX4-H (Horizonal, Light bro	wn) 2 pcs. per set		(Note 1)	
		CX-491□	1 m 3.281 ft (Note 2)		
	RF-210	CX-493□	1.5 m 4.921 ft (Note 2)		
		CX-481□		ø30 mm ø1.181 in	
		CX-483□	0.1 to 0.3 m 0.3288 to 0.984 ft (Note 2)		
Reflector		CX-482□	0.1 to 0.6 m 0.328 to 1.969 ft (Note 2)		
For retro-		CX-491□	1.5 m 4.921 ft (Note 2)		
sensor only		CX-493□	3 m 9.843 ft (Note 2)		
	RF-220	CX-481□	50 to 300 mm 1.969 to 11.811 in (Note 2)	ø35 mm ø1.378 in	
		CX-483□	0.1 to 0.7 m 0.328 to 2.297 ft (Note 2)		
		CX-482□	0.1 to 1.3 m 0.328 to 4.265 ft (Note 2)		
	RF-230(Note 3)	CX-491□-Y	3 m 9.843 ft (Note 2)	ø50 mm ø1.969 in	

 OS-CX Fitted on the front face of the sensor with one

touch.

**Round slit mask** 



Rectangular slit mask

Interference prevention filter

(Stainless steel)

#### Rectangular slit mask

• OS-CX-□x6 Fitted on the front face of the sensor with onetouch.

#### Interference prevention filter

## • PF-CX4-V

- (Vertical, Silver)
   PF-CX4-H
- (Horizontal, Light brown) Two sets of **CX-411** can be mounted close together.



2) Set the distance between the **CX-491**□/**493**□ and the reflector to 0.1 m 0.328 ft or more. However, see the table below for **CX-48**□.

The sensing range "A" may vary depending on the shape of sensing object. Be sure to check the operation with the actual sensing object.



3)  $\ensuremath{\text{RF-230}}$  is attached to the retroreflective type sensor other than the basic type.

# **OPTIONS**

Designation	Model No.	Description						
Reflector	MS-RF21-1	Protective mounting bracket It protects the reflector from	for <b>RF-210</b> n damage and	maintains alignment.				
mounting bracket	MS-RF22		For <b>RF-220</b>					
	MS-RF23		For <b>RF-230</b>					
	RF-11	• Sensing range (Note 4): 0.5 m 1.640 ft [ <b>CX-491</b> □] 0.8 m 2.625 ft [ <b>CX-493</b> □]	Ambient ter     Ambient hu     Notes: 1) Kee	mperature: -25 to +50 °C -13 to +122 °F midity: 35 to 85 % RH ep the tape free from				
Reflective tape	RF-12	Sensing range (Note 4): 0.7 m 2.297 ft [CX-491□] 1.2 m 3.937 ft [CX-493□] 0.1 to 0.6 m 0.328 to 1.969 ft [CX-482□]	stre mu det 2) Do det per	ess. If it is pressed too ch, its capability may eriorate. not cut the tape. It will eriorate the sensing formance.				
	RF-13	<ul> <li>Sensing range (Note 5): 0.5 m 1.640 ft [CX-491 ]</li> </ul>	Ambient temperature: -25 to +55 -13 to +131     Ambient humidity: 35 to 85 % RH					
	MS-CX2-1	Foot angled mounting brack It can also be used for mou						
Sensor mounting	MS-CX2-2	Foot biangled mounting bra It can also be used for mou	The thru-beam type sensor needs two					
bracket (Note 1)	MS-CX2-4	Protective mounting bracke	et	brackets.				
	MS-CX2-5	Back biangled mounting brain	acket					
	MS-CX-3	Back angled mounting brac	ket					
	MS-AJ1	Horizontal mounting type		Basic assembly				
	MS-AJ2	Vertical mounting type		Dasic assembly				
Universal	MS-AJ1-A	Horizontal mounting type		Lateral arm accombly				
stand (Note 2)	MS-AJ2-A	Vertical mounting type		Lateral ann assembly				
	MS-AJ1-M	Horizontal mounting type						
	MS-AJ2-M	Vertical mounting type		Assembly for reflector				
Sensor checker (Note 3)	CHX-SC2	It is useful for beam alignmen receiver position is given by	nt of thru-beam	type sensors. The optimum vell as an audio signal.				

Notes: 1) The plug-in connector type sensor does not allow use of some sensor mounting brackets because of the protrusion of the connector.

- 2) Refer to the general catalog for details of the universal sensor mounting stand.
- 3) Refer to the general catalog for details of the sensor checker CHX-SC2.

4) Set the distance between the sensor and the reflective tape to 0.1 m 0.328 ft (CX-482 :: 0.4 m 1.312 ft) or more.

5) Set the distance between the sensor and the reflective tape to 0.2 m 0.656 ft or more.

#### Universal sensor mounting stand



M6 screw



#### **Reflective tape**



#### Sensor mounting bracket

• MS-CX2-1 ø

> Two M3 (length 12 mm 0.472 in) screws with washers are attached.

• MS-CX2-2

• MS-CX2-5



Two M3 (length 12 mm 0.472 in) screws with



Two M3 (length 14 mm 1 in) screws with washers are attached

Two M3 (length 12 mm 0.472 in) screws with washers are attached.



Two M3 (length 12 mm 0.472 in) screws with washers are attached.

Sensor checker

#### CHX-SC2



45

45°

45°

45

Elevation

angle: ±45

Elevation

### **SPECIFICATIONS**

#### **Standard type**

Tvr			-	Thru-bean	า		Re	etroreflecti	ve		D."				
	$\mathbf{i}$	Туре		Long sens	sing range	With polarizing filters	Long sensing range	For transp	parent obje	ct sensing	Diff	use reflec	tive	Narrow-view	
	<u>Š</u>	NPN output	CX-411	CX-412	CX-413	CX-491	CX-493	CX-481	CX-483	CX-482	CX-424	CX-421	CX-422	CX-423	
Iter	n ∕ a	PNP output	CX-411-P	CX-412-P	CX-413-P	CX-491-P	CX-493-P	CX-481-P	CX-483-P	CX-482-P	CX-424-P	CX-421-P	CX-422-P	CX-423-P	
Sen	sing rang	je	10 m 32.808 ft	15 m 49.213 ft	30m 98.425 ft	3 m 9.843 ft (Note 2)	5 m 16.404 ft (Note 2)	50 to 500 mm 1.969 to 19.685 in (Note 2)	50 to 1,000mm 1.969 to 39.37 in (Note 2)	0.1 to 2 m 0.328 to 6.562 ft (Note 2)	100 mm 3.937 in (Note 3)	300 mm 11.811 in (Note 3)	800 mm 31.496 in (Note 3)	70 to 200 mm 2.756 to 7.874 in (Note 3)	
Sen	sing obje	ect	ø12 mm ø0.472 in or more opaque object (Note 4) specula object (Note 2, 5)					ø50 mm ø1.969 in or more transparent, translucent or opaque object (Note 2, 5)			Opaque, translucent or transparent object (Note 5)			Opaque, translucent or transparent object (Note 5) ( Min.sersing object 0.5 mm) e0.020 in copper wire	
Hys	teresis										15 % or le	15 % or less of operation distance (Note 3)			
Repea	tability (perpend	licular to sensing axis)			(	0.5 mm <mark>0.0</mark> 2	20 in or les	3			1 mm	n 0.039 in o	r less	0.5 mm 0.020 in or less	
Sup	ply volta	ge					12 to 24 V [	DC ±10 % I	Ripple P-P	10 % or les	S				
Current consumption			Emitter: 15 mA or less Receiver: 10 mA or less	Emitter: 20 mA or less Receiver: 10 mA or less	Emitter: 25 mA or less Receiver: 10 mA or less	13 mA or less		10 mA	or less		13 mA	or less	15 mA	or less	
Output			<npn 0<br="">NPN 0 • M • A • R</npn>	putput type> open-collect faximum sin pplied voltag cesidual vol	or transisto nk current: je: 30 V DC tage: 2 V oi 1 V oi	r 100 mA or less (betw r less (at 10 r less (at 16	veen output a 00 mA sink cu 6 mA sink cu	and 0 V) current) urrent)	<pnf PNF</pnf 	P output typ P open-colle • Maximum • Applied vo • Residual v	e> ector transis source cur ltage: 30 V D roltage: 2 V ( 1 V (	stor rent: 100 m 0C or less (b or less (at 1 or less (at 1	A etween outpi 00 mA source 6 mA source	ut and +V) ce current) e current)	
	Output o	operation		Switchable either Light-ON or Dark-ON											
	Short-cire	cuit protection		Incorporated											
Res	ponse tir	ne	1 ms o	or less	2 ms or less					1 ms or les:	6				
Operation indicator Orange LED (lights up when the outp					put is ON)(i	ncorporate	d on the rea	eiver for th	ru-beam ty	be)					
Stal	Stability indicator 0			D (lights up	under stab	le light rec	eived condi	tion or stab	le dark con	dition)(inco	porated on	the receive	er for thru-be	eam type)	
Pow	ver indica	itor	Green LED is ON) (inco	Green LED (lights up when the power is ON) (incorporated on the emitter)											
Sen	sitivity ad	djuster		Continuously variable adjuster (incorporated on the receiver for thru-beam type)											
Auto	omatic in ention fu	terference inction	Two units of sensors can be mounted close together with interference prevention filters. (Sensing range: 5 m 16.404 ft)			Incorporated (Two units of sensors can be mounted close together.)									
	Protectio	on						IP67	(IEC)						
ance	Ambient	temperature		-25 to +5	5 °C -13 to	+131 °F (N	lo dew cono	densation o	r icing allow	ved), Storaç	ge: -30 to +7	70 °C -22 to	) +158 °F		
esist	Ambient	humidity					35 to 85	% RH, Stor	rage: 35 to	85 % RH					
tal re	Ambient	illuminance				Inca	indescent li	ght: 3,000 ł	x at the ligh	nt-receiving	face				
men	Voltage v	vithstandability			1,000 V A	C for one m	in. betweer	n all supply	terminals c	onnected to	gether and	enclosure			
iron	Insulatio	n resistance		20 MΩ	, or more, v	vith 250 V E	DC megger	between al	supply terr	minals conr	ected toget	her and en	closure		
Б	Vibration	n resistance	1	0 to 500 Hz	z frequency	, 1.5 mm <mark>0</mark> .	059 in dout	ole amplitud	le (10 G ma	ax.) in X, Y a	and Z direct	ions for two	hours eac	h	
	Shock re	esistance			500 m/	s <sup>2</sup> accelera	tion (50 G a	approx.) in λ	K, Y and Z o	directions fo	or three time	es each			
Emit	ting eleme	nt (modulated)	Red LED	Infrare	d LED	Red	LED		nfrared LEI	0	I	nfrared LEI	)	Red LED	
	Peak emis	sion wavelength	680 nm 0.027 mil	870 nm 0.034 mil	850 nm 0.033 mil	680 nm 0.027 mil	650 nm 0.026 mil	87	0 nm 0.034	mil	860	0 nm 0.033	mil	645 nm 0.025 mil	
Material Enclosure: PBT (Polyb					butylene te	rephthalate	), Lens: Acr	ylic (CX-48	: Polycarb	onate), Indi	cator cover:	Acrylic (C)	<b>(-48</b> ⊡: Polyo	carbonate)	
Cable					0.2 mr	n∠ 3-core (t	hru-beam t	ype emitter:	2-core) ca	btyre cable	, 2 m 6.562	tt long			
Cab	ne extens	Not	E>		to total 100	m 328.084 f	t is possible	with 0.3 mr	n∸, or more,	cable (thru-	beam type:	both emittei	and receive	er)	
Wei	ght	Croos	Emitter: 45 g a	upprox., Receive	i: ou g approx.			0 a anne		ou g approx		60 ~ -	PPROV		
۸ -		Gross	1	uu g appro:	κ.			ou g approx				60 g a	pprox.		
Accessories							RF-23	(Reflector	). T pc.						

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F. 2) The sensing range and the sensing object of the retroreflective type sensor are specified for the **RF-230** reflector. The sensing range represents the actual sensing range of the sensor. The sensing ranges itemized in "A" of the table below may vary depending on the shape of sensing object. Be sure

actual sensing range of the sensor. The sensing ranges itemized in "A" of the table below may vary depending on the shape of sensing object. Be sure to check the operation with the actual sensing object.

Sensing		CX-491□	CX-493□	CX-481□	CX-483□	CX-482□
Sensing	А	0 to 3 m	0 to 5 m	50 to 500 mm	50 to 1,000 mm	0.1 to 2 m
object		0 to 9.843 ft	0 to 16.404 ft	1.969 to 19.685 in	1.969 to 39.37 in	0.328 to 6.562 ft
Setting range	В	0.1 to 3 m	0.1 to 5 m	100 to 500 mm	100 to 1,000 mm	0.8 to 2 m
of the reflector: B		0.328 to 9.843 ft	0.328 to 16.404 ft	3.937 to 19.685 in	3.937 to 39.37 in	2.625 to 6.562 ft
Sensor Reflector			•	•	•	

3) The sensing range and hysteresis of the diffuse reflective type sensor are specified for white non-glossy paper ( $200 \times 200 \text{ mm } 7.874 \times 7.874 \text{ in}$ ) as the object. 4) If slit masks (optional) are fitted, an object of  $\emptyset 0.5 \text{ mm } \emptyset 0.020$  in (using round slit mask) can be detected.

5) Make sure to confirm detection with an actual sensor before use.

### **SPECIFICATIONS**

#### **Standard type**

Туре		Type		Adjustable ra	nge reflective						
		.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	Small spot								
	lel No.	NPN output	CX-441	CX-443	CX-444	CX-442					
Item	N V POM	PNP output	CX-441-P	СХ-443-Р	CX-444-P	CX-442-P					
Adju	stable rang	e (Note 2)	20 to 50 mm 0.	787 to 1.969 in	20 to 100 mm 0.787 to 3.937 in	40 to 300 mm 1.575 to 11.811 in					
Sensin	ig range (with w	hite non-glossy paper)	2 to 50 mm 0.0	079 to 1.969 in	15 to 100 mm 0.591 to 3.937 in	20 to 300 mm 0.787 to 11.811 in					
Hyst (with	eresis white non-	glossy paper)	:	2 % or less of operation distance	2	5 % or less of operation distance					
Repe	eatability		Along sensing axis: 1 mm 0.039	Along sensing axis: 1 mm 0.039 in or less, Perpendicular to sensing axis: 0.2 mm 0.008 in or less (with white non-glossy paper)							
Supp	oly voltage			12 to 24 V DC ±10 % F	Ripple P-P 10 % or less						
Curre	ent consum	ption		25 mA	or less						
Output			<npn output="" type=""> NPN open-collector transistor • Maximum sink current: 1 • Applied voltage: 30 V DC o • Residual voltage: 2 V or 1 V or</npn>	<ul> <li>'N output type&gt;</li> <li>'N output type&gt;</li> <li>'N open-collector transistor</li> <li>Maximum sink current: 100 mA</li> <li>Applied voltage: 30 V DC or less (between output and 0 V)</li> <li>Residual voltage: 2 V or less (at 100 mA sink current)</li> <li>1 V or less (at 10 mA sink current)</li> </ul>							
	Output op	eration		Switchable either Detecti	ion-ON or Detection-OFF						
	Short-circu	uit protection	orated								
Resp	oonse time			1 ms (	or less						
Oper	ration indica	ator		Orange LED (lights up	when the output is ON)						
Stab	ility indicate	or		Green LED (lights up under stat	ble operating condition) (Note 3)						
Dista	ance adjust	er	5-turn mechanical adjuster								
Sens	sing mode		BGS / FGS functions Switchable with wiring of sensing mode selection input								
Automa	tic interference pre	evention function (Note 4)	Incorporated								
	Protection		IP67 (IEC)								
nce	Ambient te	emperature	-25 to +55 °C -13 to +	131 °F (No dew condensation o	r icing allowed), Storage: -30 to -	+70 °C -22 to +158 °F					
sista	Ambient h	umidity		35 to 85 % RH, Stor	rage: 35 to 85 % RH						
tal re	Ambient il	uminance		Incandescent light: 3,000 &	x at the light-receiving face						
ment	Voltage wi	thstandability	1,000 V AC	for one min. between all supply	terminals connected together an	d enclosure					
/iron	Insulation	resistance	20 MΩ, or more, with	th 250 V DC megger between all	supply terminals connected toge	ether and enclosure					
En	Vibration r	esistance	10 to 500 Hz freq	uency, 3 mm 0.118 in double am	plitude in X, Y and Z directions for	or two hours each					
	Shock res	istance	500 m/s <sup>2</sup>	<sup>2</sup> acceleration (50 G approx.) in λ	K, Y and Z directions for three tim	nes each					
Emit	ting elemer	nt	Re	ed LED (Peak emission waveleng	gth: 650 mm 25.591 in, modulate	ed)					
Spot	diameter		ø2 mm ø0.079 in approx. (at 50 mm 1.969 in distance)	ø6.5 mm ø0.256 in approx. (at 50 mm 1.969 in distance)	ø9 mm ø0.354 in approx. (at 100 mm 3.937 in distance)	□15 mm □0.591 in approx. (at 300 mm 11.811 in distance)					
Mate	erial		Enclosure: PBT (	Polybutylene terephthalate), Ler	ns: Polycarbonate, Indicator cove	er: Polycarbonate					
Cabl	е			0.2 mm <sup>2</sup> 4-core cabtyre	cable, 2 m 6.562 ft long						
Cabl	e extensior	1	Extensi	on up to total 100 m 328.084 ft is	s possible with 0.3 mm <sup>2</sup> , or more	, cable.					
Weig	ght			Net weight: 55 g approx., 0	Gross weight: 65 g approx.						

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F. 2) The adjustable range stands for the maximum sensing range which can be set with the distance adjuster. The sensor can detect an object 2 mm 0.079 in [CX-444(-P): 15 mm 0.591 in, CX-442(-P): 20 mm 0.787 in], or more, away.



3) Refer to the manual or the general catalog for operation of the stability indicator.4) Note that detection may be unstable depending on the mounting conditions or the sensing object. In the state that this product is mounted, be sure to check the operation with the actual sensing object.

### **SPECIFICATIONS**

#### **Basic type**

V				Thru-	beam		Retrore	flective				
		Туре			Long sens	sing range	With polar	zing filters				
/	$\langle \rangle$		Light-ON	Dark-ON	Light-ON	Dark-ON	Light-ON	Dark-ON				
	i	NPN output	CX-411A-C05	CX-411B-C05	CX-412A-C05	CX-412B-C05	CX-491A-C05-Y	CX-491B-C05-Y				
Item	Mode	PNP output	CX-411A-P-C05	CX-411B-P-C05	CX-412A-P-C05	CX-412B-P-C05	CX-491A-P-C05-Y	CX-491B-P-C05-Y				
Sens	sing range		10 m 3	2.808 ft	15 m 4	9.213 ft	3 m 9.843	ft (Note 2)				
Sens	sing object		ø12	2 mm ø0.472 in or mo	ø50 mm ø1.969 in or more transparent, translucent or opaque object (Note 2, 4)							
Hyst	eresis											
Repea	tability (perpend	licular to sensing axis)	0.5 mm 0.020 in or less									
Supp	oly voltage		12 to 24 V DC ±10 % Ripple P-P 10 % or less									
Current consumption			Emitter: 15 Receiver: 10	mA or less 0 mA or less	Emitter: 20 Receiver: 1	mA or less 0 mA or less	13 mA	or less				
Output			<npn output="" type=""> NPN open-collector • Maximum sink • Applied voltage: • Residual voltage</npn>	SNPN output type> NPN open-collector transistor <ul> <li>Maximum sink current: 100 mA</li> <li>Applied voltage: 30 V DC or less (between output and 0 V)</li> <li>Residual voltage: 2 V or less (at 100 mA sink current)</li> <li>1 V or less (at 16 mA sink current)</li> </ul> SNP output type> PNP open-collector transistor <ul> <li>Maximum source current: 100 mA</li> <li>Maximum source current: 100 mA</li> <li>Applied voltage: 30 V DC or less (between output and +V)</li> <li>Residual voltage: 2 V or less (at 100 mA sink current)</li> <li>1 V or less (at 16 mA sink current)</li> </ul>								
Short-circuit protection Incorporated												
Resp	oonse time				1 ms (	or less						
Oper	ration indica	ator	Orar	nge LED (lights up wh	en the output is ON)(i	ncorporated on the re	ceiver for thru-beam t	ype)				
Stab	ility indicate	or	Green LED (lights up	o under stable light rec	eived condition or stab	le dark condition)(incor	porated on the receive	r for thru-beam type)				
Pow	er indicator		Green LED (lights up when the power is ON) (incorporated on the emitter)									
Sens	sitivity adjus	ster										
Auto preve	matic interf ention func	erence tion	Two units of sensors close together with in filters. (Sensing range	can be mounted terference prevention e: 5 m 16.404 ft)	n Incorporated (Two be mounted close			inits of sensors can ogether.)				
6	Protection			IP67 (IEC)								
ance	Ambient te	emperature	-25 to +55	°C -13 to +131 °F (No	o dew condensation o	r icing allowed), Stora	ge: -30 to +70 °C -22	to +158 °F				
esist	Ambient h	umidity			35 to 85 % RH, Stor	rage: 35 to 85 % RH						
tal re	Ambient il	luminance		Incar	ndescent light: 3,000 &	x at the light-receiving	face					
nen	Voltage w	thstandability	1	,000 V AC for one mi	n. between all supply	terminals connected t	ogether and enclosur	e				
ironi	Insulation	resistance	20 MΩ, c	or more, with 250 V D	C megger between all	supply terminals con	nected together and e	nclosure				
Env	Vibration r	esistance	10 to 500 Hz f	requency, 1.5 mm 0.0	59 in double amplitud	le (10 G max.) in X, Y	and Z directions for the	vo hours each				
	Shock res	istance		500 m/s <sup>2</sup> accelerati	ion (50 G approx.) in X	K, Y and Z directions f	or three times each					
Emit	ting elemer	nt (modulated)	Red	LED	Infrare	d LED	Red	LED				
	Peak emis	sion wavelength	680 nm (	0.027 mil	870 nm (	0.034 mil	680 nm (	0.027 mil				
Mate	erial			Enclosure: PBT (Pc	lybutylene terephthal	ate), Lens: Acrylic, Ind	licator cover: Acrylic					
Cabl	е			0.2 mm <sup>2</sup> 3-core (thr	u-beam type emitter:	2-core) cabtyre cable,	0.5 m 1.640 ft long					
Cabl	e extensior	1	Extension up to to	tal 100 m <u>328.084 ft</u> i	s possible with 0.3 mr	n <sup>2</sup> , or more, cable (thr	u-beam type: both em	nitter and receiver)				
Weid	t	Net	E	Emitter: 20 g approx.,	Receiver: 20 g appro>	κ.	20 g a	pprox.				
	,	Gross		50 g a	pprox.		30 g approx.					

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F.
 2) The sensing range and the sensing object of the retroreflective type sensor are specified for the **RF-230** reflector (optional). The sensing range represents the actual sensing range of the sensor. The sensing ranges itemized in "A" of the table below may vary depending on the shape of sensing object. Be sure to check the operation with the actual sensing object.



3) If slit masks (optional) are fitted, an object of Ø0.5 mm Ø0.020 in (using round slit mask) can be detected.
4) Make sure to confirm detection with an actual sensor before use.

# I/O CIRCUIT AND WIRING DIAGRAMS

#### NPN output type

#### I/O circuit diagram



Notes: 1) The emitter of the thru-beam type sensor does not incorporate the output.

- Sensing mode selection input is incorporated only for the 2) CX-44 adjustable range reflective type. When using the CX-44, be sure to wire the sensing mode selection input (pink / 2) as mentioned \*1. Unstable operation may occur.
- 3) When the mating cable is connected to the plug-in connector type of CX-44, its color is white.

·	
• Sensing mode selection input BGS function: Connect to 0 V	
FGS function: Connect to +V	

\*1

Symbols ... D : Reverse supply polarity protection diode ZD : Surge absorption zener diode Tr : NPN output transistor

#### Wiring diagram



Notes: 1) The emitter of the thru-beam type sensor does not incorporate the black wire. 2) The pink wire is incorporated only for the CX-44 adjustable range reflective type. When using the **CX-44**, be sure to wire the pink wire as mentioned \*1. Unstable operation may occur.

3) When the mating cable is connected to the plug-in connector

type of CX-44 , its color is white.

\*1

 Sensing mode selection input BGS function: Connect to 0 V FGS function: Connect to +V

#### **Connector pin position**

#### M8 plug-in connector type



#### M12 pigtailed type



The emitter of the thru-beam type sensor does not incorporate the output. Notes: 1) Sensing mode selection input is incorporated only for the CX-44 adjustable range reflective type. When using the CX-44 , be sure to wire the sensing mode selection input (pink / 2). Unstable operation may occur.

#### **PNP** output type

#### I/O circuit diagram

Color code / Connector pin No. of the connector type



Internal circuit - User's circuit

- Notes: 1) The emitter of the thru-beam type sensor does not incorporate the output.
  - 2) Sensing mode selection input is incorporated only for the CX-44 -P adjustable range reflective type. When using the CX-44 -P, be sure to wire the sensing mode selection input (pink / 2) as mentioned \*1. Unstable operation may occur.
  - 3) When the mating cable is connected to the plug-in connector type of CX-44 -P, its color is white.

• Sensing mode selection input BGS function: Connect to 0 V FGS function: Connect to +V

Symbols D	: Reverse supply polarity protection diode
ZD	: Surge absorption zener diode
Tr	: PNP output transistor

#### Wiring diagram



- Notes: 1) The emitter of the thru-beam type sensor does not incorporate the black wire. 2) The pink wire is incorporated only for the CX-44D-P adjustable range reflective type. When using the CX-44 -P, be sure to wire the pink wire as mentioned \*1. Unstable operation may occur.
  - 3) When the mating cable is connected to the plug-in connector type of CX-44 -P, its color is white.

\*1



#### **Connector pin position**

#### M8 plug-in connector type





Notes: 1) The emitter of the thru-beam type sensor does not incorporate the output. Sensing mode selection input is incorporated only for the 2) CX-44 -P adjustable range reflective type. When using the CX-44 -P, be sure to wire the sensing mode selection input (pink / 2). Unstable operation may occur.

\*1

• Never use this product as a sensing device for personnel protection.

 In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection applicable in each region or country.

#### Mounting

• The tightening torque should be 0.5 N·m or less.



#### Wiring

- Make sure that the power supply is off while wiring.
- Take care that wrong wiring will damage the sensor.
- Verify that the supply voltage variation is within the rating.
- If power is supplied from a commercial switching regulator, ensure that the frame ground (F.G.) terminal of the power supply is connected to an actual ground.
- In case noise generating equipment (switching regulator, inverter motor, etc.) is used in the vicinity of this product, connect the frame ground (F.G.) terminal of the equipment to an actual ground.

- Do not run the wires together with high-voltage lines or power lines or put them in the same raceway. This can cause malfunction due to induction.
- Extension up to total 100 m 328.084 ft (thru-beam type: both emitter and receiver) is possible with 0.3 mm<sup>2</sup>, or more, cable. However, in order to reduce noise, make the wiring as short as possible.
- Make sure that stress by forcible bend or pulling is not applied directly to the sensor cable joint.

#### Others

- This product has been developed / produced for industrial use only.
- Do not use during the initial transient time (50 ms) after the power supply is switched on.
- Take care that the sensor is not directly exposed to fluorescent light from a rapid-starter lamp or a high frequency lighting device, as it may affect the sensing performance.
- This sensor is suitable for indoor use only.
- Do not use this sensor in places having excessive vapor, dust, etc., or where it may come in direct contact with water or corrosive gas.
- Take care that the sensor does not come in direct contact with water, oil, grease or organic solvents, such as, thinner, etc.
- This sensor cannot be used in an environment containing inflammable or explosive gases.
- Never disassemble or modify the sensor.

# DIMENSIONS (Unit: mm in)

CX-41□ Sensor Sensitivity adjuster (Note 1) Operation indicator (Orange)(Note 2) 7.85 <mark>0.30</mark>9 3.95 0.156 Stability indicator (Green)(Note 3) Operation mode switch (Note 1) 20 3 Beam axis 2.3 15.5 0.61 31 25.4 ø3.7 ø0.146 cable, 2 m 6.562 ft long (Note 4) 2-M3x0.5 0.02 thru-hole threads 3-core (emitter: 2-core)×0.2 mm<sup>2</sup> insulator diameter: ø1.2 ø0.047

Notes: 1) Not incorporated on the emitter and the basic type sensor. 2) It is the power indicator (green) on the emitter.

- 3) Not incorporated on the emitter.
- 4) Basic type: 0.5 m 1.640 ft long.

The CAD data in the dimensions can be downloaded from the website: panasonic-electric-works.net/sunx





2) It is the power indicator (green) on the emitter.

The CAD data in the dimensions can be downloaded from the website: panasonic-electric-works.net/sunx



Notes: 1) Not incorporated on the emitter.

2) It is the power indicator (green) on the emitter.







Notes: 1) Not incorporated on the Bacic type sensors. 2) Basic type: 0.5 m 1.640 ft long.



CX-44□-Z

Sensor



#### The CAD data in the dimensions can be downloaded from the website: panasonic-electric-works.net/sunx

#### **RF-220** RF-230 Reflector (Accessory for the retroreflective type sensor) Reflector (Optional) **RF-210** Reflector (Optional) 33.3 50.3 1.311 12.8 35.3 1 300 M3 nut mounting holes Reflector (for mounting at the back) 49.3 59.31 2.335 11 0 34.3 Base ¥ 30 42.31 2-ø3.4 ø0.134 thru-holes 21 827 3.2 0.126 (for mounting at the side) 25 ÷ ÷ 2-ø3.4 ø0.134 holes, 6 0.236 deep 10 0 -0 <u>5 0.1</u>97 8 0.315 10 ł 3.3 0.130 (for mounting at the back) \_3.3 0.130 2-ø3.6 ø0.142 mounting holes 40 1.575 25 8.3 - 14 → 8.3 -2-M3 nut mounting holes (for mounting at the side) Material: Acrylic (Reflector) ABS (Base) Material: Acrylic (Reflector) 2-ø4.6 ø0.181 mounting holes Material: Acrylic (Reflector) ABS (Base) ABS (Base) Two M3 (length 8 mm 0.315 in) screws with washers and two nuts are attached. **RF-11** Reflective tape (Optional) **RF-12** Reflective tape (Optional) **RF-13** Reflective tape (Optional) 30 30 .18 30 .181 0.5 \_0.7 0.028 28 .102 (28 1.102 0.7 0.028 30 8 0.315 6 Rear surface Ŧ pressure-sensitive adhesive Effective Adhesive reflecting surface \tape 25 (23) (0.906)Reflective surface (Acrylic) Material: Acrylic Adhesive tape Effective reflecting surface Material: Acrylic

#### MS-CX2-1

DIMENSIONS (Unit: mm in)



Material: Stainless steel (SUS304) Two M3 (length 12 mm 0.472 in) screws with washers are attached.

#### Sensor mounting bracket (Optional)

#### **Assembly dimensions**

Mounting drawing with the receiver of **CX-41**  $\square$ 







The CAD data in the dimensions can be downloaded from the website: panasonic-electric-works.net/sunx

#### MS-CX2-2



holes 10 25 23 15.5 0.610 ļ 1 7 0.276 197 4 0 157 4.5

8-ø3.4 ø0.134

Material: Stainless steel (SUS304) Two M3 (length 12 mm 0.472 in) screws with washers are attached.

#### MS-CX2-4



#### MS-CX2-5



Two M3 (length 12 mm 0.472 in) screws with washers are attached.

#### Sensor mounting bracket (Optional)



Sensor mounting bracket (Optional)

#### **Assembly dimensions**



Sensor mounting bracket (Optional)

#### **Assembly dimensions**



The CAD data in the dimensions can be downloaded from the website: panasonic-electric-works.net/sunx

#### MS-CX-3



Material: Stainless steel (SUS304) Two M3 (length 12 mm 0.472 in) screws with washers are attached.

#### **MS-RF21-1**



Two M3 (length 12 mm 0.472 in) screws with washers are attached.

#### MS-RF22



Two M3 (length 8 mm 0.315 in) screws with washers are attached.

#### Sensor mounting bracket (Optional)

#### **Assembly dimensions**



Reflector mounting bracket for RF-210 (Optional)

#### **Assembly dimensions**





Reflector mounting bracket for RF-220 (Optional)

#### **Assembly dimensions**



#### MS-RF23



Material: Cold rolled carbon steel (SPCC) (Uni-chrome plated)

Two M4 (length 10 mm 0.394 in) screws with washers are attached.



Note: The dimensions in the brackets indicate the adjustable range of the movable part.

# Assembly dimensions with CX-400 series (Mounting part only)



Reflector mounting bracket for RF-230 (Optional)

#### Assembly dimensions





Note: The dimensions in the brackets indicate the adjustable range of the movable part.

# Assembly dimensions with RF-210 (Reflector) (Mounting part only)





- Notes: 1) The dimensions in the brackets indicate the adjustable range of the movable part.
  - Refer to MS-AJ1 / MS-AJ2 for the assembly dimensions with the sensor mounting bracket, sensor or reflector.



Note: The dimensions in the brackets indicate the adjustable range of the movable part.

# Assembly dimensions with RF-220 (Reflector) (Mounting part only)



#### The CAD data in the dimensions can be downloaded from the website: panasonic-electric-works.net/sunx



- Notes: 1) The dimensions in the brackets indicate the adjustable range of the movable part.
  - Refer to MS-AJ1 / MS-AJ2 for the assembly dimensions with the sensor mounting bracket, sensor or reflector.



Note: The dimensions in the brackets indicate the adjustable range of the movable part.

# Assembly dimensions with RF-230 (Reflector) (Mounting part only)



# Promoting a totally lead-free working environment

Protecting the environment is one of our guiding business principles

#### We are now working to eliminate the use of lead in all our in-house manufacturing processes such as in reflow ovens, hand soldering and parts and substrates procurement.

### Using simple packaging

Simple, environmentally friendly packaging material reduces waste.



# ISO 14001 environmental management system certification acquired



Our Nagoya Head Office and Factory acquired ISO 14001 certification in September 1999. Now and into the future, we will continuously improve environmental management systems based on our Environment Policy, which focuses on the promotion of environmentally friendly business activities and product development.

Please contact .....

# Panasonic Electric Works SUNX Co., Ltd.

2431-1 Ushiyama-cho, Kasugai-shi, Aichi, 486-0901, Japan ■Telephone: +81-568-33-7211 ■Facsimile: +81-568-33-2631 Overseas Marketing Department ■Telephone: +81-568-33-7861 ■Facsimile: +81-568-33-8591 panasonic-electric-works.net/sunx



All Rights Reserved ©Panasonic Electric Works SUNX Co., Ltd. 2010

Spedfications are subject to change without notice.