

Type 4 PLe SIL3

SF4B series Ver.2



Protection structure

New version with improved environmental resistance performance

Robust type SF4B-□G<V2>

2012.02 panasonic.co.jp/id/pidsx/global

Advanced light curtains at the forefront of the industry

Protection structure IP67 is achieved in such size

Improved environmental resistance performance and easier operability New structure

A seamless structure with least seam area possible is newly developed. The inner unit is protected by a cylindrical inner case. Seams such as unit and lens surfaces have been greatly reduced, so that particles such as oil mists and dust are prevented from getting in, rising its environmental resistance performance.

SF4B series has passed the tests of IP65 and IP67 as specified by IEC / JIS standards. (Ver.2 only)

IEC / JIS	Description	
IP65	No harmful effect due to direct water jet from any direction	J ∭⊠(¢
IP67	No water penetration due to immersion in water under specified conditions	

* Refer to each standard for details of test conditions.

This new structure does not use adhesive or double-sided tape on the joints like with the previous models. There is no need to worry about water immersion or corrosion such as a coolant causing the adhesive to strip off.

Cylindrical inner case protects the internal unit.

Inner case

Error details can be understood at a glance


Equipped with a digital error indicator

The system constantly checks the light curtain for problems such as incorrect cable wiring, disconnection, short-circuits, internal circuit problems, and incoming light problems. Details of any electrical problems such as at equipment startup will appear on the digital display. The inconvenience of the previous method of counting the number of LED blinks is no longer needed.

Error number notification means smooth support via telephone









Achieving protection structure IP67 while keeping its slim body.

Locate problems easily and quickly

Light curtain diagnosis software	Free download available from our websit
Simply select the error no. that is displayed on the light curta visually. Coping process is also displayed for a quick resolution	in on the PC screen, and the section of error will be displayed on of the problem.
s	Select the number of connected light curtains (1, 2,
	Enter the error condition (error no.) (0, 19, F)
	₩
	Diagnosis starts!
	Section of error blinks
	Coping process is displayed
	 No need to connect to light curtain
	 Software can diagnose as many light curtains as possible
	 Diagnosis on the spot to ensure maintenance
9	 Misconnection can also be diagnosed, which contributes to shortened start-up time
- CRU	[Diagnosis software operation conditions] Operable in Windows Vista / XP / XP embedded (Jap / Eng). Approx. 1.5 MB of free space is required.

* Windows® is a registered trademark of Microsoft Corporation in the United States and other countries.

Resistant to impact, lessening damage to workpiece Robust type SF4BG<V2>

Thick and robust housing resistant to impact

The SF4B-G series light curtain is enclosed in a 5 mm (0.197 in) thick robust metal case, protecting the workpiece from various types of impact, such as collision or being stepped on.







Stepped on - Kicked


Collision - Impact





No guard needed

The robust light curtain can be used without an L-shape or U-shape guard, reducing installation and maintenance.





Fully protected sensing surface

The sensing surface is fully protected by narrowing and deepening the exposed area of the sensing surface.




Front protection cover

Average

thickness

5_{mm} 0.197 in

The front protection cover protects the sensing surface from welding spatter and other grime, and reduces damage due to collisions. The beam axis adjuster can be attached without removing the front protection cover.



IP67 protected structure


The seamless structure protects the sensor from being exposed to water.



The inner unit is fully protected with a thick metal case. Impact Robust between the workpiece and the sensor is prevented by narrowing and deepening the exposed area of the sensing surface.

Round design minimizes damage to the workpiece

The case is designed so that shock upon impact is dissipated alleviating potential damage to the workpiece in the event of a collision.




Workpiece not contaminated with paint

The body has a alumite-treated case whereby paint does not stick to the workpiece in the event of a collision.

Enables series connection with standard type possible


The mating cable is standard, allowing the robust and standard types to be connected in series. The mating cable can be removed or attached while the mounting bracket is fixed, allowing easy maintenance.



Use robust type only for required sections

Mounting bracket for simple & secure installation

The light curtain and the mounting bracket are firmly secured with just two bolts. The light curtain is situated in the center of the mounting bracket, preventing beam axis deviation. The dimple structure makes alignment easy to adjust.



Black and yellow caution tape

Black and yellow striped attention tape is attached to the side of the light curtain, alerting workers to use caution. Hazardous openings are very obvious.






• Fit to width of light curtain

- Made of fabric, making it easy to cut
- · Prevents scratches in the event of a collision

The cylindrical frame construction allows mechanical shock to dissipate upon impact, minimizing severe damage in the event of a collision. This unique design minimizes the possibility of beam axis misalignment and provides a safer workplace.

Impact-friendly structure


A universal design that can be used anywhere in the world



Note: Except for SF4B-□G<V2>

Supports both PNP and NPN polarities in a single model

The **SF4B** series combines PNP transistor output and NPN transistor output in a single model. Overseas equipment that uses PNP, replacement with NPN sensors, factories that are positively grounded, and transfer of equipment overseas are all situations where the control circuits for a single model are suitable for use worldwide.





PNP / NPN polarity indicator Either PNP or NPN side lights depending on which is selected.

Available

Global support for press machine / shear (paper cutting machine) safety


Can be widely used for press machines and other types of equipment from Japan, Europe, North America, South Korea, and China.

Туре	Model No.	Machinery Directive		UL Certified	Japanese Press Machine Support	Japanese Shear (Paper Cutter) Support	S-mark certification	Korean Press / Cutting Machine	Chinese GB Compatibility
Light curtains	SF4B-□ <v2></v2>	•	•	•			•		•
	SF4B-□-01 <v2></v2>	•	•	•	• (No.TA347)	• (No.TA363)		·	•
	SF4B-□G <v2></v2>	•	•	•				·	
	SF4B-□-03 <v2></v2>	•	•	•				• (No.09-AV4BI-0001 to 0009)	
	SF-C11	•	•	•	• (No.TA348) (Note 1)		•		
	SF-C12	•	•	•	·				
units	SF-C13	•	•	•	• (No.TA349) (Note 1)		•		
	SF-C14EX	•	•	•					
	SF-C14EX-01	•	•	•	• (No.TA350) (Note 1)				

Note: In combination with SF4B-D-01<V2>. Please inquire for the details.

A unified response time of 14 ms for all models makes setup easy


A fast response time of 14 ms has been achieved regardless of the number of beam channels, the beam axis pitches and the number of units connected in series. This reduces calculation work required for the safety distance.




Muting control function is built into light curtain Safety circuits are selectable

A muting control function is provided to increase both safety and productivity

The light curtain is equipped with a muting control function that causes the line to stop only when a person passes through the light curtain, and does not stop the line when an object passes through. The muting sensors and muting lamps can be connected directly to the light curtain so that a exclusive controller is not required for muting. This both reduces costs and increases safety and productivity.







Override function allows the line to be restarted smoothly after it has stopped while muting control was active

In case the power turns off while the light curtain has been interrupted by an object or in case the line stops before the muting conditions have been established (if only one muting sensor has been interrupted), the line can be restarted smoothly without having to remove the object that is interrupting the light curtain.

(e.g.) When power turns off while light curtain was interrupted



Object must be removed before restart




(excluding SF4B-□-03<V2>)

Smooth restart

Equipped with a safety circuit that does not require an exclusive safety relay unit

The light curtain has a built-in external device monitoring function (such as for fused relay monitoring) and an interlock function. The safety circuit is constructed so that a separate safety relay unit is not needed, and the control board has become smaller to help to contribute to lower costs.




Note: Contact the manufacturers for details on the recommended products.

A commitment to design that is easy to use


Beam-axis alignment indicators show the incident light position at a glance

Beam-axis alignment indicators display the beam channels of the light curtain in four blocks. When the beam channel at the bottommost channel (or topmost channel), which is used as a reference for beam-axis alignments, is correctly aligned, the LED blinks red. After this, each block lights red as the beam axes successively become aligned. When all channel beam axes are aligned, all LEDs light green. The display also has a stability indicator (STB) added so that setup can be carried out with greater stability.



Laser alignment tool for easy installation

The tool performs beam-axis alignment using a laser beam spot. As the tool is battery-operated, it is possible to perform beam-axis alignment before actual powering on the equipment.



Easy to distinguish receiver and emitter

Emitter is in gray; receiver is in black. Whether during startup or maintenance, troubles due to incorrect wiring or false recognition can be greatly reduced. Moreover, model No. can be confirmed from the front face of the light curtain.

Mutual interference is reduced without needing for interference prevention lines

The light curtain is equipped with the ELCA (Extraneous Light Check & Avoid) function. Because it automatically shifts the scan timing of the light curtain in order to avoid interference, it is not necessary to wire interference prevention lines between machineries.

Greatly improved ease of installation (excluding sF4B-□G)

The hexagon-socket head bolts used for aligning the beam axis can be tightened from the front of the light curtain. Beam adjustment can be carried out easily while checking on 360° rotation Hexagon-socket the bolts. when used with M5 hexagon-socket head bolt for beam-axis Also, the head bolt for alignment alignment (up to ±15°) beam-axis alignment part is directly fixed by M5 bolts to prevent beam Hexagon-socket misalignment. head bolt for alignment (360° rotation for every 30°) Hexagonal wrench Made of die-cast! Align from the front! **Direct fixing to prevent misalignment!** Few number of bolts! Black connector Grav cable with black line Black cover RECEIVER Receiver

Model No. is shown on the front face of the sensor

Emitter				
	Gray connector	Gray cable	Gray cover	ÉMITTER

Reducing the number of malfunctions caused by extraneous light

Double scanning method and retry processing are two new functions exclusive to our company, which are effective in eliminating the effects of momentary extraneous light from peripheral equipment. The reduction in operating errors caused by extraneous light reduces frequent stopping of machinery.


Options exclusive for light curtain are available for an easy construction of safety circuit

Handy-controller SFB-HC* that enables the user to select a variety of settings SFB-HC

Separate muting control function for each beam channel

The handy-controller **SFB-HC*** (optional) can be used to carry out muting control for specified beam channels only. Because individual beam channel can be specified to suit the object, separate guards to prevent entry do not need to be set up.

While muting control is active (line operating)



For example, depending on the height of the object, the muting function can be activated for 10 beam channels starting from the bottom, so that if the 11th or subsequent beam channels are interrupted, it is judged that a person has entered the area and the line stops.

Any valid beam channels can be selected The SF4B series incorporates a fixed blanking function.

The SF4B series is equipped with a fixed blanking function which allows specific beam channels to be selectively interrupted without causing the control output (OSSD) to output the OFF signal. This function is convenient for use with applications in which certain fixed obstacles tend to block specific beam channels. Furthermore, this function provides greater safety as the control output (OSSD) will automatically output the OFF signal if the fixed obstacles are subsequently removed from the sensing area.




Auxiliary output has selectable output configuration

Mode No.	Description
0	Negative logic of the control output (OSSD 1, OSSD 2) (factory setting)
1	Positive logic of the control output (OSSD 1, OSSD 2)
2	For emission: output ON, For non-emission: output OFF
3	For emission: output OFF, For non-emission: output ON
4	For unstable incident beam: OFF (Note 1)
5	For unstable incident beam: ON (Note 1)
6	For muting: ON
7	For muting: OFF
8	For beam received: ON, For beam interrupted: OFF (Note 2)
9	For beam received: OFF. For beam interrupted: ON (Note 2)

Notes: 1) The output cannot be used while the fix blanking function, floating blanking function or the muting function is activated.

2) This device outputs the beam received / interrupted state under activating the auxiliary output switching function using the handy controller irrespective of activating other functions, fixed blanking function, floating blanking function, and muting function.



* A handy-controller cannot be used with the SF4B---01<V2>, SF4B---03<V2> and the SF-C14EX-01.

Non-specified beam channels can be deactivated The SF4B series incorporates a floating blanking function.

1, 2 or 3 non-specified beam channels can be deactivated. If the number of beam channels that are blocked is less than or equal to the set number of beam channels, then the control output (OSSD) will not output the OFF signal. This function is useful in the event when the positions of obstacles within the sensing area must be changed during object rearrangement, or when an object passes through the light curtain's sensing area.



Note: When the floating blanking function is used, the size of the min. sensing object is changed. Refer to "**PRECAUTIONS** FOR PROPER USE" (p.36) for details.

A variety of other functions can be selected

Emission intensity control function

This function reduces the amount of emitting light. The two modes, normal mode and short mode, can be selected. The factory setting is set to the normal mode for the emission intensity control function.

Setting monitoring function

This function allows the user to confirm the details of each light curtain setting.

Protection function

Unless the password is not input, any setting change of the light curtain cannot be allowed. The factory setting is set to invalid for the protect function.

Copy function

Allows settings details to be copied into other light curtains. In the event that the same setting must be input into several different light curtains, this function will reduce the time required for the input of settings.

Muting lamp diagnosis setting

When the muting lamp diagnosis is disabled, the muting function will continue to operate even if the lamp is blown.

Refer to the SF4B<V2> manual for details.

Lineup of exclusive control units





SF-CL1T264T

Supports both PNP and NPN polarities SF-C10 series

A single unit can be used for PNP / NPN input switching, reducing the number of parts that need to be registered.

Plug-in connector type control unit SF-C11


Connecting to the light curtain is done using plug-in connector connections, which shorten setup and replacement time.

Robust type control unit

SF-C12


The strong metal enclosure has a built-in safety relay. It has an IP65 protection structure, so that it can be set up individually without the need to be inserted into a control panel.

PRODUCT CONFIGURATION



safety field network, CC-Link Safety, and a single network is complete while achieving wire-saving.


* Refer to our website or general catalog for details.



SF4B

1	1 Light curtains Mounting bracket and bottom cap cable are not supplied with the light curtain. Be sure to order them separately.							
-	Гуре	Appearance	Operating range	N	lodel No. (Note :		Number of beam	Protective height
	Type Appearance		(Note 1)	SFB-HC Korean Press complian non-compatible (SFB-HC non-ompatib		(SFB-HC non-ompatible)	ahammala	(mm in)
	Ë			SF4B-F23 <v2></v2>	SF4B-F23-01 <v2></v2>	SF4B-F23-03 <v2></v2>	23	230 9.055
	551 i	Beam 5 mm		SF4B-F31 <v2></v2>	SF4B-F31-01 <v2></v2>	SF4B-F31-03 <v2></v2>	31	310 12.205
	ø0.5	channel 0.197 in		SF4B-F39 <v2></v2>	SF4B-F39-01 <v2></v2>	SF4B-F39-03 <v2></v2>	39	390 15.354
type	nm tch)	No.		SF4B-F47 <v2></v2>	SF4B-F47-01 <v2></v2>	SF4B-F47-03 <v2></v2>	47	470 18.504
Finger protection type	Min. sensing object ø14 mm (10 mm 0.394 in beam pitch)	Protective height		SF4B-F55 <v2></v2>	SF4B-F55-01 <v2></v2>	SF4B-F55-03 <v2></v2>	55	550 21.654
otec	ect g bea			SF4B-F63 <v2></v2>	SF4B-F63-01 <v2></v2>	SF4B-F63-03 <v2></v2>	63	630 24.803
er pr	j obj		0.3 to 7 m 0.984 to 22.966 ft	SF4B-F71 <v2></v2>	SF4B-F71-01 <v2></v2>	SF4B-F71-03 <v2></v2>	71	710 27.953
Fing	0.35		0.304 10 22.300 11	SF4B-F79 <v2></v2>	SF4B-F79-01 <v2></v2>	SF4B-F79-03 <v2></v2>	79	790 31.102
-	. sen mm	Beam pitch 5 mm		SF4B-F95 <v2></v2>	SF4B-F95-01 <v2></v2>	SF4B-F95-03 <v2></v2>	95	950 37.402
	Min. (10	10 mm 0.197 in 0.394 in		SF4B-F111 <v2></v2>	SF4B-F111-01 <v2></v2>	SF4B-F111-03 <v2></v2>	111	1,110 43.701
		0.004 11		SF4B-F127 <v2></v2>	SF4B-F127-01 <v2></v2>	SF4B-F127-03 <v2></v2>	127	1,270 50.000
				SF4B-H12 <v2></v2>	SF4B-H12-01 <v2></v2>	SF4B-H12-03 <v2></v2>	12	230 9.055
				SF4B-H16 <v2></v2>	SF4B-H16-01 <v2></v2>	SF4B-H16-03 <v2></v2>	16	310 12.205
	c	+		SF4B-H20 <v2></v2>	SF4B-H20-01 <v2></v2>	SF4B-H20-03 <v2></v2>	20	390 15.354
	984 i	Beam 5 mm		SF4B-H24 <v2></v2>	SF4B-H24-01 <v2></v2>	SF4B-H24-03 <v2></v2>	24	470 18.504
	Min. sensing object ø25 mm ø0.984 in (20 mm 0.787 in beam pitch)	channel 0.197 in		SF4B-H28 <v2></v2>	SF4B-H28-01 <v2></v2>	SF4B-H28-03 <v2></v2>	28	550 21.654
type	mm itch)	No.		SF4B-H32 <v2></v2>	SF4B-H32-01 <v2></v2>	SF4B-H32-03 <v2></v2>	32	630 24.803
tion	a25 im p	Protective height	0.3 to 9 m 0.984 to 29.528 ft	SF4B-H36 <v2></v2>	SF4B-H36-01 <v2></v2>	SF4B-H36-03 <v2></v2>	36	710 27.953
otec	ect s bea		0.304 10 23.320 11	SF4B-H40 <v2></v2>	SF4B-H40-01 <v2></v2>	SF4B-H40-03 <v2></v2>	40	790 31.102
Hand protection type	j obj 7 in			SF4B-H48 <v2></v2>	SF4B-H48-01 <v2></v2>	SF4B-H48-03 <v2></v2>	48	950 37.402
Han	nsing 0.78			SF4B-H56 <v2></v2>	SF4B-H56-01 <v2></v2>	SF4B-H56-03 <v2></v2>	56	1,110 43.701
	mm	Beam pitch 5 mm		SF4B-H64 <v2></v2>	SF4B-H64-01 <v2></v2>	SF4B-H64-03 <v2></v2>	64	1,270 50.000
	Min. (20	20 mm 0.197 in 0.787 in		SF4B-H72 <v2></v2>	SF4B-H72-01 <v2></v2>	SF4B-H72-03 <v2></v2>	72	1,430 56.299
		0.767 11		SF4B-H80 <v2></v2>	SF4B-H80-01 <v2></v2>	SF4B-H80-03 <v2></v2>	80	1,590 62.598
			0.3 to 7 m	SF4B-H88 <v2></v2>	SF4B-H88-01 <v2></v2>	SF4B-H88-03 <v2></v2>	88	1,750 68.898
			0.984 to 22.966 ft	SF4B-H96 <v2></v2>	SF4B-H96-01 <v2></v2>	SF4B-H96-03 <v2></v2>	96	1,910 75.197
				SF4B-A6 <v2></v2>	SF4B-A6-01 <v2></v2>	-	6	230 9.055
				SF4B-A8 <v2></v2>	SF4B-A8-01 <v2></v2>	_	8	310 12.205
	.⊑	1		SF4B-A10 <v2></v2>	SF4B-A10-01 <v2></v2>	_	10	390 15.354
	ø1.772 i			SF4B-A12 <v2></v2>	SF4B-A12-01 <v2></v2>	-	12	470 18.504
/pe	ø1.7	Beam 15 mm channel 0.591 in		SF4B-A14 <v2></v2>	SF4B-A14-01 <v2></v2>	-	14	550 21.654
on ty	mm itch)	No.		SF4B-A16 <v2></v2>	SF4B-A16-01 <v2></v2>	-	16	630 24.803
tectic	ø45 im p	Protective height	0.3 to 9 m 0.984 to 29.528 ft	SF4B-A18 <v2></v2>	SF4B-A18-01 <v2></v2>	-	18	710 27.953
prot	Arm / Foot protection ty Min. sensing object ø45 mm (40 mm 1.575 in beam pitch)		0.007 (0 20.020 II	SF4B-A20 <v2></v2>	SF4B-A20-01 <v2></v2>	-	20	790 31.102
Toot	g obj 75 in	Beam pitch 40 mm 1 575 in		SF4B-A24 <v2></v2>	SF4B-A24-01 <v2></v2>	_	24	950 37.402
m / F	1.57			SF4B-A28 <v2></v2>	SF4B-A28-01 <v2></v2>	-	28	1,110 43.701
An	. ser mm			SF4B-A32 <v2></v2>	SF4B-A32-01 <v2></v2>	-	32	1,270 50.000
	Min (40	15 mm 0.591 in		SF4B-A36 <v2></v2>	SF4B-A36-01 <v2></v2>	_	36	1,430 56.299
				SF4B-A40 <v2></v2>	SF4B-A40-01 <v2></v2>	_	40	1,590 62.598
			0.3 to 7 m	SF4B-A44 <v2></v2>	SF4B-A44-01 <v2></v2>	_	44	1,750 68.898
			0.984 to 22.966 ft	SF4B-A48 <v2></v2>	SF4B-A48-01 <v2></v2>	_	48	1,910 75.197

Notes: 1) The operating range is the possible setting distance between the emitter and the receiver. The light curtain can detect an object less than 0.3 m 0.984 ft away.



2) The model No. with "E" shown on the label affixed to the product is the emitter, "D" shown on the label is the receiver. (e.g.) Emitter of SF4B-F23<V2>: SF4B-F23E<V2>, Receiver of SF4B-F23<V2>: SF4B-F23D<V2>.

1	1 Light curtains (Robust type) Mounting bracket and bottom cap cable are not supplied with the light curtain. Be sure to order them separately.								
-	Гуре	Appearance	Operating range	Model No.	Number of beam channels	Protective height (mm in)			
				SF4B-F23G <v2></v2>	23	244 9.606			
				SF4B-F31G <v2></v2>	31	324 12.756			
	551 in	Beam (beam (channel) 0.465 in		SF4B-F39G <v2></v2>	39	404 15.906			
ype	ø0.551	No.		SF4B-F47G <v2></v2>	47	484 19.055			
Finger protection type	Min. sensing object ø14 mm (10 mm 0.394 in beam pitch)	Protective height		SF4B-F55G <v2></v2>	55	564 22.205			
otec	t ø 14 eam		0.3 to 7 m	SF4B-F63G <v2></v2>	63	644 25.354			
ler pr	bjec in be		0.984 to 22.966 ft	SF4B-F71G <v2></v2>	71	724 28.504			
Fing	ing c			SF4B-F79G <v2></v2>	79	804 31.654			
	sens m 0	Beam pitch 11.8 mm		SF4B-F95G <v2></v2>	95	964 37.953			
	.10 m	10 mm 0.465 in 0.394 in		SF4B-F111G <v2></v2>	111	1,124 44.252			
	20			SF4B-F127G <v2></v2>	127	1,284 50.551			
				SF4B-H12G <v2></v2>	12	244 9.606			
				SF4B-H16G <v2></v2>	16	324 12.756			
				SF4B-H20G <v2></v2>	20	404 15.906			
				SF4B-H24G <v2></v2>	24	484 19.055			
	ø0.984 in	Beam 11.8 mm turk channel 0.465 in		SF4B-H28G <v2></v2>	28	564 22.205			
ype	ø0.9	No.	0.3 to 9 m 0.984 to 29.529 ft	SF4B-H32G <v2></v2>	32	644 25.354			
ion t		Protective height		SF4B-H36G <v2></v2>	36	724 28.504			
Hand protection type	Min. sensing object ø25 mm (20 mm 0.787 in beam pitch)			SF4B-H40G <v2></v2>	40	804 31.654			
nd pr	oject n be			SF4B-H48G <v2></v2>	48	964 37.953			
Har	ng ok			SF4B-H56G <v2></v2>	56	1,124 44.252			
	m 0.1			SF4B-H64G <v2></v2>	64	1,284 50.551			
	20 m		20 mm 0.465 in 0.787 in	20 mm 0.465 in 0.787 in	20 mm 0.465 in 0.787 in		SF4B-H72G <v2></v2>	72	1,444 56.850
	≥ 🙂			SF4B-H80G <v2></v2>	80	1,604 <u>63.150</u>			
			0.3 to 7 m	SF4B-H88G <v2></v2>	88	1,764 69.449			
			0.984 to 22.966 ft	SF4B-H96G <v2></v2>	96	1,924 75.748			
				SF4B-A6G <v2></v2>	6	244 9.606			
				SF4B-A8G <v2></v2>	8	324 12.756			
				SF4B-A10G <v2></v2>	10	404 15.906			
	_			SF4B-A12G <v2></v2>	12	484 19.055			
e	72 in	Beam 21.8 mm		SF4B-A14G <v2></v2>	14	564 22.205			
n typ	ø1.772 i	channel No.	0.3 to 9 m	SF4B-A16G <v2></v2>	16	644 25.354			
ectio	mm litch)		0.3 to 9 m 0.984 to 29.529 ft	SF4B-A18G <v2></v2>	18	724 28.504			
prote	ø45 am p	Protective height		SF4B-A20G <v2></v2>	20	804 31.654			
Foot	Arm / Foot protection type Min. sensing object ø45 mm ø1.77 (40 mm 1.575 in beam pitch)	Beam pitch 40 mm 1.575 in		SF4B-A24G <v2></v2>	24	964 37.953			
rm /				SF4B-A28G <v2></v2>	28	1,124 44.252			
A				SF4B-A32G <v2></v2>	32	1,284 50.551			
		21.8 mm 0.858 in		SF4B-A36G <v2></v2>	36	1,444 56.850			
	2 7			SF4B-A40G <v2></v2>	40	1,604 63.150			
			0.3 to 7 m	SF4B-A44G <v2></v2>	44	1,764 69.449			
			0.984 to 22.966 ft	SF4B-A48G <v2></v2>	48	1,924 75.748			

Differences from standard type

The Robust type **SF4B**-□**GV2**> is different from the standard type **SF4B**-□**<V2**> in the following ways: • Sensing width (protective height) • Profile • Net weight • Mounting bracket • Large alignment tool • Noncompliant with Japanese and Korean press standard • Noncompliant with Korean regulations • Noncompliant with Chinese GB standard (acquisition planned) Other specifications, input/output circuits, and options are common to the standard type.


. .

2 Mounting brackets Mounting bracket is not supplied with the light curtain. Be sure to order it separately.					
Designation		Model No.	Description		
	M8 rear mounting bracket	MS-SFB-7-T	For rear direction. Allows the light curtain to be mounted at the rear with one M8 hexagon-socket-head bolt. (4 pcs. per set for emitter and receiver)		
Rear / side mounting bracket	M8 side mounting bracket	MS-SFB-8-T	For side direction. Allows the light curtain to be mounted at the side with one M8 hexagon-socket-head bolt. (4 pcs. per set for emitter and receiver)		
(Material: Iron)	M8 rear / side mounting bracket set MS-SFB-1-T2		Can be used as either a rear mounting bracket MS-SFB-7-T or a side mounting bracket MS-SFB-8-T depending on mounting direction. (4 pcs. per set for emitter and receiver)		
	Standard mounting bracket	MS-SFB-1	Used to mount the light curtain on the rear surface and side surface. (4 pcs. per set for emitter and receiver)		
360° mounting	M8 mounting bracket	MS-SFB-1-T	Allows the light curtain to be mounted at the rear and side with one M8 hexagon- socket-head bolt. (4 pcs. per set for emitter and receiver)		
bracket (Material: Die-cast zinc alloy)	Pitch adapter bracket	MS-SFB-4	Used as the mounting bracket when changing over a previous light curtain with a protective height of 200 mm 7.874 in or more to the SF4B series. It is installed using two M5 hexagon-socket-head bolts. (4 pcs. per set for emitter and receiver)		
* Light curtain can revolve 360° horizontally.	M8 pitch adapter bracket	MS-SFB-4-T	Used as the mounting bracket when changing over a previous light curtain with a protective height of 200 mm 7.874 in or more to the SF4B series. It is installed using one M8 hexagon-socket-head bolt. (4 pcs. per set for emitter and receiver)		
Standard L mounting	g bracket (For SF4B- □ G)	MS-SF4BG-1	Mounting is possible behind or at the side of the light curtain. Mount with two M5 bolts or one M8 bolt. (4 pcs. per set for emitter and receiver)		
Dead zoneless mounting bracket (Material: Die-cast zinc alloy)		MS-SFB-3	Mounting with no dead zone is possible so that the mounting bracket does not project past the protective height. (4 pcs. per set for emitter and receiver)		
Dead zoneless mounting bracket (For SF4B -□ G) [Material: Mounting bracketSPCC (Trivalent chrome plated) [Supporting bracketPPS		MS-SF4BG-3	Allows light curtains to be installed cose together, or in locations with installation restrictions due to equipment columns or jigs. (4 pcs. per set for emitter and receiver)		

M8 rear mounting bracket


• MS-SFB-7-T

• MS-SFB-1-T2 (Rear mounting) M8 rear mounting bracket MS-SFB-7-T




M8 side mounting bracket

- MS-SFB-8-T
- MS-SFB-1-T2 (Side mounting)



Standard mounting bracket






M8 mounting bracket

• MS-SFB-1-T

M5 (length: 18 mm 0.709 in) hexagon-socket-head bolt (Accessory for MS-SFB-1.T) Light urtain Sensing surface Four bracket set Four bracket set Four M5 (length: 18 mm 0.709 in) hexagon-socket-head bolts are attached.

Standard L mounting bracket (For SF4B-□G)

• MS-SF4BG-1




Four bracket set [Eight M5 (length: 10 mm 0.394 in) hexagon-socket-head bolts are attached.]

Pitch adapter bracket

• MS-SFB-4

curtain


Sensing surface



Four bracket set Four M5 (length: 18 mm 0.709 in) hexagon-socket-head bolts are attached.

Dead zoneless mounting bracket (For SF4B-DG)

- MS-SF4BG-3
- When using M5 hexagonsocket-head bolt (Rear mounting)




Dead zoneless mounting bracket MS-SF4BG-3

Four bracket set


Twelve M5 (length: 8 mm 0.315 in) hexagon-socket-head bolts and four nut slots are attached.

M8 pitch adapter bracket MS-SFB-4-T




Four bracket set Four M5 (length: 18 mm 0.709 in) hexagon-socket-head bolts are attached.

Dead zoneless mounting bracket • MS-SFB-3



hexagon-socket-head bolts and four spacers are attached.

When using M8 hexagon bolt (Rear mounting)



15

3 4 5 6 7 Mating cable / Extension cable / Cables for series connection Mating cable is not supplied with the light curtain. Be sure to order it separately. Туре Appearance Model No. Description Length: 3 m 9.843 ft SFB-CCB3 Net weight: 370 g approx. (2 cables) Discrete wire Length: 7 m 22.966 ft SFB-CCB7 Used for connecting to the light curtain and to other cables or cable Net weight: 820 g approx. (2 cables) the SF-C13 control unit. Length: 10 m 32.808 Two cables per set for emitter and receiver SFB-CCB10 Bottom cap Net weight: 1,160 g approx. (2 cables) Length: 15 m 49.213 ft SFB-CCB15 Standard components (8-core cable) Net weight: 1,710 g approx. (2 cables) Length: 0.5 m 1.640 f SFB-CB05 Net weight: 95 g approx. (2 cables) Used for connecting to the light curtain and to an extension Connector 3 Length: 5 m 16.404 ft cable or the SF-C11 control unit. SFB-CB5 Net weight: 620 g approx. (2 cables) Two cables per set for emitter and receiver Connector outer diameter: ø14 mm ø0.551 in max. Length: 10 m 32.808 f SFB-CB10 Net weight: 1,200 g approx. (2 cables) Length: 3 m 9.843 ft With connector on one end Used for cable extension or connecting to the SF-C13 control SFB-CC3 Net weight: 380 g approx. (2 cables) unit. Length: 10 m 32.808 f Two cables per set for emitter and receiver Extension cable SFB-CC10 Connector outer diameter: ø14 mm ø0.551 in max. Net weight: 1,200 g approx. (2 cables) Length: 3 m 9.843 ft · emitter SFB-CCJ3E With connectors on both ends Vet weight: 190 g approx. (1 cables) Used for cable extension or connecting to the SF-C11 and Length: 10 m 32.808 f the SF-C14EX control unit. For SFB-CCJ10E Net weight: 580 g approx. (1 cable) One each for emitter and receiver Connector outer diameter: ø14 mm ø0.551 in max. Connector color: Gray (for emitter), Black (for receiver) Length: 3 m 9.843 ft For receiver SFB-CCJ3D Net weight: 210 g approx. (1 cables) Connector outer diameter: ø14 mm ø0.551 in max. Length: 10 m 32.808 SFB-CCJ10D Net weight: 600 g approx. (1 cable) Length: 3 m 9.843 ft Bottom cap cable Muting control components (12-core cable, with interference prevention wire) Discrete SFB-CCB3-MU Used for connecting to the light curtain and to other cables or Net weight: 420 g approx. (2 cables) wire the SF-C13 control unit. Length: 7 m 22.966 ft Two cables per set for emitter and receiver SFB-CCB7-MU Net weight: 930 g approx. (2 cables) Used for connecting to the light curtain and to an extension Connector Length: 0.5 m 1.640 f cable or the SF-C12 control unit. SFB-CB05-MU Net weight: Two cables per set for emitter and receiver 110 g approx. (2 cables 6 Connector outer diameter: ø16 mm ø0.630 in max. Length: 3 m 9.843 ft connector SFB-CC3-MU Net weight: 430 g approx. (2 cables) Used for connecting to an extension cable or the SF-C13 on one end Length: 7 m 22.966 ft control unit. SFB-CC7-MU Net weight: 1,000 g approx. (2 cables) Two cables per set for emitter and receiver Extension cable With Length: 10 m 32 Connector outer diameter: ø16 mm ø0.630 in max. SFB-CC10-MU Net weight: 1,300 g approx. (2 cables) Length: 3 m 9.843 ft emitter With connectors on both ends SFB-CCJ3E-MU Net weight: 190 g approx. (1 cables) Used for connecting to an extension cable or the SF-C12 Length: 10 m 32.808 f For SFB-CCJ10E-MU control unit. Net weight: 660 g approx. (1 cable) ى One each for emitter and receiver For receiver Length: 3 m 9.843 ft Connector color: Gray (for emitter), Black (for receiver) SFB-CCJ3D-MU Net weight: 210 g approx. (1 cables) Connector outer diameter: ø16 mm ø0.630 in max. Length: 10 m 32.808 SFB-CCJ10D-MU Net weight: 680 g approx. (1 cable) Length: 0.1 m 0.328 for series SFB-CSL01 Net weight: 45 g approx. (2 cables) Length: 0.5 m 1.640 ft Used to connect light curtains in series connectior SFB-CSL05 Net weight: 95 g approx. (2 cables) Two cables per set for emitter and receiver (common for Cable f Length: 1 m 3.281 ft emitter and receiver) SFB-CSL1 Net weight: 150 g approx. (2 cables) Cable color: Gray (common for emitter and receiver) Length: 5 m 16.404 ft 7 SFB-CSL5 Net weight: 630 g approx. (2 cables) Length: 0.5 m 1.640 mating cable for SF-C14EX SFB-CB05-EX Used for connecting to the light curtain and to SF-C14EX Exclusive Net weight: 95 g approx. (2 cables) control unit or 8-core extension cable with connectors on Length: 5 m 16.404 ft SFB-CB5-EX both ends Net weight: 620 g approx. (2 cables) Two cables per set for emitter and receiver Length: 10 m 32.808 3 SFB-CB10-EX Connector outer diameter: ø14 mm ø0.551 in max. Net weight: 1,200 g approx. (2 cables) For SF4-AHD 8-core bottom cap cable specifications. Used to allow SFB-CB05-A-P cable (PNP type) connector cables connected to previous light curtains (at the For SF4-AHD-N control circuit side) to be smoothly adapted to the SF4B series. Also, SFB-CB05-A-P and SFB-CB05-A-N are usable even SFB-CB05-A-N Length: 0.5 m 1.640 ft Adapter (NPN type) Net weight: when external device input is not used as the polarity of PNP For SF2-EHn 110 g approx. (2 cables) SFB-CB05-B-P (PNP type) output or NPN output is fixed. Two cables per set for emitter and receiver e For SF2-EHD-N SFB-CB05-B-N Connector outer diameter: ø14 mm ø0.551 in max. (NPN type)

SF4B ORDER GUIDE

Note: Where the cable color has not been specified precisely, it is black for emitter, gray with black line for receiver, outer diameter is ø6 mm ø0.236 in, min. bending radius is R6 mm R0.236 in.

For details of mating cable of CC-Link Safety system remote I/O unit with connectors for light curtain SF-CL1T264T, refer to website.

Spare parts (Accessories for light curtain)

Description
Used to mount the light curtain on the intermediate position. (2 pcs. per set for emitter and receiver) Mounting is possible behind or at the side of the light curtain.
Used to mount the light curtain in the intermediate position. (2 pcs. per set for emitter and receiver) Mounting is possible behind or at the side of the light curtain.
Min. sensing object for regular checking (\emptyset 14 mm \emptyset 0.551 in), with finger protection type (min. sensing object \emptyset 14 mm \emptyset 0.551 in)
Min. sensing object for regular checking (\emptyset 25 mm \emptyset 0.984 in), with hand protection type (min. sensing object \emptyset 25 mm \emptyset 0.984 in)

Notes: 1) The number of sets required varies depending on the product.

1 set:	SF4B-F□ <v2></v2>	. Light curtain with 79 to 111 beam channels
	SF4B-H□ <v2></v2>	. Light curtain with 40 to 56 beam channels
	SF4B-A□ <v2></v2>	. Light curtain with 20 to 28 beam channels
2 sets	SF4B-F127□ <v2></v2>	
	SF4B-H□ <v2></v2>	. Light curtain with 64 to 80 beam channels
	SF4B-A□ <v2></v2>	. Light curtain with 32 to 40 beam channels
3 sets	SF4B-H□ <v2></v2>	. Light curtain with 88 to 96 beam channels
	SF4B-A□ <v2></v2>	. Light curtain with 44 to 48 beam channels


2) The number of sets required varies depending on the product.

1 set:	SF4B-F G <v2></v2>	Light curtain with 79 to 127 beam channels
	SF4B-H□G <v2></v2>	Light curtain with 40 to 64 beam channels
	SF4B-A□G <v2></v2>	Light curtain with 20 to 32 beam channels
2 set:	SF4B-H□G <v2></v2>	Light curtain with 72 to 96 beam channels
	SF4B-A□G <v2></v2>	Light curtain with 36 to 48 beam channels


Intermediate supporting bracket

• MS-SFB-2

<In case of rear mounting>




<In case of side mounting>




• MS-SF4BG-2

<In case of rear mounting>



Material: SPCC

<In case of side mounting>



Material: SPCC

SF4B

OPTIONS

Exclusive control units

Designation	Appearance	Model No.	Application cable	Description
Connector connection type control unit		SF-C11	Bottom cap cable: SFB-CB□ Extension cable: SFB-CCJ10□	Use 8-core cable with connector to connect to the light curtain. Compatible with up to Control Category 4. Interference prevention wires and muting function cannot be used.
Robust type control unit		SF-C12	Bottom cap cable: SFB-CB05-MU Extension cable: SFB-CCJ10ロ-MU	Use 12-core cable with connector to connect to the light curtain. Interference prevention wires can be used. Compatible with up to Control Category 4. Muting function cannot be used.
Slim type control unit		SF-C13	Bottom cap cable: SFB-CCB□(-MU) Extension cable: SFB-CC□(-MU)	Use a discrete wire cable to connect to the light curtain. Muting function and interference prevention wires can be used. Compatible with up to Control Category 4.
Application expansion unit for SF4B series		SF-C14EX	Bottom cap cable: SFB-CB□-EX	The muting control function and emergency stop input expand the applications of the light curtains. Use exclusive cable to connect to the light curtain.
Handy-controller non-compatible type		SF-C14EX-01	Extension cable: SFB-CCJ10	Compatible with up to Control Category 4. The handy-controller SFB-HC cannot be used with SF-C14EX-01 .
CC-Link Safety system remote I/O unit for light curtain (Note)		SF-CL1T264T	Bottom cap cable: SFB-CB□-CL Extension cable: SFB-CCJ10□-CL	This is a remote I/O unit that allows the safety field network "CC-Link Safety" to be connected to the light curtains or the safety components. Use exclusive cable to connect to the light curtain. Compatible with up to Control Category 4. Please contact our office for details.

Note: Refer to the our website for details of the remote I/O unit SF-CL1T264T.

SF-C12 spare relay set

A set of spare relays (2 safety relays and 1 removal tool) is available for the safety relay that is built into the SF-C12. Model No.: SF-C12-RY

Recommended safety relay

Safety relay Panasonic Corporation SF series





Note: Contact Panasonic Corporation for details on the recommended products.


Туре	With LED	indicator		
Item Model No.	SFS3-L-DC24V	SFS4-L-DC24V		
Contact arrangement	3a1b	4a2b		
Rated nominal switching capacity	6 A / 250 V AC, 6 A / 30 V DC			
Min. switching capacity	1 mA / 5 V DC			
Coil rating	15 mA / 24 V DC	20.8 mA / 24 V DC		
Rated power	360 mW	500 mW		
consumption				
Operation time	20 ms or less			
Release time	20 ms or less			
Ambient temperature	-40 to +85 °C -40 to +185 °F (Humidity: 5 to 85 % RH)			
Applicable standards	UL, C-L	JL, TÜV		

OPTIONS

Handy-controller


Designation	Appearance	Model No.
Handy- controller	* Includes 2 adapter cables	SFB-HC
Cable set for cable type connection		SFC-WNC1

Note: A handy-controller cannot be used with the $SF4B-\Box-01<V2>$, the $SF4B-\Box-03<V2>$ and the SF-C14EX-01.



Note: If using a bottom cap cable with discrete wire, please order the SFB-CC3/CC10 separately. Refer to the instruction manual for the light curtain for details on wiring.

Cable type



Light curtain diagnosis software

Simply input the error number of the light curtain on the screen, and the section of maintenance needed will be located and coping process will be displayed.

* Free download aviable from our website.




Light curtain diagnosis software

Y-shaped connector


Туре	Appearance	Model No.	Description			
Wire-saving Y-shaped connector		SFB-WY1	Wire-saving connector for standard components (8-core cable). Cable emitter and receiver are consolidated into one cable for wire-saving. Wiring has +24 V, 0 V, OSSD 1, OSSD 2, output polarity setting wire (sh Power wire and synchronization wire are connected inside the connect Interlock is disabled (automatic reset).			
Cable with		WY1-CCN3	Cable length: 3 m 9.843 ft Net weight: 200 g approx. (1 cable)	Mating cable for Y-shaped connector Cable color: Gray (with black line)		
connector on one side		WY1-CCN10	Cable length: 10 m 32.808 ft Net weight: 620 g approx. (1 cable)	Connector color: Black The min. bending radius: R6 mm R0.236 in		

By using the Y-shaped connector, the least required wires such as power or safety output are consolidated into one cable. Man-hours taken for wiring is eliminated to the minimum. Construction times as well as wiring mistakes are greatly reduced.



SF4B

Product configuration




Wiring diagram of control unit SF-C13

/Gray connector

Emitter

<For PNP output (minus ground)>

Connect the light curtain control outputs OSSD 1 and OSSD 2 to S1 and S2 respectively.



Notes: 1) The above diagram is when using manual reset. If automatic reset is used, disconnect the lead from X2 and connect it to X3. In this case, a reset (RESET) button is not needed.

2) Use a momentary-type switch as the reset (RESET) button.

3) Unused wires must be insulated.

Y-shaped connector SFB-WY1 Cable with connector on one side

(Common for all models)

Extension cable

WY1-CCN3 (3 m 9.843 ft) WY1-CCN10 (10 m 32.808 ft)


SFB-CCJ3D (3 m 9.843 ft)

SFB-CCJ10D (10 m 32.808 ft)

Connector pin No.	Description
1	OSSD 2
2	+24 V
3	OSSD 1
4	Not used
5	Not used
6	Not used
D	0 V
8	Output polarity setting wire (Shield)

<For NPN output (plus ground)>

• Connect the light curtain control outputs OSSD 1 and OSSD 2 to S4 and S2 respectively and ground the + side.



Notes: 1) The above diagram is when using manual reset. If automatic reset is used, disconnect the lead from X2 and connect it to X3. In this case, a reset (RESET) button is not needed.

2) Use a momentary-type switch as the reset (RESET) button.

3) Unused wires must be insulated.

OPTIONS

Front protection cover (Except for SF4B-DG) / Protection bar set (Except for SF4B-DG) / Corner mirror

Applicable beam chan			Front protection cover	Protection bar set Rear / side protection bar set		Corner mirror		
Finger	Hand	Arm / Foot	Model No.	Model No.	Model No.	Model No.	Effective reflective surface	
23	12	6	FC-SFBH-12	MC-SFBH-12	MC-SFBH-12-T	RF-SFBH-12	236 × 72 mm 9.291 × 2.835 in	
31	16	8	FC-SFBH-16	MC-SFBH-16	MC-SFBH-16-T	RF-SFBH-16	316 × 72 mm 12.441 × 2.835 in	
39	20	10	FC-SFBH-20	MC-SFBH-20	MC-SFBH-20-T	RF-SFBH-20	396 × 72 mm 15.591 × 2.835 in	
47	24	12	FC-SFBH-24	MC-SFBH-24	MC-SFBH-24-T	RF-SFBH-24	476 × 72 mm 18.740 × 2.835 in	
55	28	14	FC-SFBH-28	MC-SFBH-28	MC-SFBH-28-T	RF-SFBH-28	556 × 72 mm 21.890 × 2.835 in	
63	32	16	FC-SFBH-32	MC-SFBH-32	MC-SFBH-32-T	RF-SFBH-32	636 × 72 mm 25.039 × 2.835 in	
71	36	18	FC-SFBH-36	MC-SFBH-36	MC-SFBH-36-T	RF-SFBH-36	716 × 72 mm 28.189 × 2.835 in	
79	40	20	FC-SFBH-40	MC-SFBH-40	MC-SFBH-40-T	RF-SFBH-40	796 × 72 mm 31.339 × 2.835 in	
95	48	24	FC-SFBH-48	MC-SFBH-48	MC-SFBH-48-T	RF-SFBH-48	956 × 72 mm 37.638 × 2.835 in	
111	56	28	FC-SFBH-56	MC-SFBH-56	MC-SFBH-56-T	RF-SFBH-56	1,116 × 72 mm 43.937 × 2.835 in	
127	64	32	FC-SFBH-64	MC-SFBH-64	MC-SFBH-64-T	RF-SFBH-64	1,276 × 72 mm 50.236 × 2.835 in	
-	72	36	FC-SFBH-72	MC-SFBH-72	MC-SFBH-72-T	RF-SFBH-72	1,436 × 72 mm 56.535 × 2.835 in	
-	80	40	FC-SFBH-80	MC-SFBH-80	MC-SFBH-80-T	RF-SFBH-80	1,596 × 72 mm 62.835 × 2.835 in	
-	88	44	FC-SFBH-88	MC-SFBH-88	MC-SFBH-88-T	RF-SFBH-88	1,756 × 72 mm 69.134 × 2.835 in	
-	96	48	FC-SFBH-96	MC-SFBH-96	MC-SFBH-96-T	RF-SFBH-96	1,916 × 72 mm 75.433 × 2.835 in	

Note: The model Nos. given above denote a single unit, not a pair of units. 2 units are required for use in mounting to the emitter / receiver. (Except for corner mirror)


Front protection cover

• FC-SFBH-□

Protects sensing surface of the light curtain from flying objects such as welding spatter. The operating range reduces when the front protection cover is used. Note: It is not available for SF4B-DG.

Material: Polycarbonate

cover



Sensing range


		SF4I	SF4B-A□		
		12 to 64 beam channels type	72 to 96 beam channels type	6 to 32 beam channels type	36 to 48 beam channels type
Only emitter installed	0.3 to 6 m	0.3 to 7.5 m	0.3 to 6 m	0.3 to 7.5 m	0.3 to 6 m
	0.984 to 19.685 ft	0.984 to 24.606 ft	0.984 to 19.685 ft	0.984 to 24.606 ft	0.984 to 19.685 ft
Only receiver installed	0.3 to 6 m	0.3 to 7.5 m	0.3 to 6 m	0.3 to 7.5 m	0.3 to 6 m
	0.984 to 19.685 ft	0.984 to 24.606 ft	0.984 to 19.685 ft	0.984 to 24.606 ft	0.984 to 19.685 ft
Both emitter and receiver installed	0.3 to 5.5 m	0.3 to 7 m	0.3 to 5.5 m	0.3 to 7 m	0.3 to 5.5 m
	0.984 to 18.045 ft	0.984 to 22.966 ft	0.984 to 18.045 ft	0.984 to 22.966 ft	0.984 to 18.045 ft

Note: The operating range is the possible setting distance between the emitter and the receiver


Corner mirror

• RF-SFBH-□

Normally for L-shaped or U-shaped installation, 2 or 3 sets of light curtains are needed. With the use of a corner mirror reflecting the light, one set of light curtain is possible for L-shaped or U-shaped installation.



f	
Percent decline of	the sensing range
With 1 mirror	Declined to 90 %
With 2 mirrors	Declined to 80 %



Protection bar intermediate Material: Iron Material: Iron supporting bracket 1 pc. **Trivalent** 1 pc. **Trivalent** MS-SFB-6 chrome plated chrome plated (Optional) (Note 2) Notes: 1) Available as a spare part. Model No.: MS-MCSFB-1-T

(length: 16 mm 0.630 in)

M5

(length: 18 mm 0.709 in)

2 pcs

M5

2 pcs


Hexagon-socket-head bolt

2) The protection bar intermediate supporting bracket MS-SFB-6 (optional) is installed to protection bars that are longer than the MC-SFBH-48(-T). Use if there is much flexure bending in the protection bar. Please contact our office for details.

SF4B

Front protection cover (For SF4B-□G)

Applicable beam chan		signation	Front protection cover
Finger	Hand	Arm / Foot	Model No.
23	12	6	FC-SF4BG-H12
31	16	8	FC-SF4BG-H16
39	20	10	FC-SF4BG-H20
47	24	12	FC-SF4BG-H24
55	28	14	FC-SF4BG-H28
63	32	16	FC-SF4BG-H32
71	36	18	FC-SF4BG-H36
79	40	20	FC-SF4BG-H40
95	48	24	FC-SF4BG-H48
111	56	28	FC-SF4BG-H56
127	64	32	FC-SF4BG-H64
-	72	36	FC-SF4BG-H72
-	80	40	FC-SF4BG-H80
-	88	44	FC-SF4BG-H88
-	96	48	FC-SF4BG-H96




Sensing range

		SF4B-H	□G <v2></v2>	SF4B-A□G <v2></v2>		
	SF4B-F⊡G <v2></v2>	F4B-FDG <v2> 12 to 64 beam channels type channels type</v2>			36 to 48 beam channels type	
Only emitter installed	0.3 to 6 m	0.3 to 7.5 m	0.3 to 6 m	0.3 to 7.5 m	0.3 to 6 m	
Only receiver installed	0.984 to 19.685 ft	0.984 to 24.606 ft	0.984 to 19.685 ft	0.984 to 24.606 ft	0.984 to 19.685 ft	
Both emitter and receiver installed	0.3 to 5.5 m 0.984 to 18.045 ft	0.3 to 7 m 0.984 to 22.966 ft	0.3 to 5.5 m 0.984 to 18.045 ft	0.3 to 7 m 0.984 to 22.966 ft	0.3 to 5.5 m 0.984 to 18.045 ft	

Note: The model Nos. given above denote a single unit, not a pair of units. 2 units are required for use in mounting to the emitter / receiver. Note: The operating range is the possible setting distance between the emitter and the receiver.


Designation	Model No.	Description
Test rod ø45	SF4B-TR45	Min. sensing object for regular checking (ø45 mm ø1.772 in), with arm / foot protection type (min. sensing object ø45 mm ø1.772 in)
Laser alignment tool	SF-LAT-2N	Allows easy beam axis alignment using easy-to-see laser beam
Laser alignment tool (For SF4B- □ G)	SF-LAT-4BG	Allows easy beam axis alignment using easy-to-see laser beam
Caution tape	SF-TP-BG10	Attached to the side of the light curtain to alert workers to hazards (10 m 32.8 ft long)

Laser alignment tool • SF-LAT-2N



Laser alignment tool (For SF4B-□G)

• SF-LAT-4BG



* Illustration shows standard type light curtain.

Caution tape


• SF-TP-BG10




OPTIONS

Designation	Model No.	Description	• SF-IND-
Large display unit for light curtain	SF-IND-2	With the auxiliary output of the light curtain, the operation is easily observable from various directions. Specifications • Supply voltage: 24 V DC ±15 % • Current consumption: 12 mA or less • Indicators: Orange LED (8 pcs. used) I Light up when external contact is ON] • Ambient temperature: -10 to +55 °C +14 to +131 °F (No dew condensation or icing allowed) • Material: POM (Enclosure) Polycarbonate (Cover) Cold rolled carbon steel (SPCC) (Bracket) • Cable: 0.3 mm ² 2-core cabtyre cable, 3 m 9.843 ft long • Weight: 70 g approx. (including bracket) I/O circuit diagrams •With NPN output type> *1 Internal circuit — Users' circuit •With PNP output type> *1 Non-voltage contact or NPN open-collector transistor or *1 Non-voltage contact or PNP open-collector transistor • *1 Non-voltage contact or PNP open-collector transistor • • • • • • • • • • • • • • • • • • •	M5 hexagy head bolt (length: 1) 0.394 in on Purcha separa Attaches Tighten to provided MS-SFB0 bracket of

Large display unit for light curtain -2



s to top of light curtain. together the mounting bracket d with the light curtain MS-SFB-1/4, 3G-1 and the attached mounting of SF-IND-2.



Recommended muting lamps

Manufactured by Maruyasu Dengyo Co.,Ltd. Model No.: BLR-30O-C Note: Contact the manufacturers for details on the recommended products.

Manufactured by IDEC Corporation Model No.: HW1P-5Q7A

Recommended safety relays Manufactured by Panasonic Corporation

Model No.: SF series (Safety Relay) Note: Contact the manufacturers for details on the recommended products.

Light curtain individual specifications

SF4B-F□(G)<V2>

Туре		Min. sensing object ø14 mm ø0.551 in type (10 mm 0.394 in beam pitch)								
Item Model No. (Note 2)	SF4B-F230 <v2></v2>	SF4B-F230G <v2></v2>	SF4B-F310 <v2></v2>	SF4B-F310G <v2></v2>	SF4B-F39□ <v2></v2>	SF4B-F390G <v2></v2>	SF4B-F47 <>>	SF4B-F470G <v2></v2>	SF4B-F55□ <v2></v2>	SF4B-F550G <v2></v2>
No. of beam channels	2	3	3	1	3	9	4	7	5	5
Protective height	230 mm 9.055 in	244 mm 9.606 in	310 mm 12.205 in	324 mm 12.756 in	390 mm 15.354 in	404 mm 15.906 in	470 mm 18.504 in	484 mm 19.055 in	550 mm 21.654 in	564 mm 22.205 in
Current consumption		Emitter: 80	mA or less, F	Receiver: 120) mA or less		Emitter: 100	mA or less,	Receiver: 160) mA or less
PFHd	2.56	×10 ⁻⁹	2.96	×10 ⁻⁹	3.36	×10 ⁻⁹	3.75	×10 ^{_9}	4.15	×10 ^{_9}
MTTFd		100 years or more								
Net weight (Total of emitter and receiver)	510 g approx.	980 g approx.	660 g approx.	1,340 g approx.	810 g approx.	1,700 g approx.	960 g approx.	2,000 g approx.	1,110 g approx.	2,400 g approx.

Туре	Mi	n. sensing	object ø14 i	mm <mark>ø0.551</mark>	in type (10	mm 0.394 i	n beam pito	ch)
Item Model No. (Note 2)	SF4B-F63□ <v2></v2>	SF4B-F63□G <v2></v2>	SF4B-F710 <v2></v2>	SF4B-F710G <v2></v2>	SF4B-F79□ <v2></v2>	SF4B-F790G <v2></v2>	SF4B-F95□ <v2>></v2>	SF4B-F950G <v2></v2>
No. of beam channels	6	3	71		79		95	
Protective height	630 mm 24.803 in	644 mm 25.354 in	710 mm 27.953 in	724 mm 28.504 in	790 mm 31.102 in	804 mm 31.654 in	950 mm 37.402 in	964 mm 37.953 in
Current consumption	Emitter: 100	mA or less,	Receiver: 16	0 mA or less	Emitter: 115 mA or less, Receiver: 190 mA or le			
PFHd	4.55	×10 ⁻⁹	4.95	×10 ⁻⁹	5.35	×10 ⁻⁹	6.15	×10 ⁻⁹
MTTFd		100 years or more						
Net weight (Total of emitter and receiver)	1,260 g approx.	2,800 g approx.	1,420 g approx.	3,200 g approx.	1,570 g approx.	3,400 g approx.	1,870 g approx.	4,200 g approx.

Туре	Min. sensing obje	ct ø14 mm <mark>ø0.551</mark>	in type (10 mm 0.3	94 in beam pitch)				
Item Model No. (Note 2)	SF4B-F1110 <v2></v2>	SF4B-F1110G <v2></v2>	SF4B-F1270 <v2></v2>	SF4B-F1270G <v2></v2>				
No. of beam channels	1'	11	12	27				
Protective height	1,110 mm 43.701 in	1,124 mm 44.252 in	1,270 mm 50.000 in	1,284 mm 50.551 in				
Current consumption	Emitter: 135 mA or less, Receiver: 230 mA or less							
PFHd	6.94	×10 ⁻⁹	7.74×10 ⁻⁹					
MTTFd		100 year	s or more					
Net weight (Total of emitter and receiver)	2,170 g approx.	5,000 g approx.	2,470 g approx.	5,600 g approx.				

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +20 °C +68 °F. The model No. with "G" is a robust type. 2) The models with the "-01" or "-03" cannot be used with the handy-controller SFB-HC.

SF4B-H□(G)<V2>

Туре		Min. sensing object ø25 mm ø0.984 in type (20 mm 0.787 in beam pitch)								
Item Model No. (Note 2)	SF4B-H12□ <v2></v2>	SF4B-H12□G <v2></v2>	SF4B-H16□ <v2></v2>	SF4B-H16□G <v2></v2>	SF4B-H20□ <v2></v2>	SF4B-H20□G <v2></v2>	SF4B-H24□ <v2></v2>	SF4B-H24□G <v2></v2>	SF4B-H28□ <v2></v2>	SF4B-H280G <v2></v2>
No. of beam channels	1	12 16 20					2	4	28	
Protective height	230 mm 9.055 in	244 mm 9.606 in	310 mm 12.205 in	324 mm 12.756 in	390 mm 15.354 in	404 mm 15.906 in	470 mm 18.504 in	484 mm 19.055 in	550 mm 21.654 in	564 mm 22.205 in
Current consumption		Emitter: 70	mA or less,	Receiver: 95	mA or less		Emitter: 80	mA or less, F	Receiver: 115	mA or less
PFHd	2.01	×10 ⁻⁹	2.21	×10 ⁻⁹	2.41	×10 ⁻⁹	2.61	×10 ⁻⁹	2.81	×10 ⁻⁹
MTTFd		100 years or more								
Net weight (Total of emitter and receiver)	510 g approx.	980 g approx.	660 g approx.	1,340 g approx.	810 g approx.	1,700 g approx.	960 g approx.	2,000 g approx.	1,110 g approx.	2,400 g approx.

Туре		Min. sensing object ø25 mm ø0.984 in type (20 mm 0.787 in beam pitch)									
Item Model No. (Note 2)	SF4B-H32□ <v2></v2>	SF4B-H32□G <v2></v2>	SF4B-H36□ <v2></v2>	SF4B-H36□G <v2></v2>	SF4B-H40□ <v2></v2>	SF4B-H40 G <v2></v2>	SF4B-H48□ <v2></v2>	SF4B-H48□G <v2></v2>	SF4B-H56□ <v2></v2>	SF4B-H560G <v2></v2>	
No. of beam channels	3	32 36		6	40		4	8	5	6	
Protective height	630 mm 24.803 in	644 mm 25.354 in	710 mm 27.953 in	724 mm 28.504 in	790 mm 31.102 in	804 mm 31.654 in	950 mm 37.402 in	964 mm 37.953 in	1,110 mm 43.701 in	1,124 mm 44.252 in	
Current consumption	Emitter: 80	Emitter: 80 mA or less, Receiver: 115 mA or less				Emitter: 90 mA or less, Receiver: 140 mA or less				Emitter: 100 mA or less, Receiver: 160 mA or less	
PFHd	3.01	×10 ⁻⁹	3.21	×10 ^{_9}	3.41×10 ⁻⁹ 3.80×10 ⁻⁹			×10 ⁻⁹	4.20×10-9		
MTTFd		100 years or more									
Net weight (Total of emitter and receiver)	1,260 g approx.	2,800 g approx.	1,420 g approx.	3,200 g approx.	1,570 g approx.	3,400 g approx.	1,870 g approx.	4,200 g approx.	2,170 g approx.	5,000 g approx.	

Туре		Min. sensing object ø25 mm ø0.984 in type (20 mm 0.787 in beam pitch)								
Item Model No. (Note 2)	SF4B-H64 <\2>	SF4B-H64_G <v2></v2>	SF4B-H72 <>2>	SF4B-H720G <v2></v2>	SF4B-H80 <> V2>	SF4B-H800G <v2></v2>	SF4B-H88□ <v2></v2>	SF4B-H88□G <v2></v2>	SF4B-H96□ <v2></v2>	SF4B-H96::G <v2></v2>
No. of beam channels	6	4	7	2	8	0	8	8	9	6
Protective height	1,270 mm 50.000 in	1,284 mm 50.551 in	1,430 mm 56.299 in	1,444 mm 56.850 in	1,590 mm 62.598 in	1,604 mm 63.150 in	1,750 mm 68.898 in	1,764 mm 69.449 in	1,910 mm 75.197 in	1,924 mm 75.748 in
Current consumption		Emitter: 100 mA or less, eceiver: 160 mA or less Emitter: 110 mA or less, Receiver: 180 mA or less				0 mA or less	Emitter: 120 mA or less, Receiver: 200 mA or le			0 mA or less
PFHd	4.60	×10 ^{_9}	5.00	×10 ⁻⁹	5.40	×10 ^{_9}	5.80	×10 ⁻⁹	6.20	×10 ⁻⁹
MTTFd		100 years or more								
Net weight (Total of emitter and receiver)	2,470 g approx.	5,600 g approx.	2,770 g approx.	6,400 g approx.	3,070 g approx.	7,000 g approx.	3,370 g approx.	7,800 g approx.	3,670 g approx.	8,400 g approx.

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +20 °C +68 °F. The model No. with "G" is a robust type. 2) The models with the "-01" or "-03" cannot be used with the handy-controller SFB-HC.

SF4B-A□(G)<V2>

Туре		Min. sensing object ø45 mm ø1.772 in type (40 mm 1.575 in beam pitch)								
Item Model No. (Note 2)	SF4B-A6□ <v2></v2>	SF4B-A60G <v2></v2>	SF4B-A8□ <v2></v2>	SF4B-A8::G <v2></v2>	SF4B-A10 <> 2>	SF4B-A100G <v2></v2>	SF4B-A12□ <v2></v2>	$SF4B\text{-}A12_{\Box}G\text{-}V2\text{>}$	SF4B-A14□ <v2></v2>	SF4B-A140G <v2></v2>
No. of beam channels	6	6	8	8 10		0	12		14	
Protective height	230 mm 9.055 in	244 mm 9.606 in	310 mm 12.205 in	324 mm 12.756 in	390 mm 15.354 in	404 mm 15.906 in	470 mm 18.504 in	484 mm 19.055 in	550 mm 21.654 in	564 mm 22.205 in
Current consumption		Emitter: 65	mA or less,	Receiver: 85	mA or less		Emitter: 70	mA or less,	Receiver: 95	mA or less
PFHd	1.71	×10 ⁻⁹	1.81	×10 ⁻⁹	1.91	×10 ⁻⁹	2.01	×10 ^{_9}	2.11	×10 ⁻⁹
MTTFd		100 years or more								
Net weight (Total of emitter and receiver)	510 g approx.	980 g approx.	660 g approx.	1,340 g approx.	810 g approx.	1,700 g approx.	960 g approx.	2,000 g approx.	1,110 g approx.	2,400 g approx.

Туре		Min. sensing object ø45 mm ø1.772 in type (40 mm 1.575 in beam pitch)									
Item Model No. (Note 2)	SF4B-A160 <v2></v2>	SF4B-A160G <v2></v2>	SF4B-A18□ <v2></v2>	SF4B-A18□G <v2></v2>	SF4B-A20□ <v2></v2>	SF4B-A20□G <v2></v2>	SF4B-A24□ <v2></v2>	$SF4B\text{-}A24_{\Box}G\text{-}V2\text{>}$	SF4B-A28□ <v2></v2>	SF4B-A280G <v2></v2>	
No. of beam channels	1	6	1	8	2	0	2	4	2	8	
Protective height	630 mm 24.803 in	644 mm 25.354 in	710 mm 27.953 in	724 mm 28.504 in	790 mm 31.102 in	804 mm 31.654 in	950 mm 37.402 in	964 mm 37.953 in	1,110 mm 43.701 in	1,124 mm 44.252 in	
Current consumption	Emitter: 70	Emitter: 70 mA or less, Receiver: 95 mA or less Emitter: 75 mA or less, I						Receiver: 105 mA or less, Receiver: 120 mA or less,			
PFHd	2.21	×10 ⁻⁹	2.31	×10 ⁻⁹	2.41	2.41×10 ⁻⁹ 2.61×10 ⁻⁹			2.81×10 ⁻⁹		
MTTFd		100 years or more									
Net weight (Total of emitter and receiver)	1,260 g approx.	2,800 g approx.	1,420 g approx.	3,200 g approx.	1,570 g approx.	3,400 g approx.	1,870 g approx.	4,200 g approx.	2,170 g approx.	5,000 g approx.	

Туре		Min. sensing object ø45 mm ø1.772 in type (40 mm 1.575 in beam pitch)								
Item Model No. (Note 2)	SF4B-A32 <>>	SF4B-A32□G <v2></v2>	SF4B-A360 <v2></v2>	SF4B-A36□G <v2></v2>	SF4B-A40 <>>	SF4B-A40 G <v2></v2>	SF4B-A44□ <v2></v2>	SF4B-A44□G <v2></v2>	SF4B-A48□ <v2></v2>	SF4B-A48::G <v2></v2>
No. of beam channels	3	32		6	4	40		4	48	
Protective height	1,270 mm 50.000 in	1,284 mm 50.551 in	1,430 mm 56.299 in	1,444 mm 56.850 in	1,590 mm 62.598 in	1,604 mm 63.150 in	1,750 mm 68.898 in	1,764 mm 69.449 in	1,910 mm 75.197 in	1,924 mm 75.748 in
Current consumption		mitter: 80 mA or less, sceiver: 120 mA or less Emitter: 85 mA or less, Receiver: 130 mA or less Emitter: 95 mA or less, Receiver: 140 mA or					mA or less			
PFHd	3.01	×10 ⁻⁹	3.21	×10 ^{_9}	3.41	×10 ⁻⁹	3.61	×10 ⁻⁹	3.80:	×10 ^{_9}
MTTFd					100 years	s or more	~		-	
Net weight (Total of emitter and receiver)	2,470 g approx.	5,600 g approx.	2,770 g approx.	6,400 g approx.	3,070 g approx.	7,000 g approx.	3,370 g approx.	7,800 g approx.	3,670 g approx.	8,400 g approx.

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +20 °C +68 °F. The model No. with "G" is a robust type. 2) The models with the "-01" or "-03" cannot be used with the handy-controller SFB-HC.

Light curtain common specifications

1	Туре	Min. sensing object ø14 mm ø0.551 in type	Min. sensing object ø25 mm ø0.984 in type	Min. sensing object ø45 mm ø1.772 in typ
	Model No.	SF4B-F□(G) <v2></v2>	SF4B-H□(G) <v2></v2>	SF4B-A□(G) <v2></v2>
	SFB-HC non-compatible	SF4B-F□-01 <v2></v2>	SF4B-H□-01 <v2></v2>	SF4B-A□-01 <v2></v2>
ten	N Korean press compliant (Note 3)	SF4B-F□-03 <v2></v2>	SF4B-H□-03 <v2></v2>	
92)	International standard	IEC 61496-1/2 (Typ	be 4), ISO 13849-1 (Category 4, PLe), IEC	61508-1 to 7 (SIL3)
Note	Japan	JIS B 9704-1/2 (T	ype 4), JIS B 9705-1 (Category 4), JIS C (0508-1 to 7 (SIL3)
ards	Europe (EU)	EN 61496-1 (Type 4), EN ISO 13849-1	1 (Category 4, PLe), EN 61508-1 to 7 (SIL3), EN 55011, EN 50178, EN 61000-6-2
Applicable standards (Note 2)	North America	ANSI/UL 61496-1/2 (Type 4), ANSI/U	L 508, UL 1998 (Class 2), CAN/CSA 61496 , ANSI B11.1 to B11.19, ANSI/RIA 15.06	
icabl	South Korea (S-Mark)	S1-	G-35-2005, S2-W-11-2003 (SF4B- □ <v2></v2> c	only)
Appl	China (GB)	G	B 4584 (SF4B- □ <v2></v2> , SF4B- □ -01<v2></v2> on	ly)
Эре	rating range (Note 3)	0.3 to 7 m 0.984 to 22.966 ft	12 to 64 beam channels type: 0.3 to 9 m 0.984 to 29.528 ft 72 to 96 beam channels type: 0.3 to 7 m 0.984 to 22.966 ft	6 to 32 beam channels type: 0.3 to 9 m 0.984 to 29.528 f 36 to 48 beam channels type: 0.3 to 7 m 0.984 to 22.966
Min.	sensing object (Note 4)	ø14 mm ø0.551 in opaque object	ø25 mm ø0.984 in opaque object	ø45 mm ø1.772 in opaque object
Effe	ctive aperture angle	±2.5° or less [for an operating	range exceeding 3 m 9.843 ft (conforming	to IEC 61496-2 / UL 61496-2)]
Sup	oly voltage		24 V DC ±10 % Ripple P-P 10 % or less	
	trol outputs SD 1, OSSD 2)	Applied voltage: same as supply voltage	e current 200 mA, When selecting NPN ou When selecting PNP output: between the When selecting NPN output: between the cting PNP output: source current 200 mA, whe	e control output and +V, e control output and 0 V
	Operation mode	ON when all beam channels are received, OFF when one or mor	re beam channels are interrupted (OFF also in case of any malfur	nction in the light curtain or the synchronization signal)(Note 5
Ī	Protection circuit		Incorporated	
Res	oonse time	OFF re	esponse: 14 ms or less, ON response: 80 to	90 ms
	liary output -safety output)	Applied voltage: same as supply voltage	e current 60 mA, When selecting NPN outp When selecting PNP output: between the When selecting NPN output: between the ecting PNP output: source current 60 mA, whe	e auxiliary output and +V, e auxiliary output and 0 V
ſ	Operation mode		outputs are OFF (Factory setting, operating mode ca	an be changed using the SFB-HC handy-controller
ł	Protection circuit	,,,,,,, _	Incorporated	
ł	Responce time	OFE	replay: 34 ms or less, ON replay 110 ms o	rless
nter	ference prevention function) (Available only when in series connection	
	ion halt function / Interlock function		ted / Incorporated [Manual reset / Auto rese	· · ·
Exte	nal device monitoring function		Incorporated	
Dver	ride function / Muting function	Incorporated (Note 7) (excludi	ing SF4B-□-03 <v2>) / Incorporated (Note 7</v2>	/) (excluding SF4B- □- 03<v2></v2>)
Opti	onal functions (Note 9)		output switching, interlock setting changing	
e	Degree of protection		IP67 / IP65 (IEC)	
Environmental resistance	Ambient temperature	–10 to +55 °C +14 to +131 °F (No	o dew condensation or icing allowed), Stora	ge: –25 to +70 °C –13 to +158 °F
SISI	Ambient humidity		30 to 85 % RH, Storage: 30 to 95 % RH	
E E	Ambient illuminance	Incandes	scent light: 3,500 {x or less at the light-recei	ving face
	Dielectric strength voltage	1,000 V AC for one mi	n. between all supply terminals connected t	ogether and enclosure
Ē	Insulation resistance	· · · · · · · · · · · · · · · · · · ·	C megger between all supply terminals con	
	Vibration resistance		75 mm 0.030 in amplitude in X, Y and Z dire	
Ξŀ	Shock resistance		on (30 G approx.) in X, Y and Z directions f	
mi	ting element		LED (Peak emission wavelength: 870 nm 0	
	erial		case: Aluminium, Sensing surface: Polycar	· · · · · · · · · · · · · · · · · · ·
	necting method / Cable length		042 ft is possible for both emitter and receiv	
Acce	essories	MS-SFB-2 (Intermediate supporting bracket): (Note 11)	MS-SFB-2 (Intermediate supporting bracket): (Note 11) MS-SF4BG-2 (Intermediate supporting bracket): (Note 12) SF4B-TR25 (Test rod): 1 No.	MS-SFB-2 (Intermediate supporting bracket): (Note 1 MS-SF4BG-2 (Intermediate supporting bracket): (Note
	 PLe SIL3 compliant from 3) The operating range is When the floating blank The outputs are not "OI 6) In case the blanking fur Please use 12-core cat The manual reset and a In case of using optional SF4B-□-03<v2> and the</v2> The cable can be extende connected in series. Furth The intermediate suppor 1 set: SF4B-F□<v2></v2> 	n production in August 2009. the possible setting distance between the e- ing function is used, the size of the min. se FF" when muting function is active even if th action is valid, the operation mode is chang- le. auto reset are possible to be switched depe function, the handy-controller (SFB-HC) (op	emitter and the receiver. Insing object is changed. For details, refer the beam channel is interruped. ed. For details, refer to "Safety distance" (anding on the wiring status. tional) is required. However, a handy-controll then two light curtains are connected in series, with a can be extended within 40 m 131.234 ft (for em- the following models. The number of sets r channels, SF4B-H □< V2>	o "Safety distance " (p.36~). p.36~). ler cannot be used with the SF4B---01<v< b="">; thin 20 m 65.617 ft when three light curtains a litter / receiver). equired varies depending on the product</v<>

- 3 sets: SF4B-H_□<V2>.........Light curtain with 88 to 96 beam channels, SF4B-A_□<V2>........Light curtain with 44 to 48 beam channels
 12) The intermediate supporting bracket (MS-SF4BG-2) is enclosed with the following models.
 1 set: SF4B-F_□G<V2>........Light curtain with 79 to 127 beam channels, SF4B-H_□G<V2>.......Light curtain with 40 to 64 beam channels
 SF4B-A_□G<V2>........Light curtain with 20 to 32 beam channels
 2 sets: SF4B-H_□G<V2>.......Light curtain with 72 to 96 beam channels, SF4B-A_□G<V2>.......Light curtain with 36 to 48 beam channels

Control units

Model No.	SF-C11 (Note 2)	SF-C12	SF-C13 (Note 2)			
Connectable light curtains	SF4B / SF2B series	SF4B series	Light curtains manufactured by Panasonic			
Control category	ISO 13849-1 (EN ISO 1	3849-1, JIS B 9705-1) compliance up to Ca	ategory 4, PLe standards			
Supply voltage / Current consumption	24 V DC ±10 % R	ipple P-P 10 % or less / 100 mA or less (ex	/ 100 mA or less (excluding light curtain)			
Fuse (rating)	Built-in electronic fu	use, Triggering current: 0.5 A or more, Rese	eset after power down			
Enabling path	NO contact × 3 (13-14, 23-24, 33-34)	NO contact × 2 (13-14, 23-24)	NO contact × 3 (13-14, 23-24, 33-34)			
Utilization category		AC-15, DC-13 (IEC 60947-5-1)	·			
Rated operation voltage (Ue) / Rated operation current (Ie)	30 V DC / 6 A, 230 V AC / 6 A, resistive load (For inductive load, during contact protection) Min. applicable load: 10 mA (at 24 V DC) (Note 3)	(For inductive load, during contact protection)	30 V DC / 4 A, 230 V AC / 4 A, resistive load (For inductive load, during contact protection) Min. applicable load: 10 mA (at 24 V DC) (Note3)			
Contact resistance	100 m Ω or less (initial value)	50 mΩ or less (initial value)	100 mΩ or less (initial value)			
Contact protection fuse rating	6 A (slow blow)	3 A (slow blow)	4 A (slow blow)			
Pick-up delay (Auto reset / Manual reset)	80 ms or less / 90 ms or less	30 ms or less / 30 ms or less	80 ms or less / 90 ms or less			
Response time	10 ms or less	14 ms or less	10 ms or less			
Auxiliary output	Safety relay contact (NC contact) ×1 (41-42) (Related to enabling path)	Safety relay contact (NC contact) × 1 (31-32) (Related to enabling path)	Safety relay contact (NC contact) × 1 (41-42) (Related to enabling path)			
Rated operation voltage / current	24 V DC / 2 A, Min. applicable load: 10 mA (at 24 V DC)	30 V DC / 3 A, Min. applicable load: 15 mA (at 24 V DC)	24 V DC / 2 A, Min. applicable load: 10 mA (at 24 V DC)			
Contact protection fuse rating	2 A (slow blow)	3 A (slow blow)	2 A (slow blow)			
Semiconductor auxiliary output (AUX)	<pre><minus (setting="" for="" ground="" pnp)=""> <plus (setting="" for="" ground="" npn)=""> PNP open-collector transistor NPN open-collector transistor</plus></minus></pre>		PNP open-collector transistor			
Output operation	Related to auxiliary output of light curtain		ON when the light curtain is interrupted			
Excess voltage category	П	Ш	П			
Polarity selection function (Note 4)	Incorporated (Sliding switch allow Minus ground: Correspond to PNF Plus ground: Correspond to NPN	Incorporated (Cable connection allows selection of plus / minus ground) Minus ground: Correspond to PNP output light curtain Plus ground: Correspond to NPN output light curtain				
Pollution degree		2				
Protection	Enclosure: IP40, Terminal: IP20	IP65	Enclosure: IP40, Terminal: IP20			
Ambient temperature	· · · · · · · · · · · · · · · · · · ·	dew condensation or icing allowed), Stora	<u> </u>			
Enclosure material	ABS	Die-cast aluminum	ABS			
Weight	Net weight: 320 g approx.	Net weight: 1 kg approx.	Net weight: 200 g approx.			
conditions used were ar 2) SF-C11 and SF-C13 h 3) If several SF-C11 or S a space of 5 mm 0.197	anditions have not been specified precisely, the number and temperature of +20 °C +68 °F. ave acquired the Korea S-mark. F-C13 units are being used in a line together in or more between each unit. If the units a refuge the state accuration current for order	are mounted close togeth	her / (are mounted close together /			
in accordance with the graphs at right. 4) Please switch the slidii the NPN side for plus g	educe the rated operating current for safety ambient operating temperature as shown in ng switch to the PNP side for minus ground ground. nit SF-C1□ (SF-C10 series), refer to the we	h the $\begin{bmatrix} 3 \\ 9 \\ 2 \\ 2 \\ 1 \\ 0 \\ 35 \\ 40 \\ 45 \\ 50 \\ 5 \\ 50 \\ 5 \\ 50 \\ 5 \\ 50 \\ 5 \\ 5$				

Item Model No.	SF-C14EX(-01) (Note 2)
Connectable light curtains	SF4B series
Control category	ISO 13849-1 (EN ISO 13849-1, JIS B 9705-1) compliance up to Category 4, PLe standards
Supply voltage / Current consumption	24 V DC ±10 % Ripple P-P 10 % or less / 0.2 A or less (Excluding light curtain and other external connecting device)
Enabling path (Enabling path 1, 2, 3)	PNP open-collector transistor 2 outputs × 3 or NPN open-collector transistor 2 outputs × 3 (selectable using a slider switch)
Operation mode (Output operation)	Enabling path 1: ON when the light curtain is in light receiving condition, OFF when the light curtain is in light interrupted condition (Note 3) Enabling path 2: ON when the light curtain is in light receiving condition or the muting function is valid OFF when the light curtain is in light interrupted condition and the muting function is invalid (Note 3) Enabling path 3: ON when the emergency stop is invalid, OFF when the emergency stop is valid
Response time	OFF response: 14 ms or less (Enabling path 1 and 2: including the response time of the light curtain) ON response: 90 ms or less (auto-reset) / 140 ms or less (manual reset) (Note 4)
Auxiliary outputs Auxiliary output 1, 2, 3, 4 (Note 5)	PNP open-collector transistor × 3 or NPN open-collector transistor × 3 (selectable using a slider switch) <when is="" output="" pnp="" selected=""> <when is="" npn="" output="" selected=""> • Maximum source current: 60 mA or less • Maximum sink current: 60 mA or less • Applied voltage: same as supply voltage (between the auxiliary output and +V) • Applied voltage: 2 V or less (at 60 mA source current) • Residual voltage: 2 V or less (at 60 mA source current) • Residual voltage: 2 V or less (at 60 mA sink current)</when></when>
Operation mode (Output operation)	Auxiliary output 1: ON when the muting function is invalid, OFF when the muting function is valid Auxiliary output 2: ON when the override function is invalid, OFF when the override function is valid Auxiliary output 3: ON when the muting lamp is normal, OFF when the muting lamp is error Auxiliary output 4: ON when the light curtain is in light interrupted condition, OFF when the light curtain is in light receiving condition (Note 5)
Muting lamp output	Applicable muting lamp: 24 V DC, 3.6 to 30 W (L1, L2 of each unit)
Protection	Enclosure: IP40, Terminal: IP20
Ambient temperature	-10 to +55 °C +14 to +131 °F (No dew condensation or icing allowed), Storage: -25 to +70 °C -13 to +158 °F
Material	Enclosure: ABS
Connection terminal	Detachable spring-cage terminal
Weight	Net weight: 250 g approx.

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +20 °C +68 °F.

2) SF-C14EX-01 is Handy-controller non-compatible type.

3) Both enabling path 1 and 2 are OFF when the emergency stop is valid regardless of whether the light curtain is in the light receiving or light interrupted condition. 4) The auto-reset cannot be used with enabling path 3.

5) The auxiliary output incorporated in the SF4B series is outputed.

6) For details of control unit SF-C14EX(-01), refer to the website or general catalog.

SF4B SPECIFICATIONS

Handy-controller

Model No.	SFB-HC
Supply voltage	24 V DC ±10 % Ripple P-P10 % or less (common to light curtain power supply)
Current consumption	65 mA or less
Communication method	RS-485 two-way communications (Specific procedure)
Digital display	4-digit red LED display × 2 (Selected beam channels, setting contents etc. are displayed.)
Function indicator	Green LED × 9 (set function is displayed.)
Functions	Fixed blanking (Factory setting: Disabled) / Floating blanking (Factory setting: Disabled) / Auxiliary output change (Factory setting: Negative Logic of OSSD) / Light emitting amount control (Factory setting: Disabled) / Muting setting change [Factory setting: All beam channels enabled, A = B, Setting of the muting lamp diagnosis function enabled (Ver. 2 or later), Muting sensor output operation setting N.O. / N.O. (Ver. 2.1 or later)] Interlock setting change (Factory setting: start / restart) / External device monitoring setting change (Factory setting: Enabled, 300 ms) / Override setting changing function 60 sec. (Ver. 2.1 or later) / Setting detail monitoring / Protecting (Factory setting: Disabled)(Factory password setting: 0000) / Initialization / Copy
Ambient temperature	-10 to +55 °C +14 to +131 °F (No dew condensation or icing allowed), Storage: -25 to +70 °C -13 to +158 °F
Ambient humidity	30 to 85 % RH, Storage: 30 to 85 % RH
Voltage withstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure
Insulation resistance	20 M Ω , or more, with 500 V DC megger between all supply terminals connected together and enclosure
Cable	8-core shielded cable, 0.5 m 1.640 ft long, with a connector at the end (2 cables)
Weight	Net weight: 200 g approx.
Accessories	Adapter cable: 2 cables

Note: Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +20 °C +68 °F.

Laser alignment tool

Model No.					
Item	SF-LAT-2N / SF-LAT-4BG (For SF4B-□G)				
Supply voltage	3 V (LR6 battery × 2 pcs.)				
Battery	1.5 V (LR6 battery) × 2 pcs. (replaceable)				
Battery lifetime	30 hours approx. of continuous operation (LR6 battery, at +25 °C +77 °F ambient temperature)				
Light source	Red semiconductor laser: Class 2 (IEC / JIS / FDA) (Max. output: 1 mW, Peak emission wavelength: 650 nm 0.026 mil) (Note 2)				
Spot diameter	10 mm 0.394 in approx. (at 5 m 16.404 ft distance)				
Ambient temperature	0 to +40 °C +32 to +104 °F (No dew condensation), Storage: 0 to +55 °C +32 to +131 °F				
Ambient humidity	35 to 85 % RH, Storage: 35 to 85 % RH				
Material	Enclosure: ABS, Mounting part: Aluminum				
Weight	Net weight: 200 g approx. (including batteries)				
Accessories	LR6 battery: 2 pcs.				

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +20 °C +68 °F. 2) As for FDA regulation, the product complies with 21 CFR 1040.10 and 1040.11 based on Laser Notice No. 50, dated June 24, 2007, issued by CDRH under the FDA.

Corner mirror


Item	Model No.	RF-SFBH-□
Atter	nuation rate of sensing range	With one mirror: Declined to 90 %, With two mirrors: Declined to 80 % (When used in combination with the SF4B series)
ntal	Ambient temperature	-10 to +55 °C +14 to +131 °F (No dew condensation or icing allowed), Storage: -25 to +70 °C -13 to +158 °F
men	Ambient humidity	30 to 85 % RH, Storage: 30 to 95 % RH
Environmer resistance	Vibration resistance	10 to 55 Hz frequency, 0.75 mm 0.030 in amplitude in X, Y and Z directions for two hours each
En S	Shock resistance	300 m/s ² acceleration (30 G approx.) in X, Y and Z directions for three times each
Mate	erial	Enclosure: Alminium, Mounting bracket: Stainless steel, Mirror (rear surface mirror): Glass, Side cover: EPDM
Accessories		Intermediate supporting bracket: 1 set (RF-SFBH-40/48/56/64), 2 sets (RF-SFBH-72/80/88/96)

Note: Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +20 °C +68 °F.

I/O CIRCUIT AND WIRING DIAGRAMS

I/O circuit diagram

<In case of using I/O circuit for PNP output>



+Users' circuit Internal circuit

Note: The above diagram is when using a 12-core cable. If an 8-core cable is used, the red, yellow, gray, gray / black, light blue / white and light blue / black lead wires are absent.

* S1

Switch S	51
----------	----

- Emission halt input / Reset input
- For manual reset
- Vs to Vs 2.5 V (sink current 5 mA or less): Emission halt (Note 1) Open: Emission
- For automatic reset

Open: Disabled

- Vs to Vs 2.5 V (sink current 5 mA or less): Emission (Note 1) Open: Emission halt
- Interlock setting input, Override input, Muting input A / B, External device monitoring input Vs to Vs – 2.5 V (sink current 5 mA or less): Enabled (Note 1)

Note: Vs is the applying supply voltage.

<In case of using I/O circuit for NPN output>

Emitter Color code of mating cable (Brown) +V P (Shield) Output polarity setting wire 0.22 µF ∰ (Yellow) Override input 470 Ω (Pale purple) Interlock setting input 0.22 µF 黄 470 Ω (Pink) Emission halt input / Reset input Load 0.22 µF 茾 470 Ω \overline{m} (Gray) Interference prevention + Sensor circuit 24 V DC (Gray / Black) Interference prevention **t**±10 % K (Yellow-green / Black) Auxiliary output S * S1 'S1 (Red) Muting lamp output * ŧ \otimes \otimes (Blue) 0 V (Orange) Synchronization + (Orange / Black) Synchronization -Internal circuit Users' circuit Receiver (Orange / Black) Synchronization (Orange) Synchronization + P (Brown) +V (Shield) Output polarity setting wire K1 K (Black) OSSD 1 K2 * Sensor circuit (White) OSSD 2 * (Gray) Interference prevention + (Gray / Black) Interference prevention ~~~ (Yellow-green) External device monitoring input 0.22 µF ± 470 Ω (Light blue / White) Muting input A ~~~ K1 0.047 µF Ŧ 1 kΩ ue / Black) Muting input B K2 ~~~ 0.047 µF * S1 1 kΩ (Blue) 0 V $\frac{1}{m}$ K1, K2: Force-guided relay or magnet contactor

- Internal circuit + Users' circuit
- Note: The above diagram is when using a 12-core cable. If an 8-core cable is used, the red, yellow, gray, gray / black, light blue / white and light blue / black lead wires are absent.

* S1

-	vitch S1 Emission halt input / Reset input For manual reset 0 to +1.5 V (source current 5 mA or less): Emission halt Open: Emission For automatic reset 0 to +1.5 V (source current 5 mA or less): Emission Open: Emission halt
•	Interlock setting input, Override input, Muting input A / B, External device monitor input 0 to +1.5 V (source current 5 mA or less): Enabled Open: Disabled


SF4B

I/O CIRCUIT AND WIRING DIAGRAMS

Connection example


Standard components (8-core cable): Interlock function "enabled (manual reset)", external device monitoring function "enabled"

<In case of using I/O circuit for PNP output>




Note: Vs is the applying supply voltage.

<In case of using I/O circuit for NPN output>




The diagram at left shows the configuration when using PNP output, interlock function "enabled (manual reset)" and external device monitoring function "enabled".

In case of setting the interlock function to "disabled (automatic reset)"



* Refer to the SF4B<V2> manual for details of the interlock function.


In case of setting the external device monitoring function to "disabled"



* Refer to the SF4B<V2> manual for details of the external device monitoring function.


The diagram at left shows the configuration when using NPN output, interlock function "enabled (manual reset)" and external device monitoring function "enabled".

In case of setting the interlock function to "disabled (automatic reset)"



* Refer to the SF4B<V2> manual for details of the interlock function.

In case of setting the external device monitoring function to "disabled"



(Yellow-green) External device monitoring input

* Refer to the SF4B<V2> manual for details of the external device monitoring function.

Refer to the manual on our website for details.

I/O CIRCUIT AND WIRING DIAGRAMS

Connection example

Muting control components (12-core cable, with interference prevention wires): Interlock function "disabled (automatic reset)", external device monitoring function "disabled"

<In case of using I/O circuit for PNP output> Color code of mating cable Emitter (Brown) +V \diamond (Red) Muting lamp output S1 * S1 Cable color: Grav (Yellow-green / Black) Auxiliary output (Gray) Interference prevention +) Uses when the prevention function is used (Grav / Black) Interference prevention -(Yellow) Override input 24 V DC Pale purple) Interlock setting input: Open ±10 % (Pink) Emission halt input / Reset input (Shield) Output polarity setting wire (Blue) 0 V (Orange) Synchronization Receiver (Orange / Black) Synchronization -(Orange / Black) Synchronization -(Orange) Synchronization Cable color: Gray (Brown) + * S1 with black line (Grav) Interference prevention + Uses when the interference S1 (Gray / Black) Interference prevention - prevention function (Light blue / White) Muting input A prevention function is used (Light blue / Black) Muting input B (Yellow-green) External device monitoring input (Black) OSSD 1 (White) OSSD 2 K1, K2: Forced-K1 Shield) Output polarity setting wire guided relay or K2 (Blue) 0 V nagnet contactor * S1 Switch S1 Emission halt input / Reset input For manual reset Vs to Vs - 2.5 V (sink current 5 mA or less): Emission halt (Note), Open: Emission

Vs to Vs - 2.5 V (sink current 5 mA or less): Emission (Note). Open: Emission halt


Vs to Vs - 2.5 V (sink current 5 mA or less): Enabled (Note), Open: Disabled

Override input, Muting input A / B, External device monitoring input

Note: Vs is the applying supply voltage.

For automatic reset

<In case of using I/O circuit for NPN output>




Switch S1

- Emission halt input / Reset input
- For manual reset
- 0 to +1.5 V (source current 5 mA or less): Emission halt, Open: Emission For automatic reset
- 0 to +1.5 V (source current 5 mA or less): Emission, Open: Emission halt
 Override input, Muting input A / B, External device monitoring input 0 to +1.5 V (source current 5 mA or less): Enabled, Open: Disabled

The diagram at left shows the configuration when using PNP output, interlock function "disabled (automatic reset)" and external device monitoring function "disabled".


In case of setting the interlock function to "enabled (manual reset)"

 When the interlock function is "enabled (manual reset)", the override function cannot be used.



* Refer to the SF4B<V2> manual for details of the interlock function.

In case of setting the external device monitoring function to "enabled"




* Refer to the SF4B<V2> manual for details of the external device monitoring function.

The diagram at left shows the configuration when using NPN output, interlock function "disabled (automatic reset)" and external device monitoring function "disabled".


In case of setting the interlock function to "enabled (manual reset)"

 When the interlock function is "enabled (manual reset)", the override function cannot be used.



* Refer to the SF4B<V2> manual for details of the interlock function.

In case of setting the external device monitoring function to "enabled"



* Refer to the SF4B<V2> manual for details of the external device monitoring function.


I/O CIRCUIT AND WIRING DIAGRAMS

SF-C11

SF4B series wiring diagram (Control Category 4)

For PNP output (minus ground)

· Set the light curtain input polarity selection switch to the PNP side and ground the 0 V line.




automatic reset is used, disconnect the lead from X2 and connect it to X3. In this case, a reset (RESET) button is not needed.

- 2) Use a momentary-type switch as the reset (RESET) button.
- 3) Emission halt occurs when the test (TEST) button is open, and emission occurs when the test (TEST) button is short-circuited. If not using the test (TEST) button, short-circuit T1 and T2

Light curtain input polarity

For NPN output (plus ground)



When SF-C11 is connected to the light curtain, be sure to use the following mating cable. SFB-CBD, SFB-CCJ10D

Terminal arrangement diagram

	Terminal	Function		
R I	A1	+24 V DC		
	A2	0 V		
	13-14, 23-24, 33-34	Enabling path (NO contact × 3)		
	41-42	Auxiliary output (NC contact × 1)		
	X1	Reset output terminal		
	X2	Reset input terminal (Manual)		
	X3	Reset input terminal (Automatic)		
	A	Netward		
	В	Not used		
	T1	Test output terminal		
	T2	Test input terminal		
	AUX	Semiconductor auxiliary output		

Pin layout for light curtain connectors




Connector pin No.	Emitter side connector	Receiver side connector
1	Interlock	OSSD 2
2	+24 V DC	+24 V DC
3	Emission halt	OSSD 1
4	Auxiliary output	EDM (External relay monitor)
5	Synchronization wire +	Synchronization wire +
6	Synchronization wire –	Synchronization wire –
7	0 V	0 V
8	Shield wire	Shield wire

SF-C12

SF4B series wiring diagram (Control Category 4)

For PNP output (minus ground)

· Set the two light curtain input polarity select switches to the PNP side and connect the FG terminal to the 0 V line.



Note: The above diagram is when using manual reset. If automatic reset is used, connect a normally closed type pushbutton switch between T1 and T2 and leave between X1 and X2 open.

For NPN output (plus ground)

· In the above diagram, set the two light curtain input polarity selection switches to the NPN side and connect the F.G. terminal to the + side.

When SF-C12 is connected to the light curtain, be sure to use the following maing cable. SFB-CB05-MU, SFB-CCJ10 -- MU

Terminal arrangement diagram

Terminal	Function	Terminal	Function
FG	Frame ground (F.G.) terminal	R+	Interference prevention wire - (Receiver side)
A2	0 V	R-	Interference prevention wire + (Receiver side)
A1	+24 V DC	E+	Interference prevention wire - (Emitter side)
13-14, 23-24	Enabling path (NO contact × 2)	E-	Interference prevention wire + (Emitter side)
31-32	Auxiliary output (NC contact × 1)	T2	Emission halt input
FB4	External relay	T1	terminal
FB3	monitor terminal 2	X2	Automatic reset / manual reset selection terminal
FB2	External relay	X1	Manual reset: X1 – X2 short-circuited
FB1	monitor terminal 1		

Pin layout for light curtain connectors

1 10 2	Connector	Emitter side	Receiver side
	pin No.	connector	connector
	1	Interlock	OSSD 2
	2	+24 V DC	+24 V DC
\mathbb{B}	3	Emission halt	OSSD 1
$0 \sim 5$	4	Auxiliary output	EDM (External relay monitor)
	5	Synchronization wire +	Synchronization wire +
Note: Input and output	6	Synchronization wire -	Synchronization wire -
for pin Nos. (1)	(7)	0 V	0 V
and 12 are not	8	Shield wire	Shield wire
used by this	9	Interference prevention wire +	Interference prevention wire +
product.	10	Interference prevention wire -	Interference prevention wire -
	(1)	(Override input)	(Muting input 1)
	(12)	(Muting lamp output)	(Muting input 2)


I/O CIRCUIT AND WIRING DIAGRAMS

SF-C13

SF4B series wiring diagram (Control Category 4)

For PNP output (minus ground)

• Connect the light curtain control outputs OSSD 1 and OSSD 2 to S1 and S2 respectively.



Notes: 1) The above diagram is when using manual reset. If automatic reset is used, disconnect the lead from X2 and connect it to X3. In this case, a reset (RESET) button is not needed.

2) Use a momentary-type switch as the reset (RESET) button.

Terminal arrangement diagram

		0	Π	A
	Ð	0	Π	Aź
	Ð	0	Π	S
	Ð	$^{\odot}$	Π	S2
	0	0	Π	S
	Ð	0	Π	S2
	Ð	0		Al
	Ð	\odot		X
	Ð	0	Π	X2
	Ð	0	Π	X
	0	0	Π	13
	1	$^{\odot}$	Γ	14
	Ð	0		23
	Ð	\odot	Ι	24
	Ð	\odot		33
	0	\odot		34
	0	\odot		41
	60	$^{\odot}$		42


TT~T

Terminal	Function	
A1	+24 V DC	
A2	0 V	
S1 to S4	Light curtain control output (OSSD) input termina	
AUX	Semiconductor auxiliary output	
X1	Reset output terminal	
X2	Reset input terminal (Manual)	
Х3	Reset input terminal (Automatic)	
13-14, 23-24, 33-34	Enabling path (NO contact × 3)	
41-42	Auxiliary output (NC contact × 1)	

Use a separate terminal block to carry out wiring for light curtains that cannot be connected to the **SF-C13**.

For NPN output (plus ground)

• Connect the light curtain control outputs OSSD 1 and OSSD 2 to S4 and S2 respectively and ground the + side.



Notes: 1) The above diagram is when using manual reset. If automatic reset is used, disconnect the lead from X2 and connect it to X3. In this case, a reset (RESET) button is not needed.

2) Use a momentary-type switch as the reset (RESET) button.

When **SF-C13** is connected to the light curtain, be sure to use the following descrete wire mating cable. **SFB-CCB**(-**MU**), **SFB-CC**(-**MU**)

SF4B


I/O CIRCUIT AND WIRING DIAGRAMS

SF-C14EX(-01)

SF4B series wiring diagram (Control Category 4)

For PNP output (minus ground)


• Set the output polarity selection switch to the PNP side and ground the 0 V line.




- not used, short-circuit between the terminals S11 to S12 and S21 to S22 directly.
- Notes: 1) The above diagram is when using manual reset. If automatic reset is used, disconnect the lead from X12 and X22, and connect them to X13 and X23, as shown by the dotted lines. In this case, a reset (RESET) button is not needed. Terminals X31 to X32 are for manual reset only. 2) Use a momentary-type switch for the reset (RESET) button.

For NPN output (plus ground)

• Set the output polarity selection switch to the NPN side and ground the side of the power supply input.



Terminal arrangement		Function	Terminal	Function
diagram		Enabling path 1, Beam received / Beam	S11	Emergency stop
14 LIGHT CURTAIN APPLICATION EXPANSION UNIT	24	interrupted output of the light curtain	S12	contact input
²⁴ SF-C14EX	34	Enabling path 2, light curtain output	S21	2 NC input Between S11 and S12
	44	including the muting function	S22	Between S21 and S22
54 OLD S12 OLD 64 OLD S21 OLD	54	Enabling path 3 Emergency stop output	X11	Enabling path 1 reset input
	64		X12	X11 - X12: Manual reset
53- QID X12 QID	S3+	Muting sensor input 1	X13	X11 - X13: Automatic reset
	S3	(PNP output type) S3+, S3–: Power supply S3: Sensor output	X21	Enabling path 2 reset input
	S3-		X22	X21 - X22: Manual reset X21 - X23: Automatic reset
	S4+	(NPN output type) S4+, S4-: Power supply S4: Sensor output Test input terminal	X23	
	S4		X31	Enabling path 3 reset input X31 - X32: Manual reset
	S4-		X32	
	T1		AUX1	Auxiliary output 1, Muting output
	T2	Open: Test mode Short-circuit: Normal operation	AUX2	Auxiliary output 2, Override output
	01	Override input terminal Open: Invalid	AUX3	Auxiliary output 3, Blown lamp output
	02	Short-circuit: Valid	AUX4	Auxiliary output 4, Light curtain auxiliary output
	L1+	Muting lamp	IE+	Interference prevention terminal, Emitter side +
	L1-	output 1	IE-	Interference prevention terminal, Emitter side -
	L2+	Muting lamp	IR+	Interference prevention terminal, Receiver side +
	L2-	output 2	IR-	Interference prevention terminal, Receiver side -
	A1	+24 V DC		
	A2	0 V		



Refer to the manual on our website for details.

Interlock function

 The selection of manual reset / automatic reset is available by applying the interlock input wiring. The interlock becomes available by selecting manual reset. (Refer to the SF4B<V2> manual for details.)

Emission halt function

- This function stops the emission process of the emitter. You can select whether emission is on or halted by means of the connection status for the emission halt input / reset input wire (pink).
- During emission halt, the control outputs (OSSD 1, OSSD 2) become OFF status.
- By using this function, malfunction due to extraneous noise or abnormality in the control outputs (OSSD 1, OSSD 2) and the auxiliary output can be determined even from the machinery side.
- Normal operation is restored when the emission halt input / reset input wire (pink) is connected to 0 V or +V. (Refer to the SF4B<V2> manual for details.)

Auxiliary output (Non-safety output)

 This light curtain incorporates the auxiliary output (yellowgreen / black) for the non-safety output. The auxiliary output is incorporated with the emitter. (Refer to the SF4B<V2> manual for details.)

External device monitoring function

 This is the function for checking whether the external safety relay connected to the control outputs (OSSD 1, OSSD 2) perform normally in accordance with the control outputs (OSSD 1, OSSD 2) or not. Monitor the contacting point "b" of the external safety relay, and if any abnormality such as deposit of the contacting point, etc. is detected, change the status of the light curtain into lockout one, and turn OFF the control outputs (OSSD 1, OSSD 2). (Refer to the SF4B<V2> manual for details.)

Muting function

- This function turns the safety function of this light curtain into disabled temporarily. When the control outputs (OSSD 1, OSSD 2) are ON, this function is available for passing the workpiece through the sensing area of the light curtain without stopping the machinery. The muting function becomes valid when all the conditions listed below are satisfied. However, this function connot be used with the SF4B-□-03<V2>.
- ① The control outputs (OSSD 1, OSSD 2) shall be ON.
- ② The incandescent lamp with 3 to 10 W shall be connected to the muting lamp output (red).
- ③ The output of the muting sensors A and B shall be changed from OFF (open) to ON. At this time, the time difference occurred by changing the output of the muting sensors A and B into ON status shall be within 0.03 to 3 sec.
- The following devices, photoelectric sensor with semiconductor output, inductive proximity sensor, position switch on N.O. (Normally open) contact, etc. are available for applying to the muting sensor.
- In case of using the muting function, please order 12-core cable.

(Refer to the SF4B<V2> manual for details.)

Override function

This function sets the safety function of this light curtain enabled forcibly. When using the muting function, the override function can be used to start the machinery at times such as when the control outputs (OSSD 1 and OSSD 2) are OFF or when the muting sensors are ON when the line is to be started.
 The override function becomes valid when all the conditions listed below are satisfied.
 However, this function cannot be used with the SF4B-□-03<V2>.

(Refer to the SF4B<V2> manual for details.)

Series connection

Connectable up to 3 sets of light curtains (however, 192 beam channels max.) (Refer to the **SF4B<V2>** manual for details.)

Parallel connection

Connectable up to 3 sets of light cartains (Refer to the SF4B<V2> manual for details.)

Series and parallel mixed connection

Connectable up to 3 sets of light curtains (however, 192 beam channels max.) (Refer to the **SF4B<V2>** manual for details.)

Wiring



Refer to the applicable regulations for the region where this device is to be used when setting up the device. In addition, make sure that all necessary measures are taken to prevent possible dangerous operating errors resulting from earth faults.

- Make sure to carry out the wiring in the power supply off condition.
- Verify that the supply voltage variation is within the rating.
- If power is supplied from a commercial switching regulator, ensure that the frame ground (F.G.) terminal of the power supply is connected to an actual ground.
- In case noise generating equipment (switching regulator, inverter motor, etc.) is used in the vicinity of this sensor, connect the frame ground (F.G.) terminal of the equipment to an actual ground.
- Do not run the wires together with high-voltage lines or power lines or put them in the same raceway. This can cause malfunction due to induction.

Part description and function

• (Refer to the SF4B<V2> manual for details.)

Others

- Do not use during the initial transient time (2 sec.) after the power supply is switched on.
- Avoid dust, dirt and steam.
- Take care that the light curtain does not come in direct contact with water, oil, grease, or organic solvents, such as, thinner, etc.
- Take care that the light curtain is not directly exposed to fluorescent light from a rapid-starter lamp or a high frequency lighting device, as it may affect the sensing performance.


PRECAUTIONS FOR PROPER USE



 When this device is used in the "PSDI mode", an appropriate control circuit must be configured between this device and the machinery. For details, be sure to refer to the standards or regulations applicable in each region or country.


- To use this product in the U.S.A., refer to OSHA 1910. 212 and OSHA 1910. 217 for installation, and in Europe, refer to EN 999 as well. Observe your national and local requirements before installing this product.
- This catalog is a guide to select a suitable product. Be sure to read instruction manual attached to the product prior to its use.
- Both emitter and receiver are combined adjusted on factory setting, please apply both emitter and receiver with the same serial No. The serial No. is indicated on the plates of both emitter and receiver. (Indicated under model No.)
- · Make sure to carry out the test run before regular operation.
- This safety system is for use only on machinery in which the dangerous parts can be stopped immediately, either by an emergency stop unit or by disconnecting the power supply. Do not use this system with machinery which cannot be stopped at any point in its operation cycle.

Sensing area





- retroreflective type arrangement.
- Furthermore, facing several receivers towards one emitter, or vice versa, could produce a non-sensing area or cause mutual interference, which may result in serious injury or death.


Correct mounting method



Wrong mounting method








Safety distance

• Calculate the safety distance correctly, and always maintain a distance which is equal to or greater than the safety distance, between the sensing area of this light curtain and the dangerous parts of the machinery. (Please check the latest standards for the equation.) If the safety distance is miscalculated or if sufficient distance is not maintained, there is a danger of serious injury or death.



Before designing the system, refer to the relevant standards of the region where this device is to be used and then install this device. Also, the below calculation is valid only when the intrusion direction is perpendicular to the sensing area. In case the intrusion direction is not perpendicular to the sensing area, be sure to refer to the relevant standard (regional standard, specification of the machine, etc.) for details of the calculation.





The sizes of the minimum sensing objects for this device vary depending on whether or not the floating blanking function is being used. Calculate the safety distance with the proper size of the minimum sensing object and appropriate equation.

Size of minimum sensing object when applying floating blanking function

			-	-
	Min. sensing object when applying floating blanking function			
	Invalid	Setting (Note)		
	Invalio	1 beam channel	2 beam channels	3 beam channels
SF4B-F¤(G) (Min. sensing object ø14 mm ø0.551 in)	ø14 mm ø0.551 in	ø24 mm ø0.945 in	ø34 mm ø1.339 in	ø44 mm ø1.732 in
SF4B-H _E (G) (Min. sensing object ø25 mm ø0.984 in)	ø25 mm ø0.984 in	ø45 mm ø1.772 in	ø65 mm ø2.559 in	ø85 mm ø3.346 in
SF4B-Ac(G) (Min. sensing object ø45 mm ø1.772 in)	ø45 mm ø1.772 in	ø85 mm ø3.346 in	ø125 mm ø4.921 in	ø165 mm ø6.496 in
Note: Refer to p.10 for details of the floating blanking function. However, the floating blanking function cannot be used with the SF4B-n-01 <v2>, the SF4B-n-03<v2> and SF-C14EX-01</v2></v2>				

For use in Europe (EU) (as EN 999)] (Also applicable to ISO 13855 / JIS B 9715)

For intrusion direction perpendicular to the sensing area <In case that the minimum sensing object is ø40 mm ø1.575 in or less>

- Equation ① S = K × T + C S: Safety distance (mm) Minimum required distance between the sensing area
 - surface and the dangerous parts of the machine K: Intrusion velocity of operator's body or object (mm/sec.)
 - Normally taken as 2,000 (mm/sec.) for calculation T: Response time of total equipment (sec.)
 - $T = T_m + T_{SF4B}$
 - T_m: Maximum halting time of machinery (sec.) T_{SF4B}: Response time of the **SF4B<V2>** series (sec.)
 - C: Additional distance calculated from the size of the minimum sensing object of the light curtain (mm) However, the value of "C" cannot be less than 0. $C = 8 \times (d - 14)$
 - d: Minimum sensing object diameter (mm)

PRECAUTIONS FOR PROPER USE

Refer to the manual on our website for details.

 For calculating the safety distance "S", there are the following five cases.

First calculate by substituting the value K = 2,000 (mm/sec.) in the equation above. Then, classify the obtained value of "S" into three cases, 1) S < 100, 2) $100 \le S \le 500$, and 3) S > 500. For Case 3) S > 500, recalculate by substituting the value K = 1,600 (mm/ sec.). After that, classify the calculation result into two cases, 4) S \leq 500 and 5) S > 500. For details, refer to the instruction manual enclosed with this product. For calculating "Tm" (maximum halt time of the machinery), use a special device called a "brake monitor".

When this device is used in the "PSDI mode", an appropriate safety distance "S" must be calculated. For details, be sure to refer to the standards or regulations applicable in each region or country.

<In the case that the minimum sensing object is ø40 mm ø1.575 in or more>

- Equation
 - $S = K \times T + C$ S: Safety distance (mm)
- K: Intrusion velocity of operator's body or object (mm/sec.) Taken as 1,600 (mm/sec.) for calculation
- T: Response time of total equipment (sec.)

 $T = T_m + T_{SF4B}$ Tm: Maximum halting time of machinery (sec.)

- T_{SF4B}: Response time of the **SF4B**<V2> series (sec.) C: Additional distance calculated from the size of the
- minimum sensing object of the light curtain (mm) C = 850 (mm) (Constant)

For use in the United States of America (as per ANSI B11.19)

- Equation (2) $S = K \times (T_S + T_C + T_{SF4B} + T_{bm}) + D_{pf}$ S: Safety distance (mm)
- Minimum required distance between the sensing area surface and the dangerous parts of the machine
- K: Intrusion velocity {Recommended value in OSHA is 63 (inch/sec.) ≈ 1,600 (mm/sec.)} ANSI B11.19 does not define the intrusion velocity "K". When determining "K", consider possible factors including physical ability of operators.
- Ts: Halting time calculated from the operation time of the control element (air valve, etc.) (sec.)
- Tc: Maximum response time of the control circuit required for functioning the brake (sec.)

TSF4B: Response time of light curtain (sec.)

Tbm: Additional halting time tolerance for the brake monitor (sec.)

The following equation holds when the machine is equipped with a brake monitor.

 $T_{bm} = T_a - (Ts + Tc)$

Ta: Setting time of brake monitor (sec.) When the machine is not equipped with a brake monitor, it is recommended that 20 % or more of (Ts + Tc) is taken as additional halting time.

Dpf: Additional distance calculated from the size of the minimum sensing of the

SF4B-F□(**G**)**<V2>**: D_{pf} = 23.8 mm 0.937 in **SF4B-H**_□(**G**)**<V2>**: D_{pf} = 61.2 mm 2.409 in **SF4B-A**□(**G**)**<V2>**: D_{pf} = 129.2 mm 5.087 in

 $Dpf = 3.4 \times (d - 0.276)$ (inch)

- ≈ 3.4 × (d 7) (mm)
- d: Minimum sensing object diameter 0.552 (inch) ≈ 14 (mm) SF4B-F□(G)<V2> Minimum sensing object diameter 0.985 (inch) ≈ 25 (mm) SF4B-H□(G)<V2> Minimum sensing object diameter 1.772 (inch) ≈ 45 (mm) SF4B-A□(G)<V2>


Output waveform [Control outputs (OSSD 1, OSSD 2) ON]

• Refer to the SF4B<V2> manual for details.

Influence of reflective surfaces

• Refer to the SF4B<V2> manual for details.

Handy-controller



· Refer to the instruction manual enclosed with the handy-controller for details of the function settings for using handy-controller SFB-HC (optional).

Troubleshooting

Refer to the SF4B<V2> manual for details.

Corner mirror

- · Be sure to carry out maintenance while referring to the instruction manual for the SF4B series of light curtains.
- · Do not use if dirt, water, or oil, etc. is attached to the reflective surface of this product. Appropriate sensing range may not be maintained due to diffusion or refraction.
- Make sure that you have read the instruction manual for the corner mirror thoroughly before setting up the corner mirrors and light curtains, and follow the instructions given. If the equipment is not set up correctly as stipulated in the instruction manual, incident light errors may result in unexpected situations which may result in serious injury or death.
- Please download the instruction manuals from our website.



- Light curtain SF4B series cannot be used as a retroreflective type. Avoid installing the light curtain as a retroreflective type when this product is applied.
- The mirror part of this product is made of glass. Note that if it is broken, the glass shards may fly apart.
- Do not use if crack or breakage appears on the reflective surface of this product. Proper sensing range may not be maintained due to diffusion or refraction.

If crack or breakage appears on the reflective surface of this product, replace the product.

- · When adjusting beam channels with a laser alignment tool, etc., take sufficient care that the laser beam reflected by this product does not enter the eyes.
- Failure to follow the above items may result in death or serious injury.


DIMENSIONS (Unit: mm in)

SF4B-□<V2>

Not available for the robust type **SF4B-G<V2>** Light curtain

Assembly dimensions

Mounting drawing for the light curtains using the standard mounting brackets **MS-SFB-1** (optional) and the intermediate supporting brackets.



Emitter

Receiver

Emitter

Receiver

	Model No.		Protective height (Main body) length	Mounting pitch	Total length	Intermediate supporting bracket mounting pitch				
		А	В	С	D	E	F			
SF4B-F23□ <v2></v2>	SF4B-H12□ <v2></v2>	SF4B-A6□ <v2></v2>	230 9.055	270 10.630	286 11.260	—		—		
SF4B-F31□ <v2></v2>	SF4B-H16□ <v2></v2>	SF4B-A8□ <v2></v2>	310 12.205	350 13.780	366 14.406		_			
SF4B-F39□ <v2></v2>	SF4B-H20□ <v2></v2>	SF4B-A10□ <v2></v2>	390 15.354	430 16.929	446 17.559	—		—		
SF4B-F47□ <v2></v2>	SF4B-H24□ <v2></v2>	SF4B-A12□ <v2></v2>	470 18.504	510 20.079	526 20.709			—		
SF4B-F55⊡ <v2></v2>	SF4B-H28□ <v2></v2>	SF4B-A14□ <v2></v2>	550 21.654	590 23.228	606 23.858		_	_		
SF4B-F63⊡ <v2></v2>	SF4B-H32□ <v2></v2>	SF4B-A16□ <v2></v2>	630 24.803	670 26.378	686 27.008	—	_	_		
SF4B-F71⊡ <v2></v2>	SF4B-H36□ <v2></v2>	SF4B-A18□ <v2></v2>	710 27.953	750 29.528	766 30.157					
SF4B-F79□ <v2></v2>	SF4B-H40□ <v2></v2>	SF4B-A20□ <v2></v2>	790 31.102	830 32.677	846 33.307	390 15.354				
SF4B-F95□ <v2></v2>	SF4B-H48□ <v2></v2>	SF4B-A24□ <v2></v2>	950 37.402	990 38.976	1,006 39.606	470 18.504	_			
SF4B-F111□ <v2></v2>	SF4B-H56□ <v2></v2>	SF4B-A28□ <v2></v2>	1,110 43.701	1,150 45.276	1,166 45.905	550 21.654	_			
SF4B-F127□ <v2></v2>	SF4B-H64□ <v2></v2>	SF4B-A32□ <v2></v2>	1,270 50.000	1,310 51.575	1,326 52.505	418 16.457	842 33.150	—		
	SF4B-H72□ <v2></v2>	SF4B-A36□ <v2></v2>	1,430 56.299	1,470 57.874	1,486 58.504	472 18.583	948 37.323			
	SF4B-H80□ <v2></v2>	SF4B-A40□ <v2></v2>	1,590 62.598	1,630 64.173	1,646 64.803	525 20.669	1,055 41.535			
	SF4B-H88□ <v2></v2>	SF4B-A44□ <v2></v2>	1,750 68.898	1,790 70.472	1,806 71.102	433 17.047	870 34.252	1,308 51.496		
	SF4B-H96□ <v2></v2>	SF4B-A48□ <v2></v2>	1,910 75.197	1,950 76.772	1,966 77.401	473 18.622	950 37.402	1,428 56.220		

Model No.	Beam pitch	First beam channel position			
	G	н			
SF4B-F□ <v2></v2>	10 0.394	5 0.197			
SF4B-H□ <v2></v2>	20 0.787	5 0.197			
SF4B-A _D <v2></v2>	40 1.575	15 0.591			

DIMENSIONS (Unit: mm in)

The CAD data in the dimensions can be downloaded from our website.


Not available for the robust type **SF4B-G<V2>** Light curtain


SF4B-□<V2>

Assembly dimensions

Mounting drawing for the light curtains using the dead zoneless brackets **MS-SFB-3** (optional) and the intermediate supporting brackets.

<Rear mounting>





Emitter

Receiver

Emitter

Receiver

	Model No.	Protective height (Main body) length	MS-SF Mountir	B-3 ng pitch	Intermediate supporting bracket mounting pitch			
					К	L	М	N
SF4B-F23□ <v2></v2>	SF4B-H12□ <v2></v2>	SF4B-A6□ <v2></v2>	230 9.055	209 8.228	201 7.913	_	_	_
SF4B-F31□ <v2></v2>	SF4B-H16□ <v2></v2>	SF4B-A8□ <v2></v2>	310 12.205	289 11.378	281 11.063	—	—	_
SF4B-F39□ <v2></v2>	SF4B-H20□ <v2></v2>	SF4B-A10□ <v2></v2>	390 15.354	369 14.528	361 14.213	_	_	_
SF4B-F47□ <v2></v2>	SF4B-H24□ <v2></v2>	SF4B-A12□ <v2></v2>	470 18.504	449 17.677	441 17.362	_	_	_
SF4B-F55□ <v2></v2>	SF4B-H28□ <v2></v2>	SF4B-A14□ <v2></v2>	550 21.654	529 20.827	521 20.512	_	_	
SF4B-F63□ <v2></v2>	SF4B-H32□ <v2></v2>	SF4B-A16□ <v2></v2>	630 24.803	609 23.976	601 23.661	_	_	
SF4B-F71□ <v2></v2>	SF4B-H36□ <v2></v2>	SF4B-A18□ <v2></v2>	710 27.953	689 27.126	681 26.811			
SF4B-F79□ <v2></v2>	SF4B-H40□ <v2></v2>	SF4B-A20□ <v2></v2>	790 31.102	769 30.276	761 29.961	370 14.567		
SF4B-F95□ <v2></v2>	SF4B-H48□ <v2></v2>	SF4B-A24□ <v2></v2>	950 37.402	929 36.575	921 36.260	450 17.717	—	_
SF4B-F1110 <v2></v2>	SF4B-H56□ <v2></v2>	SF4B-A28□ <v2></v2>	1,110 43.701	1,089 42.874	1,081 42.559	530 20.866	_	_
SF4B-F1270 <v2></v2>	SF4B-H64□ <v2></v2>	SF4B-A32□ <v2></v2>	1,270 50.000	1,249 49.173	1,241 48.858	398 15.669	822 32.362	
	SF4B-H72□ <v2></v2>	SF4B-A36□ <v2></v2>	1,430 56.299	1,409 55.472	1,401 55.157	452 17.795	928 36.535	
	SF4B-H80□ <v2></v2>	SF4B-A40□ <v2></v2>	1,590 <mark>62.598</mark>	1,569 61.772	1,561 61.457	505 19.882	1,035 40.748	
	SF4B-H88□ <v2></v2>	SF4B-A44□ <v2></v2>	1,750 68.898	1,729 68.071	1,721 67.756	413 16.260	850 33.465	1,288 50.709
	SF4B-H96□ <v2></v2>	SF4B-A48□ <v2></v2>	1,910 75.197	1,889 74.370	1,881 74.055	453 17.835	930 36.614	1,408 55.433

Model No.	Beam pitch	First beam channel position				
	G	Н				
SF4B-F□ <v2></v2>	10 0.394	5 0.197				
SF4B-H⊡ <v2></v2>	20 0.787	5 0.197				
SF4B-A⊡ <v2></v2>	40 1.575	15 0.591				

DIMENSIONS (Unit: mm in)


The CAD data in the dimensions can be downloaded from our website.

SF4B-□G<V2>

Assembly dimension

Mounting drawing for light curtains using the standard mounting brackets **MS-SF4BG-1** (optional) and the intermediate supporting brackets.

<Rear mounting>



<Side mounting>

Emitter

Receiver

Emitter

Receiver

Light curtain

				Protective height (Main body length)	Mou pitch	nting	Total length			nediate et mou						
Model No.			ŀ	4												
		SF4B-F□G <v2> SF4B-H□G<v2></v2></v2>	SF4B-A□G <v2></v2>	В	С	D	E	F	G	Н	J	K	L			
SF4B-F23G <v2></v2>	SF4B-H12G <v2></v2>	SF4B-A6G <v2></v2>	220 8.661	200 7.874	244 9.606	279 10.984	313 12.323	334 13.150	—	—	—		—	_		
SF4B-F31G <v2></v2>	SF4B-H16G <v2></v2>	SF4B-A8G <v2></v2>	300 11.811	280 11.024	324 12.756	359 <mark>14.13</mark> 4	393 15.472	414 16.299	—			—	—	—		
SF4B-F39G <v2></v2>	SF4B-H20G <v2></v2>	SF4B-A10G <v2></v2>	380 14.961	360 14.173	404 15.906	439 17.283	473 18.622	494 19.449	—		—	—	—	—		
SF4B-F47G <v2></v2>	SF4B-H24G <v2></v2>	SF4B-A12G <v2></v2>	460 18.110	440 17.323	484 19.055	519 20.433	553 21.772	574 22.598	—		—	—	—	—		
SF4B-F55G <v2></v2>	SF4B-H28G <v2></v2>	SF4B-A14G <v2></v2>	540 21.260	520 20.472	564 22.205	599 23.583	633 24.921	654 25.748	—		—	—	—	—		
SF4B-F63G <v2></v2>	SF4B-H32G <v2></v2>	SF4B-A16G <v2></v2>	620 24.409	600 23.622	644 25.354	679 26.732	713 28.071	734 28.898	—		—	—	—	—		
SF4B-F71G <v2></v2>	SF4B-H36G <v2></v2>	SF4B-A18G <v2></v2>	700 27.559	680 26.772	724 28.504	759 <mark>29.882</mark>	793 31.220	814 32.047	—	—	—	—	—	—		
SF4B-F79G <v2></v2>	SF4B-H40G <v2></v2>	SF4B-A20G <v2></v2>	780 30.709	760 29.921	804 31.654	839 <mark>33.031</mark>	873 34.370	894 35.197	441 17.362	—	414 16.299	—	419 16.496	—		
SF4B-F95G <v2></v2>	SF4B-H48G <v2></v2>	SF4B-A24G <v2></v2>	940 37.008	920 36.220	964 37.953	999 <mark>39.331</mark>	1,033 40.669	1,054 <mark>41.496</mark>	521 20.512		494 <mark>19.449</mark>	_	499 19.646	_		
SF4B-F111G <v2></v2>	SF4B-H56G <v2></v2>	SF4B-A28G <v2></v2>	1,100 43.307	1,080 42.520	1,124 44.252	1,159 <mark>45.630</mark>	1,193 46.968	1,214 47.795	601 <u>23.661</u>	—	574 22.598	—	579 22.795	—		
SF4B-F127G <v2></v2>	SF4B-H64G <v2></v2>	SF4B-A32G <v2></v2>	1,260 49.606	1,240 48.819	1,284 <u>50.551</u>	1,319 <mark>51.92</mark> 9	1,353 <mark>53.268</mark>	1,374 <mark>54.09</mark> 4	681 26.811		654 <mark>25.748</mark>	_	659 <mark>25.945</mark>	_		
—	SF4B-H72G <v2></v2>	SF4B-A36G <v2></v2>	1,420 <u>55.905</u>	1,400 55.118	1,444 56.850	1,479 58.228	1,513	1,534 60.394	520 <u>20.472</u>	1,001 39.409	493 <mark>19.40</mark> 9	974 <mark>38.346</mark>	498 1 <u>9.606</u>	979 <mark>38.543</mark>		
—	SF4B-H80G <v2></v2>	SF4B-A40G <v2></v2>	1,580 62.205	1,560 61.417	1,604 63.150	1,639 <mark>64.528</mark>	1,673 65.866	1,694 <u>66.693</u>	573 22.559	1,108 43.622	546 21.496	1,081 42.559	551 21.693	1,086 42.756		
	SF4B-H88G <v2></v2>	SF4B-A44G <v2></v2>	1,740 68.504	1,720 67.716	1,764 69.449	1,799 70.827	1,833 72.165	1,854 72.992	627 24.685	1,215 47.835	600 23.622	1,188 46.772	605 23.819	1,193 46.968		
	SF4B-H96G <v2></v2>	SF4B-A48G <v2></v2>	1,900 74.803	1,880 74.016	1,924 75.748	1,959 77.126	1,993 78.464	2,014 79.291	680 26.772	1,321 52.008	653 25.709	1,294 50.945	658 25.906	1,289 50.748		

Model No.	Beam pitch	First beam channel position				
	М	N				
SF4B-F□G <v2></v2>	10 0.394	11.8 0.465				
SF4B-H□G <v2></v2>	20 0.787	11.8 0.465				
SF4B-A□G <v2></v2>	40 1.575	21.8 0.858				

40

Light curtain


DIMENSIONS (Unit: mm in)

The CAD data in the dimensions can be downloaded from our website.

SF4B-□G<V2>

Assembly dimensions

Mounting drawing for light curtains using the Dead zoneless mounting brackets **MS-SF4B-3** (optional) and the intermediate supporting brackets.



Distance between beam ax (Top / Bottom channel				Protective height Mounting Intermediate supporting bracket mounting pitch																
	Model No.		A	4																
			SF4B-F□G <v2> SF4B-H□G<v2></v2></v2>	SF4B-A::G <v2></v2>	В	С	D	E	F	G	Н	J	М	N	Ρ	Q	R	S	Т	U
SF4B-F23G <v2></v2>	SF4B-H12G <v2></v2>	SF4B-A6G <v2></v2>	220 8.661	200 7.874	244 9.606	64.5 <mark>2.53</mark> 9	-	-	_	-	-	-	-	-	-	-	-	_	-	_
SF4B-F31G <v2></v2>	SF4B-H16G <v2></v2>	SF4B-A8G <v2></v2>	300 11.811	280 11.024	324 12.756	144.5 <u>5.689</u>	—	_	—	_	_	_	_	-	_	_	-	_	-	—
SF4B-F39G <v2></v2>	SF4B-H20G <v2></v2>	SF4B-A10G <v2></v2>	380 14.961	360 14.173	404 15.906	224.5 8.839	_	_	—	_	_	_	_	—	_	_	-	_	-	—
SF4B-F47G <v2></v2>	SF4B-H24G <v2></v2>	SF4B-A12G <v2></v2>	460 18.110	440 17.323	484 19.055	304.5 <mark>11.988</mark>	_	-	—	_	_	_	_	_	-	—	-	_	-	_
SF4B-F55G <v2></v2>	SF4B-H28G <v2></v2>	SF4B-A14G <v2></v2>	540 21.260	520 20.472	564 22.205	384.5 <mark>15.138</mark>	-	-	—	—	_	_	_	_	-	—	_	_	-	_
SF4B-F63G <v2></v2>	SF4B-H32G <v2></v2>	SF4B-A16G <v2></v2>	620 <mark>24.40</mark> 9	600 23.622	644 25.354	464.5 18.287	—	—	—	_	_	—	-	—	—	—	-	—	-	—
SF4B-F71G <v2></v2>	SF4B-H36G <v2></v2>	SF4B-A18G <v2></v2>	700 27.559	680 <u>26.772</u>	724 28.504	544.5 <mark>21.437</mark>	—	—	—	—	—	—	—	—	—	—	—	—	-	—
SF4B-F79G <v2></v2>	SF4B-H40G <v2></v2>	SF4B-A20G <v2></v2>	780 30.709	760 29.921	804 31.654	624.5 24.587	414 <mark>16.29</mark> 9	—	333 <mark>13.110</mark>	_	288 11.339	_	289 <mark>11.378</mark>	—	330 <mark>12.992</mark>	_	383 <mark>15.079</mark>	_	347 1 <mark>3.661</mark>	_
SF4B-F95G <v2></v2>	SF4B-H48G <v2></v2>	SF4B-A24G <v2></v2>	940 37.008	920 36.220	964 37.953	784.5 30.886	494 <mark>19.44</mark> 9	-	413 <mark>16.260</mark>	—	368 <mark>14.488</mark>	_	369 <mark>14.528</mark>	_	410 <mark>16.142</mark>	—	463 <mark>18.228</mark>	_	427 16.811	_
SF4B-F111G <v2></v2>	SF4B-H56G <v2></v2>	SF4B-A28G <v2></v2>	1,100 43.307	1,080 42.520	1,124 44.252	944.5 <mark>37.18</mark> 5	574 <mark>22.598</mark>	-	493 <mark>19.40</mark> 9	—	448 17.638	_	449 <mark>17.677</mark>	_	490 <mark>19.29</mark> 1	—	543 <mark>21.378</mark>	_	507 1 <u>9.961</u>	_
SF4B-F127G <v2></v2>	SF4B-H64G <v2></v2>	SF4B-A32G <v2></v2>	1,260 49.606	1,240 <mark>48.81</mark> 9	1,284 50.551	1,104.5 <mark>43.484</mark>	654 <mark>25.74</mark> 8	—	573 <mark>22.55</mark> 9	_	528 20.787	—	529 <mark>20.827</mark>	—	570 <mark>22.44</mark> 1	—	623 <mark>24.528</mark>	—	587 <mark>23.110</mark>	—
	SF4B-H72G <v2></v2>	SF4B-A36G <v2></v2>	1,420 <u>55.905</u>	1,400 <u>55.118</u>	1,444 56.850	1,264.5 <mark>49.783</mark>	493 <mark>19.409</mark>	974 38.346	412 <mark>16.220</mark>	893 35.157	367 <mark>14.44</mark> 9	848 33.386	368 <mark>14.488</mark>	849 <mark>33.42</mark> 5	409 <mark>16.102</mark>	890 35.039	462 <mark>18.18</mark> 9	943 <mark>37.126</mark>	426 16.772	907 35.709
	SF4B-H80G <v2></v2>	SF4B-A40G <v2></v2>	1,580 <mark>62.205</mark>	1,560 <mark>61.417</mark>	1,604 63.150	1,424.5 56.083	546 <mark>21.496</mark>	1,081 <mark>42</mark> .559	465 <mark>18.307</mark>	1,000 <mark>39.370</mark>	420 <mark>16.535</mark>	955 <mark>37.598</mark>	421 <mark>16.575</mark>	956 <mark>37.638</mark>	462 <mark>18.18</mark> 9	997 <mark>39.25</mark> 2	515 <mark>20.276</mark>	1,050 <mark>41.33</mark> 9	479 18.858	1,014 39.921
	SF4B-H88G <v2></v2>	SF4B-A44G <v2></v2>	1,740 <u>68.504</u>	1,720 <mark>67.716</mark>	1,764 69.449	1,584.5 <mark>62.382</mark>	600 23.622	1,188 <mark>46.772</mark>	519 <u>20.433</u>	1,107 <mark>43.58</mark> 3	474 <mark>18.661</mark>	1,062 <mark>41.811</mark>	475 <mark>18.70</mark> 1	1,063 <mark>41.850</mark>	516 20.315	1,104 43.465	569 <mark>22.402</mark>	1,157 <mark>45.551</mark>	533 <mark>20.98</mark> 4	1,121 44.134
_	SF4B-H96G <v2></v2>	SF4B-A48G <v2></v2>	1,900 74.803	1,880 74.016	1,924 75.748	1,744.5 <mark>68.681</mark>	653 <mark>25.70</mark> 9	1,294 50.945	572 <mark>22.52</mark> 0	1,213 47.756	527 20.748	1,168 <mark>45.98</mark> 4	528 20.787	1,169 <mark>46.024</mark>	569 <mark>22.402</mark>	1,210 47.638	622 <mark>24.488</mark>	1,263 <mark>49.724</mark>	586 <mark>23.071</mark>	1,227 <mark>48.307</mark>

Model No.	Beam pitch	First beam channel position				
	К	L				
SF4B-F□G <v2></v2>	10 0.394	11.8 0.465				
SF4B-H□G <v2></v2>	20 0.787	11.8 0.465				
SF4B-A□G <v2></v2>	40 1.575	21.8 0.858				

DIMENSIONS (Unit: mm in)

SF4B-D

Protection bar set MC-SFBH assembly dimensions

Mounting drawing for the light curtain on which the front protection unit (MC-SFBH-D) is mounted.


MC-SFBH-□(L) MC-SFBH-□(R) (\mathbf{A}) D ABC 5 0.197 10 0.394 <u>م</u> ł ł ŧ 43.5 ĽΨ ł 43.5 1.713 _10 0.394 10 0 3 10 0.394 - 57.5 -57.5-72.7 72.7 43 1.693 Material: Mounting bracket ... Die-cast zinc alloy 13 0.512 13 Protection barAluminum 0 Two brackets (one pc. each of R type and L type), one protection bar Two pcs. each of M5 (length 16 mm 0.630 in) hexagon-socket-head bolts, M5 (length 20 mm 0.787 in) hexagon-socket-head bolt are attached.

Model No.	Applicable	e light curtain i	model No.	А	В	С	D
MC-SFBH-12(-T)	SF4B-F23□ <v2></v2>	SF4B-H12□ <v2></v2>	SF4B-A6□ <v2></v2>	230 9.055	279 10.984	296 11.654	250 9.843
MC-SFBH-16(-T)	SF4B-F31□ <v2></v2>	SF4B-H16□ <v2></v2>	SF4B-A8□ <v2></v2>	310 12.205	359 14.134	376 14.803	330 12.992
MC-SFBH-20(-T)	SF4B-F39□ <v2></v2>	SF4B-H20□ <v2></v2>	SF4B-A10□ <v2></v2>	390 15.354	439 17.283	456 17.953	410 16.142
MC-SFBH-24(-T)	SF4B-F47□ <v2></v2>	SF4B-H24□ <v2></v2>	SF4B-A12□ <v2></v2>	470 18.504	519 20.433	536 21.102	490 19.291
MC-SFBH-28(-T)	SF4B-F55□ <v2></v2>	SF4B-H28□ <v2></v2>	SF4B-A14□ <v2></v2>	550 21.654	599 23.583	616 24.252	570 22.441
MC-SFBH-32(-T)	SF4B-F63□ <v2></v2>	SF4B-H32□ <v2></v2>	SF4B-A16□ <v2></v2>	630 24.803	679 26.732	696 27.402	650 25.591
MC-SFBH-36(-T)	SF4B-F71□ <v2></v2>	SF4B-H36□ <v2></v2>	SF4B-A18□ <v2></v2>	710 27.953	759 29.882	776 30.551	730 28.740
MC-SFBH-40(-T)	SF4B-F79□ <v2></v2>	SF4B-H40□ <v2></v2>	SF4B-A20□ <v2></v2>	790 31.102	839 33.031	856 33.701	810 31.890
MC-SFBH-48(-T)	SF4B-F95□ <v2></v2>	SF4B-H48□ <v2></v2>	SF4B-A24□ <v2></v2>	950 37.402	999 39.331	1,016 40.000	970 38.189
MC-SFBH-56(-T)	SF4B-F1110 <v2></v2>	SF4B-H56□ <v2></v2>	SF4B-A28□ <v2></v2>	1,110 43.701	1,159 45.630	1,176 46.299	1,130 44.488
MC-SFBH-64(-T)	SF4B-F1270 <v2></v2>	SF4B-H64□ <v2></v2>	SF4B-A32□ <v2></v2>	1,270 50.000	1,319 51.929	1,336 52.598	1,290 50.787
MC-SFBH-72(-T)		SF4B-H72□ <v2></v2>	SF4B-A36□ <v2></v2>	1,430 56.299	1,479 58.228	1,496 58.898	1,450 57.087
MC-SFBH-80(-T)		SF4B-H80□ <v2></v2>	SF4B-A40□ <v2></v2>	1,590 <mark>62.598</mark>	1,639 <mark>64.527</mark>	1,656 65.197	1,610 <mark>63.386</mark>
MC-SFBH-88(-T)		SF4B-H88□ <v2></v2>	SF4B-A44□ <v2></v2>	1,750 68.898	1,799 70.827	1,816 71.496	1,770 69.685
MC-SFBH-96(-T)		SF4B-H96□ <v2></v2>	SF4B-A48□ <v2></v2>	1,910 75.197	1,959 77.126	1,976 77.795	1,930 75.984


Not available for the robust type **SF4B-G<V2>** Light curtain

Protection bar set for rear / side mounting MC-SFBH-□-T assembly dimensions


Mounting drawing for the light curtain on which the front protection unit (**MC-SFBH-–-T**) is mounted.




Side mounting MC-SFBH-D-T(L)



MC-SFBH-□-T(R)





Material: Mounting bracket …Iron (Trivalent chrome plated) Protection bar……Aluminum

Two brackets (one pc. each of R type and L type),


one protection bar [Two pcs. each of M5 (length 18 mm 0.709 in) hexagon-socket-head bolts, M5 (length 20 mm 0.787 in) hexagon-socket-head bolt are attached.

Corner mirror (Optional)


DIMENSIONS (Unit: mm in)


The CAD data in the dimensions can be downloaded from our website.


RF-SFBH-D




Model No.	А	В	С	D	E	F	Net weight
RF-SFBH-12	236 9.291	246 9.685	298 11.732	_	_	272 10.709	970 g approx.
RF-SFBH-16	316 12.441	326 12.835	378 14.882	-	_	352 13.858	1,170 g approx.
RF-SFBH-20	396 15.591	406 15.984	458 18.031	_	_	432 17.008	1,370 g approx.
RF-SFBH-24	476 18.740	486 19.134	538 21.181	-	_	512 20.157	1,570 g approx.
RF-SFBH-28	556 21.890	566 22.283	618 24.331	_	_	592 23.307	1,770 g approx.
RF-SFBH-32	636 25.039	646 25.433	698 27.480	-	_	672 26.457	1,970 g approx.
RF-SFBH-36	716 28.189	726 28.583	778 30.630	_	_	752 29.606	2,170 g approx.
RF-SFBH-40	796 31.339	806 31.732	858 33.779	458 ±50 18.031 ±1.969	—	832 32.756	2,660 g approx.
RF-SFBH-48	956 37.638	966 38.031	1,018 40.079	538 ±50 21.181 ±1.969	_	992 39.055	3,060 g approx.
RF-SFBH-56	1,116 43.937	1,126 44.331	1,178 46.378	618 ±50 24.331 ±1.969	_	1,152 45.354	3,460 g approx.
RF-SFBH-64	1,276 50.236	1,286 50.630	1,338 52.677	698 ±50 27.480 ±1.969	_	1,312 51.653	3,890 g approx.
RF-SFBH-72	1,436 56.535	1,446 56.929	1,498 58.976	538 ±50 21.181 ±1.969	1,018 ±50 40.079 ±1.969	1,472 57.953	4,550 g approx.
RF-SFBH-80	1,596 62.835	1,606 63.228	1,658 65.275	591 ±50 23.268 ±1.969	1,125 ±50 44.291 ±1.969	1,632 64.252	4,950 g approx.
RF-SFBH-88	1,756 69.134	1,766 69.527	1,818 71.575	645 ±50 25.394 ±1.969	1,231 ±50 48.464 ±1.969	1,792 70.551	5,350 g approx.
RF-SFBH-96	1,916 75.433	1,926 75.827	1,978 77.874	698 ±50 27.480 ±1.969	1,338 ±50 52.677 ±1.969	1,952 76.850	5,750 g approx.










DIMENSIONS (Unit: mm in)


MS-SFB-2






MS-SF4BG-2

Rear mounting





Note: The intermediate supporting bracket **MS-SF4BG-2** is enclosed with the following products. The quantity differs depending on the product as shown below:


- 1 set: SF4B-F□G<V2> ... Light curtain with 79 to 127 beam channels SF4B-H□G<V2> ... Light curtain with 40 to 64 beam channels SF4B-A□G<V2> ... Light curtain with 20 to 32 beam channels
- 2 sets: SF4B-H_G<V2> ... Light curtain with 72 to 96 beam channels
- SF4B-ADG<V2> ... Light curtain with 36 to 48 beam channels

DIMENSIONS (Unit: mm in)


The CAD data in the dimensions can be downloaded from our website.



Not available for the robust type **SF4B-G<V2**> Dead zoneless mounting bracket (Optional)




Note: The finger protection type has a beam pitch of 10 mm 0.394 in, which produces a dead zone. Additional measures will be required, such as using a protection cover.




Material: Dead zoneless mounting bracket \cdots SPCC (Trivalent chrome plated) Dead zoneless supporting bracket \cdots PPS

Mounting adjustment range

The adjustment range of the light curtain angle is up to ±10 degrees.









DIMENSIONS (Unit: mm in)


8


MS-SFB-4-T





MS-SFB-7-T MS-SFB-1-T2 (Rear mounting)





Material: Iron (Trivalent chrome plated) Four bracket set Four M5 (length 18 mm 0.709 in) hexagon-socket-head bolts are attached.

MS-SFB-8-T MS-SFB-1-T2 (Side mounting)

MS-SFB-8-T(R)







28

Not available for the robust type SF4B-_G<V2>

The adjustment range of the light

curtain angle is up

to ±15 degrees.

Mounting adjustment range

/15


M8 side mounting bracket (Optional) M8 rear / side mounting brackets set (Optional)

M8 rear mounting bracket (Optional) M8 rear / side mounting brackets set (Optional)


15

(R20.2


Not available for the robust type SF4B-DG<V2>








Mounting adjustment range



The adjustment range of the light curtain angle is up to ±15 degrees.





Control unit (Optional)

DIMENSIONS (Unit: mm in)

SF-C13

The CAD data in the dimensions can be downloaded from our website.







SF-C14EX(-01)


SF-C12






Control unit (Optional)






SFB-WY1

Y-shaped connector




DIMENSIONS (Unit: mm in)

SF-LAT-2N




It is not available for the robust SF4B-DG<V2>.



The CAD data in the dimensions can be downloaded from our website.

SF-LAT-4BG

Laser alignment tool (Optional)



It is only available for the robust SF4B-DG<V2>.

Please contact

Panasonic Electric Works SUNX Co., Ltd.

2431-1 Ushiyama-cho, Kasugai-shi, Aichi, 486-0901, Japan ■Telephone: +81-568-33-7211 ■Facsimile: +81-568-33-2631 Global Sales & Marketing Division ■Telephone: +81-568-33-7861 ■Facsimile: +81-568-33-8591 panasonic.co.jp/id/pidsx/global



All Rights Reserved ©Panasonic Electric Works SUNX Co., Ltd. 2012