WL/WLM

Wide Range of Two-circuit Switches; Select One for the Operating Environment/Application

- A wide selection of models are available, including the overtravel models with greater OT, indicator-equipped models for checking operation, low-temperature models, heat-resistant models, and corrosion-proof models.
- Microload models are added to the product lineup.
- Approved standards: EC/IEC, UL, CSA, CCC (Chinese standard).

Contact your OMRON representative for information on approved models.

Be sure to read *Safety Precautions* on page 39 to 42 and *Safety Precautions for All Limit Switches*.

Features

Standard Models

Many Variations in Standard Limit Switches A Wide Range of Models

The WL Series provides a complete range of Limit Switches with a long history of meeting user needs. Select environment-resistant specifications, actuators for essentially any workpiece, operating sensitivity matched to the workpiece, operation indicators to aid operation and maintenance, and various wiring specifications.

Environment-resistant Models

Select from Six Types of Environment Resistance

The series includes Airtight Switches, Hermetic Switches, Heatresistant Switches, Low-temperature Switches, Corrosion-proof switches, and Weather-proof Switches. Select the one required by the onsite environment.

Spatter-prevention Models

Excellent Performance on Arc Welding Lines or Sites with Spattering Cutting Powder Ideal for Welding Sites

Stainless steel and resins that resist adhesion of spatters are used to prevent troubles caused by zinc powder generated during welding.

Long-life Models

Mechanical Endurance of 30 Million Operations Long-life Models for High-frequency Applications

Long life has been achieved by increasing the resistance to friction and creating better sliding properties in the head mechanism. Greater visibility is provided when setting with a fluorescent display for setting the stroke.




For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Features Common to All Models

DPDB Operation

The double-pole, double-break structure ensures circuit braking.



Degree of Protection; IP67

O-rings, cover seals, and other measures provide a water-proof, dripproof structure (IP67).

Approved Standards to Aid Export Machines

Various WL/WLM switches are approved by UL, CSA, TÜV, EN/IEC, and CCC making them ideal for export machines.

High-precision Models Available in All Switch Types; Ideal for Position Control

High-precision models achieve a very small movement to operation (approx. 5°) and a repeat accuracy that is twice that of basic models.

Operation Indicators for Easier Daily Inspections*

Confirm operation with a neon lamp or LED for easier startup confirmations and maintenance. * Operation indicators are provided on Indicator-

equipped switches, Spatter-prevention Basic

Switches, and Long-life Basic Switches.




Models with Connectors to Reduce Wiring

Reduce wiring with one-touch connection. Models with direct-wired and prewired connectors that make Switch replacement easier are also available.

WL/WLM

Product Configuration

Selection by Purpose



Tables of Models

General-purpose Switches

Spatter-prevention Switches

Long-life Switches

Heads (Roller levers only)

Туре	General purpose	Features	Head spe	Head specifications Spatter prevention		
туре	Model	Total travel (TT)	One-side operation	Head mounting	Model	Model
Basic	WLC	• With a Roller Lever	Possible *1 (Except for long-life models.)	Any of 4 directions	WLCA2-□S	WLMCA2
General- purpose Overtravel	WLH	 Overtravel is large, making setting the dog easier. Mounting is compatible with WLH2. 	Not possible *2	Any of 4 directions	WLH2-□S	WLH2
High-sensitivity Overtravel	WLG	 Operation is highly sensitive with only 10° pretravel. Overtravel is large, making setting the dog easier. Mounting is compatible with WLG2. 	Not possible *2	Any of 4 directions	WLG2-⊡S	WLMG2
Overtravel,	WL□-2	• Overtravel is large, making setting the dog easier. 90° 90°	Not possible *2	Any of 4 directions		
90 $^{\circ}$ operation	WL□-2N	• Mounting is compatible with WLCA2-2.	Possible *1	Either of 2 directions		_
High-precision	WLGCA2	 Repeat accuracy is twice that basic models. Operation is highly sensitive with only 5° pretravel. Ideal for positioning, e.g., 	Possible *1	Any of 4 directions	WLGCA2-⊟S	WLMGCA2
Maintained	WLCA32-🗆	• When the dog throws the lever, the output is reversed and the reversed output is held even after the dog passed. The original status is returned to only after the dog passed.	_	Any of 4 directions	_	_

*1. One-side operation means that three operational directions can be selected electrically, according to the change in direction of the operating plunger. The operating plunger is set for operation on both sides before delivery. *2. Those models for which one-side operation is impossible can only operate on both sides.

Connectors and Conduits

Wiring type	General-purpose	Connector/conduit specifications	Spatter-prevention	Long-life
winnig type	Model	Connector/conduit specifications	Model	Model
Direct-wired connector	WL-LDK	SC-2F/-4F Connector built-in	—	WLM -LDK
Pre-wired connector	WLLD-M1_ WLLDGJ_ WLLD-DK1EJ_	XS2H-series Pre-wired Connector built- in	WL □- □S-M1□J-1 WL□-□S-DGJS03	WLM□-LD-M1J WLM□-LD-□GJ□
Conduit (screw terminal)	WL	 G1/2 with no ground terminal G1/2 with ground terminal Pg13.5 with ground terminal M20 with ground terminal 1/2 14NPT with ground terminal 	_	WLM□-LD

Environment-resistant Switches

	ltem		Environment-resistant	
Туре	Model	Application	Environment-resistant construction	Applicable models
Airtight seal WL⊡-55			Uses the W-10FB3-55 Airtight Built-in Switch. Note: Use the SC Connector for the conduit opening.	All models except the low- temperature and heat-re- sistant models Note: Models can be produced using standard actuators.
	WL□-139	For uses in locations sub- ject to cutting oil or water		All models except the low- temperature and heat-re- sistant models
	WL□-140			
Hermetic seal (Molded terminals/	WL□-141		Refer to page 25 for information on the environ- ment-resistant construction of Switches with Her-	Note: Models can be produced using standard
Anti-coolant)	WL□-145		metic Seals.	actuators. Only the WLCA2, WLGCA2, or
	WLD-RP40			WLH2 can be produced
	WL -RP60			for the WL□-141 and WL□-145.
Low-temperature *	WL□-TC	Can be used at a tempera- ture of -40° C (operating temperature range: -40 to 40° C), but cannot with- stand icing.	 Uses a general-purpose built-in switch. Silicone rubber is used for rubber parts such as the O-ring, gasket, etc. 	All models except airtight seal, hermetic seal, heat- resistant, corrosion-proof, and indicator-equipped models
Heat-resistant *	ht-resistant * WL -TH Can be used in temperatures of 120°C (operating temperature range: 5 to 120°C). • Uses a special built-in switch made from heat-resistant resin. • Silicone rubber is used for rubber parts such as the O-ring, gasket etc. seal, hermeresistant, consistent resistant, consistent resistant, consistent resistant resin.		All models except airtight seal, hermetic seal, heat- resistant, corrosion-proof, and indicator-equipped, ny- lon roller (WLCA2-26N), seal roller models, and res- in rod (WLNJ-2) models	
Corrosion-proof	on-proof WLRP For use in locations subject to corrosive gases and chemicals. For use in locations subject to corrosive gases and chemicals. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For use in location in the statistic gases and solver see weather conditions. Image: For u		All models except overtrav- el (90° operation), fork le- ver lock (WLCA32-41 to - 43), low-temperature, heat- resistant, and indicator- equipped models	
Weather-proof *	WL□-P1	For use in parking lots and other outdoor locations.	 Rubber parts are made from silicone rubber, which has a high-tolerance to deterioration over time and changes in temperature. Rollers are made of stainless steel to improve corrosion resistance. Exposed nuts and screws are made of stainless steel. 	Only basic (WLCA2/CA12/ CL), general-purpose over- travel (WLH2/H12/HL) and high-sensitivity overtravel (WLG2/G12/GL) models (excluding heat-resistant models).

* Weather Resistance, Cold Resistance, and Heat Resistance

Silicon rubber is used to increase resistance to weather, cold, and heat. Silicon rubber, however, can generate silicon gas. (This can occur at room temperature, but the amount of silicon gas generated increases at higher temperatures.) Silicon gas will react as a result of arc energy and form silicon oxide (SiO₂). If silicon oxide accumulates on the contacts, contact interference can occur and can interfere with the device. Before using a Switch, test it under actual application conditions (including the environment and operating frequency) to confirm that no problems will occur in actual.

Selection Guide

With the WL Series, OMRON will combine the switch, Actuator, and wiring method required to build the ideal switch for your application.

The WL Series consists of four basic types: General-purpose, Environment-resistant, Spatter-prevention, and Long-life Switches. WLCA2 Switches can be used for the most common applications.

According to Operating Environment -

	Environment	Key specifications		Models
	Normal	-10°C +80°C Water-resistant to IP67.	WLD WLMD	General-purpose Switches Long-life Switches
Ambient operating temperature	High-temperature	To increase heat resistance, the rubber material (silicon rubber) and the material of the built-in switch have been changed.	WL□-TH	Heat-resistant Switches *1
	Low-temperature	-40°C +40°C To increase resistance to cold, silicon rubber and other measures are used.	WL□-TC	Low-temperature Switches *1
	Outdoors	Rubber parts are made from silicone rubber, which has a high-tolerance to deterioration over time and changes in temperature. Rollers are made of stainless steel to improve corrosion resistance. Exposed nuts and screws are made of stainless steel.	WL□-P1	Weather-proof Switches *1
	Chemicals and oil	Corrosion-proof aluminum diecast has been used for the housing, fluorine rubber has been used for rubber parts, and stainless steel has been used for screws and nuts (except for actuator) to increase resistance to oils, chemicals, and weather.	WL□-RP	Corrosion-proof Switches *1
l	Water drops and mist	Uses an airtight built-in switch.	WL□-55	Airtight Switches *1
		Cables attached. Uses a general-purpose built-in switch. The case cover and conduit opening are molded from epoxy resin to increase the seal. The cover cannot be removed.	WLD-139 Hermetic, M Switches *1	folded-terminal , *2
	Constant water drops and mist	Cables attached. Uses an airtight built-in switch. The case cover and box interior are molded from epoxy resin to increase the seal. The cover cannot be removed. The SC connector can be removed, so it is possible to use flexible conduits for the cable.	WL⊡-RP40 Hermetic, M Switches *1	Iolded-terminal
		Cables attached. Uses an airtight built-in switch. The cover screws, case cover, box interior, and conduit opening are molded from epoxy resin to increase the seal. (The cover cannot be removed.)	WL□-140 Hermetic, M Switches *1	folded-terminal , *2
Uperating environment	Constant water drops or splattering cutting powder	Cables attached. Uses an airtight built-in switch. The cover screws, case cover, box interior, conduit opening, box head, and head screws are molded from epoxy resin to increase the seal. (The cover cannot be removed.) The Head opening is protected from cutting powder. -141: The Head section is molded from epoxy resin; Head direction cannot be changed. -145: The Head section is molded from epoxy resin; Head can be in any of 4 directions.	Switches *1 (Only the W	olded-terminal
	Coolant	Cables attached. Uses an airtight built-in switch. The case cover, box interior, conduit opening, and head screws are molded from epoxy resin to increase the seal. (The cover cannot be removed.) Rubber parts are made from fluorine rubber to increase resistance to coolant.	WL⊡-RP60 Hermetic, N Switches *1	Iolded-terminal
	Spattering from welding	To prevent spatter during welding, a heat-resistant resin is used for the indicator cover and screws and rollers are all made from stainless steel.	WL□-S	Spatter-prevention Switches

*1. Not all functions can be combined with environment-resistant switches. Refer to the applicable models on the previous page.
 *2. Refer to page 25 for information on the construction of Hermetic Switches.


Conditions	Key specifications		Models
Switching standard loads	10 A at 125,250, or 500 VAC 0.8 A at 125 VDC 0.4 A at 250 VDC	WLD-S WLMD	General-purpose Switches Spatter-prevention Switches Long-life Switches
Switching microloads	0.1 A at 125 VAC, resistive load 0.1 A at 30 VDC, resistive load	WL01□ WL01□-S	General-purpose Microload Switches Spatter-prevention Microload Switches
Normal durability	Mechanical: 15 million operation min. (10 million operation min. for overtravel general-purpose or high-sensitivity models or flexible rod models)	WLD WLD-S	General-purpose Switches Spatter-prevention Switches
Long-life	Mechanical: 30 million operation min.	WLM	Long-life Switches


According to Ease of Installation and Maintenance –


	Conditions	Key specifications	Models
Operation indicator	Daily inspections	Switching light-ON between operating/not operating. (Switching not possible for models with molded terminals.) Neon lamp 125 to 250 VAC	WLD-LE General-purpose, Indicator-equipped (Neon Lamp) Switches WLD-LES Spatter-prevention, Indicator-equipped (Neon Lamp) Switches
	and maintenance	Switching light-ON between operating/not operating. (Switching not possible for models with molded terminals.) LED 10 to 115 VAC/DC	WL ^{-LD} General-purpose, Indicator-equipped (LED) Switches WL ^{-LDS} Spatter-prevention, Indicator-equipped (LED) Switches
Wiring specification	Screw tightening	Screw terminals. No ground terminal. Conduit size: G1/2	WL General-purpose Switches WLM Long-life Switches
	and installation	Screw terminals. Ground terminal. Conduit size: 4 sizes	WLD General-purpose Switches
	One-touch connector attachment	Direct-wired connector, 2-conductor. Greatly reduces wiring work. Water-proof to IP67.	WL□-□LDK13 General-purpose, Direct-wired Connector Switches WLM□-LDK13 Long-life, Direct-wired Connector Switches
		Direct-wired connector, 4-conductor. Greatly reduces wiring work. Water-proof to IP67.	WL□-□LDK43 General-purpose, Direct-wired Connector Switches WLM□-LDK43 Long-life, Direct-wired Connector Switches
	Connector attachment in	Pre-wired connector, 2-conductor. Greatly reduces wiring work. Water-proof to IP67.	WLD-DLD-M1J General-purpose, Pre-wired Connector Switches WLD-DS-M1J-1 Spatter-prevention, Pre-wired Connector Switches WLMD-LD-M1J Long-life, Pre-wired Connector Switches
	control and relay boxes	Pre-wired connector, 4-conductor. Greatly reduces wiring work. Water-proof to IP67.	WLD-DLD-DGJO3 General-purpose, Pre-wired Connector Switches WLD-DS-DGJSO3 Spatter-prevention, Pre-wired Connector Switches WLMD-LD-DGJO3 Long-life, Pre-wired Connector Switches


	Detection object		Key specifications		Models
	General	TT (total trav	vel) PT (pretravel)	WLCA2 WLCA2-□S WLMCA2	General-purpose Switches Spatter-prevention Switches Long-life Switches
nylea	Passing dogs	80° 8		WLH2 WLH2-□S WLMH2	General-purpose Switches Spatter-prevention Switches Long-life Switches
operation angles	Passing dogs, high sensitivity	80° 8		WLG2 WLG2-□S WLMG2	General-purpose Switches Spatter-prevention Switches Long-life Switches
Ś	Passing dogs		WLCA2-2 WLCA2-2N	WLCA2-2 WLCA2-2N	General-purpose Switches General-purpose Switches
	High precision	45° 45°	×	WLGCA2 WLGCA2-□S WLMGCA2	General-purpose Switches Spatter-prevention Switches Long-life Switches
l		R38	 Short lever One-Horizontal operation possible (WLCA only) Head mounts in any of 4 directions 	WLL2-LIS	Roller Lever Actuators Roller Lever Actuators Roller Lever Actuators
	Dogs and workpieces (Mounts in any of 4 directions)	R50	 Medium lever One-Horizontal operation possible (WLCA only) Head mounts in any of 4 directions 	VVL	Roller Lever Actuators
	4 directions)	R63	 Long lever One-Horizontal operation possible (WLCA□ only) Head mounts in any of 4 directions 	VVLLZ-0	Roller Lever Actuators
l	Adjustable between dog and lever	R25 to 89	 One-Horizontal operation possible (WLCA only) Head mounts in any of 4 directions 	WLD12	Adjustable Roller Lever Actuators
l	Dogs or workpieces with large deflection	25 to 140	 One-Horizontal operation possible (WLCL only) Head mounts in any of 4 directions 	WL□L	Adjustable Rod Lever Actuators
l		350 to 380	 One-Horizontal operation not possible. Head mounts in any of 4 directions 	WLHAL4	Adjustable Rod Lever Actuator
Actuators		427.5	 One-Horizontal operation not possible. Head mounts in any of 4 directions 	WLHAL5	Rod Spring Lever Actuator
AUIU		@	Head mounts in any of 4 directions	s. WLCA32-41	Fork Lever Lock Actuator
	Round-trip operation of		Head mounts in any of 4 directions	s. WLCA32-42	Fork Lever Lock Actuator
	passing dogs		Head mounts in any of 4 directions	s. WLCA32-43	Fork Lever Lock Actuator
			Head mounts in any of 4 directions		
				WLD	Top Plunger Actuator
			Head mounts in any of 4 directions		Horizontal Plunger Actuator
	Cams or workpieces with vertical movement		Head mounts in any of 4 directions	WLD3	Top-ball Plunger Actuator Horizontal-ball Plunger Actuator
		<u> 1</u> 	Available in sealed models.	WLD2	Top-roller Plunger Actuator
			(WLD28□)	WLD28	Sealed Top-roller Plunger Actuator


Application Examples














Model Number Structure

Model Number Legend (Not all combinations are possible. Ask your OMRON representative for details.)

General-purpose and Environment-resistant Switches

WL _____ (1) (2) (3) (4) (5) (6) (7) (8) (9) (10)

(1) Electrical Rating

Blank	Standard load	
01	Microload	

Note: Dimensions are the same as the standard models.

(3) Environment-resistant Model Specifications

Blank	Standard
RP	Corrosion-proof *1
P1	Weather-proof *1

Note: Dimensions are the same as the standard models.

*1. Refer to page 4 for applicable models.

(4) Built-in Switch Type

	Standard
55	Hermetically sealed *1

Note: Dimensions are the same as the standard models.

*1. Refer to page 4 for applicable models.

(5) Temperature Specifications

 Blank
 Standard: -10°C to +80°C

 TH
 Heat-resistant: +5°C to +120°C *1

 TC
 Low-temperature: -40°C to +40°C *1

 Note:
 Dimensions are the same as the standard

models. *1. Refer to page 4 for applicable models.

(7) Conduit Size, Ground Terminal Specifications *2

Blank G1/2 without ground terminal			
G1 G1/2 with ground terminal			
G	Pg13.5 with ground terminal		
Y	M20 with ground terminal		
TS	1/2-14NPT with ground terminal		
Note: Dimensions are the same as the standard models.			

*2. Models with ground terminals are approved by EN/IEC (CE marking).

(6) Hermetic Model Specifications

Blank No cables or molding

Dialik	No cables of molding
139	General-purpose built-in switch with cables attached and mold- ed conduit opening and cover (cover cannot be removed). *
140	Airtight built-in switch with cables attached and molded conduit open- ing, cover, and box interior cover screws (cover cannot be removed). *
141	Airtight built-in switch with cables attached and molded con- duit opening, cover, head, box interior, cover screws, and head screws (cover cannot be removed, Head direction can- not be changed). The Head opening is created to protect it from cutting powder. *
145	Airtight built-in switch with cables attached and molded conduit opening, cover, box interior, and cover screws (cover cannot be removed, Head can be mounted in any of 4 directions). The Head opening is created to protect it from cutting powder. *
RP40	Airtight built-in switch with cables attached and molded cover and box interior (cover cannot be removed, Head direction can be changed). SC Connector can be removed, so it is possible to use flexible conduits for the cable. *
RP60	Airtight built-in switch with cables attached, fluorine rubber used, and molded conduit opening, cover, and box interior (cover cannot be removed, Head direction cannot be changed). *

* Refer to page 4 for applicable models.

(2) Actuator and Head Specifications

Symbol	Actuator type	Switch without lever
CA2	Roller lever: Standard model R38	WLRCA2
CA2-7	Roller lever: Standard model R50	WLRCA2
CA2-8	Roller lever: Standard model R63	WLRCA2
H2	Roller lever: General-purpose overtravel model, 80°	WLRH2
G2	Roller lever: High-sensitivity overtravel, 80°	WLRG2
CA2-2	Roller lever: Overtravel, 90°	WLRCA2-2
CA2-2N	Roller lever: Overtravel, 90°	WLRCA2-2N
GCA2	Roller lever: High-precision R38	WLRGCA2
CA12	Adjustable roller lever: Standard	WLRCA2
H12	Adjustable roller lever: General-purpose overtravel model, 80°	WLRH2
G12	Adjustable roller lever: High-sensitivity overtravel, 80°	WLRG2
CA12-2	Adjustable roller lever: Overtravel, 90°	WLRCA2-2
CA12-2N	Adjustable roller lever: Overtravel, 90°	WLRCA2-2N
CL	Adjustable rod lever: Standard, 25 to 140 mm	WLRCL
HL	Adjustable rod lever: General-purpose overtravel model, 80°, 25 to 140 mm	WLRH2
HAL4	Adjustable rod lever: General-purpose overtravel model, 80°, 350 to 380 mm	WLRH2
GL	Adjustable rod lever: High-sensitivity overtravel, 80° , 25 to 140 mm	WLRG2
CL-2	Adjustable rod lever: Overtravel, 90°, 25 to 140 mm	WLRCA2-2
CL-2N	Adjustable rod lever: Overtravel, 90°, 25 to 140 mm	WLRCA2-2N
HAL5	Rod spring lever: General-purpose overtravel model, 80°	WLRH2
CA32-41	Fork lever lock: Maintained, WL-5A100	WLRCA32
CA32-42	Fork lever lock: Maintained, WL-5A102	WLRCA32
CA32-43	Fork lever lock: Maintained, WL-5A104	WLRCA32
D	Plunger: Top plunger	—
D2	Plunger: Top-roller plunger	—
D28	Plunger: Sealed top-roller plunger	—
D3	Plunger: Top-ball plunger	—
SD	Plunger: Horizontal plunger	—
SD2	Plunger: Horizontal-roller plunger	—
SD3	Plunger: Horizontal-ball plunger	
NJ	Flexible rod: Coil spring	
NJ-30	Flexible rod: Coil spring, multi-wire	
NJ-2	Flexible rod: Coil spring, resin rod	
NJ-S2	Flexible rod: Steel wire	

(8) Indicator Type

Symbol	Element	Voltage	Leakage current
Blank	No indicator		
LE	Neon lamp	125 to 250 VAC	Approx. 0.6 to 1.9 mA
LD	I FD	115 VAC/VDC	Approx. 0.5 mA
	LED	10 to 24 VAC/VDC	Approx. 0.4 mA

Note: Dimensions are the same for both LE and LD models.

(9) Indicator Wiring

2	NC connection: Light-ON when operating
3	NO connection: Light-ON when not operating
Note: Include the indicator wiring specification only when a (6) hermetic seal and (8) operation indicator have been selected.	

(10) Lever Type

Blank	Standard lever
Α	Double nut lever

General-purpose Switches

Sensor I/O Connector Switches



(1) Electrical Rating

Blank	Standard load
01	Microload

Note: Dimensions are the same as the standard models.

(2) Actuator Type


CA2	Roller lever: Standard model
GCA2	Roller lever: High-precision model
H2	Roller lever: General-purpose overtravel model
G2	Roller-lever: High-sensitivity over- travel model
D2	Top-roller plunger
D28	Sealed top-roller plunger

(3) Built-in Switch Type

Blank	Standard
55	Hermetically sealed

Note: Dimensions are the same as the standard models.

Spatter-prevention Switches



(1) Electrical Rating

Blank	Standard load
01	Microload

Note: Dimensions are the same as the standard models.

(2) Actuator Type

CA2	Roller lever: Standard model
GCA2	Roller lever: High-precision model
H2	Roller lever: General-purpose Overtravel model
G2	Roller lever: High-sensitivity Overtravel model
D28	Sealed top-roller plunger

(3) Built-in Switch Type

Blank	Standard
55	Hermetically sealed
Note: Dimensions are the same as the standard models.	

(4) Indicator Type


LD	LED, AC/DC
LE	Neon lamp

Note: Dimensions are the same for both LE and LD models.

(5) Wiring Specifications


Blank	Screw terminal: G1/2 conduit
	Pre-wired Connector *2 (2-conductor: DC, NO wiring, connector pins No. 3, 4)
-M1GJ-1 *1	Pre-wired Connector *2 (2-conductor: DC, NO wiring, connector pins No. 1, 4)
-DGJS03 *1	Pre-wired Connector *2 (4-conductor: DC)

*1. Models with pre-wired connectors and DC specifications are approved by EN/IEC (CE marking) except for LE Models (Neon Lamp Models). *2. With 0.3-m cable attached.



Pre-wired Connector





(4) Indicator Type LD LED, 10 to 115 VAC/DC

(5) Wiring Specifications

(-,	
K13A	Direct-wired Connector (2-conductor: AC, NO wiring, connector pins No. 3, 4)
K13	Direct-wired Connector (2-conductor: DC, NO wiring, connector pins No. 3, 4)
K43A	Direct-wired Connector (4-conductor: AC)
K43	Direct-wired Connector (4-conductor: DC)
-M1J *	Pre-wired Connector *2 (2-conductor: DC, NO wiring, connector pins No. 3, 4)
-M1GJ *1	Pre-wired Connector *2 (2-conductor: DC, NO wiring, connector pins No. 1, 4)
-M1JB	Pre-wired Connector *2 (2-conductor: DC, NC wiring, connector pins No. 3, 2)
-AGJ03	Pre-wired Connector *2 (4-conductor, AC)
-DGJ03 *1	Pre-wired Connector *2 (4-conductor, DC)
-DK1EJ03 *1	Pre-wired Connector *2 (3-conductor: DC, NO wiring, connector pins No. 2, 3, 4)

*1. Models with pre-wired connectors and DC specifications have EN/IEC approval (CE marking). *2. With 0.3-m cable attached.

Long-life Switches				

	-LD		
(1)	(2)	(3)	

(1) Actuator

CA2	Roller lever: Standard model				
GCA2	Roller lever: High-precision model				
H2	Roller lever: General-purpose overtravel model				
G2	Roller lever: High-sensitivity overtravel model				

(2) Indicator Type

LD	LED, 10 to 115 VAC/DC

(3) Wiring Specifications

Blank	Screw terminal: G1/2 conduit
K13A	Direct-wired Connector: 2-conductor, AC
K13	Direct-wired Connector: 2-conductor, DC
K43A	Direct-wired Connector: 4-conductor, AC
K43	Direct-wired Connector: 4-conductor, DC
-M1J	Pre-wired Connector: 2-conductor, DC *
-AGJ03	Pre-wired Connector: 4-conductor, AC *
-DGJ03	Pre-wired Connector: 4-conductor, DC *

* With 0.3-m cable attached.

Ordering Information

General-purpose Switches

Standard Switches

Note: Models are also available with ground terminals.

Lever

Actuator		Roller lever R38	Roller lever R50	Roller lever R63	
Item			Model	Model	Model
Basic		Standard load	WLCA2	WLCA2-7	WLCA2-8
Dasic		Microload	WL01CA2	WL01CA2-7	WL01CA2-8
	General- purpose	Standard load	WLH2	_	—
		Microload	WL01H2	—	—
	High- sensitivity	Standard load	WLG2	—	_
Overtravel		Microload	WL01G2	—	—
Overtraver		Standard load	WLCA2-2		_
	90°	Microload	WL01CA2-2	—	—
	operation	Standard load	WLCA2-2N		_
		Microload	WL01CA2-2N	_	—
High-preci	icion	Standard load	WLGCA2	_	—
ingn-preci	51011	Microload	WL01GCA2	_	—

Actuator		Adjustable roller lever	Adjustable rod lever 25 to 140mm	Adjustable rod lever 350 to 380mm	Rod spring lever	
Item	Item		Model	Model	Model	Model
Basic		Standard load	WLCA12	WLCL	—	—
Dasic	Basic Microload		WL01CA12	WL01CL	—	_
	General-	Standard load	WLH12	WLHL	WLHAL4	WLHAL5
	purpose	Microload	WL01H12	WL01HL	_	_
	High-	Standard load	WLG12	WLGL	—	—
Overtravel	sensitivity	Microload	WL01G12	WL01GL	—	—
Overtiavei		Standard load	WLCA12-2	WLCL-2	_	_
9	90°	Microload	WL01CA12-2	_	—	—
	operation	Standard load	WLCA12-2N	WLCL-2N	_	—
		Microload	WL01CA12-2N	WL01CL-2N	—	_

Actuator		(9)	Fork lever lock (with WL-5A102 plastic roller lever)	•	Fork lever lock (with WL-5A104 plastic roller lever)
Item		Model	Model	Model	Model
Maintained	Standard load	WLCA32-41	WLCA32-42	WLCA32-43	WLCA32-44
Maintaineu	Microload	WL01CA32-41	—	WL01CA32-43	WL01CA32-44

Plunger

	Actuator	Top plunger 🚔	Top-roller plunger	Top-ball plunger 🛔	Sealed top-roller A plunger
Item		Model	Model	Model	Model
Top plunger	Standard load	WLD	WLD2	WLD3	WLD28
Top plunger	Microload	WL01D	WL01D2	WL01D3	WL01D28

Actuator		Horizontal plunger	Horizontal-roller element	Horizontal-ball
Item		Model	Model	Model
Side plunger Standard load		WLSD	WLSD2	WLSD3
Side pluliger	Microload	WL01SD	WL01SD2	WL01SD3

Flexible Rod

Actuator		Coil spring (spring diameter: 6.5)	Coil spring (spring diameter: 4.8)	Coil spring (resin rod diameter: 8)	Steel wire (wire diameter: 1)
Item		Model	Model	Model	Model
Flexible rod	Standard load	WLNJ	WLNJ-30	WLNJ-2	WLNJ-S2
FIEXIBLE I DU	Microload	WL01NJ	WL01NJ-30	WL01NJ-2	WL01NJ-S2

General-purpose Switches

(Indicator-equipped Switches)

Lever

		Actuator	Roller lever R38	Roller lever R50	Roller lever R63	Adjustable roller lever
Item			Model	Model	Model	Model
Basic		Neon lamp	WLCA2-LE	WLCA2-7LE	WLCA2-8LE	WLCA12-LE
Dasic		LED	WLCA2-LD	WLCA2-7LD	WLCA2-8LD	WLCA12-LD
	General-	Neon lamp	WLH2-LE	_	_	WLH12-LE
	purpose	LED	WLH2-LD	—	—	WLH12-LD
	High- sensitivity	Neon lamp	WLG2-LE	—	—	WLG12-LE
Overtravel		LED	WLG2-LD	—	—	WLG12-LD
Overtraver		Neon lamp	WLCA2-2LE	—	—	WLCA12-2LE
	90°	LED	WLCA2-2LD	—	—	WLCA12-2LD
	operation	Neon lamp	WLCA2-2NLE	—	—	WLCA12-2NLE
		LED	WLCA2-2NLD	—	—	WLCA12-2NLD
High-proc	High-precision Neon lamp		WLGCA2-LE	—	—	—
nigit-preci	151011	LED	WLGCA2-LD	—	—	—

		Actuator	Adjustable rod lever 25 to 140 mm	Adjustable rod lever 350 to 380 mm	Rod spring lever
Item			Model	Model	Model
Basic		Neon lamp	WLCL-LE	—	—
Dasic		LED	WLCL-LD	—	—
	General- purpose	Neon lamp	WLHL-LE	WLHAL4-LE	WLHAL5-LE
		LED	WLHL-LD	WLHAL4-LD	WLHAL5-LD
	High-	Neon lamp	WLGL-LE	_	—
Overtravel	sensitivity	LED	WLGL-LD	—	—
Overtraver		Neon lamp	WLCL-2LE	_	—
	90°	LED	WLCL-2LD	—	—
	operation	Neon lamp	WLCL-2NLE	—	_
		LED	WLCL-2NLD	—	—

	Actuator	Fork lever lock (with WL-5A100 Plastic Roller Lever)	Fork lever lock (with WL-5A102 Plastic Roller Lever)	Fork lever lock (with WL-5A104 Plastic Roller Lever)
Item		Model	Model	Model
Maintained	Neon lamp	WLCA32-41LE	WLCA32-42LE	WLCA32-43LE
	LED	WLCA32-41LD	_	WLCA32-43LD

Plunger

Actuator			Top-roller plunger 🛔	Top-ball plunger Å	Sealed top-roller A glunger
Item		Model	Model	Model	Model
Top plunger	Neon lamp	WLD-LE	WLD2-LE	WLD3-LE	WLD28-LE
Top plunger	LED	WLD-LD	WLD2-LD	WLD3-LD	WLD28-LD

	Actuator	Horizontal plunger	Horizontal-roller en plunger	Horizontal-ball plunger
Item		Model	Model	Model
Side plunger	Neon lamp	WLSD-LE	WLSD2-LE	WLSD3-LE
Side pluliger	LED	WLSD-LD	WLSD2-LD	WLSD3-LD

Flexible Rod

	Actuator	Coil spring (spring diameter: 6.5)	Coil spring (spring diameter: 4.8)	Coil spring (resin rod diameter: 8)	Steel wire (wire diameter: 1)
Item		Model	Model	Model	Model
Flexible rod	Neon lamp	WLNJ-LE	WLNJ-30LE	WLNJ-2LE	WLNJ-S2LE
FIEXIBLE I UU	LED	WLNJ-LD	WLNJ-30LD	WLNJ-2LD	WLNJ-S2LD

General-purpose Switches

(Sensor I/O Connector Switches)

Direct-wired Connectors

	Item						Over	travel	High-precision					
						Basic	General-purpose	High-sensitivity	nigh-precision					
Actuator	Wiring			9	Built-in switch specification	Model	Model	Model	Model					
Roller lever	r <mark>2-con-</mark> ductor DC NG		NO	NO	connector pins	Standard	WLCA2-LDK13	WLH2-LDK13	WLG2-LDK13	WLGCA2-LDK13				
		ductor	ductor	ctor	tor	ductor	tor			No. 3, 4	Airtight seal	WLCA2-55LDK13	WLH2-55LDK13	WLG2-55LDK13
	4-con-	-con-	4-con-		4-con- DC			Standard	WLCA2-LDK43	WLH2-LDK43	WLG2-LDK43	WLGCA2-LDK43		
	ductor				Airtight seal	WLCA2-55LDK43	WLH2-55LDK43	WLG2-55LDK43	WLGCA2-55LDK43					
Top-roller	2-con-						NO	connector pins	Standard	WLD2-LDK13	_	—	_	
plunger	r ductor						r		-	No. 3, 4	Airtight seal	WLD2-55LDK13	_	—
	4-con-	DC	_		Standard	WLD2-LDK43	—	—	—					
	ductor	uctor	DC		ctor			Airtight seal	WLD2-55LDK43			_		

Pre-wired Connectors

					ltem	Basic Over		travel	High-precision												
						Dasic	General-purpose	High-sensitivity	nigh-precision												
Actuator		V	Virin	g	Built-in switch specification	Model	Model	Model	Model												
				connector pins	Standard	WLCA2-LD-M1J	WLH2-LD-M1J	WLG2-LD-M1J	WLGCA2-LD-M1J												
			NO	No. 3, 4	Airtight seal	WLCA2-55LD-M1J	_	—	WLGCA2-55LD-M1J												
	2-con-	DC				NO	NU			UN	connector pins	Standard	WLCA2-LD-M1GJ	WLH2-LD-M1GJ	WLG2-LD-M1GJ	WLGCA2-LD-M1GJ					
Roller lever	ductor						No. 1, 4	Airtight seal	WLCA2-55LD-M1GJ	_	WLG2-55LD-M1GJ	_									
			NC	connector pins	Standard	_	_	WLG2-LD-M1JB	—												
				NO	No. 3, 2	Airtight seal	WLCA2-55LD-M1JB	—	WLG2-55LD-M1JB	WLGCA2-55LD-M1JB											
	4-con-	DC			Standard	WLCA2-LD-DGJ03	WLH2-LD-DGJ03	WLG2-LD-DGJ03	_												
	ductor				Airtight seal	WLCA2-55LD-DGJ03	_	WLG2-55LD-DGJ03	WLGCA2-55LD-DGJ03												
	3-con-	DC		connector pins	Standard	WLCA2-LD-DK1EJ03	—	WLG2-LD-DK1EJ03	_												
	ductor			No. 2, 3, 4	Airtight seal	WLCA2-55LD-DK1EJ03	_	WLG2-55LD-DK1EJ03	_												
				connector pins	Standard	WLD2-LD-M1J	—	—	_												
			con- pc	NO	NO		NO	NO	NO	NO	NO	NO	NO	NO	NO	No. 3, 4	Airtight seal	WLD2-55LD-M1J	—	—	_
	2-con-			DC				connector pins	Standard	WLD2-LD-M1GJ	—	—	_								
Top-roller	ductor			No. 1, 4	Airtight seal	WLD2-55LD-M1GJ	—	—	—												
plunger			NC	connector NC pins	Standard	_	_	_	—												
<u>A</u>			NO	No. 3, 2	Airtight seal	WLD2-55LD-M1JB		_	—												
	4-con-	4-con- ductor DC	nc		4-con-			Standard	WLD2-LD-DGJ03	_	—	-									
	ductor					Airtight seal															
	3-con-	DC		connector pins	Standard	WLD2-LD-DK1EJ03	—	—	—												
	ductor			No. 2, 3, 4	Airtight seal	WLD2-55LD-DK1EJ03	_	_	_												

Environment-resistant Switches

Note: Models are also available with ground terminals.

				Actuator		Roller lever R38			
					Basic	Ove	Overtravel		
					Dasic	General-purpose	High-sensitivity		
ltem					Model	Model	Model		
			No indicat	or	WLCA2-55	WLH2-55	WLG2-55		
Airtight seal Indicator					WLCA2-55LD	WLH2-55LD	WLG2-55LD		
Nec			Neon	WLCA2-55LE	WLH2-55LE	WLG2-55LE			
		-139	No indicat	or	WLCA2-139	WLH2-139	WLG2-139		
			Indicator	NC wiring	WLCA2-139LD2	_	—		
				NO wiring	WLCA2-139LD3	_	WLG2-139LD3		
	Molded		No indicat	or	WLCA2-140	WLH2-140	WLG2-140		
	terminals	-140	Indicator	NC wiring	WLCA2-140LD2	_	WLG2-140LD2		
Hermetic				NO wiring	WLCA2-140LD3	_	WLG2-140LD3		
seal			No indicat	or	WLCA2-141	WLH2-141	WLG2-141		
		-141	Indicator	NC wiring	WLCA2-141LD2	_	WLG2-141LD2		
			Indicator	NO wiring	WLCA2-141LD3	WLH2-141LD3	WLG2-141LD3		
			No indicat	or	WLCA2-RP60	WLH2-RP60	WLG2-RP60		
	Anti-coola	nt	Indicator	NC wiring	WLCA2-RP60LD2	_	WLG2-RP60LD2		
			mulcator	NO wiring	WLCA2-RP60LD3	WLH2-RP60LD3	WLG2-RP60LD3		
Heat-resis	tant				WLCA2-TH	WLH2-TH	WLG2-TH		
Low-tempe	erature		No indicat	or	WLCA2-TC	WLH2-TC	WLG2-TC		
Corrosion	proof				WLCA2-RP	WLH2-RP	WLG2-RP		
Weather-p	roof				WLCA2-P1	WLH2-P1	WLG2-P1		

				Actuator	Roller lever R38			
					Over			
					90 $^{\circ}$ (-2 model)	90° (-2N model)	High-precision	
Item					Model	Model	Model	
No indicator					WLCA2-255	WLCA2-2N55	WLGCA2-55	
Airtight se	al		Indicator	LED	WLCA2-255LD	WLCA2-2N55LD	WLGCA2-55LD	
Neon				Neon	WLCA2-255LE	WLCA2-2N55LE	WLGCA2-55LE	
			No indicat	or	WLCA2-2139	WLCA2-2N139	WLGCA2-139	
		-139	Indicator	NC wiring	WLCA2-2139LD2	_	WLGCA2-139LD2	
			mulcator	NO wiring	WLCA2-2139LD3	_	WLGCA2-139LD3	
			No indicat	or	_	WLCA2-2N140	WLGCA2-140	
	Molded terminals	-140	Indicator	NC wiring	—	_	WLGCA2-140LD2	
Hermetic	terminais			NO wiring	_	_	WLGCA2-140LD3	
seal			No indicat	or	_	_	WLGCA2-141	
		-141	Indicator	NC wiring	—	_	—	
			Indicator	NO wiring	_	—	WLGCA2-141LD3	
			No indicat	or	WLCA2-2RP60	_	WLGCA2-RP60	
	Anti-coola	nt	Indicator	NC wiring	WLCA2-2RP60LD2	_	WLGCA2-RP60LD2	
			mulcator	NO wiring	WLCA2-2RP60LD3	_	WLGCA2-RP60LD3	
Heat-resist	ant				WLCA2-2TH	WLCA2-2NTH	WLGCA2-TH	
Low-tempe	erature		No indicat	or	WLCA2-2TC	WLCA2-2NTC	WLGCA2-TC	
Corrosion	proof				_	_	WLGCA2-RP	

				Actuator		Adjustable roller lever			
					Basic	Ove	Overtravel		
					Dasic	General-purpose	High-sensitivity		
Item					Model	Model	Model		
			No indicat	or	WLCA12-55	—	—		
Airtight se	al		Indicator	LED	WLCA12-55LD	_	-		
			mulcator	Neon	WLCA12-55LE	—	_		
	Maddad	-139		•	WLCA12-139	—	_		
Hermetic	Molded terminals	-140	No indicat	~r	WLCA12-140	—	_		
seal	terminalo	-141		or	WLCA12-141	—	_		
	Anti-coola	nt			WLCA12-RP60	—	_		
Heat-resist	tant				WLCA12-TH	WLH12-TH	WLG12-TH		
Low-tempe	erature		No indicat	or	WLCA12-TC	WLH12-TC	WLG12-TC		
Corrosion-	proof		NU Mulcal	UI III	WLCA12-RP	WLH12-RP	WLG12-RP		
Weather-p	roof				WLCA12-P1	WLH12-P1	WLG12-P1		

	Actuator	Adjustable ro	oller lever	
		Overtravel		
		90° (-2 model)	90° (-2N model)	
Item		Model	Model	
Heat-resistant	No indicator	WLCA12-2TH	WLCA12-2NTH	
Low-temperature		WLCA12-2TC	WLCA12-2NTC	

Actuator				Actuator	Adjustable rod lever 25 to 140 mm			
					Basic	Overtravel		
					Dasic	General-purpose	High-sensitivity	
Item					Model	Model	Model	
			No indicat	or	WLCL-55	_	_	
Airtight se	al		Indicator	LED	WLCL-55LD	_	—	
				Neon				
		-139	No indicator		WLCL-139	—	_	
Hermetic	Molded terminals	-140			WLCL-140			
seal	terminais	-141	- No muicat	or	_	—	_	
	Anti-coola	nt			WLCL-RP60	—	_	
Heat-resist	Heat-resistant				WLCL-TH	WLHL-TH	WLGL-TH	
Low-temperature			~ r	WLCL-TC	WLHL-TC	WLGL-TC		
Corrosion	Corrosion-proof No indicator			U	WLCL-RP	WLHL-RP	WLGL-RP	
Weather-p	roof				WLCL-P1	WLHL-P1	WLGL-P1	

	Actuator	Adjustable rod lev	er 25 to 140 mm
		Ove	rtravel
		90° (-2 model)	90° (-2N model)
Item		Model	Model
Heat-resistant		WLCL-2TH	WLCL-2NTH
Low-temperature	w-temperature No indicator		WLCL-2NTC
Corrosion-proof	1	WLCL-2RP	_

WL/WLM

Actuator			Actuator	Top-roller plunger 🛔	Sealed top-roller plunger	Horizontal plunger	
ltem					Model	Model	Model
			No indicat	or	WLD2-55	WLD28-55	WLSD-55
Airtight sea	Airtight seal		Indicator	LED	WLD2-55LD	WLD28-55LD	WLSD-55LD
			mulcator	Neon	WLD2-55LE	WLD28-55LE	—
Housetia	Molded	-139			WLD2-139	WLD28-139	WLSD-139
Hermetic seal	terminals	-140	No indicat	or	_	WLD28-140	—
	Anti-coola	nt	-		WLD2-RP60	WLD28-RP60	WLSD-RP60
Heat-resist	Heat-resistant		WLD2-TH	WLD28-TH	WLSD-TH		
Low-temperature No indicator		WLD2-TC	—	WLSD-TC			
Corrosion-	proof				WLD2-RP	WLD28-RP	WLSD-RP

Note: The standard cable length for models with airtight seals is 5 m.

				Actuator	Horizontal-roller plunger	Coil spring (spring diameter: 6.5)	Coil spring (resin rod diameter: 8)
Item					Model	Model	Model
	No indicator			or	WLSD2-55	WLNJ-55	WLNJ-255
Airtight sea	al		Indicator	LED	WLSD2-55LD	WLNJ-55LD	WLNJ-255LD
			mulcator	Neon	—	_	_
Hammatia	Molded	-139			WLSD2-139	WLNJ-139	—
Hermetic seal	terminals	-140	No indicat	or	WLSD2-140	WLNJ-140	WLNJ-2140
	Anti-coola	nt	-		WLSD2-RP60	WLNJ-RP60	WLNJ-2RP60
Heat-resistant		WLSD2-TH	WLNJ-TH	_			
Low-temperature No indicator		WLSD2-TC	WLNJ-TC	WLNJ-2TC			
Corrosion-	proof				WLSD2-RP	WLNJ-RP	WLNJ-2RP

Note: The standard cable length for models with airtight seals is 5 m.

Spatter-prevention Switches

		Actuator	Roller le	Sealed top-roller plunger	
			Double nut lever	Allen-head lever	
Item	Item		Model	Model	Model
	Basic		WLCA2-LEAS	WLCA2-LES	WLD28-LES
Neon lamp operation	Overtravel	General-purpose	WLH2-LEAS	WLH2-LES	_
indicator	Overtraver	High-sensitivity	WLG2-LEAS	WLG2-LES	_
	High-precis	ion	_	WLGCA2-LES	—
	Basic		WLCA2-LDAS	WLCA2-LDS	WLD28-LDS
LED	on Overtravel	General-purpose	WLH2-LDAS	WLH2-LDS	—
operation indicator	Overtraver	High-sensitivity	WLG2-LDAS	WLG2-LDS	—
	High-precis	ion		WLGCA2-LDS	—

Note: Ask your OMRON representative about WL01 \Box - \Box S Microload Switches.

Long-life Switches

	Item			LED operati	on indicator *1		
			Basic	Ove	Overtravel		
			Dasic	General-purpose	High-sensitivity	High-precision	
Actuator			Model	Model	Model	Model	
Roller lever, screw			WLMCA2-LD	WLMH2-LD	WLMG2-LD	WLMGCA2-LD	
0		AC	WLMCA2-LDK13A	WLMH2-LDK13A	WLMG2-LDK13A	WLMGCA2-LDK13A	
Roller lever, direct-wired		DC	WLMCA2-LDK13	WLMH2-LDK13	WLMG2-LDK13	WLMGCA2-LDK13	
connector	4-conductor	AC	WLMCA2-LDK43A	WLMH2-LDK43A	WLMG2-LDK43A	WLMGCA2-LDK43A	
		DC	WLMCA2-LDK43	WLMH2-LDK43	WLMG2-LDK43	WLMGCA2-LDK43	
Roller lever, pre-wired connector *2	2-conductor	DC	WLMCA2-LD-M1J	WLMH2-LD-M1J	WLMG2-LD-M1J	WLMGCA2-LD-M1J	
	4-conductor	DC	WLMCA2-LD-DGJ03	WLMH2-LD-DGJ03	WLMG2-LD-DGJ03	_	

*1. The default setting is "light-ON when not operating." Turn the lamp holder by 180° to change the setting to "light-ON when operating". (Ask your OMRON representative about 2-conductor models.)
 *2. With 0.3-m cable attached.

Connecting Cables

Straight Cable

Voltage specification	Number of conductors	Cable length	Model
	2	2 m	XS2F-A421-DB0-F
AC	2	5 m	XS2F-A421-GB0-F
AC	4	2 m	XS2F-A421-D90-F
	4	5 m	XS2F-A421-G90-F
	2	2 m	XS2F-D421-DD0
DC	2	5 m	XS2F-D421-GD0
	4	2 m	XS2F-D421-D80-F
	4	5 m	XS2F-D421-G80-F

Individual Parts Heads

Actuator t	уре	Set model	Head model (with Actuator)
		WLCA2	WL-1H1100
	Ø	WLG2	WL-2H1100
Roller lever		WLH2	WL-2H1100-1 *
		WLCA2-2	WL-3H1100
		WLCA2-2N	WL-6H1100
		WLCA12	WL-1H2100
Adiustable		WLG12	WL-2H2100
Adjustable roller lever		WLH12	WL-2H2100-1 *
		WLCA12-2	WL-3H2100
		WLCA12-2N	WL-6H2100
Adjustable rod lever		WLCL	WL-4H4100
		WLGL	WL-2H4100
		WLCL-2	WL-3H4100
	r—1	WLCL-2N	WL-6H4100

Actuator type	Set model	Head model (with Actuator)
	WLD	WL-7H100
Top plunger	WLD2	WL-7H200
	WLD3	WL-7H300
	WLD28	WL-7H400
llarinantal 88	WLSD	WL-8H100
Horizontal d	WLSD2	WL-8H200
planger	WLSD3	WL-8H300
	WLCA32-41	WL-5H5100
Fork lever	WLCA32-42	WL-5H5102
lock	WLCA32-43	WL-5H5104
0_0	WLCA32-44	WL-5H5104
Π	WLNJ	WL-9H100
Coil spring	WLNJ-30	WL-9H200
	WLNJ-2	WL-9H300
	WLNJ-S2	WL-9H400

* The model number of Heads without levers are same as those of Heads with levers without the numbers at the end.

Example: WL-1H1100 becomes WL-1H without the lever.

However, the WLH2 and WLH12 become WL-2H-1 and the WLGCA2 becomes WL-1H-1 for the Heads without levers. Other Heads are also available. Ask your OMRON representative.


Switches without levers

	Actuator type	Switches without levers
	Basic R38	WLRCA2
	High-precision R38	WLRGCA2
	High-sensitivity overtravel, 80°	WLRG2
Switches for roller levers	General-purpose overtravel, 80°	WLRH2
	Overtravel, 90° operation	WLRCA2-2
	Overtravel, 90° operation	WLRCA2-2N
	Basic	WLRCA2
• · · · · · · · · · · · · · · · · · · ·	High-sensitivity overtravel, 80°	WLRG2
Switches for adjustable roller levers	General-purpose overtravel, 80°	WLRH2
	Overtravel, 90° operation	WLRCA2-2
	Overtravel, 90° operation	WLRCA2-2N
	Basic, 25 to 140 mm	WLRCL
Switches for adjustable	High-sensitivity overtravel, 80°, 25 to 140 mm	WLRG2
rod lever	Overtravel, 90° operation, 25 to 140 mm	WLRCA2-2
	Overtravel, 90° operation, 25 to 140 mm	WLRCA2-2N
Switches for top plungers	_	_
Switches for horizontal plungers	—	—
Switches for fork lever locks	Maintained, WL-5A100 Maintained, WL-5A102 Maintained, WL-5A104	WLRCA32
Switches for coil springs	_	_

Covers with Operation Indicators

Cover	Cover only with indicator
Item	Model
Neon lamp	WL-LE
LED	WL-LD

Note: The default setting is "light-ON when not operating." Turn the lamp holder by 180° to change the setting to "light-ON when operating."



WL Head Replacement

Heads can be replaced within the same model group. They cannot be replaced between different model groups.

Group No.	Set model number	Head model number (with Actuator)
	WLCA2	WL-1H1100
1	WLCA2-7	WL-1H1200
I	WLCA2-8	WL-1H1300
	WLCA12	WL-1H2100
2	WLCL	WL-4H4100 *
	WLH2	WL-2H1100-1
	WLH12	WL-2H2100-1
3	WLHL	WL-2H4100
	WLHAL4	WL-2H4106
	WLHAL5	WL-2H4107
	WLCA2-2N	WL-6H1100
4	WLCA12-2N	WL-6H2100
	WLCL-2N	WL-6H4100
	WLCA2-2	WL-3H1100
5	WLCA12-2	WL-3H2100
	WLCL-2	WL-3H4100
	WLG2	WL-2H1100
6	WLG12	WL-2H2100
	WLGL	WL-2H4100
	WLCA32-41	WL-5H5100
7	WLCA32-42	WL-5H5102
/	WLCA32-43	WL-5H5104
	WLCA32-44	WL-5H5104
	WLD	WL-7H100
8	WLD2	WL-7H200
	WLD3	WL-7H300
9	WLD28	WL-7H400 *
	WLSD	WL-8H100
10	WLSD2	WL-8H200
	WLSD3	WL-8H300
11	WLNJ	WL-9H100
11	WLNJ-30	WL-9H200
12	WLNJ-2	WL-9H300 *
13	WLNJ-S2	WL-9H400 *

* This Heads are special and must be used. Do not use any other Head.

Specifications

Approved Standards

Agency	Standard	File No.	Approved models
UL	UL508	E76675	
CSA	CSA C22.2 No.14	LR45746	
TÜV Rheinland	EN60947-5-1	J50022353, J9950023, J9950959	Contact your OMRON representative for information on approved models.
CCC (CQC)	GB14048.5	2004010305128675	

General-purpose/Weather-proof Switches

Ratings

Standard-load Switches

Item		Non-	induct	ive loa	id (A)	Ind	uctive	e load	(A)
	Rated voltage (V)	Resistive load		Lamp Ioad		Inductive load		Motor Ioad	
Model	(.,	NC	NO	NC	NO	NC	NO	NC	NO
Basic models, overtravel models (except	125 VAC 250 VAC 500 VAC	10 10 10		3 2 1.5	1.5 1 0.8	10 10 3		5 3 1.5	2.5 1.5 0.8
for high- sensitivity models), and high-precision models	8 VDC 14 VDC 30 VDC 125 VDC 250 VDC	10 10 6 0.8 0.4		6 6 4 0.2 0.1	3 3 0.2 0.1	10 10 6 0.8 0.4		6 6 4 0.2 0.1	
High-sensitivity overtravel			5 5	_		—		_	
models	125 VDC 250 VDC		.4 .2			—		-	
Inrush NC (15 cur- rent NO 20	A max. *) A max. *) A max. A max. *)	(AC) and a time cor				ds have a power factor of 0.4 min. me constant of 7 ms max. (DC). has an inrush current of 10			
* For high-sensitivity 4. A overtravel models.				tor loa the st	d has eady-s	tate cu an inru tate cu the m	sh cur Irrent.		
Minimum a	pplicable loa	ad			5 V	DC 16	0 mA		

Approved Standard Ratings UL/CSA

Standard-load Switches: A600, NEMA

Rated	Carry cur-	Current (A)		Volt-amp	eres (VA)
voltage	rent	Make	Break	Make	Break
120 VAC		60	6		
240 VAC	10 A	30	3	7.200	720
480 VAC	10 A	15	1.5	7,200	720
600 VAC		12	1.2		

Microload Switches

0.1 A 125 VAC, 0.1 A 30 VDC

TÜV (EN60947-5-1) (Only models with ground terminals are approved.)

Model	Application category and ratings	Thermal cur- rent (Ithe)	Indicator
WL	AC-15: 2 A/250 V DC-12: 2 A/48 V	10 A	-
WL01	AC-14: 0.1 A/125V DC-12: 0.1 A/48 V	0.5 A	_
WLD-LE	AC-15: 2 A/250 V	10 A	Neon lamp
WL01□-LE	AC-14: 0.1 A/125 V	0.5 A	Neon lamp
WL□-LD	AC-15: 2 A/115 V DC-12: 2 A/48 V	10 A	LED
WL01□-LD	AC-14: 0.1 A/115 V DC-12: 0.1 A/48 V	0.5 A	LED

Note: As an example, AC-15: 2 A/250 V means the following:

Application category	AC-15
Rated operating current (le)	2A
Rated operating voltage (Ue)	250V


Indicator-equipped Switches

Model	Item	Max. rated voltage (V)	Leakage current (mA)	
WL-LE	Neon	125 AC	Approx. 0.6	
Iamp		250 AC	Approx. 1.9	
WIID	LED	115 AC/DC	Approx. 0.5	
WL-LD L		10 to 24 AC/DC	Approx. 0.4	

Microload Switches (Refer to these ratings before using the product.)

Rated voltage (V)	Rated current (A) - Resistive load
AC 125	0.1
DC 30	0.1

Operation in the following ranges will produce optimum performance.



Characteristics

Unaracid	51131103			
Degree of p	rotection	IP67		
Durability	Mechanical	15,000,000 operations min. *2		
*1	Electrical	750,000 operations min. *3		
Operating s	peed	1 mm/s to 1 m/s (in case of WLCA2)		
Operating	Mechanical	120 operations/minute min.		
frequency	Electrical	30 operations/minute min.		
Rated frequ	ency	50/60 Hz		
Insulation resistance		100 MΩ min. (at 500 VDC)		
Contact res	istance	25 m Ω max. (initial value for the built-in switch when tested alone) *6		
Between terminals of the same polarity		1,000 VAC (600 VAC), 50/60 Hz for 1 min		
Dielectric strength	Between current- carrying metal part and ground	2,200 VAC (1,500 VAC), 50/60 Hz for 1 min/Uimp 2.5 kV		
	Between each termi- nal and non-current- carrying metal part	2,200 VAC (1,500 VAC), 50/60 Hz for 1 min/Uimp 2.5 kV		
Rated insula	ation voltage (Ui)	250 V (EN60947-5-1)		
Pollution de environmen	egree (operating it)	3 (EN60947-5-1)		
Short-circuit	protective device (SCPD)	10 A, fuse type gG or gI (IEC60269)		
Conditional	short-circuit current	100 A (EN60947-5-1)		
Convention current (Ithe	al enclosed thermal e)	10 A, 0.5 A (EN60947-5-1)		
Protection a	against electric shock	Class I		
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude *4		
Shock	Destruction	1,000 m/s ² max.		
resistance Malfunction		300 m/s ² max. *4		
Ambient operating temperature		-10°C to +80°C (with no icing) *5		
Ambient operating humidity		35% to 95% RH		
Weight		Approx. 275 g (in case of WLCA2)		
Note: 1. The	above figures are initial	values.		

2. The figures in parentheses for dielectric strength are those for the highsensitivity overtravel models.

*1. The values are calculated at an operating temperature of +5°C to +35°C and an operating humidity of 40% to 70%RH. Contact your OMRON sales representative for more detailed information on other operating environments.
 *2. Durability is 10,000,000 operations min. for general-purpose or high-

sensitivity overtravel models, and for flexible rod models

500,000 operations min. for weather-proof models. *3. Durability is 500,000 operations min. for high-sensitivity models. All

- Durability is 500,000 operations min. for weather-proof models. An microload models are 1,000,000 operations min. 500,000 operations min. for weather-proof models.
 *4. Except flexible rod models. The shock resistance (malfunction) for microload models is 200 m/s² max.
 *5. For low-temperature models this is -40°C to +40°C (with no icing). For heat-resistant models the range is +5°C to +120°C.
 *6. For microload models the contract resistance is 50 mO max. (initial value for the statement of th
- *6. For microload models, the contact resistance is 50 m Ω max. (initial value for built-in switch).

Spatter-prevention Switches

Ratings

Screw terminals

ltem		Non-inductive load (A)				Inductive load (A)			
	Rated voltage (V)	Resistive load		Lamp Ioad		Inductive load		Motor load	
Model		NC NO		NC	NO	NC	NO	NC	NO
WLD-LES	125 VAC 250 VAC	10 10		3 2	1.5 1		0 0	5 3	2.5 1.5
	115 VAC	10		3	1.5	1	0	5	2.5
WL -LDS	12 VDC	10		6	3	1	0	6	6
	24 VDC		6		3		5	4	
	48 VDC	3	3	2	1.5		3		2

Note: 1. The above figures are for steady-state currents. 2. Inductive loads have a power factor of 0.4 min. (AC) and a time constant of 7 ms max. (DC).

3. A lamp load has an inrush current of 10 times the steady-state current.

4. A motor load has an inrush current of 6 times the steady-state current.

Inrush NC		30 A max.	
current	NO	20 A max.	
Operating temperature		-10°C to +80°C (with no icing)	
Operating hu	umidity	35% to 95%RH max.	

Approved Standard Ratings UL/CSA

LE Switches (Neon lamp): A300

Rated	Carry	Curre	nt (A)	Volt-amp	eres (VA)
voltage	current	Make Break		Make	Break
120 VAC	10 A	60	6	7.200	720
240 VAC	IUA	30	3	7,200	720

LD Switches (LED)

Rated voltage	Carry current
115 VAC	10 A
115 VDC	0.8 A

CCC (GB14048.5)

Model	Application category and ratings
WL	AC-15: 2 A/250 V DC-12: 2 A/48 V
WL01	AC-14: 0.1 A/125V DC-12: 0.1 A/48 V
WLD-LE	AC-15: 2 A/250 V
WL01□-LE	AC-14: 0.1 A/125 V
WL-LD	AC-15: 2 A/115 V DC-12: 2 A/48 V
WL01□-LD	AC-14: 0.1 A/115 V DC-12: 0.1 A/48 V

Note: As an example, AC-15: 2 A/250 V means the following:

Application category	AC-15
Rated operating current (le)	
Rated operating voltage (Ue)	250 V

Characteristics

Character	istics					
Degree of p	rotection	IP67				
Durability	Mechanical	15,000,000 operations min. *2				
*1	Electrical	750,000 operations min. *3				
Operating s	peed	1 mm/s to 1 m/s (in case of WLCA2)				
Operating	Mechanical	120 operations/minute min.				
frequency	Electrical	30 operations/minute min.				
Rated frequ	ency	50/60 Hz				
Insulation r	esistance	100 MΩ min. (at 500 VDC)				
Contact res	istance	$25 \text{ m}\Omega$ max. (initial value for the built- in switch when tested alone)				
	Between terminals of the same polarity	1,000 VAC (600 VAC), 50/60 Hz for 1 min				
Dielectric strength	Between current- carrying metal part and ground	2,200 VAC (1,500 VAC), 50/60 Hz for 1 min/Uimp 2.5 kV				
	Between each terminal and non-current- carrying metal part	2,200 VAC (1,500 VAC), 50/60 Hz for 1 min/Uimp 2.5 kV				
Rated insul (Ui)	ation voltage	250 V (EN60947-5-1)				
Pollution de (operating e	egree environment)	3 (EN60947-5-1)				
Short-circui device (SCF	it protective PD)	10 A, fuse type gG or gI (IEC60269)				
Conditional current	short-circuit	100 A (EN60947-5-1)				
Convention thermal cur	al enclosed rent (Ithe)	10 A, 0.5 A (EN60947-5-1)				
Protection a electric sho		Class I				
Vibration resistance Malfunction		10 to 55 Hz, 1.5-mm double amplitude				
Shock Destruction		1,000 m/s ² max.				
resistance Malfunction		300 m/s ² max.				
Ambient op temperature	•	-10°C to +80°C (with no icing)				
Ambient op humidity	erating	35% to 95%RH				
Weight		Approx. 275 g (in case of WLCA2)				

Note: 1. The above figures are initial values. 2. The figures in parentheses for dielectric strength are those for the high-sensitivity overtravel models.

*1. The values are calculated at an operating temperature of +5°C to +35°C and an operating humidity of 40% to 70%RH. Contact your OMRON sales representative for more detailed information on other operating environments.

2. Durability is 10,000,000 operations min. for general-purpose or high-sensitivity overtravel models.

*3. Durability is 500,000 operations min. for high-precision models. All microload models however, are 1,000,000 operations min.

Long-life Switches

Ratings

General Ratings (Refer to these ratings before using the product.) **Screw Terminal Switches**

	Item			Non-i	induct	ive loa	ad (A)	Inductive load (A)			
		vol	ited tage V)	Resi loa			mp ad		luc- Ioad		tor ad
Model		``	•,	NC	NO	NC	NO	NC	NO	NC	NO
Basic mod		115 AC		1	0	3	1.5	1	0	5	2.5
overtravel els, (excep high-sensi models), a high-precis models	t for tivity nd	12 24 48 115	DC	10 6 3 0.8		6 4 2 0.2	3 3 1.5 0.2	10 6 3 0.8		6 4 2 0.2	
High-sens		115	AC		5	—		—		_	
overtravel mod- els 115 D				0.4		—		—		_	
Inrush	NC	30 A max. (15 A max. *)									
current	NO	20 A max. (10 A max. *)									

Characteristics

Degree of pr	otection	IP67				
Degree of pr	Mechanical	30,000,000 operations min.				
Durability *	Electrical	30,000,000 operations min. (10 mA at 24 VDC, resistive load) 750,000 operations min. (10 A at 115 VAC, resistive load), but for high-pre- cision models: 500,000 operations min. (10 A at 115 VAC, resistive load)				
Operating sp	beed	1 mm/s to 1 m/s (in case of WLCA2)				
Operating	Mechanical	120 operations/minute				
frequency	Electrical	30 operations/minute				
Rated frequency		50/60 Hz				
Insulation resistance		100 MΩ min. (at 500 VDC)				
Contact resistance		25 m Ω max. (initial value for the built- in switch when tested alone)				
	Between terminals of the same polarity	1,000 VAC (except connector models)				
Dielectric strength (50/60 Hz for 1 min)	Between current- carrying metal part and ground	2,200 VAC (1,500 V)				
	Between each terminal and non-current- carrying metal part	2,200 VAC (1,500 V)				
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude				
Shock	Destruction	1,000 m/s ² max.				
resistance Malfunction		300 m/s ² max.				
Ambient ope temperature	erating	-10°C to +80°C (with no icing)				
Ambient ope humidity	erating	35% to 95%RH				
Weight		Approx. 275 g (in case of WLCA2)				
Note: The figure	e in narentheses	for dielectric strength, are those for overtravel				

Note: The figures in parentheses for dielectric strength, are those for overtravel (high-sensitivity) or connector models.

* The values are calculated at an operating temperature of +5°C to +35°C, and an operating humidity of 40% to 70%RH. Contact your OMRON sales representative for more detailed information on other operating environments. * For high-sensitivity overtravel models.

Direct-wired Connector and Pre-wired Connector Switches

		Non	-induct	ive load	d (A)	Inductive load (A)			
Model Rated (V)	Resistive load		Lamp load		Inductive load		Motor load		
	NC	NO	NC	NO	NC	NO	NC	NO	
	12 DC	3	3	3	3	3	3	3	3
DC	24 DC	3	3	3	3	3	3	3	3
DC	48 DC	3	3	3	3	3	3	3	3
	115 DC	0.8	0.8	0.2	0.2	0.8	0.8	0.2	0.2
AC	115 AC	3	3	3	1.5	3	3	3	2.5

Note: 1. The above figures are for steady-state currents.


2. Inductive loads have a power factor of 0.4 min. (AC) and a time constant of 7 ms max. (DC).

3. A lamp load has an inrush current of 10 times the steady-state current.

4. A motor load has an inrush current of 6 times the steady-state current.


Engineering Data Electrical Durability: coso= 1

(Operating temperature: +5°C to +35°C, operating humidity: 40% to 70%RH)




Structure

General-purpose Switches: WLCA2



^{*1.} The display for conduit threads has changed from PF½ to G½, according to revisions of JIS B 0202. This is only a change in the display, so the thread size and pitch have not changed. (Conduit threads Pg 13.5 and ½-14NPT are also available.)


*2. By changing the orientation of the operational plunger, any one of the three operational directions (both sides, left, or right) can be selected electrically.




2. Leakage current from indicator circuit may cause load's malfunction. Please check the load's OFF current before use the indicator-equipped switch.

Leakage current non-indicator circuit may cause load's manufiction. Please circuit in load's OFP current before use the indicator equipped switch
 1. Light-ON when operating means that the lamp lights when the Limit Switch contacts (NC) release, or when the actuator rotates or is pushed down.


*2. Light-ON when not operating means the lamp remains lit when the actuator is free, or when the Limit Switch contacts (NO) close when the actuator rotates or is pushed down.



Spatter-prevention Switches: WLCA2-LEAS




Long-life Switches: WLMGCA2-LD




* By changing the direction of the operational plunger, any one of the three operational directions (both sides, left, or right) can be selected.

Contact Forms Screw Terminal Switches




Direct-wired Connector Switches Indicator-equipped (Light-ON when Not Operating) Switches *1




Screw Terminal Switches

Indicator-equipped (Light-ON when Not Operating) Switches *1



Pre-wired Connector Switches Indicator-equipped (Light-ON when Not Operating) Switches *1



Note: Leakage current from indicator circuit may cause load's malfunction. Please check the load's OFF current before use the indicator-equipped switch. *1. Light-ON when not operating means the indicator is lit when the actuator is free and is not light when the Switch contacts (NO) close when the actuator rotates or is pushed down.

*2. The position of the positioning piece is not always the same. If using an L-shaped connector causes problems in application, use a straight connector.

Dimensions and Operating Characteristics


(Unit: mm)

General-purpose Models

Standard Models

Basic

Rotating Lever For all models WL indicates a standard-load model and WL01 indicates a microload model.



Operating characte		WLCA2 WL01CA2	WLCA2-7 WL01CA2-7	WLCA2-8 WL01CA2-8	WLCA12 *1 WL01CA12 *1	WLCL *2 WL01CL *2
Operating force Release force	OF max. RF min.	13.34 N 2.23 N	10.2 N 1.67 N	8.04 N 1.34 N	13.34 N 2.23 N	1.39 N 0.27 N
Pretravel	PT	15° ±5°	15° ±5°	15° ±5°	15° ±5°	15° ±5°
Overtravel	OT min.	30°	30°	30°	30°	30°
Movement Differential	MD max.	12°	12°	12°	12°	12°

*1. The operating characteristics for WLCA12 and WL01CA12 are measured at the lever length of 38 mm.


*2. The operating characteristics for WLCL and WL01CL are measured at the rod length of 140 mm.

Model Operating characteristics	WLCA32-41 to 44 *1 WL01CA32-41 to 44 *1				
Force necessary to reverse the direction of the lever: Max.	11.77 N				
Movement until the lever reverses	50° ±5°				
Movement until switch operation: Min. Movement after switch operation: Max.	55° 35°				
OF and RF for WLCA12, with a lever length of 89 mm.					

	WLCA12, WL01CA12
OF	5.68 N
RF	0.95 N

WL/WLM





Operating Position Total travel Position OP

TTP max

34 ±0.8 mm

29.5 mm

44 ±0.8 mm

39.5 mm

44.5 ±0.8 mm

41 mm

44 ±0.8 mm


39.5 mm

54.2 ±0.8 mm

54.1 ±0.8 mm | 40.6 ±0.8 mm

Basic

Flexible Rod For all models WL indicates a standard-load model and WL01 indicates a microload model.




Note: Unless otherwise indicated, a tolerance of ± 0.4 mm applies to all dimensions.

Model	WLNJ *	WLNJ-30 *	WLNJ-2 *	WLNJ-S2 *	
Operating characteristics	WL01NJ *	WL01NJ-30 *	WL01NJ-2 *	WL01NJ-S2 *	
Operating force OF max.	1.47 N	1.47 N	1.47 N	0.28 N	
Pretravel PT	20 ±10mm	20 ±10mm	40 ±20mm	40 ±20mm	

* These values are taken from the top end of the wire or spring.

Overtravel




	Model		WLG2	WLH12 *1	WLG12 *1		WLGL *2	WLHAL4 *3	WLHAL5
Operating character	istics	WL01H2	WL01G2	WL01H12 *1	WL01G12 *1	WL01HL *1	WL01GL *2	WL01HAL4*3	WL01HAL5
Operating force	OF max.	9.81 N	9.81 N	9.81 N	9.81 N	2.84 N	2.84 N	0.98 N	0.90 N
Release force	RF min.	0.98 N	0.98 N	0.98 N	0.98 N	0.25 N	0.25 N	0.15 N	0.09 N
Pretravel	PT	15° ±5°	10° ^{+2°}	15° ±5°	10° ^{+2°}	15° ±5°	10° ^{+2°}	15° ±5°	15° ±5°
Overtravel	OT min.	55°	65°	55°	65°	55°	65°	55°	55°
Movement Differenti	al MD max.	12°	7 °	12°	7 °	12°	7 °	12°	12°

Note: With WLHAL4, WL01HAL4, WLHAL5, and WL01HAL5, the actuator's tare is large, so depending on the installation direction, they may not be properly reset. Always install so that the actuator is facing downwards.

*1. The operating characteristics of WLH12, WL01HL12, WLG12, and WL01G12 are measured at the lever length of 38 mm.
*2. The operating characteristics of WLHL, WL01HL, WLGL, and WL01GL are measured at the rod length of 140 mm.
*3. The operating characteristics of WLHAL4, and WL01HAL4 are measured at the rod length of 380 mm.

Overtravel



Note: Unless otherwise indicated, a tolerance of ± 0.4 mm applies to all dimensions.


Operating charac		WLCA2-2N WL01CA2-2N		WLCL-2N *2 WL01CL-2N *2	WLCA2-2 WL01CA2-2	WLCA12-2 *1 WL01CA12-2 *1	WLCL-2 *2 WL01CL-2 *2
Operating force	OF max.	9.61 N	9.61 N	2.84 N	8.83 N	8.83 N	2.55 N
Release force	RF min.	1.18 N	1.18 N	0.25 N	0.49 N	0.49 N	0.1 N
Pretravel	PT	20° max.	20° max.	20° max.	25° ±5°	25° ±5°	25° ±5°
Overtravel	OT min.	70°	70°	70°	60°	60°	60°
Movement Differenti	al MD max.	10°	10°	10°	16°	16°	16°

*1. The operating characteristics of WLCA12-2N and WL01CA12-2N are measured at the lever length of 38 mm. *2. The operating characteristics of WLCL-2N and WL01CL-2N are measured at the rod length of 140 mm.

OF and RF for WLCA12-2N and WL01CA12-2N, with a lever length of 89 mm.

High-precision Models

WL are Standard Models and WL01 are Microload Models.



Operating characte	WLGCA2 WL01GCA2	
Operating force	OF max.	13.34 N
Release force	RF min.	1.47 N
Pretravel	PT	5° ^{+2°} 0°
Overtravel	OT min.	40°
Movement Different	tial MD max.	3°

Note: Unless otherwise indicated, a tolerance of ± 0.4 mm applies to all dimensions.

(Sensor I/O Connector Switches)


Direct-wired Connector/Pre-wired Connector Models

Refer to page 17 for the connecting cable.

Roller Lever PlungersWL are Standard Models and WL01 are Microload Models.

Standard Models (WLCA2), High-precision Models (WLGCA2),

Overtravel General-purpose Models (WLH2), Overtravel High-sensitivity Models (WLG2)




Note: 1. Only the dimension of the set position marker plate is different for WLG2 Models.

2. Unless otherwise indicated, a tolerance of ± 0.4 mm applies to all dimensions. 3. The models with operation indicators are shown in the above diagrams.

Operating characte	Actuator ristics	Standard roller lever actuator	High-precision roller lever actuator	Overdrive general- purpose actuator	Overdrive high-sensitivity actuator
Operating force	OF max.	13.34 N	13.34 N	9.81 N	9.81 N
Release force	RF min.	2.23 N	1.47 N	0.98 N	0.98 N
Pretravel	PT	15° ±5°	5° ^{+2°}	15° ±5°	10° ^{+2°}
Overtravel	OT min.	30 °	40°	55°	65°
Movement Differenti	al MD max.	12°	3°	12°	7 °

Top-roller Plunger (WLD2)


Direct-wired Connector Models



Note: 1. Unless otherwise indicated, a tolerance of ±0.4 mm applies to all dimensions. 2. The following diagrams are for a indicator-equipped models.


Actuate Operating characteristics	or Top-roller plunger
Operating force OF max	c. 26.67 N
Release force RF min	. 8.92 N
Pretravel PT max	. 1.7 mm
Overtravel OT min	5.6 mm
Movement Differential MD ma	x. 1 mm
Operating Position OP	44 ±0.8mm
Total travel Position TTP ma	x. 39.5 mm


Indicator-equipped Models




Note: Unless otherwise indicated, a tolerance of $\pm 0.4~\text{mm}$ applies to all dimensions.

Operating characteris	WLCA2-LE/LD WL01CA2-LE/LD	
Operating force	OF max.	13.34 N
Release force	RF min.	2.23 N
Pretravel	PT	15° ±5°
Overtravel	OT min.	30°
Movement Differential	MD max.	12°










Note: Unless otherwise indicated, a tolerance of ± 0.4 mm applies to all dimensions.

		Roller	Seeled Ten reller				
		Basic		el models	High-precision	Sealed Top-roller Plunger	
Operating characteristics		Dasic	General-purpose	High-sensitivity	nigh-precision	rungen	
Operating force	OF max.	13.34 N	9.81 N	9.81 N	13.34 N	16.67 N	
Release force	RF min.	2.23 N	0.98 N	0.98 N	1.47 N	4.41 N	
Pretravel	PT	15° ±5°	15° ±5°	10° ^{+2°}	5° ^{+2°}	1.7 mm max.	
Overtravel	OT min.	30°	55°	65°	40°	5.6 mm	
Movement Differential	MD max.	12°	12°	7 °	3°	1 mm	
Operating Position	OP	_	—	_	—	44 ±0.8 mm	
Total travel Position	TTP max.	—	_	_	_	39.5 mm	

Long-life Models

Rotating Lever Models




Operating characteris	Model tics	WLMCA2-LD Basic models	WLMH2-LD General-purpose overtravel models	WLMG2-LD High-sensitivity overtravel models	WLMGCA2-LD High-precision models
Operating force	OF max.	9.81 N	9.81 N	9.81 N	13.34 N
Release force	RF min.	0.98 N	0.98 N	0.98 N	1.47 N
Pretravel	PT	15° ±5°	15° ±5°	10° ^{+2°}	5° ^{+2°}
Overtravel	OT min.	30 °	55°	65°	40°
Movement Differential	MD max.	12°	12°	7 °	3°

WL/WLM


Actuators (Levers Only)

Lever: Only rotating lever models are illustrated.



Note: Unless otherwise indicated, a tolerance of ±0.4 mm applies to all dimensions.

WL/WLM



Note: 1. Unless otherwise indicated, a tolerance of ± 0.4 mm applies to all dimensions.

2. When using the adjustable roller (rod) lever, make sure that the lever is facing downwards. Use caution, as telegraphing (the Switch turns ON and OFF repeatedly due to inertia) may occur.

Safety Precautions

Refer to Safety Precautions for All Limit Switches.

Precautions for Safe Use

 When a rod or wired-type actuator is used, do not touch the top end of the actuator. Doing so may result in injury. (Applicable models)

WLHAL5 and WL01HAL5 Rod Spring Levers and WLNJ-S2 and WL01NJ-S2 Steel-wire Actuators.

- A short-circuit may cause damage to the Switch, so insert a circuit breaker fuse, of 1.5 to 2 times the rated current, in series with the Switch.
- In order to meet EN approval ratings, use a 10-A fuse that corresponds to IEC60269, either a gl or gG for general-purpose types and spatter-prevention models only.

Precautions for Correct Use

- When wiring terminal screws, use M4 round crimp terminals and tighten screws to the recommended torque. Wiring with bare wires, or incorrect crimp terminals, or not tightening screws to the recommended torque can lead to short-circuits, leakage current, and fire.
- When performing internal wiring there is a chance of short-circuit, leakage current, or fire, so be sure to protect the inside of the Switch from splashes of oil or water, corrosive gases, and cutting powder.
- Using an inappropriate connector or assembling Switches incorrectly (assembly, tightening torque) can result in malfunction, leakage current, or fire, so be sure to read the instruction manual thoroughly beforehand.
- Even when the connector is assembled and set correctly, the end of the cable and the inside of the Switch may come in contact. This can lead to malfunction, leakage current, or fire, so be sure to protect the end of the cable from splashes of oil or water and corrosive gases.

Operating Environment

- Seal material may deteriorate if a Switch is used outdoor or where subject to special cutting oils, solvents, or chemicals. Always appraise performance under actual application conditions and set suitable maintenance and replacement periods.
- Install Switches where they will not be directly subject to cutting chips, dust, or dirt. The Actuator and Switch must also be protected from the accumulation of cutting chips or sludge.




- Constantly subjecting a Switch to vibration or shock can result in wear, which can lead to contact interference with contacts, operation failure, reduced durability, and other problems.
 Excessive vibration or shock can lead to false contact operation or damage. Install Switches in locations not subject to shock and vibration and in orientations that will not produce resonance.
- The Switches have physical contacts. Using them in environments containing silicon gas will result in the formation of silicon oxide (SiO₂) due to arc energy. If silicon oxide accumulates on the contacts, contact interference can occur. If silicon oil, silicon filling agents, silicon cables, or other silicon products are present near the Switch, suppress arcing with contact protective circuits (surge killers) or remove the source of silicon gas.

Using Switches for Micro Loads

Contact faults may occur if a Switch for a general-load is used to switch a micro load circuit. Use switches in the ranges shown in the diagram below. However, even when using micro load models within the operating range shown here, if inrush current occurs when the contact is opened or closed, it may increase contact wear and so decrease durability. Therefore, insert a contact protection circuit where necessary. The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% (λ_{60}).

The equation, λ_{60} = 0.5 \times 10⁻⁶/operations indicates that the estimated malfunction rate is less than 1/2,000,000 operations with a reliability level of 60%.



Built-in Switch

Do not remove or replace the built-in switch. If the position of the builtin switch moves, it can cause reduced performance, and if the insulation sheet moves (separator), the insulation may become ineffective.

Tightening Torque


- If screws are too loose they can lead to an early malfunction of the Switch, so ensure that all screws are tightened using the correct torque.
- In particular, when changing the direction of the Head, make sure that all screws are tightened again to the correct torque. Do not allow foreign objects to fall into the Switch.

1.	No.	Туре	Appropriate tightening torque
3.	1.	Head mounting screw	0.78 to 0.88 N•m
6.	2.	Cover mounting screw	1.18 to 1.37 N·m
4.	3.	Allen-head bolt (for securing the lever)	4.90 to 5.88 N•m
□ □ □ − 2.	4.	Terminal screw	0.59 to 0.78 N·m
5	5.	Connector	1.77 to 2.16 N-m

Installing the Switch

To install the Switch, make a mounting panel, as shown in the following diagram, and tighten screws using the correct torque. Mounting

Mounting




Connectors

Either the easy-to-use Allen-head nut or the SC Connector can be used as connectors. To ensure high-sealing properties, use the SC Connector. Refer to *Limit Switch Connectors* for details on SC Connectors.

Wiring

• Use 1.25-mm² lead wires and M4-insulation covered crimp terminals for wiring.

Crimp Terminal External Dimensions



Wiring Method

• The ground terminal is only installed on models with ground terminals.

Rotating Lever Set Position (General-purpose or Spatterprevention Switches Only)


All rotating lever models, except the fork lever lock models, have a set position marker plate. (See page 23.) After operation, set the indicator needle on the marker plate so that is in the convex section of the bearing.

Operation Set Position (Long-life Switches Only)

For all Long-life Switching, there is a set position marker slit on the rubber cap of the head. After operation, set the slit on the rubber cap so that the fluorescent color on the shaft section can be seen.

Terminal Plate

By using a short circuit plate, as shown in the following diagram, the Switch can be fabricated into a single-polarity double-break switch. When ordering, specify WL Terminal Plate (product code: WL-9662F).



Indicator


Indicator-equipped switch has contacts and indicator in parallel. When contacts are open, leakage current flows through the indicator circuit and may cause load's malfunction.

Please check the load's OFF current before use the indicatorequipped switch.

WL/WLM

Using the Switches

Using the Switches		
Item	Applicable models and Actuators	Details
Changing the Installation Position of the Actuator By loosening the Allen-head bolt on the actuator lever, the position of the actua- tor can be set anywhere within the 360°. With Indicator-equipped Switches, the actuator lever comes in contact with the top of the indicator cover, so use caution when rotating and setting the lever. When the lever only moves forwards and backwards, it will not contact the lamp cover (except for long-life models).	Roller Levers: WLCA2, WL01CA2, WLCA2-2, WL01CA2-2, WLH2,WL01H2, WLG2, WL01G2, WLMCA2 , WLMH2 , WLMG2 , WLMGCA2 Adjustable Roller Levers: WLCA12, WL01CA12, WLCA12-2, WL01CA12-2, WLH12, WL01H12, WLG12, WL01G12, Adjustable Rod Levers: WLCL, WL01CL, WLCL-2, WL01CL-2, WLHL, WL01HL, WLGL, WL01GL	Loosen the M5 × 12 bolt, set the actuator's position and then tighten the bolt again.
Changing the Orientation of the Head By removing the screws in the four cor- ners of the Head, the Head can be set in any of the four directions. Be sure to change the plunger for internal opera- tions at the same time. (The operation- al plunger does not need to be changed on general-purpose and high- sensitivity overtravel models.) The roll- er plunger can be set in either two po- sitions at 90°. WLCA2-2N and WL01CA2-2N can be set only in either the forward or back- ward direction.	Roller Levers: WLCA , WL01CA, WLCA-2, WL01CA-2, WLGCA, WLH, WL01H, WLG, WL01G, WLMCA2, WLMH2, WLMG2, WLMGCA2 Adjustable Rod Levers: WLCL, WL01CL, WLCL-2, WL01CL-2 Horizontal Plungers: WLSD, WL01SD Top-roller Plungers: WLD2, WL01D2 Sealed Top-roller Plungers: WLD28, WL01D28 Does not include -RP60 Series or -141 Series.	Head Loosen the screws.
Changing the Operating Direction By removing the Head on models which can operate on one-side only, and then changing the direction of the operational plunger, one of three oper- ating directions can be selected. For overtravel 90° operation models, one of three operating directions can be se- lected by loosening the rubber holder using either a coin or a flat-blade screwdriver and changing the direction of the internal rubber section. The tightening torque for the screws on the Head is 0.78 to 0.88 N•m.	Roller Levers: WLCA2, WL01CA2, WLGCA2, WLMGCA2□ Adjustable Roller Levers: WLCA12, WL01CA12 Adjustable Rod Levers: WLCL, WL01CL Overtravel Models: WLCA□-2N, WL01CA□-2N	One-side Operation for General-purpose and High-precision Switches The output of the Switch will be changed, regardless of which direction the lever is pushed. The output of the Switch will only be changed when the lever is pushed in one direction. Operating Operating Not operating Operating Operating Operation in both directions Counterclockwise operation Cam Direction Changing Procedure for Overtravel, 90° Operation Switches Loosen the cam holder with a coin or screwdriver. Take out the cam from the Switch. Change the direction of the carm as coin or screwdriver. Take out the carm from the Switch. Change the direction of the carm as coin or screwdriver. Take out the carm from the Switch. Change the direction of the carm as coin or screwdriver. Take out the carm from the Switch. Change the direction of the carm as required by your intended operation and then reinstall the carn. Change the direction of the carm as required by your intended operation and then reinstall the carn. Change the direction of the carm as required by your intended operation and then reinstall the carn. Change the direction of the carm as required by your intended operation and then reinstall the carn. Change the direction of the carm as required by your intended operation and then reinstall the carn. Change the direction of the carm as required by your intended operation and then reinstall the carn. Change the direction of the carm as counterclockwise operation on both sides Operation on one side Operation on one side



Operation of Fork Lever Locks

The fork lever lock is configured so that the dog pushes the lever to reverse the output and this reversed state is maintained even after the dog continues on. If the dog then pushes the lever from the opposite direction, the lever will return to its original position.


Example





NC terminal: ON

NO terminal: ON



NO terminal: ON

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company