E3Z

CSM_E3Z_DS_E_18_1

The Standard for Photoelectric Sensors with a Secure Track Record of One Million Sold Yearly.

- Long sensing distance of 30 m for Through-beam Models, 4 m for Retro-reflective Models, and 1 m for Diffuse-reflective Models.
- \bullet Mechanical axis and optical axis offset of less than $\pm 2.5^\circ$ simplifies optical axis adjustment.
- High stability with unique algorithm that prevents interference of external light.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.




Be sure to read *Safety Precautions* on page 13.

Features

Industry's Top-level Sensing Distance with Built-in Amplifier

A separately sold filter is available to prevent mutual interference for Through-beam Models with red lights sources and a sensing distance of 10 m. Reflective Models include functionality to prevent mutual interference (up to 2 sensors).

Long-distance, Through-beam Sensors with a detection distance of 30 m (response time: 2 ms) are also available.




Low-temperature Operation for Applications in Cold-storage Warehouses

A wider ambient operating range from -40 to 55°C (main models with connectors). We also provide Sensor I/O Connectors with PUR Cables for high resistance to cold environments.

Improved Matching of Optical Axis and Mechanical Axis for Through-beam Models and Retro-reflective Models

The offset between the optical axis and the mechanical axis is kept within $\pm 2.5^{\circ}$, so the optical axis can be accurately set simply by mounting the Sensor according to the mechanical axis.



-30 m

Sensor Protection against Incorrect Wiring

The Sensor includes output reverse polarity protection. (A diode to protect against reverse polarity is added to the output line.)


Through-beam Model receivers and Reflective Models (except the E3Z-LS) Operation Operation Operation Orange) Photoelectric Sensor main circuit O V

Protection for NPN output models

Complete Compliance with the EU's RoHS Directive

Lead, mercury, cadmium hexachrome, polybrominated biphenyl (PBB), and polybrominated diphenyl ether (PBDE) have all been eliminated. Also, burnable polyethylene packaging has been used.





OMRON 1

Ordering Information

Sensors [Refer to I	Dimensions on pag		R	Red light Infrared light		
Sensing method	Appearance	Connection method	Sensing d	istance		odel
	71000101100	Commodation modatou	Contenting to		NPN output	PNP output
		Pre-wired (2 m)		(15 m	E3Z-T61 2M *4 *5 Emitter E3Z-T61-L 2M Receiver E3Z-T61-D 2M	E3Z-T81 2M *4 *5 Emitter E3Z-T81-L 2M Receiver E3Z-T81-D 2M
		Standard M8 connector		15 m	E3Z-T66 Emitter E3Z-T66-L Receiver E3Z-T66-D	E3Z-T86 Emitter E3Z-T86-L Receiver E3Z-T86-D
Through-beam (Emitter + Receiver) *3		Pre-wired (2 m)		140	E3Z-T61A 2M *4 Emitter E3Z-T61-A-L 2M Receiver E3Z-T61-A-D 2M	E3Z-T81A 2M *4 Emitter E3Z-T81-A-L 2M Receiver E3Z-T81-A-D 2M
		Standard M8 connector		10 m	E3Z-T66A Emitter E3Z-T66-A-L Receiver E3Z-T66-A-D	E3Z-T86A Emitter E3Z-T86-A-L Receiver E3Z-T86-A-D
		Pre-wired (2 m)		(20	E3Z-T62 2M *4 Emitter E3Z-T62-L 2M Receiver E3Z-T62-D 2M	E3Z-T82 2M Emitter E3Z-T82-L 2M Receiver E3Z-T82-D 2M
		Standard M8 connector		30 m	E3Z-T67 Emitter E3Z-T67-L Receiver E3Z-T67-D	E3Z-T87 Emitter E3Z-T87-L Receiver E3Z-T87-D
Retro-reflective with		Pre-wired (2 m)	4 1	m *2	E3Z-R61 2M *4 *5	E3Z-R81 2M *4 *5
MSR function	*1	Standard M8 connector		0 mm)	E3Z-R66	E3Z-R86
		Pre-wired (2 m)	5 to 100 mm		E3Z-D61 2M *4	E3Z-D81 2M *4 *5
		Standard M8 connector	(wide view)		E3Z-D66	E3Z-D86
Diffuse-reflective		Pre-wired (2 m)			E3Z-D62 2M *4 *5	E3Z-D82 2M *4 *5
Dilluse-reliective		Standard M8 connector	1 m		E3Z-D67	E3Z-D87
	•	Pre-wired (2 m)	90±30 mm		E3Z-L61 2M *4 *5	E3Z-L81 2M *4 *5
		Standard M8 connector	(narrow bea	am)	E3Z-L66	E3Z-L86
		Pre-wired (2 m)	20 to 40 mm (BGS min 20 to 200 mm (BGS min	0,	E3Z-LS61 2M *4	E3Z-LS81 2M *4
Distance-settable Refer to E3Z-LS .	<u></u>	Standard M8 Connector	40 min. Incident threshold	,	E3Z-LS66	E3Z-LS86
		Pre-wired (2 m)	2 to 20 mm (BG	0,	E3Z-LS63 2M	E3Z-LS83 2M *5
		Standard M8 connector	2 to 80 mm (BGS	3 max setting	E3Z-LS68	E3Z-LS88
	1 axis	Pre-wired (2 m)			E3Z-G61 2M *4 *5	E3Z-G81 2M *4 *5
Slit-type Through- beam	2 axes	(2)	25 mm		E3Z-G62 2M *4	E3Z-G82 2M *4
Refer to E3Z-G .	1 axis	Pre-wired M8 connector	25 11111		E3Z-G61-M3J	E3Z-G81-M3J
	2 axes	T TO WING ING CONTINUES.			E3Z-G62-M3J	E3Z-G82-M3J
Limited-reflective for	□	Pre-wired (2 m)	30±20 mm		E3Z-L63 2M	E3Z-L83 2M
transparent glasses		Standard M8 connector	00120 111111		E3Z-L68	E3Z-J88
		Pre-wired (2 m)		*2	E3Z-B61 2M	E3Z-B81 2M *4
Retro-reflective with- out MSR function for		Standard M8 connector	500 mm (8	,	E3Z-B66	E3Z-B86
clear, plastic bottles		Pre-wired (2 m)	0.5	*2 n (500 mm)	E3Z-B62 2M *4	E3Z-B82 2M *4
		Standard M8 connector	21	(300 11111)	E3Z-B67	E3Z-B87

^{*1.} The Reflector is sold separately. Select the Reflector model most suited to the application.

*2. The sensing distance specified is possible when the E39-R15 is used. Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

*3. Through-beam Sensors are normally sold in sets that include both the Emitter and Receiver.

*4. M12 Standard Pre-wired Connector Models are also available.

When ordering, add "-M1J 0.3M" to the end of the model number (e.g., E3Z-T61-M1J 0.3M).

The cable is 0.3 m long.

^{*5.} M12 Pre-wired Smartclick Connector Models are also available.
*5. M12 Pre-wired Smartclick Connector Models are also available.
When ordering, add "-M1TJ 0.3M" to the end of the model number (e.g., E3Z-T61-M1TJ 0.3M).
The cable is 0.3 m long.

Oil-resistive Sensors (Refer to Dimensions on na

Oil-resistive Sens	OIS [Refer to Di	Red light Infrared light				
Sensing method	Appearance	Connection method	Sensing distance		del	
censing metrica	Appearance	Connection metrica	Cerising distance	NPN output	PNP output	
Through-beam (Emitter + Receiver) *3	<u> </u>	Pre-wired (2 m)		E3Z-T61K 2M *4 Emitter E3Z-T61K-L 2M Receiver E3Z-T61K-D 2M	E3Z-T81K 2M *4 Emitter E3Z-T81K-L 2M Receiver E3Z-T81K-D 2M	
		Pre-wired M8 connector	\$\frac{\sqrt{15 m}}{\sqrt{15 m}}	E3Z-T61 K-M3J 0.3M Emitter E3Z-T61K-L-M3J 2M Receiver E3Z-T61K-D-M3J 2M	E3Z-T81K-M3J 0.3M Emitter E3Z-T81K-L-M3J 2M Receiver E3Z-T81K-D-M3J 2M	
Retro-reflective with	↓ ★1	Pre-wired (2 m)	*2	E3Z-R61K 2M *4	E3Z-R81K 2M	
MSR function		Pre-wired M8 connector	3 m (150 mm)	E3Z-R61K-M3J 0.3M	E3Z-R81K-M3J 0.3M	
		Pre-wired (2 m)	[E3Z-D61K 2M *4	E3Z-D81K 2M	
Diffuse-reflective	□ +	Pre-wired M8 connector	5 to 100 mm (wide view)	E3Z-D61K-M3J 0.3M		
Dilluse-reliective		Pre-wired (2 m)		E3Z-D62K 2M *4	E3Z-D82K 2M	
		Pre-wired M8 connector	1 m	E3Z-D62K-M3J 0.3M	E3Z-D82K-M3J 0.3M	

^{*1.} The Reflector is sold separately. Select the Reflector model most suited to the application.

Accessories (Order Separately)

Slit (A Slit is not provided with Through-beam Sensors) Order a Slit separately if required. [Refer to Dimensions on page 16.]

` '		,	· · · · ·			
Slit width		distance	Minimum detectable object	Model	Contents	
	E3Z-T□□	E3Z-T□□A	(Reference value)			
0.5-mm dia.	50 mm	35 mm	0.2-mm dia.	E39-S65A		
1-mm dia.	200 mm	150 mm	0.4-mm dia.	E39-S65B	One set	
2-mm dia.	800 mm	550 mm	0.7-mm dia.	E39-S65C	(contains Slits for	
0.5 × 10 mm	1 m	700 mm	0.2-mm dia.	E39-S65D	both the Emitter and	
1 × 10 mm	2.2 m	1.5 m	0.5-mm dia.	E39-S65E	Receiver)	
2 × 10 mm	5 m	3.5 m	0.8-mm dia.	E39-S65F		

Reflectors (Reflector required for Retroreflective Sensors) A Reflector is not provided with the Sensor. Be sure to order a Reflector separately. [Refer to Dimensions on E39-L/E39-S/E39-R]

		S						
	E37	Z-R	E3Z-R□K	E3Z-R□K E3Z-B□1/-B□6 E3Z-B□2/-B□7				
Name	Rated value (sensing distance of 15 m)	Reference value (sensing distance of 10 m)	Rated value	Rated value	Rated value	Model	Quantity	Remarks
	3 m (100 mm)		2 m (100 mm)			E39-R1	1	
	4 m (100 mm)		3 m (150 mm)	500 mm (80 mm)	2 m (500 mm)	E39-R1S	1	1
Reflector		5 m (100 mm)				E39-R2	1	Retro-reflective
		2.5 m (100 mm)				E39-R9	1	models are not
		3.5 m(100 mm)				E39-R10	1	provided with
Fog Preventive Coating		3 m (100 mm)		500 mm (80 mm)	2 m (500 mm)	E39-R1K	1	Reflectors. • The MSR function
Small Reflector		1.5 m (50 mm)				E39-R3	1	is enabled.
		700 mm (150 mm)				E39-RS1	1	
Tape Reflector		1.1 m (150 mm)				E39-RS2	1	
		1.4 m (150 mm)				E39-RS3	1	

Note: 1. If you use the Reflector at any distance other than the rated distance, make sure that the stability indicator lights properly when you install the Sensor.

2. Refer to Reflectors on E39-L/E39-S/E39-R for details.

* Values in parentheses indicates the minimum required distance between the Sensor and Reflector.

Mutual Interference Protection Filter A Filter is not provided with the Sensor (for the through-beam E3Z-T□□A). Order a Filter separately if required.

	indicate interest and in the provided man are defined in the degree beam 202 in 201, or defined an interest and in the degree and in the d							
Sensing distance	Appearance/Dimensions	Model	Quantity	Remarks				
3 m	10.8 17.4 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	E39-E11	Two sets each for the Emitter and Receiver (total of four pieces)	Can be used with the E3Z-T A Through- beam models. The arrow indicates the direc- tion of polarized light. Mutual interference can be prevented by altering the direction of polarized light from or to adjacent Emitters and Receivers.				

Note: The polarization directions of the Filters are offset by 90° to prevent interference. When you install the Emitter and Receiver, install them at the same angle to maintain this offset.

^{*2.} The sensing distance specified is possible when the E39-R1S is used. Values in parentheses indicate the minimum required distance between the Sensor and Reflector.
*3. Through-beam Sensors are normally sold in sets that include both the Emitter and Receiver.

^{*4.} M12 Standard Pre-wired Connector Models are also available. When ordering, add "-M1J 0.3M" to the end of the model number (e.g., E3Z-T61-M1J 0.3M). The cable is 0.3 m long.

Mounting Brackets A Mounting Bracket is not enclosed with the Sensor. Order a Mounting Bracket separately if required. [Refer to Dimensions on E39-L/E39-S/E39-R]

Appearance	Model (material)	Quantity	Remarks	Appearance	Model (material)	Quantity	Remarks
	E39-L153 (SUS304) *1	1	Maritimo		E39-L98 (SUS304) *2	1	Metal Protective Cover Bracket
5	E39-L104 (SUS304) *1	1	Mounting Brackets	***	E39-L150 (SUS304)	1	(Sensor adjuster)
io .	E39-L43 (SUS304) *2	1	Horizontal Mounting Brackets		E39-L151		Easily mounted to the aluminum frame rails of conveyors and easily adjusted.
	E39-L142 (SUS304) *2	1	Horizontal Protective Cover Bracket		(SUS304)	1	For left to right adjust- ment
-	E39-L44 (SUS304)	1	Rear Mounting Bracket		E39-L144 (SUS304) *2	1	Compact Protective Cover Bracket (For E3Z only)

Sensor I/O Connectors (Sockets on One Cable End)

(Models for Connectors and Pre-wired Connectors: A Connector is not provided with the Sensor. Be sure to order a Connector separately.) [Refer to Dimensions for XS3.]

Size	Cable	Appearance		Cable type		Model
		Otroinlet *0		2 m		XS3F-M421-402-A
M8 *1	Ctondord	Straight *3	O Mirano	5 m	4-wire	XS3F-M421-405-A
IVIO I	Standard	L-shaped *3 *4		2 m	4-wire	XS3F-M422-402-A
				5 m		XS3F-M422-405-A
		Straight *3		2 m	4-wire	XS3F-M421-402-L
PUR (Polyure-thane) cable *2				5 m		XS3F-M421-405-L
	thane) cable *2	L-shaped *3 *4		2 m		XS3F-M422-402-L
		L onapou o 4		5 m		XS3F-M422-405-L

Note: When using Through-beam models, order one connector for the Receiver and one for the Emitter.

Note: 1. When using Through-beam models, order one bracket for the Receiver and one for the Emitter.

2. Refer to *Mounting Brackets* on *E39-L/E39-S/E39-R* for details.

*1. Cannot be used for Standard Connector models with mounting surface on the bottom. In that case, use Pre-wired Connector models.

^{*2.} Cannot be used for Standard Connector models.

^{*1.} Refer to Introduction to Sensor I/O Connectors/Sensor Controllers for details.

^{*2.} The Sensor can be used in low-temperature environments (-25°C to -40°C). Do not use the Sensor in locations that are subject to oil.

^{*3.} The connector will not rotate after connecting.

^{*4.} The cable is fixed at an angle of 180° from the sensor emitter/receiver surface.

Ratings and Specifications

			Sensing method	-	Through-beam		Retro-reflective w	-	Diffuse-r	eflective	(Narrow-
	Г					ı	MSR function	1			beam Models)
		NPN out-	Pre-wired	E3Z-T61	E3Z-T62	E3Z-T61A	E3Z-R61		E3Z-D61	E3Z-D62	E3Z-L61
Мо	odel	put	Connector (M8)	E3Z-T66	E3Z-T67	E3Z-T66A	E3Z-R66		E3Z-D66	E3Z-D67	E3Z-L66
		PNP out-	Pre-wired	E3Z-T81	E3Z-T82	E3Z-T81A	E3Z-R81		E3Z-D81	E3Z-D82	E3Z-L81
Item		put	Connector (M8)	E3Z-T86	E3Z-T87	E3Z-T86A	E3Z-R86		E3Z-D86	E3Z-D87	E3Z-L86
Sensing dist	Sensing distance			15 m	30 m	10 m	4 m (100 mm) *1 (when using E39-R 3 m (100 mm) *1 (when using E39-R	115)	100 mm (white paper: 100 × 100 mm)	1 m (white paper: 300 × 300 mm)	90 + 30 mm (white paper, 100 x 100 mm)
Spot diameter (reference value)			ce value)								(2.5 dia. and sensing dis- tance of 90 mm)
Standard se	nsing	obje	ct	Opaque: 12-m	nm dia. min.		Opaque: 75-mm dia.	min.			*
Minimum de (reference va		ble ol	oject					·			0.1 mm (cop- per wire)
Differential t	travel							2	20% max. of sett	ing distance	Refer to Engi- neering data on page 8.
Directional angle				Both emitter a	nd receiver: 3	to 15°	2 to 10°				
Light source	e (wa	velenç	gth)	Infrared LED	(870 nm)	Red LED (660 nm)	Red LED (660 nm)) 1	Infrared LED (86	0 nm)	Red LED (650 nm)
Current con:	sump	tion		35 mA max. (I er: 20 mA ma	Emitter: 15 mA x.)	max., Receiv-	30 mA max.	mA max.			
Protection c	ircuit	s		Output short-o	er supply polar circuit protectio polarity protec	n, and Re-	Reversed power supply polarity protection, Output short-circuit protection Mutual interference prevention, and Reversed output polarity protection				
Response ti	me			Operate or reset: Operate or reset: 1 ms max. 2 ms max.							
Degree of pr	rotect	ion		IEC, IP67							
Connection	meth	od		Pre-wired cable (standard length: 2 m and 0.5 m), Connector (M8)							
Weight		Pre-w	vired cable (2 m)	Approx. 120 g Approx. 65 g							
(packedstate	e)	Conn	ector	Approx. 30 g Approx. 20 g							
Material		Case		PBT (polybutylene terephthalate)			Mathematic vesion Medified polygodete				
		Lens		Modified polya	arylate		Methacrylic resin Modified polyarylate				
		Se	ensing method		Retro-	reflective fo	r clear, plastic bottles (without MSR function)				
	Mod	461	NPN output	E3Z	-B61	E32	Z-B66		E3Z-B62	E	BZ-B67
Item	IVIO	JEI	PNP output	E3Z	-B81	E32	Z-B86		E3Z-B82	E;	BZ-B87
Sensing di	istan	се		500 mm (80	mm) *1 (usir	g E39-R1S)	2 1	m (50	0 mm) *1 *2 (ι	sing E39-R1S)
Standard s	sensi	ng o	bject	500-ml (65-r	nm dia.) tran	sparent roun	d plastic bottles				
Light source	ce (w	avel	ength)	Red LED (660 nm)							
Current co	nsur	nptic	on	30 mA max.							
Protection	circ	uits			ower supply p	, ,	tion, Output short-	-circui	t protection, M	utual interferer	ice prevention,
Response	time			Operate or r	eset: 1 ms m	ax.					
Degree of protection		IEC, IP67									
Connection method			Pre-wired cal	•	Connector			ed cable (standa 2 m and 0.5 m)	Connecto	r (M8, 4 pins)	
	Pre-	wired	cable (2 m)	Approx. 65 g							
(packed state)	Stan	dard	Connector	Approx. 20 g)						
Material	Case	;		PBT (polybu	tylene tereph	thalate)					
	Lens	;		Modified pol	yarylate						

^{*1.} Values in parentheses indicate the minimum required distances between the Sensors and Reflectors. *2. Plastic bottles must pass with the minimum clearance of 500 mm.

	Sensing method	Transparent glass Limited-reflecti	Transparent glass Limited-reflective (for transparent object detection)						
Model	NPN output	E3Z-L63	E3Z-L68						
Item	PNP output	E3Z-L83	E3Z-L88						
Sensing distanc	е	30±20 mm (transparent glasses 100 × 100 mm)							
Spot diameter (r	eference value)	2-mm dia. min. (at sensing distance of 30 mm)							
Minimum detect (reference value	•	0.1 mm dia. (copper wire)							
Light source (wa	avelength)	Red LED (660 nm)							
Current consum	ption	30 mA max.							
Protection circu	its	Power supply reverse polarity protection, Output short-circ Reverse output polarity protection	Power supply reverse polarity protection, Output short-circuit protection, Mutual interference prevention, Reverse output polarity protection						
Response time		Operate or reset: 1 ms max.							
Degree of protect	ction	IEC, IP67							
Connection met	hod	Pre-wired (standard length: 2 m)	M8 connector						
Weight	Pre-wired cable (2 m)	Approx. 65 g							
(packed state)	Standard Connector	Approx. 20 g							
Material	Case	PBT (polybutylene terephthalate)							
wateriai	Lens	Modified polyarylate							

Oil-resistant

Sensing method			Sensing method	Through-beam	Retro-reflective	Diffuse	reflective	
	•	NPN	Pre-wired Models	E3Z-T61K	E3Z-R61K	E3Z-D61K	E3Z-D62K	
	Model	out- put	M8 Pre-wired connector	E3Z-T61K-M3J	E3Z-R61K-M3J	E3Z-D61K-M3J	E3Z-D62K-M3J	
	Model	PNP	Pre-wired Models	E3Z-T81K	E3Z-R81K	E3Z-D81K	E3Z-D82K	
Item		out- put	M8 Pre-wired connector	E3Z-T81K-M3J	E3Z-R81K-M3J	E3Z-D81K-M3J	E3Z-D82K-M3J	
Sensing distance		15 m	3 m (150 mm) * (when using E39-R1S) 2 m (100 mm) * (when using E39-R1)	100 mm (white paper: 100 × 100 mm)	1 m (white paper: 300 × 300 mm)			
Standard	l sensin	ıg obje	ect	Opaque: 12-mm dia. min.	Opaque: 75-mm dia. min.			
Differenti	ial trave	el		-		20% max. of setting dista	nce	
Direction	nal angl	е		Both emitter and receiver: 3 to 15°	2 to 10°			
Light sou	urce (wa	avelen	gth)	Infrared LED (870 nm)	Red LED (660 nm)	Infrared LED (860 nm)		
Current o	consum	ption		35 mA max. (Emitter: 15 mA max., Receiver: 20 mA max.)	30 mA max.			
Protectio	on circu	its		Reversed power supply polarity protection, Output short-circuit protection, and Reversed output po- larity protection	Reversed power supply polarity protection, Output short-circuit protection, Mutual terference prevention, and Reversed output polarity protection			
Respons	e time			Operate or reset: 1 ms max.				
Degree o	f prote	ction		IP67 (IEC), Oil resistant models: IP67 (IEC) (in-house standards: oilproof), excluding cables and connectors				
Connecti	ion met	hod		Pre-wired cable (standard I	ength: 2 m), M8 Pre-wired C	onnector		
Weight Pre-wired cable (2 m)		Approx. 120 g	Approx. 65 g					
state) Connector (M8, 4 pins)		M8, 4 pins)	Approx. 50 g	Approx. 30 g				
Material	Case			PBT (polybutylene terephth	nalate)			
Material Lens		Modified polyarylate	Methacrylic resin Modified polyarylate					

^{*} Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

Common

Power supply voltage	12 to 24 VDC±10%, ripple (p-p): 10% max.
Control output	Load power supply voltage: 26.4 VDC max., Load current: 100 mA max. Residual voltage: Load current of less than 10 mA: 1 V max. Load current of 10 to 100 mA: 2 V max. Open collector output (NPN/PNP depending on model) Light-ON/Dark-ON selectable
Sensitivity adjustment	One-turn adjuster
Ambient illumination (Receiver side)	Incandescent lamp: 3,000 lx max. Sunlight: 10,000 lx max.
Ambient temperature range	Operating: –25 to 55°C, Some connector models: –40°C to 55°C * (with no icing or condensation) Storage: –40 to 70°C (with no icing or condensation)
Ambient humidity range	Operating: 35% to 85%, Storage: 35% to 95% (with no condensation)
Insulation resistance	20 MΩ min. at 500 VDC
Dielectric strength	1,000 VAC, 50/60 Hz for 1 min
Vibration resistance	Destruction: 10 to 55 Hz, 1.5 mm double amplitude for 2 hours each in X, Y, and Z directions
Shock resistance	Destruction: 500 m/s² 3 times each in X, Y, and Z directions
Indicator	Operation indicator (orange) Stability indicator (green) Through-beam Emitter has power indicator (orange) only.
Accessories	Instruction manual (Neither Reflectors nor Mounting Brackets are provided with any of the above models.)

^{*} The ambient temperature range during operation for connector models depends on the model. For the E3Z-T66/T86/R66/R86, the range is -40°C to 55°C. For the E3Z-D66/D86/D87/D87, the range is -30°C to 55°C. For other connector models, the range is -25°C to -55°C.

The sensing distance for Retro-reflective Models (E3Z-R66/R86) between -40°C to -25°C, however, will be as follows (not the values in the table): With E39-R1S: 3 m (100 mm), With E39-R1: 2 m (100 mm).

Also, use the XS3F-M42 -4 -- L Sensor I/O Connector (PUR cable) for applications between -25°C to -40°C. (Refer to page 4.)




Engineering Data (Reference Value)

Parallel Operating Range


Through-beam Models

E3Z-T□1(T□6)




Through-beam Models

E3Z-T□1(T□6) and Slit (A Slit is mounted to the Emitter and Receiver.)




E3Z-B□1/B□6 + E39-R1S Reflector (Order Separately)




Through-beam Models

E3Z-T□A




Through-beam Models

E3Z-T□A and Slit (A Slit is mounted to the Emitter and Receiver.)




E3Z-B 2/B 7 + E39-R1S Reflector (Order Separately)




Through-beam Models

E3Z-T□2(T□7)



Retro-reflective Models


E3Z-R□1(R□6) and Reflector



Operating Range


Diffuse-reflective Models

E3Z-D□1(D□6)




Diffuse-reflective Models

E3Z-D□2(D□7)



Narrow-beam Reflective Models


E3Z-L□1(L□6)



Excess Gain vs. Set Distance


Through-beam Models

E3Z-T \square 1(T \square 6)/-T \square A/-T \square 2(T \square 7)




Retro-reflective Models

E3Z-R□1(R□6) and Reflector




Diffuse-reflective Models

E3Z-D□1(D□6)




Diffuse-reflective Models

E3Z-D□2(D□7)




Narrow-beam Reflective Models

E3Z-L□1(L□6)




Limited reflective Models

E3Z-L□3(L□8)




Excess Gain vs. Set Distance

E3Z-B□1/B□6 + E39-R1S Reflector (Order Separately)




E3Z-B 2/B 7 + E39-R1S Reflector (Order Separately)




Sensing Object Size vs. Sensing Distance

Diffuse-reflective Models

E3Z-D□1(D□6)




Diffuse-reflective Models E3Z-D□2(D□7)




Narrow-beam Reflective Models

E3Z-L□1(L□6)



Spot Diameter vs. Sensing Distance


Narrow-beam Reflective Models E3Z-L 1(L 6)



Differential Travel vs. Sensing Distance

Narrow-beam Reflective Models

E3Z-L□1(L□6)




I/O Circuit Diagrams

NPN Output

Model*	Operation mode	Timing charts	Operation selector	Output circuit
E3Z-T61(K) E3Z-T66 E3Z-T62 E3Z-T67 E3Z-T61A E3Z-T66A	Light-ON	Incident light No incident light Operation ON indicator (orange) Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown (1) and black (4) leads)	L side (LIGHT ON)	Through-beam Receivers, Retro-reflective Models, Diffuse-reflective Models, Limited reflective Models. Operation Indicator Orange Or
E3Z-R61(K) E3Z-R66 E3Z-D61(K) E3Z-D66 E3Z-D62(K) E3Z-D67 E3Z-L61	Dark-ON	No incident light No incident light Operation ON Indicator (orange) OUtput ON Itransistor OFF Load Operate (e.g., relay) Reset (Between brown (1) and black (4) leads)	D side (DARK ON)	Connector Pin Arrangement (2) (3) (1) (2) (3) (4) (5) (7) (7) (8) (8) (9) (9) (9) (9) (9) (10) (10) (10) (10) (10) (10) (10) (10
E3Z-L66 E3Z-B61 E3Z-B66 E3Z-B62 E3Z-B67 E3Z-L63 E3Z-L68	Through-beam Emitter Power indicator (orange) Photoelectric Sensor main circuit		B B	Connector Pin Arrangement 12 to 24 VDC Pins 2 and 4 are not used.

PNP Output




^{*} Models numbers for Through-beam Sensors (E3Z-T□□) are for sets that include both the Emitter and Receiver.

The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3Z-T61-L 2M), the model number of the Receiver, by adding "-D" (example: E3Z-T61-D 2M.) Refer to *Ordering Information* to confirm model numbers for Emitter and Receivers.

OMRON 1

Plugs (Sensor I/O Connectors)

M8 connector



Pin arrangement

Classifi- cation	Wire color	Connector pin No.	Application
	Brown	1	Power supply (+V)
DC	White	2	-
DC	Blue	3	Power supply (0 V)
	Black	4	Output

Note: Pin 2 is not used.

Nomenclature

Through-beam Models E3Z-T (Receiver) E3Z-T A (Receiver)	
Retro-reflective Models E3Z-R□□	Stability indicator Operation indicator (green) Sensitivity adjuste
E3Z-B □□	Operation selector
Diffuse-reflective Models	

E3Z-D□□

Narrow-beam Reflective Models

E3Z-L

Limited reflective Models

E3Z-L□□

Safety Precautions

Refer to Warranty and Limitations of Liability.



This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Precautions for Correct Use

Do not use the product in atmospheres or environments that exceed product ratings.

Wiring


M8 Metal Connector

- Be sure to connect or disconnect the metal connector after turning OFF the Sensor.
- Hold the connector cover to connect or disconnect the metal connector.
- Secure the connector cover by hand. Do not use any pliers, otherwise the connector may be damaged.
- The proper tightening torque range is between 0.3 and 0.4 N·m. Be sure to tighten the connector securely, otherwise the specified degree of protection may not be maintained or the connector may be disconnected due to vibration.

Mounting

Sensor Mounting

Use M3 screws to mount the sensor and tighten each screw to a maximum torque of 0.53 N·m.



Oil-resistant Models

Oil Resistance

- Although the E3Z-_\Secondskip K Sensors have oil-resistant specifications, performance may be affected by certain types of oil. Refer to the following table.
- E3Z- Sensors are tested for resistance to the oils given in the following table. Refer to the information in the table when deciding which type of oil to use.

Test oil clas- sification	Product name	Kinematic viscosity (mm²/s) at 40°C	рН
Lubricant	Velocity No.3 (manufactured by Exx- on Mobil)	2.02	
Water insolu- ble machining oil	Yushiron Oil No.2 ac (manufactured by Yushiro Chemical In- dustry Co., Ltd.)	Less than 10	
Water soluble machining oil	Yushiroken EC50T-3 (manufactured by Yushiro Chemical In- dustry Co., Ltd.)		7 to 9.5
	Yushiron Lubic HWC68 (manufactured by Yushiro Chemical In- dustry Co., Ltd.)		7 to 9.9
	Gryton 1700D (manufactured by Toho Chemical Industry Co., Ltd.)		7 to 9.2
	Yushironken S50N (manufactured by Yushiro Chemical In- dustry Co., Ltd.)		7 to 9.8

- Note: 1. The E3Z maintained a minimum insulation resistance of 100 $M\Omega$ after it was dipped in all the above oils for 240 hours.
 - When using the Sensors in environments subject to oils other than
 those listed above, use the figures for kinematic viscosity and pH from
 the table as general guidelines. Additives and other substances
 contained in oils may affect the E3Z. Be sure to consider this before
 use.

(Unit: mm)

Dimensions


Sensors

E3Z-T82

Through-beam*


Pre-wired Models E3Z-T61(K) E3Z-T81(K) E3Z-T61A E3Z-T81A E3Z-T62






Terminal No.	Specifi- cations
1	+V
2	
3	0V
4	
Pins 2 and 4 are not used.	

M8 Pre-wired Connector



* The Emitter cable has two conductors and the Receiver cable has three conductors.



 Terminal No.
 Specifications

 1
 +V

 2
 --

 3
 0V

 4
 Output


 Pin 2 is not used.

Through-beam*


Connector Models E3Z-T66 E3Z-T86 E3Z-T66A E3Z-T86A

E3Z-T67 E3Z-T87





Terminal No.	Specifi- cations
1	+V
2	
3	0V
4	
Pins 2 and 4	are not used.



Terminal No.	Specifi- cations
1	+V
2	
3	0V
4	Output
Pin 2 is not used.	

^{*} Models numbers for Through-beam Sensors (E3Z-T□□) are for sets that include both the Emitter and Receiver.

The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3Z-T61-L 2M), the model number of the Receiver, by adding "-D" (example: E3Z-T61-D 2M.) Refer to *Ordering Information* to confirm model numbers for Emitter and Receivers.


Retro-reflective Models

Pre-wired Models

E3Z-R61(K) E3Z-B61 E3Z-R81(K) E3Z-B81 E3Z-D61(K) E3Z-B62 E3Z-D81(K) E3Z-B82 E3Z-D62(K) E3Z-L63 E3Z-D82(K) E3Z-L83

E3Z-L61 E3Z-L81





Operation Indicator (orange)

11.2

7.5

M8 Pre-wired Connector (E3Z-T□□K-M3J)
4 dia. vinyl-insulated round cable with 3 conductors, Standard length: 0.3 m
M8 1 3

Terminal No.	Specifica- tions
1	+V
2	
3	0V
4	Output


Retro-reflective Models

Connector Models

E3Z-R66 E3Z-B66 E3Z-R86 E3Z-B86 E3Z-D66 E3Z-B67 E3Z-D86 E3Z-B87 E3Z-D67 E3Z-L68 E3Z-D87 E3Z-L88

E3Z-L66 E3Z-L86





Operation Indicator (orange)


11.2

7.5

Terminal No.	Specifica- tions
1	+V
2	
3	0V
4	Output

Note: The lens for the E3Z-D \square 1/D \square 6/L \square \square /B \square \square is red. The lens for the E3Z-D \square 2/D \square 7 is black.


Accessories (Order Separately)





E39-S65C

steel

2.0 dia.







Mounting Brackets

Refer to E39-R for details.

Sensor I/O Connectors

Refer to $XS3\square$ for details.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

<u>Errors and Omissions.</u> <u>Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is accurate.</u> assumed for clerical, typographical or proofreading errors or omissions.

2014.12

In the interest of product improvement, specifications are subject to change without notice.

