
General-purpose Basic Switch


Best-selling Basic Switch Boasting High Precision and Wide Variety

- A large switching capacity of 15 A with high repeat accuracy.
- A wide range of variations in contact form for your selection: basic, split-contact and maintained-contact.
- A series of standard models for micro loads is available.
- A series of molded terminal-type models incorporating safety terminal protective cover is available.



Model Number Structure

Available types



Basic Models

General-purpose

- A variety of actuators is available for a wide range of application.
- The contact mechanism of models for micro loads is a crossbar type with gold-alloy contacts, which ensures highly reliable operations for micro loads.
- · Contact Gap:
 - 0.20 mm (extra-high-sensitivity) H2:
 - H: 0.25 mm (high-sensitivity, micro voltage current load)
 - G: 0.5 mm (standard)
 - E: 1.8 mm (high-capacity)
 - 1.0 mm (split-contact models)

Drip-proof

- These Switches use a rubber boot on the actuator and adhesive fill between the case and cover to increase resistance to drips.
- Models with drip-proof terminal protective covers and molded terminals with resin filling are also available.

Split-contact Models

- This type is identical in construction to the general-purpose basic switch except that it has two pairs of simultaneous acting contacts by splitting moving contacts.
- · Since the moving contacts are connected to a common terminal, either parallel or series connection is possible.
- · Highly reliable micro load switching is ensured if the model is used as a twin-contact switch.

Maintained-contact Models

- The maintained-contact type has a reset button at the bottom of the switch case, in addition to the pushbutton (plunger) located on the opposite side of the reset button. Use these buttons alternately.
- Since the Switch has greater pretravel than overtravel, it is suitable for use in reversible control circuits, manual reset circuits, safety limit circuits, and other circuits which are not preferable for automatic resetting. (For further details, refer to individual datasheets.)

■ Model Number Legend

Basic Models

Z - \square \square \square - \square 1 2 3 4

1. Ratings

01: 0.1 A (micro load) 15: 15 A

2. Contact Gap

H2: 0.20 mm

(extra-high sensitivity)

0.25 mm (high-sensitivity, micro load)

0.5 mm

E: 1.8 mm (high-capacity)

3. Actuator

None: Pin plunger

Slim spring plunger Short spring plunger D: Spring plunger (medium OP) K: Spring plunger (high OP) K3: Panel mount plunger (low OP) Q3: Panel mount plunger Q: (medium OP) Q8: Panel mount plunger (high OP) Panel mount roller plunger Q22: Q21: Panel mount cross roller plunger Leaf spring (high OF) Roller leaf spring L2: W21: Short hinge lever Hinge lever (low OF) Hinge lever (medium OF) W32: Hinge lever (high OF) Low-force hinge lever W4:

W44: Long hinge lever W78: Low-force wire hinge lever (low OF)

W52: Low-force wire hinge lever (high OF) W22: Short hinge roller lever

Hinge roller lever W2: W25: Hinge roller lever

W49:

M:

(large roller) Short hinge

cross roller lever W54: Hinge cross roller lever W2277: Unidirectional short hinge

> roller lever (low OF) Reverse hinge lever

M22: Reverse short hinge roller lever M2: Reverse hinge roller lever Flexible rod (high OF) NJ: Flexible rod (low OF) NJS:

4. Degree of Protection

None: General-purpose Drip-proof 55: Drip-proof

(including terminals)

5. Terminals

None: Solder terminal Screw terminal (with toothed washer) B5V: Screw terminal with terminal cover

(for Z-15G□A55 only)

Split-contact Models

$$Z - \frac{10}{1} \frac{F}{2} \frac{\Box}{3} \frac{Y}{4} - \frac{B}{5}$$

1. Ratings

10: 10 A (split-contact models)

2. Contact Gap

F: 1 mm (high-capacity)

3. Actuator

None: Pin plunger

Slim spring plunger D: Short spring plunger Panel mount plunger Q:

Q22: Panel mount roller plunger

W: Hinge lever

W22: Short hinge roller lever Hinge roller lever W2:

Reverse short hinge roller lever M22:

4. Construction

Split-contact type

5. Terminals

None: Solder terminal Screw terminal (with toothed washer)

Maintained-contact models

$$Z - \frac{15}{1} \stackrel{\mathsf{E}}{=} \frac{\square}{3} \stackrel{\mathsf{R}}{=} \frac{\mathsf{R}}{4}$$

1. Ratings

15: 15 A

2. Contact Gap

1.8 mm (high-capacity)


3. Actuator

None: Pin plunger Slim spring plunger Hinge lever

4. Construction

Maintained-contact models

Drip-proof with Molded Terminal Models



1. Drip-proof model

(Insert model number of basic, drip-proof version with solder terminals)

2. Lead Outlets

None: VSF VCT


3. Direction of Lead Outlets

Left R: Right D:

Descending D type R type

4. Length of Leads

1 m 3: 3 m



Ordering Information

Basic Models (General-purpose)

	Classific	ation	Standard	High-sensitivity	Extra-high sensitivity	High-capacity	Micro load	
Actuator	Contact gap Terminal *1		G (0.5 mm)	H (0.25 mm)	H2 (0.20 mm)	E (1.8 mm)	H (0.25 mm)	
			Model	Model	Model	Model	Model	
Din always			Z-15G	Z-15H	Z-15H2	Z-15E	Z-01H	
Pin plunger		章	Z-15G-B	Z-15H-B	Z-15H2-B	Z-15E-B	Z-01H-B	
	Δ.		Z-15GS	Z-15HS			Z-01HS	
Slim spring plunger	<u> </u>	富	Z-15GS-B	Z-15HS-B			Z-01HS-B	
Short spring			Z-15GD	Z-15HD		Z-15ED	Z-01HD	
olunger	4	国	Z-15GD-B	Z-15HD-B		Z-15ED-B	Z-01HD-B	
	1 O.D.		Z-15GQ3					
Panel mount	Low OP	Ī	Z-15GQ3-B					
olunger	Medium		Z-15GQ	Z-15HQ		Z-15EQ	Z-01HQ	
	OP	重	Z-15GQ-B	Z-15HQ-B	Ī	Z-15EQ-B	Z-01HQ-B	
	High OP		Z-15GQ8					
	Tilgit Oi	重	Z-15GQ8-B					
Panel mount roller	\Box		Z-15GQ22	Z-15HQ22		Z-15EQ22		
olunger	凰	国	Z-15GQ22-B	Z-15HQ22-B		Z-15EQ22-B		
Panel mount cross	-A-		Z-15GQ21	Z-15HQ21		Z-15EQ21		
oller plunger	豊	国	Z-15GQ21-B	Z-15HQ21-B		Z-15EQ21-B		
			Z-15GL					
Leaf spring		基	Z-15GL-B					
Roller leaf spring	<u> </u>		Z-15GL2					
	<u></u>	事	Z-15GL2-B					
	-		Z-15GW21					
Short hinge lever	6	事	Z-15GW21-B					
			Z-15GW	Z-15HW				
	Low OP	富	Z-15GW-B	Z-15HW-B				
Hinge lever	Medium		Z-15GW3					
	OP	重	Z-15GW3-B					
	High OP		Z-15GW32					
	r ligit Oi	重	Z-15GW32-B					
_ow-force hinge			Z-15GW4	Z-15HW24				
ever	4	重	Z-15GW4-B	Z-15HW24-B				
	Low OP			Z-15HW78	1			
_ow- force wire hinge	LOW OI	臣		Z-15HW78-B	<u> </u>			
ever	High OP			Z-15HW52				
		国		Z-15HW52-B				
Short hinge roller	Q		Z-15GW22	Z-15HW22		Z-15EW22	Z-01HW22	
ever		臣	Z-15GW22-B	Z-15HW22-B		Z-15EW22-B	Z-01HW22-B	
Short hinge cross	Пъ		Z-15GW49			-		
roller lever	A LIBERT	国	Z-15GW49-B					
	Standard		Z-15GW2	Z-15HW2				
Hinge roller lever		重	Z-15GW2-B	Z-15HW2-B	<u></u>			
	Large roller Z-15GW25							
		国	Z-15GW25-B					

	Classific	ation	Standard	High-sensitivity	Extra-high sensitivity	High-capacity	Micro load	
Actuator	Contac	t gap	G (0.5 mm)	H (0.25 mm)	H2 (0.20 mm)	E (1.8 mm)	H (0.25 mm)	
	Terminal *	1	Model	Model	Model	Model	Model	
Hinge cross roller	Пъ		Z-15GW54					
lever	<u> </u>	富	Z-15GW54-B					
Unidirectional Q	(0)		Z-15GW2277					
short hinge roller lever	Parallel	重	Z-15GW2277-B					
Reverse hinge lever			Z-15GM					
*2	<u> </u>	重	Z-15GM-B					
Reverse short hinge	Z-15GM22							
roller lever *2		重	Z-15GM22-B					
Reverse hinge			Z-15GM2					
roller lever *2		軍	Z-15GM2-B				1	

^{*1. 😸 :} Solder terminal 🗵 : Screw terminal

Split-contact Models

			= (4.6)
	Conta	ct gap	F (1.0 mm)
Actuator	Termin	al *1	Model
Din plunger			
Pin plunger	4	重	Z-10FY-B
Clim oneing alumane	А		
Slim spring plunger	<u> Н</u>	重	Z-10FSY-B
Chart apring plunger	_		
Short spring plunger	Ā	重	Z-10FDY-B
	Ь		
Panel mount plunger	프	軍	Z-10FQY-B
Panel mount roller	@		
plunger	蒕	重	Z-10FQ22Y-B
Hinge lever			
i iiige ievei		画	Z-10FWY-B
Short hinge roller	a		
lever	<u></u>	重	Z-10FW22Y-B
I linear wellow laves	<u>a</u>		
Hinge roller lever		重	Z-10FW2Y-B
Reverse short hinge			
roller lever *2		重	Z-10FM22Y-B

Maintained-contact Models

Actuator	Model	
Pin plunger	_	Z-15ER
Slim spring plunger	<u>A</u>	Z-15ESR
Hinge lever		Z-15EWR

^{*2.} The pin plungers of reverse-type models are continuously pressed by the actuator levers with compression coil springs and the pin plungers are freed by operating the levers. Reverse-type models are highly vibration- and shock-resistive because the pin plungers are normally

^{*1. |} Solder terminal 宴: Screw terminal *2. The pin plungers of reverse-type models are continuously pressed by the actuator levers with compression coil springs and the pin plungers are freed by operating the levers. Reverse-type models are highly vibration- and shock-resistive because the pin plungers are normally

Drip-proof Models

	Classification		ndard	High-sensitivity	Micro load
	Contact gap	G (0.	5 mm)	H (0.25 mm)	H (0.25 mm)
	Drip-proof terminal protective cover	Not provided	Provided	Not provided	Not provided
Actuator	Terminal *1	Model	Model	Model	Model
Pin plunger		Z-15G55			Z-01H55
p.ago.	— E	Z-15G55-B	Z-15GA55-B5V		Z-01H55-B
Short spring plunger		Z-15GD55			Z-01HD55
	<u>ā</u>	Z-15GD55-B			Z-01HD55-B
	Low	Z-15GK55			
Spring plunger	OP E	Z-15GK55-B			
	High	Z-15GK355			
	- □	Z-15GK355-B	Z-15GK3A55-B5V		
Panel mount plunger	<u>_</u>	Z-15GQ55			
	<u> </u>	Z-15GQ55-B	Z-15GQA55-B5V		
Panel mount roller	@	Z-15GQ2255			
plunger	<u>男</u> I	Z-15GQ2255-B	Z-15GQ22A55-B5V		
Panel mount cross	rTh U				
roller plunger		Z-15GQ2155-B	Z-15GQ21A55-B5V		
		Z-15GL55			
Leaf spring	¥ §	Z-15GL55-B			
	a b	Z-15GL255			
Roller leaf spring	1 3	Z-15GL255-B			
		Z-15GW2155			
Short hinge lever	重	Z-15GW2155-B			
		Z-15GW4455			
Long hinge lever	1 3	Z-15GW4455-B	Z-15GW44A55-B5V		
		Z-15GW55			
Hinge lever	重	Z-15GW55-B	Z-15GWA55-B5V		
	a	Z-15GW2255			Z-01HW2255
Short hinge roller lever	<u> </u>	Z-15GW2255-B	Z-15GW22A55-B5V		Z-01HW2255-B
	Q	Z-15GW255			
Hinge roller lever	3	Z-15GW255-B	Z-15GW2A55-B5V		
	11	Z-15GW227755			
Unidirectional short hinge roller lever	□	Z-15GW227755-B	Z-15GW2277A55- B5V		
		Z-15GM55			
Reverse hinge lever *2	1	Z-15GM55-B			
Reverse short hinge	2	Z-15GM2255			
roller lever *2	4 3	Z-15GM2255-B] 		
Reverse hinge roller		Z-15GM255			
lever *2	3	Z-15GM255-B			
		Z-15GNJ55			
Flexible rod (coil spring) *3		Z-15GNJ55-B			
Flexible rod				Z-15HNJS55	
(steel wire)				Z-15HNJS55-B	

^{*1. 🖟:} Solder terminal 🗵 : Screw terminal *2. The pin plungers of reverse-type models are continuously pressed by the actuator levers with compression coil springs and the pin plungers are freed by operating the levers.
*3. The tip is made of resin.

Specifications

■ Characteristics

Item	Classification	Z-15 (except micro load and flexible rod)		Z-15 (flexible rod)	Z-10F	Z-15H2
Operating speed		0.01 mm to 1 m/s (*1)		1 mm to 1 m/s	0.1 mm to 1 m/s (*1)	0.01 mm to 1 m/s
Operating	Mechanical	240 operations/min		120 operations/min	240 operations/min	240 operations/min
frequency	Electrical	20 operations/min				
Contact resist	ance	15 m Ω max. (initial value)	50 mΩ max. (initial value)	15 mΩ max. (initial value)	25 m $Ω$ max. (initial value)	15 m Ω max. (initial value)
Insulation res	stance	100 M Ω min. (at 500 VD	C)			
Dielectric stre (50 / 60 Hz for	ngth 1 min.)	Between contacts of san Contact gap G: 1,000 VA Contact gap H: 600 VAC Contact gap E: 1,500 VA	AC AC	Between contacts of same polarity Contact gap G: 1,000 VAC Contact gap H: 600 VAC	Between contacts of same polarity Contact gap F: 1,500 VAC	Between contacts of same polarity 600VAC
		2,000 VAC		and between each terminal and no	, , ,	
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm dou	0 to 55 Hz, 1.5-mm double amplitude (*5) 10 to 20 Hz, 1.5-mm double amplitude			ıble amplitude (*5)
Shock	Destruction	1,000 m/s ² max.				
resistance	Malfunction	300 m/s ² max. (*2, *5)		50 m/s ² max. (*5)	300 m/s ² max. (*3, *5)	100 m/s ² max.
Degree of protection	General- purpose	IP00				
protection	Drip-proof	Equivalent to IP62 (exce	pt terminals)			
Degree of pro		Class I				
Proof tracking (PTI)	index	175				
Ambient operating	General- purpose	–25°C to 80°C (with no id	cing)			
temperature	Drip-proof	-15°C to 80°C (with no id	cing)			
Ambient operating	General- purpose	35% to 85%RH				
humidity	Drip-proof	35% to 95%RH				
Service life	Mechanical	Contact gap H2: 10,000, Contact gap G, H: 20,000 Contact gap E: 300,000	0,000 operations min.(*4) operations	1,000,000 operations min.	500,000 operations min. (*1)	20,000,000 operations min.
	Electrical	Contact gap G, H: 500,0 Contact gap E: 100,000		100,000 operations min.	100,000 operations min.	500,000 operations min.
Weight		Approx. 22 to 58 g		Approx. 42 to 48 g	Approx. 34 to 61 g	Approx. 22 g

^{*1} The values are for the plunger models. (For the lever models, the values are at the plunger section.)
*2 The values are for the Z-15G pin plunger.
*3 The values are for the Z-10FY-B.

■ Ratings (Basic, Split-contact and Maintained contact Models)

Z-15 (Except Micro Load and Flexible Rod Models)

	Item		Non-indu	ctive load (A)		Inductive load (A)			
		Resis	tive load	Lam	load	Induct	Inductive load		r load
Contact gap	Rated voltage	NC	NO	NC	NO	NC	NO	NC	NO
	125 VAC	15	(10) *	3	1.5	15 (10) *	5	2.5
G, H, H2, E	250 VAC	15	(10) *	2.5	1.25	15 (10) *	3	1.5
	500 VAC *		10	1.5	0.75		6	1.5	0.75
	8 VDC		15	3	1.5	1	15	5	2.5
	14 VDC		15	3	1.5	1	10	5	2.5
G	30 VDC		6	3	1.5	5		5	2.5
	125 VDC		0.5	0.5	0.5	0	.05	0.05	0.05
	250 VDC	(0.25	0.25	0.25	0	.03	0.03	0.03
	8 VDC		15	3	1.5	1	15	5	2.5
	14 VDC		15	3	1.5	1	10	5	2.5
H, H2	30 VDC		2	2	1.4		1	1	1
	125 VDC		0.4	0.4	0.4	0	.03	0.03	0.03
	250 VDC		0.2	0.2	0.2	0	.02	0.02	0.02
	8 VDC		15	3	1.5		15	5	2.5
	14 VDC		15	3	1.5	1	15	5	2.5
E	30 VDC		15	3	1.5	1	10	5	2.5
	125 VDC	(0.75	0.75	0.75	C	.4	0.4	0.4
	250 VDC		0.3	0.3	0.3	C	.2	0.2	0.2

^{*} Figures in parentheses are for the Z-15HW52, Z-15HW78(-B) and Z-15H2(-B) models, the AC ratings of these models are 125 and 250 V only.

 $^{^{\}star}4$ The values are for the pin plunger. The service life for models other than the pin plunger is 10,000,000 min.

Z-15 (Flexible Rod Models)

		Non-induct	tive load (A)	load (A) Inductive			e load (A)		
Rated voltage	Resisti	ve load	Lamp	load	Induct	ive load	Motor load		
	NC	NO	NC	NO	NC	NC NO		NO	
125 VAC	1	5	2	1		7	2.5	2	
250 VAC	1	5	1	0.5		5	1.5	1	
8 VDC	1	5	2	1		7	3	1.5	
14 VDC	1	5	2	1		7	3	1.5	
30 VDC	2	2	2	1		1	1	0.5	
125 VDC	0.	.4	0.4	0.4	0	.03	0.03	0.03	
250 VDC	0.	.2	0.2	0.2	0	.02	0.02	0.02	


Z-10F

Item		Non-inductive load (A)				Inductive load (A)			
		Resisti	ve load	Lamp	load	Inducti	ve load	Moto	r load
Contact gap	Rated voltage	NC	NO	NC	NO	NC	NO	NC	NO
Series	125 VAC 250 VAC		0 0	4 2.5	2 1.5	6) }	5 3	2.5 1.5
connection	30 VDC 125 VDC 250 VDC		0 1 .6	4 1 0.6	2 1 0.6	0. 0.	1	6 0.1 0.05	3 0.1 0.05
Parallel	125 VAC 250 VAC		6 6	3 2.5	1.5 1.25	2		4 2	2 1
connection	30 VDC 125 VDC 250 VDC	0	6 .6 .3	4 0.6 0.3	2 0.6 0.3	0. 0.	.1	6 0.1 0.05	3 0.1 0.05

Z-01H

Poted voltage	Resistive load (A)				
Rated voltage	NC NO				
125 VAC	0.1				
8 VDC	0.	.1			
14 VDC	0.1				
30 VDC	0.1				

Applicable Load Range



	Z-01H	Z-15□, Z-10FY
Minimum applicable load	1 mA at 5 VDC	160 mA at 5 VDC

Note: 1. The above current ratings are the values of the steady-state current.

- 2. Inductive load has a power factor of 0.4 min. (AC) and a time constant of 7 ms max. (DC).
- 3. Lamp load has an inrush current of 10 times the steady-state current.
- 4. Motor load has an inrush current of 6 times the steady-state current.
- The normally closed and normally open ratings of reverse hinge lever models are opposite to each other.

■ Contacts Specification

Item	Classification	Z-15	Z-01H	Z-10F
Contacts	Shape	Rivet	Single crossbar	Rivet
	Material	Silver	Gold alloy	Silver
Inrush current	NC	30 A max.	0.1 A max.	40 A max.
illiusii curreiit	NO	15 A max.	0.1 A max.	20 A max.

■ Safety Standards Ratings

UL/CSA (General ratings only)

Rated voltage	Model	Z-15	Z-10F	Z-01H
125 VAC		15A and 1/8HP	6A and 1/10HP	0.1A
250 VAC		15A and 1/4HP	6A and 1/8HP	
480 VAC		15A	6A	
30 VDC				0.1A
125 VDC		0.5A	0.6A	
250 VDC		0.25A	0.3A	

TÜV (EN61058-1)


Rated voltage	Model	Z-15H□-B	Z-15G□-B	Z-01H□-B
250 VAC		15 A	15 A	
125 VAC				0.1 A
30 VDC				0.1 A

- 6. The AC ratings of molded terminals are 125 and 250 V only.
- The ratings values apply under the following test conditions:


 - (1) Ambient temperature: 20±2°C (2) Ambient humidity: 65±5%RH (3) Operating frequency: 20 operations/min

Engineering Data

■ Mechanical Durability (Z-15G)




■ Electrical Durability (Z-15G)



■ Structure


Basic Models

Contact Form (SPDT)




Note: The Z-15GM is a reversible model and the NO and NC positions are reversed.

Drip-proof ConstructionWithout Terminal Protective Cover




Molded Terminals




Note: The Z-15GM is a reversible model and the NO and NC positions are reversed.

With Terminal Protective Cover




Split-Contact Models

Contact Form



Note: The NO and NC terminal arrangement is reversed for Models with reverse operation (Z-10FM).

Connection Example Series Connection




Parallel Connection



Maintained-contact Models

Contact Form




Dimensions

■ General-purpose and Split Contact Models


Note: Unless otherwise specified, all units are in millimeters and a tolerance of \pm 0.4 mm applies to all dimensions

Terminals



Mounting

All switches can be side mounted using M4 mounting screws with plane washers or spring washers to securely mount the Switch. Tighten the screws to a torque of 1.18 to 1.47 N·m.



Versions with panel mount plungers can be panel mounted via the plunger, provided that the hexagonal nut of the actuator is tightened to a torque of 2.94 to 4.9 N·m.

Panel Mount Roller Plunger

12.5^{+0.2}dia.

Panel Mount Plunger

12.5^{+0.2} dia

Note: Mount using either the side mounting holes or the panel mount plunger, not both. If using the side mounting holes, then remove the hexagonal nut(s) from the panel mount plunger.

Accessories (Terminal Covers, Actuators, and Separators): Refer to 'Z/A/X/DZ Common Accessories' datasheet


Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.

2. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.

Pin Plunger

Z-15G-B Z-15E-B Z-15H2-B Z-01H-B Z-15H-B **Z-10FY-B**






Operating Characterist	tics	Z-15G-B	Z-15H2-B	Z-15H-B	Z-15E-B	Z-01H-B	Z-10FY-B
Operating force	OF	250 to 350 gf	200 to 255 gf	200 to 280 gf	625 to 800 gf	250 gf max.	455 to 740 gf
Release force	RF min.	114 gf	114 gf	114 gf	114 gf	80 gf	114 gf
Pretravel	PT max.	0.4 mm	0.3 mm	0.3 mm	0.8 mm	0.5 mm	0.8 mm
Overtravel	OT min.	0.13 mm	0.13 mm	0.13 mm	0.13 mm	0.13 mm	0.13 mm
Movement Differential	MD max.	0.05 mm	0.005 to 0.008 mm	0.025 mm	0.13 mm	0.04 mm	0.1 mm
Operating Position	OP	15.9±0.4 mm					

Slim Spring Plunger Z-15GS-B Z-01HS-B Z-15HS-B Z-10FSY-B






Model	Z-15GS-B	Z-15HS-B	Z-01HS	Z-10FSY-B	
OF	250 to 350 gf	200 to 285 gf	250 gf max.	455 to 740 gf	
RF min.	114 gf	114 gf	80 gf	114 gf	
PT max.	0.4 mm	0.3 mm	0.5 mm	0.8 mm	
OT min.	1.6 mm	1.6 mm	1.6 mm	1.6 mm	
MD max.	0.05 mm	0.025 mm	0.05 mm	0.1 mm	
OP	28.2±0.5 mm				

Short Spring Plunger Z-15GD-B Z-01HD-B Z-15HD-B Z-10FDY-B **Z-15ED-B**





Model	Z-15GD-B	Z-15HD-B	Z-15ED-B	Z-01HD-B	Z-10FDY-B
OF	250 to 350 gf	200 to 285 gf	625 to 800 gf	250 gf max.	455 to 740 gf
RF min.	114 gf	114 gf	114 gf	80 gf	114 gf
PT max.	0.4 mm	0.3 mm	0.8 mm	0.5 mm	0.8 mm
OT min.	1.6 mm	1.6 mm	1.6 mm	1.6 mm	1.6 mm
MD max.	0.05 mm	0.025 mm	0.13 mm	0.05 mm	0.1 mm
OP	21.5+0.5 mm				

Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-b" from the end of the part number.

2. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.


Panel Mount Plunger

Z-15GQ-B Z-01HQ-B Z-15HQ-B Z-10FQY-B Z-15EQ-B Z-15GQ3-B *

Z-15GQ8-B *



The external dimensions of the actuator vary.




- Note: 1. Do not use the M12 mounting screw and the case mounting hole at the same time, or excessive pulling force will be imposed on the switch and the case and cover may be damaged.
 - 2. On the model Z-15GQ3-B, PT can be set to a value larger than that for the Z-15GQ.
 - 3. On the model Z-15GQ8-B. operating position can be adjusted by providing a screw in the plunger section.
 - On the model Z-15GQ8-B, the M3 hole with a depth of 10 mm is a through hole. Take precautions so that no water or screw lock agent penetrates into the hole.

Model	Z-15GQ-B	Z-15HQ-B	Z-15EQ-B	Z-01HQ-B	Z-10FQY-B	Z-15GQ3-B	Z-15GQ8-B
OF RF min. PT max. OT min. MD max.	250 to 350 gf 114 gf 0.4 mm 5.5 mm 0.05 mm	200 to 285 gf 114 gf 0.3 mm 5.5 mm 0.025 mm	625 to 800 gf 114 gf 0.8 mm 5.5 mm 0.13 mm	250 gf max. 80 gf 0.5 mm 5.5 mm 0.05 mm	455 to 740 gf 114 gf 0.8 mm 5.5 mm 0.1 mm	250 to 350 gf 114 gf 4.2 mm 2.5 mm 2.2 mm	250 to 350 gf 114 gf 0.5 mm 5.5 mm 0.05 mm
OP			18.8±0.8 mm	32.5±1 mm			

Panel Mount Roller Plunger

Z-15GQ22-B Z-15EQ22-B Z-15HQ22-B Z-10FQ22Y-B





Note: Do not use the M12 mounting screw and the case mounting hole at the same time, or the case may be damaged.

*2. Two hexagonal nuts (3 t × 17 width across flats)


Z-15GQ22-B Z-10FQ22Y-B Model Z-15HQ22-B Z-15EQ22-B OF RF min. PT max. 200 to 285 gf 625 to 800 gf 455 to 740 gf 250 to 350 gf 114 gf 0.4 mm 114 gf 0.3 mm 114 gf 0.8 mm 114 gf 1 mm OT min. 3.58 mm 3.58 mm 3.58 mm 3.55 mm MD max 0.05 mm 0.025 mm 0.13 mm 0.1 mm OP 33.4±1.2 mm

Panel Mount Cross Roller Plunger

Z-15GQ21-B Z-15EQ21-B Z-15HQ21-B



Note: Do not use the M12 mounting screw and the case mounting hole at the same time, or the case may be damaged.



1	*1. Stainless-steel roller
1	*2. Two hexagonal nuts (3 t × 17 width
	across flats)
	*3. Incomplete screw part with a maximum
	length of 1.5 mm.

Model	Z-15GQ21-B	Z-15HQ21-B	
OF	250 to 350 gf	200 to 285 gf	
RF min.	114 gf	114 gf	
PT max.	0.4 mm	0.3 mm	
OT min.	3.58 mm	3.58 mm	
MD max.	0.05 mm	0.025 mm	
OP	33.4±1.2 mm		


Model	Z-15EQ21-B
OF RF min. PT max. OT min. MD max.	625 to 800 gf 114 gf 0.8 mm 3.58 mm 0.13 mm
OP	33.4±1.2 mm

Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.

2. Unless otherwise specified, all units are in millimeters and a tolerance of $\pm\,0.4$ mm applies to all dimensions.

Leaf Spring Z-15GL-B






OF max.	141 gf
RF min.	14 gf
*OT min.	1.6 mm
MD max.	1.3 mm
FP max.	20.6 mm
OP	17.4±0.8 mm

When operating, be sure not to exceed 1.6 mm.

Roller Leaf Spring Z-15GL2-B






OF max.	141 gf
RF min.	14 gf
*OT min.	1.6 mm
MD max.	1.3 mm
FP max.	31.8 mm
OP	28.6±0.8 mm

* When operating, be sure not to exceed 1.6 mm.

Short Hinge Lever Z-15GW21-B






OF max.	160 gf
RF min.	28 gf
OT min.	2 mm
MD max.	1 mm
FP max.	24.8 mm
OP	19±0.8 mm

Hinge Lever

Z-15GW-B Z-15GW32-B **Z-15HW-B** Z-10FWY-B Z-15GW3-B (Lever Length: 56R)*



* The external dimensions of the actuator vary.



Model	Z-15GW-B	Z-15HW-B	Z-15GW32-B	Z-10FWY-B	Z-15GW3-B
OF RF min. OT min. MD max.	70 gf max. 14 gf 5.6 mm 1.27 mm	67 gf max. 14 gf 5.6 mm 0.63 mm	150 to 200 gf 93 gf 5.6 mm 1.27 mm	90 gf max. 14 gf 5.6 mm 2.4 mm	80 gf max. 15 gf 4.8 mm 1.12 mm
FP max.	28.2 mm	27.4 mm	28.2 mm	29.8 mm	27.2 mm
OΡ	19+0.8 mm				





Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.

2. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.

Low-force Hinge Lever Z-15GW4-B









Z-15HW24-B








Low-force Wire Hinge Lever

Z-15HW52-B

Z-15HW78-B (Lever Length: 110R) *



* The external dimensions of the actuator vary.



Model	Z-15HW52-B
OF max.	6 gf
RF min.	0.5 gf
PT max.	8.3 mm
OT min.	5.6 mm
MD max.	0.65 mm
OP	19±1 mm

Model	Z-15HW78-B
OF max.	4 gf
RF min.	0.3 gf 10 mm
PT max.	10 mm
OT min.	6 mm
MD max.	3 mm
OP	20±1 mm

Note: AC electrical ratings: 10 A, 125/250 V.

Short Hinge Roller Lever

Z-15GW22-B Z-01HW22-B

Z-10FW22Y-B Z-15HW22-B


Z-15EW22-B


Z-15GW2-B * Z-15HW2-B *

Z-10FW2Y-B *




The external dimensions of the actuator vary. (Lever Length: 48.5R)





Model	Z-15GW22-B	Z-15HW22-B	Z-15EW22-B	Z-01HW22-B	Z-10FW22Y-B	Z-15GW2-B	Z-15HW2-B	Z-10FW2Y-B
OFmax.	160 gf	150 gf	198 gf	160 gf	250 gf	100 gf	86 gf	130 gf
RF min.	42 gf	42 gf	42 gf	28 gf	35 gf	22 gf	22 gf	22 gf
OT min.	2.4 mm	2.4 mm	2.4 mm	2.4 mm	2.4 mm	4 mm	4 mm	4 mm
MD max.	0.5 mm	0.45 mm	1.3 mm	0.5 mm	1 mm	1.02 mm	0.6 mm	2 mm
FP max.	32.5 mm		35.1 mm	32.5 mm	34.8 mm		mm	37.4 mm
OP	30.2±0.4 mm		30.2±0.4 mm	30.2±0.4 mm	30.2±0.4 mm).8 mm	30.2±0.8 mm


Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number. 2. Unless otherwise specified, all units are in millimeters and a tolerance of \pm 0.4 mm applies to all dimensions.



Model	Z-15GW49-B	Z-15GW54-B
OF max.	170 gf	100 gf
RF min.	42 gf	22 gf
OT min.	2.4 mm	4 mm
MD max.	0.51 mm	1 mm
FP max.	33.3 mm	37.3 mm
OP	31±0.4 mm	31±0.8 mm

Hinge Roller Lever Z-15GW25-B






OF max.	100 gf
RF min.	21 gf
OT min.	4 mm
MD max.	1.6 mm
FP max.	47.5 mm
OP	41.2±0.8 mm

Unidirectional Short Hinge Roller Lever Z-15GW2277-B






OF max.	170 gf
RF min.	42 gf
OT min.	2.4 mm
MD max.	0.51 mm
FP max.	43.6 mm
OP	41.3±0.8 mm

Reverse Hinge Lever ** Z-15GM-B






OF max.	170 gf
RF min.	28 gf
OT min.	5.6 mm
MD max.	0.89 mm
FP max.	23.8 mm
OP	19±0.8 mm

Reverse Short Hinge Roller Lever ** Z-15GM22-B








	Z-15GM22-B	Z-10FM22Y-B
OF max.	538 gf	650 gf
RF min.	170 gf	170 gf
OT min.	2 mm	2 mm
MD max.	0.28 mm	0.56mm
FP max.	31.8 mm	33 mm
OP	29.4±0.4 mm	29.4±0.4 mm

Reverse Hinge Roller Lever ** Z-15GM2-B





OF max.	240 gf
RF min.	56 gf
OT min.	4 mm
MD max.	0.64 mm
FP max.	35 mm
OP	30.2±0.8 mm


**The pin plungers of reverse-type models are continuously pressed by the actuator levers with compression coil springs and the pin plungers are freed by operating the levers. Reverse-type models are highly vibration- and shock-resis-tive because the pin plungers are normally pressed.

■ Drip-proof Models (without Terminal Protective Cover)

Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.

2. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.


Terminals



Note: With reverse action models (Z-15GM), the positions of NO and NC terminals are reversed.

Pin Plunger Z-15G55-B Z-01H55-B






Model	Z-15G55-B	Z-01H55-B	
OF	250 to 430 gf	350 gf max.	
RF min.	114 gf	80 gf	
PT max.	2.2 mm	2.2 mm	
OT min.	0.13 mm	0.13 mm	
MD max.	0.06 mm	0.06 mm	
OP	15.9±0.4 mm		

Short Spring Plunger Z-15GD55-B Z-01HD55-B






Model	Z-15GD55-B	Z-01HD55-B	
OF max. RF min. PT max. OT min. MD max.	540 gf 114 gf 1.8 mm 1.6 mm 0.06 mm	370 gf 80 gf 1.9 mm 1.6 mm 0.06 mm	
ОР	21.5±0.5 mm		

Spring Plunger Z-15GK55-B






OF max. RF min.	540 gf 114 gf 2.3 mm
PT max. OT min. MD max.	1.6 mm 0.06 mm
OP	28.2±0.5 mm

Z-15GK355-B






OF max.	540 gf
RF min.	114 gf
PT max.	2.4 mm
OT min.	3.5 mm
MD max.	0.06 mm
OP	37.8±1.2 mm



- Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.
 - 2. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.

Panel Mount Plunger Z-15GQ55-B






OF max.	540 gf
RF min.	114 gf
PT max.	1.8 mm
OT min.	5.5 mm
MD max.	0.06 mm
OP	21.8±0.8 mm

Note: Do not use the M12 mounting screw and the case mounting hole at the same time, or the case may be damaged.

Panel Mount Roller Plunger Z-15GQ2255-B






- *1. Stainless-steel roller
 *2. Two hexagonal nuts (3 t × 17 width across flats)
 *3. Incomplete screw part with a maximum length of 1.5 mm.

case mounting hole at the same time, or the

Panel Mount Cross Roller Plunger Z-15GQ2155-B





- *1. Stainless-steel roller
 *2. Two hexagonal nuts (3 t × 17 width across flats)
 *3. Incomplete screw part with a maximum length of 1.5 mm.

PIM	ax.		1.8	mm	
OT min.		3.58 mm			
MD m	ıax.		0.0	mm	1
OP		3	3.4±	1.2 n	nm
Note:			use		

OF max.

RF min.

OF max. RF min.

case may be damaged.


540 gf 114 gf

540 gf 114 gf 1.8 mm PT max. OT min. 3.58 mm MD max 0.06 mm OP 33.4±1.2 mm Do not use the M12

mounting screw and the case mounting hole at the same time, or the case may be damaged.

Leaf Spring Z-15GL55-B





OF max.	200 gf
RF min.	14 gf
*OT min.	1.6 mm
MD max.	1.3 mm
FP max.	20.6 mm
OP	17.5±0.8 mm


When operating, be sure not to exceed 1.6 mm.




Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.

2. Unless otherwise specified, all units are in millimeters and a tolerance of \pm 0.4 mm applies to all dimensions.








OF max.	200 gf
RF min.	14 gf
* OT min.	1.6 mm
MD max.	1.3 mm
FP max.	31.8 mm
OP	28.6±0.8 mm

When operating, be sure not to exceed 1.6 mm.


Short Hinge Lever Z-15GW2155-B






OF max.	190 gf
RF min.	28 gf
OT min.	2 mm
MD max.	1 mm
FP max.	25 mm
OP	19±0.8 mm

Long Hinge Lever Z-15GW4455-B






OF max.	90 gf
RF min.	14 gf
OT min.	5.6 mm
MD max.	3.5 mm
FP max.	33 mm
OP	19±1.2 mm

Hinge Lever Z-15GW55-B






OF max.	100 gf
RF min.	14 gf
OT min.	5.6 mm
MD max.	2 mm
FP max.	28.2 mm
OP	19±0.8 mm

Short Hinge Roller Lever

Z-15GW2255-B Z-01HW2255-B





Model	Z-15GW2255-B	Z-01HW2255-B
OF max.	200 gf	200 gf
RF min.	42 gf	28 gf
OT min.	2.4 mm	2.4 mm
MD max.	0.8 mm	0.8 mm
FP max.	32.9 mm	
OP	30.2±0.4 mm	




Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.

2. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.

Hinge Roller Lever Z-15GW255-B






OF max.	130 gf
RF min.	21 gf
OT min.	4 mm
MD max.	1.6 mm
FP max.	36.5 mm
OP	30.2±0.8 mm

Unidirectional Short Hinge Roller Lever

Z-15GW227755-B






OF max.	180 gf
RF min.	50 af
OT min.	2.4 mm
MD max.	0.8 mm
FP max.	43.6 mm
OP	41.3±0.8 mm

Reverse Hinge Lever * Z-15GM55-B






OF max.	200 gf
RF min.	28 gf
OT min.	5.6 mm
MD max.	0.89 mm
FP max.	23.8 mm
OP	19±0.8 mm

Reverse Short Hinge Roller Lever *






OF max.	580 gf
RF min.	170 gf
OT min.	2 mm
MD max.	0.28 mm
FP max.	31.8mm
ОР	29.4±0.4mm

Reverse Hinge Roller Lever * Z-15GM255-B






OF max.	270 gf
RF min.	56 gf
OT min.	4 mm
MD max.	0.64 mm
FP max.	35 mm
OP	30.2±0.8 mm

^{*} The pin plungers of reverse-type models are continuously pressed by the actuator levers with compression coil springs and the pin plungers are freed by operating the levers.



- Note: 1. All drawings show the switches with screw terminals. For versions with solder terminals, remove the "-B" from the end of the part number.
 - 2. Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.

Flexible Rod (Coil Spring) Z-15GNJ55-B




OF max. PT max.	50 gf (20 mm)
TT max.	40 mm

- *1. Operation is possible in any direction other than the axial direction (indicated by the arrow ♣).
 *2. Use only the area within the top 30 mm of the rod as the operating part. (Do not use the area that falls within 80 mm from the mounting hole as the operating part. Using this area may cause damage to the nylon rod.

Flexible Rod (Steel Wire) Z-15HNJS55-B





OF max. 15 gf (25 mm)

- *1. Operation is possible in any direction other than the axial direction (indicated by the arrow ♣).

 *2. Use only the area within the top 30 mm of the rod as the operating part. (Do not use the area that falls within 100 mm from the mounting hole as the operating part.

 Using this area may cause damage to the steel wire.)

 *3. The steel wire can be replaced if damaged.


 (Model: Lever for HNJS55)


■ Drip-proof Models (with Terminal Protective Cover)

Note: Unless otherwise specified, all units are in millimeters and a tolerance of \pm 0.4 mm applies to all dimensions.

Pin Plunger Z-15GA55-B5V










OF max.	250 to 430 gf
RF min.	114 gf
PT max.	2.2 mm
OT min.	0.13 mm
MD max.	0.06 mm
OP	15.9±0.4 mm

Z-15GK3A55-B5V









OF max.	540 gf
RF min.	114 gf
PT max.	2.4 mm
OT min.	3.5 mm
MD max.	0.06 mm
OP	37.8±1.2 mm

Panel Mount Plunger Z-15GQA55-B5V







OF max.	540 gf
RF min.	114 gf
PT max.	1.8 mm
OT min.	5.5 mm
MD max.	0.06 mm
OP	21.8±0.8 mm

Note: Do not use the M12

mounting screw and the case mounting hole at the same time, or the case may be damaged.


540 gf 114 gf 1.8 mm


3.58 mm 0.06 mm

*1. Stainless-steel plunger *2. Two hexagonal nuts (2 t \times 14 width across flat) *3. Two lock nuts (2 t \times 15.6 width across flats)

Panel Mount Roller Plunger Z-15GQ22A55-B5V








OP 33.4±1.2 mm


OF max. RF min. PT max. OT min. MD max.

 Stainless-steel roller *2. Two hexagonal nuts (3 t × 17 width across flats)

Panel Mount Cross-roller Plunger Z-15GQ21A55-B5V







 Stainless-steel 	roller	
*2. Two hexagonal	nuts (3 t × 17 width across	flats

OF max.	540 gf
RF min.	114 gf
PT max.	1.8 mm
OT min.	3.58 mm
MD max.	0.06 mm
OP	33.4±1.2 mm


Note: Do not use the M12 mounting screw and the case mounting hole at the same time, or the case may be damaged.



Note: Unless otherwise specified, all units are in millimeters and a tolerance of ± 0.4 mm applies to all dimensions.

Long Hinge Lever Z-15GW44A55-B5V






OF max.	90 gf
RF min.	14 gf
OT min.	5.6 mm
MD max.	3.5 mm
FP max.	33 mm
OP	19±1.2 mm

Hinge Lever Z-15GWA55-B5V






OF max.	100 gf
RF min. OT min. MD max.	14 gf 5.6 mm 2 mm
FP max.	28.2 mm
ОР	19±0.8 mm

Short Hinge Roller Lever Z-15GW22A55-B5V







OF max.	200 gf
RF min.	42 gf
OT min.	2.4 mm
MD max.	0.8 mm
FP max.	32.9 mm
OP	30.2±0.4 mm

Hinge Roller Lever Z-15GW2A55-B5V








OF max.	130 gf
RF min.	21 gf
OT min.	4 mm
MD max.	1.6 mm
FP max. OP	36.5 mm 30.2±0.8 mm

Unidirectional Short Hinge Roller Lever Z-15GW2277A55-B5V






OF max.	180 gf
RF min.	50 gf
OT min.	2.4 mm
MD max.	0.8 mm
FP max.	43.6 mm
OP	41.3±0.8 mm
	l .




■ Drip-proof Models (with Molded Terminal Cover)

Note: Unless otherwise specified, all units are in millimeters and a tolerance of \pm 0.4 mm applies to all dimensions.

L/R Type (The following illustration is the R type.)





Size (mm) Lead wire	а	b	С
VSF	12	4	12
VCT	19	11	16

Lead Wire Specifications

Specifications Lead wire	Nominal cross sectional area (mm²)	Finished outer diameter (mm)	Connection to terminal	Length (m)
VSF (single-core, vinyl cord)		Approx. 3.1 dia.	Black: COM	
VCT (vinyl-insulated cable)	1.25	Three-core: approx. 10.5 dia.	White: NO Red: NC	1, 3

Note: 1. No models with molded terminals are approved by UL, CSA, or EN.


2. Molded terminals are not available on all models. Contact your OMRON representative for applicable products.


■ Maintained Contact Models

Note: Unless otherwise specified, all units are in millimeters and a tolerance of \pm 0.4 mm applies to all dimensions.

Pin Plunger **Z-15ER**







*1. Stainless steel plunger *2. Plastic plunger

Plunger


OF	200 to 255 gf
PT max.	0.4 mm
OT min.	0.13 mm
OP	15.9±0.4 mm


Reset Button

OFmax.	56 to 285 gf
OTmin.	0.4 mm

Slim Spring Plunger Z-15ESR







Plunger


OF max.	270 gf
PT max.	0.4 mm
OT min.	1.6 mm
OP	28.2±0.5 mm

Reset Button

|--|

Hinge Lever Z-15EWR





Lever Tip

OF max.	55 gf
OT min.	5.6 mm
FP max.	28.2 mm
OP	19±0.8 mm

Reset Button

OF max.	300 gf
OT min.	0.4 mm

Safety Precautions

Be sure to read the precautions and information common to all Snap Action and Detection Switches, contained in the Technical User's Guide, "Snap Action Switches, Technical Information" for correct use.

Precautions for Safe Use **Terminal Connection**


When soldering lead wires to the Switch, make sure that the capacity of the soldering iron is 60 W maximum. Do not take more than 5 s to solder any part of the Switch. The characteristics of the Switch will deteriorate if a soldering iron with a capacity of more than 60 W is applied to any part of the Switch for 5 s or more.

Operation

- Make sure that the switching frequency or speed is within the specified range.
- 1. If the switching speed is extremely slow, the contact may not be switched smoothly, which may result in a contact failure or contact welding.
- 2. If the switching speed is extremely fast, switching shock may damage the Switch soon. If the switching frequency is too high, the contact may not catch up with the speed.
 - The rated permissible switching speed and frequency indicate the switching reliability of the Switch.
 - The life of a Switch is determined at the specified switching speed. The life varies with the switching speed and frequency even when they are within the permissible ranges. In order to determine the life of a Switch model to be applied to a particular use, it is best to conduct an appropriate durability test on some samples of the model under actual conditions.
- Make sure that the actuator travel does not exceed the permissible OT position. The operating stroke must be set to 70% to 100% of

Precautions for Correct Use Mounting Location

- Do not use the switch alone in atmospheres such as flammable or explosive gases. Arcing and heat generation associated with switching may cause fires or explosions.
- · Switches are generally not constructed with resistance against water. Use a protective cover to prevent direct spraying if the switch is used in locations subject to splashing or spurting oil or water, dust adhering.



· Install the switch in a location that is not directly subject to debris and dust from cutting. The actuator and the switch body must be protected from accumulated cutting debris and dirt.



- Do not use the switch in locations subject to hot water (greater than 60°C) or in water vapor.
- Do not use the switch outside the specified temperature and atmospheric conditions.

The permissible ambient temperature depends on the model. (Refer to the specifications in this catalog.) Sudden thermal changes may cause thermal shock to distort the switch and result in faults.



• Mount a cover if the switch is to be installed in a location where worker inattention could result in incorrect operation or accidents.



- Subjecting the switch to continuous vibration or shock may result in contact failure or faulty operation due to abrasion powder and in reduced durability. Excessive vibration or shock will cause the contacts to operate malfunction or become damaged. Mount the switch in a location that is not subject to vibration or shock and in a direction that does not subject the switch to resonance
- If silver contacts are used with relatively low frequency for a long time or are used with microloads, the sulfide coating produced on the contact surface will not be broken down and contact faults will result. Use a microload switch that uses gold contacts.
- Do not use the switch in atmospheres with high humidity or heat or in harmful gases, such as sulfide gas (H2S, SO2), ammonia gas (NH₃), nitric acid gas (HNO₃), or chlorine gas (Cl₂). Doing so may impair functionality, such as with damage due to contacting faults or corrosion.
- The switch includes contacts. If the switch is used in an atmosphere with silicon gas, arc energy may cause silicon oxide (SiO₂) to accumulate on the contacts and result in contact failure. If there is silicon oil, silicon filling, silicon wiring, or other silicon products in the vicinity of the switch, use a contact protection circuit to limit arcing and remove the source of the silicon gas.

Mounting

Always make sure that the power is turned OFF before mounting, removing, or wiring the Switch, or performing maintenance. Electric shock or burning may occur.

Selecting Models

We recommend using Drip-proof Models (protection equivalent to IP62) in locations subject to floating dirt and dust. Other models do not have a protective structure.

Wiring

For wiring, use a wire size that is appropriate for the applied voltage and the supplied current. When soldering the Switch, make sure that the capacity of the soldering iron is 60 W maximum. Do not take more than 5 s to solder any part of the Switch. Using the Switch with incomplete soldering may result in errors and heat, which may cause burning. The characteristics of the Switch will deteriorate if a soldering iron with a capacity of more than 60 W is used or if any part of the Switch is soldered for 6 s or longer.



Tightening

The suitable tightening torque for screw terminals is given below.

- Screw terminals except for those on Split-contact Models (Z-10FY-B): 0.78 to 1.18 N·m
- · Screw terminals on Split-contact Models (Z-10FY-B): 0.49 to 1.18 N·m

Operation

- Make sure that the switching speed and frequency are is within the specified ranges.
- 1. If the switching speed is extremely slow, the contacts may not be switched smoothly, which may result in a contact failure or contact welding.
- 2. If the switching speed is extremely fast, switching shock may damage the Switch prematurely. If the switching frequency is too high, the contacts may not be able to keep up with the speed.
 - The rated permissible switching speed and frequency indicate the switching reliability of the Switch.
 - The life of a Switch is determined at the specified switching speed. The life varies with the switching speed and frequency even when they are within the permissible ranges.
 - Always conduct appropriate durability tests under actual conditions before using a Switch.
- Make sure that the actuator travel does not exceed the permissible OT position. The operating stroke must be set to 70% to 100% of the rated OT.

Panel Mount Switch (Z-15 Q , Z-01 Q)

- When mounting the panel mount plunger model with screws on a side surface, be careful of the dog angle and operation speed. Excessive dog angle or operation speed may damage the Switch.
- When using the panel mount plunger model mounted with screws on a side surface, be careful not to apply a large shock. Applying a shock exceeding 1,000 m/s² may damage the Switch.
- When using the panel mount plunger model mounted with screws on a side surface, remove the hexagonal nuts from the actuator.


High-sensitivity Switch (Z-15H)/ Extra-high-sensitivity Switch (Z-15H2)

- When using the Switch in a DC circuit, be sure to provide an arc suppressor as well because the small contact gap of the Switch may result in contact troubles.
- In an application where a high repeat accuracy is required, limit the current that flows through the Switch to within 0.1 A. Also, use a relay to control a high-capacity load if the Switch is connected to such a load. (In this case, the exciting current of the relay coil is the load of the Switch.)
- Do not apply a force of 19.6 N or higher to the pin plunger.
- Exercise care that the environment conditions such as temperature and humidity do not change abruptly.

Micro Load Applicable Range

Using a model for ordinary loads to open or close the contact of a micro load circuit may result in faulty contact. Use models that operate in the following range. However, even when using micro load models within the operating range shown here, if inrush current occurs when the contact is opened or closed, it may increase contact wear and so decrease durability. Therefore, insert a contact protection circuit where necessary.


The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% ($\lambda_{60}).$ The equation, λ_{60} = 0.5×10-6/operations indicates that the estimated malfunction rate is less than 1/2,000,000 operations with a reliability level of 60%.




	Z-01H	Z-15□, Z-10FY
Minimum applicable load	1 mA at 5 VDC	160 mA at 5 VDC

Models with Drip-proof Terminal Cover (Z-□A55-B5V) Wiring

• To attach the Protective Cover to the case, hold the cover in almost parallel to the case and then push it to the case. If the cover is pushed diagonally, the rubber packing may slip off, degrading the sealability of the Switch.



• Use round solderless terminals having the following dimensions to connect leads to the terminals. Tighten the screws of terminals to a torque of 0.78 to 1.18 N·m. Use the terminal shown below.



- A cable 8.5 to 10.5 mm in diameter can be applicable to the sealing rubber of the lead outlet of the Switch. A two-core or three-core VCT cable having a cross-sectional area of 1.25 mm² is especially
- M4 small screws with spring toothed washer are used as the terminal screws.



Drip-proof Switch (Z-□55)

- The Switch is not perfectly oil-tight; so do not dip it in oil or water.
- The rubber boots are made from weather-resistive chloroprene rubber.
- Do not use Basic Switches in places with radical changes in temperature.
- Rubber boots and rubber caps will tend to harden at lower ambient temperatures. If an Actuator is used in a pressed state for an extended period of time at low temperatures, it may return slowly or it may not return at all. OMRON can provide special Actuators for use at low temperature with rubber boots or rubber caps made of silicon rubber, which has superior resistance to cold. Ask your OMRON representative for details.

Split-contact Switch (Z-10F□Y)


The applicable current varies depending on how the contacts are used. If the Switch is connected in series, the Switch can endure a current 1.5 to 2 times higher than the current that can be applied in parallel connection.

Flexible Rod Switch (Z-15 NJ 55, Drip-proof)

- · When the rod is fully swung, the Switch may operate when the lever returns, causing chattering. Use a circuit that compensates for chattering wherever possible.
- Do not switch the rod to the fullest extent when the Switch is to break a power circuit because such a practice may cause metal deposition to occur between the mating contacts of the Switch.

Other Precautions

• Do not apply excessive force with a screwdriver or other tool when attaching or removing the Protective Cover. Doing so may deform the Switch.



- The Drip-proof Terminal Protective Cover (AP-DV) can be used only with Switches with model numbers ending in "-B5V."
- The Drip-proof Terminal Protective Cover is only available for maintenance purposes.

Accessories (Order Separately)

Refer to "Z/A/X/DZ Common Accessories" datasheet for details about Terminal Covers, Separators, and Actuators.


Drip-proof Terminal Cover (Order Separately)

The Drip-proof Terminal Protective Cover is provided for maintenance for Z
A55-B5V Switches.


Ordering Information

Name	Model
Drip-proof Terminal Protective Cover	AP-DV

Dimensions (Unit: mm)







Omron Electronic Components, LLC

Terms and Conditions of Sales

I. GENERAL

Definitions: The words used herein are defined as follows.

Terms: These terms and conditions

(b) Seller: Omron Electronic Components LLC and its subsidiaries

The buyer of Products, including any end user in section III through VI Buyer: (c)

Products: Products and/or services of Seller Including without limitation Including:

- Offer: Acceptance: These Terms are deemed part of all quotations, acknowledgments, invoices, purchase orders and other documents, whether electronic or in writing, relating to the sale of Products by Seller. Seller hereby objects to any Terms proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these
- <u>Distributor</u>: Any distributor shall inform its customer of the contents after and including section III of these Terms.

- Prices: Payment: All prices stated are current, subject to change without notice by Seller. Buyer agrees to pay the price in effect at the time the purchase order is accepted by Seller. Payments for Products received are due net 30 days unless otherwise stated in the invoice. Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice.
- Discounts: Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (a) the invoice is paid according to Seller's payment terms and (b) Buyer has no past due amounts owing to Seller.
- Interest: Seller, at its option, may charge Buyer 1.5% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the stated terms. Orders: Seller will accept no order less than 200 U.S. dollars net billing.

- Currencies: If the prices quoted herein are in a currency other than U.S. dollars, Buyer shall make remittance to Seller at the then current exchange rate most favorable to Seller; provided that if remittance is not made when due, Buyer will convert the amount to U.S. dollars at the then current exchange rate most favorable to Seller available during the period between the due date and the date remittance is actually made.
- Governmental Approvals: Buyer shall be responsible for all costs involved in obtaining any government approvals regarding the importation or sale of the Products.
- Taxes: All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Seller or required to be collected directly or indirectly by Seller for the manufacture, production, sale, delivery, importation, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Seller.
- Financial: If the financial position of Buyer at any time becomes unsatisfactory to Seller, Seller reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Seller may (without liability and in addition to other remedies) cancel any unshipped portion of Products sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid
- Cancellation; Etc: Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Seller fully against all costs or expenses arising in connection therewith.
- Force Majeure: Seller shall not be liable for any delay or failure in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.

Shipping: Delivery: Unless otherwise expressly agreed in writing by Seller:
(a) All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Seller), at which point title to and all risk of loss of the Products shall pass from Seller to Buyer, provided that Seller shall retain a security interest in the Products until the full purchase price is paid by Buyer;

Delivery and shipping dates are estimates only; and

- Seller will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.
- 12. Claims: Any claim by Buyer against Seller for shortage or damage to the Products occurring before delivery to the carrier or any claim related to pricing or other charges must be presented in detail in writing to Seller within 30 days of receipt of shipment.

III. PRECAUTIONS

- Suitability: IT IS THE BUYER'S SOLE RESPOINSIBILITY TO ENSURE THAT ANY OMRON PRODUCT IS FIT AND SUFFICIENT FOR USE IN A MOTORIZED VEHICLE APPLICATION. BUYER SHALL BE SOLELY RESPONSIBLE FOR DETERMINING APPROPRIATENESS OF THE PARTICULAR PRODUCT WITH RESPECT TO THE BUYER'S APPLICATION INCLUDING (A) ELECTRICAL OR ELECTRONIC COMPONENTS, (B) CIRCUITS, (C) SYSTEM ASSEMBLIES, (D) END PRODUCT, (E) SYSTEM, (F) MATÉRIALS OR SUBSTANCES OR (G) OPERATING ENVIRONMENT. Buyer acknowledges that it alone has determined that the Products will meet their requirements of the intended use in <u>all</u> cases. Buyer must know and observe all prohibitions of use applicable to the Product/s.
- Use with Attention: The followings are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible use of any Product, nor to imply that any use listed may be suitable for any Product:
 - Outdoor use, use involving potential chemical contamination or electrical interference.

(b) Use in consumer Products or any use in significant quantities.

Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and

installations subject to separate industry or government regulations.

(d) Systems, machines, and equipment that could present a risk to life or property.

Prohibited Use: NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Motorized Vehicle Application: USE OF ANY PRODUCT/S FOR A MOTORIZED VEHICLE APPLICATION MUST BE EXPRESSLY STATED IN THE SPECIFICATION BY

SELLER.

<u>Programmable Products:</u> Seller shall not be responsible for the Buyer's programming of a programmable Product.

IV. WARRANTY AND LIMITATION

- Warranty: Seller's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Seller (or such other period expressed in writing by Seller). SELLER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT ALL OTHER WARRANTIES, NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS.
- Buyer Remedy: Seller's sole obligation hereunder shall be to replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product or, at Seller's election, to repay or credit Buyer an amount equal to the purchase price of the Product; provided that there shall be no liability for Seller or its affiliates unless Seller's analysis confirms that the Products were correctly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be
- approved in writing by Seller before shipment.

 <u>Limitation on Liability</u>: SELLER AND ITS AFFILIATES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. FURTHER, IN NO EVENT SHALL LIABILITY OF SELLER OR ITS AFFILITATES EXCEED THE INDIVIDUAL PRICE OF THE PRODUCT ON WHICH LIABILITY IS ASSERTED.
- Indemnities: Buyer shall indemnify and hold harmless Seller, its affiliates and its employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, investigation, litigation or proceeding (whether or not Seller is a party) which arises or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products.

V. INFORMATION; ETC.

- Intellectual Property: The intellectual property embodied in the Products is the exclusive property of Seller and its affiliates and Buyer shall not attempt to duplicate it in any way without the written permission of Seller. Buyer (at its own expense) shall indemnify and hold harmless Seller and defend or settle any action brought against Seller to the extent that it is based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
- Property: Confidentiality: Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Seller. All information and materials supplied by Seller to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly prevent disclosure to any third party.

 <u>Performance Data</u>: Performance data is provided as a guide in determining suitability
- and does not constitute a warranty. It may represent the result of Seller's test conditions, and the users must correlate it to actual application requirements.
- Change In Specifications: Product specifications and descriptions may be changed at any time based on improvements or other reasons. It is Seller's practice to change part numbers when published ratings or features are changed, or when significant engineering changes are made. However, some specifications of the Product may be changed without any notice.
- Errors And Omissions: The information on Seller's website or in other documentation has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.
- Export Controls: Buyer shall comply with all applicable laws, regulations and licenses regarding (a) export of the Products or information provided by Seller; (b) sale of Products to forbidden or other proscribed persons or organizations; (c) disclosure to noncitizens of regulated technology or information.

VI. MISCELLANEOUS

- <u>Waiver</u>: No failure or delay by Seller in exercising any right and no course of dealing between Buyer and Seller shall operate as a waiver of rights by Seller.
- Assignment: Buyer may not assign its rights hereunder without Seller's written consent. Law: These Terms are governed by Illinois law (without regard to conflict of laws). Federal and state courts in Cook County, Illinois have exclusive jurisdiction for any dispute hereunder.
- Amendment: These Terms constitute the entire agreement between Buyer and Seller relating to the Products, and no provision may be changed or waived unless in writing signed by the parties.
- Severability: If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision.

Certain Precautions on Specifications and Use

- <u>Suitability for Use</u>. Seller shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in Buyer's application or use of the Product. At Buyer's request, Seller will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:
 - Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.
 - (ii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government

 - Use in consumer products or any use in significant quantities. Systems, machines and equipment that could present a risk to life or property. Please know and observe all prohibitions of use applicable to this

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

- <u>Programmable Products.</u> Seller shall not be responsible for the user's programming of a programmable product, or any consequence thereof. <u>Performance Data.</u> Performance data given in this publication is provided as
- a guide for the user in determining suitability and does not constitute a war-ranty. It may represent the result of Seller's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to
- correlate it to actual application requirements. Actual performance is subject to Seller's Warranty and Limitations of Liability.

 Change in Specifications. Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are change, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Seller representative at any time to confirm actual specifications of purchased Product. your application. Please consult will your speller representative at any time to confirm actual specifications of purchased Product.

 <u>Errors and Omissions</u>. The information in this publication has been carefully
- checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors, or omissions.

 RoHS Compliance. Where indicated, our products currently comply, to the best of our knowledge as of the date of this publication, with the requirements of the European Union's Directive on the Restriction of certain Hazardous Substances ("RoHS"), although the requirements of RoHS do not take effect until July 2006. These requirements may be subject to change. Please consult until July 2006. These requirements may be subject to change. Please consult our website for current information.

Complete "Terms and Conditions of Sale" for product purchase and use are on Omron's website at http://www.components.omron.com - under the "About Us" tab, in the Legal Matters section.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON OMRON ELECTRONIC COMPONENTS LLC

55 E. Commerce Drive, Suite B Schaumburg, IL 60173

847-882-2288

Cat. No. X303-E-1

11/09

Specifications subject to change without notice

USA - http://www.components.omron.com

OMRON ON-LINE

Global - http://www.omron.com

Printed in USA