# Three-phase monitoring relays Product group picture



# Three-phase monitoring relays Table of content

Three phase monitoring relays	
Product group picture	2/27
Table of contents	2/28
Benefits and advantages, Applications	2/29
Notes	2/30
Selection and conversion	2/31
Ordering details	2/33
Function diagrams	2/35
Connection diagrams, DIP switches	2/40
Connection diagrams, DIP switches, Rotary switches	2/41
Notes	2/42
Technical data	2/43


## Three-phase monitoring relays Benefits and advantages, Applications

### Characteristics of the CM range three-phase monitors

- Adjustable phase unbalance threshold value 1)
- Adjustable ON-delay/OFF-delay time 1)
- Dual frequency measuring 50/60 Hz
- Powered by the measuring circuit
- 1 n/o contact, 1 or 2 contacts
- LED status indication
- Approvals: (I) us (I) (CB scherus







- Phase loss monitoring
- Phase sequence monitoring 1)
- Over- and undervoltage monitoring (fixed or adjustable)1)
- Wide-range operating voltage guarantees world-wide operation

#### Phase unbalance monitoring

If the supply by the three-phase system is unbalanced due to uneven distribution of the load, the motor will convert a part of the energy into reactive power. This energy gets lost unexploited; also the motor is exposed to higher thermal strain. Other thermal protection devices fail to detect continuing unbalances which can lead to damage or destruction of the motor. The CM range three-phase monitors with phase unbalance monitoring can reliably detect this critical situation.

### Phase sequence

Changing the phase sequence during operation or a wrong phase sequence prior to startup causes a change of the rotational direction of the connected device. Generators, pumps or fans rotate in the wrong direction and the installation is no longer working properly. Especially for moveable equipment, such as construction machinery, phase sequence detection prior to the startup process is highly reasonable.

#### Phase loss

In case of phase loss, undefined stats of the installation are likely to occur. E.g. the startup process of motors is disturbed. All three-phase monitors of the ABB CM range detect a phase loss as soon as the voltage of one phase drops below 60% of its nominal value.

#### **Expanded functionality**

ABB's new generation of three-phase monitoring relays feature additional functions making the application field for the devices considerably larger.

#### Selectable phase sequence monitoring

The phase sequence monitoring can be switched off by means of a rotary switch or a DIP switch. This enables monitoring of three-phase mains where phase sequence is not relevant for the application, for example in case of motors with forward and reverse rotation, heating applications, etc.

#### Voltage monitoring

All electric devices can be damaged when operated continuously in a network with out-of-range voltages. For example, safe starting is not ensured in case of undervoltage. Also, the switching state of a contactor is not clearly defined when operated in a "forbidden" voltage range. This can lead to undefined stats of the installtion and cause damage or destruction of valuable parts.

#### Structure of the type designation

 $CM-_ x.yz$ 

x: width of enclosure

y: Control supply voltage / measuring range

1	110, 115, 120, 127 V supply systems (phase-neutral)
2	220, 230, 240 V supply systems (phase-neutral)
3	200, 208, 220, 230, 240, 257, 260 V supply systems (phase-phase)
4	440, 460 V supply systems (phase-phase)
5	480, 500 V supply systems (phase-phase)
6	575, 600 V supply systems (phase-phase)
7	660, 690 V supply systems (phase-phase)
8	200, 400 V supply systems (phase-phase)

### z: Rated frequency / output circuit

1	50/60 Hz - 1x2 c/o
2	50/60 Hz – 1x2 or 2x1 c/o
3	50/60/400 Hz - 1x2 oder 2x1 c/o



- 1 Threshold value V<sub>min</sub>/V<sub>max</sub>
- 2 R/T: yellow LED Relay status, timing


F1: red LED fault message

F2: red LED failure:

- overvoltage: F1
- undervoltage: F2
- phase unbalance: F1 and F2 constant
- phase loss: F1 on F2 flashing
- phase sequence: F1 and F2 alternately flashing
- 3 Adjustment of the tripping delay
- 4 Time setting 0.1-10 s Phase sequence and phase loss are indicated without any time delay

<sup>1)</sup> depending on device type

# Three-phase monitoring relays Notes



# Three-phase monitoring relays Selection and conversion

Three-phase monitoring relays	nber	8	00	8	00	00	00	00	00	00	00	00	00	00	00	00	00	00	00	8	8	8	00	8	00	
	order numbe	1SVR 550 881 R9400	882 R9500	870 R9400	871 R9500	1SVR 550 824 R9100	1SVR 430 824 R9300	1SVR 730 784 R2300	1SVR 740 784 R2300	1SVR 730 784 R3300	1SVR 740 784 R3300	1SVR 730 794 R1300	1SVR 740 794 R1300	1SVR 730 794 R3300	1SVR 740 794 R3300	1SVR 730 794 R2300	1SVR 740 794 R2300	1SVR 730 774 R1300	1SVR 740 774 R1300	1SVR 730 774 R3300	1SVR 740 774 R3300	1SVR 730 885 R1300	1SVR 740 885 R1300	1SVR 730 885 R3300	R3300	
	ord	881	882	870	871	824	824	784	784	784	784	794	794	794	794	794	794	774	774	774	774	885	885	885	1SVR 740 885	
		250	550	550	550	250	430	730	740	730	740	730	740	730	740	730	740	730	740	730	740	730	740	730	740	
		Ä.	1SVR	1SVR	1SVR	Ä.	Ä.	Ä	Ä	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	Ä	Ä	Ä	Ä	Ä	Ä	Y.	Ä.	Ä.	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	Ä	Ä	Ä	Y.	
	0	-	8	8	8	8	8	5	5	8	5	5	5	5	5	5	5	50	5	8	8	$\overline{}$				
	Type							318	31P	418	41P	318	31P	418	41P	318	31P	31S	31P	41S	# #	CM-MPS.11S	CM-MPS.11P	CM-MPS.21S	CM-MPS.21P	
		닒	H	Š	Š	밅	FS	SS.	SS.	SS.	SS.	VS.	VS.	VS.	VS.	VS.8	VS.8	AS.	AS.	AS.	AS.	IPS.	IPS.	IPS.	IPS.	
Rated control supply voltage U <sub>s</sub>		CM-PBE	CM-PBE	CM-PVE	CM-PVE	CM-PFE	CM-PFS	CM-PSS.31S	CM-PSS.31P	CM-PSS.41S	CM-PSS.41P	CM-PVS.31S	CM-PVS.31P	CM-PVS.41S	CM-PVS.41P	CM-PVS.81S	CM-PVS.81P	CM-PAS.31S	CM-PAS.31P	CM-PAS.41S	CM-PAS.41P	Σ	₹	Σ	M-N	
Phase to Phase		10	0	O	0	0	O	O	0	0	0	O	0	O	O	O	O	O	0	0	0	10	0	O	O	
160-300 V AC	T											•	•					•	•							
200-400 V AC 200-500 V AC	+															•	•					-				
208-440 V AC	+					-	-															-				
300-500 V AC	十					-																$\vdash$				
320-460 V AC	$\perp$			•	•																					
350-580 V AC 380 V AC	+	_											_									_	<u> </u>			
380-440 V AC	+							•	•													╁				
400 V AC	t	•	-								•															
450-720 V AC																										
530-820 V AC	丄																									
Phase to Neutral 90-170 V AC	Т	Π	Γ	Π	Π			Π		Π	Π		Г							Ι	Π	Τ.				1
180-280 V AC	$\top$																					† <b>-</b>	-	-	•	
185-265 V AC	I			•																						
220-240 V AC 230 V AC	+	-																								
Rated frequency	_								<u> </u>																	<u> </u>
50 Hz	Т																									
50/60 Hz	┺		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•		•	•	•	
50/60/400 Hz Suitable for monitoring													<u> </u>									<u> </u>				
Single-phase mains	Т	•											Π						П		Π	T .	•		•	
Three-phase mains	I		•	•	•	•	•	•		•	•	•		•	•	•		•		•	•	•	•	•	•	
Monitoring function Phase failure	т	Γ_	Ι_	_	Γ_	Ι_	Γ_	Γ_		Ι_	Ι_		Γ_	_	_	Γ_	_	_		Τ_	Π_	Τ_	_	Г_		
Phase sequence	╁	-	-	-	-		-	ad	ad	ad	ad	■ ad	■ ad	ad	ad	ad	ad	-				■ ad	ad	ad	■ ad	
Automatic phase sequence correction																										
Overvoltage	╄	_		•				•	•	•		•	•	•	•	•	•						•		•	
Undervoltage Unbalance	+	-		•	•			•	•	-	-	•	•	•	•	•	•		<u> </u>	-	<u> </u>	-	•	-	-	
Neutral	+	-		•														-	-	-	-	-	-	-	-	
Overfrequency		Ē		_																		Ť				
Underfrequency	$\perp$	L			-			_									L .			L.	L.	L.				
Thresholds		fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	ad	ad	ad	ad	ad	ad							
Timing functions for tripping delay		П					fix						Π					ad	ad	ad	ad	П				
Timing functions for tripping delay  ON delay						C.																				
ON delay On and OFF delay	L	fix	fix	fix	fix	fix							ad	ad	ad	ad	ad				1	ad	ad		ad	
ON delay		fix	fix	fix	fix	fix		ad	ad	ad	ad	ad	au		au	0.0.	0.0		_	+	-	$\overline{}$	au	ad		
ON delay On and OFF delay		fix	fix	fix	fix	TIX			ad		ad	_	au		au		9.0	300		8		$\overline{}$	au			
ON delay On and OFF delay		fix	fix	fix	fix	TIX		R2300	ad	R3300	ad	R1300	au	R3300	au			R1300		R3300		R1300	au	R3300		
ON delay On and OFF delay		fix	fix	fix	fix	TIX		R2300	ad	R3300	ad	R1300	au	R3300	au			74 R1300		74 R3300		R1300	au	R3300		
ON delay On and OFF delay		fix	fix	fix	fix	ŤΙΧ		784 R2300	ad	784 R3300	ad	794 R1300	au	R3300	au			774		774		885 R1300	au	885 R3300		
ON delay On and OFF delay		fix	fix	fix	fix	TIX		630 784 R2300	ad	630 784 R3300	ad	630 794 R1300	au	630 794 R3300	au			774		630 774		630 885 R1300	au	630 885 R3300		
ON delay On and OFF delay		fix	fix	fix	fix	İΙΧ		630 784 R2300	ad	630 784 R3300	ad	630 794 R1300	au	SVR 630 794 R3300	au			774		630 774		630 885 R1300	au	630 885 R3300		
ON delay On and OFF delay		fix	fix	fix	fix	TIX.		1SVR 630 784 R2300	ad	1SVR 630 784 R3300	ad	1SVR 630 794 R1300	au	1SVR 630 794 R3300	au	1SVR630794R2300		1SVR 630 774		1SVR 630 774		1SVR 630 885 R1300	au	1SVR 630 885 R3300		
ON delay On and OFF delay	ion		fix	fix	fix	TIX		1SVR 630 784 R2300	ad	1SVR 630 784 R3300	ad	1SVR 630 794 R1300	au	1SVR 630 794 R3300	au	1SVR630794R2300		1SVR 630 774		1SVR 630 774		1SVR 630 885 R1300	au	1SVR 630 885 R3300		
ON delay On and OFF delay	Conversion		fix	fix	fix	TIX.		630 784 R2300	ad	630 784 R3300	ad	630 794 R1300	au	SVR 630 794 R3300	au			774		630 774		630 885 R1300	au	630 885 R3300		

# Three-phase monitoring relays Selection and conversion

CM-MPS.31	1SVR 630 884 R1300	ad	ad	-	<b>a</b> u	■ ad	•	•										CM-MPS.31S	1SVR 730 884 R1300	
		ad	ad	•	<b>a</b> u	■ ad		-								_		CM-MPS.31P	1SVR 740 884 R1300	
CM-MPS.41	1SVR 630 884 R4300	ad	ad	•	•	■ ad	•	-							-		O	CM-MPS.41S	1SVR 730 884 R4300	_
		ad	ad	•	•	■ ad		-							-		O	CM-MPS.41P	1SVR 740 884 R4300	
CM-MPS.23	CM-MPS.23 1SVR 630 885 R4300	ad	ad	•	ad	■ ad	•	-			-						O	CM-MPS.23S	1SVR 730 885 R4300	
		ad	ad	•	ad	■ ad	•	•			•						O	CM-MPS.23P	1SVR 740 885 R4300	
CM-MPS.43	CM-MPS.43 1SVR 630 884 R4300	ad	ad	•	ad	■ ad	-	-							-		O	CM-MPS.43S	1SVR 730 884 R4300	
		ad	ad	-	ad	■ ad	•	-							-		O	CM-MPS.43P	1SVR 740 884 R4300	
CM-MPN.52	CM-MPN.52 1SVR 650 487 R8300	ad	ad	•	ad	■ ad		-						•			O	CM-MPN.52S	1SVR 750 487 R8300	_
		ad	ad	•	ad	■ ad	•	-						•			O	CM-MPN.52P	1SVR 760 487 R8300	
CM-MPN.62	CM-MPN.62 1SVR 650 488 R8300	ad	ad	-	ad	■ ad	•	-					-				O	CM-MPN.62S	1SVR 750 488 R8300	
		ad	ad	•	ad	■ ad		-					-				O	CM-MPN.62P	1SVR 760 488 R8300	
CM-MPN.72	CM-MPN.72 1SVR 650 489 R8300	ad	ad	•	ad	■ ad	_	-				•					ပ	CM-MPN.72S	1SVR 750 489 R8300	_
		ad	ad	-	ad	■ ad	•	-				•					O	CM-MPN.72P	1SVR 760 489 R8300	
CM-UFS.2	1SVR 630 736 R1300		fix	fix	fix	fix	•		•	•			•				O	CM-UFS.2S	1SVR 730 736 R1300	
			fix	fix	fix	fix	-		•	•			•				O	CM-UFS.2P	1SVR 740 736 R1300	

# Three-phase monitoring relays Ordering details



CM-PBE



CM-PSS.41P



### Description

Only reliable and continuous monitoring of a three-phase network guarantees the trouble-free and economic operation of machines and installations.t

Ordering details

Rated control supply voltage = measuring voltage	Monitoring function	Neutral moni- toring	Туре	Order code	Price 1 pce	Weight (1 pce) kg (lb)
3x380-440 V AC, 220-240 V AC	Phase failure detection	yes	CM-PBE <sup>1)</sup>	1SVR550881R9400		0.08 (0.17)
3x380-440 V AC	(Single- and three-phase)	no	CM-PBE	1SVR550882R9500		0.08 (0.17)
3x320-460 V AC, 185-265 V AC	Over- / under- voltage and phase failure	yes	CM-PVE 1)	1SVR550870R9400		0.08 (0.17)
3x320-460 V AC	detection (Single- and three-phase)	no	CM-PVE	1SVR550871R9500		0.08 (0.17)
3x208-440 V AC	Phase sequence monitoring and		CM-PFE <sup>2)</sup>	1SVR550824R9100		0.08 (0.17)
3x200-500 V AC	phase failure detection (Three-phase)		CM-PFS <sup>2)</sup>	1SVR430824R9300		0.15 (0.33)
0000 \ / A O			CM-PSS.31S	1SVR730784R2300		0.132 (0.291)
3x380 V AC	Over- / under- voltage with		CM-PSS.31P	1SVR740784R2300		0.123 (0.271)
3x400 V AC	fixed threshold values ± 10 %		CM-PSS.41S	1SVR740784R3300		0.132 (0.291)
3x400 V AC			CM-PSS.41P	1SVR730784R3300		0.123 (0.271)
3x160-300 V AC			CM-PVS.31S	1SVR730794R1300		0.141 (0.311)
3X100-300 V AC	Over- and		CM-PVS.31P	1SVR740794R1300		0.132 (0.291)
3x300-500 V AC	under- voltage with adjustable		CM-PVS.41S	1SVR730794R3300		0.139 (0.306)
3X300-300 V AC	threshold values (Three-		CM-PVS.41P	1SVR740794R3300		0.131 (0.289)
3x200-400 V AC	phase) `		CM-PVS.81S	1SVR730794R2300		0.136 (0.300)
0.200-400 V AO			CM-PVS.81P	1SVR740794R2300		0.128 (0.282)
3x160-300 V AC			CM-PAS.31S	1SVR730774R1300		0.133 (0.293)
0X100-000 V AO	Phase unba- lance (Three-		CM-PAS.31P	1SVR740774R1300		0.124 (0.273)
3x300-500 V AC	phase)		CM-PAS.41S	1SVR730774R3300		0.132 (0.291)
0x000-000 v AC			CM-PAS.41P	1SVR740774R3300		0.123 (0.271)



<sup>1)</sup> The version with neutral monitoring is also suitable for monitoring single-phase mains. For this, all three external conductors (L1,L2,L3) have to be

<sup>&</sup>lt;sup>2)</sup> For applications where a reverse fed voltage >60% is expected, we recommend to use our three-phase monitoring relays for unbalance CM-PAS.xx

# Three-phase monitoring relays Ordering details



CM-MPS.23P




CM-MPN.52P

Rated control supply voltage = measuring voltage	Monitoring function	Neutral moni- toring	Туре	Order code	Price 1 pce	Weight (1 pce) kg (lb)
00 170 \ / A C			CM-MPS.11S	1SVR730885R1300		0.148 (0.326)
90-170 V AC	Multifunctional		CM-MPS.11P	1SVR740885R1300		0.137 (0.302)
180-280 V AC	(Three-phase phase failure	yes	CM-MPS.21S	1SVR730885R3300		0.146 (0.322)
180-280 V AC	detection, Phase		CM-MPS.21P	1SVR740885R3300		0.135 (0.298)
	sequence monitoring, overvoltage,		CM-MPS.31S	1SVR730884R1300		0.142 (0.313)
0000 500 1/ 40	undervoltage, Phase unba-		CM-MPS.31P	1SVR740884R1300		0.133 (0.293)
3x300-500 V AC	lance)	yes  no  yes	CM-MPS.41S	1SVR730884R3300		0.140 (0.309)
			CM-MPS.41P	1SVR740884R3300		0.132 (0.291)
400,000,1/40			CM-MPS.23S	1SVR730885R4300		0.149 (0.328)
180-280 V AC		yes	CM-MPS.23P	1SVR740885R4300		0.138 (0.304)
3x300-500 V AC	Multifunctional	yes no	CM-MPS.43S	1SVR730884R4300		0.148 (0.327)
3X300-300 V AC	(Three-phase phase failure detection.	110	CM-MPS.43P	1SVR740884R4300		0.137 (0.302)
3x350-580 V AC	Phase sequence		CM-MPN.52S	1SVR750487R8300		0.230 (0.507)
3X330-360 V AC	monitoring, overvoltage, undervoltage,		CM-MPN.52P	1SVR760487R8300		0.226 (0.498)
3x450-720 V AC	Phase unba- lance)	20	CM-MPN.62S	1SVR750488R8300		0.229 (0.505)
3x450-720 V AC		yes  no  yes	CM-MPN.62P	1SVR760488R8300		0.225 (0.496)
3x530-820 V AC		yes	CM-MPN.72S	1SVR750489R8300		0.224 (0.494)
IJSU-8∠U V A∪		no yes	CM-MPN.72P	1SVR760489R8300		0.220 (0.485)
3 x 400 V AC (L-L) /	see Three-		CM-UFS.2S	1SVR730736R1300		0.146 (0.322)
230 V AC (L-N)	Phase overview page	yes	CM-UFS.2P	1SVR740736R1300		0.134 (0.295)


# Three-phase monitoring relays Function diagrams

### Function diagrams - Three-phase monitoring CM-PBE




If all phases (and the neutral) are present, the output relay energizes after the start-up delay to is complete. If a phase failure occurs, the tripping delay t starts. When timing is complete, the output relay de-energizes. As soon as the voltage returns to the tolerance range, timing of to starts. When timing is complete, the output relay reenergizes automatically. The yellow LED glows when the output relay

#### Function diagrams - Three-phase monitoring CM-PVE



If all phases (and the neutral) are present with correct voltage, the output relay energizes after the start-up delay to is complete. If the voltage exceeds or falls below the fixed threshold value or if a phase failure occurs, the tripping delay t, starts. When timing is complete, the output relay de-energizes. As soon as the voltage returns to the tolerance range, timing of t<sub>s</sub> starts. When timing is complete, the output relay re-energizes automatically. The yellow LED glows when the output relay is energized.


#### Function diagram - CM-PFE



If all phases are present with the correct phase sequence, the output relay energizes after the start-up delay  $\boldsymbol{t}_{_{\!S}}$  is complete. If a phase failure or a phase sequence error occurs, the tripping delay to starts. When timing is complete, the output relay de-energizes. The yellow LED glows when the output relay is energized.

In case of motors which continue running with only two phases, the CM-PFE detects phase failure if the reverse fed voltage is less than 60 % of the originally applied voltage.

### Function diagram - CM-PFS



### ATTENTION

If several CM-PFS units are placed side by side and the control supply voltage is higher than 415 V, spacing of at least 10 mm has to be kept between the individual units

If all phases are present with the correct phase sequence, the output relay energizes after the start-up delay t is complete. If a phase failure or a phase sequence error occurs, the output relay de-energizes instantaneous. The yellow LED glows when the output relay is ener-

In case of motors which continue running with only two phases, the CM-PFS detects phase failure if the reverse fed voltage is less than 60 % of the originally applied voltage.

# Three-phase monitoring relays Function diagrams

## Phase sequence and phase failure monitoring CM-PSS.xx, CM-PVS.xx, CM.PAS.xx, CM-MPS.xx, CM-MPN.xx


Applying control supply voltage begins the fixed start-up delay  $t_{\rm s}.$  When  $t_{\rm s}$  is complete and all phases are present with correct voltage, the output relays energize and the yellow LED R/T glows.

#### Phase sequence monitoring

If phase sequence monitoring is activated, the output relays deenergize as soon as a phase sequence error occurs. The fault is displayed by alternated flashing of the LEDs F1 and F2. The output relays reenergize automatically as soon as the phase sequence is correct again.

#### Phase failure monitoring

The output relays de-energize instantaneous if a phase failure occurs. The fault is indicated by lightning of LED F1 and flashing of LED F2. The output relays re-energize automatically as soon as the voltage returns to the tolerance range.



## Interrupted neutral monitoring CM-MPS.11, CM-MPS.21, CM-MPS.23

The interruption of the neutral in the main to be monitored is detected by means of phase unbalance evaluation.

Determined by the system, in case of unloaded neutral, i.e. symmetrical load between all three phases, it may happen that an interruption of the neutral will not be detected.

If the star point is displaced by asymmetrical load in the three-phase main, an interrupted neutral will be detected.

#### Displacement of the star point




### Automatic phase sequence correction CM-MPS.x3, CM-MPN.x2


This function can be selected only if phase sequence monitoring is activated  $\square$  and operating mode 2x1 c/o (SPDT) contact  $\square$  is selected.

Applying control supply voltage begins the fixed start-up delay  $t_{\rm S1}$ . When  $t_{\rm S1}$  is complete and all phases are present with correct voltage, output relay R1 energizes. Output relay R2 energizes when the fixed start-up delay  $t_{\rm S2}$  is complete and all phases are present with correct phase sequence. Output relay R2 remains de-energized if the phase sequence is incorrect.


If the voltage to be monitored exceeds or falls below the set threshold values for phase unbalance, over- or undervoltage or if a phase failure occurs, output relay R1 de-energizes and the LEDs F1 and F2 indicate the fault.

Output relay R2 is responsive only to a false phase sequence. In conjunction with a reversing contactor combination, this enables an automatic correction of the rotation direction. See circuit diagrams on the right.





Control circuit diagram (K1 = CM-MPS.xx or CM-MPN.xx)



Power circuit diagram

# Three-phase monitoring relays Function diagrams

Over- and undervoltage monitoring 1x2 c/o

#### CM-PSS.xx1, CM-PVS.xx2, CM-MPS.xx2, CM-MPN.xx2

Applying control supply voltage begins the fixed start-up delay  $t_{\rm s}.$  When  $t_{\rm s}$  is complete and all phases are present with correct voltage and with correct phase sequence, the output relays energize and the yellow LED R/T glows.

#### Type of tripping delay = ON-delay


If the voltage to be monitored exceeds or falls below the fixed<sup>1)</sup> or set<sup>2)</sup> threshold value, the output relays de-energize after the set tripping delay  $\mathbf{t}_{_{\mathrm{V}}}$  is complete. The LED R/T flashes during timing and turns off as soon as the output relays de-


The output relays re-energize automatically as soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 % and the LED R/T glows.

#### Type of tripping delay = OFF-delay

If the voltage to be monitored exceeds or falls below the fixed<sup>1)</sup> or set<sup>2)</sup> threshold value, the output relays de-energize instantaneously and the LED R/T turns off.

As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %, the output relays re-energize automatically after the set tripping delay  $t_{\mbox{\tiny N}}$  is complete. The LED R/T flashes during timing and turns steady when timing is complete.





### Over- and undervoltage monitoring 2x1 c/o

#### CM-MPS.x3, CM-MPN.x2

Applying control supply voltage begins the fixed start-up delay t<sub>s</sub>. When ts is complete and all phases are present with correct voltage and with correct phase sequence, the output relays energize. The yellow LED R/T glows as long as at least one output relay is energized.

### Type of tripping delay = ON-delay


If the voltage to be monitored exceeds or falls below the set threshold value, output relay R1 (overvoltage) or output relay R2 (undervoltage) de-energizes after the set tripping delay t, is complete. The LED R/T flashes during timing.


The corresponding output relay re-energizes automatically as soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %.

#### Type of tripping delay = OFF-delay

If the voltage to be monitored exceeds or falls below the set threshold value, output relay R1 (overvoltage) or output relay R2 (undervoltage) de-energizes instantaneously.

As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %, the corresponding output relay reenergizes automatically after the set tripping delay t, is complete. The LED R/T flashes during timing.





# Three-phase monitoring relays Function diagrams

#### Phase unbalance monitoring CM-PAS.xx, CM-MPS.xx, CM-MPN.xx

Applying control supply voltage begins the fixed start-up delay t<sub>s</sub>. When t<sub>s</sub> is complete and all phases are present with correct voltage and with correct phase sequence, the output relays energize and the yellow LED R/T glows.

#### Type of tripping delay = ON-delay


If the voltage to be monitored exceeds or falls below the set phase unbalance threshold value, the output relays de-energize after the set tripping delay  $\boldsymbol{t}_{\boldsymbol{v}}$  is complete. The LED R/T flashes during timing and turns off as soon as the output relavs de-energize.


The output relays re-energize automatically as soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 20 % and the LED R/T glows.

### Type of tripping delay = OFF-delay

If the voltage to be monitored exceeds or falls below the set phase unbalance threshold value, the output relays de-energize instantaneously and the LED R/T turns

As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 20 %, the output relays re-energize automatically after the set tripping delay  $t_v$  is complete. The LED R/T flashes during timing and turns steady when timing





#### **LED** functions CM-PSS.xx, CM-PSV.xx, CM-PAS.xx, CM-MPS.xx, CM-MPN.xx

Function	R/T:	F1:	F2:
	yellow LED	red LED	red LED
Control supply voltage applied, output relay energized		-	-
Tripping delay t <sub>v</sub> active	ПП	-	-
Phase failure	-		лл
Phase sequence	-	Л∟П∟ alte	ernating
Overvoltage	-		-
Undervoltage	-	-	
Phase unbalance	-		
Interruption of the neutral	-		лл
Adjustment error 1)	пп	пп	

<sup>1)</sup> Possible misadjustments of the front-face operating controls:

Overlapping of the threshold values: An overlapping of the threshold values is given, if the threshold value for overvoltage is set to a smaller value than the threshold value for undervoltage.

DIP switch 3 = OFF and DIP switch 4 = ON: Automatic phase sequence correction is activated and selected operating mode is 1x2 c/o contacts

DIP switch 2 and 4 = ON: Phase sequence detection is deactivated and the automatic phase sequence correction is actived

#### Type of tripping delay CM-PSS.xx, CM-PSV.xx, CM-PAS.xx, CM-MPS.xx, CM-MPN.xx

The type of tripping delay / can be adjusted via a rotary (CM-PxS.xx) or a DIP switch (CM-MPx.xx).

### Switch position ON-delay :

In case of a fault, the de-energizing of the output relays and the respective fault message are suppressed for the adjusted tripping delay t<sub>v</sub>.

### Switch position OFF-delay

In case of a fault, the output relays de-energize instantaneously and a fault message is displayed and stored for the length of the adjusted tripping delay  $t_{_{\! V}}$ . Thereby, also momentary undervoltage conditions are recognized.

# Three-phase monitoring relays Function diagrams

### Grid feeding monitoring CM-UFS.2


#### Function of the yellow LED

The yellow LED is flashing during timing and turns steady as soon as the output relays are energized.

#### Phase failure monitoring

Applying control supply voltage begins the fixed start-up delay  $t_{\rm s1}$ . When  $t_{\rm s1}$  is complete and all phases are present with correct voltage and frequency, the output relays energize. They de-energize instantaneously if a phase failure occurs. The fault is indicated by LEDs.

As soon as all 3 phases are present again, the output relays re-energize automatically after the set restart delay  $t_{\rm sp}$  is complete.




#### Over- and undervoltage monitoring

Applying control supply voltage begins the fixed start-up delay  $t_{\rm s_1}$ . When  $t_{\rm s_1}$  is complete and all phases are present with correct voltage and frequency, the output relays energize.

If the voltage to be monitored exceeds or falls below the fixed threshold value, the output relays de-energize instantaneously. The fault type is indicated by LEDs. As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %, the

output relays re-energize after the set restart delay  $t_{\rm so}$  is complete.




### LED Funktionen

Function	R/T:	F1:	F2:
Output relay energized		-	-
Delay active	лл	-	-
Overvoltage	-		-
Undervoltage	-	-	
Overfrequency	-	ПП	-
Underfrequency	-	-	ПП
Phase failure	-		ПП

#### Over- and underfrequency monitoring

Applying control supply voltage begins the fixed start-up delay  $t_{\rm S1}$ . When  $t_{\rm S1}$  is complete and all phases are present with correct voltage and frequency, the output relays energize.


If the frequency to be monitored exceeds or falls below the fixed threshold value, the output relays deenergize instantaneously. The fault type is indicated by LEDs. As soon as the frequency returns to the tolerance range, taking into account a fixed hysteresis, the output relays re-energize after the set restart delay  $t_{\rm S2}$  is complete.



### Function diagram legend

Control supply voltage not applied / Output contact open / LED off


Control supply voltage applied / Output contact closed / LED glowing




Automatized grid connection instead of a permanently accessible switching point with a disconnection function

# Three-phase monitoring relays Connection diagrams, DIP switches


### Connection diagrams CM-PBE



### Connection diagram CM-PVS.x1



### Connection diagram CM-PFS



#### Rotary switch "Function" CM-PVS



ON-delay

with phase sequence monitoring



OFF-delay

with phase sequence monitoring



ON-delay


without phase sequence monitoring




OFF-delay

without phase sequence monitoring


#### Connection diagrams CM-PVE



### Connection diagram CM-PSS.x1



#### Connection diagram CM-PFE



### Rotary switch "Function" CM-PSS



with phase sequence monitoring



OFF-delay

with phase sequence monitoring



ON-delay


without phase sequence monitoring




OFF-delay

without phase sequence monitoring


### Connection diagram CM-UFS.2



### Connection diagram CM-MPN.x2




### Connection diagram CM-PAS.x1




# Three-phase monitoring relays Connection diagrams, DIP switches, Rotary switches


### Connection diagram CM-MPS.x3




### DIP switch functions CM-MPS.x3 and CM-MPN.x2




### Connection diagram CM-MPS.x1



#### DIP switch functions CM-MPS.x1



# Three-phase monitoring relays Notes



Data at  $\rm T_a = 25~^{\circ}C$  and rated values, unless otherwise indicated

Туре		CM-PBE 1)	CM-PBE	CM-PVE 1)	CM-PVE	CM-PFE	CM-PFS
Supply circuit = measuring circu	it	L1-L2-L3-N	L1-L2-L3	L1-L2-L3-N	L1-L2-L3	L1-l	_2-L3
Rated control supply voltage $U_s$ = measu		3x380- 440 V AC, 220-240 V AC	3x380- 440 V AC	3x320- 460 V AC, 185-265 V AC	3x320- 460 V AC	3x208- 440 V AC	3x200- 500 V AC
Power consumption						approx	к. 15 VA
Rated control supply voltage U <sub>s</sub> tolerance	<del></del>	-15	+15 %	-15	-10 %	-10+10 %	-15+10 %
Rated frequency	······	50/6	0 Hz	50/	60 Hz (-10+1	 O %)	50/60 Hz
Duty time			•	100			
Measuring circuit		L1-L2-L3-N	L1-L2-L3	L1-L2-L3-N	L1-L2-L3	L1-L	_2-L3
Monitoring functions	phase failure		•	•			•
	phase sequence over- / undervoltage	ļ			······		
	neutral		-	-	<del>-</del>	-	-
Measuring ranges		3x380- 440 V AC, 220-240 V AC	3x380- 440 V AC	3x320- 460 V AC, 185-265 V AC	3x320- 460 V AC	3x208- 440 V AC	3x200- 500 V AC
Thresholds	U <sub>min</sub>			fixed 185 V / 320 V	fixed 320 V	0.0	
	U <sub>max</sub>	0.6 >	x UN	fixed 265 V / 460 V	fixed 460 V	0.6	x UN
Hysteresis related to the threshold value			15 % e = 0.65 x UN)	fixed	5 %		
Measuring voltage frequency Response time			50/60 HZ (-	10 %+10 %) 80	me		
Accuracy within the rated control supply	voltage tolerance	40.	1115	00	1115		
Accuracy within the temperature range		······			$\Delta U \leq 0$ .		
Timing circuit						L1-L  3x208- 440 V AC  approx -10+10 % -10 %)  L1-L  3x208- 440 V AC  0.6  500/6  500/6  500  AU ≤  fixed 500 ms  2ed  11-12/14  1 c/o contact	
Start-up delay t <sub>s</sub>			fixed 500	ms (±20 %)		fixed	500 ms
Tripping t <sub>v</sub>		fixed 1	50 ms	at over-/ ur fixed 500 r	dervoltage	fixed 500 ms	-
Indication of operational states					- (	:	:
Relay status	R: yellow LED			☐ Output	relay energize	d	
Output circuits				3-14			11(15)- 12(16)/14(18), 21(25)- 22(26)/24(28)
Kind of output	<u>.</u>		1 n/o	contact		1 c/o contact	2 c/o contacts
Operating principle 2) Contact material				closed-circ	uit principle		
Rated operational voltage U	IEC/EN 60947-1		•	AgCdO 250	) V		AgNi
Minimum switching voltage / Minimum sw	vitching current		•	- /			
Maximum switching voltage				250 V AC,	250 V DC		
Rated operational current I	AC12 (resistive) 230 V			4			
(IEC/EN 60947-5-1)	AC15 (inductive) 230 V DC12 (resistive) 24 V			3			
	DC12 (resistive) 24 V		•	4 2	Α Δ		
Mechanical lifetime	2010 (11000110) 24 V	<b>†</b>	<b></b>	30 x 106 swi			
Electrical lifetime (AC12, 230 V, 4 A)				0.1 x 106 swi	tching cycles		
Max. fuse rating to achieve short-circuit protection	n/c contact			10 A fast-acting			4 A fast- acting
	n/o contact			10 A fast-acting			6 A fast- acting
(UL 508)	tegory (Control Circuit Rating Code) max. rated operational voltage		•	B 3	V AC		
	continuous thermal current at B 300	ļ	***************************************	5		.*	.*
max. making/	breaking apparent power at B 300			3600/3	360 VA		

Device with neutral monitoring: The external conductor voltage towards the neutral conductor is measured.

<sup>&</sup>lt;sup>2)</sup> Closed-circuit principle: Output relay is de-energized if the measured value exceeds/drops below the adjusted threshold.

Data at  $T_a$  = 25 °C and rated values, unless otherwise indicated

Туре		CM-PBE 1)	CM-PBE	CM-PVE 1)	CM-PVE	CM-PFE	CM-PFS
General data						•	•
Dimensions (W x H x D)							22.5 x 78
				2.5 x 78 x 78.5 n			x 100 mm
			(0.	89 x 3.07 x 3.09	in)		(0.89 x 3.07
					•		x 3.94 in)
Weight		ļ		see dat			<b>.</b>
Mounting				DIN rail (IEC	•		···•··································
Mounting position	havaina / tarminala	ļ		ar			···•
Degree of protection	housing / terminals			IP50 /	IP2U		
Electrical connection Wire size fine							
vvire size time	e-strand with wire end ferrule						
			2 x 0.75-	1.5 mm² (2 x 18-	-16 AWG)		2 x 0.75-
							2.5 mm <sup>2</sup>
fine-st	rand without wire end ferrule		2 v 1 1 i	5 mm² (2 x 18-1	6 V/V/C/	••••	(2 x 8-14 AWG)
			Z X 1-1.	J IIIII- (2 X 10-1	O AVVG)		
	rigid						2 x 0.5- 4 mm <sup>2</sup>
			2 x 0.75-	1.5 mm <sup>2</sup> (2 x 18-	16 AWG)		(2 x 20-12 AWG)
							(2 / 20 / 2 / 11/6)
Stripping length		•		10 (0 00 :-)	•••••	••••••	7 mm
5				10 mm (0.39 in)			(0.28 in)
Tightening torque				0.6-0.	8 Nm		
Environmental data							
Ambient temperature range	operation / storage			-20+60 °C /	-40+85 °C		
Environmental testing (IEC 68-2-30)			24	h cycle time, 55	°C, 93 % rel., 9	96 h	
Operational reliability (IEC 68-2-6)				6 g	•••••	. *************************************	4 g
Mechanical resistance (IEC 68-2-6)				10 g			6 g
Isolation data							
Rated insulation volt. between supply, measuring	g and output circuits		40	00 V		5	00 V
(VDE 0110, IEC 60947-1)					• • • • • • • • • • • • • • • • • • • •		
Rated impulse withstand voltage U <sub>imp</sub> between al (VDE 0110, IEC 664)	I isolated circuits			4 kV / 1.	2 - 50 µs		
Test voltage between all isolated circuits		ļ		2.5 kV, 50	∐z 1 min	•	···•
Pollution category (VDE 0110, IEC/EN 60664, IE	C 255-5)				, 1 111111. 3	•••••	······································
Overvoltage category (VDE 0110, IEC/EN 60664		· · · · · · · · · · · · · · · · · · ·			) 	•••••	···•
Standards	,					-	
Product standard				IEC 255-6,	EN 60255-6		
Low Voltage Directive		······		2006/		•••••	••••
EMC Directive				2004/1	• · · · · · · · · · · · · · · · · · · ·	•••••	····•
Electromagnetic compatibility				20017	00/20		
Interference immunity to				EN 610	00-6-2		
electrostatic discharge	IEC/EN 61000-4-2	·····			6 kV/ 8 kV	•••••	···•
radiated, radio-frequency,	IEC/EN 61000-4-3	†		••••••	•••••		····
electromagnetic field				Level 3	- 10 V/m		
electrical fast transient / burst	IEC/EN 61000-4-4				kV / 5 kHz		····
surge	IEC/EN 61000-4-5			Level 4 -	2 kVL-L		
conducted disturbances, induced by	IEC/EN 61000-4-6			Level 3			
radio-frequency fields		ļ			•		···•
Interference emission				EN 610	00-6-4		

Device with neutral monitoring: The external conductor voltage towards the neutral conductor is measured.

<sup>&</sup>lt;sup>2)</sup> Closed-circuit principle: Output relay is de-energized if the measured value exceeds/drops below the adjusted threshold.

Data at  $T_a$  = 25 °C and rated values, unless otherwise indicated

Туре		CM-PSS.31	CM-PSS.41	CM-PVS.31	CM-PVS.41	CM-PVS.81	CM-PAS.31	CM-PAS.41
Input circuit = Measuring	circuit			•	L1, L2, L3	•	•	
Rated control supply voltage U <sub>s</sub> =	= measuring voltage	3x380 V AC	3x400 V AC	3x160- 300 V AC	3x300- 500 V AC	3x200- 400 V AC	3x160- 300 V AC	3x300- 500 V AC
Rated control supply voltage U <sub>s</sub> t	olerance		•••••	•	-15+10 %	••••	•••••	•
Rated frequency			• • • • • • • • • • • • • • • • • • • •	•	50/60 Hz		•••••	•
Frequency range	•		• • • • • • • • • • • • • • • • • • • •	•	45-65 Hz		•••••	•
Typical current / power consump	tion	25 mA / 18 VA (380 V AC)	25 mA / 18 VA (400 V AC)	25 mA / 10 VA (230 V AC)	· •· · · · · · · · · · · · · · · · · ·	19 mA / 10 VA (300 V AC)	25 mA / 10 VA (230 V AC)	25 mA / 18 VA (400 V AC)
Measuring circuit					L1, L2, L3			
Monitoring functions	Phase failure	-						
	Phase sequence		ca	n be switched	· •· · · · · · · · · · · · · · · · · ·			
	Automatic phase sequence correction	-	-	-	-	-	-	- -
	Over- / undervoltage		-	_	-	_	-	_
	Phase unbalance	-	-	-	-	-		
·········	Neutral	-	-	-	-	-	-	<u>-</u>
Measuring range	Overvoltage	3x418 V AC	3x440 V AC	3x220- 300 V AC	3x420- 500 V AC	3x300- 400 V AC	-	-
	Undervoltage	3x342 V AC	3x360 V AC	3x160- 230 V AC	3x300- 380 V AC	3x210- 300 V AC	-	-
	Phase unbalance	-	-	-	-	-	2-25 % of phase	average
Thresholds	Overvoltage	fix	 ad	adiuetabl	: e within measu	i	-	· -
	Undervoltage	fix	•		e within measu			<u> </u>
 Pł	nase unbalance (switch-off value)		_	aujustabi	· · · · · ·		adjust. within	meas range
Hysteresis related to the	Over- / undervoltage			fixed 5 %	. <u>i.</u>	. <u>.</u>	aajast. Withiii	incas. range
threshold value	Phase unbalance	-	-	-	<u> </u>	<u> </u>	fixed	20 %
Rated frequency of the measuring	g signal			·	50/60 Hz			***************************************
Frequency range of the measurin			•••••	•	45-65 Hz	•••••	•••••	•
Maximum measuring cycle time			•	•	100 ms	•	•••••	
Accuracy within the rated contro	l supply voltage tolerance		••••	•	$\Delta$ U $\leq$ 0.5 %	•	•	•
Accuracy within the temperature	range		•	ΔΙ	U ≤ 0.06 % /°	C		
Measuring method					True RMS			
Timing circuit								
Start-up delay t					fixed 200 ms			
Tripping delay t,				N- or OFF-del	· <b>*</b> · · · · · · · · · · · · · · · · · · ·	•••••	ON- (	 delav
				0.1-30 s adjusta			0; 0.1-30 s	
Repeat accuracy (constant paran	neters)	-	-	-	-	I w 0.2 %	-	-
Accuracy within the rated control			······································	<b>1</b>	$\Delta t \leq 0.5 \%$			
Accuracy within the temperature	range		•	Δ	t ≤ 0.06 % / °0	<u> </u>	•	•
Indication of operational states			•	1 yell	ow LED, 2 red	LED's		•
		Details se description	e function / -diagrams		perating mode cription / -diag		Details se description	
Output circuits		·		15-	16/18, 25-26	/28	•	
Kind of output					/o contacts (Re			
Operating principle 1)			• • • • • • • • • • • • • • • • • • • •		ed-circuit princ		•	•
Contact material			• • • • • • • • • • • • • • • • • • • •		Ni alloy, Cd fre		••••	•
Rated operational voltage U	IEC/EN 60947-1		• • • • • • • • • • • • • • • • • • • •		250 V	•••••	•····	•
Minimum switching power			•	•	24 V / 10 mA	•	•••••	•
Maximum switching voltage			•	•	e load limit cur	• • • • • • • • • • • • • • • • • • • •	• • • • • • • • • • • • • • • • • • • •	*

Data at  $T_a$  = 25 °C and rated values, unless otherwise indicated

Туре		CM-PSS.31 CM-PSS.41 CM-PVS.31 CM-P	VS.41 CM-PVS.81 CM-PAS.31 CM-PAS.41			
Rated operational current (IEC/EN 60947-5-1)	t I <sub>e</sub> AC12 (resistive) 230 V	4 A				
(IEC/EIN 60947-5-1)		3 A				
	DC12 (resistive) 24 V DC13 (inductive) 24 V	4	ΑΔ			
AC rating (UL 508)	Utilization category					
(Control Circuit Rating Co		B 300 300 V AC				
	max. rated operational voltage	300 \	/ AC			
	max. continuous thermal current at B 300	5.	A			
	max. making/breaking apparent					
	power at B 300	3600/3	60 VA			
Mechanical lifetime		30 x 10 <sup>6</sup> swite				
Electrical lifetime (AC12, 2 Max. fuse rating to achiev		0.1 x 10 <sup>6</sup> swit				
short-circuit protection	ve n/c contact n/o contact	6 A fast 10 A fas				
General data	Ty o domain	107/140	t dotting			
MTBF		on rec	nuest			
Duty time		100	9%			
Dimensions (W x H x D)	product dimensions	22.5 x 85.6 x 103.7 mm				
\\\/a: = =1	packaging dimensions	97 x 109 x 30 mm (3				
Weight Mounting		depending on device, DIN rail (IEC/				
Mounting		snap-on mounting				
Mounting position		an	V			
Minimum distance to other	er units vertical / horizontal	not necessary /				
Material of housing Degree of protection	housing / terminals	UL 94 IP50 /				
Electrical connection		[F307	IF20			
Wire size		_				
VIII 0 0120		Screw connection technology	Easy Connect Technology (Push-in)			
	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 20-14 AWG)	2 x 0.5-1.5 mm² (2 x 20-16 AWG)			
	et esta	2 x 0.5-1.5 mm² (2 x 20-16 AWG)	2 x 0.5-1.5 mm² (2 x 20-16 AWG)			
	rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)	2 x 0.5-1.5 mm² (2 x 20-16 AWG)			
Stripping length	······································	8 mm (C	0.32 in)			
Tightening torque		0.6-0.8 Nm (5.31-7.08 lb.in)	-			
	<u>.</u>					
Environmental data  Ambient temperature ran	ages operation / storage	-25+60 °C /	-/∩ ±85 °C			
Damp heat (IEC 60068-2		55 °C, 6	cycles			
Climatic category		3K	3			
Vibration (sinusoidal) (IEC		Clas				
Shock (IEC/EN 60255-21	1-2)	Clas	S 2			
Rated insulation	input circuit / output circuit	600				
voltage U	output circuit 1 / output circuit 2	300				
Rated impulse withstand	voltage input circuit	6 kV; 1.2				
U <sub>imp</sub> (VDE 0110, IEC/EN 6		4 kV; 1.2				
	isolated circuits (type test)	2.5 kV, 50				
Basis isolation Protective separation (VDI	input circuit / output circuit / E 0106 input circuit /	600	J V			
part 101 and 101/A, IEC/	/EN 1140) output circuit	-				
Pollution degree (VDE 01	<del>-</del>	3				
Overvoltage category (VD	DE UTTU, IEG 60664)	<u> </u>	I			
Standards  Product standard		IFO/FN 00055	6 EN 50170			
Product standard  Low Voltage Directive		IEC/EN 60255   2006/9				
EMC directive		2004/1				
RoHS directive		2002/95/EG				
Electromagnetic co	mpatibility					
Interference immunity to		EN 61000-6-1,				
electrostatic discharge radiated, radio-freque		Level 3 (6 kV / 8 kV)				
electromagnetic field	FIG., IEC/EN 01000-4-3	Level 3 (10 V/m)				
electrical fast transien	nt / burst IEC/EN 61000-4-4	Level 3 (2 kV / 2 kHz)				
surge	IEC/EN 61000-4-5	Level 4 (2	······································			
conducted disturbance						
induced by radio-frequ	iericy lieias					
Interference emission high-frequency radiate	ed IEC/CISPR 22, EN 50022	Class 3 EN 61000-6-3, EN 61000-6-4				
high-frequency condu		EN 61000-6-3, EN 61000-6-4  Class B				
		,				

Data at  $T_a = 25~^{\circ}\text{C}$  and rated values, unless otherwise indicated

Туре	CM-MPS.11	CM-MPS.21	CM-MPS.31	CM-MPS.41			
Input circuit = Measuring circuit	L1, L2	2, L3, N	L1, L2, L3				
Rated control supply voltage U <sub>s</sub> = measuring voltage	3x90-170 V AC	3x180-280 V AC	3x160-300 V AC	3x300-500 V AC			
Rated control supply voltage U <sub>s</sub> tolerance		-15	+10 %	•			
Rated frequency		50/6		• • • • • • • • • • • • • • • • • • • •			
Frequency range		45-6	65 Hz	•			
Typical current / power consumption	25 mA / 10 VA	25 mA / 18 VA (230 V AC)	25 mA / 10 VA (230 V AC)	25 mA / 18 VA			
	(115 V AC)		, ,	(400 V AC)			
Measuring circuit	·	L1, L2, L3, N L1, L2, I					
Monitoring functions Phase failu							
Phase sequer Automatic phase sequence correct		can be sv	vitched off				
Over- / undervolta			-	-			
Phase unbalar		-	-	-			
Interrupted neut		-	-	-			
Measuring range Overvolta		3x240-280 V AC	3x220-300 V AC	3x420-500 V AC			
Undervolta	ge 3x90-130 V AC	3x180-220 V AC	3x160-230 V AC	3x300-380 V AC			
Phase unbalar			of phase voltages	<b>.</b>			
Thresholds Overvolta	ge	adjustable within	measuring range	***************************************			
Undervolta	ge	adjustable within	measuring range	•			
Phase unbalance (switch-off val	ue)	adjustable within measuring range					
Hysteresis related to the Over- / undervolta threshold value Phase unbalar		fixed 5 %					
T TIGO GI DGIGI	ice	fixed 20 %					
Rated frequency of the measuring signal		50/60 Hz					
Frequency range of the measuring signal		45-65 Hz					
Maximum measuring cycle time		100 ms					
Accuracy within the rated control supply voltage tolerance		ΔU ≤ 0.5 %					
Accuracy within the temperature range		ΔU ≤ 0.06 % / °C True RMS					
Measuring method		Irue	RMS				
Timing circuit			200				
Start-up delay t <sub>s</sub>		<b>.</b>	200 ms	•			
Tripping delay t <sub>v</sub>		ON- or OFF-delay 0; 0.1-30 s adjustable					
Accuracy within the rated control supply voltage tolerance		$\Delta t \le 0.5\%$					
Accuracy within the temperature range		Δt ≤ 0.06 % / °C					
Indication of operational states		Details see function description / -diagrams					
Output circuits		15-16/18, 25-26/28					
Kind of output  Operating principle 1)		1x2 c/o contacts (Relays)					
Contact material		closed-circuit principle AgNi alloy, Cd free					
Rated operational voltage U_ (IEC/EN 60947-1)		Agini alioy, Cd free 250 V					
Minimum switching power		24 V / 10 mA					
Maximum switching voltage		see load limit curve					
Rated operational current I. AC12 (resistive) 230	) V	4 A					
(IEC/EN 60947-5-1) AC15 (inductive) 230		3 A					
DC12 (resistive) 24			Α	•••••			
DC13 (inductive) 24				•			
AC rating (UL 508) Utilization catego (Control Circuit Rating Co		Р 200					
max. rated operational volta				• • • • • • • • • • • • • • • • • • • •			
max. continuous thermal current at B 3				***************************************			
max. making/breaking apparent power at B 3							
Mechanical lifetime		30 x 10 <sup>6</sup> switching cycles					
Electrical lifetime (AC12, 230 V, 4 A)			tching cycles	***************************************			
Max. fuse rating to achieve n/c conta			t-acting				
short-circuit protection n/o conta	act	10 A fast-acting					

Data at  $\rm T_a$  = 25  $^{\circ}\rm C$  and rated values, unless otherwise indicated

Туре		CM-MPS.11	CM-MPS.21	CM-MPS.31	CM-MPS.41	
General data			•			
MTBF			on re	equest		
Duty time			00%			
Dimensions product dimensions			22.5 x 85.6 x 103.7 m	m (0.89 x 3.37 x 4.08 ii	1)	
$(W \times H \times D)$	packaging dimensions		97 x 109 x 30 mm	(3.82 x 4.29 x 1.18 in)		
Weight		Screw connection technology Easy Connect Te		Easy Connect Tec	hnology (Push-in)	
	net weight	depending on device,		e, see ordering details	•	
	gross weight		depending on devic	e, see ordering details	•	
Mounting		DIN rail (IEC/EN 60715),				
Mounting position		snap-on mounting without any tool				
Minimum distance to other units	vertical / horizontal			any /not necessary	•	
Material of housing			·•···	94 V-0	• • • • • • • • • • • • • • • • • • • •	
Degree of protection	housing / terminals		IP50	/ IP20	•	
Electrical connection						
Wire size		Screw connec	tion technology	Easy Connect Ted	hnology (Push-in)	
	fine-strand with(out) wire end ferrule		2 (1 x 20-14 AWG)		(2 x 20-16 AWG)	
		2 x 0.5-1.5 mm2	2 (2 x 20-16 AWG)		,	
	rigid	1 x 0.5-4 mm2	(1 x 20-12 AWG) 2 (2 x 20-14 AWG)	2 x 0.5-1.5 mm2	(2 x 20-16 AWG)	
Stripping length		L X 0.0 L.0 IIIIII		(0.32 in)	•	
Tightening torque		0.6-0.8 Nm (	5.31-7.08 lb.in)		-	
Environmental data				•		
Ambient temperature ranges	operation / storage	-25+60 °C / -40+85 °C				
Damp heat (IEC 60068-2-30)		55 °C, 6 cycles			•	
Climatic category		3K3				
Vibration (sinusoidal) (IEC/EN 60255-21-1	1)	Class 2				
Shock (IEC/EN 60255-21-2)	Class 2					
Isolation data	1					
Rated insulation voltage U	input circuit / output circuit		60	00 V		
0 1	output circuit 1 / output circuit 2		30	00 V	•••••	
Rated impulse withstand voltage U.	input circuit	6 kV; 1.2/50 μs				
Rated impulse withstand voltage U <sub>imp</sub> (VDE 0110, IEC/EN 60664)	output circuit	4 kV; 1.2/50 μs				
Test voltage between all isolated circuits (		2.5 kV, 50 Hz, 1 s				
Basis isolation	input circuit / output circuit	600 V			•	
Protective separation	input circuit / output circuit				•	
(VDE 0106 part 101 and 101/A, IEC/EN 6	61140)	У	es		-	
Pollution degree (VDE 0110, IEC/EN 6066	64)	3				
Overvoltage category (VDE 0110, IEC 606	664)	III				
Standards						
Product standard			IEC/EN 6025	55-6, EN 50178		
Low Voltage Directive		2006/95/EG				
EMC directive		2004/108/EG				
RoHS directive		2002/95/EG				
Electromagnetic compatibility						
Interference immunity to			EN 61000-6-1	I, EN 61000-6-2		
electrostatic discharge IEC/EN 61000-4-2		Level 3 (6 kV / 8 kV)				
radiated, radio-frequency, IEC/EN 61000-4-3 electromagnetic field		Level 3 (10 V/m)				
electrical fast transient / burst	IEC/EN 61000-4-4		Level 3 (2	kV / 2 kHz)	•	
		Level 4 (2 kV L-L)				
surge IEC/EN 61000-4-5  conducted disturbances, IEC/EN 61000-4-6 induced by radio-frequency fields		Level 3 (10 V)				
harmonics and interharmonics	IEC/EN 61000-4-13		CI	ass 3	•	
	ILO/LIN 01000-4-10		•••••	······		
Interference emission	IEC/CISPD 22 EN 50022			3, EN 61000-6-4	•	
high-frequency radiated	IEC/CISPR 22, EN 50022	Class B			•	
high-trequency conducted	high-frequency conducted IEC/CISPR 22, EN 50022		Class B			

<sup>1)</sup> Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value

Data at  $T_a$  = 25 °C and rated values, unless otherwise indicated

Туре	CM-MPS.23	CM-MPS.43	CM-MPN.52	CM-MPN.62	CM-MPN.72	
Input circuit = Measuring circuit	L1, L2, L3, N		L1, L	.2, L3		
Rated control supply voltage $U_S$ = measuring voltage	3x180-280 V AC	3x300-500 V AC	3x350-580 V AC	3x450-720 V AC	3x530-820 V AC	
Rated control supply voltage U <sub>c</sub> tolerance			-15+10 %		<u>.</u>	
Rated frequency	50/60/4	400 Hz		50/60 Hz	• • • • • • • • • • • • • • • • • • • •	
Frequency range	45-44			45-65 Hz	• • • • • • • • • • • • • • • • • • • •	
Typical current / power consumption	5 mA / 4 VA (230 V AC)	5 mA / 4 VA (400 V AC)	29 mA / 41 VA (480 V AC)	29 mA / 52 VA (600 V AC)	29 mA / 59 VA (690 V AC)	
Measuring circuit	L1, L2, L3, N		L1, L	.2, L3		
Monitoring functions Phase failure	•	•	•	•	•	
Phase sequence					•	
Automatic phase sequence correction			configurable			
Over- / undervoltage		•			•	
Phase unbalance				<u> </u>		
Interrupted neutral		-		<u>:</u>	-	
Measuring range Overvoltage	3x240-280 V AC	3x420-500 V AC	3x480-580 V AC	3x600-720 V AC	3x690-820 V AC	
Undervoltage	3x180-220 V AC	3x300-380	37350 460 1/ 40	3x450-570 V AC	3x530-660	
	3X10U-22U V AC	V AC		<u></u>	V AC	
Phase unbalance			of average of phase		••••	
Thresholds Overvoltage			ble within measuri		***************************************	
Undervoltage			ble within measuri		***************************************	
Phase unbalance (switch-off value)		adjusta	ble within measuri	ng range	***************************************	
Hysteresis related to the Over- / undervoltage			fixed 5 %	***************************************	•••••	
threshold value Phase unbalance		• • • • • • • • • • • • • • • • • • • •	fixed 20 %		••••	
Rated frequency of the measuring signal	50/60/400 Hz 50/60 Hz					
Frequency range of the measuring signal	45-440 Hz 45-65 Hz					
Maximum measuring cycle time	100 ms					
Accuracy within the rated control supply voltage tolerance		• • • • • • • • • • • • • • • • • • • •	ΔU ≤ 0.5 %		•••••	
Accuracy within the temperature range		• • • • • • • • • • • • • • • • • • • •	$\Delta U \leq 0.06 \% / °C$	<u>)</u>	***************************************	
Measuring method			True RMS			
Timing circuit						
Start-up delay $t_s$ and $t_{s2}$			fixed 200 ms		•	
Start-up delay t <sub>S1</sub>	fixed 250 ms					
Tripping delay t <sub>v</sub>				ON-0 0; 0.1-30 s	delay adjustable	
Accuracy within the rated control supply voltage tolerance	Δt ≤ 0.5 %					
Accuracy within the temperature range	<u>Δt</u> ≤ 0.06 % / °C					
Indication of operational states	Details see function description / -diagrams					
Output circuits	15-16/18, 25-26/28					
Kind of output	2x1 or 1x2 c/o contacts configurable (Relays)					
Operating principle 1)	closed-circuit principle					
Contact material	AgNi alloy, Cd free					
Rated operational voltage U <sub>o</sub> IEC/EN 60947-1	250 V					
Minimum switching power	24 V / 10 mA					
Maximum switching voltage	see load limit curve					
Rated operational current I <sub>2</sub> AC12 (resistive) 230 V						
(IEC/EN 60947-5-1) AC15 (inductive) 230 V						
DC12 (resistive) 24 V			• • • • • • • • • • • • • • • • • • • •			
DC13 (inductive) 24 V					• • • • • • • • • • • • • • • • • • • •	
AC rating Utilization category (Control Circuit Rating Code)			••••••	•••••		
(UL 508) max. rated operational voltage	age 300 V AC			•••••		
max. continuous thermal current at B 300				•••••		
max. making/breaking apparent power at B 300				***************************************		
Mechanical lifetime	30 x 10 <sup>6</sup> switching cycles					
Electrical lifetime (AC12, 230 V, 4 A)	0,1 x 10° switching cycles					
	· <del> </del>			•	•	
Max. fuse rating to achieve n/c contact	6 A fast	t-acting	10 A fast-acting	10 A fast-acting		

Data at  $\rm T_a = 25~^{\circ}C$  and rated values, unless otherwise indicated

Туре		CM-MPS.23	CM-MPS.43	CM-MPN.52	CM-MPN.62 CM	I-MPN.72
General data				•		
MTBF				on request		
Duty time			100%			
Dimensions (W x H x D)			103.7 mm (0.89 x			
Weight	packaging dimensions			30 mm (3.82 x 4. on device, see ord		
Mounting		DIN			nting without any tool	
Mounting position			***************************************	anv		
Minimum distance to other units	vertical / horizontal		not ne	ecessary / not nec	cessary	
Material of housing	E	UL 94 V-0				
Degree of protection	housing / terminals			IP50 / IP20		
Electrical connection		Г				
Wire size		Screw	connection tech	nology	Easy Connect Tec	hnology
	_			0,	(Push-in)	
	fine-strand with(out) wire end ferrule	1 x 0.5-	2.5 mm2 (1 x 20-	14 AWG)	2 x 0.5-1.5 mm2 (2 x 2	20-16 AWG)
	wald	2 x 0.5-	1.5 mm2 (2 x 20- -4 mm2 (1 x 20-1	16 AWG)	0 v 0 F 1 F mm0 (0 v 0	20 16 414/01
	rigid		-4 mm2 (1 x 20-1 2.5 mm2 (2 x 20-		2 x 0.5-1.5 mm2 (2 x 2	20-16 AWG)
Stripping length	······································		***************************************	8 mm (0.32 in)	<u></u>	
Tightening torque		0.6-0	0.8 Nm (5.31-7.08	lb.in)	-	
Environmental data						
Ambient temperature ranges	operation / storage		-25.	+60 °C / -40+8	35 °C	
Damp heat (IEC 60068-2-30)			•••••	55 °C, 6 cycles		
Climatic category	······		• • • • • • • • • • • • • • • • • • • •	3K3	••••••	
Vibration (sinusoidal) (IEC/EN 60255-21-1 Shock (IEC/EN 60255-21-2)	)	Class 2 Class 2				
Isolation data				Ulass 2		
	h	0.0	0.17	:	1000 //	
Rated insulation voltage U <sub>i</sub>	input circuit / output circuit output circuit 1 / 2	60	<u>U</u> V	300 V	1000 V	
Rated impulse withstand voltage Uimn	input circuit	6 kV; 1.	2/50 us	500 V	8 kV: 1.2/50 us	
(VDE 0110, IEC/EN 60664)	output circuit			4 kV; 1.2/50 µs		
Test voltage (type test)	isolated output circuits		• • • • • • • • • • • • • • • • • • • •	2.5 kV, 50 Hz, 1	s	
between	input circuit and isolated output circuits	2.5 kV, 5	0 Hz, 1 s		4 kV, 50 Hz, 1 s	
Basis isolation	input circuit / output circuit	60	0 V		1000 V	
Protective separation	input circuit /			_		
(VDE 0106 part 101 and 101/A, IEC/EN 6	· Output Grount					
Pollution degree (VDE 0110, IEC/EN 6066		3				
Overvoltage category (VDE 0110, IEC 606	004)			III		
Standards			IFO	EN 00055 0 EN	-0470	
Product standard Low Voltage Directive			IEC/	EN 60255-6, EN 5 2006/95/EG	00178	
EMC directive		2004/108/EG				
RoHS directive	···············		•••••	2002/95/EG	•••••	
Electromagnetic compatibility		-				
Interference immunity to			EN 61	1000-6-1, EN 610	00-6-2	
electrostatic discharge	IEC/EN 61000-4-2			_evel 3 (6 kV / 8 k		
radiated, radio-frequency,	IEC/EN 61000-4-3			Level 3 (10 V/m)		
electromagnetic field electrical fast transient / burst	IEC/EN 61000-4-4			evel 3 (2 kV / 2 kH		
STILUD	IEC/EN 61000-4-4	Level 4 (2 kV L-N)	<u>L</u>	Level 3 (2 KV / 2 Kr		
conducted disturbances,	IEC/EN 61000-4-5	LUVUI + ( L NV L-IN)	<b></b>	•	( <u>-   \                                  </u>	
induced by radio-trequency fields			***************************************	Level 3 (10 V)		
harmonics and interharmonics	IEC/EN 61000-4-13		••••••••••• <u>••</u> •••••	Class 3		
Interference emission	IFO/OICDD 00 FN 50000		EN 61	000-6-3, EN 610	UU-6-4	
high-frequency radiated high-frequency conducted	IEC/CISPR 22, EN 50022 IEC/CISPR 22, EN 50022		• • • • • • • • • • • • • • • • • • • •	Class B Class B	••••••	
riign-irequency conducted	1EU/UIOFN 22, EIN 30022			Class B		

<sup>1)</sup> Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value

Data at  $T_a$  = 25 °C and rated values, unless otherwise indicated

Туре		CM-UFS.2			
Input circuit - Measuring circuit		L1, L2, L3 L-N			
Rated control supply voltage U <sub>s</sub> = measuring voltage		3 x 400 V AC	3 x 230 V AC		
Rated control supply voltage tolerance U <sub>s</sub>		-20.	+20 %		
Control supply voltage range		3 x 300-500 V AC	3 x 180-280 V AC		
Rated frequency		50 Hz			
Frequency range Typical current / power consumption		45-55 Hz 23 mA / 16 VA			
Power failure buffering time		min. 20 ms			
Input circuit - measuring circuit		L1, L2, L3	L-N		
Monitoring functions	Phase failure		-		
	Over-/ undervoltage		•		
<u></u>	Over-/ underfrequency  10 minutes average value				
Measuring range	Voltage range	3 x 320-480 V AC	3 x 184-276 V AC		
	Frequency range		-55 Hz		
Thresholds	Overvoltage		20 % of U		
	Undervoltage Overfrequency		0 % of U Hz, configurable		
	Underfrequency		Hz, configurable		
	10 minutes average value				
Hysteresis related to the threshold value	Over-/ undervoltage Over-/ underfrequency	fíx 5 % fix 20 mHz			
Rated frequency of the measuring signal	Over-7 underfrequency	11X 20 11H2 50 Hz			
Frequency range of the measuring signal		45-55 Hz			
Maximum measuring cycle time		50 ms			
Maximum reaction time (time between fault detection and change of switching status	Over-/ undervoltage   Over-/ underfrequency	< 120 ms < 100 ms			
of the relay)	10 minutes average value		-		
Accuracy within the rated control supply voltage tolerance			≤ 0,5 %		
Accuracy within the temperature range Measuring method			),06 % / °C Je RMS		
Timing circuit		III	ie nivio		
Start-up delay t <sub>s1</sub> prior to grid connection after a short in	nterruntion	fi	x. 1 s		
	iterraption				
Restart delay t <sub>s2</sub> Accuracy within the rated control supply voltage tolera		adjustable, 0 s; 0,1 − 30 s Δt ≤ 0,5 %			
Accuracy within the rated control supply voltage tolera Accuracy within the temperature range	irice		<u>≤ 0,5 %</u> 0,06 % / °C		
			,		
Indication of operational states		1 yellow LED, 2 red LEDs Details see operation mode and function description/diagrams			
Output circuits		15-16/18, 25-26/28			
Kind of output		Relais, 1 x 2 changeover			
Operation principle 1)		closed-circuit principle			
Contact material Rated operational voltage U <sub>a</sub> (IEC/EN 60947-1)		AgNi alloy, Cd free			
Minimum switching voltage / switching current		250 V 24 V / 10 mA			
vinimum switching voltage / switching current  Vlaximum switching voltage / switching current		see load limit curve			
Rated operational current I AC12 (resistive) 230 V		4 A			
(IEC/EN 60947-5-1)	AC15 (inductive) 230 V	3 A			
<u></u>	DC12 (resistive) 24 V DC13 (inductive) 24 V		4 A 2 A		
Mechanical lifetime	2010 (Inductive) 24 V	30 x 10 <sup>6</sup> sv	witching cycles		
Electrical lifetime (AC12, 230 V, 4 A)		0,1 x 10 <sup>6</sup> switching cycles			
Max. fuse rating to achieve	n/c contact   n/o contact	6 A fast-acting			
short-circuit protection	n/o contact	10 A fast-acting			

Data at  $T_a = 25$  °C and rated values, unless otherwise indicated

Туре		CM-UFS.2	
General data			
MTBF		on request	
Duty time		100%	
Dimensions (W x H x D) product dimensions		7 mm (0.89 x 3.37 x 4.08 in)	
packaging dimensions		nm (3.82 x 4.29 x 1.18 in)	
Weight gross weight	depending on device, see ordering details		
Mounting	DIN rail (IEC/EN 60715),	snap-on mounting without any tool	
Mounting position		any	
Minimum distance to other units vertical / horizonta  Material of housing		sary / not necessary UL 94 V-0	
Degree of protection housing / terminals		P50 / IP20	
Electrical connection		1 00 / 11 20	
Wire size	Screw connection technology	Easy Connect Technology (Push-in)	
fine-strand with(out) wire end ferrule		2 x 0.5-1.5 mm <sup>2</sup> (2 x 20-16 AWG)	
rigic		2 x 0.5-1.5 mm <sup>2</sup> (2 x 20-16 AWG)	
		(0.00.1.)	
Stripping length		mm (0.32 in)	
Tightening torque	0.6-0.8 Nm (5.31-7.08 lb.in)	-	
Environmental data			
Ambient temperature range operation / storage		) °C / -40+85 °C	
Damp heat, cyclic (IEC/EN 60068-2-30)	2 x 12 h cy	rcle, 55 °C, 95 % RH	
Climatic category (IEC/EN 60721-3-1)	3K3 Class 2		
Vibration (sinusoidal) (IEC/EN 60255-21-1) Shock (IEC/EN 60255-21-2)	Class 2		
		Class 2	
Isolation data		000.1/	
Rated impulse withstand voltage U <sub>i</sub> input circuit / output circuit and output circuit 1 / 2		600 V 300 V	
Rated impulse withstand voltage U <sub>imp</sub> input circuit		300 V (V; 1,2/50 μs	
(VDE 0110, IEC/EN 60664) output circuit		(V; 1,2/50 μs	
Test voltage between all isolated circuits (type test)		кV, 50 Hz, 1 s	
Basis isolation input circuit / output circuit		600 V	
Protective separation input circuit / output circuit		yes	
(VDE 0160 Part 101 and 101/A, IEC/EN 61140) Pollution degree (VDE 0110, IEC/EN 60664)		3	
Overvoltage category (VDE 0110, IEC 60664)		III	
Standards			
Product standard		Guideline for Connections to ENEL distribution Ed.2.1., January 2011	
Further standards	EN 50	0178, EN 61727	
Low Voltage Directive	2	006/95/EG	
EMV-Directive	2004/108/EG		
RoHS-Directive	2	002/95/EG	
Electromagnetic compatibility			
Interference immunity to		-6-1, IEC/EN 61000-6-2	
electrostatic discharge IEC/EN 61000-4-2	Leve	3 (6 kV / 8 kV)	
radiated, radio-frequency, IEC/EN 61000-4-3 electromagnetic field		vel 3 (10 V/m)	
electrical fast transient / burst IEC/EN 61000-4-4		3 (2 kV / 2 kHz)	
surge IEC/EN 61000-4-5	Level	4 (2 kV L-L, L-N)	
conducted disturbances, IEC/EN 61000-4-6	Le	evel 3 (10 V)	
induced by radio-frequency fields harmonics and interharmonics IEC/EN 61000-4-13	-	Class 3	
Interference emission	IEC/EN 61000	-6-3, IEC/EN 61000-6-4	
high-frequency radiated IEC/CISPR 22, EN 50022		Class B	
high-frequency conducted IEC/CISPR 22, EN 50022		Class B	

<sup>1)</sup> Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value