

# Signal Conditioning & *Communication Interfaces* **Product Catalog**

PERFORMANCE  
MADE  
SMARTER



TEMPERATURE | I.S. INTERFACES | COMMUNICATION INTERFACES | MULTIFUNCTIONAL | ISOLATION | DISPLAY

**PR**  
electronics

# *Our purpose*

is to create market-leading site standard solutions with high signal integrity and simplicity for our customers, concentrating on innovation in six core business areas: Temperature, I.S. Interfaces, Communication Interfaces, Multifunctional, Isolation and Display.

Our products are individually outstanding, but when our point-to-point temperature measurement devices, I.S. interfaces, backplanes, multifunctional signal devices and future-proof communication interfaces are combined, our solutions are truly unrivalled.

# *We will be*

our customer's trusted partner for the best and most innovative signal conditioning solutions in the process and factory automation industries.

# *We provide*

a wide range of benefits to our customers through innovative solutions and close collaboration:

- The highest signal integrity from your measurement point to control system
- Maximum uptime based on our Install and Forget® philosophy
- Easy and cost-effective deployment and monitoring with intuitive communication interfaces
- Site standard devices that are easily programmable to suit your specific application
- Day-to-day delivery

Since 1974, we have been dedicated to perfecting our core competence of innovating high precision technology with low power consumption. With a dedicated R&D center that is integrated with our lean production facility at our headquarters in Denmark, we are today one of the leading companies within signal conditioning.



# CONTENTS

## MULTIFUNCTIONAL TRANSMITTERS

3114 - 4104 - 4114 - 4116 - 4131.....	4
5114A - 5115A - 5116A - 5131A - 9116A.....	5

## FREQUENCY / PULSE

4222 - 5202A - 5223A - 5225 - 9202A.....	6
--	---

## ISOLATORS

3103 - 3104 - 3105 - 3108 - 3109 - 3117.....	7
3118 - 3185 - 3186 - 5104A - 5106A - 6185 .....	8
9106A .....	9

## TEMPERATURE TRANSMITTERS

3101 - 3102 - 3111 - 3112 - 3113.....	10
3331 - 3333 - 3337.....	11
5331A - 5333A - 5334A - 5335/7A - 5343A - 5350A .....	12
6331A - 6333A - 6334A - 6335/7A - 6350A - 9113A .....	13

## I.S. TEMPERATURE TRANSMITTERS

5331D - 5333D - 5334B - 5335/7D - 5343B - 5350B .....	14
6331B - 6333B - 6334B - 6335/7D - 6350B.....	15
7501.....	16

## I.S. INTERFACES

9106B - 9107B - 9113B - 9116B - 9202B - 9203B.....	17
5104B - 5105B - 5106B - 5107B - 5114B - 5115B.....	18
5116B - 5131B - 5202B - 5203B - 5223B - 5420B.....	19

## DISPLAYS

5531A - 5531B1 - 5714 - 5715 - 5725.....	20
--	----

## I.S. DISPLAYS

5531B - 5531B2.....	21
---------------------	----

## POWER SUPPLIES

3405 - 9410 - 9420.....	22
-------------------------	----

## SPECIAL PRODUCTS

2224 - 2231 - 2261.....	23
2255 - 2279.....	24

## BACKPLANE

.....	25
-------	----

## SIGNAL TYPES

.....	25
-------	----

## PROGRAMMING UNITS

4501 - 4511 - 4590 - 5909.....	26
--------------------------------	----

## POWER RAIL

3000 power rail - 9000 power rail.....	27
--	----

## ENVIRONMENTAL SPECIFICATIONS

.....	27
-------	----

## ENCLOSURE SPECIFICATIONS

.....	27
-------	----

# MULTIFUNCTIONAL TRANSMITTERS



TYPE	3114	4104	4114	4116	4131	
<b>INPUT:</b>	Isolated universal converter	Universal uni-/bipolar signal transmitter	Universal transmitter	Universal transmitter	Universal trip amplifier	
<b>RTD, TC, linear resistance, mV, mA, V, potentiometer</b>						
<b>OUTPUT:</b>	mA, V, relays					
mA, measurement range / min. span	0...23 mA / 16 mA	-23...+23 mA	0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA	
V, measurement range / min. span	0...12 VDC / 0.8 V	-12...+12 VDC / 0.8 V	0...12 VDC / 0.8 V	0...12 VDC / 0.8 V	0...12 VDC / 0.8 V	
RTD, measurement range / min. span	-200...+850°C / 25°C	-200...+850°C / -	-200...+850°C / -	-200...+850°C / -	-200...+850°C / -	
Lin. R, measurement range / min. span	0...10000 Ω / -	0...10000 Ω / -	0...10000 Ω / -	0...10000 Ω / -	0...10000 Ω / -	
Potentiometer	10 Ω...100 kΩ		10 Ω...100 kΩ	10 Ω...100 kΩ	10 Ω...100 kΩ	
Sensor connection, wires	2 - 3 - 4		2 - 3 - 4	2 - 3 - 4	2 - 3 - 4	
TC types	BEJKNRSTUW3W5Lr		BEJKNRSTUW3W5Lr	BEJKNRSTUW3W5Lr	BEJKNRSTUW3W5Lr	
Cold junction compensation	Internal		Internal / external	Internal / external	Internal / external	
Reference voltage / 2-wire supply	- / > 15 V	- / 16 VDC	- / 16 VDC	- / 16 VDC	- / 16 VDC	
<b>OUTPUT:</b>						
mA, signal range / min. span	0...23 mA / 16 mA	-23...+23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA	
Load (@ current output)	≤ 600 Ω	≤ 800 Ω	≤ 800 Ω	≤ 800 Ω	≤ 800 Ω	
V, signal range / min. span	0...10 VDC / 0.8 VDC	-10...+10 VDC / 0.8 VDC	0...10 VDC / 0.8 VDC	0...10 VDC / 0.8 VDC	0...10 VDC / 0.8 VDC	
Load (@ voltage output)	≥ 10 kΩ	≥ 500 kΩ				
Relays				2 x SPST, AC: 500 VA	2 x SPST, AC: 500 VA	
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-25...+70°C	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	
Supply voltage, universal AC / DC	- / 16.8...31.2 VDC	21.6...253V / 19.2...300V	21.6...253V / 19.2...300V	21.6...253V / 19.2...300V	21.6...253V / 19.2...300V	
Max. required power	1.2 W	2.5 W	2.0 W	2.5 W	2.0 W	
Isolation voltage, test / operation	2.5 kVAC / 250 VAC	2.3 kVAC / 250 VAC	2.3 kVAC / 250 VAC	2.3 kVAC / 250 VAC	2.3 kVAC / 250 VAC	
Response time	0.4 / 1.0 s	< 20 ms	< 400 ms	< 400 ms	< 400 ms	
Signal dynamics, input / output	24 bit / 16 bit	20 bit / 18 bit	24 bit / 16 bit	24 bit / 16 bit	24 bit / 16 bit	
Accuracy	< ±0.1% of span	< ±0.05% of span	< ±0.1% of span	< ±0.1% of span	< ±0.1% of span	
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	
NAMUR	NE 21, NE 43	NE 21	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43	
Channels	1	1	1	1	1	
Programming	4501 / 4590	4501 / 4511	4501 / 4511	4501 / 4511	4501 / 4511	


## APPROVALS:

ATEX, Zone 2	✓					
IECEx, Zone 2	✓					
FM, Zone 2 - DIV 2	✓	✓	✓	✓	✓	
CCOE	✓					
UL 61010 / 508	✓ / -	- / ✓	- / ✓	- / ✓	- / ✓	
DNV-GL	✓	✓	✓	✓	✓	
EAC	✓	✓	✓	✓	✓	
SIL 2, Hardware Assessment			✓	✓		

## APPLICATION GUIDE:

mA / V / temperature input	✓ / ✓ / ✓	✓ / ✓ / -	✓ / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓	
Bipolar mA / V input		✓ / ✓				
Lin. R / potentiometer input	✓ / ✓		✓ / ✓	✓ / ✓	✓ / ✓	
4...20 mA Tx input	✓	✓	✓	✓	✓	
V-curve function		✓				
Buffered voltage output	✓					
Active / passive current output	✓ / -	✓ / ✓	✓ / -	✓ / -	✓ / -	
Analog / relay output	✓ / -	✓ / -	✓ / -	✓ / ✓	- / ✓	
Custom sensor linearization						
Process signal calibration	✓	✓	✓	✓	✓	
Power rail option	✓					

# MULTIFUNCTIONAL TRANSMITTERS



TYPE	5114A	5115A	5116A	5131A	9116A
<b>INPUT:</b> RTD, TC, linear resistance, mV, mA, V, potentiometer	Programmable transmitter	Signal calculator	Programmable transmitter w. limit switch	2-wire programmable transmitter	Universal converter
<b>OUTPUT:</b> mA, V, relays					

<b>INPUT:</b>	mA, measurement range / min. span	0...100 mA / 4 mA	0...100 mA / 4 mA	0...100 mA / 4 mA	0...100 mA / 4 mA	0...23 mA / 16 mA
V, measurement range / min. span	0...250 VDC / 5 mV	0...250 VDC / 5 mV	0...250 VDC / 5 mV	0...250 VDC / 5 mV	0...12 VDC / 0.8 V	
mV, measurement range / min. span	-150...+150 mV / 5 mV	-150...+150 mV / 5 mV	-2500...+2500 mV/5 mV	-150...+150 mV / 5 mV		
RTD, measurement range / min. span	-200...+850°C / 25°C	-200...+850°C / 25°C	-200...+850°C / 25°C	-200...+850°C / 25°C	-200...+850°C / 25°C	
Lin. R, measurement range / min. span	0...5000 Ω / 30 Ω	0...5000 Ω / 30 Ω	0...5000 Ω / 30 Ω	0...5000 Ω / 30 Ω	0...10000 Ω / -	
Potentiometer	200 Ω...100 kΩ	200 Ω...100 kΩ	200 Ω...100 kΩ		10 Ω...10000 Ω	
Sensor connection, wires	2 - 3 - 4	2 - 3 - 4	2 - 3 - 4	2 - 3 - 4	2 - 3 - 4	
TC types	BE/JKLNRSUW3W5Lr	BE/JKLNRSUW3W5Lr	BE/JKLNRSUW3W5Lr	BE/JKLNRSUW3W5Lr	BE/JKLNRSUW3W5Lr	
Max. offset	50% of selec. max. value	50% of selec. max. value	50% of selec. max. value	50% of selec. max. value		
Cold junction compensation	Internal / external	Internal / external	Internal / external	Internal / external	Internal / external	
Reference voltage / 2-wire supply	2.5 VDC / > 17.1 VDC	2.5 VDC / > 17.1 VDC	2.5 VDC / > 16.5 VDC		- / > 16.5 VDC	
<b>OUTPUT:</b>						
mA, signal range / min. span	0...23 mA / 10 mA	0...23 mA / 10 mA	0...23 mA / 10 mA	3.5...23 mA / 10 mA	0...23 mA / 16 mA	
Load (@ current output)	≤ 600 Ω	≤ 600 Ω	≤ 600 Ω	≤ (V <sub>supply</sub> -7.5)/0.023 [Ω]	≤ 600 Ω	
V, signal range / min. span	0...10 VDC / 0.5 VDC	0...10 VDC / 0.5 VDC	0...10 VDC / 0.5 VDC			
Load (@ voltage output)	≥ 500 kΩ	≥ 500 kΩ	≥ 500 kΩ			
Relays			2 x SPST, AC: 500 VA		1 x SPST, AC: 500 VA	
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	
Supply voltage, universal AC / DC	21.6...253V / 19.2...300V	21.6...253V / 19.2...300V	21.6...253V / 19.2...300V	/ - 7.5...35 VDC	/ 19.2...31.2 VDC	
Max. required power, 1 / 2 channels	2.1 W / 2.8 W	2.1 W / 2.8 W	2.4 W / -	0.8 W	≤ 2.1 W	
Isolation voltage, test / operation	3.75 kVAC / 250 VAC	3.75 kVAC / 250 VAC	3.75 kVAC / 250 VAC	3.75 kVAC / 250 VAC	2.6 kVAC / 250 VAC	
Response time	250 ms...60 s	250 ms...60 s	250 ms...60 s	1...60 s	0.4 / ...60 s	
Signal dynamics, input / output	22 bit / 16 bit	22 bit / 16 bit	22 bit / 16 bit	22 bit / 16 bit	24 bit / 16 bit	
Accuracy	< ±0.05% of span	< ±0.05% of span	< ±0.05% of span	< ±0.05% of span	< ±0.1% of span	
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	
NAMUR	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43	
Channels	1 or 2	2	1	1 or 2	1	
Programming	5909 + DIP switch	5909 + DIP switch	5909	5909 + DIP switch	4501 / 4511	

<b>APPROVALS:</b>					
ATEX, Zone 2					✓
IECEx, Zone 2					
FM, Zone 2					
CCOE					
UL 61010 / 508			- / ✓		✓ / -
DNV-GL	✓	✓	✓		✓
EAC	✓	✓	✓	✓	✓
SIL 2 Full Assessment IEC 61508					✓

<b>APPLICATION GUIDE:</b>					
mA / V / temperature input	✓ / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓
Bipolar mV input	✓	✓	✓	✓	
Lin. R / potentiometer input	✓ / ✓	✓ / ✓	✓ / ✓	✓ / -	✓ / ✓
4...20 mA Tx input	✓	✓	✓	✓	✓
Dual input - math functions		✓			
Buffered voltage output					
Active / passive current output	✓ / ✓	✓ / ✓	✓ / ✓	✓	✓ / ✓
Analog / relay output	✓ / -	✓ / -	✓ / ✓	✓ / -	✓ / ✓
Custom sensor linearization	✓	✓	✓		
Process signal calibration	✓	✓	✓	✓	✓
Power rail option					✓



= Full assessment acc. to IEC 61508

Of span = Of the presently selected range

# FREQUENCY / PULSE



TYPE	4222	5202A	5223A	5225	9202A
<b>INPUT:</b>	Universal I/f converter	Pulse isolator	Programmable f/I - f/f converter	Programmable f/I - f/f converter	Pulse isolator
Frequency, pulse, V, mA, Pt100, TC, mV					
<b>OUTPUT:</b>	mA, V, pulse, relays				
Sensor type	NAMUR / switch	All standard sensors	All standard sensors	NAMUR / switch	
Hz, measurement range / min. span	0...5 kHz	0...20 kHz / 0.001 Hz	0...20 kHz / 0.001 Hz	0...5 kHz	
Min. pulse width	> 100 µs	25 µs	25 µs	> 100 µs	
mA, measurement range / min. span	0...23 mA / 16 mA				
V, measurement range / min. span	0...12 VDC				
RTD, measurement range / min. span	200...+850°C / -				
Lin. R, measurement range / pot.-meter	0 Ω...10 kΩ/10 Ω...100 kΩ				
Sensor connection, wires	2 - 3 - 4				
TC types	BEJKLNRSTUW3W5Lr				
<b>OUTPUT:</b>					
mA, signal range / min. span		0...23 mA / 5 mA	0...23 mA / 5 mA		
V, signal range / min. span		0...10 VDC / 0.25 VDC	0...10 VDC / 0.25 VDC		
Hz, signal range / min. span	0...25000 Hz / 0.001 Hz	0...5 kHz / -		0...5 kHz	
Pulse output	NPN / PNP / TTL	NPN / relay	NPN / PNP or relays	NPN / PNP or relays	NPN / relay
Relays		2 x SPDT, AC: 100 VA	2 x SPST, AC: 500 VA	2 x SPST, AC: 500 VA	1 x SPST, AC: 500 VA
Max. output frequency	25 kHz		1000 Hz	1000 Hz	
Sensor supply	> 16 VDC		5...17 VDC	5...17 VDC	
<b>TECHNICAL SPECIFICATIONS:</b>					
Ambient temperature	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C
Supply voltage, AC / DC	21.6...253V / 19.2...300V	21.6...253V / 19.2...300V	21.6...253V / 19.2...300V	- / 19.2...28.8 VDC	- / 19.2...31.2 VDC
Max. required power, 1 / 2 channels	2.5 W / -	- / 1.5 W or 1.8 W*	3 W	3.5 W	≤ 1.1...1.3 W / ≤ 1.5...1.9 W
Isolation voltage, test / operation	2.3 kVAC / 250 VAC	3.75 kVAC / 250 VAC	3.75 kVAC / 250 VAC	3.75 kVAC / 250 VAC	2.6 kVAC / 250 VAC
Response time	< 1 s		60 ms...1000 s	60 ms...1000 s	200 ms
Signal dynamics, input / output	24 bit / -		- / 16 bit	- / 16 bit	
Accuracy	≤ ±0.1% of span		≤ ±0.1% of span	≤ ±0.1% of span	
Temperature coefficient	≤ ±0.01% of span / °C		≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	
NAMUR	NE 21	NE 21			NE 21
Channels	1	2	1	1	1 or 2
Programming	4501 / 4511	DIP switch	5909 + DIP switch	5909 + DIP switch	4501 / 4511

## APPROVALS:

ATEX, Zone 2				✓	
IECEx, Zone 2					
FM, Zone 2 - DIV 2	✓				
CCOE					
UL 61010 / 508	- / ✓	- / ✓		✓ / -	
DNV-GL				✓	
EAC	✓	✓	✓	✓	
SIL 2 Full Assessment IEC 61508				✓	

## APPLICATION GUIDE:

Frequency to analog converter		✓	✓	✓	
Analog to frequency converter	✓				
Lin. R / potentiometer input	✓ / ✓				
Concurrent f/I and f/f				✓	
Pulse converter / scaler			✓	✓	
Pulse isolator 1:1					✓
Dual input - math functions		✓	✓		
Digital output	✓		✓	✓	✓
Relay output		✓	✓	✓	✓
Process signal calibration	✓	✓	✓	✓	
Power rail option					✓




= Full assessment acc. to IEC 61508

\*1.5 W (2 relays) / 1.8 W (4 relays)

Of span = Of the presently selected range

# ISOLATORS



TYPE	3103	3104	3105	3108	3109	3117
<b>INPUT:</b> mA, V, potentiometer	Isolated repeater	Isolated converter	Isolated converter	Isolated repeater / splitter	Isolated converter / splitter	Bipolar isolated converter
<b>OUTPUT:</b> mA, V						

<b>INPUT:</b>	mA, measurement range / min. span	0...23 mA / 1:1	0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 1:1	0...23 mA / 16 mA	-23...+23 mA
V, measurement range / min. span		0...10.25 VDC / 4 VDC	0...10.25 VDC / 4 VDC			0...10.25 VDC / 4 VDC	±5 and ±10 VDC
Reference voltage / 2-wire supply		- / > 17 V				- / > 17 V	
<b>OUTPUT:</b>	mA, signal range / min. span	0...23 mA / 1:1	0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 1:1	0...23 mA / 16 mA	0...23 mA / 16 mA
Load (@ current output)	≤ 600 Ω	≤ 600 Ω	≤ 600 Ω	≤ 300 Ω per channel	≤ 300 Ω per channel	≤ 600 Ω	≤ 600 Ω
V, signal range / min. span	0...10 VDC / 4 VDC	0...10 VDC / 4 VDC			0...10 VDC / 4 VDC	0...10 VDC / 4 VDC	
Load (@ voltage output)	≥ 10 kΩ	≥ 10 kΩ	≥ 10 kΩ		≥ 10 kΩ	≥ 10 kΩ	≥ 10 kΩ
<b>TECHNICAL SPECIFICATIONS:</b>	Ambient temperature	-25...+70°C	-25...+70°C	0...+70°C	-25...+70°C	-25...+70°C	-25...+70°C
Supply voltage, AC / DC	- / 16.8...31.2 VDC	- / 16.8...31.2 VDC	- / 16.8...31.2 VDC	- / 16.8...31.2 VDC	- / 16.8...31.2 VDC	- / 16.8...31.2 VDC	- / 16.8...31.2 VDC
Max. required power*	0.65 W	1.2 W	0.8 W	0.75 W	1.2 W	0.8 W	
Isolation voltage, test / operation	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC
Response time	< 7 ms	< 7 ms	< 7 ms	< 7 ms	< 7 ms	< 7 ms	< 7 ms
Signal dynamics, input / output	Analog signal chain	Analog signal chain	Analog signal chain	Analog signal chain	Analog signal chain	Analog signal chain	Analog signal chain
Accuracy	< ±0.05% of span	< ±0.05% of span	< ±0.2% of span	< ±0.05% of span	< ±0.05% of span	< ±0.05% of span	< ±0.05% of span
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.015% of span / °C	< ±0.01% of span / °C			
NAMUR	NE 21	NE 21	NE 21	NE 21	NE 21	NE 21	NE 21
Channels	1	1	1	1	1	1	1
Programming	No	DIP switch	DIP switch	No	DIP switch	DIP switch	DIP switch

<b>APPROVALS:</b>	ATEX, Zone 2	✓	✓		✓	✓	✓
IECEx, Zone 2	✓	✓			✓	✓	✓
FM, Zone 2 - DIV 2	✓	✓			✓	✓	✓
CCOE	✓	✓			✓	✓	✓
UL 61010 / 508	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -
DNV-GL	✓	✓	✓	✓	✓	✓	✓
EAC	✓	✓	✓	✓	✓	✓	✓


<b>APPLICATION GUIDE:</b>	Signal repeater	✓			✓		
Signal converter		✓	✓	✓		✓	✓
Signal splitter					✓	✓	
mA / V bipolar input							✓
4...20 mA Tx input		✓				✓	
Buffered voltage output		✓	✓	✓		✓	✓
mA / V output	✓ / -	✓ / ✓	✓ / ✓	✓ / -	✓ / -	✓ / ✓	✓ / ✓
Active / passive mA output	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -
Mounting in Zone 2 / Div 2	✓	✓	✓	✓	✓	✓	✓
Power rail option	✓	✓	✓	✓	✓	✓	✓







\* = @ 24 VDC

Of span = Of the presently selected range

# ISOLATORS

**HART**   
COMMUNICATION FOUNDATION



TYPE	3118	3185	3186	5104A	5106A	6185
<b>INPUT, DC:</b> mA, mV, V, HART communication	Bipolar isolated converter / splitter	Loop-powered isolator	2-wire transmitter isolator	Repeater / power supply	HART transparent repeater	Loop-powered isolator
<b>OUTPUT:</b> mA, V, HART communication						
<b>INPUT:</b>						
mA, measurement range / min. span	-23...+23 mA	0...23 mA / 1:1	3.5...23 mA / 1:1	0...23 mA / 16 mA	3.5...23 mA / 1:1	0...23 mA / 1:1
V, measurement range / min. span	±5 and ±10 VDC			0...10 VDC / 8 VDC		
Max. offset				20% of selec. max. value		
Reference voltage / 2-wire supply			- / V <sub>loop</sub> -2.5 VDC	- / > 17.1 VDC	- / > 17 VDC	
<b>OUTPUT:</b>						
mA, signal range / min. span	0...23 mA / 16 mA	0...23 mA / 1:1	3.5...23 mA / 1:1	0...23 mA / 16 mA	3.5...23 mA / 1:1	0...23 mA / 1:1
Load (@ current output)	≤ 300 Ω per channel	≤ 600 Ω		≤ 600 Ω	≤ 600 Ω	≤ 600 Ω
V, signal range / min. span	0...10 VDC / 4 VDC			0...10 VDC / 0.8 VDC		
Load (@ voltage output)	≥ 10 kΩ			≥ 500 kΩ		
Max. offset				20% of selec. max. value		
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-25...+70°C	-25...+70°C	-25...+70°C	-20...+60°C	-20...+60°C	-20...+60°C
Supply voltage, AC / DC	- / 16.8...31.2 VDC	≤ 1.25 V + (0.015 x V <sub>out</sub> )	- / 6...35 VDC	21.6...253 V / 19.2...300 V	21.6...253 V / 19.2...300 V	- / ≤ 1.8 VDC
Max. required power, 1 / 2 channels	*0.8 W / -	30 mW per channel	50 mW per channel	2.0 W / 2.8 W	2.0 W / 2.8 W	40 mW per channel
Isolation voltage, test / operation	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC	2.5 kVAC / 250 VAC	3.75 kVAC / 250 VAC	3.75 kVAC / 250 VAC	2 kVAC / -
Response time	< 7 ms	< 5 ms	< 5 ms	< 25 ms	< 25 ms	< 4 ms
Signal dynamics, input / output	Analog signal chain	Analog signal chain	Analog signal chain	Analog signal chain	Analog signal chain	Analog signal chain
Accuracy	< ±0.05% of span	< ±0.1% of span	< ±0.05% of span	< ±0.1% of span	< ±0.1% of span	< ±0.1% of span
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C			
NAMUR	NE 21	NE 21	NE 21	NE 21	NE 21	
Channels	1	1 or 2	1 or 2	1 or 2	1 or 2	1, 2 or 4
Programming	DIP switch	No	No	DIP switch	DIP switch	No

APPROVALS:						
ATEX, Zone 2	✓	✓	✓			
IECEx, Zone 2	✓	✓	✓			
FM, Zone 2 - DIV 2	✓	✓	✓			
CCOE	✓	✓	✓			
UL 61010 / 508	✓ / -	✓ / -	✓ / -	- / ✓	- / ✓	
DNV-GL	✓	✓	✓	✓		
EAC	✓	✓	✓	✓	✓	✓

APPLICATION GUIDE:						
Signal repeater		✓	✓	✓	✓	✓
Signal converter	✓			✓		
Signal splitter	✓					
mA / V bipolar input	✓ / ✓					
4...20 mA Tx input			✓	✓	✓	
Buffered voltage output	✓					
Active / passive input signal		✓ / -	✓ / ✓			✓ / -
mA / V output	✓ / ✓	✓ / -	✓ / -	✓ / ✓	✓ / -	✓ / -
Active / passive mA output	✓ / -	✓ / -	- / ✓	✓ / ✓	✓ / ✓	✓ / -
Mounting in Zone 2 / Div 2	✓	✓	✓			
Power rail option	✓					

\* = @ 24 VDC

Of span = Of the presently selected range


**TYPE 9106A**

<b>INPUT, DC:</b> mA, HART communication	HART transparent repeater					
<b>OUTPUT:</b> mA, HART communication						


<b>INPUT:</b>						
mA, measurement range / min. span	3.5...23 mA / 16 mA					
V, measurement range / min. span						
Max. offset						
Reference voltage / 2-wire supply	- / > 16 VDC					
<b>OUTPUT:</b>						
mA, signal range / min. span	3.5...23 mA					
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-20...+60°C					
Supply voltage, AC / DC	- / 19.2...31.2 VDC					
Max. required power, 1 / 2 channels	≤ 1.1 W / ≤ 1.9 W					
Isolation voltage, test / operation	2.6 kVAC / 250 VAC					
Response time	< 5 ms					
Signal dynamics,input	Analog signal chain					
Accuracy	≤ ±16 µA					
Temperature coefficient	≤ ±1.6 µA / °C					
NAMUR	NE 21					
Channels	1 or 2					
Programming	4501 / 4511					

<b>APPROVALS:</b>						
ATEX, Zone 2	✓					
IECEx, Zone 2						
FM, Zone 2 - DIV 2						
CCOE						
UL 61010 / 508	✓ / -					
DNV-GL	✓					
EAC	✓					
SIL 2/3 Full Assessment IEC 61508	✓					

<b>APPLICATION GUIDE:</b>						
Signal repeater	✓					
Signal converter						
Signal splitter	✓					
mA / V bipolar input						
4...20 mA Tx input	✓					
Active / passive input signal						
mA / V output	✓ / -					
Active / passive mA output	✓ / ✓					
Mounting in Zone 2 / Div 2	✓					
Power rail option	✓					

# TEMPERATURE TRANSMITTERS

**HART**  
COMMUNICATION FOUNDATION



TYPE	3101	3102	3111	3112	3113
<b>INPUT:</b>	TC converter	Pt100 converter	TC converter - isolated	Pt100 converter - isolated	HART 7 temperature converter
RTD, linear resistance, TC, mV, mA, potentiometer					
<b>OUTPUT:</b>					
RTD, measurement range / min. span		-200...+850°C / 10°C		-200...+850°C / 10°C	-200...+850°C / 10°C
Lin. R, measurement range / min. span					
Sensor connection, wires	2 - 3 - 4			2 - 3 - 4	2 - 3 - 4
TC types	J & K		J & K		J & K
Max. offset					
Cold junction compensation	Internal		Internal / external		Internal / external
<b>OUTPUT:</b>					
mA, signal range / min. span	0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA
Load (@ current output)	≤ 600 Ω	≤ 600 Ω	≤ 600 Ω	≤ 600 Ω	≤ 600 Ω
V, signal range / min. span	0...10 VDC / 4 VDC	0...10 VDC / 4 VDC	0...10 VDC / 4 VDC	0...10 VDC / 4 VDC	
Load (@ voltage output)	≥ 10 kΩ	≥ 10 kΩ	≥ 10 kΩ	≥ 10 kΩ	
<b>TECHNICAL SPECIFICATIONS:</b>					
Ambient temperature	-25...70°C	-25...70°C	-25...70°C	-25...70°C	-25...70°C
Supply voltage, DC	16.8...31.2 VDC	16.8...31.2 VDC	16.8...31.2 VDC	16.8...31.2 VDC	16.8...31.2 VDC
Max. required power*	0.52 W	0.52 W	0.7 W	0.7 W	0.7 W
Isolation voltage, test / operation			2.5 KVAC / 250 VAC	2.5 KVAC / 250 VAC	2.5 KVAC / 250 VAC
Response time	< 30 ms	< 30 ms	< 30 ms	< 30 ms	< 60 ms
Signal dynamics, input / output	23 bit / 18 bit	23 bit / 18 bit	23 bit / 18 bit	23 bit / 18 bit	23 bit / 18 bit
Accuracy	≤ ±0.1% of span	≤ ±0.1% of span	≤ ±0.05% of span	≤ ±0.05% of span	≤ ±0.05% of span
Temperature coefficient	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C
NAMUR	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43
Channels	1	1	1	1	1
Programming	DIP switch	DIP switch	DIP switch	DIP switch	DIP switch / HART
<b>APPROVALS:</b>					
ATEX, Zone 2	✓	✓	✓	✓	✓
IECEx, Zone 2	✓	✓	✓	✓	✓
FM, Zone 2 - DIV 2	✓	✓	✓	✓	✓
CCOE	✓	✓	✓	✓	✓
UL 61010 / 508	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -
DNV-GL	✓	✓	✓	✓	✓
EAC	✓	✓	✓	✓	✓


APPLICATION GUIDE:					
RTD / TC / mV input	- / ✓ / -	✓ / - / -	- / ✓ / -	✓ / - / -	✓ / ✓ / -
mA / V output	✓ / ✓	✓ / ✓	✓ / ✓	✓ / ✓	✓ / -
Loop-powered					
Galvanically isolated			✓	✓	✓
HART protocol					✓
Mounting in Zone 2 / DIV 2	✓ / ✓	✓ / ✓	✓ / ✓	✓ / ✓	✓ / ✓
Process signal calibration					✓
Power rail option			✓	✓	✓

\* = @ 24 VDC

Of span = Of the presently selected range

# TEMPERATURE TRANSMITTERS

**HART**  
COMMUNICATION FOUNDATION



TYPE	3331	3333	3337			
<b>INPUT:</b>	Temperature converter, loop-powered - isolated	Pt100 converter, loop-powered	HART 7 temperature converter, loop-powered			
RTD, linear resistance, TC, mV						
<b>OUTPUT:</b>	mA, V, HART communication					

<b>INPUT:</b>						
RTD, measurement range / min. span	-200...+850°C / 10°C	-200...+850°C / 10°C	-200...+850°C / 10°C			
Lin. R, measurement range / min. span						
Sensor connection, wires	2 - 3 - 4	2 - 3 - 4	2 - 3 - 4			
TC types	J & K		J & K			
Max. offset						
Cold junction compensation	Internal / external		Internal / external			
<b>OUTPUT:</b>						
mA, signal range / min. span	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA			
Load (@ current output)	≤ (V <sub>supply</sub> -5.5)/0.023 [Ω]	≤ (V <sub>supply</sub> -3.3)/0.023 [Ω]	≤ (V <sub>supply</sub> -6.2)/0.023 [Ω]			
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-25...70°C	-25...70°C	-25...70°C			
Supply voltage, DC	5.5...35 VDC	3.3...35 VDC	6.2...35 VDC			
Max. required power	0.8 W	0.8 W	0.8 W			
Isolation voltage, test / operation	2.5 kVAC / 250 VAC		2.5 kVAC / 250 VAC			
Response time	< 30 ms	< 30 ms	< 60 ms			
Signal dynamics, input / output	23 bit / 18 bit	23 bit / 18 bit	23 bit / 18 bit			
Accuracy	≤ ±0.05% of span	≤ ±0.1% of span	≤ ±0.05% of span			
Temperature coefficient	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C			
NAMUR	NE 21, NE 43	NE 21, NE 43	NE 21, NE 43			
Channels	1	1	1			
Programming	DIP switch	DIP switch	DIP switch / HART			

<b>APPROVALS:</b>						
ATEX, Zone 2	✓	✓	✓			
IECEx, Zone 2	✓	✓	✓			
FM, Zone 2 - DIV 2	✓	✓	✓			
CCOE	✓	✓	✓			
UL 61010 / 508	✓ / -	✓ / -	✓ / -			
DNV-GL	✓	✓	✓			
EAC	✓	✓	✓			

<b>APPLICATION GUIDE:</b>						
RTD / TC / mV input	✓ / ✓ / -	✓ / - / -	✓ / ✓ / -			
mA / V output	✓ / -	✓ / -	✓ / -			
Loop-powered	✓	✓	✓			
Galvanically isolated	✓		✓			
HART protocol			✓			
Mounting in Zone 2 / DIV 2	✓ / ✓	✓ / ✓	✓ / ✓			
Process signal calibration			✓			


Of span = Of the presently selected range

# TEMPERATURE TRANSMITTERS



TYPE	5331A	5333A	5334A	5335/7A	5343A	5350A
<b>INPUT:</b>	2-wire programmable transmitter	2-wire programmable transmitter	2-wire programmable transmitter	2-wire transmitter with HART protocol	2-wire level transmitter	Profibus PA / Foundation Fieldbus transmitter
<b>RTD, linear resistance, TC, mV, potentiometer</b>						
<b>mA, HART communication, Profibus PA, Foundation Fieldbus</b>						
<b>INPUT:</b>						
mV, measurement range / min. span	-12...800 mV / 5 mV		-12...150 mV / 5 mV	-800...+800 mV / 2.5 mV		-800...+800 mV / -
RTD, measurement range / min. span	-200...+850°C / 25°C	-200...+850°C / 25°C		-200...+850°C / 10°C		-200...+850°C / -
Lin. R, measurement range / min. span	0...5000 Ω / 30 Ω	0...10 kΩ / 30 Ω		0...7000 Ω / 25 Ω		0...10 kΩ / -
Potentiometer					0...100 kΩ / 1 kΩ	0...100 kΩ
Sensor connection, wires	2 - 3 - 4	2 - 3		2 - 3 - 4		2 - 3 - 4
TC types	BEJKLNRSTUW3W5Lr		BEJKLNRSTUW3W5Lr	BEJKLNRSTUW3W5		BEJKLNRSTUW3W5
Max. offset	50% of selec. max. value	50% of selec. max. value				
Cold junction compensation	Internal / external		Internal	Internal / external	Internal / external	Internal / external
<b>OUTPUT:</b>						
mA, signal range / min. span	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	Profibus PA/Foundation F.			
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C
Supply voltage, DC	7.2...35 VDC	8...35 VDC	7.2...35 VDC	8...35 VDC	8...35 VDC	9...32 VDC
Max. required power	0.8 W	0.8 W	0.8 W	0.8 W	0.8 W	< 350 mW
Isolation voltage, test / operation	1500 VAC / 50 V		1500 VAC / 50 V	1500 VAC / 50 V		1500 VAC / 50 V
Response time	1...60 s	0.33...60 s	1...60 s	1...60 s	0.33...60 s	1...60 s
Signal dynamics, input / output	20 bit / 16 bit	19 bit / 16 bit	18 bit / 16 bit	22 bit / 16 bit	19 bit / 16 bit	24 bit / -
Accuracy	≤ ±0.05% of span	≤ ±0.1% of span	≤ ±0.05% of span	≤ ±0.05% of span	≤ ±0.1% of span	≤ ±0.05% of MV
Temperature coefficient	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.005% of span / °C	≤ ±0.01% of span / °C	≤ ±0.002% of MV / °C
NAMUR	NE 21, NE 43	NE 43	NE 21, NE 43	NE 21, NE 43, NE89	NE 43	NE 21, NE 43
Channels	1	1	1	1	1	1
Programming	5909	5909	5909	5909/HART 5/HART 7	5909	Profibus PA/Foundation F.
<b>APPROVALS:</b>						
ATEX, Zone 2	✓	✓	✓	✓	✓	✓
IECEx, Zone 2	✓	✓	✓	✓	✓	
CSA, Zone 2 - DIV 2						✓
FM, Zone 2 - DIV 2						✓
CCOE	✓	✓	✓			
INMETRO	✓	✓	✓	✓	✓	
NEPSI						✓
DNV-GL	✓	✓	✓	✓	✓	
EAC	✓	✓	✓	✓	✓	✓
SIL 2, Hardware Assessment				✓		
<b>APPLICATION GUIDE:</b>						
RTD / TC / mV input	✓ / ✓ / ✓	✓ / - / -	- / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓
Lin. R / potentiometer input	✓ / -	✓ / -		✓ / -	✓ / ✓	✓ / ✓
Dual sensor input				✓		✓
Custom sensor linearization	✓	✓	✓	✓	✓	✓
mA / V output	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -	
Loop-powered	✓	✓	✓	✓	✓	
Galvanically isolated	✓		✓	✓		✓
HART protocol				✓		
Mounting in Zone 2 / DIV 2	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -
Process signal calibration	✓	✓	✓	✓	✓	✓

# TEMPERATURE TRANSMITTERS



TYPE	6331A	6333A	6334A	6335/7A	6350A	9113A
<b>INPUT:</b>	2-wire programmable transmitter	2-wire programmable transmitter	2-wire programmable transmitter	2-wire HART transmitter	Profibus PA / Foundation Fieldbus transmitter	Temperature / mA converter
<b>RTD, linear resistance, TC, mV, mA, potentiometer</b>						
<b>mA,</b> <b>HART communication,</b> <b>Profibus PA,</b> <b>Foundation Fieldbus</b>						
<b>OUTPUT:</b>						
<b>mA, signal range / min. span</b>	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	Profibus PA/Foundation F.	0...23 mA / 16 mA
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C	-20...+60°C
Supply voltage, DC	7.2...35 VDC	8...35 VDC	7.2...35 VDC	8...35 VDC	9...32 VDC	19.2...31.2 VDC
Max. required power, 1 / 2 channels	0.8 W / 1.6 W	0.8 W / 1.6 W	0.8 W / 1.6 W	0.8 W / 1.6 W	< 350 mW per channel	≤ 0.8 W / ≤ 1.4 W
Isolation voltage, test / operation	1500 VAC / 50 V		1500 VAC / 50 V	1500 VAC / 50 V	1500 VAC / 50 V	2.6 KVAC / 250 VAC
Response time	1...60 s	0.33...60 s	1...60 s	1...60 s	1...60 s	0.4 / 1...60 s
Signal dynamics, input / output	20 bit / 16 bit	19 bit / 16 bit	18 bit / 16 bit	22 bit / 16 bit	24 bit / -	24 bit / 16 bit
Accuracy	≤ ±0.05% of span	≤ ±0.1% of span	≤ ±0.05% of span	≤ ±0.05% of span	≤ ±0.05% of MV	≤ ±0.1% of span
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.005% of span / °C	< ±0.002% of MV / °C	< ±0.01% of span / °C
NAMUR	NE 21, NE 43	NE 43	NE 21, NE 43	NE 21, NE 43, NE 89	NE 21, NE 43	NE 21, NE 43
Channels	1 or 2	1 or 2	1 or 2	1 or 2	1 or 2	1 or 2
Programming	5909	5909	5909	5909/HART 5/HART 7	Profibus PA/Foundation F.	4501 / 4511
<b>APPROVALS:</b>						
ATEX, Zone 2	✓	✓	✓	✓	✓	✓
IECEx, Zone 2	✓	✓	✓	✓	✓	✓
CSA, Zone 2 - DIV 2					✓	
FM, Zone 2 - DIV 2					✓	
CCOE						
UL 61010 / 508						✓ / -
DNV-GL						✓
EAC	✓	✓	✓	✓	✓	✓
SIL 2, Hardware Assessment				✓		
SIL 2 Full Assessment IEC 61508						✓
<b>APPLICATION GUIDE:</b>						
RTD / TC / mV input	✓ / ✓ / ✓	✓ / - / -	- / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / -
Lin. R / potentiometer input	✓ / -	✓ / -		✓ / -	✓ / ✓	
Dual sensor input				✓	✓	
Custom sensor linearization	✓	✓	✓	✓	✓	
mA / V output	✓ / -	✓ / -	✓ / -	✓ / -		✓ / -
Loop-powered	✓	✓	✓	✓		
Galvanically isolated	✓		✓	✓	✓	✓
HART protocol				✓		
Mounting in Zone 2 / DIV 2	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -	✓ / ✓
Process signal calibration	✓	✓	✓	✓	✓	✓
Power rail option						✓



= Full assessment acc. to IEC 61508



= FMEDA report


Of span = Of the presently selected range

Of MV = Of the present measurement value

# I.S. TEMPERATURE TRANSMITTERS



TYPE	5331D	5333D	5334B	5335/7D	5343B	5350B
<b>INPUT:</b>	2-wire programmable transmitter	2-wire programmable transmitter	2-wire programmable transmitter	2-wire transmitter with HART protocol	2-wire level transmitter	Profibus PA / Foundation Fieldbus transmitter
<b>RTD, linear resistance, TC, mV, potentiometer</b>						
<b>mA, HART communication, Profibus PA, Foundation Fieldbus</b>						
<b>INPUT:</b>						
mV, measurement range / min. span	-12...800 mV / 5 mV		-12...150 mV / 5 mV	-800...+800 mV / 2.5 mV		-800...+800 mV / -
RTD, measurement range / min. span	-200...+850°C / 25°C	-200...+850°C / 25°C		-200...+850°C / 10°C		-200...+850°C / -
Lin. R, measurement range / min. span	0...5000 Ω / 30 Ω	0...10 kΩ / 30 Ω		0...7000 Ω / 25 Ω	0...100 kΩ / 1 kΩ	0...10 kΩ / -
Potentiometer					1 kΩ...100 kΩ	0...100 kΩ
Sensor connection, wires	2 - 3 - 4	2 - 3		2 - 3 - 4		2 - 3 - 4
TC types	BEJKLNRSTUW3W5Lr		BEJKLNRSTUW3W5Lr	BEJKLNRSTUW3W5		BEJKLNRSTUW3W5
Max. offset					50% of selec. max. value	
Cold junction compensation	Internal / external		Internal	Internal / external		Internal / external
<b>OUTPUT:</b>						
mA, signal range / min. span	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	Profibus PA/Foundation F.			
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C
Supply voltage, DC	7.2...30 VDC	8...30 VDC	7.2...30 VDC	8...30 VDC	8...30 VDC	9...32 VDC
Max. required power	0.7 W	0.7 W	0.7 W	0.7 W	0.7 W	< 350 mW
Isolation voltage, test / operation	1500 VAC / 50 V		1500 VAC / 50 V	1500 VAC / 50 V		1500 VAC / 50 V
Response time	1...60 s	0.33...60 s	1...60 s	1...60 s	0.33...60 s	1...60 s
Signal dynamics, input / output	20 bit / 16 bit	19 bit / 16 bit	18 bit / 16 bit	22 bit / 16 bit	19 bit / 16 bit	24 bit / -
Accuracy	≤ ±0.05% of span	≤ ±0.1% of span	≤ ±0.05% of span	≤ ±0.05% of span	≤ ±0.1% of span	≤ ±0.05% of MV
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.005% of span / °C	< ±0.01% of span / °C	< ±0.002% of MV / °C
NAMUR	NE 21, NE 43	NE 43	NE 21, NE 43	NE 21, NE 43, NE89	NE 43	NE 21, NE 43
Channels	1	1	1	1	1	1
Programming	5909	5909	5909	5909/HART 5/HART 7	5909	Profibus PA/Foundation F.
<b>APPROVALS:</b>						
ATEX	✓	✓	✓	✓	✓	✓
IECEx	✓	✓	✓	✓	✓	✓
FM	✓	✓	✓	✓	✓	✓
CSA	✓	✓	✓	✓	✓	✓
CCOE	✓	✓	✓	✓	✓	✓
INMETRO	✓	✓	✓	✓	✓	✓
DNV-GL	✓	✓	✓	✓	✓	✓
EAC Ex	✓	✓	✓	✓	✓	✓
NEPSI						
SIL 2 Hardware Assessment				✓		
<b>APPLICATION GUIDE:</b>						
RTD / TC / mV input	✓ / ✓ / ✓	✓ / - / -	- / ✓ / ✓	✓ / ✓ / ✓		✓ / ✓ / ✓
Lin. R / potentiometer input	✓ / -	✓ / -		✓ / -	✓ / ✓	✓ / ✓
Dual sensor input						
Custom sensor linearization	✓	✓	✓	✓	✓	✓
Bus-powered PA/FF						
Loop-powered	✓	✓	✓	✓	✓	
Galvanically isolated	✓		✓	✓		
HART protocol				✓		
Process signal calibration	✓	✓	✓	✓	✓	✓



TYPE	6331B	6333B	6334B	6335/7D	6350B
<b>INPUT:</b>	2-wire programmable transmitter	2-wire programmable transmitter	2-wire programmable transmitter	2-wire HART transmitter	Profibus PA / Foundation Fieldbus transmitter
<b>RTD, linear resistance, TC, mV, mA, potentiometer</b>					
<b>mA,</b> <b>HART communication,</b> <b>Profibus PA,</b> <b>Foundation Fieldbus</b>					
<b>INPUT:</b>					
mA, measurement range / min. span					
mV, measurement range / min. span	-12...800 mV / 5 mV		-12...+150 mV / 5 mV	-800...+800 mV / 2.5 mV	-100...+100 mA
RTD, measurement range / min. span	-200...+850°C / 25°C	-200...+850°C / 25°C		-200...+850°C / 10°C	-200...+850°C / -
Lin. R, measurement range / min. span	0...5000 Ω / 30 Ω	0...10 kΩ / 30 Ω		0...7000 Ω / 25 Ω	0...10 kΩ / -
Potentiometer					0...100 kΩ / -
Sensor connection, wires	2 - 3 - 4	2 - 3		2 - 3 - 4	2 - 3 - 4
TC types	BEJKLNRSTUW3W5Lr		BEJKLNRSTUW3W5Lr	BEJKLNRSTUW3W5	BEJKLNRSTUW3W5
Max. offset	50% of selec. max. value	50% of selec. max. value	50% of selec. max. value	50% of selec. max. value	
Cold junction compensation	Internal / external		Internal	Internal / external	Internal / external
<b>OUTPUT:</b>					
mA, signal range / min. span	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	Profibus PA/Foundation F.
<b>TECHNICAL SPECIFICATIONS:</b>					
Ambient temperature	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C	-40...+85°C
Supply voltage, DC	7.2...30 VDC	8...30 VDC	7.2...30 VDC	8...30 VDC	9...32 VDC
Max. required power, 1 / 2 channels	0.7 W / 1.4 W	0.7 W / 1.4 W	0.7 W / 1.4 W	0.7 W / 1.4 W	< 350 mW per channel
Isolation voltage, test / operation	1500 VAC / 50 V		1500 VAC / 50 V	1500 VAC / 50 V	1500 VAC / 50 V
Response time	1...60 s	0.33...60 s	1...60 s	1...60 s	1...60 s
Signal dynamics, input / output	20 bit / 16 bit	19 bit / 16 bit	18 bit / 16 bit	22 bit / 16 bit	24 bit / -
Accuracy	≤ ±0.05% of span	≤ ±0.1% of span	≤ ±0.05% of span	≤ ±0.05% of span	≤ ±0.05% of MV
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.005% of span / °C	< ±0.002% of MV / °C
NAMUR	NE 21, NE 43	NE 43	NE 21, NE 43	NE 21, NE 43, NE 89	NE 21, NE 43
Channels	1 or 2	1 or 2	1 or 2	1 or 2	1 or 2
Programming	5909	5909	5909	5909/HART 5/HART 7	Profibus PA/Foundation F.
<b>APPROVALS:</b>					
ATEX	✓	✓	✓	✓	✓
IECEx	✓	✓	✓	✓	✓
FM	✓	✓		✓	✓
CSA	✓	✓		✓	✓
UL					
DNV-GL					
EAC Ex	✓	✓	✓	✓	✓
SIL 2, Hardware Assessment				✓	
<b>APPLICATION GUIDE:</b>					
RTD / TC / mV input	✓ / ✓ / ✓	✓ / - / -	- / ✓ / ✓	✓ / ✓ / ✓	✓ / ✓ / ✓
Lin. R / potentiometer input	✓ / -	✓ / -		✓ / -	✓ / ✓
Dual sensor input				✓	✓
Custom sensor linearization	✓	✓	✓	✓	✓
Bus-powered PA/FF					✓ / ✓
Loop-powered	✓	✓	✓	✓	
Galvanically isolated	✓		✓	✓	✓
HART protocol				✓	
Process signal calibration	✓	✓	✓	✓	✓



## TYPE

## 7501


## INPUT:

RTD, linear resistance,  
TC, mV, potentiometer

## OUTPUT:

mA,  
HART communication,  
Profibus PA,  
Foundation Fieldbus

Field mounted  
HART temperature  
transmitter



## INPUT:

RTD, measurement range / min. span	-200...+850°C / 10°C				
Lin. R, measurement range / min. span	0...7000 Ω / 25 Ω				
Sensor connection, wires	2 - 3 - 4				
TC types	BEJKNRSTUW3W5				

## OUTPUT:

mA, signal range / min. span	3.5...23 mA / 16 mA				
------------------------------	---------------------	--	--	--	--

## TECHNICAL SPECIFICATIONS:

Ambient temperature	-40...+85°C				
Supply voltage, DC	10 / 12...30 / 35 VDC				
Max. required power					
Isolation voltage, test / operation	1500 VAC / 50 V				
Signal dynamics, input / output	22 bit / 16 bit				
Response time	1...60 s				
Accuracy	≤ ±0.05% of span				
Temperature coefficient	< ±0.005% of span / °C				
NAMUR	NE 21, NE 43				
Channels	1				
Programming	LOI / HART				

## APPROVALS:

ATEX	✓				
IECEx	✓				
FM	✓				
CSA	✓				
CCOE					
INMETRO	✓				
EU-RO marine	✓				
EAC Ex	✓				
NEPSI	✓				

## APPLICATION GUIDE:

RTD / TC / mV input	✓ / ✓ / ✓				
Lin. R / potentiometer input	✓ / -				
Dual sensor input	✓				
Custom sensor linearization	✓				
Bus-powered PA/FF					
Loop-powered	✓				
Galvanically isolated	✓				
HART protocol	✓				
Process signal calibration	✓				



TYPE	9106B	9107B	9113B	9116B	9202B	9203B
<b>INPUT:</b>	HART transparent repeater	HART transparent driver	Temperature / mA converter	Universal converter	Pulse isolator	Solenoid / alarm driver
<b>mA, mV, V, potentiometer,</b> <b>RTD, Lin. R, TC, Hz,</b> <b>HART communication</b>						
<b>mA, relays,</b> <b>HART communication</b>						
<b>OUTPUT:</b>						
<b>mA, measurement range / min. span</b>	3.5...23 mA / 16 mA	3.5 ...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA		
<b>V, measurement range / min. span</b>						
<b>RTD, measurement range / min. span</b>			-200...+850°C / 25°C			
<b>Lin. R, measurement range / min. span</b>				-200...+850°C / 25°C		
<b>Potentiometer</b>				0...10000 Ω / -		
<b>Sensor connection, wires</b>			2 - 3 - 4	2 - 3 - 4		
<b>TC types</b>			BEJKLNRSTUW3W5Lr	BEJKLNRSTUW3W5Lr		
<b>Sensor type</b>					NAMUR / switch	NPN / PNP / switch
<b>Hz, measurement range / min. span</b>					0..5 kHz	
<b>Min. pulse width</b>					100 µs	
<b>OUTPUT:</b>						
<b>mA, signal range / min. span</b>	3.5...23 mA / 16 mA	3.5...23 mA / 16 mA	0...23 mA / 16 mA	0 ...23 mA / 16 mA		
<b>Pulse output</b>					NPN / relay	Valves etc.
<b>Hz, signal range</b>					0..5 kHz	
<b>Relay</b>					1 x SPST, AC: 500 VA	1 x SPST, AC: 500 VA
<b>TECHNICAL SPECIFICATIONS:</b>						
<b>Ambient temperature</b>	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C
<b>Supply voltage, DC</b>	19.2...31.2 VDC	19.2...31.2 VDC	19.2...31.2 VDC	19.2...31.2 VDC	19.2...31.2 VDC	19.2...31.2 VDC
<b>Max. required power, 1 / 2 channels</b>	≤ 1.1 W / ≤ 1.9 W	≤ 1.0 W / ≤ 1.8 W	≤ 0.8 W / ≤ 1.4 W	≤ 2.1 W / -	≤ 1.1...1.3 W / ≤ 1.5...1.9 W	≤ 1.9...2.5 W / ≤ 3.1 W
<b>Isolation voltage, test / operation</b>	2.6 kVAC / 250 VAC	2.6 kVAC / 250 VAC	2.6 kVAC / 250 VAC	2.6 kVAC / 250 VAC	2.6 kVAC / 250 VAC	2.6 kVAC / 250 VAC
<b>Response time</b>	< 5 ms	< 5 ms	0.4 / 1...60 s	0.4 / 1...60 s	200 ms	< 10 ms
<b>Signal dynamics, input / output</b>	Analog signal chain	Analog signal chain	24 bit / 16 bit	24 bit / 16 bit		
<b>Accuracy</b>	≤ ±16 µA	≤ ±16 µA	≤ ±0.1% of span	≤ ±0.1% of span		
<b>Temperature coefficient</b>	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C		
<b>NAMUR</b>	NE 21	NE 21	NE 21, NE 43	NE 21, NE 43	NE 21	NE 21
<b>Channels</b>	1 or 2	1 or 2	1 or 2	1	1 or 2	1 or 2
<b>Programming</b>	4501 / 4590	4501 / 4511	4501 / 4511	4501 / 4511	4501 / 4511	4501 / 4511
<b>APPROVALS:</b>						
ATEX	✓	✓	✓	✓	✓	✓
IECEx	✓	✓	✓	✓	✓	✓
FM	✓	✓	✓	✓	✓	✓
CCOE	✓	✓	✓	✓	✓	✓
INMETRO	✓	✓	✓	✓	✓	✓
UL 61010	✓	✓	✓	✓	✓	✓
DNV-GL	✓	✓	✓	✓	✓	✓
EAC Ex	✓	✓	✓	✓	✓	✓
SIL 2/3 Full Assessment IEC 61508	✓	✓ / -	✓ / -	✓ / -	✓ / -	✓ / -

APPLICATION GUIDE:	AI barrier	AO barrier	DI barrier	DO barrier		
AI barrier	✓					
AO barrier		✓				
DI barrier						
DO barrier						
mA / V / temperature input	✓ / - / -	✓ / - / -	✓ / - / ✓	✓ / ✓ / ✓		
4...20 mA Tx input	✓					
mA / V / relay output	✓ / - / -	✓ / - / -	✓ / - / -	✓ / - / ✓	- / - / ✓	
Active / passive mA output	✓ / ✓	✓ / -	✓ / ✓	✓ / ✓		
HART signal transparent	✓	✓				
Process signal calibration						
Power rail option	✓	✓				



= Full assessment acc. to IEC 61508


Of span = Of the presently selected range



TYPE	5104B	5105B	5106B	5107B	5114B	5115B
<b>INPUT:</b> mA, mV, V, potentiometer, RTD, linear resistance, TC, HART communication	Ex repeater / power supply	Ex-isolated driver	HART transparent repeater	HART transparent driver	Programmable transmitter	Signal calculator
<b>OUTPUT:</b> mA, V, relays, HART communication						
<b>INPUT:</b> mA, measurement range / min. span V, measurement range / min. span mV, measurement range / min. span RTD, measurement range / min. span Lin. R, measurement range / min. span Potentiometer Sensor connection, wires TC types Max. offset	0...23 mA / 16 mA 0...10 VDC / 8 VDC	0...23 mA / 16 mA 0...10 VDC / 8 VDC	3.5...23 mA / 16 mA -	3.5...23 mA / 16 mA -	0...100 mA / 4 mA 0...250 VDC / 5 mV -150...+150 mV / 5 mV -200...+850°C / 25°C 0...5000 Ω / 30 Ω 200 Ω...100 kΩ 2 - 3 - 4 BEJKLNRSTUW3W5Lr 50% of selec. max. value	0...100 mA / 4 mA 0...250 VDC / 5 mV -150...+150 mV / 5 mV -200...+850°C / 25°C 0...5000 Ω / 30 Ω 200 Ω...100 kΩ 2 - 3 - 4 BEJKLNRSTUW3W5Lr 50% of selec. max. val.
<b>OUTPUT:</b> mA, signal range / min. span Load (@ current output) V, signal range / min. span Max. offset	0...23 mA / 16 mA ≤ 600 Ω	0...23 mA / 16 mA ≤ 770 Ω	3.5...23 mA / 16 mA ≤ 600 Ω	3.5...23 mA / 16 mA ≤ 770 Ω	0...23 mA / 10 mA 600 Ω 0...10 VDC / 0.5 VDC 0...10 VDC / 0.5 VDC 50% of selec. max. value	0...23 mA / 10 mA 600 Ω 0...10 VDC / 0.5 VDC 0...10 VDC / 0.5 VDC 50% of selec. max. val.
<b>TECHNICAL SPECIFICATIONS:</b> Ambient temperature Supply voltage, AC / DC Max. required power, 1 / 2 channels Isolation voltage, test / operation Response time Signal dynamics, input / output Accuracy Temperature coefficient NAMUR Channels Programming	-20...+60°C 21.6...253V / 19.2...300V 2.0 W / 2.8 W 3.75 KVAC / 250 VAC < 25 ms Analog signal chain ≤ ±0.1% of span ≤ ±0.01% of span / °C NE 21 1 or 2 DIP switch	-20...+60°C 21.6...253V / 19.2...300V 1.3 W / 2.0 W 3.75 KVAC / 250 VAC < 25 ms Analog signal chain ≤ ±0.1% of span ≤ ±0.01% of span / °C NE 21 1 or 2 DIP Switch	-20...+60°C 21.6...253V / 19.2...300V 2.0 W / 2.8 W 3.75 KVAC / 250 VAC < 25 ms Analog signal chain ≤ ±0.1% of span ≤ ±0.01% of span / °C NE 21 1 or 2 No	-20...+60°C 21.6...253V / 19.2...300V 1.4 W / 2.1 W 3.75 KVAC / 250 VAC < 25 ms Analog signal chain ≤ ±0.1% of span ≤ ±0.01% of span / °C NE 21 1 or 2 No	-20...+60°C 21.6...253V / 19.2...300V 2.1 W / 2.8 W 3.75 KVAC / 250 VAC 250 ms...60 s 22 bit / 16 bit ≤ ±0.05% of span ≤ ±0.01% of span / °C NE 21, NE 43 1 or 2 5909 + DIP switch	-20...+60°C 21.6...253V / 19.2...300V 2.1 W / 2.8 W 3.75 KVAC / 250 VAC 250 ms...60 s 22 bit / 16 bit ≤ ±0.05% of span ≤ ±0.01% of span / °C NE 21, NE 43 2 5909 + DIP switch

APPROVALS:	✓	✓	✓	✓	✓	✓
ATEX	✓					
IECEx						
FM						
CSA						
UL	✓		✓			
DNV-GL	✓		✓			
EAC Ex	✓		✓			

APPLICATION GUIDE:	✓	✓	✓	✓	✓	✓
AI barrier	✓					
AO barrier		✓				
DI barrier						
DO barrier					✓ / ✓	✓ / ✓
RTD / TC input	✓ / ✓ / -	✓ / ✓ / -	✓ / - / -	✓ / - / -	✓ / ✓ / ✓	✓ / ✓ / ✓
mA / V / mV input	✓				✓	✓
4...20 mA Tx input					✓ / ✓	✓ / ✓
Lin. R / potentiometer input	✓ / ✓ / -	✓ / ✓ / -	✓ / - / -	✓ / - / -	✓ / ✓ / -	✓ / ✓ / -
mA / V / relay output	✓ / ✓	✓ / -	✓ / ✓	✓ / -	✓ / ✓	✓ / ✓
Active / passive mA output					✓	✓
Process signal calibration						



TYPE	5116B	5131B	5202B	5203B	5223B	5420B
<b>INPUT:</b> mA, mV, V, potentiometer, RTD, linear resistance, TC, Hz <b>OUTPUT:</b> mA, V, relays	Programmable transmitter 	2-wire programmable transmitter 	Pulse isolator 	Ex solenoid / alarm driver 	Programmable f/I - f/f converter 	Ex power supply for 2-wire Tx 

<b>INPUT:</b> mA, measurement range / min. span V, measurement range / min. span mV, measurement range / min. span RTD, measurement range / min. span Lin. R, measurement range / min. span Potentiometer Sensor connection, wires TC types Sensor type Hz, measurement range / min. span <b>OUTPUT:</b> mA, signal range / min. span Pulse output Hz, signal range Relays Voltage / current	0...100 mA / 4 mA 0...250 VDC / 5 mV -2500...+2500 mV / 5 mV -200...+850°C / 25°C 0...5000 Ω / 30 Ω 200 Ω...100 kΩ 2 - 3 - 4 BEJKLNRSTUW3W5Lr NAMUR / switch 0..5 kHz 0...23 mA / 10 mA 3.5...23 mA / 10 mA NPN / relay 0..5 kHz 2 x SPST, AC: 500 VA 0...23 mA / 5 mA NPN / PNP / relay 0...1000 Hz 2 x SPDT, AC: 100 VA > 18 VDC / 20 mA	0...100 mA / 4 mA 0...250 VDC / 5 mV -150...+150 mV / 5 mV -200...+850°C / 25°C -200...+850°C / 25°C 200 Ω...100 kΩ 2 - 3 - 4 BEJKLNRSTUW3W5Lr NPN / PNP / switch 0..20 kHz / 0.001 Hz 2 - 3 - 4 0.5 kHz Valves etc. 0..5 kHz 2 x SPDT, AC: 100 VA 0...23 mA / 5 mA NPN / PNP / relay 0...1000 Hz 2 x SPDT, AC: 100 VA > 18 VDC / 20 mA				
<b>TECHNICAL SPECIFICATIONS:</b> Ambient temperature Supply voltage, AC / DC Max. required power, 1 / 2 channels Isolation voltage, test / operation Response time Signal dynamics, input / output Accuracy Temperature coefficient NAMUR Channels Programming	-20...+60°C 21.6...253 V / 19.2...300 V 2.4 W / - 3.75 KVAC / 250 VAC 250 ms...60 s 22 bit / 16 bit ≤ ±0.05% of span < ±0.01% of span / °C NE 21, NE 43 1 5909	-20...+60°C -/ 7.5...35 VDC 0.8 W / 1.6 W 3.75 KVAC / 250 VAC 250 ms...60 s 22 bit / 16 bit ≤ ±0.05% of span < ±0.01% of span / °C NE 21 2 1 or 2 NE 21 1 or 2 DIP switch	-20...+60°C 21.6...253 V / 19.2...300 V -/ 1.8 W 3.75 KVAC / 250 VAC 250 ms...60 s 22 bit / 16 bit ≤ ±0.05% of span < ±0.01% of span / °C NE 21 1 or 2 DIP switch	-20...+60°C 21.6...253 V / 19.2...300 V 2.0 W / 2.5 W 3.75 KVAC / 250 VAC 60 ms...1000 s Valves etc. 0..5 kHz 2 x SPDT, AC: 100 VA - / 16 bit ≤ ±0.01% of span / °C NE 21 1 DIP switch	-20...+60°C 21.6...253 V / 19.2...300 V 3 W / - 3.75 KVAC / 250 VAC 60 ms...1000 s - / 16 bit ≤ ±0.01% of span / °C NE 21 2 DIP switch	-20...+60°C 21.6...253 V / 19.2...300 V -/ 2.5 W 3.75 KVAC / 250 VAC - / 16 bit NE 21 2 No

<b>APPROVALS:</b> ATEX IECEx FM CSA UL DNV-GL EAC Ex SIL 2, Hardware Assessment	✓	✓	✓	✓	✓	✓
---	---	---	---	---	---	---

<b>APPLICATION GUIDE:</b> AI barrier AO barrier DI barrier DO barrier mA / V / temperature input 4...20 mA Tx input mA / V / relay output Active / passive mA output Process signal calibration Power rail option	✓	✓	✓	✓	✓	✓
---	---	---	---	---	---	---



TYPE	5531A	5531B1	5714	5715	5725	
<b>INPUT:</b>	Loop-powered LCD indicator	Loop-powered LCD indicator in I.S. enclosure	Programmable LED indicator	Programmable LED indicator	Programmable frequency indicator	
<b>RTD, TC, mV, mA, V, potentiometer, frequency, pulse</b>						
<b>OUTPUT:</b>	Display, mA, relays					
<b>mA, measurement range / min. span</b>	3.6...23 mA / 16 mA	3.6...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA		
<b>V, measurement range / min. span</b>			0...12 VDC / 0.8 V	0...12 VDC / 0.8 V		
<b>Sensor type</b>					All standard sensors	
<b>Hz, measurement range / min. span</b>					0...50 kHz / 0.001 Hz	
<b>Min. pulse width</b>					25 µs	
<b>RTD, measurement range / min. span</b>			-200...+850°C	-200...+850°C		
<b>Lin. R, measurement range / min. span</b>			0...10000 Ω / -	0...10000 Ω / -		
<b>Potentiometer</b>			10 Ω...100 kΩ	10 Ω...100 kΩ		
<b>Sensor connection, wires</b>			2 - 3 - 4	2 - 3 - 4		
<b>TC types</b>			BEJKLNRSTUW3W5Lr	BEJKLNRSTUW3W5Lr		
<b>Cold junction compensation</b>			Internal	Internal		
<b>Reference voltage / 2-wire supply</b>			- / >15 VDC	- / >15 VDC		
<b>Sensor supply</b>					5...17 VDC	
<b>OUTPUT:</b>						
<b>Display, digit / type</b>	4-digit / LCD	4-digit / LCD	4-digit / LED	4-digit / LED	4-digit / LED	
<b>Display, digit height</b>	16 mm	16 mm	13.8 mm	13.8 mm	13.8 mm	
<b>mA, signal range / min. span</b>			0...23 mA / 16 mA	0...23 mA / 16 mA	0...23 mA / 16 mA	
<b>Relay</b>			2 x SPDT, AC: 500 VA	4 x SPDT, AC: 500 VA	2 x SPDT, AC: 500 VA	
<b>TECHNICAL SPECIFICATIONS:</b>						
<b>Ambient temperature</b>	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	-20...+60°C	
<b>Supply voltage, universal AC / DC</b>	- / 1.5 VDC	- / 1.5 VDC	21.6...253 V / 19.2...300 V	21.6...253 V / 19.2...300 V	21.6...253 V / 19.2...300 V	
<b>Max. required power</b>	<35 mW	<35 mW	3.5 W	3.8 W	3.6 W	
<b>Isolation voltage, test / operation</b>			2.3 kVAC / 250 VAC	2.3 kVAC / 250 VAC	2.3 kVAC / 250 VAC	
<b>Response time</b>	< 1 s	< 1 s	< 400 ms / < 1 s	< 400 ms / < 1 s	1...60 s	
<b>Accuracy</b>	≤ ±0.1% of span	≤ ±0.1% of span	≤ ±0.1% of reading	≤ ±0.1% of reading	≤ ±0.1% of reading	
<b>Temperature coefficient</b>	≤ ±0.01% of span / °C	≤ ±0.01% of span / °C	≤ ±0.01% of reading / °C	≤ ±0.01% of reading / °C	≤ ±0.01% of reading / °C	
<b>NAMUR</b>			NE 43	NE 43	NE 43	
<b>Programming</b>	Switch / front keys	Switch / front keys	Front keys	5909 / front keys	Front keys	
<b>APPROVALS:</b>						
ATEX, Zone 2	✓	✓				
UL 508			✓	✓	✓	
DNV-GL			✓	✓	✓	
EAC	✓	✓	✓	✓	✓	

APPLICATION GUIDE:	✓ / - / -	✓ / - / -	✓ / ✓ / -	✓ / ✓ / -	
mA / V / mV input	✓ / - / -	✓ / - / -	✓ / ✓ / -	✓ / ✓ / -	
Temperature input			✓	✓	
Lin. R / potentiometer input			✓ / ✓	✓ / ✓	
Frequency input					✓
Custom sensor linearization				✓	
4...20 mA Tx input			✓	✓	
Loop-powered	✓	✓			
mA output			✓	✓	
2 / 4 relay outputs			✓ / -	- / ✓	✓ / -
Process signal calibration	✓	✓	✓	✓	✓
Mounting in Zone 2	✓	✓			



TYPE	5531B	5531B2				
<b>INPUT:</b> mA	Loop-powered LCD indicator	Loop-powered LCD indicator in I.S. enclosure				
<b>OUTPUT:</b> Display						

<b>INPUT:</b> mA, measurement range / min. span	3.6...23 mA / 16 mA	3.6...23 mA / 16 mA				
<b>OUTPUT:</b> Display, digit / type	4-digit / LCD	4-digit / LCD				
Display, digit height	16 mm	16 mm				
<b>TECHNICAL SPECIFICATIONS:</b>						
Ambient temperature	-20...+60°C	-20...+60°C				
Supply voltage, universal AC / DC	- / 1.5 VDC	- / 1.5 VDC				
Max. required power	<35 mW	<35 mW				
Isolation voltage, test / operation						
Response time	< 1 s	< 1 s				
Accuracy	≤ ±0.1% of span	≤ ±0.1% of span				
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C				
NAMUR						
Programming	Switch / front keys	Switch / front keys				
<b>APPROVALS:</b>						
ATEX	✓	✓				
DNV-GL	✓	✓				
EAC Ex						

<b>APPLICATION GUIDE:</b>						
Loop-powered	✓	✓				
Mounting in Zone 1 / 21	✓	✓				
Field enclosure		✓				

# POWER SUPPLIES



TYPE	3405	9410	9420			
<b>INPUT:</b> AC, DC voltage OUTPUT: Stabilized VDC	<p>Power connector unit</p>	<p>Power control unit</p>	<p>Power supply</p>			
<b>INPUT:</b> Supply voltage, AC Supply voltage, DC Supply voltage, back-up				85...132 VAC or 187...264 VAC		
Voltage Current Power, max. Status relay	16.8...31.2 VDC 16.8...31.2 VDC 21.6...26.4 VDC 21.6...26.4 VDC	21.6...26.4 VDC 4 ADC 96 W 1 x SPDT, AC: 500 VA	24 VDC 4.8 ADC 115 W 			
<b>OUTPUT:</b> Voltage Current Power, max. Status relay						
<b>TECHNICAL SPECIFICATIONS:</b> Ambient temperature Max. required power Isolation, test Short circuit protection Output ripple Channels Programming	-25...+70°C 96 W 2.6 kVAC No Same as input 1 No	-20...+60°C < 135 W 4.3 kVAC Yes Same as input 1 No	-20...+60°C 24 VDC 115 W Yes 200 mV peak / peak 1 No			
<b>APPROVALS:</b> ATEX, Zone 2 IECEx, Zone 2 CSA, Zone 2 - DIV 2 FM, Zone 2 - DIV 2 CCOE UL 61010 / 508 DNV-GL EAC INMETRO, Zone 2 SIL 2 Full Assessment IEC 61508	✓ ✓ ✓ ✓ ✓ ✓ / - ✓ ✓ ✓ ✓ ✓ ✓	✓ ✓ ✓ ✓ ✓ / - ✓ ✓ ✓ ✓ ✓ ✓ ✓	✓ ✓ ✓ ✓ / ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓			
<b>APPLICATION GUIDE:</b> 115 / 230 VAC mains supply 24 VDC output 60 W power rail connector unit 96 W power rail connector unit Redundancy power rail function Collective status signal monitor Internal fuse Mounting in Zone 2 / Div 2				✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓ ✓		



TYPE	2224	2231	2261			
<b>INPUT, DC:</b> mA, V, potentiometer, frequency, pulse, joystick, load cell, mV	Valve controller	Trip amplifier	mV transmitter			
<b>INPUT, AC:</b> A, V						
<b>OUTPUT:</b> mA, V, relays						

<b>INPUT:</b>				
mA, DC measurement range / min. span	0...20 mA / 16 mA	0...20 mA / 10 mA		
V, DC measurement range / min. span	-10...+10 VDC / 0.8 VDC	0...250 VDC / 0.5 VDC	-40...+100 mV / 10 mV	
A, AC measurement range / min. span		0...1 ARMS / 0.5 ARMS		
V, AC measurement range / min. span		0...250 VRMS/0.5 VRMS		
Potentiometer	> 1 kΩ			
Digital input	3 x PNP		1 x NPN / 1 x PNP	
Max. offset	20% of selec. max. value		70% of selec. max. value	
Excitation / reference voltage	- / -10...+10 VDC		5...13 VDC / -	
<b>OUTPUT:</b>				
mA, signal range / min. span	3000 mA		0...20 mA / 5 mA	
V, signal range / min. span	Supply-0.5 VDC		0...10 VDC / 0.25 VDC	
Max. offset			50% of selec. max. value	
Relays		2 x SPST, AC: 500 VA		
Display, digit / type	3-digit / LED	3-digit / LED	3-digit / LED	
<b>TECHNICAL SPECIFICATIONS:</b>				
Ambient temperature	-20...+60°C	-20...+60°C	-20...+60°C	
Supply voltage, universal AC / DC		21.6...253V / 19.2...300V		
Supply voltage, DC	12 or 24 VDC	19.2...28.8 VDC	19.2...28.8 VDC	
Max. required power	2.2 W	1.5 W DC / 2 W, UNI	2.2 W / max. 7.2 W	
Isolation voltage, test / operation		3.75 KVAC / 250 VAC		
Response time	< 75 ms	250 ms...60 s	60 ms...999 s	
Signal dynamics, input / output	12 bit / -	16 bit / -	17 bit / 16 bit	
Setpoint adjustment / repetition		0.1% / 0.1%		
Delay / hysteresis		0...99.9 s / 0...99.9%		
Temperature coefficient	< ±0.01% of span / °C	< ±0.01% of span / °C	< ±0.01% of span / °C	
Channels	1 or 2 outputs	1 input, 2 relays	1	
Programming	Switch / front keys	Switch / front keys	Switch / front keys	



TYPE	2255	2279				
frequency, pulse	f/I - f/f converter	AC / DC transmitter				
delays, pulse						

**INPUT: PV / SP**

A, AC measurement range / min. span		0...1 ARMS / 0.5 ARMS				
V, AC measurement range / min. span		0...250 VRMS/0.5 VRMS				
Max. offset		50% of selec. max. value				
Sensor type	All standard sensors	Π				
Hz, measurement range / min. span	0...20 kHz	/ 0.001 Hz				
Min. pulse width	25 µs					
Sensor supply	5...15 VDC					
<b>OUTPUT:</b>						
mA, signal range / min. span	0...20 mA	/ 5 mA	0...20 mA	/ 4 mA		
V, signal range / min. span	0...10 VDC	/ 0.25 VDC	0...10 VDC	/ 0.2 VDC		
Max. offset	50% of selec. max. value		20% of selec. max. value			
Load (@ current output)	≤ 600 Ω		600 Ω			
Pulse output	NPN					
Max. output frequency	1000 Hz					
Relays	1 x SPDT, AC: 300 VA					
Display, digit / type	3-digit	/ LED				

## **TECHNICAL SPECIFICATIONS:**


<b>Ambient temperature</b>	-20...+60°C	-20...+60°C					
<b>Supply voltage, universal AC / DC</b>		21.6...253V / 19.2...300V					
<b>Supply voltage, DC</b>	19.2...28.8 VDC	19.2...28.8 VDC					
<b>Max. required power</b>	2.4 W	1.3 W / 2.2 W, UNI					
<b>Isolation voltage, test / operation</b>	1.4 kVAC / 150 VAC	3.75 kVAC / 250 VAC					
<b>Response time</b>	60 ms...999 s	< 1.5 s					
<b>Signal dynamics, input / output</b>	- / 16 bit	Analog signal chain					
<b>Accuracy</b>							
<b>Temperature coefficient</b>	< ±0.01% of span / °C	< ±0.01% of span / °C					
<b>Channels</b>	1	1					
<b>Programming</b>	Switch / front keys	Switch					

APPROVALS:

APPLICATION GUIDE

<b>AC signal input</b>		✓				
<b>Frequency / pulse applications</b>	✓					
<b>mA / V output</b>	✓	✓				
<b>Relay output</b>	✓					


A user-friendly and reliable mounting solution between  
*the DCS/PLC/SIS system and isolators/I.S. interfaces*




**Honeywell**  
**YOKOGAWA** ♦  
**PRUNIVERSAL**

## SIGNAL TYPES

### INPUT



### OUTPUT



## PROGRAMMING UNITS

### 4501 DISPLAY FRONT



PR 4104, 4114, 4116, 4131, 4222



PR 9106, 9107, 9113, 9116, 9202, 9203

### 4511 COMMUNICATION ENABLER



PR 4104, 4114, 4116, 4131, 4222




PR 9106, 9107, 9113, 9116, 9202, 9203

### 4590 CONFIGMATE



PR 3114  
PR 4104, 4114, 4116, 4131, 4222  
PR 9106, 9107, 9113, 9116, 9202, 9203

### SOFTWARE



### 5909 LOOP LINK



### Display / programming front 4501

Communications interface with front keys for modification of operational parameters in the 4000 and 9000 series. The scrolling help text in the display is available in 7 languages and guides the user effortlessly through all the configuration steps. The 4501 is easily moved from one device to another whereby the configuration can be copied to other devices of the same type. When mounted in the process, the 4501 displays process data and device status.

### Communication enabler 4511

Wired or wireless, locally or remotely, analog and digital, this advanced device enables easy and cost-effective access to your process values from your existing 4000 and 9000 devices. You can manage processes onsite, connect to Modbus RTU devices, connect to any major communication protocols via gateway or remotely using the PR Process Supervisor (PPS) app. The 4511 offers the same advantages as the 4501 with the added feature of digital communication.

### ConfigMate 4590

The 4590 is an adapter unit for the display / programming front 4501. It is used to program the 3114 and connect to this device with a jack plug. The 4590 is battery-driven or driven by the USB port of the PC. It can be used both for programming and as a diagnostic tool to display process parameters, when the 4501 is mounted. The 4590 is easily moved from one device to another.

### PReset

PReset is an easy-to-use menu-driven software program for set-up of PR products via a standard PC and a programming interface. PReset gives a high degree of flexibility for each product and when the menus are completed, the data is transmitted to the unit which is then ready for operation.

### Loop Link 5909

Loop Link 5909 is a USB communications interface for configuration and monitoring of PR electronics' PC-programmable devices. PR devices available in the configuration program PReset ver. 5.0 or higher, can be programmed by way of Loop Link 5909.

**POWER RAIL**

The data sheet specifies the maximum required power at nominal operating values, e.g. 24 V supply voltage, 60°C ambient temperature, 600 Ω load, and 20 mA output current.

In typical applications, the devices are not running at worst-case conditions, specifically when many devices are located together. For engineering purposes, 70% (P70%) of maximum required power is often used.

**3000 power rail**

The number of 3000 devices that can be powered from different power sources is listed in the table below:

	Using a PR converter device as power feed-in	3405 power feed-in	9410 power feed-in
P70%	Up to 25 devices	Up to 160 devices	Up to 250 devices
P100%	Up to 18 devices	Up to 115 devices	Up to 184 devices

The devices can be stacked vertically or horizontally.

**9000 power rail**

The number of 9000 devices that can be powered from the 9400 power sources is listed in the table below:

	9410 power feed-in
P70%	Up to 150 devices
P100%	Up to 120 devices

**ENVIRONMENTAL SPECIFICATIONS**

	PR 2200 series	PR 3000 series	PR 4000 series	PR 5000 series	PR 5300 series
Specifications range	-20°C to +60°C	-25°C to +70°C (3105: 0°C to +70°C)	-20°C to +60°C	-20°C to +60°C	-40°C to +85°C
Relative humidity	< 95% RH (non-cond.)	< 95% RH (non-cond.)	< 95% RH (non-cond.)	< 95% RH (non-cond.)	< 95% RH (non-cond.)
Protection degree	IP50	IP20	IP20	IP20	IP68 / IP00
	PR 5500 / 5700 series	PR 6300 series	PR 7500 series	PR 9000 series	
Specifications range	-20°C to +60°C	-40°C to +85°C	-20 / -40°C to +85°C	-20°C to +60°C	
Relative humidity	< 95% RH (non-cond.)	< 95% RH (non-cond.)	0...100% RH (cond.)	< 95% RH (non-cond.)	
Protection degree	IP65 from front (5500) IP65 / Type 4X, UL50E	IP20	IP54 / IP66 / IP68 / type 4X	IP20	

**ENCLOSURE SPECIFICATIONS**

Dimensions (mm)	PR 2200 series	PR 3000 series	PR 4000 / 6000 / 9000 series	PR 5000 series	PR 5300 series	PR 5500 / 5700 series	PR 7500 series
Height	80.5	113	109	109	20.2	48	109
Width	35.5	6.1	23.5	23.5	Ø44	96	145
Depth	84.5+socket	115	104	130		120	125.5
Panel cut-out						44.5 x 91.5	
Material	Cyclooy/Noryl	Cyclooy	Cyclooy	Cyclooy	Cyclooy	Noryl	Aluminum

# Benefit today from ***PERFORMANCE MADE SMARTER***

PR electronics is the leading technology company specialized in making industrial process control safer, more reliable and more efficient. Since 1974, we have been dedicated to perfecting our core competence of innovating high precision technology with low power consumption. This dedication continues to set new standards for products communicating, monitoring and connecting our customers' process measurement points to their process control systems.

Our innovative, patented technologies are derived from our expansive R&D facilities and from having a great understanding of our customers' needs and processes. We are guided by principles of simplicity, focus, courage and excellence, enabling some of the world's greatest companies to achieve PERFORMANCE MADE SMARTER.

1015EN-W12 (1634)

