# **Smart Fiber Amplifier Units**

# E3NX-FA

CSM\_E3NX-FA\_DS\_E\_15\_1

# A Smart Fiber Amplifier Unit with Ultra-stable Detection and Ultra-easy Setup

- Improved basic performance with 1.5 times the sensing distance and approx. 1/10th the minimum sensing object.\*
- Ultra-easy setup with Smart Tuning with a light intensity adjustment range expanded 20 times to 40,000:1. Optimum stable detection achieved with light intensity adjustment even for saturated incident light.
- White on black display characters for high visibility.
- Solution Viewer that shows the passing time and difference in incident levels and Change Finder that allows you to see display values even for fast workpieces.

\* Compared to the E3X-HD.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Refer to the Safety Precautions on page 17.

## **Ordering Information**

## Fiber Amplifier Units (Dimensions → pages 19 and 20)

Type	Connecting method Appearance		Innuto/outnuto	Мо	del
Туре	Connecting method	Appearance	Inputs/outputs	NPN output	PNP output
	Pre-wired (2 m)		1 output	E3NX-FA11 2M	E3NX-FA41 2M
Standard models	Tre wiled (2 m)		Τομφαί	E3NX-FA11-5 2M *1	
Standard models	Wire-saving Connector		1 output	E3NX-FA6	E3NX-FA8
	Pre-wired (2 m)	re-wired (2 m)		E3NX-FA21 2M	E3NX-FA51 2M
Advanced models			1 output + 1 input	E3NX-FA7	E3NX-FA9
	Wire-saving Connector		2 outputs	E3NX-FA7TW	E3NX-FA9TW
	M8 Connector	and the same of th	1 output + 1 input	E3NX-FA24	E3NX-FA54
	M8 Connector		2 outputs		E3NX-FA54TW

 $<sup>{\</sup>bf *1.}$  This type can prevent mutual interference for two units in the SHS2 mode.

Typo	Connecting method Appearance		Inputs/outputs	Model			
Туре	Connecting method	Appearance	Inputs/outputs	NPN output	PNP output		
Infrared models	Pre-wired (2 m)		1 output	E3NX-FAH11 2M	E3NX-FAH41 2M		
	Wire-saving Connector		1 output	E3NX-FAH6	E3NX-FAH8		
Analog output models	Pre-wired (2 m)		2 outputs	E3NX-FA11AN 2M	E3NX-FA41AN 2M		
Model for Sensor	Connector for Sensor			E3NX-FA0			
Communications Unit *2	Communications Unit			E3NX-FAH0			

**<sup>\*2.</sup>** A Sensor Communications Unit is required if you want to use the Fiber Amplifier Unit on a network.

## **Accessories (Sold Separately)**

Wire-saving Connectors (Required for models for Wire-saving Connectors.) (Dimensions → page 21)

Connectors are not provided with the Fiber Amplifier Unit and must be ordered separately. Note: Protective stickers are provided.

Туре	Appearance	Cable length	No. of conductors	Model	Applicable Fiber Amplifier Units
Master Connector	*		4	E3X-CN21	E3NX-FA7 E3NX-FA7TW
Slave Connector	*	2 m	2	E3X-CN22	E3NX-FA9 E3NX-FA9TW
Master Connector	*	2 111	3	E3X-CN11	E3NX-FA6
Slave Connector	*		1	E3X-CN12	E3NX-FA8

## Sensor I/O Connectors (Required for models for M8 Connectors.) (Dimensions → page 21)

Connectors are not provided with the Fiber Amplifier Unit and must be ordered separately.

Size	Cable	Appearance		Cable type		Model	
M8	Standard cable	Straight		2m		XS3F-M421-402-A	
		Straight		5m	4	XS3F-M421-405-A	
		Labanad		2m	4-wire	XS3F-M422-402-A	
		L-shaped		5m		XS3F-M422-405-A	

Mounting Bracket (Dimensions → page 22)
A Mounting Bracket is not provided with the Fiber Amplifier Unit. It must be ordered separately as required.

Appearance	Model	Quantity
	E39-L143	1

#### **DIN Track** (Dimensions → page 22)

A DIN Track is not provided with the Fiber Amplifier Unit. It must be ordered separately as required.

Appearance	Туре	Model	Quantity
	Shallow type, total length: 1 m	PFP-100N	
	Shallow type, total length: 0.5 m	PFP-50N	1
	Deep type, total length: 1 m	PFP-100N2	

#### End Plate (Dimensions → page 22)

Two End Plates are provided with the Sensor Communications Unit. End Plates are not provided with the Fiber Amplifier Unit. They must be ordered separately as required.

Appearance	Model	Quantity
3	PFP-M	1

#### Cover

Attach these Covers to Amplifier Units.
Order a Cover when required, e.g., if you lose the covers.

Appearance	Model	Quantity		
	E39-G25 FOR E3NX-FA	1		

## **Related Products**

**Sensor Communications Units** 

Туре	Appearance	Model
Sensor Communications Unit for EtherCAT		E3NW-ECT
Sensor Communications Unit for CompoNet	7	E3NW-CRT *1
Sensor Communications Unit for CC-Link		E3NW-CCL
Distributed Sensor Unit *2		E3NW-DS

Refer to your OMRON website for details.

- \*1. Only E3NX-FA0 can be connected to E3NW-CRT.
- \*2. The Distributed Sensor Unit can be connected to any of the Sensor Communications Units.

EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.

CompoNet is a registered trademark of the ODVA. CC-Link is a registered trademark of Mitsubishi Electric Corporation. The trademark is managed by the CC-Link Partner Association.

## **Ratings and Specifications**

#### Standard models/ Advanced models/ Infrared models

	Тур	e S	Standard models Advanced models							Infrared	Infrared models	
	NPN outp	t E3NX-FA11	E3NX-FA6	E3NX-FA11-5 *1	E3NX-FA21	E3NX-FA7	E3NX-FA7TW	E3NX-FA24		E3NX-FAH11	E3NX-FAH6	
	PNP outp	t E3NX-FA41	E3NX-FA8		E3NX-FA51	E3NX-FA9	E3NX-FA9TW	E3NX-FA54	E3NX-FA54TW	E3NX-FAH41	E3NX-FAH8	
Item	Connectir method	g Pre-wired	Wire-saving Connector	Pre-wired	Pre-wired	Wire-saving	Connector	M8 Co	nector	Pre-wired	Wire-saving Connector	
Inputs/	Outputs	1 output			2 outputs	1 output	2 outputs	1 output	2 outputs	1 outputs		
outputs	External inpu	s			1 input	1 input		1 input				
Light sour	ce (wavelengt	Red, 4-elem	ent LED (625	nm)						Infrared LED	(870nm)	
Power su	ipply voltage	10 to 30 VD	C, including 10	0% ripple (p-p	)							
Power co	nsumption *	Standard Mo Normal mod Eco function Advanced M Normal mod Eco function Eco function Infrared mod Normal mod	At Power supply voltage of 24 VDC Standard Models: Normal mode : 840 mW max. (Current consumption at 35 mA max.) Eco function ON: 650 mW max. (Current consumption at 27 mA max.) Eco function LO: 750 mW max. (Current consumption at 31 mA max.) Advanced Models or Model for Sensor Communications Unit: Normal mode : 920 mW max. (Current consumption at 38 mA max.) Eco function ON: 680 mW max. (Current consumption at 28 mA max.) Eco function LO: 800 mW max. (Current consumption at 33 mA max.) Infrared models: Normal mode : 1080 mW max. (Current consumption at 45 mA max.) Eco function ON: 920 mW max. (Current consumption at 38 mA max.)									
Load power supply voltage: 30 VDC max., open-collector output (depends on the NPN/PNP output format) Load current: Groups of 1 to 3 Amplifier Units: 100 mA max., Groups of 4 to 30 Amplifier Units: 20 mA max.  Residual voltage: At load current of less than 10 mA: 1 V max. At load current of 10 to 100 mA: 2 V max.												
External i	inputs		OFF current: 0.1 mA max Refer to *3 Refer to *3									
Indicators	<u> </u>	Display direction OUT indicate	ction: Switchal or (orange), L/	digital display: ble between n 'D indicator (o or (orange, on	green, Main o ormal and rev range), ST ind	ersed. licator (blue),	DPC indicator					
Protectio	n circuits	Power suppl	Power supply reverse polarity protection, output short-circuit protection, and output reverse polarity protection									
	Super-high- speed mode (SHS)	Operate or r	eset for mode	I with 1 output	: 30 μs (Supe	r High Speed	mode (SHS2)	of E3NX-FA1	1-5 is 60 μs e	ach), with 2 ou	itputs: 32 μs	
Response time	High-speed mode (HS)	Operate or r	eset: 250 μs									
	Standard mode (Stnd)	Operate or r	eset: 1 ms									
	Giga-power mode (GIGA	•										
	ty adjustment	percentage t		ng, full auto tu o 99%)) or ma			num sensitivity	/ tuning, powe	er tuning, or			
Maximum connectable Units 30												
No. of Units	Super-high- speed mode (SHS)		s when the det on is disabled.		set to Super I	High Speed m	ode (SHS2), a	nd for other m	odels, the mut	ual interferenc	e prevention	
No. of Units for mutual interference interference mode (HS)  10												
prevention <b>*4</b>	Standard mode (Stnd	10										
	Giga-power mode (GIGA	) 10										

**<sup>\*1.</sup>** This type can prevent mutual interference for two units in the SHS2 mode.

 $\mathbf{*2.}$  At Power supply voltage of 10 to 30 VDC

Standard Models:

Normal mode : 990 mW max. (Current consumption: 33 mA max. at 30 VDC, 65 mA max. at 10 VDC)
Eco function ON : 780 mW max. (Current consumption: 26 mA max. at 30 VDC, 42 mA max. at 10 VDC)
Eco function LO : 840 mW max. (Current consumption: 28 mA max. at 30 VDC, 45 mA max. at 10 VDC)

Advanced Models:

Normal mode : 1,020 mW max. (Current consumption: 34 mA max. at 30 VDC, 67 mA max. at 10 VDC)
Eco function ON : 810 mW max. (Current consumption: 27 mA max. at 30 VDC, 44 mA max. at 10 VDC)
Eco function LO : 870 mW max. (Current consumption: 29 mA max. at 30 VDC, 48 mA max. at 10 VDC)

Infrared models:

Normal mode : 1,260 mW max. (Current consumption: 42 mA max. at 30 VDC, 80 mA max. at 10 VDC) Eco function ON : 1,050 mW max. (Current consumption: 35 mA max. at 30 VDC, 60 mA max. at 10 VDC) Eco function LO : 1,140 mW max. (Current consumption: 38 mA max. at 30 VDC, 70 mA max. at 10 VDC)

**\*3.** The following details apply to the input.

		Contact input (relay or switch)	Non-contact input (transistor)	Input time *3-1
N	IPN		ON: 1.5 V max. (Sourcing current: 1 mA max.) OFF: Vcc – 1.5 V to Vcc (Leakage current: 0.1 mA max.)	ON: 9 ms min.
P	NP		ON: Vcc – 1.5 V to Vcc (Sinking current: 3 mA max.) OFF: 1.5 V max. (Leakage current: 0.1 mA max.)	OFF: 20 ms min.

<sup>\*3-1.</sup>Input time is 25 ms (ON)/(OFF) only when (in tUnE) or (in PtUn) input is selected.

<sup>\*4.</sup> The tuning will not change the number of units. The least unit count among the mutual interference prevention units of E3NX and E3NC. Check the mutual interference prevention unit count and response speed of each model.

	Tuna	C		ıla.		Λ.		ala.		Infrared	madala	
	Type NPN output	E3NX-FA11	E3NX-FA6	E3NX-FA11-5*1	E3NX-FA21	E3NX-FA7	E3NX-FA7TW	E3NX-FA24		Infrared models E3NX-FAH11 E3NX-FAH6		
	PNP output	E3NX-FA11	E3NX-FA8	E3NA-FATT-3-#T	E3NX-FA21	E3NX-FA9	E3NX-FA7TW	E3NX-FA24	E3NX-FA54TW	E3NX-FAH41	E3NX-FAH8	
Item	Connectin g method	Pre-wired	Wire-saving Connector	Pre-wired	Pre-wired		g Connector		nnector	Pre-wired	Wire-saving Connector	
	Automatic power control (APC)	Always enab	led.									
	Dynamic power control (DPC)	Provided										
	Timer	Select from t	Select from timer disabled, OFF-delay, ON-delay, one-shot, or ON-delay + OFF-delay timer: 1 to 9,999 ms									
	Zero reset	Negative values can be displayed. (Threshold value is shifted.)										
	Resetting settings *5	Select from i	Select from initial reset (factory defaults) or user reset (saved settings).									
	Eco mode *6	Select from 0	OFF (digital di	splay lit), Eco	ON (digital di	splay not lit), a	and Eco LO (d	igital display o	dimmed).			
	Bank switching	Select from I	oanks 1 to 4.									
	Power tuning	Select from 0	ON, OFF or E	xecution on po	wer-up.					Select from 0	ON or OFF.	
	Output 1	Select from r	normal detecti	on mode, area	a detection mo	ode or differen	ntial detection	mode.		Select from redetection modetection modetection modetection modetection model.	de or area	
Functions	Output 2				Select from normal detection mode, alarm output mode, error output mode or differential detection mode.		Select from normal detection mode, alarm output mode, error output mode or differential detection mode.		Select from normal detection mode, alarm output mode, error output mode or differential detection mode.			
	External input				Select from input OFF, tuning, power tuning, emission OFF, zero reset, or bank switching.			Select from input OFF, tuning, power tuning, emission OFF, zero reset, or bank switching.				
	Hysteresis width	Select from standard setting or user setting. For a user setting, the hysteresis width can be set from 0 to 9,999.										
Ambient i	illumination		it lamp: 20,000				,,,,,,,,,,			<u></u>		
Ambient trange *7	temperature	Groups of 3 Groups of 11 Groups of 17	or 2 Amplifier to 10 Amplifie to 16 Amplifi to 30 Amplifi to 70°C (with	r Units: –25 to er Units: –25 t er Units: –25 t	50°C, o 45°C, o 40°C							
Ambient I	humidity range	Operating ar		to 85% (with	no condensat	ion) within the	surrounding a	air temperatur	e range showi	n above		
Installatio		Pollution deg										
	n resistance	20 MΩ min.	(at 500 VDC)									
	strength		it 50/60 Hz for	1 min								
	resistance	,			tude for 2 hou	rs each in X, `	Y, and Z direc	tions				
Shock res (destructi		500 m/s <sup>2</sup> for	3 times each	in X, Y, and Z	directions							
Weight (p Sensor o	packed state/ nly)	Approx. 115 g/ approx. 75 g	Approx. 60g/ approx. 20g	Approx. 115 g/ approx. 75 g	Approx. 115 g/ approx. 75 g	Approx. 60g/ approx. 20g	/	Approx. 65 g approx. 25 g		Approx. 115 g/ approx. 75 g	Approx. 60g/ approx. 20g	
	Case	Polycarbona	te (PC)									
Materials	Cover	Polycarbona	te (PC)									
	Cable	PVC										
Accessor	ries	Instruction M	lanual									

<sup>\*5.</sup> The bank is not reset by the user reset function or saved by the user save function.
\*6. Eco LO is supported for Amplifier Units manufactured in July 2014 or later.
\*7. When the number of connected units is 11 or more, the ambient temperature is less than 50°C.

## **Analog output models/ Model for Sensor Communications Unit**

		Туре	Analog output models	Model for Sensor C	ommunications Unit			
		NPN output	E3NX-FA11AN	E3NX-FA0	E3NX-FAH0			
		PNP output	E3NX-FA41AN	ESINA-FAU	ESIVA-FAI IU			
Item		Connecting method	Pre-wired	Connector for Sensor	Communications Unit			
Inputs/	Outputs		2 outputs	*1	*1			
outputs	External in	puts		*	4			
Light source	(wavelengt	ih)	Red, 4-element LED (625 nm)		Infrared LED (870nm)			
Power sup	ply voltage	1	10 to 30 VDC, including 10% ripple (p-p)	Supplied from the connector through the communication units.				
Power con	sumption *	<b>*2</b>	At Power supply voltage of 24 VDC Normal mode : 960 mW max. (Current consumption at 40 mA max.) Eco function ON: 770 mW max. (Current consumption at 32 mA max.) Eco function LO : 870 mW max. (Current consumption at 36 mA max.)	At Power supply voltage of 24 VDC Normal mode : 920 mW max. (Current consumption at 38 mA max.) Eco function ON: 680 mW max. (Current consumption at 28 mA max.) Eco function LO : 800 mW max. (Current consumption at 33 mA max.)	At Power supply voltage of 24 VDC Normal mode: 1,080 mW max. (Current consumption at 45 mA max.) Eco function ON: 920 mW max. (Current consumption at 38 mA max.) Eco function LO: 1,020 mW max. (Current consumption at 42 mA max.)			
Control output			Load power supply voltage: 30 VDC max., open-collector output (depends on the NPN/PNP output format) Load current: Groups of 1 to 3 Amplifier Units: 100 mA max., Groups of 4 to 30 Amplifier Units: 20 mA max.  Residual voltage: At load current of less than 10 mA: 1 V max. At load current of 10 to 100 mA: 2 V max.  OFF current: 0.1 mA max.					
Analog out	put		Voltage output: 1-5 VDC (10 kΩ or more connected load), temperature characteristics: 0.3% F.S. / °C	-				
Indicators			7-segment displays (Sub digital display: green, Main digital display: white) Display direction: Switchable between normal and reversed. OUT indicator (orange), L/D indicator (orange), ST indicator (blue), DPC indicator (green), and OUT selection indicator (orange, only on models with 2 outputs)					
Protection	circuits		Power supply reverse polarity protection, output short-circuit protection, and output reve rse polarity protection	Power supply reverse polarity protection and output short-circuit protection				
0	Super-hig (SHS)	h-speed mode	Operate or reset: 80 μs	Operate or reset: 32 µs				
Control output	High-spee	ed mode (HS)	Operate or reset: 250μs	Operate or reset: 250 µs				
Response time	Standard	mode (Stnd)	Operate or reset: 1 ms	Operate or reset: 1 ms				
ume	Giga-pow (GIGA)	er mode	Operate or reset: 16 ms	Operate or reset: 16 ms				
Sensitivity	adjustmen	t	Smart Tuning (2-point tuning, full auto tu percentage tuning (–99% to 99%)) or ma	ining, position tuning, maximum sensitivity anual adjustment	y tuning, power tuning,			
Maximum o	connectabl	e Units	30	With E3NW-ECT: 30 units (When conne With E3NW-CRT: 16 units (Note: E3NX- With E3NW-CCL: 16 units	cted to an OMRON NJ-series Controller., -FAH0 can not be connected.)			
No. of Units	Super-hig (SHS)	h-speed mode	0 (The mutual interference prevention fu	nction is disabled if the detection mode is	s set to super-high-speed mode.)			
for mutual interference	High-spee	ed mode (HS)	10					
prevention	Standard	mode (Stnd)	10					
*3	Giga-pow (GIGA)	er mode	10					

Analog output models:

Normal mode : 1,080 mW max. (Current consumption: 36 mA max. at 30 VDC, 75 mA max. at 10 VDC)

Eco function ON : 840 mW max. (Current consumption: 28 mA max. at 30 VDC, 55 mA max. at 10 VDC)

Eco function LO : 960 mW max. (Current consumption: 32 mA max. at 30 VDC, 65 mA max. at 10 VDC)

**\*3.** The tuning will not change the number of units.

The least unit count among the mutual interference prevention units of E3NX and E3NC. Check the mutual interference prevention unit count and response speed of each model.

<sup>\*1.</sup> Two sensor outputs are allocated in the programmable logic controller PLC I/O table. PLC operation via Communications Unit enables reading detected values and changing settings.

<sup>\*2.</sup> At Power supply voltage of 10 to 30 VDC

	Туј	e Analog output models	Model for Sensor C	Communications Unit				
	NPN output	E3NX-FA11AN						
	PNP output	E3NX-FA41AN	E3NX-FA0	E3NX-FAH0				
Item	Connecting method	Pre-wired	Connector for Senso	r Communications Unit				
	Automatic power control (AF	C) Always enabled.						
	Dynamic power control (DPC	) Provided						
	Timer	Select from timer disabled, OFF-delay,	ON-delay, one-shot, or ON-delay + OFF-	delay timer: 1 to 9,999 ms				
	Zero reset	Negative values can be displayed. (Three	eshold value is shifted.)					
	Resetting settings *4	Select from initial reset (factory defaults	s) or user reset (saved settings).					
	Eco mode	Select from OFF (digital display lit), Eco	Select from OFF (digital display lit), Eco ON (digital display not lit), and Eco LO (digital display dimmed).					
Functions	Bank switching	Select from banks 1 to 4.						
Power tuning		Select from ON or OFF.						
	Output 1	Select from normal detection mode or a	Select from normal detection mode or area detection mode.					
	Output 2	Select from Analog scaling or Analog offset.	Select from normal detection mode, alarm output mode, error output mode or differential detection mode (E3NX-FA0 only).					
	Hysteresis width	Select from standard setting or user set	ting. For a user setting, the hysteresis with	dth can be set from 0 to 9,999.				
Ambient ill	umination (Receiver sid	) Incandescent lamp: 20,000 lx max., Sur	nlight: 30,000 lx max.					
Ambient te	mperature range <mark>*</mark> 5	Operating: Groups of 1 or 2 Amplifier Units: -25 to 55°C, Groups of 3 to 10 Amplifier Units: -25 to 50°C, Groups of 11 to 16 Amplifier Units: -25 to 45°C, Groups of 17 to 30 Amplifier Units: -25 to 40°C Storage: -30 to 70°C (with no icing or condensation)	Groups of 3 to 10 Amplifier Units: 0 to 50°C, Groups of 11 to 16 Amplifier Units: 0 to 45°C, Groups of 17 to 30 Amplifier Units: 0 to 40°C					
Ambient hu	umidity range	Operating and storage: 35 to 85% (with	no condensation) within the surrounding	air temperature range shown above				
Altitude		2,000 m max.						
Installation	environment	Pollution degree 3						
Insulation i	resistance	20 MΩ min. (at 500 VDC)						
Dielectric s	strength	1,000 VAC at 50/60 Hz for 1 min						
Vibration re	esistance (destruction)	10 to 55 Hz with a 1.5-mm double ampl	itude for 2 hours each in X, Y, and Z direct	otions				
Shock resid	stance (destruction)	500 m/s² for 3 times each in X, Y, and Z directions	150 m/s <sup>2</sup> for 3 times each in X, Y, and 2	Z directions				
Weight (pa	cked state/Sensor only)	Approx. 115 g/approx. 75 g	Approx. 65 g/approx. 25 g Approx. 65 g/approx. 25 g					
	Case	Polycarbonate (PC)						
Materials	Cover	Polycarbonate (PC)						
	Cable	PVC						

<sup>\*4.</sup> The bank is not reset by the user reset function or saved by the user save function.

\*5. When the number of connected units is 11 or more, the ambient temperature is less than 50°C.

# **Sensing Distances**

## Standard models/ Advanced models/ Analog output models

## **Threaded Models**

Oi	Oi				Sensing dis	tance (mm)	
Sensing method	Sensing direction	Size	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode
	Right-angle		E32-T11N 2M	3,000	1,500	1,050	280
	night-angle		E32-LT11N 2M	4,000 *1	4,000 *1	3,450	920
Through-beam		M4	E32-T11R 2M	3,000	1,500	1,050	280
	Straight		E32-LT11 2M	4,000 *1	4,000 *1	4,000 *1	1,080
			E32-LT11R 2M	4,000 *1	4,000 *1	3,450	920
	Right-angle	МЗ	E32-C31N 2M	160	75	69	14
		IVIO	E32-C21N 2M	440	190	130	39
		M4	E32-D21N 2M	1,260	520	360	100
		M6	E32-C11N 2M	1,170	520	480	100
			E32-LD11N 2M	1,260	520	360	100
Ī			E32-D21R 2M	210	90	60	16
Reflective		М3	E32-C31 2M	490	220	150	44
			E32-C31M 1M	490	220	150	44
	Ctualabt	M4	E32-D211R 2M	210	90	60	16
	Straight		E32-D11R 2M	1,260	520	360	100
		M6	E32-CC200 2M	2,100	900	600	180
		M6	E32-LD11 2M	1,290	540	370	110
			E32-LD11R 2M	1,260	520	360	100

<sup>\$1.</sup> The fiber length is 2 m on each side, so the sensing distance is given as 4,000 mm.

## **Cylindrical Models**

Oi		Compine		Sensing distance (mm)					
Sensing method	Size	Sensing direction	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode		
	1 dia.		E32-T223R 2M	670	370	220	60		
Through-beam	1.5 dia.	Top-view	E32-T22B 2M	1,020	600	330	90		
	3 dia.		E32-T12R 2M	3,000	1,500	1,050	280		
		Side-view	E32-T14LR 2M	1,120	670	390	100		
	1.5 dia.		E32-D22B 2M	210	90	60	16		
İ	1.5 dia. + 0.5 dia.		E32-D43M 1M	42	18	12	4		
Dofloativo		Tan Man	E32-D22R 2M	210	90	60	16		
Reflective	3 dia.	Top-view	E32-D221B 2M	450	210	130	40		
			E32-D32L 2M	1,050	450	300	90		
	3 dia. + 0.8 dia.		E32-D33 2M	100	45	30	8		

## **Flat Models**

Sensing			Sensing distance (mm)					
method	Sensing direction	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode		
	Top-view	E32-T15XR 2M	3,000	1,500	1,050	280		
Through-beam	Side-view	E32-T15YR 2M	1,120	670	390	100		
	Flat-view	E32-T15ZR 2M	1,120	670				
	Top-view	E32-D15XR 2M	1,260	520	360	100		
Reflective	Side-view	E32-D15YR 2M	300	450	70	24		
	Flat-view	E32-D15ZR 2M	300	150	78	24		

## **Sleeve Models**

0				Sensing dis	tance (mm)	
Sensing method	Sensing direction	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode
	Side-view	E32-T24R 2M	250	150	75	20
	Side-view	E32-T24E 2M	670	370	220	60
Through-beam		E32-T33 1M	220	130	75	20
	Top-view	E32-T21-S1 2M	760	450	250	68
		E32-TC200BR 2M	3,000	1,500	1,050	280
	Side-view	E32-D24R 2M	100	45	30	8
		E32-D24-S2 2M	180	79	67	14
		E32-D43M 1M	42	18	12	4
		E32-D331 2M	21	9	6	2
		E32-D33 2M	100	45	30	8
Deficetive		E32-D32-S1 0.5M	0.4	40	27	
Reflective	Top view	E32-D31-S1 0.5M	94	40	27	7
	Top-view	E32-DC200F4R 2M	210	90	60	16
		E32-D22-S1 2M	070	100	100	
		E32-D21-S3 2M	370	160	100	30
		E32-DC200BR 2M	1,260	520	360	100
		E32-D25-S3 2M	370	160	100	30

## **Small-spot, Reflective Models**

		Center			Sensing dis	tance (mm)	_		
Туре	Spot diameter	distance (mm)	Models	Giga mode	Standard mode	High-speed mode	Super-high- speed mode		
Variable spot	0.1 to 0.6 dia.	6 to 15	E32-C42 1M + E39-F3A	Spot diameter of	f 0.1 to 0.6 mm at 6	to 15 mm.			
variable spot	0.3 to 1.6 dia.	10 to 30	E32-C42 1M + E39-F17	Spot diameter of 0.3 to 1.6 mm at 10 to 30 mm.					
Parallel light	4 dia.	0 to 20	E32-C31 2M + E39-F3C	Snot diameter of	f 4 mm may at 0 to	20 mm			
Farallel light		0 10 20	E32-C31N 2M + E39-F3C	Spot diameter of 4 mm max. at 0 to 20 mm.					
Intograted lone	0.1 dia.	5	E32-C42S 1M	Spot diameter of 0.1 mm at 5 mm.					
ntegrated lens —	6 dia.	50	E32-L15 2M	Spot diameter of 6 mm at 50 mm.					
	0.1 dia.		E32-C41 1M + E39-F3A-5	Spot diameter of 0.1 mm at 7 mm.					
·	0.5 dia.	7	E32-C31 2M + E39-F3A-5	Spot diameter of 0.5 mm at 7 mm.					
	0.5 dia.		E32-C31N 2M + E39-F3A-5						
Cmall anat	0.2 dia.		E32-C41 1M + E39-F3B	Spot diameter of	f 0.2 mm at 17 mm.				
Small-spot	O.E.dia	17	E32-C31 2M + E39-F3B	Coat diameter of	60 5 mm at 17 mm				
	0.5 dia.		E32-C31N 2M + E39-F3B	Spot diameter of 0.5 mm at 17 mm.					
İ	3 dia.	50	E32-CC200 2M + E39-F18	0 1 5 1 10 150					
	o uia.	a. 50	E32-C11N 2M + E39-F18	Spot diameter of 3 mm at 50 mm.					

## **High-power Beam Models**

	Compine				Sensing dis	tance (mm)	
Туре	Sensing direction	Aperture angle	Models	Giga mode	Standard mode	High-speed mode	Super-high- speed mode
	Right-angle	15°	E32-LT11N 2M	4,000 *2	4,000 *2	3,450	920
Through-beam		10°	E32-T17L 10M	20,000 *1	20,000 *1	20,000 *1	8,000
models with	Top-view	15°	E32-LT11 2M	4,000 *2	4,000 *2	4,000 *2	1,080
integrated lens		15	E32-LT11R 2M	4,000 *2	4,000 *2	3,450	920
	Side-view	30°	E32-T14 2M	4,000 *2	4,000 *2	4,000 *2	1,800
	Right-angle	12°	E32-T11N 2M + E39-F1	4,000 *2	4,000 *2	4,000 *2	2,000
		6°	E32-T11N 2M + E39-F16	4,000 *2	4,000 *2	4,000 *2	3,600
	Top-view	12°	E32-T11R 2M + E39-F1	4,000 *2	4,000 *2	4,000 *2	2,000
		6°	E32-T11R 2M + E39-F16	4,000 *2	4,000 *2	4,000 *2	3,600
	Side-view	60°	E32-T11R 2M + E39-F2	2,170	1,200	750	200
	Top-view	12°	E32-T11 2M + E39-F1	4,000 *2	4,000 *2	4,000 *2	1,860
	Top-view	6°	E32-T11 2M + E39-F16	4,000 *2	4,000 *2	4,000 *2	4,000 *2
	Side-view	60°	E32-T11 2M + E39-F2	3,450	1,980	1,290	320
Through-beam	Top-view	12°	E32-T51R 2M + E39-F1	4,000 *2	4,000 *2	4,000 *2	1,500
models with		6°	E32-T51R 2M + E39-F16	4,000 *2	4,000 *2	4,000 *2	4,000 *2
lenses	Side-view	60°	E32-T51R 2M + E39-F2	2,100	1,080	750	200
	Top-view	12°	E32-T81R-S 2M + E39-F1	4,000 *2	4,000 *2	4,000 *2	1,000
	rop-view	6°	E32-T81R-S 2M + E39-F16	4,000 *2	4,000 *2	4,000 *2	1,800
	Side-view	60°	E32-T81R-S 2M + E39-F2	1,500	820	540	140
	Top-view	12°	E32-T61-S 2M + E39-F1	4,000 *2	4,000 *2	4,000 *2	1,800
	rop-view	6°	E32-T61-S 2M + E39-F16	4,000 *2	4,000 *2	4,000 *2	3,100
	Side-view	60°	E32-T61-S 2M + E39-F2	2,520	1,350	900	240
Ţ	Top-view	12°	E32-T51 2M + E39-F1-33	4,000 *2	4,000 *2	3,450	1,400
	i op-view	6°	E32-T51 2M + E39-F16	4,000 *2	4,000 *2	4,000 *2	4,000 *2
Reflective models with integrated lens	Top-view	<b>4</b> °	E32-D16 2M	40 to 4,000 *2	40 to 2,100	40 to 1,350	40 to 480

**<sup>\*1.</sup>** The fiber length is 10 m on each side, so the sensing distance is given as 20,000 mm.

## **Narrow View Models**

Sensing	Sensing	Aperture angle		Sensing distance (mm)					
method	direction		Models	Giga mode Standard mo		High-speed mode	Super-high- speed mode		
	Side-view	1.5°	E32-A03 2M	4,000 *1	2,670	1,800	500		
			E32-A03-1 2M				300		
Through-beam		3.4°	E32-A04 2M	1,920	1,020	670	200		
mough-beam		<b>4</b> °	E32-T24SR 2M	4,000 *1	3,300	2,190	580		
			E32-T24S 2M	4,000 *1	3,900	2,610	700		
			E32-T22S 2M	4,000 *1	4,000 *1	3,750	1,000		

<sup>\*1.</sup> The fiber length is 2 m on each side, so the sensing distance is given as 4,000 mm.

## **Models for Detection without Background Interference**

Sensing			Sensing distance (mm)			
method	Sensing direction	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode
	Flat-view	E32-L16-N 2M	0 to 15 0 to 12			
Limited- reflective	Flat-view	E32-L24S 2M	0 to 4			
	Side-view	E32-L25L 2M	5.4 to 9 (center 7.2)			

## **Transparent Object Detection (Retro-reflective Models)**

Sensing				Sensing distance (mm)				
method	Feature	Size	Models	Giga mode	Standard mode	High-speed mode	Super-high- speed mode	
	Film detection	M3	E32-C31 2M + E39-F3R + E39-RP37	370		300		
Retro-reflective	Square		E32-R16 5M	150 t		1,500		
netro-reflective	Threaded		E32-R21 2M	10 to 370			10 to 250	
	Hex-shaped	M6	E32-LR11NP 2M + E39-RP1	2,020	1,800	1,500	550	

**<sup>\*2.</sup>** The fiber length is 2 m on each side, so the sensing distance is given as 4,000 mm.

## **Transparent Object Detection (Limited-reflective Models)**

Sensing	Feature	Sensing direction	Model	Sensing distance (mm)				
method	reature	Sensing direction	Woder	Giga mode	Standard mode	High-speed mode	Super-high-speed mode	
	Small size		E32-L24S 2M	0 to 4				
	Standard		E32-L16-N 2M	0 to 15			0 to 12	
Limited-	Glass substrate alignment, 70°C	Flat-view	E32-A08 2M		10 to 20			
reflective	Standard/long-distance		E32-A12 2M		12 to 30			
	Side-view form	Side-view	E32-L25L 2M		5.4 to	9 (center 7.2)		
	Glass substrate mapping, 70°C	Top-view	E32-A09 2M	15 to 38				

## **Chemical-resistant, Oil-resistant Models**

Sensing	Type	Sensing direction	Model	Sensing distance (mm)					
method	Туре	Sensing direction	Wodei	Giga mode	Standard mode	High-speed mode	Super-high-speed mode		
	Oil-resistant	Right-angle	E32-T11NF 2M	4,000 *1	4,000 <b>*</b> 1	4,000 <b>*</b> 1	2,200		
		Top-view	E32-T12F 2M	4,000 *1	4,000 *1	4,000 *1	1,600		
Through-beam	Chemical/oil-resistant	Top-view	E32-T11F 2M	4,000 *1	4,000 <b>*</b> 1	3,900	1,000		
		Side-view	E32-T14F 2M	2,100	1,200	750	200		
	Chemical/oil-resistant at 150°C	Top-view	E32-T51F 2M	4,000 *1	4,000 <b>*</b> 1	2,700	700		
	Semiconductors: Cleaning, developing, and etching; 60°C		E32-L11FP 5M	8 to 20 mm from tip of lens (Recommended sensing distance: 11 mm), 19 to 31 mm from center of mounting hole A (Recommended sensing distance: 22 mm)					
Reflective	Semiconductors: Resist stripping; 85°C	Top-view	E32-L11FS 5M	8 to 20 mm from tip of lens (Recommended sensing distance: 11 mm), 32 to 44 mm from center of mounting hole A (Recommended sensing distance: 35 mm					
	Chemical/oil-resistant		E32-D12F 2M	<b>*</b> 2	280	190	60		
	Chemical-resistant cable		E32-D11U 2M	1,260	520	360	100		

## **Bending-resistant Models**

Sensing	Size	Model	Sensing distance (mm)					
method	Size	Model	Giga mode	Standard mode	High-speed mode	Super-high-speed mode		
	1.5 dia.	E32-T22B 2M	1,020	600	330	90		
Through boom	M3	E32-T21 2M	1,020	600		90		
Through-beam	M4	E32-T11 2M	3,750	2,020	1,350	360		
	Square	32-T25XB 2M	750	450	250	70		
	1.5 dia.	E32-D22B 2M	210	90	60	16		
	M3	E32-D21 2M	210	90	00	10		
Reflective	3 dia.	E32-D221B 2M	450	210	130	40		
nellective	M4	E32-D21B 2M	450	210	130	40		
	M6	E32-D11 2M	1,260	520	360	100		
	Square	E32-D25XB 2M	360	150	90	30		

## **Heat-resistant Models**

Sensing	Heat-resistant temperature	Model	Sensing distance (mm)					
method	neat-resistant temperature	Wodei	Giga mode	Standard mode	High-speed mode	Super-high-speed mode		
	100°C	E32-T51R 2M	2,400	1,200	840	225		
Through beem	150°C	E32-T51 2M	4,000 *1	2,250	1,500	400		
Through-beam —	200°C	E32-T81R-S 2M	1,500	820	540	140		
	350°C	E32-T61-S 2M	2,520	1,350	900	240		
	100°C	E32-D51R 2M	1,000	420	280	80		
	150°C	E32-D51 2M	1,680	670	480	144		
	200°C	E32-D81R-S 2M	630	270	180	54		
Reflective	300°C	E32-A08H2 2M						
Hellective	300°C	E32-A09H2 2M		20 to 30 (center 2	5)			
	05000	E32-D611-S 2M	600	070	400	F.4		
	350°C	E32-D61-S 2M	630	270	180	54		
	400°C	E32-D73-S 2M	420	180	120	36		

<sup>\$1.</sup> The fiber length is 2 m on each side, so the sensing distance is given as 4,000 mm.

<sup>\*1.</sup> The fiber length is 2 m on each side, so the sensing distance is given as 4,000 mm.
\*2. Even if there is no sensing object, the Sensor will detect light that is reflected by the fluororesin.

## **Area Detection Models**

Sensing	Туре	Sensing width	Model	Sensing distance (mm)					
method	Туре	Sensing width	Wodel	Giga mode	Standard mode	High-speed mode	Super-high-speed mode		
		11 mm	E32-T16PR 2M	4,000 *1	2,550	1,680	440		
Through-beam	Area		E32-T16JR 2M	4,000 *1	2,250	1,440	380		
		30 mm	E32-T16WR 2M	4,000 *1	3,900	2,550	680		
Reflective	Array	11 mm	E32-D36P1 2M	1,050	450	300	90		

<sup>\$1.</sup> The fiber length is 2 m on each side, so the sensing distance is given as 4,000 mm.

## **Liquid-level Detection Models**

Sensing	Tube diameter	Feature	Feature Model		Sensir	ng distance (mm)			
method	rube diameter	reature	Wodel	Giga mode	Standard mode	High-speed mode	Super-high-speed mode		
	3.2, 6.4, or 9.5 dia	Stable residual quantity detection	E32-A01 5M	Applicable tube: Transparent tube with a diameter of 3.2, 6.4, or 9.5 mm, Recommended wall thickness: 1 mm					
Tube-mounting	8 to 10 dia	E32-L25T 2M	Applicable tube: Transparent tube with a diameter of 8 to 10 mm, Recommended wall thickness: 1 mm						
	No restrictions	Large tubes	E32-D36T 5M	Applicable tube: Transparent tube (no restrictions on diameter)					
Liquid contact (heat-resistant up to 200°C)			E32-D82F1 4M	Liquid-contact type					

## **Vacuum-resistant Models**

Sensing	Heat-resistant temperature	resistant temperature Model		Sensing distance (mm)					
method	near-resistant temperature	Woder	Giga mode	Standard mode	High-speed mode	Super-high-speed mode			
Through-beam		E32-T51V 1M	1,080	600	390	100			
	120°C	E32-T51V 1M + E39-F1V	2,000 *1	2,000 *1	2,000 *1	520			
	200°C	E32-T84SV 1M	2,000 *1	1,420	960	260			

<sup>\*1.</sup> The fiber length is 1 m on each side, so the sensing distance is given as 2,000 mm.

## Models for FPD, Semiconductors, and Solar Cells

Sensing	Amuliantian	Operating	Model		Sensir	ng distance (mm)			
method	Application	temperature	Wodei	Giga mode	Standard mode	High-speed mode	Super-high-speed mode		
	Glass presence detection	70°C	E32-L16-N 2M		0 to 15		0 to 12		
			E32-A08 2M		10 to 20				
	Glass substrate alignment	300°C	E32-A08H2 3M		10 10 20				
	angrimone	70°C	E32-A12 2M		12 to 30				
Limited-	Glass substrate	70°C	E32-A09 2M		15 to 38				
reflective	mapping	300°C	E32-A09H2 2M						
	Wet processes: Cleaning, Resist developing and etching	60°C	E32-L11FP 5M	8 to 20 mm from tip of lens (Recommended sensing distance: 11 mm), 19 to 31 mm from center of mounting hole A (Recommended sensing distance: 22 mm					
	Wet process: Resist stripping	85°C	E32-L11FS 5M			ended sensing distance nole A (Recommende	e: 11 mm), d sensing distance: 35 mm)		
			E32-A03 2M	4.000 *1	2,670	1,800	500		
			E32-A03-1 2M	4,000 *1	2,670	1,000	500		
Through-beam	Wafer mapping	70°C	E32-A04 2M	1,920	1,020	670	200		
			E32-T24SR 2M	4,000 *1	3,300	2,190	580		
			E32-T24S 2M	4,000 *1	3,900	2,610	700		

 $<sup>\</sup>pmb{*1.}$  The fiber length is 2 m on each side, so the sensing distance is given as 4,000 mm.

## **Infrared models**

## **Threaded Models**

Sensing				Sensing distance (mm)				
method	Sensing direction	Size	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode	
Right-angle	Right-angle	M4	E32-T11N 2M	280	190	130	55	
Through-beam	Straight		E32-T11R 2M					
		М3	E32-C31 2M	50	37	25	8.5	
Reflective	Straight	M6	E32-D11R 2M	120	90	60	21	
			E32-CC200 2M	200	150	100	35	

## **Cylindrical Models**

Sensing method		Sensing		Sensing distance (mm)				
	Size	direction	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode	
Through-beam	3 dia.	Top-view	E32-T12R 2M	280	190	130	55	
		Side-view	E32-T14LR 2M	100	75	80	21	
Reflective	3 dia.	Top-view	E32-D32L 2M	100	75	50	17	

## **Flat Models**

Sensing			Sensing distance (mm)					
method	Sensing direction	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode		
	Top-view	E32-T15XR 2M	280	190	130	55		
Through-beam	Side-view	E32-T15YR 2M	100	75	80	21		
·	Flat-view	E32-T15ZR 2M	100					
	Top-view	E32-D15XR 2M	120	90	60	21		
Reflective	Side-view	E32-D15YR 2M	28	00	10	_		
•	Flat-view	E32-D15ZR 2M	28	20	13	5		

## **Sleeve Models**

Sensing method			Sensing distance (mm)				
	Sensing direction	Model	Giga mode	Standard mode	High-speed mode	Super-high- speed mode	
Through-beam	Top-view	E32-TC200BR 2M	280	190	130	55	
Reflective	Top-view	E32-DC200BR 2M	120	90	60	21	

## **High-power Beam Models**

Туре	Sensing direction	Aperture angle		Sensing distance (mm)				
			Models	Giga mode	Standard mode	High-speed mode	Super-high- speed mode	
Through-beam models with integrated lens	Side-view	30°	E32-T14 2M	1800	1200	820	360	

# I/O Circuit Diagrams


## NPN Output

Model	Operation mode	Timing chart	L/D indicator	Output circuit					
E3NX-FA11 E3NX-FA6 E3NX-FA11-5 E3NX-FAH11 E3NX-FAH6	Light-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	L lit.	Display OUT indicator (orange)  Brown  Black  Control output  T 30 VDC					
	Dark-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	D lit.						
E3NX-FA21	Light-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black (orange) leads)	L lit.	Display  OUT2 indicator  Orange)  Brown  Black  Control output  Load  Orange off  10 to					
	Dark-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black (orange) leads)	D lit.	Control output Pink ch2    Document of the Control output Pink ch2   Blue   External Input   Pink	E3NX-FA7 E3NX-FA24	Light-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	L lit.	Display OUT indicator (orange)  Brown  Black  Control output  10 to 30 VDC
	Dark-ON	No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	D lit.	M8 Connector Pin Arrangement     (2 4)     (1)     (2)					
E3NX-FA7TW	Light-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black (orange) leads)	L lit.	Display  OUT2 indicator  Orange)  Photoelectric  Orange  Orange ch1  10 to					
	Dark-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black (orange) leads)	D lit.	Photoelectric Sensor main direut Tool Tool Tool Tool Tool Tool Tool Too					
E3NX-FA11AN	Light-ON	No incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	L lit.	Display OUT indicator (orange)  Brown  Black  Control output  10 to					
	Dark-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	D lit.	Photoelectric sensor main oricult  Photoelectric sensor main oricult  Orange Analog output Load 10 kΩ min.  Blue					

## **PNP Output**

Model	Operation mode	Timing chart	L/D indicator	Output circuit
E3NX-FA41 E3NX-FA8 E3NX-FAH41 E3NX-FAH8	Light-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	L lit.	Display OUT indicator (orange)  Brown  Control  Black output — 10 to
	Dark-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	D lit.	Photoelectric sensor main circuit Black output 10 30 100 100 100 100 100 100 100 100 1
E3NX-FA51	Light-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black (orange) leads)	L lit.	Display  OUT2 indicator (orange)  Brown  Pink  Control output  Sensor main  circuit  Orange  Display  OUT2 indicator (orange)  Brown  External input  Control output  Orange
	Dark-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Outputs ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black (orange) leads)	D lit.	sensor main circuit Orange ch2 Load Blue Load
E3NX-FA9 E3NX-FA54	Light-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	L lit.	Display OUT indicator (orange)  Brown  Orange input  Control  Black output  10 to  30 VDC
	Dark-ON	Incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	<b>D</b> lit.	M8 Connector Pin Arrangement     ①     ①     ①
E3NX-FA9TW E3NX-FA54TW	Light-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black (orange) leads)	L lit.	Display OUT2 indicator (orange) Brown  Control output Black ch1 Tonic output Sensor main circuit Orange ch2 Load
	Dark-ON	ch1/ Incident light ch2 No incident light OUT indicator Lit (orange) Not lit Outputs ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black (orange) leads)	D lit.	M8 Connector Pin Arrangement     ①     ③     ③     ③
E3NX-FA41AN	Light-ON	No incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	L/lit.	表示部 OUT表示灯 Brown  (僧) Orange Analog output 10 to 30 VDC
	Dark-ON	No incident light No incident light OUT indicator Lit (orange) Not lit Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	<b>D</b> lit.	Photoelectric sensor main circuit  Black Control output  Blue Load Load 10kΩ min.


## Plug (Sensor I/O Connector)




Wire color	Connection pin	Application
Brown	1	Power supply (+V)
White	2	External input / Output
Blue	3	Power supply (0 V)
Black	4	Output

## **Nomenclature**

#### E3NX-FA11/FA41/FA6/FA8/FA7/FA9/FA24/FA54/ FA11-5/FAH11/FAH41/FAH6/FAH8/FA11AN/FA41AN



#### E3NX-FA21/FA51/FA7TW/FA9TW/FA54TW/FA0/FAH0



## **Safety Precautions**

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

## **Warning Indications**

<u>^</u> WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally, there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

### **Meaning of Product Safety Symbols**

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.
Caution, fire Indicates the possibility of fire under specific conditions.

## **⚠ WARNING**

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Do not use the product with voltage in excess of the rated voltage.

Excess voltage may result in malfunction or fire.



Never use the product with an AC power supply. Otherwise, explosion may result.



#### **Precautions for Safe Use**

The following precautions must be observed to ensure safe operation of the Amplifier Unit. Doing so may cause damage or fire.

- 1. Do not install the product in the following locations.
- Locations subject to direct sunlight
- · Locations subject to condensation due to high humidity
- · Locations subject to corrosive gas
- · Locations subject to vibration or mechanical shocks exceeding the rated values
- · Locations subject to exposure to water, oil, chemicals
- · Locations subject to stream
- · Locations subjected to strong magnetic field or electric field
- 2. Do not use the product in environments subject to flammable or explosive gases.
- 3. Do not use the product in any atmosphere or environment that exceeds the ratings.
- 4. To secure the safety of operation and maintenance, do not install the product close to high-voltage devices and power devices.
- 5. High-voltage lines and power lines must be wired separately from the product. Wiring them together or placing them in the same duct may cause induction, resulting in malfunction or damage.
- 6. Do not apply any load exceeding the ratings. Otherwise, damage or fire may result.
- 7. Do not short the load. Otherwise, damage or fire may result.
- 8. Connect the load correctly.
- 9. Do not miswire such as the polarity of the power supply.
- 10.Do not use the product if the case is damaged.
- 11. Burn injury may occur. The product surface temperature rises depending on application conditions, such as the ambient temperature and the power supply voltage. Attention must be paid during operation or cleaning.
- 12. When setting the sensor, be sure to check safety such as by stopping the equipment.
- 13. Be sure to turn off the power supply before connecting or disconnecting wires.
- 14. Do not attempt to disassemble, repair, or modify the product in any
- 15. When disposing of the product, treat it as industrial waste.
- **16.**Do not use the Sensor in water, rainfall, or outdoors. **17.**Use the product in the IP54 enclosure.
- 18.UL Standard Certification (Applicable Models: E3NX-FA11/21/41/51

Only the sensors with Enhanced UL Certification Mark are certified by UL. They are intended to be supplied by a "Class 2 circuit". When used in United States and Canada, Please use the same Class 2 source for input and output. The overcurrent protection current rating is 2A max. They were evaluated as Open type and shall be installed within a enclosure.


## **Precautions for Correct Use**

- 1. Be sure to mount the unit to the DIN track until it clicks.
- 2. When using the Amplifier Units with Wire-saving Connectors, attach the protective stickers (provided with E3X-CN-series Connectors) on the unused power pins to prevent electrical shock and short circuiting.

When using the Amplifier Units with Connectors for Communications Units, attach the protective caps (provided with E3NW-series Sensor Communications Unit).

#### Amplifier Unit with Wiresaving Connector









- 3. The length for the cable extension must be 30 m or less (or less than 10 m for S-mark certified models). Be sure to use a cable of at least 0.3 mm<sup>2</sup> for extension. The power voltage must be 24 to 30 V when connecting amplifier units with extension cable and wire-saving connector.
- 4. Do not apply the forces on the cord exceeding the following limits: Pull: 40N; torque: 0.1N·m; pressure: 20N; bending: 29.4N
- 5. Do not apply excessive force such as tension, compression or torsion to the Amplifier Unit with the Fiber Unit fixed to the Amplifier
- 6. Always keep the protective cover in place when using the Amplifier Unit. Not doing so may cause malfunction.
- 7. It may take time until the received light intensity and measured value become stable immediately after the power is turned on depending on use environment.
- The product is ready to operate 200 ms after the power supply is turned ON.
- The Mobile Console E3X-MC11, E3X-MC11-SV2 and E3X-MC11-S cannot be connected.
- 10. The mutual interference prevention function does not work when in combination with E3C/E2C/E3X.
- 11.If the unit receives excessive sensor light, the mutual interference prevention function may not work properly, resulting in malfunction of the unit. In such case, increase the threshold.
- 12. Standard models and Advanced models
  - The Sensor Communication Unit E3X-DRT21-S, E3X-CRT, E3X-ECT and E3NW cannot be connected.
  - Model for Sensor Communication Unit (E3NX-FA0)
  - The Sensor Communication Unit E3NW can be connected.
  - E3X-DRT21-S, E3X-CRT, E3X-ECT cannot be connected.
- 13.If you notice an abnormal condition such as a strange odor, extreme heating of the unit, or smoke immediately stop using the product, turn off the power, and consult your dealer.
- 14. Do not use thinner, benzene, acetone, and lamp oil for cleaning.


(Unit: mm)


## **Fiber Amplifier Units**













# Amplifier Unit with Connector for Sensor Communications Unit E3NX-FA0/FAH0




## **Accessories (Sold Separately)**

## **Wire-saving Connectors**



\* E3X-CN11: 4-dia. cable with 3 conductors, Standard cable length: 2 m (Conductor cross-section: 0.2 mm² (AWG24), Insulator diameter: 1.1 mm) E3X-CN21: 4-dia. cable with 4 conductors, Standard cable length: 2 m (Conductor cross-section: 0.2 mm² (AWG24), Insulator diameter: 1.1 mm)




\* E3X-CN12: 2.6-dia. cable with 1 conductor, Standard cable length: 2 m (Conductor cross-section: 0.2 mm² (AWG24), Insulator diameter: 1.1 mm) E3X-CN22: 4-dia. cable with 2 conductors, Standard cable length: 2 m (Conductor cross-section: 0.2 mm² (AWG24), Insulator diameter: 1.1 mm)

## **Sensor I/O Connectors**

## Straight








#### L-shaped XS3F-M422-40□-A






# **Mounting Bracket** E39-L143




Material: Stainless steel (SUS304)





# DIN Track PFP-100N







Material: Aluminum

#### PFP-100N2









Material: Aluminum

# End Plate PFP-M







Materials: Iron, zinc plating

### Terms and Conditions Agreement

#### Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

#### Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warrantv.

See <a href="http://www.omron.com/global/">http://www.omron.com/global/</a> or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2017.11

In the interest of product improvement, specifications are subject to change without notice.

