OMRON

NX-series I/O System

Unique I/O increases application quality and range

Standardization of control system

Quality improvement by synchronizing data collection Flexible system configuration

Unique I/O increases application quality and range

The NX I/O connects sensors and actuators on production lines to optimize applications



SQL Server and Visual Basic are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Other company names and product names in this document are the trademarks or registered trademarks of their respective companies. The product photographs and figures that are used in this catalog may vary somewhat from the actual products. Microsoft product screen shot(s) reprinted with permission from Microsoft Corporation.



its	Position interface	End cover
outs,	 Incremental and absolute encoder support 	
,	Pulse output unit (line driver output model)	
	New	

Simplicity for advanced control

A fully integrated platform

The NX I/O is used to integrate sequence, motion, analog, vision, and safety control, previously done by PLC and dedicated controllers, and visualization of previously invisible sensor data within the Sysmac automation platform.

Sequence control

Multi-tasking and fully compliant with IEC 61131-3 standard programming and PLCopen[®] Function Blocks.







Motion control

PLCopen® Function Blocks for the motion control library are available to implement advanced motion control.



Analog control

The Sysmac Library* and instructions make temperature, weighing, and load control easier.



* The Sysmac Library is a collection of software functional components that can be used in programs for the NJ/NX/NY Controllers. Sample programs and HMI templates are also available. Download from Omron website and install to use in the Automation Software Sysmac Studio. http://www.ia.omron.com/sysmac_library/

	mining .					HOO	
Progra	e0 x						CHAILER
Ecterals	Name ResetAUTO SUC Activate DNO Activa	Exits Type SAFEROL SY_ESPE ROOL S7_EmergencyStop ROOL	Factor RALSE RALSE TRUE		Convert		 Carse Mails Other Solid
Artine Elter	Artivate	arystop Seasy-	Д	A30	Antine	Artivate Seaty-	
i Jam	- I, Startheet - I, Jacobeet - Jeet	Error - DiagCode -			ER, Jore ER, Jore Energial	8,000 Dreer- 8,000 Displode Residential	

Sysmac Library

Safety control

Conforms with PLCopen® Function Blocks for Safety.

EtherNet/IP



Feature of Sysmac

One Control through One Software and One Network simplifies control system configuration

Interfaces for sequence, motion, safety, and analog control and communications required for machines







OMRON



Visualized sensor data

TIO-Link makes communication down to the sensor level visible



Synchronized control for high-speed performance

Production data collection synchronized at high speed

Based on an internal high-speed bus running in synchronization with the EtherCAT network and CPU cycle, the NX I/O can be controlled and used for position, analog, and digital data collection with microsecond accuracy and with nanosecond resolution.

Feature
High-speed I/O units accurately synchronized with the CPU cycle*
Digital I/O: High-speed and time-stamp models (NsynX) Analog I/O: 10 us conversion time per channel and 1:30000 resolution
\cdot Load cell inputs: 125 μ s conversion time per channel and 24-bit resolution
*Fastest cycle time: NX7=125 μs, NJ5=500 μs



The NsynX technology is provided by the internal high-speed bus synchronized with the EtherCAT network. This technology is designed for machine control and includes: I/O units with distributed clock High-speed I/O units synchronized with the EtherCAT cycle

 I/O units with Time-Stamp function (accuracy < 1 μs)

Slave clock

Load data



 (\mathbf{k})

Master clock

Position data Torque data Synchronous data Synchronous data Synchronous data Synchronous data Synchron

Distributed clock

The EtherCAT node slave measures the time difference between incoming and returning frame - Time-Stamp function. With this Time-Stamp function the master can determine the propagation delay offset to the individual slave accurately. This mechanism ensures accurate synchronization between devices with less than 1 µs jitter.

HEADER DATAGRA

DATAGR

MerCAT.





Accurate control of input events and perfect control of output with nanosecond resolution

Synchronized with CPU cycle

TTTTT

Synchronous production data collection

Data can be collected from the load cell (load data) and servo system (position and torque data) in synchronization with the CPU cycle.

Note: Functionality provided by the EtherCAT coupler unit

Simplify system configurations

The choice is yours

The modern control system demands increasing levels of flexibility.

The NX I/O enables connection with various controllers through the global standard network, which expands system configuration possibilities.

Modular remote I/O systems offer flexibility in I/O configuration and a wide choice of signal types and performance levels so that every I/O station can be assembled with just the right combination without changing the control architecture.



EtherCAT specification is governed by the EtherCAT Technology Group (ETG). EtherCAT is suitable for motion control and other applications that require high speed and high precision because of no need of handshaking and high bandwidth utilization.



NJ/NX/NY Series or EtherCAT master from other vendors

Ether**CAT**

EtherNet/IP

EtherNet/IP specification is governed by the Open DeviceNet Vendors Association (ODVA). Based on standardized Ethernet protocols (TCP/IP, UDP/IP), EtherNet/IP devices can be mixed with standard Ethernet devices.



CJ Series or PLC from other vendors



Safety integrated



- Note: 1. Communications coupler units vary depending on the connected network.
 - 2. Connectable units vary depending on the communications coupler unit.
 - 3. The number of connectable nodes varies depending on the master.

Downsize machines and control panels

Reduce wiring time and save space

Push-In Plus connections reduce the work and time required for wiring. Modular design saves space. Also designed for installation in any orientation, the NX I/O can be freely allocated in machines.

Up to 63 units per communication coupler





Corresponding to our shared Value Design for Panel concept for the specifications of products



Save space in control panels

V and G terminals are provided for each input signal (NX-PC0030). No relay terminal block is required, which saves space in control panels.



OMRON

Greatly reduce wiring work with Push-In Plus terminal blocks

Push-In Plus terminal blocks make wiring work easy - just insert wires.



11

Flexible connectivity expands system configuration possibilities

One I/O system for various controllers

While different machines may require different levels of controller performance, the NX I/O is the only remote I/O system you will need. This will unify wiring and installation techniques, and simplify spare parts stock.



OIO-Link

Features

- Multivendor compatibility The NX I/O can be connected with PLC from other vendors as well as Omron PLC
- Start a small-scale IO-Link





IO-Link and other unique I/O systems can be easily integrated into existing machine configurations



Easy configuration with NX-IO Configurator



The NX-IO Configurator is software to set up and maintain EtherNet/IP coupler units and NX I/O Units on an EtherNet/IP coupler

* Connect the NX I/O system to a PLC from another vendor via a switching hub and set up with the CX-One.

Application example 1- Load cells

Press fit using servo press

Improve both speed and quality of the press-fit process

Load data is collected in synchronization with the CPU cycle for high-speed measurement, high-speed servo press control, and precision improvement.

Previous issues

Wait time must be considered to operate the dedicated press
controller together with the main PLC.

 Load, position, and torque data collected at the same time cannot be checked from the host device.

Solution using Sysmac

- One CPU system capable of switching between position, velocity, and torque control without stopping
- \cdot Fastest control cycle of 125 μs and servo press function using software for required control
- High-speed measurement and control by collecting load data synchronized with servo data (position and torque data).

TO





NJ/NX/NY Controller + NX I/O + 1S Servo

integrate control elements

Application example 2- Temperature control

Packaging machines and molding machines

(Temperature/motion/weighing)

Reduce material and design costs to implement temperature control

TCO can be reduced by eliminating the need for the dedicated temperature controller and reducing inventory control work and communications programming work.

Previous issues

- Communications networks are selected for each device, and dedicated software for each component is used.
- Ladder program and memory configuration for communications are required.

Solution using Sysmac

• Dedicated controllers, dedicated software, separate networks, and separate programs are no longer required



OMRON





Application example 3 - Photoelectric sensors and proximity sensors Improving system commissioning and changeover efficiency

Reduce work by individual identification

IO-Link photoelectric sensors and proximity sensors allow you to check individual sensor identificationsin batches without going to the site, which results in a significant reduction of commissioning time.



Setup

Setting all sensors from a host device at the same time

Reduce setting time and inconsistent settings



Identification checks with HMI

I/O check

Check sensor installation before commissioning to prevent installation mistakes



Ordering Information

International Standards

- Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, CE: EU Directives, RCM: Regulatory Compliance Mark, and KC: KC Registration
- · Contact your OMRON representative for further details and applicable conditions for these standards.

Communications Coupler Units • EtherCAT Coupler Units

Unit type	Product name	Communications cycle in DC Mode	Current consumption	Maximum I/O power supply current	Model	Standards	
NX-series Communications Coupler Unit * 1	EtherCAT Coupler Unit	250 to 4000 μs * 2	1.45 W or lower	4 A	NX-ECC201	UC1, N, L,	
		250 to 4000 μs * 2	1.45 W 01 10 Wei	10.4	NX-ECC202	KC	
		125 to 10000 μs * 2	1.25 W or lower	IUA	NX-ECC203	UC1, CE, RCM, KC	

*1. One End Cover NX-END01 is provided with the EtherCAT Coupler Unit. This depends on the Unit configuration.

• EtherNet/IP Coupler Unit



* One End Cover NX-END01 is provided with the EtherCAT Coupler Unit.

Digital Input Units

• DC Input Units (Screwless Clamping Terminal Block, 12 mm Width)



* To use input refreshing with input changed time, the NJ-series CPU Unit with unit version 1.06 or later, EtherCAT Coupler Unit with unit version 1.1 or later, and Sysmac Studio version 1.07 or higher are required.

• DC Input Unit (M3 Screw Terminal Block, 30 mm Width)

	Product name							
Unit type		Number of points	Internal I/O common	Rated input voltage	I/O refreshing method	ON/OFF response time	Model	Standards
	DC Input Unit							
NX-series Digital Input Unit		16 points	For both NPN/PNP	24 VDC	Switching Synchronous I/O refreshing and Free-Run refreshing	20 μs max./ 400 μs max.	NX-ID5142-1	UC1, CE, RCM, KC

• The standards are abbreviated as follows: U: UL, U1: UL (Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2

*2. This depends on the specifications of the EtherCAT master. For example, the values are as follows when the EtherCAT Coupler Unit is connected to the built-in EtherCAT port on an NJ5-series CPU Unit: 500 µs, 1,000 µs, 2,000 µs, and 4,000 µs. For the specifications of the built-in EtherCAT port, refer to the user's manual for the built-in EtherCAT port on the connected CPU Unit or the Industrial PC.

umption	Maximum I/O power supply current	Model	Standards
	10 A	NX-EIC202	UC1, CE, RCM, KC

Specification

cilication				
I/O refreshing method	ON/OFF response time	Model	Standards	
Switching Synchronous I/O refreshing	20 μs max./ 400 μs max.	NX-ID3317		
and Flee-Run Telleshing	100 no mov /	NX-ID3343		
Input refreshing with input changed ime only *	100 ns max.	NX-ID3344		
Switching Synchronous I/O refreshing and Free-Run refreshing	20 μs max./ 400 μs max.	NX-ID3417	UC1, N, L,	
nput refreshing with input changed	100 ns max./	NX-ID3443	KC	
time only *	100 ns max.	NX-ID3444		
		NX-ID4342		
Switching Synchronous I/O refreshing	20 μs max./	NX-ID4442		
and Free-Run refreshing	400 µs max.	NX-ID5342		
		NX-ID5442		

• DC Input Units (MIL Connector, 30 mm Width)

	Product							
Unit type	name	Number of points	Internal I/O common	Rated input voltage	I/O refreshing method	ON/OFF response time	Model	Standards
NX-series Digital Input Unit	DC Input Unit	16 points	For both		Switching Synchronous I/O	20 us may /	NX-ID5142-5	
		32 points	NPN/PNP	24 VDC	refreshing	400 μs max.	NX-ID6142-5	RCM, KC

• DC Input Unit (Fujitsu Connector, 30 mm Width)

	Droduct							
Unit type	name	Number of points	Internal I/O common	Rated input voltage	I/O refreshing method	ON/OFF response time	Model	Standards
	DC Input Unit							
NX-series Digital Input Unit		32 points	For both NPN/PNP	24 VDC	Switching Synchronous I/O refreshing and Free-Run refreshing	20 μs max./ 400 μs max.	NX-ID6142-6	UC1, N, CE, RCM, KC

• AC Input Unit (Screwless Clamping Terminal Block, 12 mm Width)

	Droduct		Specification					
Unit type	name	Number of points	Rated input voltage I/O refreshing method		ON/OFF response time	Model	Standards	
NX-series Digital Input	AC Input Unit	4 points	200 to 240 VAC, 50/60 Hz (170 to 264 VAC, ±3 Hz)	Free-Run refreshing	10 ms max./ 40 ms max.	NX-IA3117	UC1, N, CE, RCM, KC	
Unit								

Digital Output Units

• Transistor Output Units (Screwless Clamping Terminal Block, 12 mm Width)



* To use output refreshing with specified time stamp, the NJ-series CPU Unit with unit version 1.06 or later, EtherCAT Coupler Unit with unit version 1.1 or later, and Sysmac Studio version 1.07 or higher are required.

• Transistor Output Units (M3 Screw Terminal Block, 30 mm Width)

		Specification							
Unit type	Product name	Number of points	Internal I/O common	Maximum value of load current	Rated voltage	I/O refreshing method	ON/OFF response time	Model	Standards
NX-series Digital Output Unit	Transistor Output Unit		NPN	0.5 A/point	12 to 24 VDC	Switching Synchronous I/O refreshing	0.1 ms max./ 0.8 ms max.	NX-OD5121-1	UC1 N CE
		16 points	PNP	5 A/Unit	24 VDC	and Free-Run refreshing	0.5 ms max./ 1.0 ms max.	NX-OD5256-1	RCM, KC

• Transistor Output Units (MIL Connector, 30 mm Width)

		Specification									
Unit type	Product name	Number of points	Internal I/O common	Maximum value of load current	Rated voltage	I/O refreshing method	ON/OFF response time	Model	Standards		
	Transistor Output	16 pointo	NPN	0.5 A/point,	12 to 24 VDC		0.1 ms max./ 0.8 ms max.	NX-OD5121-5	UC1 N CE		
NX-series Digital	Unit I	Unit	PNP	2 A/Unit	24 VDC	Switching Synchronous I/O refreshing	0.5 ms max./ 1.0 ms max.	NX-OD5256-5			
Output Unit				7	NPN	0.5 A/point,	12 to 24 VDC	and Free-Run refreshing	0.1 ms max./ 0.8 ms max.	NX-OD6121-5	RCM, KC
						32 points PNP	PNP	2 A/common, 4 A/Unit	24 VDC		0.5 ms max./ 1.0 ms max.

• Transistor Output Unit (Fujitsu Connector, 30 mm Width)

	Product name								
Unit type		Number of points	Internal I/O common	Maximum value of load current	Rated voltage	I/O refreshing method	ON/OFF response time	Model	Standards
NX-series Digital Output Unit	Transistor Output Unit	32 points	NPN	0.5 A/point, 2 A/common, 4 A/Unit	12 to 24 VDC	Switching Synchronous I/O refreshing and Free-Run refreshing	0.1 ms max./ 0.8 ms max.	NX-OD6121-6	UC1, N, CE, RCM, KC

cif	ication				
	I/O refreshing method	ON/OFF response time	Model	Standards	
	Output refreshing with specified time	300 ns max./	NX-OD2154		
	stamp only *	300 ns max.	NX-OD2258	UC1, N, L, CE, RCM, KC	
С		0.1 ms max./ 0.8 ms max.	NX-OD3121		
		300 ns max./ 300 ns max.	NX-OD3153		
		0.5 ms max./ 1.0 ms max.	NX-OD3256		
		300 ns max./ 300 ns max.	NX-OD3257		
	Switching Synchronous I/O refreshing and Free-Run refreshing	0.5ms max./ 1.0ms max.	NX-OD3268	UC1, N, CE, RCM, KC	
С		0.1 ms max./ 0.8 ms max.	NX-OD4121		
		0.5 ms max./ 1.0 ms max.	NX-OD4256	UC1, N, L,	
С		0.1 ms max./ 0.8 ms max.	NX-OD5121	KC	
		0.5 ms max./ 1.0 ms max.	NX-OD5256		

• Relay Output Units (Screwless Clamping Terminal Block, 12 mm Width)

Unit type		Product name	Number Relay of points type		Maximum switching capacity	I/O refreshing method	ON/OFF response time	Model	Standards
	NX-series Digital Output Unit	Relay Output Unit	Alay htput it 2 points	N.O.	250 VAC/2 A (cosφ = 1), 250 VAC/2 A (cosφ = 0.4)		15 ms max /	NX-OC2633	UC1, N, L, CE, RCM, KC
				N.O.+N.C.	24 VDC/2 A, 4 A/Unit	Free-Run refreshing	15 ms max.	NX-OC2733	UC1, N, CE, RCM, KC

• Relay Output Unit (Screwless Clamping Terminal Block, 24 mm Width)

				Specif	ication				
Unit type	pe Product name	Number of points	Relay type	Maximum switching capacity	I/O refreshing method	ON/OFF response time	Model	Standards	
NX-seri Digital Output Unit	Relay Output Unit	8 points	N.O.	250 VAC/2 A (cosφ=1) 250 VAC/2 A (cosφ=0.4) 24 VDC/2 A 8 A/Unit	Free-Run refreshing	15 ms max./ 15 ms max.	NX-OC4633	UC1, CE, RCM, KC	

Note: For details of connection patterns for I/O relay terminals, refer to the NX-series Digital I/O Units User's Manual (Cat. No. W521).

Digital Mixed I/O Units

• DC Input/Transistor Output Units (MIL Connector, 30 mm Width)

Unit type	Product name	Number of points	Internal I/O common	Rated voltage	I/O refreshing method	ON/OFF response time	Model	Standards
NX-series Digital Mixed I/O Unit	DC Input/ Transistor Output Unit	Outputs: 16 points	Outputs: NPN Inputs: For both NPN/PNP Outputs: 12 to 24 VDC Inputs: 24 VDC		Switching Synchronous	Outputs: 0.1 ms max./ 0.8 ms max. Inputs: 20 μs max./ 400 μs max.	NX-MD6121-5	UC1, N, CE,
		Inputs: 16 points	Outputs: PNP Inputs: For both NPN/PNP	Outputs: 24 VDC Inputs: 24 VDC	I/O refreshing and Free-Run refreshing	Outputs: 0.5 ms max./ 1.0 ms max. Inputs: 20 μs max./ 400 μs max.	NX-MD6256-5	RCM, KC

• DC Input/Transistor Output Unit (Fujitsu Connector, 30 mm Width)

Unit type	Product name	Number of Internal I/O points common		Rated voltage I/O refreshing method		ON/OFF response time	Model	Standards
NX-series Digital Output Unit	DC Input/ Transistor Output Unit	Outputs: 16 points Inputs: 16 points	Outputs: NPN Inputs: For both NPN/PNP	Outputs: 12 to 24 VDC Inputs: 24 VDC	Switching Synchronous I/O refreshing and Free-Run refreshing	Outputs: 0.1 ms max./ 0.8 ms max. Inputs: 20 μs max./ 400 μs max.	NX-MD6121-6	UC1, N, CE, RCM, KC

Connection Patterns for Connector-Terminal Block Conversion Units



Connections to Connector-Terminal Block Conversion

Unit	I/O capacity	Number of connectors	Polarity	Con- nection pattern	Number of branches	Connecting Cable	Connector-Terminal Block Conversion Unit	Common terminal
				Α	None	XW2Z-🗆 🗆 X	XW2B-20G4	None
	16 inputo	1 MIL	NPN/	Α	None	XW2Z-🗆 🗆 X	XW2B-20G5	None
NA-ID5142-5	To inputs	connector	PNP	Α	None	XW2Z-🗆 🗆 X	XW2D-20G6	None
				Α	None	XW2Z-🗆 🗆 X	XW2R-J20G-T	None
				Α	None	XW2Z-🗆 🗆 K	XW2B-40G4	None
				Α	None	XW2Z-🗆 🗆 K	XW2B-40G5	None
				Α	None	XW2Z-🗆 🗆 K	XW2D-40G6	None
				Α	None	XW2Z-🗆 🗆 K	XW2D-40G6-RM * 1	None
				Α	None	XW2Z-🗆 🗆 K	XW2R-J40G-T	None
				В	2	XW2Z-🗆 🗆 N	XW2B-20G4 (2 Units)	None
NX-ID6142-5	32 inpute	1 MIL	NPN/	В	2	XW2Z-🗆 🗆 N	XW2B-20G5 (2 Units)	None
117-100142-3	52 inputs	connector	PNP	В	2	XW2Z-🗆 🗆 N	XW2C-20G5-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-🗆 🗆 N	XW2C-20G6-IO16 (2 Units)	Yes
				В	2	XW2Z-🗆 🗆 N	XW2D-20G6 (2 Units)	None
				В	2	XW2Z-□□□N	XW2E-20G5-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-□□□N	XW2F-20G7-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-□□□N	XW2N-20G8-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-□□□N	XW2R-J20G-T (2 Units)	None
				A	None	XW2Z-🗆 🗆 🛛 🛛 🛛 🛛 🖓	XW2B-40G4	None
				A	None	XW2Z-□□□B	XW2B-40G5	None
				A	None	XW2Z-🗆 🗆 🛛 🛛 🛛 🛛 🖓	XW2D-40G6	None
				A	None	XW2Z-🗆 🗆 🛛 🛛 🛛 🛛 🖓	XW2D-40G6-RF * 1	None
				A	None	XW2Z-□□□B	XW2R-J40G-T	None
				A	None	XW2Z-🗆 🗆 BU	XW2D-40C6	None
		1 Euliteu		В	2	XW2Z-□□□D	XW2B-20G4 (2 Units)	None
NX-ID6142-6	32 inputs	connector	PNP	В	2	XW2Z-□□□D	XW2B-20G5 (2 Units)	None
				В	2	XW2Z-□□□D	XW2C-20G5-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-□□□D	XW2C-20G6-IO16 (2 Units)	Yes
				В	2	XW2Z-🗆 🗆 🗆 D	XW2D-20G6 (2 Units)	None
				В	2	XW2Z-□□□D	XW2E-20G5-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-□□□D	XW2F-20G7-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-🗆 🗆 🗆 D	XW2N-20G8-IN16 (2 Units) * 2	Yes
				В	2	XW2Z-🗆 🗆 🗆 D	XW2R-J20G-T (2 Units)	None

*1. Bleeder resistor (5.6 k Ω) is built in.

*2. The inputs are NPN. For PNP inputs, reverse the polarity of the external power supply connections to the power supply terminals on the Connector-Terminal Block Conversion Unit.

iversion Units		
	Number of connectors	Branching
al Block		None
nches minal Block iit	1	2 branches
erminal Block Init	2	None

Slave Terminals NX Series

Unit	I/O capacity	Number of connectors	Polarity	Con- nection pattern	Number of branches	Connecting Cable	Connector-Terminal Block Conversion Unit	Common terminal
				Α	None	XW2Z-🗆 🗆 X	XW2B-20G4	None
	16 outputs	1 MIL		Α	None	XW2Z-🗆 🗆 X	XW2B-20G5	None
NA-0D5121-5	10 Outputs	connector	INFIN	Α	None	XW2Z-🗆 🗆 X	XW2D-20G6	None
				Α	None	XW2Z-🗆 🗆 X	XW2R-J20G-T	None
				Α	None	XW2Z-🗆 🗆 X	XW2B-20G4	None
	16 outputs	1 MIL	DND	Α	None	XW2Z-🗆 🗆 X	XW2B-20G5	None
NA-0D5250-5	10 Outputs	connector	FINE	A	None	XW2Z-🗆 🗆 🗆 X	XW2D-20G6	None
				Α	None	XW2Z-🗆 🗆 X	XW2R-J20G-T	None
				Α	None	XW2Z-🗆 🗆 K	XW2B-40G4	None
				Α	None	XW2Z-🗆 🗆 K	XW2B-40G5	None
				Α	None	XW2Z-🗆 🗆 K	XW2D-40G6	None
				Α	None	XW2Z-🗆 🗆 K	XW2R-J40G-T	None
	00	1 MIL		В	2	XW2Z-🗆 🗆 N	XW2B-20G4 (2 Units)	None
NX-OD6121-5	32 outputs	connector	INPIN	В	2	XW2Z-🗆 🗆 N	XW2B-20G5 (2 Units)	None
				В	2	XW2Z-🗆 🗆 N	XW2C-20G6-IO16 (2 Units)	Yes
				В	2	XW2Z-□□□N	XW2D-20G6 (2 Units)	None
				В	2	XW2Z-🗆 🗆 N	XW2F-20G7-OUT16 (2 Units)	Yes
				В	2	XW2Z-	XW2R-J20G-T (2 Units)	None
				Α	None	XW2Z-	XW2B-40G4	None
				Α	None	XW2Z-	XW2B-40G5	None
		1 Fujitsu	NPN	Α	None	XW2Z-	XW2D-40G6	None
				Α	None	XW2Z-	XW2R-J40G-T	None
				Α	None	XW2Z-	XW2D-40C6	None
NX-OD6121-6	32 outputs			В	2	XW2Z-	XW2B-20G4 (2 Units)	None
		connector		В	2	XW2Z-□□□L	XW2B-20G5 (2 Units)	None
				В	2	XW2Z-	XW2C-20G6-IO16 (2 Units)	Yes
				В	2	XW2Z-	XW2D-20G6 (2 Units)	None
				В	2	XW2Z-□□□L	XW2F-20G7-OUT16 (2 Units)	Yes
				В	2	XW2Z-🗆 🗆 🗆 L	XW2R-J20G-T (2 Units)	None
				Α	None	XW2Z-DDDK	XW2B-40G4	None
				A	None	XW27-000K	XW2B-40G5	None
				A	None	XW27-000K	XW2D-40G6	None
				A	None	XW27-00K	XW2B-,140G-T	None
		1 MII		B	2	XW27-000N	XW2B-20G4 (2 Units)	None
NX-OD6256-5	32 outputs	connector	PNP	B	2	XW2Z-000N	XW2B-20G5 (2 Units)	None
				B	2	XW27-000N	XW2C-20G6-IO16 (2 Units)	Yes
				B	2	XW2Z-000N	XW2D-20G6 (2 Units)	None
				B	2	XW27-	XW2F-20G7-OUT16 (2 Units)	Yes
				B	2	XW27-000N	XW2B-,120G-T (2 Inits)	None
				C.	None	XW27-	XW2B-20G4	None
		1 MII		с С	None	XW27-	XW2B-20G5	None
	16 inputs	connector	PNP	C.	None		XW2D-20G6	None
		201100101		С С	None		XW2B-120G-T	None
NX-MD6121-5				0	None		XW2B-20G4	None
		1 MII		0	None	XW27-	XW2B-20G5	None
	16 outputs	connector	NPN	C	None		XW2D-20G6	None
		2011100101		С С	Nono		XW2B-120G0	None
	1	1		U	NOLIE			NOUG

Unit	I/O capacity	Number of connectors	Polarity	Con- nection pattern	Number of branches	Connecting Cable	Connector-Terminal Block Conversion Unit	Common terminal
				С	None	XW2Z-🗆 🗆 🗛	XW2B-20G4	None
				С	None	XW2Z-🗆 🗆 🗛	XW2B-20G5	None
				С	None	XW2Z-🗆 🗆 🗛	XW2C-20G5-IN16 *	Yes
				С	None	XW2Z-🗆 🗆 🗛	XW2C-20G6-IO16	Yes
	16 inputs	1 Fujitsu	NPN/ PNP	С	None	XW2Z-🗆 🗆 🗛	XW2D-20G6	None
		0011100101		С	None	XW2Z-🗆 🗆 🗛	XW2E-20G5-IN16 *	Yes
				С	None	XW2Z-🗆 🗆 🗛	XW2F-20G7-IN16 *	Yes
NX-MD6121-6			· · ·	С	None	XW2Z-🗆 🗆 🗛	XW2N-20G8-IN16 *	Yes
				С	None	XW2Z-🗆 🗆 🗛	XW2R-J20G-T	None
	16 outputs	1 Fujitsu connector	NPN	С	None	XW2Z-🗆 🗆 🗛	XW2B-20G4	None
				С	None	XW2Z-🗆 🗆 🗛	XW2B-20G5	None
				С	None	XW2Z-🗆 🗆 🗛	XW2C-20G6-IO16	Yes
				С	None	XW2Z-🗆 🗆 🗛	XW2D-20G6	None
				С	None	XW2Z-🗆 🗆 🗛	XW2F-20G7-OUT16	Yes
				С	None	XW2Z-🗆 🗆 🗛	XW2R-J20G-T	None
				С	None	XW2Z-🗆 🗆 X	XW2B-20G4	None
	16 inpute	1 MIL	NPN/	С	None	XW2Z-🗆 🗆 X	XW2B-20G5	None
	TO INPULS	connector	PNP	С	None	XW2Z-🗆 🗆 X	XW2D-20G6	None
				С	None	XW2Z-🗆 🗆 X	XW2R-J20G-T	None
NX-MD6256-5				С	None	XW2Z-🗆 🗆 X	XW2B-20G4	None
	16 outputo	1 MIL	DND	С	None	XW2Z-🗆 🗆 X	XW2B-20G5	None
		connector	PNP	С	None	XW2Z-🗆 🗆 X	XW2D-20G6	None
				С	None	XW2Z-🗆 🗆 X	XW2R-J20G-T	None

* The inputs are NPN. For PNP inputs, reverse the polarity of the external power supply connections to the power supply terminals on the Connector-Terminal Block Conversion Unit.

Slave Terminals NX Series

Analog Input Units

Unit type	Product name	Number of points	Input range	Resolution	Conversion value, decimal number (0 to 100%)	Over all accuracy (25°C)	Input method	Conversion time	Input impedance	I/O refreshing method	Model	Standards	
					4000 4-	.0.00/	Single-	050/		Free Dur	NX-AD2603		
				1/8000	4000 10	±0.2% (full scale)	Differential input	point		refreshing	NX-AD2604		
		2 points	s	1/30000	-15000 to 15000	±0.1% (full scale)	Differential input	10 μs/ point		Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-AD2608		
	Voltage Input type			1/8000	-4000 to 4000	±0.2% (full scale)	Single- ended input Differential input	250 μs/ point	Free-Ru refreshir	Free-Run refreshing	NX-AD3603 NX-AD3604		
		4 points	points -10 to +10 V	1/30000	-15000 to 15000	±0.1% (full scale)	Differential input	10 μs/ point	1 MΩ min.	Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-AD3608		
		8 points				4000 to	.0.0%	Single- ended input	250		Free Dup	NX-AD4603	
NX-series			points	1/8000	4000 10	(full scale)	Differential input	point	refreshing	NX-AD4604			
				1/30000	-15000 to 15000	±0.1% (full scale)	Differential input	10 μs/ point		Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-AD4608	UC1, N, L, CE, RCM.	
Analog Input Unit		2 points		1/0000	0.4- 0000	±0.2%	Single- ended input	250 μs/		Free-Run	NX-AD2203	KC	
				1/8000	0 10 8000	(full scale)	Differential input	point		refreshing	NX-AD2204		
				1/30000	0 to 30000	±0.1% (full scale)	Differential input	10 μs/ point	Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-AD2208			
	Current Input					+0.2%	Single- ended input	250 us/	250 52	Free-Bun	NX-AD3203		
	type			1/8000	0 to 8000	(full scale)	Differential input	point		refreshing	NX-AD3204	-	
		4 points 4 to 20 mA	1/30000	0 to 30000	±0.1% (full scale)	Differential input	10 μs/ point		Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-AD3208	-		
			-			+0.2%	Single- ended input	250 us/		Free-Bun	NX-AD4203		
				1/8000	0 to 8000	(full scale)	Differential input	point		refreshing	NX-AD4204		
			8 points		1/30000	0 to 30000	±0.1% (full scale)	Differential input	10 μs/ point	85 Ω	Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-AD4208	

Analog Output Units



Temperature Input Units



*1. The resolution is 0.2°C max. when the input type is R, S, or W.
*2. The NX-TS2202 and NX-TS3202 only support Pt100 three-wire sensor.

ecification					
ut setting , decimal umber o 100%)	Over all accuracy (25°C)	Conversion time	I/O refreshing method	Model	Standards
to 4000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	NX-DA2603	
) to 15000	±0.1% (full scale)	10 μs/point	Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-DA2605	
to 4000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	NX-DA3603	
) to 15000	±0.1% (full scale)	10 μs/point	Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-DA3605	UC1,N, L,
000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	NX-DA2203	KC
0000	±0.1% (full scale)	10 μs/point	Selectable Synchronous I/O refreshing or Free-Run refreshing	NX-DA2205	
000	±0.3% (full scale)	250 μs/point	Free-Run refreshing	NX-DA3203	
0000	±0.1% (full scale)	10 μs/point	Selectable Synchronous I/Orefreshing or Free-Run refreshing	NX-DA3205	

Specification					
Over all accuracy (25°C)	Conversion time	I/O refreshing method	Terminals	Model	Standards
			16 Terminals	NX-TS2101	
	250 ms/Unit		16 Terminals x 2	NX-TS3101	
			16 Terminals	NX-TS2102	
	10 ms/Unit	- Free-Run	16 Terminals x 2	NX-TS3102	UC1, N, L,
efer to the eference accuracy			16 Terminals	NX-TS2104	
the input type and essurement	60 ms/Unit		16 Terminals x 2	NX-TS3104	
mperature of NX- pries Temperature	250 ms/Unit	refreshing	16 Terminals	NX-TS2201	KC
<i>usmac Integrated</i> <i>atalog</i> (Cat. No. 072).			16 Terminals x 2	NX-TS3201	
·· _).			16 Terminals	NX-TS2202	
	10 ms/Unit		16 Terminals x 2	NX-TS3202	
			16 Terminals	NX-TS2204	
	60 ms/Unit		16 Terminals x 2	NX-TS3204	

Heater Burnout Detection Units

		Specification								
		CT inpu	t section		Control output section					
Unit type	Product name	Number of inputs	Maximum heater current	Number of outputs	Internal I/O common	Maximum load current	Rated voltage	I/O refreshing method	Model	Standards
NX-series Heater	Heater Burnout Detection Unit		50.4.40	4	NPN	0.1 A/point,	12 to 24 VDC	Free-Run	NX-HB3101	UC1, CE,
Burnout Detection Unit		4 50 A AC	4	PNP	0.4 A/Unit	24 VDC	refreshing	NX-HB3201	RCM, KC	

Optional Products

Product name	Specification	Model	Standards
Current Transformer (CT)	Hole diameter: 5.8 mm	E54-CT1	
Current transformer (CT)	Hole diameter: 12.0 mm	E54-CT3	

Load Cell Input Unit

Unit type	Product name							
		Number of points	Conversion cycle	I/O refreshing method *	Load cell excitation voltage	Input range	Model	Standards
	Load Cell Input Unit							
NX-series Load Cell Input Unit	1	1	125 μs	 Free-Run refreshing Synchronous I/O refreshing Task period prioritized refreshing 	5 VDC ± 10%	-5.0 to 5.0 mV/V	NX-RS1201	UC1, CE, RCM, KC

* Refer to the *I/O Refreshing* in the *NX-series Load Cell Input Unit User's Manual* (Cat. No. W565) for detailed information on I/O refresh cycle. **Note:** The NX-RS1201-K Load Cell Input Unit with the test and calibration certificate is also available. Ask your OMRON representative for details.

Position Interface Units

• Incremental Encoder Input Units

	Product name								
Unit type		Number of channels	External inputs	Maximum response frequency	I/O refreshing method	Number of I/O entry mappings	Remarks	Model	Standards
		1 (NPN)	3 (NPN)	IPN) NP) IPN) NP) 4 MHz			24-V voltage	NX-EC0112	UC1, N, CE, RCM, KC
	Encoder	1 (PNP)	3 (PNP)		 Free-Run refreshing Synchronous I/O refreshing 	1/1	input	NX-EC0122	UC1, N, L, CE, RCM, KC
NX-series		1	3 (NPN)				Line receiver input	NX-EC0132	UC1, N, CE, RCM, KC
Interface Unit		1	3 (PNP)					NX-EC0142	UC1, N, L, CE, RCM, KC
		2 (NPN)	Nono	500 kHz		2/2	24-V voltage	NX-EC0212	UC1, N, CE, RCM, KC
		2 (PNP)	INUTIE				input	NX-EC0222	UC1, N, L, CE, RCM, KC

• SSI Input Units

Unit type	Product name				_			
		Number of channels	Input/Output form	Maximum data length	Encoder power supply	Type of external connections	Model	Standards
NX-series Position Interface Unit	SSI Input Unit	1	EIA standard RS-422-A	32 bits	24 VDC, 0.3 A/CH	Screwless push-in terminal block (12 terminals)	NX-ECS112	UC1, N, L, CE, RCM, KC
		2	EIA standard RS-422-A	32 bits	24 VDC, 0.3 A/CH	Screwless push-in terminal block (12 terminals)	NX-ECS212	UC1, N, L, CE, RCM, KC

Pulse Output Units

					Specificatio	n				
Unit type	Product name	Number of channels * 1	External inputs	External outputs	Maximum pulse output speed	I/O refreshing method	Number of I/O entry mappings	Control output interface	Model	Standards
		1 (NPN)	2 (NPN)	1 (NPN)	— 500 kpps — 4 Mpps	Synchronous I/O refreshing Task period prioritized refreshing * 2	1/1	Open	NX-PG0112	UC1, N, CE, RCM, KC
	Pulse Output Unit	1 (PNP)	2 (PNP)	1 (PNP)				output	NX-PG0122	UC1, N, L, CE, RCM, KC
NX-series		0	5 inputs/CH (NPN)	3 outputs/ CH (NPN)			2/2	Line driver output	NX-PG0232-5	
Interface Unit		2	5 inputs/CH (PNP)	3 outputs/ CH (PNP)					NX-PG0242-5	UC1, CE,
		4	5 inputs/CH (NPN)	3 outputs/ CH (NPN)					NX-PG0332-5	RCM, KC
	4	4	5 inputs/CH (PNP)	CH 3 outputs/ CH (PNP)					NX-PG0342-5	

*1. This is the number of pulse output channels.

*2. Unit version 1.2 or later and an NX-ECC203 EtherCAT Coupler Unit are required.

Cables and Connectors for Line Driver Output Units with MIL Connectors

Product name	Specifications		Model	Standards	
	Flat Cable Connectors type (Terminal block with M3 screws) 34 terminals		XW2B-34G4		
	Flat Cable Connectors type (Terminal block with M3.5 screws) 34 terminals		XW2B-34G5		
Connector-Terminal Block	MIL Connectors type (Slim Connector) 34 terminals	-	XW2D-34G6		
Conversion Unit	MIL Connectors type (Phillips screw) 34 terminals		XW2R-J34GD-T		
	MIL Connectors type (Slotted screw (rise up)) 34 terminals		XW2R-E34GD-T		
	MIL Connectors type (Push-in spring) 34 terminals		XW2R-P34GD-T		
		Cable length: 0.5 m	XW2Z-050EE		
		Cable length: 1 m	XW2Z-100EE		
Cable for Connector-Terminal	34-terminal MIL Connector to	Cable length: 1.5 m	XW2Z-150EE	- 	
Block Conversion Unit	34-terminal MIL Connector	Cable length: 2 m	XW2Z-200EE		
	•	Cable length: 3 m	XW2Z-300EE		
		Cable length: 5 m	XW2Z-500EE		

Note: Each of NX-PG0232-5 and NX-PG0242-5 has one MIL connector. Therefore, one Connector-Terminal Block Conversion Unit is required. Each of NX-PG0332-5 and NX-PG0342-5 has two MIL connectors. Therefore, two Connector-Terminal Block Conversion Units are required.

Communications Interface Units

Unit type	Product name	Serial interface	External connection terminals	Number of serial ports	Communications function	Model	Standards
NX-series Communications Interface Unit	Communications Interface Unit	RS-232C	Screwless clamping			NX-CIF101	
		RS-422A/485	terminal block	I port	 No-protocol serial communications Serial line monitor 	NX-CIF105	UL, CE, RCM, KC
		RS-232C	D-Sub connector	2 ports		NX-CIF210	

IO-Link Master Unit

Unit type	Product name		Specification			
		Number of IO-Link ports	I/O refreshing method	I/O connection terminals	Model	Standards
	IO-Link Master Unit					
NX-series IO-Link Master Unit	I	4	Free-Run refreshing	Screwless clamping terminal block	NX-ILM400	UC1, CE, RCM, KC

Note: For details of IO-Link sensors and sensor I/O connectors, refer to the IO-Link Series Catalog (Cat. No. Y212).

System Units • Additional NX Unit Power Supply Unit

Unit type	Product name	Power supply voltage	capacity	Model	Standards
	Additional NX Unit Power Supply Unit				
NX-series System Unit		24 VDC (20.4 to 28.8 VDC)	10 W max.	NX-PD1000	UC1, N, L, CE, RCM, KC

Additional I/O Power Supply Units

Unit type	Product name	Power supply voltage	I/O power feed maximum current	Model	Standards
Additi Power NX-series System Unit	Additional I/O Power Supply Unit	5 to 24 VDC	4 A	NX-PF0630	UC1 N I
		(4.5 to 28.8 VDC)	10 A *	NX-PF0730	CE, RCM, KC

* Use the NX-PF0730 at 4 A or less on the CPU Rack where the NX1P2 CPU Unit is mounted.

• I/O Power Supply Connection Units

Unit type	Product name	Number of I/O power terminals	Current capacity of I/O power terminal	Model	Standards
NX-series System Unit	I/O Power Supply Connection Unit	IOG: 16 terminals	4 A/terminal max.	NX-PC0010	UC1, N, L, CE, RCM, KC
		IOV: 16 terminals	4 A/terminal max.	NX-PC0020	UC1, N, L, CE, RCM, KC
		IOV: 8 terminals IOG: 8 terminals	4 A/terminal max.	NX-PC0030	UC1, N, L, CE, RCM, KC

• Shield Connection Unit

Unit type	Product name	Number of shield terminals	Model	Standards
NX-series	Shield Connection	14 terminals	NX-TBX01	UC1, N, L,
System Unit	Unit	(The two lower terminals are functional ground terminals.)		CE, RCM, KC

Optional Products and Maintenance Products

Product name	Specification	Model	Standards
Unit/Terminal Block Coding Pins	For 10 Units (Terminal Block: 30 pins, Unit: 30 pins)	NX-AUX02	
End Cover	One End Cover is provided as a standard accessory with the Communication Coupler Unit.	NX-END01	
DIN Track Insulation Spacer	A Spacer to insulate the control panel from the DIN Track. To insulate the Slave Terminal from the control panel, use Din Track Insulation Spacers.	NX-AUX01	

				Standards			
Product name		No. of terminals Terminal number indications Ground terminal Term			Terminal current capacity	Model	
		8	A/B			NX-TBA082	- - - - - -
		12	A/B			NX-TBA122	
		16	A/B	None		NX-TBA162	
	Terminal Block	12	C/D		10 A	NX-TBB122	
		16	C/D		1	NX-TBB162	
		8	A/B	Broyidad		NX-TBC082	
		16	A/B	FIUMUEU		NX-TBC162	

Ordering Information

Safety CPU Units

	Appearance	Specification							
Unit type		Maximum number of safety I/O points	Program capacity	Number of safety master connections	I/O refreshing method	Unit version	Model		
Safety CPU Unit		256 points	512 KB	32	Free-Run refreshing	Ver.1.1	NX-SL3300		
		1024 points	2048 KB	128	Free-Run refreshing	Ver.1.1	NX-SL3500		

Note: Connect the Safety CPU Unit to the NX1P2 CPU Unit via the EtherCAT Coupler Unit.

Safety Input Units

		Specification								
Unit type	Appearance	Number of safety input points	Number of test output points	Internal I/O common	Rated input voltage	OMRON special safety input devices	Number of safety slave connections	I/O refreshing method	Unit version	Model
Safety Input Unit		4 points	2 points	Sinking inputs (PNP)	24 VDC	Can be connected.	1	Free-Run refreshing	Ver.1.1	NX-SIH400
		8 points	2 points	Sinking inputs (PNP)	24 VDC	Cannot be connected.	1	Free-Run refreshing	Ver.1.0	NX-SID800

Note: Connect the Safety Input Unit to the NX1P2 CPU Unit via the EtherCAT Coupler Unit.

Safety Output Units

	Appearance	Specification								
Unit type		Number of safety output points	Internal I/O common	Maximum load current	Rated voltage	Number of safety slave connections	I/O refreshing method	Unit version	Model	
Safety Output Unit		2 points	Sourcing outputs (PNP)	2.0 A/point, 4.0 A/Unit at 40°C, and 2.5 A/Unit at 55°C The maximum load current depends on the installation orientation and ambient temperature.	24 VDC	1	Free-Run refreshing	Ver.1.0	NX-SOH200	
		4 points	Sourcing outputs (PNP)	0.5 A/point and 2.0 A/Unit	24 VDC	1	Free-Run refreshing	Ver.1.0	NX-SOD400	

Note: Connect the Safety Output Unit to the NX1P2 CPU Unit via the EtherCAT Coupler Unit.

Optional Products	•								
Product Name		Specification							
Unit/Terminal Block Coding Pins	For 10 Units (Terminal Block: 30 pins, U	^z or 10 Units Terminal Block: 30 pins, Unit: 30 pins)							
	Specification								
Product name	No. of terminals	Terminal number indications	Ground terminal mark	Terminal current capacity	Model				
Terminal Block	8	A/B	None	10 A	NX-TBA082				
тегтіпаї віоск	16	A/B	None	10 A	NX-TBA162				



OMRON AUTOMATION AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE México DF • 52.55.59.01.43.00 • 01-800-226-6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO · SALES OFFICE Apodaca, N.L. · 52.81.11.56.99.20 · 01-800-226-6766 · mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br **OMRON ARGENTINA • SALES OFFICE** Cono Sur • 54.11.4783.5300

OMRON CHILE • SALES OFFICE Santiago • 56.9.9917.3920

OTHER OMRON LATIN AMERICA SALES 54.11.4783.5300

OMRON EUROPE B.V. • Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. • +31 (0) 23 568 13 00 • www.industrial.omron.eu

Authorized Distributor:

Controllers & I/O

Machine Automation Controllers (MAC)
 Motion Controllers

Programmable Logic Controllers (PLC)
 Temperature Controllers
 Remote I/O

Robotics

Industrial Robots
 Mobile Robots

Operator Interfaces

• Human Machine Interface (HMI)

Motion & Drives

- Machine Automation Controllers (MAC)
 Motion Controllers
 Servo Systems
- Frequency Inverters

Vision, Measurement & Identification

Vision Sensors & Systems
 Measurement Sensors
 Auto Identification Systems

Sensing

- Photoelectric Sensors Fiber-Optic Sensors Proximity Sensors
- Rotary Encoders
 Ultrasonic Sensors

Safety

- Safety Light Curtains
 Safety Laser Scanners
 Programmable Safety Systems
- Safety Mats and Edges
 Safety Door Switches
 Emergency Stop Devices
- Safety Switches & Operator Controls Safety Monitoring/Force-guided Relays

Control Components

- Power Supplies
 Timers
 Counters
 Programmable Relays
- Digital Panel Meters
 Monitoring Products

Switches & Relays

- Limit Switches Pushbutton Switches Electromechanical Relays
- Solid State Relays

Software

Programming & Configuration • Runtime

© 2017 Omron. All Rights Reserved.

Printed in U.S.A.