

SPECIFICATION

FOR

EUROPEAN POWER SUPPLY CORDSET (PB FR)

CORD : H05VV-F 3X1.00mm² PVC LEAD FREE

CUSTOMER : VPE/RS COMPONENTS

CUSTOMER'S PART No. : 8188903

VOLEX'S SPEC. REF. No. : 144310/2

ISSUE No. : 003

DATE : 28TH JULY 2014

CUSTOMER APPROVED :

APPROVED BY :	
SIGNATURE :	
APPROVED DATE :	
No. OF PAGES :	



Volex (Asia) Pte Ltd





35 Tampines St. 92

Singapore 528880

Tel : (65) 6788 7833

Fax : (65) 6788 7822

2500±75



APPROVED SOURCE FOR CABLE

1. BAO HING(SHENZHEN).
2. TA HING(SHENZHEN).

NOTE :

1. ALL DIMENSIONS IN mm.
2. THE CORD SHALL COMPLY WITH EN 50525-2-11.
3. THE MOLDED PLUG SHALL COMPLY WITH VARIOUS EUROPEAN COUNTRIES' CONFIGURATION (NATIONAL STANDARD) AND TESTED TO IEC 60884-1.
4. THE MOLDED CONNECTOR SHALL COMPLY WITH IEC 60320-1 OR EN 60320-1.
5. LABEL DETAILS : REFER TO LABEL DRAWING NO. : VL-0538.
6. THIS PART CAN BE MANUFACTURED AT ANY LOCATION WHICH HAS SAFETY APPROVAL.

S/N	DESCRIPTION	ITEM NUMBER	QTY
8	LABEL PP WARNING 50X20MM	6102941	1
7	PRINTED LABEL	VL-0538	1
6	BAG PE 150X300X0.05	904076	1
5	8" PE TIE BLK	6310062	1
4	IP60G NL7976B BLK	4100115	-
3	MOLDED DUO-CORD (10A 250V)	DUO-CORD	1
2	IP60G NL7976B BLK	4100115	-
1	MOLDED CONNECTOR V1625 (10A 250V)	V1625	2
	IP60G NL7976B BLK	4100115	-
	MOLDED PLUG M2511A (16A 250V)	M2511A	1
	H05W-F 3X1.00 BLK PVC LEAD FREE	1210365	3

TITLE :		EUROPEAN POWER SUPPLY CORDSET (PB FR)	SCALE : N.T.S.
CUSTOMER :		VPE/RS COMPONENTS	PAGE : 1/1
CUSTOMER PART NUMBER :		8188903	ISSUE
Reference Number :		144310/2 (HG07-169-14)	003
SALES :	QA :	ENGRG :	CHECKED BY :
Date :	Date :	Date :	DATE :
		20/7/14	30/07/14
			28/07/14
DRAWN BY :		CARRY HOU	
Reference Number :		144310/2 (HG07-169-14)	
Voilex (Asia) Pte Ltd <small>Confidential property of Voilex. Information contained herein shall not be disclosed to any third party without the written approval of an authorized official of Voilex Asia.</small>			


DRAWING NUMBER : L-0538
 REVISION : A

SPECIFICATION :

FACESTOCK MATERIAL	PP SYNTHETIC WITH PP COATING
FACESTOCK THICKNESS	50µm +/- 10%
FACESTOCK COLOUR	WHITE
FACESTOCK SURFACE FINISH	GLOSSY
ADHESIVE BASE	SOLVENT ACRYLIC
OPERATING TEMPERATURE	-20°C~+100°C
SHELF LIFE	1 YEAR
HF COMPLIANT	YES

NOTES :


- ALL DIMENSION IN MM.
- GENERAL TOLERANCE ±2MM, UNLESS OTHERWISE SPECIFIED.
- WHITE SURFACE WITH BLACK PRINT.
 FONT: ARIAL, 2.5MM HIGH.
- INK SHOULD NOT SMEAR AFTER PRINT.
- CRITICAL DIMENSIONS, WHERE Y IS IN NUMERICAL DIGITS.



Volvo (Asia) Pte Ltd
 Confidential Property of Volvo.
 Information contained herein shall
 not be disclosed to others,
 reproduced or used for any other
 purposes except as authorized in
 writing by an authorized official of
 Volvo Asia.

DRAWN : ALICE HUA	REV	IMM/ECR	BY	DATE	REV	IMM/ECR	BY	DATE	TITLE :	PP WARNING LABEL 50X20MM
RELEASED : 06/03/14	A	IMM	ALICE	06/03/14					ITEM NO.:	6102941-XXXX
CHECKED : <i>[Signature]</i>									SCALE :	1 : 1
APPROVED : <i>[Signature]</i>									PROJ. :	THIRD ANGLE
									FILENAME :	-\LABEL\PREPRINTED\L-0538
									PAGE :	1/1

DRAWING NUMBER : VL-0538
 REVISION : A



BARCODE: CODE 128A, SCAN SHOW CUSTOMER P/N

NOTES :-

1. ALL DIMENSION IN MM.
2. GENERAL TOLERANCE ±2MM, UNLESS OTHERWISE SPECIFIED.
3. YELLOW BACKGROUND WITH BLACK PRINT.
 FONT: ARIAL, 1.5mm. BUT 2mm FOR '1', 3mm AND ARIAL BOLD FOR P/N.
4. PRINTED MARKING SHALL BE DURABLE & LEGIBLE, SURFACE RUBBED WITH THUMB PRESSURE BACK & FORTH 10X, AND INK SHOULD NOT SMEAR.
5. PRINTER/RIBBON TYPE: TEC B-SX5 OR DATAMAX/905018 OR 905021.

S/N.	DESCRIPTION	ITEM NO.	REMARKS												
1	ART PAPER LABEL 45X25MM	6102940													
<table border="1"> <tr> <td colspan="2">TITLE: PE BAG LABEL</td> <td>PROJ.:</td> <td>PAGE:</td> </tr> <tr> <td>PRINT FILE:</td> <td>FILENAME:</td> <td>SCALE:</td> <td>THIRD ANGLE:</td> </tr> <tr> <td>VL0538A</td> <td>\\JABEL\WHOUSE-M\VL-0538</td> <td>2 : 1</td> <td>1/1</td> </tr> </table>				TITLE: PE BAG LABEL		PROJ.:	PAGE:	PRINT FILE:	FILENAME:	SCALE:	THIRD ANGLE:	VL0538A	\\JABEL\WHOUSE-M\VL-0538	2 : 1	1/1
TITLE: PE BAG LABEL		PROJ.:	PAGE:												
PRINT FILE:	FILENAME:	SCALE:	THIRD ANGLE:												
VL0538A	\\JABEL\WHOUSE-M\VL-0538	2 : 1	1/1												

Volex (Asia) Pte Ltd
 Confidential property of Volex.
 Information contained herein shall not be disclosed to others, reproduced or used for any other purpose except as authorized in writing by an authorized official of Volex Asia.

REV.	DESCRIPTION	DATE
I	REMOVE INSULATION COLOR 'BLUE, BROWN, BLACK'	01/09/06
	FM. REV. H PER HD STANDARD.	
J	CHANGE THE COMPLIANCE STANDARD	23/12/13
	PER SAFETY.	
	UPDATE FORMAT AS SHOWN.	

1. PVC FLEXIBLE CORD

1.1 SCOPE

This specification shall be in accordance with EN 50525-2-11. \triangle

1.2 CONSTRUCTION


CONDUCTOR	ANNEALED COPPER WIRE
INSULATION	PVC (BLUE, BROWN, GREEN&YELLOW)
JACKET	PVC

ITEM	UNIT	SPEC. VALUE	
TEMPERATURE RATING	°C	70	
RATED VOLTAGE	V	300/500	
NO. OF CORE	NO.	3	
CONDUCTOR NOMINAL AREA	mm ²	1.00	
MIN. AVE. THICKNESS OF INSULATION	mm	0.60	
MIN. THICKNESS AT ANY POINT OF INSULATION	mm	0.44	
MIN. AVE. THICKNESS OF JACKET	mm	0.80	
MIN. THICKNESS AT ANY POINT OF JACKET	mm	0.58	
OVERALL DIAMETER OF JACKET	mm	6.3~8.0	
DIELECTRIC-STRENGTH TEST IMMERSSED IN WATER, 20±5°C FOR MINIMUM 1HR	ON COMPLETED CABLE	—	2000 V FOR 15 MINS (MINIMUM)
	ON CORES	—	1500 V FOR 5 MINS (MINIMUM)
VOLTAGE TEST (D.C)	—	—	2000 V _{a.c} FOR 5 MINS (MINIMUM) OR 5000 V _{d.c} FOR 5 MINS (MINIMUM)
INSULATION RESISTANCE TEST (70°C)	MΩ km	> 0.01	
CONDUCTOR RESISTANCE TEST (20°C)	Ω /km	≤ 19.5	

TITLE : CABLE SPECIFICATION

EUROPEAN APPROVED POWER SUPPLY CABLE

H05VV-F 3X1.00mm²

SPEC NO. : CS-048EU	APPROVED BY :	CHECKED BY :	DRAWN BY :	REVISION :	 Confidential property of Volex. Information contained herein shall not be disclosed to others, reproduced or used for any other purpose except as authorized in writing by an authorized official of volex asia.
	DATE :	DATE :	DATE :	PAGE :	
	20/12/13	27/12/13	23/12/13	1/1	

REV.	DESCRIPTION	DATE
A	INITIAL RELEASE.	12/10/02
B	UPDATE MARKING DETAILS.	19/01/05
	UPDATE THE FORMAT AS SHOWN.	
	ADD IN '(EU/SAA/SAB/IEC)' ON THE TITLE.	

CABLE MARKING

BAO HING (SHENZHEN)

⚠ :- H05VV-F 3G1.0mm² <VDE> KEMA-KEUR +s+s+s
 <ÖVE> CEBC IEMMEQU SABS 1574 (S) (N) (D) (FI)
 BAOHING GTSA-3 N14586 **CE** LF

DRAWN	LI XF	19/01/05	FILENAME :	TITLE : CABLE MARKING (EU/SAA/SAB/IEC) ⚠
CHECK	<i>[Signature]</i>	19/01/05	CABLE MARKING/ BH/H05/H05VV-F 3X1.0 LF- BH	
APPR	<i>[Signature]</i>	19/01/05	B	
SCALE	N.T.S.	REV.	B	
REFERENCE :				Volex (Asia) Pte Ltd <small>Confidential property of Volex. Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of Volex Asia.</small>
H05VV-F 3X1.0mm ² LF				

REV.	DESCRIPTION	DATE
	ADD IN NEW MARKING PER ECN006-10.	
B	ADD IN NOTE 1.	26/07/10
C	REMOVE OLD MARKING PER ECR101239.	26/10/10

CABLE MARKING

△ TA HSING(SHENZHEN)

-- <VDE> KEMA-KEUR CEBEC IEMMEQU (D) (N) (S) (FI)

<öVE> +s+s+s NF-USE-1344 Q050104 H05VV-F 3G1.00mm²

TA HSING INDUSTRIES LTD. LF



DRAWN	WANGHUI	26/10/10	FILENAME :	TITLE : CABLE MARKING (EU/SAA/IEC)
CHECK	<i>hm</i>	<i>26/10/10</i>	CABLE MARKING	
APPR	<i>Wanghui</i>	<i>26/10/10</i>	/TH(SZ)/H05VV-F	
SCALE	N.T.S.	REV.	3X1.00 - LF	
REFERENCE :				<i>Volex (Asia) Pte Ltd</i>
H05VV-F 3X1.00mm ² LF				
<small>Confidential property of Volex. Information contained herein shall not be disclosed to others. reproduced or used for any other purposes except as authorized in writing by an authorized official of volex asia.</small>				

2. PLUG

REV	DESCRIPTION	DATE
	CHANGE 'TEST RESULT' TO 'ACCEPTANCE CRITERIA'.	
	CHANGE FORMAT AS SHOWN.	
W	ADD IN CATALOGUE 'PH16HA3'.	08/04/13
X	ADD IN CATALOGUE 'APEU16CS3 & APEU16CS3G'.	11/04/13

2.1. SCOPE

The plug shall be in accordance with various European countries' configuration (national standard) and tested to IEC 60884-1 "Plugs and socket-outlets for household and similar purposes - Part 1: General requirements.

2.2. CONSTRUCTION

The plug construction shall comply with our catalogue No: M3204, EUH16S2, MP2210 EUC6, M2511, M2511A, EU10SC3, EU16VS2, EU16VJS2, EU16CS3, PH16CS3, PH16HA3, EU16CA3, EU16DS2, EU16DJS2, EU16JS2, VPEU16S3, GPEU16S3, VPEU16S2, DS16CS2, APEU16S3, APEU16BS3G, DS16ES2, *APEU16CS3* & *APEU16CS3G*.

2.3. CHARACTERISTICS

NO.	TEST ITEM	DESCRIPTION	ACCEPTANCE CRITERIA
1.	Moisture resistance test	Samples are kept in a humidity cabinet containing air with a relative humidity between 91 to 95% and a temperature of 20°C-30°C for a duration of 48 hours.	No damage
2.	Electric strength test	A voltage of A.C 2000V with a trip current of min. 100mA is applied for 1 min after the moisture resistance test.	No flashover and breakdown
3.	Insulation resistance test	This test is measured after 1 min. application of D.C 500V after the moisture resistance test.	Min. 5 M Ohm
4	Pressure test	The plug is pressed with a force of 150N for 5 minutes.	The plug shall not have been deformed.
5.	Temperature rise test	An alternating current of 10A (0.75mm ²), 12A (1mm ²) or 16A (1.5mm ²) is passed through poles for 1 hour.	The temperature rise at any points shall not exceed 45°C.
6.	Bending test	The sample shall be loaded with a weight of 10N for 0.75mm ² or 20N for 1.00mm ² and bigger and the oscillating member shall be moved backward and forward through an angle of 90° (45° on either side of the vertical) the number of flexing being 10,000. A current of 10A (0.75mm ²) or 16A (1.0mm ² and above) is passed through the conductors.	No damage and the voltage drop shall not exceed 10mV.
7	Pin pull test	A pull force of 50N is applied on the pins (in turn) after the plug has been aged for 1 hour at 70°C.	The displacement of the pin shall not be more than 1 mm.

DRAWN:	MAYING	11/04/13	TITLE : EUROPEAN PLUG (IEC 60884-1)
CHECK:	<i>hromgth</i>	11/04/13	
APPR:	<i>hromgth</i>	11/04/13	
REV:	X		
REFERENCE:			<i>Voalex (Asia) Pte Ltd</i>
			<small>Confidential property of Voalex. Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of voalex asia.</small>

NO.	TEST ITEM	DESCRIPTION	ACCEPTANCE CRITERIA
8	Tumbling test	The samples are dropped from a height of 50cm onto a steel plate (3mm thick) for a total of 1000 times. A torque of 0.4Nm is applied in one direction for 1 min. first then follow by the other direction for another min. on the pins.	No damage and the pins shall not turn.
9	Cold impact test	The samples are kept in a refrigerator at a temperature of - 15±2°C for at least 16 hours. The samples are then allowed to fall by the hammer (1000g) from a height of 10cm.	No damage
10	Heat deformation test	The samples are kept for 1 hour in a heating cabinet at temperature of 100±5°C.	No damage
11	Heat pressure test	The samples are applied 20N (2.04kg) at a temperature of 80±2°C for 1 hour.	No damage
12	Ageing test	The samples are kept for 168 hours in a heating cabinet at temperature of 70±2°C.	No damage
13	Pressure test II	The samples are applied 300N (30.6kg) at a temperature of 20±2°C for 1 min.	No damage
14	Cord-anchorage test	The cord is subjected to pulls of 50N (2.5A) or 60N (10/16A) force 100 times without jerk each lasting 1 sec. Thereafter the cord is subjected to a torque of 0.15Nm (2 core 0.75mm ²) or 0.25Nm (others) for 1 min.	The cord shall not be damaged and shall not been displaced by more than 2mm.
15	Ball pressure test	A steel ball of 5mm in diameter is applied with 20N force on the sample at a temperature of 125±5°C for 1 hour on the insert.. The sample is than cooled by cold water.	The diameter of the impression shall not exceed 2mm.
16	Glow wire test	The tip of the glow wire heated electrically to 750±10°C shall be applied at the portion between the current-carrying pins and for a period of 30s. For all other parts, the wire is heated to 650±10°C.	Any flame and glowing shall extinguish within 30s after the removal of the glow-wire. There shall be no ignition of the tissue papernor sorching of the board.

DRAWN:	MAYING	11/04/13	TITLE : EUROPEAN PLUG (IEC 60884-1)
CHECK:	<i>[Signature]</i>	11/04/13	
APPR:	<i>[Signature]</i>	11/4/13	
REV:	X		
REFERENCE:			<i>Volex (Asia) Pte Ltd</i>
			<small>Confidential property of Volex. Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of volex asia.</small>

3. CONNECTOR

REV	DESCRIPTION	DATE
	CHANGE 'TEST RESULT' TO 'ACCEPTANCE CRITERIA'	
AP	CHANGE FORMAT AS SHOWN.	11/03/14
AQ	ADD IN CATALOGUE NO. VAC17KS.	24/02/14

3.1. SCOPE

The connector shall be in accordance with IEC 60320-1 or EN 60320-1, Test specification - appliance couplers.

3.2. CONSTRUCTION

The connector construction shall comply with our catalogue No: VAC5S, APC5A, APC5S, APC5M, VAC5AR, APC5SM, DLC5A3, V1625, V1625A, VAC19, VAC17S, VSCC13, AVLC13, APC13, APC13S, VSC19, V1625LA, VAC19A, VSCC15, APC5SP, APC13F, V1625BS, APC13G, VAC13A, VAC13S, PIC17S, VIC13A, DLC5U3, VAC13KS, SOC5S, V1625H, VAC19KS, DLC5E3, HPC13A, V1625AT, VAC17A, APC5SF, VCC13, VCC5S, APC13H, VCC17S, VAC19H, APC13FH, APC13HC & VAC17KS "All connectors complying to Standard Sheet C5, C13, C15, C15A, C17 and C19"

3.3. CHARACTERISTICS

NO.	TEST ITEM	DESCRIPTION	ACCEPTANCE CRITERIA
1.	Moisture resistance test	Samples are kept in a humidity cabinet containing air with a relative humidity between 91 to 95% and a temperature of 20°C-30°C for a duration of 48 hours.	No damage
2.	Electric strength test	Voltages of 3000V±60V and 1500V±60V, with min. trip current of 100mA is applied for 60s±5s between current-carrying contacts and body and between each contacts respectively after the moisture resistance tests.	No flashover and breakdown
3.	Insulation resistance test	This test is measured with a D.C 500V after the moisture resistance test. Readings are taken after 60s ± 5s of application of voltage.	Min. 5 M Ohm
4.	Withdrawal force test	<p>i) Min. 1.5N (2N for 16A) - A single pin made to the minimum dimension is inserted into the connector. The pin, together with the weight should exert a force of 1.5N (2N for 16A connector). Each individual pole of the connector is tested separately.</p> <p>ii) Max. 50N (60N for 16A) - Insert and withdraw the connector from a socket having pin dimension to the maximum and shroud dimension to the minimum for 10 times. The connector is then inserted again into the socket hang with a total weight of 50N(60N for 16A). The weight consist of a principal weight which is 90% of the total weight and a supplementary weight of 10%.</p> <p>The test is repeated for hot connector with temperature of 120°C±2°C on the pins.</p>	<p>i) The pin with the weight should not be withdrawn from the connector for more than 3 seconds.</p> <p>ii) The connector shall be withdrawn from the socket. If not the supplementary weight is lifted from a height of 5cm and drop. The connector must be withdrawn.</p> <p>The test is repeated after temperature rise test.</p>

DRAWN:	MOLLY	24/02/14	TITLE: EUROPEAN & BRITISH APPLIANCE COUPLERS
CHECK:	<i>[Signature]</i>	24/02/14	
APPR:	<i>[Signature]</i>	24/2/14	
REV:	AQ		
REFERENCE:			Volex (Asia) Pte Ltd
			<small>Confidential property of Volex. Information contained herein shall not be disclosed to others. reproduced or used for any other purposes except as authorized in writing by an authorized official of volex asia.</small>



NO.	TEST ITEM	DESCRIPTION	ACCEPTANCE CRITERIA
5.	Glow wire test	Glow wire is applied for 30s with temperature of 750°C on inserts and housings retaining contacts and 650°C on elsewhere.	Flame (if any) shall be self-extinguished within 30s. upon the removal of the glow wire and molten droplets shall not ignite paper.
6.	Bending test	The sample shall be loaded with a weight of 10N for 0.75mm ² or 20N for 1.00mm ² or bigger and the oscillating member shall be moved backward and forward through an angle of 90°(45° on either side of the vertical) the number of flexing being 20,000. A rated current is applied. For round cord, the sample is turned 90 degree around the axis of cable after 10,000 cycles. The flexing is further completed in this axis. Flat cable is flexed only along the bigger axis of the cable.	There shall be no complete breakage of any of the conductor. Broken conductor shall not have pierced the insulation.
7.	Tumbling test	The sample is dropped from a height of 50cm onto a steel plate(3mm thick) for a total of 500 times.	No damage to impair further use of connector.
8.	Breaking capacity test	The connector is connected and disconnected 50 times (100 strokes) with the inlet at a rate of 30 strokes per minute with 275V and 1.25 times of rated current.	No flashover or sustained arcing during the test and no damage to impair further use of connector.
9.	Normal operation test	Test is similar to breaking capacity except that the test voltage is 250V with the connector connected and disconnected with the inlet for 1000 times (2000 strokes) with rated current and 3000 times (6000 strokes) without current.	Withstand electric strength at 1500V for 1 min, and show no damage.
10.	Temperature rise test	An alternating current at 1.25 times rated current is passed through the current carrying contacts for 1 hour. This is repeated for connector with earth contact passing current between earth and each of the current carrying contacts.	The temperature rise shall not exceed 45K.
11.	Cord-anchorage test	The cord is subjected to pulls of 50N(2.5A) or 60N(others) for 100 times each time for 1 sec. without jerk. Thereafter the cord is subjected for 1 min. to a torque of 0.15Nm(0.75mm ²) or 0.25Nm(others).	The cord shall not be damaged and shall not be displaced by more than 2mm.
12.	Heat deformation test	Samples are kept for 1 hour in a heating cabinet at temperature of 100±2°C.	No damage to impair further use of connector.
13.	Heat pressure test	A pressure of 20N is applied at a temperature of 100°C ± 2°C for 1 hour.	No damage to impair further use of connector.

DRAWN:	MOLLY	24/02/14	TITLE: EUROPEAN & BRITISH APPLIANCE COUPLERS
CHECK:	<i>honda</i>	24/02/14	
APPR:	<i>Huy</i>	24/2/14	
REV:	AO		
REFERENCE:			<i>Voilex (Asia) Pte Ltd</i>
			<small>Confidential property of Voilex. Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of voilex asia.</small>

NO.	TEST ITEM	DESCRIPTION	ACCEPTANCE CRITERIA
14.	Aging test	The samples are kept for 168 hours in a heating cabinet at a temperature of 80±2°C.	No damage & marking shall be legible.
15.	Ball pressure test	A ball of 5mm in diameter is applied on the connector with the following temperature with 20N force for 1 hour. i) 125°C for hot connectors. ii) 125°C for parts retaining current carrying parts and earth circuit. iii) 75°C for other parts for cold connector. The connector is then cooled down to room temperature with cold water.	The diameter of the impression shall not exceed 2mm.

DRAWN:	MOLLY	24/02/14	TITLE: EUROPEAN & BRITISH APPLIANCE COUPLERS
CHECK:	<i>honey</i>	24/02/14	
APPR:	<i>Huy</i>	24/2/14	
REV:	AQ		
REFERENCE:			<i>Volet (Asia) Pte Ltd</i>
			<small>Confidential property of Volet. Information contained herein shall not be disclosed to others. reproduced or used for any other purposes except as authorized in writing by an authorized official of volet asia.</small>

REV.	DESCRIPTION	DATE
J	UPDATE FORMAT AS SHOWN. REMOVE THE CLOSED FACTORY FROM MANUFACTURE MARK.	03/11/06
K	REMOVE THE CLOSED FACTORY FROM MANU. LOCATION MARK.	20/07/09



MARKING DETAILS

DRAWN		LI	X/A	20/07/09	FILE NAME :	TITLE :	
X	HENG GANG (CHINA)	hengkang			A-PLUG/EURO	MOLDED PLUG	
X	ZHONGSHAN (CHINA)	Wang			/GENERAL/	M2511A	
X	HANOI (VIETNAM)				M2511A-EURO		
X	BATAM (INDONESIA)				N.T.S.		
X	CHENNAI (INDIA)						
MANUFACTURE LOCATION MARK		REFERENCE :		EUROPEAN APPROVAL		Volex (Asia) Pte Ltd	
(* X * IS APPLICABLE ONLY)						Confidential property of Volex.	



NOTES :

- 1.) ALL DIMENSIONS IN mm.
- 2.) X - CAVITY NO. (OPTIONAL)
- 3.) XXX - MANUFACTURING LOCATION.



Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of Volex Asia.

REV.	DESCRIPTION	DATE
	REMOVE THE CLOSED FACTORY FM. MANU. LOCATION MARK.	
F	UPDATE THE DIM. AS SHOWN.	27/07/09
G	ADD IN MANU. LOCATION MARK 'SMI'.	26/02/10



MARKING DETAILS :

NOTES :

- 1.) ALL DIMENSIONS IN mm
- 2.) XXX MAX. - CURRENT RATING. (REFER TO TABLE)
- 3.) XXX - MANUFACTURING LOCATION.

TABLE :

CURRENT (XXX MAX.)	7A	10A	13A
			✓

HG	HENG GANG (CHINA)	X	DRAWN	HONGYAN	26/02/10	FILE NAME :	TITLE :	
SM1/SMI	ZHONGSHAN (CHINA)	X	CHECK	hongyan	02/03/10	A-PLUG/ NON-APPROVAL/ GENERAL/DUO-CORD	DUO-CORD	
VH	HANOI (VIETNAM)	X	APPR	WPT	2/3/10	N.T.S.		
B	BATAM (INDONESIA)	X	REV.	G	SCALE			
VC	CHENNAI (INDIA)	X	REFERENCE :					
MANUFACTURE LOCATION MARK			NON APPROVAL					
(' X ' IS APPLICABLE ONLY)			Volex (Asia) Pte Ltd					

Confidential property of Volex.
Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of volex.asia.