

HDO4000 High Definition Oscilloscopes

200 MHz - 1 GHz



Key Features

- 12-bit ADC resolution, up to
 15-bit with enhanced resolution
- 200 MHz, 350 MHz, 500 MHz,
 1 GHz bandwidths
- Long Memory up to 50 Mpts
- 12.1" touch screen display
- Multi-language User Interface
- WaveScan Search and Find
- LabNotebook Documentation and Report Generation
- History Mode
- Spectrum Analyzer Mode
- Power Analysis Software
- Serial Data Trigger and Decode
- 16 Digital Channels with 1.25 GS/s
 - Analog and Digital
 Cross-Pattern Triggering
 - Digital Pattern Search and Find
 - Analog and Digital Timing
 Measurements
 - Activity Indicators

Combining Teledyne LeCroy's HD4096 high definition technology, with long memory, a compact form factor, 12.1" wide touch screen display, powerful debug tools, and mixed signal capability, the HDO4000 is the ideal oscilloscope for precise measurements and quick debug. Tools such as WaveScan Search and Find, LabNotebook Report Generator, and History Mode help identify and isolate problems for faster troubleshooting.

HD4096 Technology

HD4096 high definition technology consists of high sample rate 12-bit ADCs, high signal-to-noise input amplifiers and a low-noise system architecture. This technology enables high definition oscilloscopes to capture and display signals of up to 1 GHz with high sample rate and 16 times more resolution than other oscilloscopes.

Long Memory

With up to 50 Mpts of memory the HDO4000 High Definition Oscilloscopes can capture large amounts of data with more precision than other oscilloscopes. The 2.5 GS/s, 50 Mpts architecture provides the ability to capture a fast transient or a long acquisition.


Large 12.1" Touch Screen

Navigating complicated user interfaces is a thing of the past thanks to the large touch screen display of the HDO4000. The user interface was designed for touch screens which makes navigating the HDO4000 extremely intuitive. Every aspect of the interface is touchable making channel, timebase and trigger settings only one touch away.

Compact Form Factor

The HDO4000 builds upon Teledyne LeCroy's history of "Large Screen, Small Footprint" with its 12.1" wide touch screen display and 5" depth. Additionally, the innovative rotating, tilting feet enable the HDO4000 to be placed in 4 different viewing positions ensuring optimal viewing no matter where it is being positioned in the lab.

HD4096 HIGH DEFINITION TECHNOLOGY



HD4096 high definition technology consists of high sample rate 12-bit ADCs, high signal-to-noise ratio amplifiers and a low-noise system architecture. This technology enables high definition oscilloscopes to capture and display signals of up to 1 GHz with high sample rate and 16 times more resolution than other oscilloscopes.

Oscilloscopes with HD4096 technology have higher resolution and measurement precision than 8-bit alternatives. The high sample rate 12-bit ADCs provide high resolution sampling at up to 2.5 GS/s. The high performance input amplifiers deliver phenomenal signal fidelity with a 55 dB signal-to-noise ratio and provide a pristine signal to the ADC to be digitized. The low-noise signal architecture ensures that nothing interferes with the captured signal and the oscilloscope displays a waveform that accurately represents the signals from the device under test.



16x More Resolution

12-bits of vertical resolution provides sixteen times more resolution than 8-bits. The 4096 discrete levels reduce the quantization error. Signals captured with lower resolution oscilloscopes have a higher level of quantization error resulting in less accurate waveforms on the display. Signals captured on an oscilloscope with 12-bit HD4096 technology are accurately displayed with minimal quantization error.

DEBUG IN HIGH DEFINITION WITH HD4096



Oscilloscopes with HD4096 have a variety of benefits that allow the user to debug in high definition. Waveforms displayed by high definition oscilloscopes are cleaner and crisper. More signal details can be seen and measured; these measurements are made with unmatched precision resulting in better test results and shorter debug time.

Clean, Crisp Waveforms

When compared to waveforms captured and displayed by 8-bit oscilloscopes, waveforms captured with HD4096 technology are dramatically crisper and cleaner. Oscilloscopes with HD4096 acquire waveforms at high resolution, high sample rate and low noise to display the most accurate waveforms.

More Signal Details

Signal details often lost in the noise are clearly visible and easy to distinguish when captured on oscilloscopes with HD4096. Details which were previously difficult to even see can now be easily seen and measured. Using the oscilloscope zoom capabilities gives an even closer look at the details for unparalleled insight to the signals on screen.

Unmatched Measurement Precision

Precise measurements are critical for effective debug and analysis. HD4096 enables oscilloscopes to deliver unmatched measurement precision to improve testing capabilities and provide better results.



- Clean, Crisp Waveforms | Thin traces show the actual waveform with minimal noise interference
- **More Signal Details** | Waveform details lost on an 8-bit oscilloscope can now be clearly seen
- C Unmatched Measurement Precision | Measurements are more precise and not affected by quantization noise

HDO4000 - HIGH DEFINITION OSCILLOSCOPE



HDO4000 High Definition Oscilloscopes combine Teledyne LeCroy's HD4096 high definition technology with long memory, powerful debug tools and mixed signal capability in a compact form factor with a 12.1" touch screen display.

- 1. Only 13 cm (5") Deep The most space-efficient oscilloscope for your bench from 200 MHz to 1 GHz
- 2. 12.1" Widescreen (16 x 9) high resolution WXGA color touch screen display. The most time-efficient user interface is even easier to use with a built-in stylus
- Local language user interface Select from 10 language preferences. Add a front panel overlay with your local language
- "Push" Knobs All knobs have push functionality that provides shortcuts to common actions such as Set to Variable, Find Trigger Level, Zero Offset, and Zero Delay
- **5.** Waveform Control Knobs Control channel, zoom, math and memory traces with the multiplexed vertical and horizontal knobs









- **6.** Dedicated Cursor Knob Select type of cursor, position them on your signal, and read values without ever opening a menu
- **7.** Dedicated buttons to quickly access popular debug tools.
- **8.** Easy connectivity with two convenient USB ports on the front, two on the side
- **9.** Mixed Signal Capability Debug complex embedded designs with integrated 16 channel mixed signal capability
- **10.** Rotating and Tilting Feet provide 4 different viewing positions
- **11.** Auxiliary Output and Reference Clock Input/Output connectors for connecting to other equipment
- **12.** USBTMC (Test and Measurement Class) port simplifies programming



Document and Share:

- Quickly save all files with LabNotebook
- Create custom reports with LabNotebook
- · Save to internal hard disk or network drive
- Print to a USB printer
- Save to USB memory stick
- · Connect with LAN or GPIB
- View data on a PC with free WaveStudio utility

POWERFUL MIXED SIGNAL CAPABILITIES



Teledyne LeCroy's HDO4000-MS High Definition mixed signal oscilloscope combines the high definition analog channels of the HDO4000 with the flexibility of 16 digital inputs. In addition, the many triggering and decoding options turn the HDO4000-MS into an all-in-one analog, digital, serial debug machine.

High-performance 16 Channel Mixed Signal Capability

With embedded systems growing more complex, powerful mixed signal debug capabilities are an essential part of modern oscilloscopes. The 16 integrated digital channels and set of tools designed to view, measure and analyze analog and digital signals enable fast debugging of mixed signal designs.

Extensive Triggering

Flexible analog and digital cross-pattern triggering across all 20 channels provides the ability to quickly identify and isolate problems in an embedded system. Event triggering can be configured to arm on an analog signal and trigger on a digital pattern.

Advanced Digital Debug Tools

Using the powerful parallel pattern search capability of WaveScan, patterns across many digital lines can be isolated and analyzed. Identified patterns are presented in a table with timestamp information and enables quick searching for each pattern occurrence.

Use a variety of many timing parameters to measure and analyze the characteristics of digital busses.


Powerful tools like trends, statistics and histicons provide additional insight and help find anomalies.

Quickly see the state of all the digital lines at the same time using convenient activity indicators.



SERIAL TRIGGER AND DECODE OPTIONS





View decoded protocol information on top of physical layer waveforms and trigger on protocol specific messages.

Trigger and Decode

The serial data trigger will quickly isolate events on a bus eliminating the need to set manual triggers and hoping to catch the right information. Trigger conditions can be entered in binary or hexadecimal formats and conditional trigger capabilities even allow triggering on a range of different events.

Protocol decoding is shown directly on the waveform with an intuitive, color-coded overlay and presented in binary, hex or ASCII. Decoding on the HDO4000 is fast even with long memory and zooming in to the waveform shows precise byte by byte decoding.

Table and Search

To further simplify the debug process all decoded data can be displayed in a table below the waveform grid. Selecting an entry in the table with the touch screen will display just that event. Additionally, built-in search functionality will find specific decoded values.

Serial data messages can be quickly located by searching on address, data and other attributes specific to a particular protocol. Once found, the specific location containing the specified search criteria can be automatically zoomed to.

Supported Serial Data Protocols


- I²C, SPI, UART
- CAN, LIN, FlexRay[™], SENT
- Ethernet 10/100BaseT,
 USB 1.0/1.1/2.0, USB 2.0-HSIC
- Audio (I²S, LJ, RJ, TDM)
- MIL-STD-1553, ARINC 429
- MIPI D-PHY, DigRF 3G, DigRF v4
- Manchester, NRZ


IDENTIFY AND ISOLATE PROBLEMS FASTER



Touch Screen Simplicity

Configuring the HDO4000 is simple thanks to the intuitive touch screen user interface. Everything on the screen is interactive. To adjust channel, timebase, or trigger settings, simply touch the associated descriptor box and the appropriate menu is opened. Measurements can be touched to adjust their settings and cursors can be positioned precisely by touching and dragging them to the proper location. A box can be drawn around a portion of a waveform to create a zoom. Even waveform offset and delay can be adjusted by touching and dragging the waveform.






WaveScan Advanced Search

WaveScan provides powerful isolation capabilities that hardware triggers can't provide. WaveScan allows searching analog, digital or parallel bus signal in a single acquisition using more than 20 different criteria. Or, set up a scan condition and scan for an event over hours or even days.



Advanced Math and Measure

With many math functions and measurement parameters available, the HDO4000 can measure and analyze every aspect of analog and digital waveforms. By utilizing HD4096 technology, the HDO4000 measures 16 times more precisely than traditional 8-bit architectures. Additionally, the HDO4000 provides statistics, histicons and trends to show how waveforms change over time.




Advanced Waveform Capture with Sequence Mode

Use Sequence mode to store up to 10,000 triggered events as segments. This is ideal when capturing fast pulses in quick succession or when capturing events separated by long time periods. Each segment has a timestamp and dead-time between triggers is less than 1 µs. Isolate rate events over time by combining with advanced triggers.



History Mode Waveform Playback


Scroll back in time using History Mode to view previous waveforms and isolate anomalies. Use cursors and measurement parameters to quickly find the source of problems. History mode is always available with a single button press, no need to enable this mode and never miss a waveform.



LabNotebook

communicate important results.

The LabNotebook feature of HDO4000 provides a report generation tool to save and document all your work. Saving all displayed waveforms, relevant settings, and screen images is all done through LabNotebook, eliminating the need to navigate multiple menus to save all these files independently.



waveforms, settings, and screen images.

LabNotebook in a

single button press.


by using the Flashback capability.

SPECTRUM ANALYZER MODE



Key Features

- Spectrum analyzer style controls for the oscilloscope
- Select from six vertical scales
- Automatically identify frequency peaks
- Display up to 20 markers, with interactive table readout of frequencies and levels
- Easily make measurements with reference and delta markers
- Automatically identify and mark fundamental frequency and harmonics
- Spectrogram shows how spectra changes over time in 2D or 3D views



Simplify Analysis of FFT Power Spectrum

Get better insight to the frequency content of any signal with use of the Spectrum Analyzer mode on the HDO4000. This mode provides a spectrum analyzer style user interface with controls for start/stop frequency or center frequency and span. The resolution bandwidth is automatically set for best analysis or can be manually selected. Vertical Scale can be selected as dBm, dBV, dBmV, dBuV, Vrms or Arms for proper viewing and analysis while the unique peak search automatically labels spectral components and presents frequency and level in an interactive table. Utilize up to 20 markers to automatically identify harmonics and quickly analyze frequency content by making measurements between reference and delta markers. To monitor how the spectrum changes over time, view the spectrogram which can display a 2D or 3D history of the fequency content.



Spectrum analyzer style controls simplify waveform analysis in the frequency domain.

POWER ANALYZER OPTION





Key Features

- Automatic switching device measurements
- Color coded overlay to identify power losses
- Control loop and time domain response analysis
- Line power and harmonics tests to IEC 61000-3-2
- Total harmonic distortion table shows frequency contribution
- B-H Curve shows magnetic device saturation

Power Analyzer Automates Switching Device Loss Measurements


Quickly measure and analyze the operating characteristics of power conversion devices and circuits with the Power Analyzer option. Critical power switching device measurements, control loop modulation analysis, and line power harmonic testing are all simplified with a dedicated user interface and automatic measurements. Areas of turn-on, turn-off, and conduction loss are all identified with color-coded waveform overlays for faster analysis.

Power Analyzer provides quick and easy setup of voltage and current inputs and makes measurements as simple as the push of a button. Tools are provided to help reduce sources of measurement errors and the measurement parameters provide details of single cycle or average device power losses.

Beyond the advanced power loss measurement capabilities,

the Power Analyzer modulation analysis

capabilities provide insight to understand control loop response to critical events such as a power supply's soft start performance or step response to line and load changes. The Line Power Analysis tool allows simple and quick pre-compliance testing to EN 61000-3-2.



Teledyne LeCroy has a variety of probes and probing accessories such as high common mode rejection ratio (CMRR) differential amplifiers, differential probes, current probes, and deskew fixtures.

PROBES



The right probe is an essential tool for accurate signal capture and Teledyne LeCroy offers an extensive range of probes to meet virtually every probing need.

ZS Series High Impedance Active Probes

ZS2500, ZS1500, ZS1000, ZS2500-QUADPAK, ZS1500-QUADPAK, ZS1000-QUADPAK



The ZS Series probes provide high impedance and an extensive set of probe tips and ground accessories to handle a wide range of probing scenarios. The high 1 $M\Omega$ input resistance and low 0.9 pF input capacitance mean this probe is ideal for all frequencies. The ZS Series probes provide full system bandwidth for all Teledyne LeCroy oscilloscopes having bandwidths of 1 GHz and lower.

Differential Probes(200 MHz – 1.5 GHz) ZD1500, ZD1000, ZD500, ZD200



High bandwidth, excellent common-mode rejection ratio (CMRR) and low noise make these active differential probes ideal for applications such as automotive development (e.g. FlexRay) and failure analysis, as well as wireless and data communication design. The ProBus interface allows sensitivity, offset and common-mode range to be displayed on the oscilloscope screen.

High Voltage Differential Probes ADP305, ADP300, AP031



Low cost active differential probes are intended for measuring higher voltages. The differential techniques employed permit measurements to be taken at two points in a circuit without reference to the ground, allowing the oscilloscope to be safely grounded without the use of opto-isolators or isolating transformers.

High Voltage Passive Probes PPE1.2KV, PPE2KV, PPE4KV, PPE5KV, PPE6KV



The PPE Series includes five fixed-attenuation probes covering a range from 2 kV to 20 kV, and one switchable probe providing ÷10/÷100 attenuation for voltage inputs up to 1.2 kV. All fixed-attenuation, standard probes automatically rescale compatible Teledyne LeCroy oscilloscopes for the appropriate attenuation of the probe.

Current Probes

CP031, CP030, AP015, CP150, CP500, DCS015



Available current probes reach bandwidths of 100 MHz, peak currents of 700 A and sensitivities of 10 mA/div. Use multiple current probes to make measurements on three-phase systems or a single current probe with a voltage probe to make instantaneous power measurements. Teledyne LeCroy current probes enable the design and testing of switching power supplies, motor drives, electric vehicles, and uninterruptible power supplies.

SPECIFICATIONS



	HD04022 HD04022-MS	HD04024 HD04024-MS	HD04032 HD04032-MS	HD04034 HD04034-MS	HD04054 HD04054-MS	HD04104 HD04104-MS		
Analog - Vertical								
Bandwidth (@ 50Ω)	200	MHz	350	MHz	500 MHz	1 GHz		
Rise time	1.75 ns	typical	1 ns	typical	700 ps typical	450 ps typical		
Input Channels	2	4	2	4	4	4		
Vertical Resolution	12-bits; up to 15-bit	ts with enhanced res	olution (ERES)					
Sensitivity	50 Ω: 1mV/div - 1 V/div; 1 MΩ: 1 mV/div - 10 V/div							
DC Gain Accuracy	±(0.5%) Full Scale, offset at 0 V							
BW Limit	20 MHz, 200 MHz							
Maximum Input Voltage	50 Ω: 5 Vrms; 1 MΩ: 400 V max (DC + Peak AC ≤ 10 kHz)							
Input Coupling	50 Ω: DC, GND; 1 MΩ: AC, DC, GND							
Input Impedance	50 Ω ±2.0%, 1 MΩ ±2.0% 15 pF							
Offset Range	50 Ω : 1 mV - 4.95 mV: ± 1.6 V, 5 mV - 9.9 mV: ± 4 V, 10 mV - 19.8 mV: ± 8 V, 20 mV - 1 V: ± 10 V 1 M Ω : 1 mV - 4.95 mV: ± 1.6 V, 5 mV - 9.9 mV: ± 4 V, 10 mV - 19.8 mV: ± 8 V, 20 mV - 100 mV: ± 16 V, 100 mV - 102 mV - 198 mV: ± 8 V, 20 mV - 100 mV: ± 160 V; ± 160 V, 1.02 V -10 V: ± 400 V							
Offset Accuracy	±(1.0% of offset value	±(1.0% of offset value + 0.5%FS + 0.02% of max offset + 1 mV)						
Analog - Acquisition								
Sample Rate (Single-shot)	2.5 GS/s							
Sample Rate (Repetitive)	125 GS/s	125 GS/s						
Record Length	Standard -STD: 12.	5 Mpts/ch (all chann	els) 25 Mpts (interle	aved)				
		Optional -L: 25 Mpts/ch (all channels), 50 Mpts (interleaved)						
Acquisition Modes	Real Time, Roll, RIS (Random Interleaved Sampling),							
Timebase Range	Sequence (Segmented Memory up to 10,000 segments with 1µs intersegment time) 200 ps/div - 1.25 ks/div with standard memory (up to 2.5 ks/div with -L memory);							
Time also a constant	RIS available at ≤ 10) ns/div; Roll Mode a	vailable at ≥ 100 ms	/div and ≤ 5 MS/s				
Timebase Accuracy	±2.5 ppm for 5 to 4t	OC + 1.0 ppm/year fro	om calibration					
Digital - Vertical and Acquis	sition (-MS Models	Only)						
Input Channels	16 Digital Channels							
Threshold Groupings	Pod 2: D15 - D8, Pod	1: D7 - D0						
Threshold Selections	TTL, ECL, CMOS (2.5	V, 3.3 V, 5 V), PECL, L\	/DS or User Defined					
Maximum Input Voltage	±30V Peak							
Threshold Accuracy	±(3% of threshold setting + 100mV)							
Input Dynamic Range	±20V							
Minimum Input Voltage Swing	400mV							
Input Impedance (Flying Leads)	100 kΩ 5 pF							
Maximum Input Frequency	250 MHz							
Sample Rate	1.25 GS/s							
Record Length	Standard STD: 25MS	S - 16 Channels						
		S - 16 Channels						
Minimum Detectable Pulse	optional El conte	1001141111010						
Width	2 ns							
Channel-to-Channel Skew	350ps							
User defined threshold range	±10V in 20mV steps							
User defined hysteresis range	±10V in 20mV steps 100 mV to 1.4 V in 100 mV steps							
Trigger System								
Modes	Auto, Normal, Single	Ston						
Sources			ne: slone and level ur	nique to each source	(except for line triage	or)		
Coupling	DC, AC, HFREJ, LFR		ic, siope and level un	inque to cacif soulce	(chocht for life trigge	·1 <i>J</i>		
Pre-trigger Delay	0-100% of full scale							
Post-trigger Delay	0-100% of full scale							
Hold-off	· · · · · · · · · · · · · · · · · · ·	2 1 000 000 000 000	ate.					
Internal Trigger Level Range		o 1,000,000,000 ever	11.5					
External Trigger Level Range	±4.1 Divisions							
	Ext: ±400mV, Ext/10		NITCO DAL OFOARA	LIDTV 700- 1000: 1	000m) Dunt Olaus D	+0		
Trigger Types			NTSC, PAL, SECAM, I Ilified (State or Edge)	HDTV–720p, 1080i, 1 I	υουρ <i>)</i> , κυπτ, Siew Ra	le,		

SPECIFICATIONS

HD04022

HD04024

HD04032

HD04034

HD04054



HD04104

HD04022-MS HD04024-MS HD04032-MS HD04034-MS HD04054-MS HD04104-MS Measure, Zoom and Math Tools Measurement Parameters Up to 8 of the following parameters can be calculated at one time on any waveform: Amplitude, Area, Base (Low), Delay, Delta Period @ Level, Delta Time @ Level, Duty, Duty @ Level, Edge @ Level, Fall Time (90%-10%), Fall Time (80%-20%), Frequency, Frequency @ level, Maximum, Mean, Minimum, Overshoot+, Overshoot-, Peak-Peak, Period, Period @ Level, Phase, Rise Time (10%-90%), Rise Time (20%-80%), RMS, Skew, Standard Deviation, Time @ Level, Top (High), Width+, Width-. Statistics and Histicons can be added to any measurement and all measurements can be gated. Use front panel QuickZoom button, or use touch screen or mouse to draw a box around the zoom area. Zooming Math Functions Functions include Sum. Difference. Product. Ratio. Absolute Value, Averaging (summed and continuous). Derivative, Envelope, Enhanced Resolution (to 15-bits), Floor, Integral, Invert, Reciprocal, Rescale (change scale and units), Roof, Square, Square Root, Trend, Zoom and FFT (up to 1 Mpts with power spectrum output and rectangular, VonHann, and FlatTop windows). 2 dual operator math functions may be defined at a time. **Probes** Standard Probes One PP017 (5mm) per channel One PP018(5mm) per channel Probing System BNC and Teledyne LeCroy ProBus for Active voltage, current and differential probes **Display System** 12.1" Wide TFT-LCD Touch-Screen Display Size Display Resolution 1280 x 800 Connectivity (2) 10/100/1000Base-T Ethernet interface (RJ-45 connector) Ethernet Port (6) USB Ports Total - (2) Front USB Ports **USB Host Ports USB Device Port** (1) USBTMC GPIB Port (Optional) Supports IEEE - 488.2 External Monitor Port Standard 15-pin D-Type SVGA-compatible DB-15 connector, DVI connector and HDMI connector Remote Control Via Windows Automation, or via Teledyne LeCroy Remote Command Set Processor/CPU Intel B810 Celeron processor 1.6 GHz or better Туре Processor Memory 4 GB Standard Operating System Windows Embedded Standard 7 64-Bit **Power Requirements** 100-240 VAC + 10% at 45-440 Hz; Automatic AC Voltage Selection Voltage Power Consumption (Nominal) 200 W / 200 VA Max Power Consumption Max Power Consumption 320 W / 320 VA (with all PC peripherals and active probes connected to 4 channels) **Environmental** Temperature Operating: 5 °C to 40 °C; Non-Operating: -20 °C to 60 °C Operating: 5% to 90% relative humidity (non-condensing) up to +31 °C, Upper limit derates to 50% relative humidity (non-Humidity condensing) at +40 °C; Non-Operating: 5% to 95% relative humidity (non-condensing) as tested per Operating: 3,048 m (10,000 ft) max at \leq 30C; Non-Operating: Up to 12,192 meters (40,000 ft) Altitude **Physical** Dimensions (HWD) 11.48"H x 15.72"W x 5.17"D (291.7 mm x 399.4 mm x 131.31 mm) Weight 5.86 kg (12.9 lbs) Regulatory CE Certification Low Voltage Directive 2006/95/EC EN 61010-1:2010, EN 61010-2-030:2010 EMC Directive 2004/108/EC EN 61326-1:2006. EN61326-2-1:2006 UL and cUL Listing UL 61010-1 (3rd Edition), UL 61010-2-030 (1st Edition) CAN/CSA C22.2 No.61010-1-12

ORDERING INFORMATION



Product Description	Product Code	Product Description	Product Code
HDO4000 Oscilloscopes		Software Options	
200 MHz, 2.5 GS/s, 2 Ch, 12.5 Mpts/Ch 12-bit HD	HD04022	Electrical Telecom Mask Test Package	HD04K-ET-PMT
Oscilloscope with 12.1" WXGA Touch Display	11001022		HD04K-SPECTRUM
200 MHz, 2.5 GS/s, 4 Ch, 12.5 Mpts/Ch 12-bit HD	HD04024	Power Analysis Option	HDO4K-PWR
Oscilloscope with 12.1" WXGA Touch Display 350 MHz, 2.5 GS/s, 2 Ch, 12.5 Mpts/Ch 12-bit HD	HD04032	Serial Data Options	
Oscilloscope with 12.1" WXGA Touch Display		ARINC 429 Symbolic Decode Option HDO4K-ARINC	C429bus DSymbolic
350 MHz, 2.5 GS/s, 4 Ch, 12.5 Mpts/Ch 12-bit HD Oscilloscope with 12.1" WXGA Touch Display	HD04034	Audiobus Trigger and Decode Option for HI I ² S, LJ, RJ, and TDM	DO4K-Audiobus TD
500 MHz, 2.5 GS/s, 4 Ch, 12.5 Mpts/Ch 12-bit HD	HD04054	CAN, LIN and FlexRay Trigger and Decode Option	HD04K-AUT0
Oscilloscope with 12.1" WXGA Touch Display	11004004		HD04K-CANbus TD
1 GHz, 2.5 GS/s, 4 Ch, 12.5 Mpts/Ch 12-bit HD	HD04104		HD04K-DPHYbus D
Oscilloscope with 12.1" WXGA Touch Display		<u> </u>	04K-DigRF3Gbus D
		· · · · · · · · · · · · · · · · · · ·	O4K-DigRFv4bus D
HDO4000-MS Mixed Signal Oscilloscopes			HDO4K-ENETbus D
200 MHz, 2.5 GS/s, 2+16ch, 12.5 Mpts/Ch 12-bit HD	HD04022-MS	· · · · · · · · · · · · · · · · · · ·	04K-FlexRaybus TD
Mixed Signal Oscilloscope w/ 12.1" WXGA Color Display		I ² C, SPI and UART Trigger and Decode Option	HD04K-EMB
200 MHz, 2.5 GS/s, 4+16ch, 12.5 Mpts/Ch 12-bit HD	HD04024-MS	I ² C Bus Trigger and Decode Option	HD04K-I2Cbus TD
Mixed Signal Oscilloscope w/ 12.1" WXGA Color Display			HD04K-LINbus TD
350 MHz, 2.5 GS/s, 2+16ch, 12.5 Mpts/Ch 12-bit HD	HD04032-MS		K-Manchesterbus D
Mixed Signal Oscilloscope w/ 12.1" WXGA Color Display		MIL-STD-1553 Trigger and Decode Option	HD04K-1553 TD
350 MHz, 2.5 GS/s, 4+16ch, 12.5 Mpts/Ch 12-bit HD	HD04034-MS		HD04K-NRZbus D
Mixed Signal Oscilloscope w/ 12.1" WXGA Color Display	11004054 140	<u> </u>	HDO4K-SENTbus D
500 MHz, 2.5 GS/s, 4+16ch, 12.5 Mpts/Ch 12-bit HD	HD04054-MS	<u> </u>	HD04K-SPIbus TD
Mixed Signal Oscilloscope w/ 12.1" WXGA Color Display	11004104 140		-UART-RS232bus TD
1 GHz, 2.5 GS/s, 4+16ch, 12.5 Mpts/Ch 12-bit HD	HD04104-MS		DO4K-USB2bus TD
Mixed Signal Oscilloscope w/ 12.1" WXGA Color Display			K-USB2-HSICbus D
÷10 Passive Probe (Total of 1 Per Channel), Getting Started Anti-virus Software (Trial Version), Microsoft Windows Eml 7 P 64-Bit License, Commercial NIST Traceable Calibration	pedded Standard with	250 MHz Passive Probe 10:1, 10 M Ω 500 MHz Passive Probe 10:1, 10 M Ω Set of 4 ZS1500, 1.5 GHz, 0.9 pF, 1 M Ω	PP017 PP018 ZS1500-QUADPAK
Certificate, Power Cable for the Destination Country, 3-year Included with HDO4000-MS	warranty	High Impedance Active Probe Set of 4 ZS1000, 1 GHz, 0.9 pF, 1 MΩ	ZS1000-QUADPAK
16 Channel Digital Leadset, Extra Large Gripper Probe Set (0)ty 22)	High Impedance Active Probe	Z31000-QUADFAK
Ground Extenders (Qty. 20), Flexible Ground Leads (Qty. 5)	Δ(y. ΔΔ),	200 MHz, 3.5 pF, 1 M Ω Active Differential Probe	ZD200
0.00.11.0 Externation (0.1). 20), 1.10.11.01.01.00 0.100.11.0 Ecoulo (0.1). 0)		500 MHz, 1.0 pF, 1 M Ω Active Differential Probe	ZD500
Memory Option		1 GHz, 1.0 pF, 1 MΩ Active Differential Probe	ZD1000
25 Mpts/ch (50 Mpts interleaved) memory	HD04K-L	1.5 GHz, 1.0 pF, 1 MΩ Active Differential Probe	ZD1500
		1,400 V, 100 MHz High-Voltage Differential Probe	ADP305
Hardware Options		1,400 V, 20 MHz High-Voltage Differential Probe	ADP300
Removable Hard Drive Package (includes removable hard drive kit and two hard drives)	HD04K-RHD	1 Ch, 100 MHz Differential Amplifier with Precision Voltage Source	DA1855A
Additional Removable Hard Drive	HDO4K-RHD-02	30 A; 100 MHz Current Probe – AC/DC; 30 A _{rms} ; 50 A _{peak} Pul	lse CP031
Canaval Assessanics		30 A; 50 MHz Current Probe – AC/DC; 30 A _{rms} ; 50 A _{beak} Pulse	
General Accessories	LICDA CDID	30 A; 50 MHz Current Probe – AC/DC; 30 A _{rms} ; 50 A _{peak} Pulse	
External GPIB Accessory	USB2-GPIB	150 A; 10 MHz Current Probe – AC/DC; 150 A _{rms} ; 500 A _{peak} F	
	DO4K-SOFTCASE	500 A; 2 MHz Current Probe – AC/DC; 500 A _{rms} ; 700 A _{peak} Pu	
Rack Mount Accessory	HD04K-RACK	Deskew Calibration Source for CP031, CP030 and AP015	DCS015
Accessory Pouch	HD04K-P0UCH	10:1/100:1 200/300 MHz, 50 MΩ High-voltage Probe 600 V/1,2 kV Max. Volt. DC	PPE1.2KV
Local Language Overlays	0.417 ED 0.557 1177	100:1 400 MHz 50 MΩ 2 kV High-voltage Probe	PPE2KV
	04K-FP-GERMAN	100:1 400 MHz 50 M Ω 4 kV High-voltage Probe	PPE4KV
	04K-FP-FRENCH	1000:1 400 MHz 50 MΩ 5 kV High-voltage Probe	PPE5KV
	DO4K-FP-ITALIAN	1000:1 400 MHz 50 MΩ 6 kV High-voltage Probe	PPE6KV
	04K-FP-SPANISH	. 113 100 12 00 IVILLO IXV Filight Voltage Frobe	I I LOIV
	4K-FP-JAPANESE		
	004K-FP-KOREAN		
	4K-FP-CHNES-TR		
	94K-FP-CHNES-SI		
Russian Front Panel Overlay HD0	04K-FP-RUSSIAN		

Customer Service Teledyne LeCroy oscilloscopes and probes are designed, built, and tested to ensure high reliability. In the unlikely event you experience difficulties, our digital oscilloscopes are fully warranted for three years and our probes are warranted for one year. This warranty includes: • No charge for return shipping • Long-term 7-year support • Upgrade to latest software at no charge

1-800-5-LeCroy

teledynelecroy.com

TELEDYNE LECROY Everywhereyoulook™ Local sales offices are located throughout the world.

Visit our website to find the most convenient location.