EM271



Multi-channel power analyzer



Description

Multi-load power analyzer for single or three-phase systems installable on panels or DIN rails.

Manages current input via two groups of split-core current sensors connected with RJ-11 connectors. The EM271 is equipped with a LCD display with controls to display measurements and configure the system, a RS485 port and two pulse outputs or two RS485 ports for daisy chain connections. Thanks to the SUM function, it also displays total load consumption values.

Benefits

- Reduced installation time and errors. Equipped with detachable terminals for all connections, with possibility of requesting pre-wired cables (optional). Connected to two groups of split-core current sensors with two cables fitted with RJ-11 connectors. For connections in cascade of multiple EM271s the voltage reference is required once only.
- Installation flexibility. It can be installed in new or existing single- and three-phase systems. Suitable for panel or DIN rail mounting.
- Granular analysis. It provides total measurements or single load measurements (up to 2 three-phase loads or up to 6 single-phase loads).
- Specific software. The UCS proprietary configuration software enables rapid configuration and the display of all measurements. The software and subsequent updates are free.
- **Tamper-proof.** Configuration access can be locked. The terminals and display can be sealed.
- Self detection of primary current of the TCDxM (the dedicated current transformers).

Applications

EM271 is connected directly to current sensors in switchboards for simultaneous monitoring of multiple singleor three-phase loads in low voltage systems.


Created for both commercial and industrial environments (e.g. data centers), this device guarantees quick and space-saving installations with just a few simple connections.

Suitable for retro-fit applications and for new installations where more flexibility is required.

Main functions

- · Measurement of energy consumption and main electrical variables of single- or three-phase loads.
- · Display of single load measurements and total measurements
- Transmission of data via serial communication.
- · Transmission of power consumption via pulse output (optional).

Architecture




Main features

- Up to 2 three-phase loads or 6 single-phase loads managed simultaneously.
- Up to 400 A input current via pre-cabled groups of current sensors (TCDxM) or any primary current of current up to 10000 A sensor with 0.333 V secondary output (via connection adapter TCDMM).
- Three installation configurations: on DIN rails, mounted on panel of 72 x 72 or 96 x 96 (with optional adapter)
- Single load measurements: V, A, W/VA/var, kWh, kvarh. Total load measurements: W/VA/var, kWh, kvarh.
- Display of electrical variables: 3 digits. Display of energy meters: 7 digits.
- · Accuracy: better than a combination of a class 1 meter and a class 0.5 current transformer.
- Easy connection function.
- Up to 20 EM271 connected in cascade.
- RS485 port.
- Optional outputs: additional RS485 port for chain connection or two pulse outputs.
- · Self power supply via voltage inputs.
- · Detachable terminals and sealable terminal caps.
- · Configuration via keypad or UCS configuration software.



Structure



Area	Description
Α	RJ-11 connector for connection to transformer block.
В	Power supply status LED.
С	Detachable voltage input terminals.
D	Area for mounting on DIN rail or for housing the LCD display in the case of panel mounting.
E	LCD display and controls.
F	LED that blinks with frequency proportional to active energy consumption, see "LED features".
G	Rotary selector to lock configuration.
Н	RS485 port terminals and pulse outputs.
I	Plastic protection cover or terminals for voltage connection in cascade.



Features

General

Material	Noryl, self-extinguishing V-0 (UL 94)	
Protection degree	Front: IP40, Terminals: IP20	
Terminals	Type: detachable Maximum section: 2.5 mm², Torque: 0.2/0.25 Nm	
Overvoltage category	Cat. III	
Pollution degree	2	
Noise rejection (CMRR)	100 dB, from 48 to 62 Hz	
Insulation	See "Input and output insulation"	
Mounting	DIN rail Panel 72 x 72, Panel 96 x 96 (with optional adapter)	
Weight	400 g (packaging included)	




Fig. 1 DIN rail

Fig. 2 Panel 72 x 72

Environmental specifications

Operating temperature	From -25 to +55 °C/from -13 to +131 °F
Storage temperature	From -30 to +70 °C/from -22 to +158 °F

NOTE: R.H. < 90 % non-condensing @ 40 °C / 104 °F.

Input and output insulation

Туре	Voltage input and self power supply	Current inputs	Pulse out- puts	RS485 port
Voltage input and self power supply	-	Reinforced *	Double **	Double **
Current inputs	Reinforced *	-	Double **	Double **
Pulse outputs	Double **	Double **	-	-
RS485 port	Double **	Double **	-	-

^{*}By limiting impedance

^{**2.5} kV ac 1 min (4 kV pk 1.2/50 μ S)+ limiting impedance



Conformity

Directives	2014/30/EU (Electro Magnetic Compatibility) 2011/65/EU (Electric-electronic equipment hazardous substances)
Standards	Electromagnetic compatibility (EMC) - emissions and immunity: EN62052-11 Electrical safety: EN61010-1 Pulse outputs: IEC62053-31, DIN43864 Metrology: EN62053-21, EN62053-23
Approvals	



Electrical specifications

Electrical system and loads

Managed electrical system	Single-phase (2-wire) Three-phase without neutral (3-wire) Three-phase with neutral (4-wire)
Number of loads man-	Single-phase systems: up to 6 single-phase loads
aged	Three-phase systems: up to 2 three-phase loads or up to 6 single-phase loads

Voltage inputs

	MV5	MV6	
Voltage connection	Direct or via VT		
Rated voltage L-N (from Un min to Un max)	From 160 to 240 V	From 57.7 to 133 V	
Rated voltage L-L (from Un min to Un max)	From 277 to 415 V	From 100 to 230 V	
Voltage tolerance	-10%, +10%		
Overload	Continuous: 1.2 Un max For 500 ms: 2 Un max		
Input impedance	1600 kΩ		
Frequency	From 45 to 65 Hz		

Current inputs

Current connection	Only via transformer block TCDxM or TCDMM
	60 A: TCD0M
	100 A: TCD1M
Rated current (In)	200 A: TCD2M
	400 A: TCD3M
	Up to 10000 A: TCDMM
Minimum current (Imin)	0.02 ln
Maximum current (Imax)	1.2 ln
Start-up current (Ist)	0.002 In
Overland	Continuous: 1.2 In
Overload	For 500 ms: 2 ln
Input impedance	< 0.2 VA





Power supply

Power supply	Self powered, between L2 and L3
Consumption	2 W, ≤ 4 VA



Measurements

Method	TRMS measurements of distorted waveforms
Sampling	1600 samples/s @50 Hz 1900 samples/s @60 Hz



Available measurements

Three-phase loads

Energy	Active imported
	Reactive imported
	Phase 1
Current	Phase 2
	Phase 3
Voltage	Phase-phase
voitage	Phase-neutral
	Total load
Active power	Average (dmd)
	Maximum dmd
	Total load
Apparent power	Average (dmd)
	Maximum dmd
Reactive power	Total load
Power factor	Total load

Single-phase loads

Energy	Active
Current	Phase
Voltage	Phase-neutral
	Total load
Active power	Average (dmd)
	Maximum dmd
Reactive power	Phase
Power factor	Phase





Measurement accuracy

EM271

	Current		
From 0.05 In to Imax	±(0.5% rdg)		
From 0.02 In to 0.05 In	±(1.0% rdg)		
	Phase-phase voltage		
From (Un min -10%) to (Un max +10%)	±(0.5% rdg)		
	Phase-neutral voltage		
From (Un min -10%) to (Un max +10%)	±(1% rdg)		
	Active power (PF=1)		
From 0.05 In to Imax	±(1% rdg)		
From 0.02 In to 0.05 In	±(1.5% rdg)		
	Active power (PF=0.5L, 0.8C)		
From 0.1 In to Imax	±(1% rdg)		
From 0.05 In to 0.1 In	±(1.5% rdg)		
	Reactive power (sinφ=1)		
From 0.05 In to Imax	±(2% rdg)		
From 0.02 In to 0.05 In	±(2.5% rdg)		
	Reactive power (sinφ=0.5 L or C)		
From 0.1 In to Imax	±(2% rdg)		
From 0.05 In to 0.1 In	±(2.5% rdg)		
Active energy			
Equivalent to class 1 (EN62053-21)			
Reactive energy			
Equivalent to class 2 (EN62053-23)			
Frequency			
From 45 to 65 Hz	±1 Hz		

EM271+TCD0M, TCD1M, TCD2M or TCD3M

Current			
From 0.2 In to Imax	±(0.75% rdg)		
From 0.05 to 0.2 In	±(1% rdg)		
From 0.02 In to 0.05 In	±(1.25% rdg)		
	Active power (PF=1)		
From 0.2 In to Imax	±(1.25% rdg)		
From 0.05 to 0.2 In	±(1.5% rdg)		
From 0.02 In to 0.05 In	±(2% rdg)		
	Reactive power (sinφ=1)		
From 0.2 In to Imax	±(2.25% rdg)		
From 0.05 to 0.2 In	±(2.5% rdg)		
From 0.02 In to 0.05 In	±(3% rdg)		





Display

Туре	LCD
Refresh time	1 s
	2 rows:
Description	1st: 7 digits (7 mm)
	2 nd : 3 digits (7 mm)
Variable readout	Electrical variables: 3 digits, min: 0.00, max: 999
variable readout	Energy meters: 7 digits, min: 0.0, max: 9 999 999



Digital outputs

Connection type	Detachable terminals	
Maximum number of	2	
outputs		
Туре	Opto-mosfet	
Function	Pulse output. Each output transmits the consumption of a single three-phase load or the total consumption of three single-phase loads.	
Features	V _{ON} : 2.5 V ac/dc, 70 mA max V _{OFF} : 40 V ac/dc max	
Configuration param-	Pulse weight (from 0.01 to 9.99 kWh per pulse)	
eters	Pulse duration (from 40 to 100 ms)	
Configuration mode	Via keypad or UCS software	



RS485 port

Protocol	Modbus RTU	
Protocol	Modbus KTO	
Devices on the same	Max 160 (1/5 unit load)	
bus	I Wax 100 (1/3 utilit load)	
Communication type	Multidrop, bidirectional	
Connection type	Detachable terminals, 2 wires, maximum distance 1000 m	
Configuration parameters	Modbus address (from 1 to 247)	
	Baud rate (9.6 / 19.2 / 38.4 kbps)	
eters	Parity (None / Even)	
Configuration mode	Via keypad or UCS software	



Special functions


- Display of total loads connected in relation to energy consumption and power measurements (SUM function)
- Measurements independent from direction of current (Easy connectionfunction)
- · Resetting of active energy meters of single and total loads
- · Resetting of maximum values within set active and apparent power interval
- · Password protected settings menu



Connection Diagrams

Note: for three-phase systems without neutral (3 wires) do not consider the connection to neutral **N**.

Note: fuses F of 315 mA, if required by local law.






Fig. 3 Three-phase system, one three-phase load.

Fig. 4 Three-phase system, three single-phase loads.

Fig. 5 Three-phase system, two three-phase loads.




Fig. 6 Three-phase system, six single-phase loads.




Fig. 7 One-phase system, three single-phase loads.




Fig. 8 One-phase system, six single-phase loads.




Fig. 9 Example of connection of multiple EM271s in cascade.




Fig. 10 Pulse output 1.




Fig. 11 Pulse output 2.






Fig. 12 RS485 port.

Fig. 13 Double RS485 port for daisy chain connection.



References

Order code

F EM271 72D MV □ 3X □ □ (16 total characters)

Enter the code, replacing the symbol \square with the selected option (e.g.: EM271 72D MV5 3X **O**S **X**).

Code	Options	Description
E	-	-
M	-	-
2	-	-
7	-	-
1	-	-
7	-	-
2	-	-
D	-	-
M	-	-
V	-	-
	5	230 V L-N, 400 V L-L ac, connection via TCD_M or TCDMM
	6	120 V L-N, 230 V L-L ac, connection via TCD_M or TCDMM
3	-	-
X	-	-
	os	RS485 port and double digital output
	28	Double RS485 port for daisy chain connection
	Х	Standard configuration
	N	"Naked" configuration. With respect to the standard configuration, the "naked" version does NOT include: detachable terminals for voltage connections, detachable terminals for daisy chain connection via RS485 port (only for option 25).

Accessories: order codes

Code	Options	Description
EM270WS V 1T	Replacing the symbol \square with the cable length. Lengths available: 30 , 60 , 90 , 150 , 200 cm.	Pre-wired cables for voltage connection (one terminal block).
EM270WS V 2T	Replacing the symbol \square with the cable length. Lengths available: 30 , 60 , 90 , 150 , 200 cm.	Pre-wired cables for voltage connection (two terminal blocks).
EM270WS S 2T	Replacing the symbol \square with the cable length. Lengths available: 60 , 90 , 120 , 180 , 230 cm.	Pre-wired cables for RS485 connection (two terminal blocks).
EM270WS T V	-	20 detachable terminal blocks for voltage connections.
EM270WS T C	-	20 plastic protection covers for voltage output.
EM270WS T S	-	20 detachable terminal blocks for daisy chain connection of RS485 port.
7296ADAPTER	-	Adapter to 96 x 96 panel mounting.





Further reading

Information	Document	Where to find it
Instruction manual	Instruction manual - EM271	www.productselection.net



CARLO GAVAZZI compatible components

Purpose	Component name/code key	Notes
	TCD0M	
	TCD1M	
Current measurement accessories (mandatory)	TCD2M	See next chapter
	TCD3M	
	TCDMM	
Configure analyzer via desktop application	LICS configuration coftware	Available for free download at:
Configure analyzer via desktop application	UCS configuration software	www.productselection.net
Monitor data from several analyzers	VMU-C EM	See relevant datasheet

TCD_M family



TCD0M, TCD1M, TCD2M, TCD3M for EM271



Main features

- 3 split core current sensors
- Primary current from 60 A to 400 A (depends on the model)
- Hole diameter from 9.6 mm to 20.5 mm (depends on the model)
- Connection to the EM271 with cable with RJ-11 connector
- DIN rail mounting
- · Self primary current detection

Description

3-channel split core current transformer block for power analyzer EM271.


It manages primary current from 60 A to 400 A (depends on the model) and the value is read automatically by the EM271 to eliminate the need for configuration and calibration by the user.

It is equipped with RJ-11 connectors for simple connection to the EM271.

Main functions

Conversion of current for input to the power analyzer EM271.

Structure



Area	Description
Α	Integrator
В	Cable with RJ-11 connectors for connection to the EM271
С	Split core current sensors



Features

General

Material	PC, PA66
Protection degree	IP20
Terminals	RJ-11 connector
Overvoltage category	Cat. III
Pollution degree	2
Insulation	60s 1500 V ac (RJ connectors to housing)
Mounting	DIN rail
	TCD0M: 290 g
Weight (packaging	TCD1M: 360 g
included)	TCD2M: 535 g
	TCD3M: 885 g






Fig. 14 Integrator (mm)




Fig. 15 TCD0M (mm)




Fig. 17 TCD2M (mm)




Fig. 16 TCD1M (mm)




Fig. 18 *TCD3M (mm)*



Environmental specifications

Operating temperature	From -40 to +65 °C/from -40 to +149 °F
Storage temperature	From -40 to +65 °C/from -40 to +149 °F

Electrical specifications

Primary current (In)	60 A: TCD0M 100 A: TCD1M 200 A: TCD2M 400 A: TCD3M	
Maximum current (continuous)	1.2 ln	
Maximum system voltage	0.72 kV ac	
Frequency	From 45 to 65 Hz	
Accuracy	0.5%	
Phase error	≤4°	

Connection Diagrams




Fig. 19 Current connection




Fig. 20 RJ11 connections



References

Order code

7 TCD □ □ 80 CM X

Enter the code, replacing the symbol \square with the selected option (e.g.: TCD 0 M 60 80 CM X)

Code	Options	Description
Т		-
С		-
D		-
	0M60	60 A Primary current
	1M100	100 A Primary current
	2M200	200 A Primary current
	3M400	400 A Primary current
8		-
0		-
С		-
M		-
X		-

Further reading

Information	Document	Where to find it
Instruction manual	Instruction manual - TCD_M	www.productselection.net

CARLO GAVAZZI compatible components

Purpose	Component name/code key	Notes
Measure and display consumption of connected loads	EM271	-

TCDMM



3-phase adapter for EM271



Main features

- Suitable for 3 current sensors (0.333 V)
- · Primary current up to 10000 A
- · Connection to the EM271 with cable with RJ-11 connector
- DIN rail mounting
- Screwless terminals

Main functions


 Conversion of current for input to the power analyzer EM271.

Description

3-phase adapter for power analyzer EM271. This manages 3 current sensor (0.333 V output) and the primary value is set by the user via keypad or via software.

It is equipped with RJ-11 connectors for simple connection to the EM271.

Structure




Area	Description
Α	Integrator
В	Push-in wire connector
С	Cable with RJ-11 connectors for connection to the EM271




Features

General

Material	PC, PA66
Protection degree	IP20
Terminals	RJ-11 connector
Overvoltage category	Cat. III
Pollution degree	2
Mounting	DIN rail
Weight (packaging included)	80 g





Environmental specifications

Operating temperature	From -40 to +65 °C/from -40 to +149 °F
Storage temperature	From -40 to +65 °C/from -40 to +149 °F

Electrical specifications

Primary current (In)	3x 0.333V
Maximum current (continuous)	1.2 ln
Maximum system voltage	0.72 kV ac
Frequency	From 45 to 65 Hz



Connection Diagrams




Fig. 22 Current connection




Fig. 23 RJ11 connections

References



Order code



TCDMM XXX 80CM X



Further reading

Information	Document	Where to find it
Instruction manual	Instruction manual - TCDxM	www.productselection.net



CARLO GAVAZZI compatible components

Purpose	Component name/code key	Notes
Measure and display consumption of connected loads	EM271	-
Current sensors 0.333 V secondary output	CTV1X, CTV2X, CTV3X, CTV4X, CTV8X	-



COPYRIGHT ©2017

Content subject to change. Download the PDF: www.productselection.net